

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934088

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934088
REPORT IS A COMBINATION OF REPORTS P933683 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6786.6 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12776	12776	12776	12776
5°	12867	12897	12867	10141
10°	12776	12704	12776	9082
15°	12633	12429	12633	10379
20°	12364	12103	12364	10400
25°	11818	11627	11818	10180
30°	11115	11232	11115	9696
35°	9904	10732	9904	9164
40°	8248	10145	8248	8762
45°	7364	9457	7364	8300
50°	7817	8636	7817	7837
55°	7349	7752	7349	7568
60°	7566	6583	7566	6932
65°	6849	5442	6849	6083
70°	4730	4337	4730	5099
75°	4134	3205	4134	3840
80°	3307	2120	3307	2308
85°	1866	1123	1866	955

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 11295 cd/sqm

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.7
10°-20°	529.3	7.8
20°-30°	818.2	12.1
30°-40°	976.8	14.4
40°-50°	982.5	14.5
50°-60°	854.9	12.6
60°-70°	606.1	8.9
70°-80°	320.7	4.7
80°-90°	80.7	1.2
90°-100°	107.6	1.6
100°-110°	282.9	4.2
110°-120°	293.3	4.3
120°-130°	235.3	3.5
130°-140°	184.6	2.7
140°-150°	141.7	2.1
150°-160°	102.0	1.5
160°-170°	62.4	0.9
170°-180°	21.1	0.3
0°-30°	1534.0	22.6
0°-40°	2510.8	37.0
0°-60°	4348.3	64.1
0°-90°	5355.8	78.9
90°-120°	683.7	10.1
90°-150°	1245.2	18.3
90°-180°	1431.0	21.1
0°-180°	6786.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2065	2065	2065	2065	2065	
5°	2075	2140	2075	1682	2075	197
15°	1981	2120	1981	1770	1981	557
25°	1745	1977	1745	1731	1745	801
35°	1327	1764	1327	1506	1327	821
45°	856	1454	856	1276	856	686
55°	698	1073	698	1047	698	641
65°	485	647	485	723	485	463
75°	184	307	184	367	184	193
85°	31	78	31	66	31	42
90°	2	6	2	6	2	3
95°	14	65	14	65	14	16
105°	51	443	51	443	51	54
115°	90	570	90	570	90	89
125°	126	454	126	454	126	112
135°	150	352	150	352	150	116
145°	174	286	174	286	174	109
155°	197	246	197	246	197	90
165°	212	229	212	229	212	60
175°	221	222	221	222	221	21
180°	221	221	221	221	221	

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3
2.5°	2082.9	2082.9	2094.7	2098.5	2098.5	2092.7	2086.8	2092.7	2110.2	2116.2	2114.2
5°	2075.0	2090.7	2112.2	2116.2	2120.0	2118.0	2114.2	2118.0	2137.5	2141.5	2143.5
7.5°	2059.5	2088.7	2116.2	2122.0	2127.8	2122.0	2120.0	2123.9	2143.5	2147.4	2147.4
10°	2039.9	2081.0	2112.2	2116.2	2122.0	2116.2	2116.2	2123.9	2143.5	2147.4	2149.3
12.5°	2012.5	2069.2	2098.5	2102.4	2110.2	2108.3	2106.3	2114.2	2133.7	2137.5	2137.5
15°	1981.3	2047.7	2075.0	2079.0	2092.7	2088.7	2088.7	2096.5	2118.0	2123.9	2122.0
17.5°	1938.3	2020.3	2051.7	2057.5	2067.2	2065.3	2067.2	2075.0	2094.7	2098.5	2100.5
20°	1889.5	1983.2	2020.3	2026.2	2036.0	2036.0	2036.0	2045.8	2065.3	2073.2	2073.2
22.5°	1823.0	1944.2	1983.2	1987.2	1998.9	1998.9	2002.8	2016.5	2034.0	2036.0	2036.0
25°	1744.8	1901.2	1934.4	1946.1	1957.8	1963.7	1969.5	1977.4	1983.2	1981.3	1983.2
27.5°	1662.8	1846.5	1889.5	1897.3	1912.9	1918.8	1926.5	1928.5	1930.5	1936.3	1932.5
30°	1571.0	1770.3	1834.7	1842.5	1868.0	1871.8	1864.0	1868.0	1877.7	1881.7	1885.5
32.5°	1467.4	1657.0	1778.1	1795.7	1819.1	1807.3	1805.5	1811.3	1827.0	1827.0	1830.8
35°	1326.8	1569.0	1725.3	1741.0	1758.5	1744.8	1752.7	1754.6	1764.3	1770.3	1768.3
37.5°	1172.4	1492.8	1670.6	1682.3	1696.0	1678.5	1690.1	1696.0	1703.8	1700.0	1700.0
40°	1035.6	1373.6	1606.1	1614.0	1625.7	1612.0	1623.7	1627.6	1631.5	1627.6	1625.7
42.5°	933.9	1242.7	1537.8	1547.5	1539.7	1549.5	1553.3	1561.2	1555.3	1547.5	1547.5
45°	855.8	1207.6	1463.5	1475.3	1463.5	1479.1	1485.0	1485.0	1467.4	1463.5	1461.5
47.5°	830.4	1137.2	1389.3	1389.3	1383.4	1402.9	1412.6	1399.0	1381.4	1375.6	1375.6
50°	828.4	1059.1	1287.6	1279.8	1307.1	1330.6	1320.8	1307.1	1293.5	1272.0	1272.0
52.5°	752.2	963.3	1156.7	1186.1	1229.0	1242.7	1227.1	1213.4	1189.9	1180.1	1172.4
55°	697.6	863.6	1037.6	1096.1	1141.1	1158.6	1129.4	1115.7	1080.6	1074.6	1070.8
57.5°	685.9	719.1	928.1	1002.4	1057.1	1055.1	1037.6	1012.1	982.8	976.9	975.1
60°	629.2	519.7	810.9	898.8	955.4	949.6	933.9	910.6	883.2	879.3	875.4
62.5°	570.5	377.1	678.0	777.7	857.8	855.8	842.1	806.9	787.4	777.7	769.9
65°	484.6	316.5	482.6	646.7	762.1	765.9	736.6	711.2	689.7	678.0	676.1
67.5°	369.3	257.9	326.3	539.2	670.2	666.3	629.2	617.4	590.1	584.2	572.5
70°	273.5	172.0	226.7	437.7	580.4	570.5	541.2	527.6	502.2	488.5	480.7
72.5°	226.7	138.7	166.0	340.0	488.5	476.7	451.4	435.7	414.2	402.5	394.7
75°	183.7	146.5	127.0	252.0	396.7	388.9	365.4	349.7	332.2	316.5	318.5
77.5°	134.8	136.8	101.6	185.7	314.5	302.9	289.2	269.7	261.8	246.2	246.2
80°	101.6	107.5	76.2	127.0	226.7	226.7	214.9	201.2	187.5	179.7	179.7
82.5°	68.4	68.4	56.7	80.1	154.4	148.5	140.7	136.8	129.0	125.0	125.0
85°	31.3	39.0	35.2	48.8	84.0	88.0	88.0	84.0	82.0	78.2	80.1
87.5°	9.8	17.6	21.5	27.3	43.0	45.0	46.9	46.9	46.9	48.8	48.8
90°	1.5	2.7	3.8	4.1	6.5	9.7	11.2	10.0	7.5	5.6	5.6
92.5°	5.9	16.0	26.0	28.6	40.2	55.7	63.4	55.5	39.8	28.1	27.0
95°	14.2	32.6	51.1	55.7	98.9	156.5	185.3	165.4	125.4	95.5	92.2
97.5°	24.6	40.8	57.1	61.1	133.2	229.2	277.3	264.6	239.5	220.6	214.2
100°	32.6	47.3	62.1	65.8	145.7	252.3	305.6	306.4	308.3	309.7	302.0
102.5°	39.4	53.2	66.9	70.4	151.4	259.5	313.5	329.6	361.8	385.9	379.3
105°	51.0	62.6	74.2	77.2	155.7	260.3	312.7	348.6	420.7	474.8	471.2
107.5°	62.8	73.7	84.5	87.3	156.5	248.8	294.9	345.2	445.7	521.0	521.9
110°	70.8	80.7	90.4	92.9	155.3	238.5	280.1	336.3	448.6	532.8	536.5

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	78.7	88.0	97.3	99.7	155.3	229.5	266.6	324.1	439.1	525.2	530.9
115°	90.5	99.2	107.8	109.9	156.8	219.2	250.4	305.9	416.6	499.6	507.5
117.5°	102.2	110.0	117.8	119.8	159.6	212.8	239.4	289.4	389.3	464.2	472.9
120°	109.1	116.4	123.7	125.6	162.1	210.7	235.0	280.6	371.9	440.4	448.9
122.5°	115.7	123.2	130.5	132.4	165.5	209.5	231.5	272.6	354.9	416.6	425.0
125°	125.9	132.7	139.5	141.2	170.1	208.6	227.9	262.8	332.7	385.0	392.7
127.5°	134.2	141.0	147.9	149.6	174.6	208.0	224.7	254.7	314.7	359.7	366.2
130°	138.6	146.0	153.3	155.2	178.0	208.3	223.5	250.2	303.6	343.6	349.6
132.5°	143.3	150.7	158.0	159.8	180.7	208.6	222.5	246.4	294.2	330.0	335.3
135°	150.1	156.8	163.5	165.2	183.7	208.4	220.8	240.8	280.8	310.8	315.4
137.5°	157.1	163.7	170.3	172.0	188.1	209.7	220.5	237.4	271.2	296.6	300.3
140°	162.8	168.9	175.0	176.6	190.9	209.9	219.4	234.0	263.3	285.2	288.7
142.5°	167.2	172.8	178.6	179.9	193.1	210.6	219.4	232.2	257.9	277.2	280.2
145°	174.0	179.0	183.9	185.2	196.1	210.6	217.9	228.4	249.4	265.1	267.4
147.5°	180.8	185.7	190.5	191.7	200.5	212.1	217.9	226.2	242.7	255.1	257.0
150°	185.3	189.6	194.0	195.1	202.7	212.9	217.9	224.9	238.8	249.3	250.8
152.5°	189.9	193.2	196.5	197.3	204.2	213.4	217.9	223.8	235.8	244.7	245.9
155°	196.7	199.2	201.6	202.2	207.5	214.5	217.9	222.6	232.1	239.2	240.0
157.5°	201.7	204.1	206.5	207.1	210.7	215.5	217.9	221.6	228.9	234.5	235.1
160°	205.2	207.1	208.8	209.3	212.2	216.0	217.9	221.1	227.4	232.1	232.4
162.5°	208.5	209.9	211.3	211.7	213.8	216.5	217.9	220.6	225.9	229.9	230.2
165°	212.3	213.5	214.8	215.0	216.0	217.3	217.9	219.8	223.6	226.5	226.8
167.5°	215.6	216.2	216.8	217.0	217.8	218.9	219.4	220.7	223.1	225.0	225.1
170°	217.9	218.5	219.1	219.2	219.3	219.4	219.4	220.7	223.1	225.0	225.0
172.5°	219.1	219.2	219.4	219.4	219.4	219.4	219.4	220.4	222.3	223.8	223.7
175°	220.8	220.8	220.8	220.8	220.3	219.7	219.4	220.0	221.3	222.2	222.2
177.5°	220.8	220.8	220.8	220.8	220.4	219.9	219.7	220.2	221.2	221.9	221.8
180°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3
2.5°	2118.0	2112.2	2118.0	2114.2	2116.2	2110.2	2092.7	2086.8	2092.7	2098.5	2098.5
5°	2143.5	2139.5	2143.5	2143.5	2141.5	2137.5	2118.0	2114.2	2118.0	2120.0	2116.2
7.5°	2151.3	2145.4	2151.3	2147.4	2147.4	2143.5	2123.9	2120.0	2122.0	2127.8	2122.0
10°	2151.3	2145.4	2151.3	2149.3	2147.4	2143.5	2123.9	2116.2	2116.2	2122.0	2116.2
12.5°	2141.5	2137.5	2141.5	2137.5	2137.5	2133.7	2114.2	2106.3	2108.3	2110.2	2102.4
15°	2125.9	2120.0	2125.9	2122.0	2123.9	2118.0	2096.5	2088.7	2088.7	2092.7	2079.0
17.5°	2102.4	2094.7	2102.4	2100.5	2098.5	2094.7	2075.0	2067.2	2065.3	2067.2	2057.5
20°	2075.0	2069.2	2075.0	2073.2	2073.2	2065.3	2045.8	2036.0	2036.0	2036.0	2026.2
22.5°	2032.0	2026.2	2032.0	2036.0	2036.0	2034.0	2016.5	2002.8	1998.9	1998.9	1987.2
25°	1983.2	1977.4	1983.2	1983.2	1981.3	1983.2	1977.4	1969.5	1963.7	1957.8	1946.1
27.5°	1936.3	1932.5	1936.3	1932.5	1936.3	1930.5	1928.5	1926.5	1918.8	1912.9	1897.3
30°	1889.5	1885.5	1889.5	1885.5	1881.7	1877.7	1868.0	1864.0	1871.8	1868.0	1842.5
32.5°	1830.8	1827.0	1830.8	1830.8	1827.0	1827.0	1811.3	1805.5	1807.3	1819.1	1795.7
35°	1770.3	1764.3	1770.3	1768.3	1770.3	1764.3	1754.6	1752.7	1744.8	1758.5	1741.0
37.5°	1700.0	1694.0	1700.0	1700.0	1700.0	1703.8	1696.0	1690.1	1678.5	1696.0	1682.3
40°	1627.6	1619.8	1627.6	1625.7	1627.6	1631.5	1627.6	1623.7	1612.0	1625.7	1614.0
42.5°	1545.6	1543.6	1545.6	1547.5	1547.5	1555.3	1561.2	1553.3	1549.5	1539.7	1547.5
45°	1457.6	1453.8	1457.6	1461.5	1463.5	1467.4	1485.0	1485.0	1479.1	1463.5	1475.3
47.5°	1363.8	1354.1	1363.8	1375.6	1375.6	1381.4	1399.0	1412.6	1402.9	1383.4	1389.3
50°	1264.2	1266.1	1264.2	1272.0	1272.0	1293.5	1307.1	1320.8	1330.6	1307.1	1279.8
52.5°	1166.5	1164.6	1166.5	1172.4	1180.1	1189.9	1213.4	1227.1	1242.7	1229.0	1186.1
55°	1068.8	1072.7	1068.8	1070.8	1074.6	1080.6	1115.7	1129.4	1158.6	1141.1	1096.1
57.5°	971.1	965.2	971.1	975.1	976.9	982.8	1012.1	1037.6	1055.1	1057.1	1002.4
60°	857.8	849.9	857.8	875.4	879.3	883.2	910.6	933.9	949.6	955.4	898.8
62.5°	758.1	744.4	758.1	769.9	777.7	787.4	806.9	842.1	855.8	857.8	777.7
65°	652.6	646.7	652.6	676.1	678.0	689.7	711.2	736.6	765.9	762.1	646.7
67.5°	556.9	556.9	556.9	572.5	584.2	590.1	617.4	629.2	666.3	670.2	539.2
70°	468.9	467.0	468.9	480.7	488.5	502.2	527.6	541.2	570.5	580.4	437.7
72.5°	384.9	383.0	384.9	394.7	402.5	414.2	435.7	451.4	476.7	488.5	340.0
75°	310.7	306.7	310.7	318.5	316.5	332.2	349.7	365.4	388.9	396.7	252.0
77.5°	238.4	238.4	238.4	246.2	246.2	261.8	269.7	289.2	302.9	314.5	185.7
80°	177.8	175.9	177.8	179.7	179.7	187.5	201.2	214.9	226.7	226.7	127.0
82.5°	125.0	121.2	125.0	125.0	125.0	129.0	136.8	140.7	148.5	154.4	80.1
85°	78.2	78.2	78.2	80.1	78.2	82.0	84.0	88.0	88.0	84.0	48.8
87.5°	50.8	48.8	50.8	48.8	48.8	46.9	46.9	46.9	45.0	43.0	27.3
90°	5.6	5.6	5.6	5.6	5.6	7.5	10.0	11.2	9.7	6.5	4.1
92.5°	22.5	18.0	22.5	27.0	28.1	39.8	55.5	63.4	55.7	40.2	28.6
95°	78.6	65.1	78.6	92.2	95.5	125.4	165.4	185.3	156.5	98.9	55.7
97.5°	188.3	162.5	188.3	214.2	220.6	239.5	264.6	277.3	229.2	133.2	61.1
100°	271.3	240.6	271.3	302.0	309.7	308.3	306.4	305.6	252.3	145.7	65.8
102.5°	353.0	326.7	353.0	379.3	385.9	361.8	329.6	313.5	259.5	151.4	70.4
105°	457.1	442.9	457.1	471.2	474.8	420.7	348.6	312.7	260.3	155.7	77.2
107.5°	525.2	528.7	525.2	521.9	521.0	445.7	345.2	294.9	248.8	156.5	87.3
110°	551.3	566.1	551.3	536.5	532.8	448.6	336.3	280.1	238.5	155.3	92.9

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	553.5	576.2	553.5	530.9	525.2	439.1	324.1	266.6	229.5	155.3	99.7
115°	538.8	570.3	538.8	507.5	499.6	416.6	305.9	250.4	219.2	156.8	109.9
117.5°	507.8	542.6	507.8	472.9	464.2	389.3	289.4	239.4	212.8	159.6	119.8
120°	482.7	516.6	482.7	448.9	440.4	371.9	280.6	235.0	210.7	162.1	125.6
122.5°	458.3	491.6	458.3	425.0	416.6	354.9	272.6	231.5	209.5	165.5	132.4
125°	423.4	454.2	423.4	392.7	385.0	332.7	262.8	227.9	208.6	170.1	141.2
127.5°	392.1	418.1	392.1	366.2	359.7	314.7	254.7	224.7	208.0	174.6	149.6
130°	373.6	397.6	373.6	349.6	343.6	303.6	250.2	223.5	208.3	178.0	155.2
132.5°	356.8	378.3	356.8	335.3	330.0	294.2	246.4	222.5	208.6	180.7	159.8
135°	333.9	352.4	333.9	315.4	310.8	280.8	240.8	220.8	208.4	183.7	165.2
137.5°	315.5	330.6	315.5	300.3	296.6	271.2	237.4	220.5	209.7	188.1	172.0
140°	302.8	317.0	302.8	288.7	285.2	263.3	234.0	219.4	209.9	190.9	176.6
142.5°	292.3	304.6	292.3	280.2	277.2	257.9	232.2	219.4	210.6	193.1	179.9
145°	276.7	285.9	276.7	267.4	265.1	249.4	228.4	217.9	210.6	196.1	185.2
147.5°	264.6	272.2	264.6	257.0	255.1	242.7	226.2	217.9	212.1	200.5	191.7
150°	257.1	263.3	257.1	250.8	249.3	238.8	224.9	217.9	212.9	202.7	195.1
152.5°	250.5	255.3	250.5	245.9	244.7	235.8	223.8	217.9	213.4	204.2	197.3
155°	243.0	246.2	243.0	240.0	239.2	232.1	222.6	217.9	214.5	207.5	202.2
157.5°	237.2	239.4	237.2	235.1	234.5	228.9	221.6	217.9	215.5	210.7	207.1
160°	233.7	235.0	233.7	232.4	232.1	227.4	221.1	217.9	216.0	212.2	209.3
162.5°	231.4	232.6	231.4	230.2	229.9	225.9	220.6	217.9	216.5	213.8	211.7
165°	228.1	229.3	228.1	226.8	226.5	223.6	219.8	217.9	217.3	216.0	215.0
167.5°	225.7	226.2	225.7	225.1	225.0	223.1	220.7	219.4	218.9	217.8	217.0
170°	225.0	225.0	225.0	225.0	225.0	223.1	220.7	219.4	219.4	219.3	219.2
172.5°	223.2	222.8	223.2	223.7	223.8	222.3	220.4	219.4	219.4	219.4	219.4
175°	222.2	222.2	222.2	222.2	222.2	221.3	220.0	219.4	219.7	220.3	220.8
177.5°	221.3	220.8	221.3	221.8	221.9	221.2	220.2	219.7	219.9	220.4	220.8
180°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3
2.5°	2094.7	2082.9	2082.9	2063.3	2055.5	2049.7	2039.9	2010.6	2002.8	1995.0	2006.7
5°	2112.2	2090.7	2075.0	2039.9	2010.6	1998.9	1961.7	1891.4	1844.5	1809.3	1789.8
7.5°	2116.2	2088.7	2059.5	2004.7	1934.4	1903.1	1789.8	1660.8	1625.7	1594.4	1574.8
10°	2112.2	2081.0	2039.9	1957.8	1791.8	1737.0	1623.7	1539.7	1518.2	1512.3	1518.2
12.5°	2098.5	2069.2	2012.5	1875.8	1643.3	1606.1	1539.7	1490.8	1487.0	1496.7	1549.5
15°	2075.0	2047.7	1981.3	1766.3	1561.2	1533.8	1487.0	1469.3	1490.8	1559.3	1717.5
17.5°	2051.7	2020.3	1938.3	1658.8	1498.6	1479.1	1445.9	1481.1	1602.2	1694.0	1746.8
20°	2020.3	1983.2	1889.5	1580.8	1453.8	1436.1	1420.5	1578.8	1670.6	1703.8	1733.1
22.5°	1983.2	1944.2	1823.0	1526.0	1406.8	1393.1	1402.9	1633.5	1670.6	1694.0	1719.5
25°	1934.4	1901.2	1744.8	1483.0	1369.8	1354.1	1391.2	1627.6	1649.1	1655.0	1705.8
27.5°	1889.5	1846.5	1662.8	1444.0	1324.8	1318.9	1401.0	1602.2	1617.8	1623.7	1678.5
30°	1834.7	1770.3	1571.0	1402.9	1277.9	1275.9	1402.9	1571.0	1567.0	1582.7	1637.4
32.5°	1778.1	1657.0	1467.4	1352.1	1232.9	1231.0	1389.3	1524.1	1520.1	1541.6	1582.7
35°	1725.3	1569.0	1326.8	1293.5	1176.3	1178.2	1356.0	1469.3	1471.3	1490.8	1516.3
37.5°	1670.6	1492.8	1172.4	1229.0	1121.6	1121.6	1311.1	1418.6	1414.6	1420.5	1455.6
40°	1606.1	1373.6	1035.6	1145.0	1070.8	1064.9	1256.4	1363.8	1350.1	1348.3	1397.1
42.5°	1537.8	1242.7	933.9	1033.6	1012.1	1004.3	1189.9	1297.4	1272.0	1277.9	1340.4
45°	1463.5	1207.6	855.8	873.4	951.6	945.7	1117.6	1221.2	1203.6	1219.3	1283.8
47.5°	1389.3	1137.2	830.4	724.9	887.1	885.1	1037.6	1146.9	1137.2	1152.8	1221.2
50°	1287.6	1059.1	828.4	621.4	814.8	822.6	941.8	1074.6	1074.6	1088.3	1160.6
52.5°	1156.7	963.3	752.2	562.7	730.7	754.2	857.8	1012.1	1016.1	1029.7	1094.2
55°	1037.6	863.6	697.6	517.7	631.1	681.9	775.7	947.6	955.4	969.1	1027.8
57.5°	928.1	719.1	685.9	465.0	539.2	588.1	703.4	885.1	889.1	900.8	957.4
60°	810.9	519.7	629.2	408.4	459.2	496.3	637.0	810.9	824.6	832.4	881.2
62.5°	678.0	377.1	570.5	369.3	420.1	427.9	582.2	740.6	758.1	764.0	793.3
65°	482.6	316.5	484.6	336.0	379.0	381.0	523.7	668.2	683.9	693.7	715.1
67.5°	326.3	257.9	369.3	304.8	347.8	349.7	467.0	584.2	605.7	613.5	627.2
70°	226.7	172.0	273.5	271.6	312.7	316.5	406.4	508.0	527.6	533.4	541.2
72.5°	166.0	138.7	226.7	244.2	275.5	279.4	343.9	422.0	441.6	447.4	451.4
75°	127.0	146.5	183.7	213.0	234.5	236.4	281.4	343.9	357.5	361.5	363.4
77.5°	101.6	136.8	134.8	172.0	191.5	187.5	220.8	265.7	277.5	277.5	277.5
80°	76.2	107.5	101.6	123.1	140.7	136.8	158.3	189.5	193.5	197.3	195.4
82.5°	56.7	68.4	68.4	78.2	93.8	89.9	105.5	123.1	123.1	123.1	127.0
85°	35.2	39.0	31.3	41.0	52.8	50.8	58.7	66.5	68.4	68.4	64.5
87.5°	21.5	17.6	9.8	15.7	23.5	23.5	27.3	29.3	27.3	27.3	27.3
90°	3.8	2.7	1.5	2.7	3.8	4.1	6.5	9.7	11.2	10.0	7.5
92.5°	26.0	16.0	5.9	16.0	26.0	28.6	40.2	55.7	63.4	55.5	39.8
95°	51.1	32.6	14.2	32.6	51.1	55.7	98.9	156.5	185.3	165.4	125.4
97.5°	57.1	40.8	24.6	40.8	57.1	61.1	133.2	229.2	277.3	264.6	239.5
100°	62.1	47.3	32.6	47.3	62.1	65.8	145.7	252.3	305.6	306.4	308.3
102.5°	66.9	53.2	39.4	53.2	66.9	70.4	151.4	259.5	313.5	329.6	361.8
105°	74.2	62.6	51.0	62.6	74.2	77.2	155.7	260.3	312.7	348.6	420.7
107.5°	84.5	73.7	62.8	73.7	84.5	87.3	156.5	248.8	294.9	345.2	445.7
110°	90.4	80.7	70.8	80.7	90.4	92.9	155.3	238.5	280.1	336.3	448.6

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	97.3	88.0	78.7	88.0	97.3	99.7	155.3	229.5	266.6	324.1	439.1
115°	107.8	99.2	90.5	99.2	107.8	109.9	156.8	219.2	250.4	305.9	416.6
117.5°	117.8	110.0	102.2	110.0	117.8	119.8	159.6	212.8	239.4	289.4	389.3
120°	123.7	116.4	109.1	116.4	123.7	125.6	162.1	210.7	235.0	280.6	371.9
122.5°	130.5	123.2	115.7	123.2	130.5	132.4	165.5	209.5	231.5	272.6	354.9
125°	139.5	132.7	125.9	132.7	139.5	141.2	170.1	208.6	227.9	262.8	332.7
127.5°	147.9	141.0	134.2	141.0	147.9	149.6	174.6	208.0	224.7	254.7	314.7
130°	153.3	146.0	138.6	146.0	153.3	155.2	178.0	208.3	223.5	250.2	303.6
132.5°	158.0	150.7	143.3	150.7	158.0	159.8	180.7	208.6	222.5	246.4	294.2
135°	163.5	156.8	150.1	156.8	163.5	165.2	183.7	208.4	220.8	240.8	280.8
137.5°	170.3	163.7	157.1	163.7	170.3	172.0	188.1	209.7	220.5	237.4	271.2
140°	175.0	168.9	162.8	168.9	175.0	176.6	190.9	209.9	219.4	234.0	263.3
142.5°	178.6	172.8	167.2	172.8	178.6	179.9	193.1	210.6	219.4	232.2	257.9
145°	183.9	179.0	174.0	179.0	183.9	185.2	196.1	210.6	217.9	228.4	249.4
147.5°	190.5	185.7	180.8	185.7	190.5	191.7	200.5	212.1	217.9	226.2	242.7
150°	194.0	189.6	185.3	189.6	194.0	195.1	202.7	212.9	217.9	224.9	238.8
152.5°	196.5	193.2	189.9	193.2	196.5	197.3	204.2	213.4	217.9	223.8	235.8
155°	201.6	199.2	196.7	199.2	201.6	202.2	207.5	214.5	217.9	222.6	232.1
157.5°	206.5	204.1	201.7	204.1	206.5	207.1	210.7	215.5	217.9	221.6	228.9
160°	208.8	207.1	205.2	207.1	208.8	209.3	212.2	216.0	217.9	221.1	227.4
162.5°	211.3	209.9	208.5	209.9	211.3	211.7	213.8	216.5	217.9	220.6	225.9
165°	214.8	213.5	212.3	213.5	214.8	215.0	216.0	217.3	217.9	219.8	223.6
167.5°	216.8	216.2	215.6	216.2	216.8	217.0	217.8	218.9	219.4	220.7	223.1
170°	219.1	218.5	217.9	218.5	219.1	219.2	219.3	219.4	219.4	220.7	223.1
172.5°	219.4	219.2	219.1	219.2	219.4	219.4	219.4	219.4	219.4	220.4	222.3
175°	220.8	220.8	220.8	220.8	220.8	220.8	220.3	219.7	219.4	220.0	221.3
177.5°	220.8	220.8	220.8	220.8	220.8	220.8	220.4	219.9	219.7	220.2	221.2
180°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3	2065.3
2.5°	1993.0	1987.2	1995.0	1973.5	1995.0	1987.2	1993.0	2006.7	1995.0	2002.8	2010.6
5°	1748.8	1739.0	1707.8	1682.3	1707.8	1739.0	1748.8	1789.8	1809.3	1844.5	1891.4
7.5°	1563.1	1555.3	1547.5	1531.8	1547.5	1555.3	1563.1	1574.8	1594.4	1625.7	1660.8
10°	1522.1	1524.1	1535.8	1533.8	1535.8	1524.1	1522.1	1518.2	1512.3	1518.2	1539.7
12.5°	1627.6	1645.2	1709.7	1705.8	1709.7	1645.2	1627.6	1549.5	1496.7	1487.0	1490.8
15°	1748.8	1754.6	1768.3	1770.3	1768.3	1754.6	1748.8	1717.5	1559.3	1490.8	1469.3
17.5°	1760.5	1762.5	1772.2	1772.2	1772.2	1762.5	1760.5	1746.8	1694.0	1602.2	1481.1
20°	1750.7	1754.6	1774.2	1778.1	1774.2	1754.6	1750.7	1733.1	1703.8	1670.6	1578.8
22.5°	1746.8	1754.6	1770.3	1768.3	1770.3	1754.6	1746.8	1719.5	1694.0	1670.6	1633.5
25°	1727.3	1727.3	1729.2	1731.2	1729.2	1727.3	1727.3	1705.8	1655.0	1649.1	1627.6
27.5°	1686.3	1690.1	1701.8	1700.0	1701.8	1690.1	1686.3	1678.5	1623.7	1617.8	1602.2
30°	1649.1	1645.2	1635.5	1627.6	1635.5	1645.2	1649.1	1637.4	1582.7	1567.0	1571.0
32.5°	1586.6	1576.8	1567.0	1561.2	1567.0	1576.8	1586.6	1582.7	1541.6	1520.1	1524.1
35°	1512.3	1514.3	1512.3	1506.5	1512.3	1514.3	1512.3	1516.3	1490.8	1471.3	1469.3
37.5°	1459.6	1463.5	1461.5	1453.8	1461.5	1463.5	1459.6	1455.6	1420.5	1414.6	1418.6
40°	1404.9	1406.8	1404.9	1399.0	1404.9	1406.8	1404.9	1397.1	1348.3	1350.1	1363.8
42.5°	1352.1	1350.1	1344.3	1340.4	1344.3	1350.1	1352.1	1340.4	1277.9	1272.0	1297.4
45°	1291.6	1293.5	1281.8	1275.9	1281.8	1293.5	1291.6	1283.8	1219.3	1203.6	1221.2
47.5°	1231.0	1231.0	1221.2	1215.3	1221.2	1231.0	1231.0	1221.2	1152.8	1137.2	1146.9
50°	1166.5	1164.6	1150.9	1148.9	1150.9	1164.6	1166.5	1160.6	1088.3	1074.6	1074.6
52.5°	1092.3	1092.3	1094.2	1098.1	1094.2	1092.3	1092.3	1094.2	1029.7	1016.1	1012.1
55°	1027.8	1029.7	1043.4	1047.3	1043.4	1029.7	1027.8	1027.8	969.1	955.4	947.6
57.5°	961.4	961.4	971.1	971.1	971.1	961.4	961.4	957.4	900.8	889.1	885.1
60°	885.1	889.1	896.9	894.9	896.9	889.1	885.1	881.2	832.4	824.6	810.9
62.5°	805.0	808.9	810.9	806.9	810.9	808.9	805.0	793.3	764.0	758.1	740.6
65°	721.0	724.9	726.9	722.9	726.9	724.9	721.0	715.1	693.7	683.9	668.2
67.5°	635.0	633.1	631.1	638.9	631.1	633.1	635.0	627.2	613.5	605.7	584.2
70°	547.1	547.1	545.2	549.0	545.2	547.1	547.1	541.2	533.4	527.6	508.0
72.5°	453.3	451.4	459.2	453.3	459.2	451.4	453.3	451.4	447.4	441.6	422.0
75°	361.5	365.4	361.5	367.4	361.5	365.4	361.5	363.4	361.5	357.5	343.9
77.5°	275.5	279.4	275.5	275.5	275.5	279.4	275.5	277.5	277.5	277.5	265.7
80°	195.4	193.5	193.5	191.5	193.5	193.5	195.4	195.4	197.3	193.5	189.5
82.5°	125.0	123.1	123.1	127.0	123.1	123.1	125.0	127.0	123.1	123.1	123.1
85°	68.4	70.3	66.5	66.5	66.5	70.3	68.4	64.5	68.4	68.4	66.5
87.5°	25.4	23.5	23.5	23.5	23.5	23.5	25.4	27.3	27.3	27.3	29.3
90°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	7.5	10.0	11.2	9.7
92.5°	28.1	27.0	22.5	18.0	22.5	27.0	28.1	39.8	55.5	63.4	55.7
95°	95.5	92.2	78.6	65.1	78.6	92.2	95.5	125.4	165.4	185.3	156.5
97.5°	220.6	214.2	188.3	162.5	188.3	214.2	220.6	239.5	264.6	277.3	229.2
100°	309.7	302.0	271.3	240.6	271.3	302.0	309.7	308.3	306.4	305.6	252.3
102.5°	385.9	379.3	353.0	326.7	353.0	379.3	385.9	361.8	329.6	313.5	259.5
105°	474.8	471.2	457.1	442.9	457.1	471.2	474.8	420.7	348.6	312.7	260.3
107.5°	521.0	521.9	525.2	528.7	525.2	521.9	521.0	445.7	345.2	294.9	248.8
110°	532.8	536.5	551.3	566.1	551.3	536.5	532.8	448.6	336.3	280.1	238.5

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	525.2	530.9	553.5	576.2	553.5	530.9	525.2	439.1	324.1	266.6	229.5
115°	499.6	507.5	538.8	570.3	538.8	507.5	499.6	416.6	305.9	250.4	219.2
117.5°	464.2	472.9	507.8	542.6	507.8	472.9	464.2	389.3	289.4	239.4	212.8
120°	440.4	448.9	482.7	516.6	482.7	448.9	440.4	371.9	280.6	235.0	210.7
122.5°	416.6	425.0	458.3	491.6	458.3	425.0	416.6	354.9	272.6	231.5	209.5
125°	385.0	392.7	423.4	454.2	423.4	392.7	385.0	332.7	262.8	227.9	208.6
127.5°	359.7	366.2	392.1	418.1	392.1	366.2	359.7	314.7	254.7	224.7	208.0
130°	343.6	349.6	373.6	397.6	373.6	349.6	343.6	303.6	250.2	223.5	208.3
132.5°	330.0	335.3	356.8	378.3	356.8	335.3	330.0	294.2	246.4	222.5	208.6
135°	310.8	315.4	333.9	352.4	333.9	315.4	310.8	280.8	240.8	220.8	208.4
137.5°	296.6	300.3	315.5	330.6	315.5	300.3	296.6	271.2	237.4	220.5	209.7
140°	285.2	288.7	302.8	317.0	302.8	288.7	285.2	263.3	234.0	219.4	209.9
142.5°	277.2	280.2	292.3	304.6	292.3	280.2	277.2	257.9	232.2	219.4	210.6
145°	265.1	267.4	276.7	285.9	276.7	267.4	265.1	249.4	228.4	217.9	210.6
147.5°	255.1	257.0	264.6	272.2	264.6	257.0	255.1	242.7	226.2	217.9	212.1
150°	249.3	250.8	257.1	263.3	257.1	250.8	249.3	238.8	224.9	217.9	212.9
152.5°	244.7	245.9	250.5	255.3	250.5	245.9	244.7	235.8	223.8	217.9	213.4
155°	239.2	240.0	243.0	246.2	243.0	240.0	239.2	232.1	222.6	217.9	214.5
157.5°	234.5	235.1	237.2	239.4	237.2	235.1	234.5	228.9	221.6	217.9	215.5
160°	232.1	232.4	233.7	235.0	233.7	232.4	232.1	227.4	221.1	217.9	216.0
162.5°	229.9	230.2	231.4	232.6	231.4	230.2	229.9	225.9	220.6	217.9	216.5
165°	226.5	226.8	228.1	229.3	228.1	226.8	226.5	223.6	219.8	217.9	217.3
167.5°	225.0	225.1	225.7	226.2	225.7	225.1	225.0	223.1	220.7	219.4	218.9
170°	225.0	225.0	225.0	225.0	225.0	225.0	225.0	223.1	220.7	219.4	219.4
172.5°	223.8	223.7	223.2	222.8	223.2	223.7	223.8	222.3	220.4	219.4	219.4
175°	222.2	222.2	222.2	222.2	222.2	222.2	222.2	221.3	220.0	219.4	219.7
177.5°	221.9	221.8	221.3	220.8	221.3	221.8	221.9	221.2	220.2	219.7	219.9
180°	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2065.3	2065.3	2065.3	2065.3	2065.3
2.5°	2039.9	2049.7	2055.5	2063.3	2082.9
5°	1961.7	1998.9	2010.6	2039.9	2075.0
7.5°	1789.8	1903.1	1934.4	2004.7	2059.5
10°	1623.7	1737.0	1791.8	1957.8	2039.9
12.5°	1539.7	1606.1	1643.3	1875.8	2012.5
15°	1487.0	1533.8	1561.2	1766.3	1981.3
17.5°	1445.9	1479.1	1498.6	1658.8	1938.3
20°	1420.5	1436.1	1453.8	1580.8	1889.5
22.5°	1402.9	1393.1	1406.8	1526.0	1823.0
25°	1391.2	1354.1	1369.8	1483.0	1744.8
27.5°	1401.0	1318.9	1324.8	1444.0	1662.8
30°	1402.9	1275.9	1277.9	1402.9	1571.0
32.5°	1389.3	1231.0	1232.9	1352.1	1467.4
35°	1356.0	1178.2	1176.3	1293.5	1326.8
37.5°	1311.1	1121.6	1121.6	1229.0	1172.4
40°	1256.4	1064.9	1070.8	1145.0	1035.6
42.5°	1189.9	1004.3	1012.1	1033.6	933.9
45°	1117.6	945.7	951.6	873.4	855.8
47.5°	1037.6	885.1	887.1	724.9	830.4
50°	941.8	822.6	814.8	621.4	828.4
52.5°	857.8	754.2	730.7	562.7	752.2
55°	775.7	681.9	631.1	517.7	697.6
57.5°	703.4	588.1	539.2	465.0	685.9
60°	637.0	496.3	459.2	408.4	629.2
62.5°	582.2	427.9	420.1	369.3	570.5
65°	523.7	381.0	379.0	336.0	484.6
67.5°	467.0	349.7	347.8	304.8	369.3
70°	406.4	316.5	312.7	271.6	273.5
72.5°	343.9	279.4	275.5	244.2	226.7
75°	281.4	236.4	234.5	213.0	183.7
77.5°	220.8	187.5	191.5	172.0	134.8
80°	158.3	136.8	140.7	123.1	101.6
82.5°	105.5	89.9	93.8	78.2	68.4
85°	58.7	50.8	52.8	41.0	31.3
87.5°	27.3	23.5	23.5	15.7	9.8
90°	6.5	4.1	3.8	2.7	1.5
92.5°	40.2	28.6	26.0	16.0	5.9
95°	98.9	55.7	51.1	32.6	14.2
97.5°	133.2	61.1	57.1	40.8	24.6
100°	145.7	65.8	62.1	47.3	32.6
102.5°	151.4	70.4	66.9	53.2	39.4
105°	155.7	77.2	74.2	62.6	51.0
107.5°	156.5	87.3	84.5	73.7	62.8
110°	155.3	92.9	90.4	80.7	70.8

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	155.3	99.7	97.3	88.0	78.7
115°	156.8	109.9	107.8	99.2	90.5
117.5°	159.6	119.8	117.8	110.0	102.2
120°	162.1	125.6	123.7	116.4	109.1
122.5°	165.5	132.4	130.5	123.2	115.7
125°	170.1	141.2	139.5	132.7	125.9
127.5°	174.6	149.6	147.9	141.0	134.2
130°	178.0	155.2	153.3	146.0	138.6
132.5°	180.7	159.8	158.0	150.7	143.3
135°	183.7	165.2	163.5	156.8	150.1
137.5°	188.1	172.0	170.3	163.7	157.1
140°	190.9	176.6	175.0	168.9	162.8
142.5°	193.1	179.9	178.6	172.8	167.2
145°	196.1	185.2	183.9	179.0	174.0
147.5°	200.5	191.7	190.5	185.7	180.8
150°	202.7	195.1	194.0	189.6	185.3
152.5°	204.2	197.3	196.5	193.2	189.9
155°	207.5	202.2	201.6	199.2	196.7
157.5°	210.7	207.1	206.5	204.1	201.7
160°	212.2	209.3	208.8	207.1	205.2
162.5°	213.8	211.7	211.3	209.9	208.5
165°	216.0	215.0	214.8	213.5	212.3
167.5°	217.8	217.0	216.8	216.2	215.6
170°	219.3	219.2	219.1	218.5	217.9
172.5°	219.4	219.4	219.4	219.2	219.1
175°	220.3	220.8	220.8	220.8	220.8
177.5°	220.4	220.8	220.8	220.8	220.8
180°	220.8	220.8	220.8	220.8	220.8

TEST NUMBER: P934088

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-6-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.99	17.19	16.65	17.86	18.65	18.81	20.01	19.47	20.69	21.48
	3H	16.49	17.57	17.17	18.26	19.08	20.18	21.26	20.86	21.95	22.77
	4H	16.70	17.71	17.39	18.41	19.25	20.64	21.66	21.33	22.35	23.19
	6H	16.83	17.77	17.54	18.48	19.33	20.94	21.88	21.65	22.59	23.44
	8H	16.84	17.74	17.56	18.47	19.32	21.02	21.92	21.74	22.65	23.50
	12H	16.83	17.68	17.55	18.40	19.28	21.07	21.93	21.80	22.65	23.53
4H	2H	17.06	18.07	17.76	18.77	19.61	19.26	20.28	19.96	20.98	21.81
	3H	18.12	18.96	18.83	19.70	20.55	20.80	21.64	21.51	22.38	23.23
	4H	18.41	19.18	19.13	19.91	20.80	21.34	22.11	22.07	22.85	23.73
	6H	18.55	19.22	19.30	19.98	20.87	21.72	22.39	22.47	23.15	24.04
	8H	18.57	19.19	19.32	19.95	20.85	21.83	22.46	22.58	23.22	24.12
	12H	18.55	19.11	19.32	19.89	20.80	21.91	22.47	22.68	23.25	24.16
8H	4H	18.89	19.51	19.64	20.27	21.17	21.49	22.11	22.24	22.87	23.78
	6H	19.16	19.68	19.94	20.48	21.39	21.94	22.45	22.72	23.26	24.16
	8H	19.21	19.67	20.00	20.47	21.39	22.09	22.55	22.89	23.36	24.28
	12H	19.21	19.61	20.00	20.41	21.39	22.21	22.61	23.00	23.40	24.38
12H	4H	18.91	19.47	19.68	20.25	21.16	21.47	22.03	22.24	22.81	23.72
	6H	19.23	19.69	20.02	20.49	21.41	21.94	22.40	22.73	23.20	24.12
	8H	19.31	19.71	20.10	20.51	21.49	22.11	22.52	22.91	23.31	24.29