

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934093

Luminaire Tested: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934093
REPORT IS A COMBINATION OF REPORTS P933684 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9049.5 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83			79
1	104	100	96	92	100	96	92	89	88	85	82	80	78	76	73	72	70			67
2	95	87	81	76	91	84	78	73	77	72	68	70	67	64	65	62	59			56
3	87	77	69	63	83	74	67	61	68	62	57	62	58	54	57	54	50			47
4	79	68	60	53	76	65	58	52	60	54	49	56	50	46	51	47	43			41
5	73	61	52	46	70	58	51	45	54	47	42	50	44	40	46	41	38			35
6	67	55	46	40	64	53	45	39	49	42	37	45	39	35	42	37	33			31
7	62	50	41	35	59	48	40	34	44	38	33	41	35	31	38	33	30			27
8	58	45	37	31	55	44	36	31	40	34	29	38	32	28	35	30	26			24
9	54	41	33	28	52	40	33	27	37	31	26	35	29	25	32	27	24			22
10	51	38	30	25	48	37	30	25	34	28	24	32	27	23	30	25	22			20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12778	12778	12778	12778
5°	12873	12898	12873	10142
10°	12787	12705	12787	9084
15°	12648	12430	12648	10380
20°	12383	12104	12383	10401
25°	11842	11629	11842	10180
30°	11142	11234	11142	9697
35°	9933	10734	9933	9165
40°	8277	10146	8277	8763
45°	7395	9458	7395	8301
50°	7857	8637	7857	7837
55°	7392	7753	7392	7569
60°	7620	6584	7620	6933
65°	6908	5443	6908	6084
70°	4783	4338	4783	5100
75°	4194	3207	4194	3839
80°	3381	2120	3381	2309
85°	1942	1123	1942	953

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 11335 cd/sqm

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.6	2.7
10°-20°	705.8	7.8
20°-30°	1091.1	12.1
30°-40°	1302.5	14.4
40°-50°	1310.2	14.5
50°-60°	1140.0	12.6
60°-70°	808.3	8.9
70°-80°	427.6	4.7
80°-90°	107.6	1.2
90°-100°	143.4	1.6
100°-110°	377.1	4.2
110°-120°	391.1	4.3
120°-130°	313.7	3.5
130°-140°	246.1	2.7
140°-150°	188.9	2.1
150°-160°	136.0	1.5
160°-170°	83.2	0.9
170°-180°	28.1	0.3
0°-30°	2045.5	22.6
0°-40°	3348.0	37.0
0°-60°	5798.2	64.1
0°-90°	7141.7	78.9
90°-120°	911.7	10.1
90°-150°	1660.4	18.3
90°-180°	1908.0	21.1
0°-180°	9049.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2754	2754	2754	2754	2754	
5°	2767	2853	2767	2243	2767	262
15°	2642	2827	2642	2361	2642	743
25°	2327	2637	2327	2308	2327	1068
35°	1769	2353	1769	2009	1769	1094
45°	1141	1938	1141	1701	1141	914
55°	930	1430	930	1397	930	855
65°	646	862	646	964	646	618
75°	245	409	245	490	245	257
85°	42	104	42	88	42	56
90°	2	8	2	8	2	3
95°	19	87	19	87	19	21
105°	68	590	68	590	68	72
115°	121	760	121	760	121	119
125°	168	606	168	606	168	149
135°	200	470	200	470	200	155
145°	232	381	232	381	232	145
155°	262	328	262	328	262	121
165°	283	306	283	306	283	80
175°	294	296	294	296	294	28
180°	294	294	294	294	294	

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0
2.5°	2777.5	2777.5	2793.0	2798.3	2798.3	2790.5	2782.7	2790.5	2813.9	2821.7	2819.2
5°	2767.0	2787.8	2816.5	2821.7	2827.0	2824.3	2819.2	2824.3	2850.4	2855.7	2858.2
7.5°	2746.2	2785.3	2821.7	2829.5	2837.4	2829.5	2827.0	2832.2	2858.2	2863.4	2863.4
10°	2720.1	2774.8	2816.5	2821.7	2829.5	2821.7	2821.7	2832.2	2858.2	2863.4	2866.0
12.5°	2683.6	2759.2	2798.3	2803.5	2813.9	2811.3	2808.7	2819.2	2845.2	2850.4	2850.4
15°	2642.0	2730.5	2767.0	2772.2	2790.5	2785.3	2785.3	2795.7	2824.3	2832.2	2829.5
17.5°	2584.6	2694.0	2735.8	2743.5	2756.6	2754.0	2756.6	2767.0	2793.0	2798.3	2800.9
20°	2519.5	2644.6	2694.0	2701.8	2715.0	2715.0	2715.0	2728.0	2754.0	2764.4	2764.4
22.5°	2430.9	2592.5	2644.6	2649.8	2665.4	2665.4	2670.6	2688.8	2712.3	2715.0	2715.0
25°	2326.7	2535.1	2579.4	2595.1	2610.7	2618.5	2626.3	2636.8	2644.6	2642.0	2644.6
27.5°	2217.2	2462.1	2519.5	2529.9	2550.8	2558.6	2569.0	2571.6	2574.2	2582.0	2576.8
30°	2094.8	2360.6	2446.6	2457.0	2490.8	2496.1	2485.6	2490.8	2503.8	2509.1	2514.3
32.5°	1956.7	2209.4	2371.0	2394.4	2425.7	2410.1	2407.4	2415.3	2436.1	2436.1	2441.3
35°	1769.1	2092.2	2300.6	2321.4	2344.9	2326.7	2337.1	2339.7	2352.8	2360.6	2357.9
37.5°	1563.3	1990.5	2227.7	2243.3	2261.6	2238.1	2253.7	2261.6	2271.9	2266.8	2266.8
40°	1380.9	1831.7	2141.7	2152.1	2167.7	2149.5	2165.2	2170.4	2175.6	2170.4	2167.7
42.5°	1245.4	1657.1	2050.5	2063.5	2053.1	2066.2	2071.4	2081.7	2074.0	2063.5	2063.5
45°	1141.2	1610.1	1951.5	1967.2	1951.5	1972.4	1980.2	1980.2	1956.7	1951.5	1948.9
47.5°	1107.4	1516.4	1852.5	1852.5	1844.7	1870.7	1883.8	1865.5	1842.0	1834.3	1834.3
50°	1104.7	1412.1	1717.0	1706.6	1743.1	1774.3	1761.3	1743.1	1724.8	1696.1	1696.1
52.5°	1003.2	1284.5	1542.4	1581.5	1638.8	1657.1	1636.3	1618.0	1586.8	1573.8	1563.3
55°	930.2	1151.6	1383.6	1461.6	1521.6	1545.1	1505.9	1487.8	1440.8	1433.1	1427.8
57.5°	914.5	958.8	1237.6	1336.6	1409.6	1406.9	1383.6	1349.6	1310.6	1302.7	1300.1
60°	839.0	693.1	1081.2	1198.5	1274.1	1266.2	1245.4	1214.2	1177.7	1172.5	1167.2
62.5°	760.8	502.9	904.1	1037.0	1143.8	1141.2	1123.0	1076.0	1050.0	1037.0	1026.5
65°	646.1	422.1	643.6	862.5	1016.2	1021.3	982.3	948.4	919.7	904.1	901.5
67.5°	492.4	343.9	435.1	719.1	893.7	888.5	839.0	823.3	786.8	779.0	763.4
70°	364.7	229.2	302.2	583.6	773.8	760.8	721.8	703.5	669.6	651.4	640.9
72.5°	302.2	185.0	221.5	453.4	651.4	635.8	601.9	581.0	552.4	536.7	526.3
75°	244.9	195.4	169.4	336.1	528.9	518.5	487.2	466.4	442.9	422.1	424.7
77.5°	179.7	182.4	135.5	247.5	419.4	403.9	385.6	359.6	349.1	328.3	328.3
80°	135.5	143.3	101.7	169.4	302.2	302.2	286.6	268.4	250.1	239.7	239.7
82.5°	91.2	91.2	75.5	106.8	205.9	198.0	187.6	182.4	172.0	166.7	166.7
85°	41.7	52.1	46.9	65.2	112.0	117.2	117.2	112.0	109.4	104.2	106.8
87.5°	13.0	23.5	28.7	36.5	57.3	59.9	62.5	62.5	62.5	65.2	65.2
90°	2.0	3.5	5.1	5.5	8.7	12.9	15.0	13.3	10.0	7.5	7.5
92.5°	7.9	21.3	34.8	38.2	53.6	74.2	84.5	74.0	53.2	37.6	36.1
95°	18.9	43.5	68.1	74.2	131.8	208.6	247.1	220.5	167.3	127.4	122.9
97.5°	32.8	54.5	76.1	81.5	177.6	305.7	369.8	353.0	319.4	294.1	285.5
100°	43.5	63.1	82.7	87.7	194.2	336.3	407.4	408.7	411.2	413.0	402.8
102.5°	52.6	70.9	89.2	93.8	201.9	346.1	418.2	439.6	482.4	514.5	505.7
105°	67.9	83.5	99.1	102.9	207.7	347.2	417.0	465.0	561.0	633.0	628.3
107.5°	83.7	98.2	112.7	116.3	208.6	331.7	393.2	460.2	594.2	694.6	695.8
110°	94.5	107.5	120.6	123.8	207.1	318.0	373.5	448.3	598.1	710.4	715.3

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	104.9	117.3	129.8	132.9	207.2	306.1	355.6	432.2	585.4	700.4	707.9
115°	120.7	132.1	143.7	146.5	209.0	292.3	334.0	407.8	555.5	666.2	676.7
117.5°	136.3	146.7	157.2	159.8	213.0	283.8	319.2	385.8	519.0	619.0	630.6
120°	145.3	155.2	165.1	167.5	216.1	280.9	313.3	374.1	495.9	587.2	598.4
122.5°	154.2	164.2	174.1	176.6	220.7	279.3	308.7	363.5	473.2	555.4	566.6
125°	167.9	177.0	186.0	188.2	226.8	278.2	303.8	350.3	443.5	513.3	523.6
127.5°	179.0	188.0	197.2	199.5	232.9	277.4	299.6	339.7	419.6	479.6	488.3
130°	184.9	194.7	204.5	207.0	237.3	277.9	298.1	333.7	404.9	458.2	466.2
132.5°	191.0	200.8	210.6	213.1	241.0	278.2	296.7	328.5	392.2	440.1	447.2
135°	200.1	209.0	218.0	220.3	244.9	277.9	294.3	321.0	374.4	414.4	420.5
137.5°	209.3	218.2	227.1	229.3	250.8	279.5	293.9	316.5	361.6	395.4	400.4
140°	217.0	225.2	233.4	235.5	254.5	279.8	292.5	312.1	351.0	380.2	384.9
142.5°	223.0	230.5	238.1	240.0	257.5	280.9	292.5	309.7	343.9	369.6	373.6
145°	232.1	238.7	245.2	246.9	261.5	280.9	290.6	304.6	332.6	353.6	356.6
147.5°	241.2	247.6	254.0	255.6	267.2	282.8	290.6	301.6	323.6	340.1	342.6
150°	247.1	252.9	258.6	260.1	270.3	283.8	290.6	299.8	318.5	332.4	334.5
152.5°	253.2	257.5	262.0	263.1	272.2	284.5	290.6	298.5	314.3	326.3	327.8
155°	262.3	265.5	268.8	269.6	276.6	285.9	290.6	296.9	309.5	319.0	320.0
157.5°	269.0	272.1	275.3	276.1	280.9	287.3	290.6	295.5	305.3	312.7	313.4
160°	273.5	276.0	278.4	279.0	282.9	288.0	290.6	294.8	303.2	309.5	309.9
162.5°	278.1	279.9	281.7	282.2	285.0	288.7	290.6	294.1	301.2	306.5	306.9
165°	283.1	284.8	286.4	286.8	288.1	289.8	290.6	293.1	298.2	302.0	302.4
167.5°	287.6	288.4	289.2	289.4	290.5	291.9	292.5	294.2	297.6	300.0	300.2
170°	290.6	291.4	292.2	292.3	292.4	292.5	292.5	294.2	297.6	300.0	300.0
172.5°	292.2	292.3	292.5	292.5	292.5	292.5	292.5	293.8	296.5	298.5	298.3
175°	294.3	294.3	294.3	294.3	293.7	292.9	292.5	293.3	295.0	296.3	296.3
177.5°	294.3	294.3	294.3	294.3	293.8	293.2	292.9	293.6	294.9	295.9	295.7
180°	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0
2.5°	2824.3	2816.5	2824.3	2819.2	2821.7	2813.9	2790.5	2782.7	2790.5	2798.3	2798.3
5°	2858.2	2853.0	2858.2	2858.2	2855.7	2850.4	2824.3	2819.2	2824.3	2827.0	2821.7
7.5°	2868.7	2860.8	2868.7	2863.4	2863.4	2858.2	2832.2	2827.0	2829.5	2837.4	2829.5
10°	2868.7	2860.8	2868.7	2866.0	2863.4	2858.2	2832.2	2821.7	2821.7	2829.5	2821.7
12.5°	2855.7	2850.4	2855.7	2850.4	2850.4	2845.2	2819.2	2808.7	2811.3	2813.9	2803.5
15°	2834.8	2827.0	2834.8	2829.5	2832.2	2824.3	2795.7	2785.3	2785.3	2790.5	2772.2
17.5°	2803.5	2793.0	2803.5	2800.9	2798.3	2793.0	2767.0	2756.6	2754.0	2756.6	2743.5
20°	2767.0	2759.2	2767.0	2764.4	2764.4	2754.0	2728.0	2715.0	2715.0	2715.0	2701.8
22.5°	2709.7	2701.8	2709.7	2715.0	2715.0	2712.3	2688.8	2670.6	2665.4	2665.4	2649.8
25°	2644.6	2636.8	2644.6	2644.6	2642.0	2644.6	2636.8	2626.3	2618.5	2610.7	2595.1
27.5°	2582.0	2576.8	2582.0	2576.8	2582.0	2574.2	2571.6	2569.0	2558.6	2550.8	2529.9
30°	2519.5	2514.3	2519.5	2514.3	2509.1	2503.8	2490.8	2485.6	2496.1	2490.8	2457.0
32.5°	2441.3	2436.1	2441.3	2441.3	2436.1	2436.1	2415.3	2407.4	2410.1	2425.7	2394.4
35°	2360.6	2352.8	2360.6	2357.9	2360.6	2352.8	2339.7	2337.1	2326.7	2344.9	2321.4
37.5°	2266.8	2258.9	2266.8	2266.8	2266.8	2271.9	2261.6	2253.7	2238.1	2261.6	2243.3
40°	2170.4	2159.9	2170.4	2167.7	2170.4	2175.6	2170.4	2165.2	2149.5	2167.7	2152.1
42.5°	2060.9	2058.4	2060.9	2063.5	2063.5	2074.0	2081.7	2071.4	2066.2	2053.1	2063.5
45°	1943.7	1938.5	1943.7	1948.9	1951.5	1956.7	1980.2	1980.2	1972.4	1951.5	1967.2
47.5°	1818.6	1805.6	1818.6	1834.3	1834.3	1842.0	1865.5	1883.8	1870.7	1844.7	1852.5
50°	1685.8	1688.3	1685.8	1696.1	1696.1	1724.8	1743.1	1761.3	1774.3	1743.1	1706.6
52.5°	1555.5	1552.9	1555.5	1563.3	1573.8	1586.8	1618.0	1636.3	1657.1	1638.8	1581.5
55°	1425.2	1430.4	1425.2	1427.8	1433.1	1440.8	1487.8	1505.9	1545.1	1521.6	1461.6
57.5°	1294.9	1287.1	1294.9	1300.1	1302.7	1310.6	1349.6	1383.6	1406.9	1409.6	1336.6
60°	1143.8	1133.4	1143.8	1167.2	1172.5	1177.7	1214.2	1245.4	1266.2	1274.1	1198.5
62.5°	1010.9	992.7	1010.9	1026.5	1037.0	1050.0	1076.0	1123.0	1141.2	1143.8	1037.0
65°	870.2	862.5	870.2	901.5	904.1	919.7	948.4	982.3	1021.3	1016.2	862.5
67.5°	742.6	742.6	742.6	763.4	779.0	786.8	823.3	839.0	888.5	893.7	719.1
70°	625.3	622.8	625.3	640.9	651.4	669.6	703.5	721.8	760.8	773.8	583.6
72.5°	513.3	510.6	513.3	526.3	536.7	552.4	581.0	601.9	635.8	651.4	453.4
75°	414.3	409.1	414.3	424.7	422.1	442.9	466.4	487.2	518.5	528.9	336.1
77.5°	317.9	317.9	317.9	328.3	328.3	349.1	359.6	385.6	403.9	419.4	247.5
80°	237.1	234.5	237.1	239.7	239.7	250.1	268.4	286.6	302.2	302.2	169.4
82.5°	166.7	161.5	166.7	166.7	166.7	172.0	182.4	187.6	198.0	205.9	106.8
85°	104.2	104.2	104.2	106.8	104.2	109.4	112.0	117.2	117.2	112.0	65.2
87.5°	67.7	65.2	67.7	65.2	65.2	62.5	62.5	62.5	59.9	57.3	36.5
90°	7.5	7.5	7.5	7.5	7.5	10.0	13.3	15.0	12.9	8.7	5.5
92.5°	30.1	24.1	30.1	36.1	37.6	53.2	74.0	84.5	74.2	53.6	38.2
95°	104.8	86.7	104.8	122.9	127.4	167.3	220.5	247.1	208.6	131.8	74.2
97.5°	251.0	216.6	251.0	285.5	294.1	319.4	353.0	369.8	305.7	177.6	81.5
100°	361.8	320.7	361.8	402.8	413.0	411.2	408.7	407.4	336.3	194.2	87.7
102.5°	470.6	435.5	470.6	505.7	514.5	482.4	439.6	418.2	346.1	201.9	93.8
105°	609.4	590.5	609.4	628.3	633.0	561.0	465.0	417.0	347.2	207.7	102.9
107.5°	700.4	704.9	700.4	695.8	694.6	594.2	460.2	393.2	331.7	208.6	116.3
110°	735.0	754.7	735.0	715.3	710.4	598.1	448.3	373.5	318.0	207.1	123.8

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	738.1	768.3	738.1	707.9	700.4	585.4	432.2	355.6	306.1	207.2	132.9
115°	718.6	760.4	718.6	676.7	666.2	555.5	407.8	334.0	292.3	209.0	146.5
117.5°	677.1	723.5	677.1	630.6	619.0	519.0	385.8	319.2	283.8	213.0	159.8
120°	643.6	688.7	643.6	598.4	587.2	495.9	374.1	313.3	280.9	216.1	167.5
122.5°	611.0	655.5	611.0	566.6	555.4	473.2	363.5	308.7	279.3	220.7	176.6
125°	564.6	605.6	564.6	523.6	513.3	443.5	350.3	303.8	278.2	226.8	188.2
127.5°	522.8	557.4	522.8	488.3	479.6	419.6	339.7	299.6	277.4	232.9	199.5
130°	498.1	530.1	498.1	466.2	458.2	404.9	333.7	298.1	277.9	237.3	207.0
132.5°	475.8	504.4	475.8	447.2	440.1	392.2	328.5	296.7	278.2	241.0	213.1
135°	445.2	469.8	445.2	420.5	414.4	374.4	321.0	294.3	277.9	244.9	220.3
137.5°	420.6	440.8	420.6	400.4	395.4	361.6	316.5	293.9	279.5	250.8	229.3
140°	403.8	422.7	403.8	384.9	380.2	351.0	312.1	292.5	279.8	254.5	235.5
142.5°	389.9	406.0	389.9	373.6	369.6	343.9	309.7	292.5	280.9	257.5	240.0
145°	369.0	381.2	369.0	356.6	353.6	332.6	304.6	290.6	280.9	261.5	246.9
147.5°	352.8	363.0	352.8	342.6	340.1	323.6	301.6	290.6	282.8	267.2	255.6
150°	342.7	351.0	342.7	334.5	332.4	318.5	299.8	290.6	283.8	270.3	260.1
152.5°	334.1	340.3	334.1	327.8	326.3	314.3	298.5	290.6	284.5	272.2	263.1
155°	324.1	328.2	324.1	320.0	319.0	309.5	296.9	290.6	285.9	276.6	269.6
157.5°	316.3	319.2	316.3	313.4	312.7	305.3	295.5	290.6	287.3	280.9	276.1
160°	311.6	313.3	311.6	309.9	309.5	303.2	294.8	290.6	288.0	282.9	279.0
162.5°	308.5	310.1	308.5	306.9	306.5	301.2	294.1	290.6	288.7	285.0	282.2
165°	304.1	305.8	304.1	302.4	302.0	298.2	293.1	290.6	289.8	288.1	286.8
167.5°	300.9	301.6	300.9	300.2	300.0	297.6	294.2	292.5	291.9	290.5	289.4
170°	300.0	300.0	300.0	300.0	300.0	297.6	294.2	292.5	292.5	292.4	292.3
172.5°	297.7	297.1	297.7	298.3	298.5	296.5	293.8	292.5	292.5	292.5	292.5
175°	296.3	296.3	296.3	296.3	296.3	295.0	293.3	292.5	292.9	293.7	294.3
177.5°	295.0	294.3	295.0	295.7	295.9	294.9	293.6	292.9	293.2	293.8	294.3
180°	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0
2.5°	2793.0	2777.5	2777.5	2751.4	2741.0	2733.2	2720.1	2681.0	2670.6	2660.2	2675.8
5°	2816.5	2787.8	2767.0	2720.1	2681.0	2665.4	2615.9	2522.1	2459.6	2412.6	2386.6
7.5°	2821.7	2785.3	2746.2	2673.2	2579.4	2537.8	2386.6	2214.7	2167.7	2126.1	2100.0
10°	2816.5	2774.8	2720.1	2610.7	2389.2	2316.3	2165.2	2053.1	2024.5	2016.7	2024.5
12.5°	2798.3	2759.2	2683.6	2501.3	2191.2	2141.7	2053.1	1988.0	1982.7	1995.8	2066.2
15°	2767.0	2730.5	2642.0	2355.4	2081.7	2045.3	1982.7	1959.3	1988.0	2079.2	2290.2
17.5°	2735.8	2694.0	2584.6	2212.1	1998.4	1972.4	1928.0	1975.0	2136.5	2258.9	2329.3
20°	2694.0	2644.6	2519.5	2107.9	1938.5	1915.0	1894.2	2105.2	2227.7	2271.9	2311.1
22.5°	2644.6	2592.5	2430.9	2034.9	1876.0	1857.7	1870.7	2178.2	2227.7	2258.9	2292.8
25°	2579.4	2535.1	2326.7	1977.5	1826.5	1805.6	1855.1	2170.4	2199.0	2206.9	2274.6
27.5°	2519.5	2462.1	2217.2	1925.5	1766.5	1758.7	1868.2	2136.5	2157.4	2165.2	2238.1
30°	2446.6	2360.6	2094.8	1870.7	1704.0	1701.3	1870.7	2094.8	2089.6	2110.4	2183.4
32.5°	2371.0	2209.4	1956.7	1803.0	1644.1	1641.5	1852.5	2032.2	2027.0	2055.7	2110.4
35°	2300.6	2092.2	1769.1	1724.8	1568.5	1571.1	1808.2	1959.3	1961.9	1988.0	2021.9
37.5°	2227.7	1990.5	1563.3	1638.8	1495.6	1495.6	1748.3	1891.5	1886.4	1894.2	1941.0
40°	2141.7	1831.7	1380.9	1526.8	1427.8	1419.9	1675.3	1818.6	1800.3	1797.8	1862.9
42.5°	2050.5	1657.1	1245.4	1378.3	1349.6	1339.2	1586.8	1730.0	1696.1	1704.0	1787.3
45°	1951.5	1610.1	1141.2	1164.7	1268.9	1261.1	1490.3	1628.4	1605.0	1625.8	1711.8
47.5°	1852.5	1516.4	1107.4	966.7	1182.9	1180.2	1383.6	1529.4	1516.4	1537.3	1628.4
50°	1717.0	1412.1	1104.7	828.5	1086.5	1096.9	1255.9	1433.1	1433.1	1451.3	1547.6
52.5°	1542.4	1284.5	1003.2	750.3	974.5	1005.7	1143.8	1349.6	1354.9	1373.1	1459.1
55°	1383.6	1151.6	930.2	690.5	841.6	909.3	1034.4	1263.7	1274.1	1292.4	1370.4
57.5°	1237.6	958.8	914.5	620.1	719.1	784.3	938.0	1180.2	1185.5	1201.1	1276.7
60°	1081.2	693.1	839.0	544.6	612.3	661.8	849.3	1081.2	1099.5	1109.9	1175.1
62.5°	904.1	502.9	760.8	492.4	560.1	570.6	776.5	987.5	1010.9	1018.7	1057.8
65°	643.6	422.1	646.1	448.1	505.4	508.1	698.3	891.0	912.0	925.0	953.6
67.5°	435.1	343.9	492.4	406.4	463.8	466.4	622.8	779.0	807.7	818.1	836.3
70°	302.2	229.2	364.7	362.2	416.9	422.1	541.9	677.4	703.5	711.3	721.8
72.5°	221.5	185.0	302.2	325.7	367.4	372.6	458.6	562.8	588.8	596.6	601.9
75°	169.4	195.4	244.9	284.0	312.7	315.2	375.2	458.6	476.8	482.1	484.6
77.5°	135.5	182.4	179.7	229.2	255.4	250.1	294.4	354.4	369.9	369.9	369.9
80°	101.7	143.3	135.5	164.2	187.6	182.4	211.0	252.7	257.9	263.2	260.5
82.5°	75.5	91.2	91.2	104.2	125.0	119.9	140.7	164.2	164.2	164.2	169.4
85°	46.9	52.1	41.7	54.7	70.3	67.7	78.2	88.5	91.2	91.2	86.0
87.5°	28.7	23.5	13.0	20.8	31.3	31.3	36.5	39.0	36.5	36.5	36.5
90°	5.1	3.5	2.0	3.5	5.1	5.5	8.7	12.9	15.0	13.3	10.0
92.5°	34.8	21.3	7.9	21.3	34.8	38.2	53.6	74.2	84.5	74.0	53.2
95°	68.1	43.5	18.9	43.5	68.1	74.2	131.8	208.6	247.1	220.5	167.3
97.5°	76.1	54.5	32.8	54.5	76.1	81.5	177.6	305.7	369.8	353.0	319.4
100°	82.7	63.1	43.5	63.1	82.7	87.7	194.2	336.3	407.4	408.7	411.2
102.5°	89.2	70.9	52.6	70.9	89.2	93.8	201.9	346.1	418.2	439.6	482.4
105°	99.1	83.5	67.9	83.5	99.1	102.9	207.7	347.2	417.0	465.0	561.0
107.5°	112.7	98.2	83.7	98.2	112.7	116.3	208.6	331.7	393.2	460.2	594.2
110°	120.6	107.5	94.5	107.5	120.6	123.8	207.1	318.0	373.5	448.3	598.1



TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	129.8	117.3	104.9	117.3	129.8	132.9	207.2	306.1	355.6	432.2	585.4
115°	143.7	132.1	120.7	132.1	143.7	146.5	209.0	292.3	334.0	407.8	555.5
117.5°	157.2	146.7	136.3	146.7	157.2	159.8	213.0	283.8	319.2	385.8	519.0
120°	165.1	155.2	145.3	155.2	165.1	167.5	216.1	280.9	313.3	374.1	495.9
122.5°	174.1	164.2	154.2	164.2	174.1	176.6	220.7	279.3	308.7	363.5	473.2
125°	186.0	177.0	167.9	177.0	186.0	188.2	226.8	278.2	303.8	350.3	443.5
127.5°	197.2	188.0	179.0	188.0	197.2	199.5	232.9	277.4	299.6	339.7	419.6
130°	204.5	194.7	184.9	194.7	204.5	207.0	237.3	277.9	298.1	333.7	404.9
132.5°	210.6	200.8	191.0	200.8	210.6	213.1	241.0	278.2	296.7	328.5	392.2
135°	218.0	209.0	200.1	209.0	218.0	220.3	244.9	277.9	294.3	321.0	374.4
137.5°	227.1	218.2	209.3	218.2	227.1	229.3	250.8	279.5	293.9	316.5	361.6
140°	233.4	225.2	217.0	225.2	233.4	235.5	254.5	279.8	292.5	312.1	351.0
142.5°	238.1	230.5	223.0	230.5	238.1	240.0	257.5	280.9	292.5	309.7	343.9
145°	245.2	238.7	232.1	238.7	245.2	246.9	261.5	280.9	290.6	304.6	332.6
147.5°	254.0	247.6	241.2	247.6	254.0	255.6	267.2	282.8	290.6	301.6	323.6
150°	258.6	252.9	247.1	252.9	258.6	260.1	270.3	283.8	290.6	299.8	318.5
152.5°	262.0	257.5	253.2	257.5	262.0	263.1	272.2	284.5	290.6	298.5	314.3
155°	268.8	265.5	262.3	265.5	268.8	269.6	276.6	285.9	290.6	296.9	309.5
157.5°	275.3	272.1	269.0	272.1	275.3	276.1	280.9	287.3	290.6	295.5	305.3
160°	278.4	276.0	273.5	276.0	278.4	279.0	282.9	288.0	290.6	294.8	303.2
162.5°	281.7	279.9	278.1	279.9	281.7	282.2	285.0	288.7	290.6	294.1	301.2
165°	286.4	284.8	283.1	284.8	286.4	286.8	288.1	289.8	290.6	293.1	298.2
167.5°	289.2	288.4	287.6	288.4	289.2	289.4	290.5	291.9	292.5	294.2	297.6
170°	292.2	291.4	290.6	291.4	292.2	292.3	292.4	292.5	292.5	294.2	297.6
172.5°	292.5	292.3	292.2	292.3	292.5	292.5	292.5	292.5	292.5	293.8	296.5
175°	294.3	294.3	294.3	294.3	294.3	294.3	293.7	292.9	292.5	293.3	295.0
177.5°	294.3	294.3	294.3	294.3	294.3	294.3	293.8	293.2	292.9	293.6	294.9
180°	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0	2754.0
2.5°	2657.6	2649.8	2660.2	2631.5	2660.2	2649.8	2657.6	2675.8	2660.2	2670.6	2681.0
5°	2331.9	2318.9	2277.2	2243.3	2277.2	2318.9	2331.9	2386.6	2412.6	2459.6	2522.1
7.5°	2084.4	2074.0	2063.5	2042.7	2063.5	2074.0	2084.4	2100.0	2126.1	2167.7	2214.7
10°	2029.7	2032.2	2047.9	2045.3	2047.9	2032.2	2029.7	2024.5	2016.7	2024.5	2053.1
12.5°	2170.4	2193.8	2279.8	2274.6	2279.8	2193.8	2170.4	2066.2	1995.8	1982.7	1988.0
15°	2331.9	2339.7	2357.9	2360.6	2357.9	2339.7	2331.9	2290.2	2079.2	1988.0	1959.3
17.5°	2347.6	2350.1	2363.1	2363.1	2363.1	2350.1	2347.6	2329.3	2258.9	2136.5	1975.0
20°	2334.6	2339.7	2365.8	2371.0	2365.8	2339.7	2334.6	2311.1	2271.9	2227.7	2105.2
22.5°	2329.3	2339.7	2360.6	2357.9	2360.6	2339.7	2329.3	2292.8	2258.9	2227.7	2178.2
25°	2303.2	2303.2	2305.9	2308.4	2305.9	2303.2	2303.2	2274.6	2206.9	2199.0	2170.4
27.5°	2248.6	2253.7	2269.4	2266.8	2269.4	2253.7	2248.6	2238.1	2165.2	2157.4	2136.5
30°	2199.0	2193.8	2180.7	2170.4	2180.7	2193.8	2199.0	2183.4	2110.4	2089.6	2094.8
32.5°	2115.7	2102.6	2089.6	2081.7	2089.6	2102.6	2115.7	2110.4	2055.7	2027.0	2032.2
35°	2016.7	2019.2	2016.7	2008.8	2016.7	2019.2	2016.7	2021.9	1988.0	1961.9	1959.3
37.5°	1946.3	1951.5	1948.9	1938.5	1948.9	1951.5	1946.3	1941.0	1894.2	1886.4	1891.5
40°	1873.3	1876.0	1873.3	1865.5	1873.3	1876.0	1873.3	1862.9	1797.8	1800.3	1818.6
42.5°	1803.0	1800.3	1792.5	1787.3	1792.5	1800.3	1803.0	1787.3	1704.0	1696.1	1730.0
45°	1722.2	1724.8	1709.2	1701.3	1709.2	1724.8	1722.2	1711.8	1625.8	1605.0	1628.4
47.5°	1641.5	1641.5	1628.4	1620.6	1628.4	1641.5	1641.5	1628.4	1537.3	1516.4	1529.4
50°	1555.5	1552.9	1534.6	1532.0	1534.6	1552.9	1555.5	1547.6	1451.3	1433.1	1433.1
52.5°	1456.4	1456.4	1459.1	1464.3	1459.1	1456.4	1456.4	1459.1	1373.1	1354.9	1349.6
55°	1370.4	1373.1	1391.3	1396.6	1391.3	1373.1	1370.4	1370.4	1292.4	1274.1	1263.7
57.5°	1281.9	1281.9	1294.9	1294.9	1294.9	1281.9	1281.9	1276.7	1201.1	1185.5	1180.2
60°	1180.2	1185.5	1195.9	1193.4	1195.9	1185.5	1180.2	1175.1	1109.9	1099.5	1081.2
62.5°	1073.5	1078.7	1081.2	1076.0	1081.2	1078.7	1073.5	1057.8	1018.7	1010.9	987.5
65°	961.4	966.7	969.2	964.0	969.2	966.7	961.4	953.6	925.0	912.0	891.0
67.5°	846.8	844.2	841.6	852.0	841.6	844.2	846.8	836.3	818.1	807.7	779.0
70°	729.5	729.5	726.9	732.1	726.9	729.5	729.5	721.8	711.3	703.5	677.4
72.5°	604.5	601.9	612.3	604.5	612.3	601.9	604.5	601.9	596.6	588.8	562.8
75°	482.1	487.2	482.1	489.8	482.1	487.2	482.1	484.6	482.1	476.8	458.6
77.5°	367.4	372.6	367.4	367.4	367.4	372.6	367.4	369.9	369.9	369.9	354.4
80°	260.5	257.9	257.9	255.4	257.9	257.9	260.5	260.5	263.2	257.9	252.7
82.5°	166.7	164.2	164.2	169.4	164.2	164.2	166.7	169.4	164.2	164.2	164.2
85°	91.2	93.8	88.5	88.5	88.5	93.8	91.2	86.0	91.2	91.2	88.5
87.5°	33.9	31.3	31.3	31.3	31.3	31.3	33.9	36.5	36.5	36.5	39.0
90°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	10.0	13.3	15.0	12.9
92.5°	37.6	36.1	30.1	24.1	30.1	36.1	37.6	53.2	74.0	84.5	74.2
95°	127.4	122.9	104.8	86.7	104.8	122.9	127.4	167.3	220.5	247.1	208.6
97.5°	294.1	285.5	251.0	216.6	251.0	285.5	294.1	319.4	353.0	369.8	305.7
100°	413.0	402.8	361.8	320.7	361.8	402.8	413.0	411.2	408.7	407.4	336.3
102.5°	514.5	505.7	470.6	435.5	470.6	505.7	514.5	482.4	439.6	418.2	346.1
105°	633.0	628.3	609.4	590.5	609.4	628.3	633.0	561.0	465.0	417.0	347.2
107.5°	694.6	695.8	700.4	704.9	700.4	695.8	694.6	594.2	460.2	393.2	331.7
110°	710.4	715.3	735.0	754.7	735.0	715.3	710.4	598.1	448.3	373.5	318.0

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	700.4	707.9	738.1	768.3	738.1	707.9	700.4	585.4	432.2	355.6	306.1
115°	666.2	676.7	718.6	760.4	718.6	676.7	666.2	555.5	407.8	334.0	292.3
117.5°	619.0	630.6	677.1	723.5	677.1	630.6	619.0	519.0	385.8	319.2	283.8
120°	587.2	598.4	643.6	688.7	643.6	598.4	587.2	495.9	374.1	313.3	280.9
122.5°	555.4	566.6	611.0	655.5	611.0	566.6	555.4	473.2	363.5	308.7	279.3
125°	513.3	523.6	564.6	605.6	564.6	523.6	513.3	443.5	350.3	303.8	278.2
127.5°	479.6	488.3	522.8	557.4	522.8	488.3	479.6	419.6	339.7	299.6	277.4
130°	458.2	466.2	498.1	530.1	498.1	466.2	458.2	404.9	333.7	298.1	277.9
132.5°	440.1	447.2	475.8	504.4	475.8	447.2	440.1	392.2	328.5	296.7	278.2
135°	414.4	420.5	445.2	469.8	445.2	420.5	414.4	374.4	321.0	294.3	277.9
137.5°	395.4	400.4	420.6	440.8	420.6	400.4	395.4	361.6	316.5	293.9	279.5
140°	380.2	384.9	403.8	422.7	403.8	384.9	380.2	351.0	312.1	292.5	279.8
142.5°	369.6	373.6	389.9	406.0	389.9	373.6	369.6	343.9	309.7	292.5	280.9
145°	353.6	356.6	369.0	381.2	369.0	356.6	353.6	332.6	304.6	290.6	280.9
147.5°	340.1	342.6	352.8	363.0	352.8	342.6	340.1	323.6	301.6	290.6	282.8
150°	332.4	334.5	342.7	351.0	342.7	334.5	332.4	318.5	299.8	290.6	283.8
152.5°	326.3	327.8	334.1	340.3	334.1	327.8	326.3	314.3	298.5	290.6	284.5
155°	319.0	320.0	324.1	328.2	324.1	320.0	319.0	309.5	296.9	290.6	285.9
157.5°	312.7	313.4	316.3	319.2	316.3	313.4	312.7	305.3	295.5	290.6	287.3
160°	309.5	309.9	311.6	313.3	311.6	309.9	309.5	303.2	294.8	290.6	288.0
162.5°	306.5	306.9	308.5	310.1	308.5	306.9	306.5	301.2	294.1	290.6	288.7
165°	302.0	302.4	304.1	305.8	304.1	302.4	302.0	298.2	293.1	290.6	289.8
167.5°	300.0	300.2	300.9	301.6	300.9	300.2	300.0	297.6	294.2	292.5	291.9
170°	300.0	300.0	300.0	300.0	300.0	300.0	300.0	297.6	294.2	292.5	292.5
172.5°	298.5	298.3	297.7	297.1	297.7	298.3	298.5	296.5	293.8	292.5	292.5
175°	296.3	296.3	296.3	296.3	296.3	296.3	296.3	295.0	293.3	292.5	292.9
177.5°	295.9	295.7	295.0	294.3	295.0	295.7	295.9	294.9	293.6	292.9	293.2
180°	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2754.0	2754.0	2754.0	2754.0	2754.0
2.5°	2720.1	2733.2	2741.0	2751.4	2777.5
5°	2615.9	2665.4	2681.0	2720.1	2767.0
7.5°	2386.6	2537.8	2579.4	2673.2	2746.2
10°	2165.2	2316.3	2389.2	2610.7	2720.1
12.5°	2053.1	2141.7	2191.2	2501.3	2683.6
15°	1982.7	2045.3	2081.7	2355.4	2642.0
17.5°	1928.0	1972.4	1998.4	2212.1	2584.6
20°	1894.2	1915.0	1938.5	2107.9	2519.5
22.5°	1870.7	1857.7	1876.0	2034.9	2430.9
25°	1855.1	1805.6	1826.5	1977.5	2326.7
27.5°	1868.2	1758.7	1766.5	1925.5	2217.2
30°	1870.7	1701.3	1704.0	1870.7	2094.8
32.5°	1852.5	1641.5	1644.1	1803.0	1956.7
35°	1808.2	1571.1	1568.5	1724.8	1769.1
37.5°	1748.3	1495.6	1495.6	1638.8	1563.3
40°	1675.3	1419.9	1427.8	1526.8	1380.9
42.5°	1586.8	1339.2	1349.6	1378.3	1245.4
45°	1490.3	1261.1	1268.9	1164.7	1141.2
47.5°	1383.6	1180.2	1182.9	966.7	1107.4
50°	1255.9	1096.9	1086.5	828.5	1104.7
52.5°	1143.8	1005.7	974.5	750.3	1003.2
55°	1034.4	909.3	841.6	690.5	930.2
57.5°	938.0	784.3	719.1	620.1	914.5
60°	849.3	661.8	612.3	544.6	839.0
62.5°	776.5	570.6	560.1	492.4	760.8
65°	698.3	508.1	505.4	448.1	646.1
67.5°	622.8	466.4	463.8	406.4	492.4
70°	541.9	422.1	416.9	362.2	364.7
72.5°	458.6	372.6	367.4	325.7	302.2
75°	375.2	315.2	312.7	284.0	244.9
77.5°	294.4	250.1	255.4	229.2	179.7
80°	211.0	182.4	187.6	164.2	135.5
82.5°	140.7	119.9	125.0	104.2	91.2
85°	78.2	67.7	70.3	54.7	41.7
87.5°	36.5	31.3	31.3	20.8	13.0
90°	8.7	5.5	5.1	3.5	2.0
92.5°	53.6	38.2	34.8	21.3	7.9
95°	131.8	74.2	68.1	43.5	18.9
97.5°	177.6	81.5	76.1	54.5	32.8
100°	194.2	87.7	82.7	63.1	43.5
102.5°	201.9	93.8	89.2	70.9	52.6
105°	207.7	102.9	99.1	83.5	67.9
107.5°	208.6	116.3	112.7	98.2	83.7
110°	207.1	123.8	120.6	107.5	94.5



TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	207.2	132.9	129.8	117.3	104.9
115°	209.0	146.5	143.7	132.1	120.7
117.5°	213.0	159.8	157.2	146.7	136.3
120°	216.1	167.5	165.1	155.2	145.3
122.5°	220.7	176.6	174.1	164.2	154.2
125°	226.8	188.2	186.0	177.0	167.9
127.5°	232.9	199.5	197.2	188.0	179.0
130°	237.3	207.0	204.5	194.7	184.9
132.5°	241.0	213.1	210.6	200.8	191.0
135°	244.9	220.3	218.0	209.0	200.1
137.5°	250.8	229.3	227.1	218.2	209.3
140°	254.5	235.5	233.4	225.2	217.0
142.5°	257.5	240.0	238.1	230.5	223.0
145°	261.5	246.9	245.2	238.7	232.1
147.5°	267.2	255.6	254.0	247.6	241.2
150°	270.3	260.1	258.6	252.9	247.1
152.5°	272.2	263.1	262.0	257.5	253.2
155°	276.6	269.6	268.8	265.5	262.3
157.5°	280.9	276.1	275.3	272.1	269.0
160°	282.9	279.0	278.4	276.0	273.5
162.5°	285.0	282.2	281.7	279.9	278.1
165°	288.1	286.8	286.4	284.8	283.1
167.5°	290.5	289.4	289.2	288.4	287.6
170°	292.4	292.3	292.2	291.4	290.6
172.5°	292.5	292.5	292.5	292.3	292.2
175°	293.7	294.3	294.3	294.3	294.3
177.5°	293.8	294.3	294.3	294.3	294.3
180°	294.3	294.3	294.3	294.3	294.3

TEST NUMBER: P934093

CATALOG NUMBER: SQ4-FA-025U-100D-B2750-1D-UNV-W2A-W-8-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.99	17.19	16.65	17.87	18.66	18.83	20.03	19.49	20.71	21.50
	3H	16.49	17.57	17.17	18.26	19.08	20.20	21.28	20.88	21.97	22.79
	4H	16.70	17.72	17.40	18.42	19.25	20.66	21.68	21.36	22.38	23.21
	6H	16.84	17.78	17.55	18.49	19.33	20.97	21.91	21.68	22.62	23.47
	8H	16.85	17.74	17.57	18.47	19.32	21.05	21.95	21.77	22.68	23.53
	12H	16.83	17.68	17.56	18.41	19.29	21.10	21.96	21.83	22.68	23.56
4H	2H	17.07	18.08	17.77	18.78	19.62	19.28	20.30	19.98	21.00	21.83
	3H	18.13	18.97	18.84	19.71	20.56	20.82	21.67	21.53	22.40	23.26
	4H	18.42	19.18	19.14	19.92	20.81	21.36	22.13	22.09	22.87	23.75
	6H	18.56	19.23	19.31	19.99	20.88	21.75	22.41	22.50	23.18	24.07
	8H	18.57	19.20	19.32	19.96	20.86	21.86	22.49	22.61	23.25	24.15
	12H	18.56	19.12	19.33	19.90	20.81	21.94	22.50	22.71	23.28	24.19
8H	4H	18.90	19.52	19.65	20.28	21.18	21.51	22.14	22.26	22.90	23.80
	6H	19.17	19.69	19.95	20.49	21.40	21.97	22.48	22.75	23.28	24.19
	8H	19.22	19.68	20.01	20.48	21.40	22.12	22.58	22.92	23.38	24.31
	12H	19.22	19.62	20.01	20.42	21.40	22.24	22.64	23.03	23.44	24.42
12H	4H	18.92	19.48	19.69	20.26	21.17	21.49	22.05	22.27	22.84	23.75
	6H	19.24	19.70	20.03	20.50	21.42	21.97	22.43	22.76	23.23	24.15
	8H	19.32	19.72	20.11	20.52	21.50	22.14	22.55	22.94	23.34	24.32