

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934393

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934393
REPORT IS A COMBINATION OF REPORTS P933696 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9332.5 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9670	9670	9670	9670
5°	9743	9762	9743	7676
10°	9678	9616	9678	6874
15°	9572	9407	9572	7855
20°	9372	9161	9372	7872
25°	8962	8801	8962	7705
30°	8433	8502	8433	7339
35°	7518	8124	7518	6936
40°	6265	7679	6265	6632
45°	5597	7158	5597	6282
50°	5946	6537	5946	5932
55°	5595	5868	5595	5729
60°	5767	4983	5767	5247
65°	5229	4119	5229	4605
70°	3621	3283	3621	3860
75°	3175	2427	3175	2906
80°	2557	1605	2557	1747
85°	1472	850	1472	722

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8578 cd/sqm

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.1	2.0
10°-20°	534.2	5.7
20°-30°	825.8	8.8
30°-40°	985.8	10.6
40°-50°	991.6	10.6
50°-60°	862.8	9.2
60°-70°	611.8	6.6
70°-80°	323.7	3.5
80°-90°	82.9	0.9
90°-100°	295.2	3.2
100°-110°	776.1	8.3
110°-120°	804.7	8.6
120°-130°	645.5	6.9
130°-140°	506.5	5.4
140°-150°	388.8	4.2
150°-160°	280.0	3.0
160°-170°	171.3	1.8
170°-180°	57.9	0.6
0°-30°	1548.1	16.6
0°-40°	2533.9	27.2
0°-60°	4388.3	47.0
0°-90°	5406.6	57.9
90°-120°	1876.0	20.1
90°-150°	3416.8	36.6
90°-180°	3926.0	42.1
0°-180°	9332.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2084	2084	2084	2084	2084	
5°	2094	2159	2094	1698	2094	199
15°	2000	2140	2000	1786	2000	563
25°	1761	1996	1761	1747	1761	809
35°	1339	1781	1339	1520	1339	828
45°	864	1467	864	1288	864	692
55°	704	1083	704	1057	704	647
65°	489	653	489	730	489	467
75°	185	310	185	371	185	195
85°	32	79	32	67	32	43
90°	4	16	4	16	4	5
95°	39	178	39	178	39	43
105°	140	1215	140	1215	140	148
115°	248	1565	248	1565	248	245
125°	346	1246	346	1246	346	307
135°	412	967	412	967	412	319
145°	478	784	478	784	478	299
155°	540	676	540	676	540	248
165°	582	629	582	629	582	164
175°	606	610	606	610	606	57
180°	606	606	606	606	606	

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3
2.5°	2102.1	2102.1	2113.9	2117.8	2117.8	2111.9	2106.0	2111.9	2129.7	2135.6	2133.6
5°	2094.2	2109.9	2131.6	2135.6	2139.5	2137.5	2133.6	2137.5	2157.3	2161.2	2163.2
7.5°	2078.4	2108.0	2135.6	2141.5	2147.4	2141.5	2139.5	2143.5	2163.2	2167.1	2167.1
10°	2058.7	2100.1	2131.6	2135.6	2141.5	2135.6	2135.6	2143.5	2163.2	2167.1	2169.1
12.5°	2031.1	2088.2	2117.8	2121.8	2129.7	2127.7	2125.7	2133.6	2153.3	2157.3	2157.3
15°	1999.5	2066.6	2094.2	2098.1	2111.9	2108.0	2108.0	2115.9	2137.5	2143.5	2141.5
17.5°	1956.1	2038.9	2070.5	2076.4	2086.3	2084.3	2086.3	2094.2	2113.9	2117.8	2119.8
20°	1906.8	2001.5	2038.9	2044.9	2054.7	2054.7	2054.7	2064.6	2084.3	2092.2	2092.2
22.5°	1839.8	1962.0	2001.5	2005.4	2017.3	2017.3	2021.2	2035.0	2052.8	2054.7	2054.7
25°	1760.9	1918.7	1952.2	1964.0	1975.8	1981.8	1987.7	1995.6	2001.5	1999.5	2001.5
27.5°	1678.1	1863.4	1906.8	1914.7	1930.5	1936.4	1944.3	1946.3	1948.2	1954.2	1950.2
30°	1585.4	1786.5	1851.6	1859.5	1885.1	1889.1	1881.2	1885.1	1895.0	1898.9	1902.9
32.5°	1480.9	1672.2	1794.4	1812.2	1835.8	1824.0	1822.0	1827.9	1843.7	1843.7	1847.7
35°	1338.9	1583.4	1741.2	1757.0	1774.7	1760.9	1768.8	1770.8	1780.6	1786.5	1784.6
37.5°	1183.1	1506.5	1686.0	1697.8	1711.6	1693.8	1705.7	1711.6	1719.5	1715.5	1715.5
40°	1045.2	1386.2	1620.9	1628.8	1640.6	1626.8	1638.6	1642.6	1646.5	1642.6	1640.6
42.5°	942.6	1254.1	1551.9	1561.7	1553.8	1563.7	1567.6	1575.5	1569.6	1561.7	1561.7
45°	863.7	1218.6	1476.9	1488.8	1476.9	1492.7	1498.6	1498.6	1480.9	1476.9	1475.0
47.5°	838.1	1147.7	1402.0	1402.0	1396.1	1415.8	1425.7	1411.9	1394.1	1388.2	1388.2
50°	836.1	1068.8	1299.4	1291.6	1319.2	1342.8	1333.0	1319.2	1305.4	1283.7	1283.7
52.5°	759.2	972.2	1167.4	1196.9	1240.3	1254.1	1238.3	1224.5	1200.8	1191.0	1183.1
55°	704.0	871.6	1047.1	1106.3	1151.6	1169.4	1139.8	1126.0	1090.5	1084.6	1080.7
57.5°	692.2	725.7	936.7	1011.6	1066.9	1064.9	1047.1	1021.5	991.9	986.0	984.0
60°	635.0	524.6	818.4	907.1	964.3	958.4	942.6	919.0	891.3	887.4	883.5
62.5°	575.8	380.6	684.3	784.9	865.7	863.7	849.9	814.4	794.7	784.9	777.0
65°	489.1	319.5	487.1	652.7	769.1	773.0	743.4	717.8	696.1	684.3	682.3
67.5°	372.7	260.3	329.3	544.3	676.4	672.5	635.0	623.2	595.5	589.6	577.8
70°	276.1	173.5	228.8	441.7	585.7	575.8	546.2	532.4	506.8	493.0	485.1
72.5°	228.8	140.0	167.6	343.1	493.0	481.2	455.5	439.8	418.1	406.2	398.3
75°	185.4	147.9	128.2	254.4	400.3	392.4	368.8	353.0	335.2	319.5	321.4
77.5°	136.1	138.0	102.5	187.3	317.5	305.7	291.9	272.1	264.2	248.5	248.5
80°	102.5	108.5	76.9	128.2	228.8	228.8	216.9	203.1	189.3	181.4	181.4
82.5°	69.0	69.0	57.2	80.9	155.8	149.9	142.0	138.0	130.2	126.2	126.2
85°	31.6	39.4	35.5	49.3	84.8	88.7	88.7	84.8	82.8	78.9	80.9
87.5°	9.9	17.7	21.7	27.6	43.4	45.4	47.3	47.3	47.3	49.3	49.3
90°	4.0	7.3	10.6	11.3	17.8	26.5	30.9	27.4	20.6	15.5	15.5
92.5°	16.3	43.9	71.6	78.5	110.3	152.7	173.9	152.4	109.4	77.2	74.1
95°	39.0	89.6	140.2	152.8	271.3	429.4	508.5	453.8	344.3	262.2	252.9
97.5°	67.4	112.0	156.7	167.8	365.5	629.1	760.9	726.3	657.1	605.2	587.5
100°	89.4	129.9	170.3	180.4	399.8	692.3	838.5	841.1	846.1	849.8	828.7
102.5°	108.2	145.9	183.6	193.1	415.5	712.2	860.5	904.6	992.7	1058.8	1040.7
105°	139.8	171.8	203.8	211.8	427.2	714.5	858.0	956.8	1154.5	1302.7	1292.9
107.5°	172.4	202.1	231.9	239.4	429.3	682.6	809.2	947.1	1222.7	1429.5	1431.9
110°	194.2	221.2	248.2	254.9	426.1	654.4	768.6	922.7	1230.8	1461.9	1472.1

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	215.8	241.5	267.1	273.5	426.2	629.9	731.6	889.3	1204.7	1441.2	1456.8
115°	248.4	272.0	295.7	301.6	430.2	601.7	687.3	839.3	1143.1	1370.9	1392.4
117.5°	280.4	301.9	323.4	328.8	438.2	583.9	656.8	793.9	1068.1	1273.8	1297.7
120°	299.2	319.4	339.7	344.7	444.7	578.0	644.6	769.9	1020.4	1208.3	1231.5
122.5°	317.4	337.8	358.2	363.3	454.0	574.8	635.3	748.1	973.8	1143.0	1165.8
125°	345.5	364.0	382.7	387.3	466.6	572.3	625.1	721.0	912.6	1056.4	1077.5
127.5°	368.3	387.0	405.7	410.5	479.2	570.8	616.5	698.9	863.4	986.9	1004.6
130°	380.4	400.6	420.9	426.0	488.4	571.7	613.3	686.6	833.1	942.9	959.4
132.5°	393.0	413.2	433.5	438.6	495.9	572.3	610.5	676.1	807.2	905.5	920.2
135°	411.8	430.2	448.5	453.2	503.9	571.7	605.6	660.5	770.4	852.7	865.4
137.5°	430.9	449.1	467.4	471.9	516.2	575.2	604.8	651.3	744.1	813.7	824.1
140°	446.7	463.5	480.3	484.5	523.7	575.8	602.0	642.1	722.2	782.4	792.1
142.5°	458.9	474.4	489.9	493.8	529.9	577.9	602.0	637.2	707.7	760.5	768.9
145°	477.6	491.1	504.7	508.1	538.1	578.0	597.9	626.7	684.4	727.6	733.9
147.5°	496.3	509.5	522.7	525.9	549.9	581.9	597.9	620.6	665.8	699.9	705.1
150°	508.5	520.4	532.3	535.3	556.2	584.0	597.9	617.0	655.4	684.1	688.3
152.5°	521.1	530.2	539.1	541.4	560.2	585.4	597.9	614.3	646.9	671.5	674.7
155°	539.7	546.4	553.1	554.8	569.2	588.3	597.9	610.9	636.9	656.4	658.5
157.5°	553.5	560.0	566.6	568.2	578.1	591.3	597.9	608.0	628.2	643.4	644.8
160°	562.9	568.0	573.1	574.3	582.2	592.7	597.9	606.6	623.8	636.9	637.7
162.5°	572.3	576.1	579.9	580.9	586.6	594.2	597.9	605.2	619.9	630.8	631.6
165°	582.4	585.9	589.2	590.1	592.7	596.1	597.9	603.1	613.6	621.5	622.4
167.5°	591.8	593.4	595.1	595.4	597.6	600.5	602.0	605.4	612.3	617.4	617.8
170°	597.9	599.5	601.2	601.6	601.7	601.9	602.0	605.4	612.3	617.4	617.4
172.5°	601.2	601.6	601.9	602.0	602.0	602.0	602.0	604.7	610.1	614.2	613.9
175°	605.6	605.6	605.6	605.6	604.4	602.7	602.0	603.6	607.1	609.6	609.6
177.5°	605.6	605.6	605.6	605.6	604.6	603.3	602.7	604.1	606.8	608.9	608.5
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3
2.5°	2137.5	2131.6	2137.5	2133.6	2135.6	2129.7	2111.9	2106.0	2111.9	2117.8	2117.8
5°	2163.2	2159.2	2163.2	2163.2	2161.2	2157.3	2137.5	2133.6	2137.5	2139.5	2135.6
7.5°	2171.1	2165.2	2171.1	2167.1	2167.1	2163.2	2143.5	2139.5	2141.5	2147.4	2141.5
10°	2171.1	2165.2	2171.1	2169.1	2167.1	2163.2	2143.5	2135.6	2135.6	2141.5	2135.6
12.5°	2161.2	2157.3	2161.2	2157.3	2157.3	2153.3	2133.6	2125.7	2127.7	2129.7	2121.8
15°	2145.4	2139.5	2145.4	2141.5	2143.5	2137.5	2115.9	2108.0	2108.0	2111.9	2098.1
17.5°	2121.8	2113.9	2121.8	2119.8	2117.8	2113.9	2094.2	2086.3	2084.3	2086.3	2076.4
20°	2094.2	2088.2	2094.2	2092.2	2092.2	2084.3	2064.6	2054.7	2054.7	2054.7	2044.9
22.5°	2050.8	2044.9	2050.8	2054.7	2054.7	2052.8	2035.0	2021.2	2017.3	2017.3	2005.4
25°	2001.5	1995.6	2001.5	2001.5	1999.5	2001.5	1995.6	1987.7	1981.8	1975.8	1964.0
27.5°	1954.2	1950.2	1954.2	1950.2	1954.2	1948.2	1946.3	1944.3	1936.4	1930.5	1914.7
30°	1906.8	1902.9	1906.8	1902.9	1898.9	1895.0	1885.1	1881.2	1889.1	1885.1	1859.5
32.5°	1847.7	1843.7	1847.7	1847.7	1843.7	1843.7	1827.9	1822.0	1824.0	1835.8	1812.2
35°	1786.5	1780.6	1786.5	1784.6	1786.5	1780.6	1770.8	1768.8	1760.9	1774.7	1757.0
37.5°	1715.5	1709.6	1715.5	1715.5	1715.5	1719.5	1711.6	1705.7	1693.8	1711.6	1697.8
40°	1642.6	1634.7	1642.6	1640.6	1642.6	1646.5	1642.6	1638.6	1626.8	1640.6	1628.8
42.5°	1559.8	1557.8	1559.8	1561.7	1561.7	1569.6	1575.5	1567.6	1563.7	1553.8	1561.7
45°	1471.0	1467.1	1471.0	1475.0	1476.9	1480.9	1498.6	1498.6	1492.7	1476.9	1488.8
47.5°	1376.4	1366.5	1376.4	1388.2	1388.2	1394.1	1411.9	1425.7	1415.8	1396.1	1402.0
50°	1275.8	1277.8	1275.8	1283.7	1283.7	1305.4	1319.2	1333.0	1342.8	1319.2	1291.6
52.5°	1177.2	1175.3	1177.2	1183.1	1191.0	1200.8	1224.5	1238.3	1254.1	1240.3	1196.9
55°	1078.7	1082.6	1078.7	1080.7	1084.6	1090.5	1126.0	1139.8	1169.4	1151.6	1106.3
57.5°	980.1	974.2	980.1	984.0	986.0	991.9	1021.5	1047.1	1064.9	1066.9	1011.6
60°	865.7	857.8	865.7	883.5	887.4	891.3	919.0	942.6	958.4	964.3	907.1
62.5°	765.1	751.3	765.1	777.0	784.9	794.7	814.4	849.9	863.7	865.7	784.9
65°	658.6	652.7	658.6	682.3	684.3	696.1	717.8	743.4	773.0	769.1	652.7
67.5°	562.0	562.0	562.0	577.8	589.6	595.5	623.2	635.0	672.5	676.4	544.3
70°	473.3	471.3	473.3	485.1	493.0	506.8	532.4	546.2	575.8	585.7	441.7
72.5°	388.5	386.5	388.5	398.3	406.2	418.1	439.8	455.5	481.2	493.0	343.1
75°	313.5	309.6	313.5	321.4	319.5	335.2	353.0	368.8	392.4	400.3	254.4
77.5°	240.6	240.6	240.6	248.5	248.5	264.2	272.1	291.9	305.7	317.5	187.3
80°	179.5	177.5	179.5	181.4	181.4	189.3	203.1	216.9	228.8	228.8	128.2
82.5°	126.2	122.3	126.2	126.2	126.2	130.2	138.0	142.0	149.9	155.8	80.9
85°	78.9	78.9	78.9	80.9	78.9	82.8	84.8	88.7	88.7	84.8	49.3
87.5°	51.3	49.3	51.3	49.3	49.3	47.3	47.3	47.3	45.4	43.4	27.6
90°	15.5	15.5	15.5	15.5	15.5	20.6	27.4	30.9	26.5	17.8	11.3
92.5°	61.8	49.6	61.8	74.1	77.2	109.4	152.4	173.9	152.7	110.3	78.5
95°	215.6	178.5	215.6	252.9	262.2	344.3	453.8	508.5	429.4	271.3	152.8
97.5°	516.7	445.9	516.7	587.5	605.2	657.1	726.3	760.9	629.1	365.5	167.8
100°	744.4	660.0	744.4	828.7	849.8	846.1	841.1	838.5	692.3	399.8	180.4
102.5°	968.4	896.2	968.4	1040.7	1058.8	992.7	904.6	860.5	712.2	415.5	193.1
105°	1254.1	1215.2	1254.1	1292.9	1302.7	1154.5	956.8	858.0	714.5	427.2	211.8
107.5°	1441.2	1450.6	1441.2	1431.9	1429.5	1222.7	947.1	809.2	682.6	429.3	239.4
110°	1512.5	1553.0	1512.5	1472.1	1461.9	1230.8	922.7	768.6	654.4	426.1	254.9

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1518.9	1581.1	1518.9	1456.8	1441.2	1204.7	889.3	731.6	629.9	426.2	273.5
115°	1478.6	1564.8	1478.6	1392.4	1370.9	1143.1	839.3	687.3	601.7	430.2	301.6
117.5°	1393.3	1488.9	1393.3	1297.7	1273.8	1068.1	793.9	656.8	583.9	438.2	328.8
120°	1324.4	1417.3	1324.4	1231.5	1208.3	1020.4	769.9	644.6	578.0	444.7	344.7
122.5°	1257.4	1349.0	1257.4	1165.8	1143.0	973.8	748.1	635.3	574.8	454.0	363.3
125°	1161.8	1246.2	1161.8	1077.5	1056.4	912.6	721.0	625.1	572.3	466.6	387.3
127.5°	1075.8	1147.0	1075.8	1004.6	986.9	863.4	698.9	616.5	570.8	479.2	410.5
130°	1025.1	1090.9	1025.1	959.4	942.9	833.1	686.6	613.3	571.7	488.4	426.0
132.5°	979.2	1038.1	979.2	920.2	905.5	807.2	676.1	610.5	572.3	495.9	438.6
135°	916.2	967.0	916.2	865.4	852.7	770.4	660.5	605.6	571.7	503.9	453.2
137.5°	865.7	907.2	865.7	824.1	813.7	744.1	651.3	604.8	575.2	516.2	471.9
140°	830.9	869.8	830.9	792.1	782.4	722.2	642.1	602.0	575.8	523.7	484.5
142.5°	802.2	835.6	802.2	768.9	760.5	707.7	637.2	602.0	577.9	529.9	493.8
145°	759.2	784.5	759.2	733.9	727.6	684.4	626.7	597.9	578.0	538.1	508.1
147.5°	726.1	747.1	726.1	705.1	699.9	665.8	620.6	597.9	581.9	549.9	525.9
150°	705.3	722.2	705.3	688.3	684.1	655.4	617.0	597.9	584.0	556.2	535.3
152.5°	687.5	700.4	687.5	674.7	671.5	646.9	614.3	597.9	585.4	560.2	541.4
155°	667.0	675.5	667.0	658.5	656.4	636.9	610.9	597.9	588.3	569.2	554.8
157.5°	650.9	656.8	650.9	644.8	643.4	628.2	608.0	597.9	591.3	578.1	568.2
160°	641.2	644.6	641.2	637.7	636.9	623.8	606.6	597.9	592.7	582.2	574.3
162.5°	634.9	638.1	634.9	631.6	630.8	619.9	605.2	597.9	594.2	586.6	580.9
165°	625.7	629.2	625.7	622.4	621.5	613.6	603.1	597.9	596.1	592.7	590.1
167.5°	619.2	620.7	619.2	617.8	617.4	612.3	605.4	602.0	600.5	597.6	595.4
170°	617.4	617.4	617.4	617.4	617.4	612.3	605.4	602.0	601.9	601.7	601.6
172.5°	612.6	611.3	612.6	613.9	614.2	610.1	604.7	602.0	602.0	602.0	602.0
175°	609.6	609.6	609.6	609.6	609.6	607.1	603.6	602.0	602.7	604.4	605.6
177.5°	607.1	605.6	607.1	608.5	608.9	606.8	604.1	602.7	603.3	604.6	605.6
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3
2.5°	2113.9	2102.1	2102.1	2082.3	2074.4	2068.5	2058.7	2029.1	2021.2	2013.3	2025.1
5°	2131.6	2109.9	2094.2	2058.7	2029.1	2017.3	1979.8	1908.8	1861.5	1826.0	1806.3
7.5°	2135.6	2108.0	2078.4	2023.2	1952.2	1920.6	1806.3	1676.1	1640.6	1609.1	1589.3
10°	2131.6	2100.1	2058.7	1975.8	1808.2	1753.0	1638.6	1553.8	1532.1	1526.2	1532.1
12.5°	2117.8	2088.2	2031.1	1893.0	1658.4	1620.9	1553.8	1504.5	1500.6	1510.5	1563.7
15°	2094.2	2066.6	1999.5	1782.6	1575.5	1547.9	1500.6	1482.8	1504.5	1573.6	1733.3
17.5°	2070.5	2038.9	1956.1	1674.1	1512.4	1492.7	1459.2	1494.7	1616.9	1709.6	1762.9
20°	2038.9	2001.5	1906.8	1595.2	1467.1	1449.3	1433.5	1593.3	1686.0	1719.5	1749.1
22.5°	2001.5	1962.0	1839.8	1540.0	1419.7	1405.9	1415.8	1648.5	1686.0	1709.6	1735.3
25°	1952.2	1918.7	1760.9	1496.6	1382.3	1366.5	1404.0	1642.6	1664.3	1670.2	1721.5
27.5°	1906.8	1863.4	1678.1	1457.2	1336.9	1331.0	1413.8	1616.9	1632.7	1638.6	1693.8
30°	1851.6	1786.5	1585.4	1415.8	1289.6	1287.6	1415.8	1585.4	1581.4	1597.2	1652.4
32.5°	1794.4	1672.2	1480.9	1364.5	1244.2	1242.3	1402.0	1538.1	1534.1	1555.8	1597.2
35°	1741.2	1583.4	1338.9	1305.4	1187.0	1189.0	1368.5	1482.8	1484.8	1504.5	1530.2
37.5°	1686.0	1506.5	1183.1	1240.3	1131.9	1131.9	1323.1	1431.6	1427.6	1433.5	1469.0
40°	1620.9	1386.2	1045.2	1155.6	1080.7	1074.7	1267.9	1376.4	1362.6	1360.6	1409.9
42.5°	1551.9	1254.1	942.6	1043.2	1021.5	1013.6	1200.8	1309.3	1283.7	1289.6	1352.7
45°	1476.9	1218.6	863.7	881.5	960.4	954.4	1128.0	1232.4	1214.7	1230.4	1295.5
47.5°	1402.0	1147.7	838.1	731.6	895.3	893.3	1047.1	1157.6	1147.7	1163.5	1232.4
50°	1299.4	1068.8	836.1	627.1	822.3	830.2	950.5	1084.6	1084.6	1098.4	1171.4
52.5°	1167.4	972.2	759.2	567.9	737.5	761.2	865.7	1021.5	1025.4	1039.2	1104.3
55°	1047.1	871.6	704.0	522.6	637.0	688.2	782.9	956.4	964.3	978.1	1037.3
57.5°	936.7	725.7	692.2	469.3	544.3	593.6	709.9	893.3	897.3	909.1	966.3
60°	818.4	524.6	635.0	412.1	463.4	500.9	642.9	818.4	832.2	840.1	889.4
62.5°	684.3	380.6	575.8	372.7	424.0	431.9	587.7	747.4	765.1	771.1	800.6
65°	487.1	319.5	489.1	339.2	382.6	384.5	528.5	674.4	690.2	700.1	721.8
67.5°	329.3	260.3	372.7	307.6	351.0	353.0	471.3	589.6	611.3	619.2	633.0
70°	228.8	173.5	276.1	274.1	315.5	319.5	410.2	512.7	532.4	538.4	546.2
72.5°	167.6	140.0	228.8	246.5	278.1	282.0	347.1	426.0	445.7	451.6	455.5
75°	128.2	147.9	185.4	214.9	236.6	238.6	284.0	347.1	360.9	364.8	366.8
77.5°	102.5	138.0	136.1	173.5	193.3	189.3	222.8	268.2	280.0	280.0	280.0
80°	76.9	108.5	102.5	124.2	142.0	138.0	159.7	191.3	195.2	199.2	197.2
82.5°	57.2	69.0	69.0	78.9	94.7	90.7	106.5	124.2	124.2	124.2	128.2
85°	35.5	39.4	31.6	41.4	53.2	51.3	59.2	67.0	69.0	69.0	65.1
87.5°	21.7	17.7	9.9	15.8	23.7	23.7	27.6	29.6	27.6	27.6	27.6
90°	10.6	7.3	4.0	7.3	10.6	11.3	17.8	26.5	30.9	27.4	20.6
92.5°	71.6	43.9	16.3	43.9	71.6	78.5	110.3	152.7	173.9	152.4	109.4
95°	140.2	89.6	39.0	89.6	140.2	152.8	271.3	429.4	508.5	453.8	344.3
97.5°	156.7	112.0	67.4	112.0	156.7	167.8	365.5	629.1	760.9	726.3	657.1
100°	170.3	129.9	89.4	129.9	170.3	180.4	399.8	692.3	838.5	841.1	846.1
102.5°	183.6	145.9	108.2	145.9	183.6	193.1	415.5	712.2	860.5	904.6	992.7
105°	203.8	171.8	139.8	171.8	203.8	211.8	427.2	714.5	858.0	956.8	1154.5
107.5°	231.9	202.1	172.4	202.1	231.9	239.4	429.3	682.6	809.2	947.1	1222.7
110°	248.2	221.2	194.2	221.2	248.2	254.9	426.1	654.4	768.6	922.7	1230.8

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	267.1	241.5	215.8	241.5	267.1	273.5	426.2	629.9	731.6	889.3	1204.7
115°	295.7	272.0	248.4	272.0	295.7	301.6	430.2	601.7	687.3	839.3	1143.1
117.5°	323.4	301.9	280.4	301.9	323.4	328.8	438.2	583.9	656.8	793.9	1068.1
120°	339.7	319.4	299.2	319.4	339.7	344.7	444.7	578.0	644.6	769.9	1020.4
122.5°	358.2	337.8	317.4	337.8	358.2	363.3	454.0	574.8	635.3	748.1	973.8
125°	382.7	364.0	345.5	364.0	382.7	387.3	466.6	572.3	625.1	721.0	912.6
127.5°	405.7	387.0	368.3	387.0	405.7	410.5	479.2	570.8	616.5	698.9	863.4
130°	420.9	400.6	380.4	400.6	420.9	426.0	488.4	571.7	613.3	686.6	833.1
132.5°	433.5	413.2	393.0	413.2	433.5	438.6	495.9	572.3	610.5	676.1	807.2
135°	448.5	430.2	411.8	430.2	448.5	453.2	503.9	571.7	605.6	660.5	770.4
137.5°	467.4	449.1	430.9	449.1	467.4	471.9	516.2	575.2	604.8	651.3	744.1
140°	480.3	463.5	446.7	463.5	480.3	484.5	523.7	575.8	602.0	642.1	722.2
142.5°	489.9	474.4	458.9	474.4	489.9	493.8	529.9	577.9	602.0	637.2	707.7
145°	504.7	491.1	477.6	491.1	504.7	508.1	538.1	578.0	597.9	626.7	684.4
147.5°	522.7	509.5	496.3	509.5	522.7	525.9	549.9	581.9	597.9	620.6	665.8
150°	532.3	520.4	508.5	520.4	532.3	535.3	556.2	584.0	597.9	617.0	655.4
152.5°	539.1	530.2	521.1	530.2	539.1	541.4	560.2	585.4	597.9	614.3	646.9
155°	553.1	546.4	539.7	546.4	553.1	554.8	569.2	588.3	597.9	610.9	636.9
157.5°	566.6	560.0	553.5	560.0	566.6	568.2	578.1	591.3	597.9	608.0	628.2
160°	573.1	568.0	562.9	568.0	573.1	574.3	582.2	592.7	597.9	606.6	623.8
162.5°	579.9	576.1	572.3	576.1	579.9	580.9	586.6	594.2	597.9	605.2	619.9
165°	589.2	585.9	582.4	585.9	589.2	590.1	592.7	596.1	597.9	603.1	613.6
167.5°	595.1	593.4	591.8	593.4	595.1	595.4	597.6	600.5	602.0	605.4	612.3
170°	601.2	599.5	597.9	599.5	601.2	601.6	601.7	601.9	602.0	605.4	612.3
172.5°	601.9	601.6	601.2	601.6	601.9	602.0	602.0	602.0	602.0	604.7	610.1
175°	605.6	605.6	605.6	605.6	605.6	605.6	604.4	602.7	602.0	603.6	607.1
177.5°	605.6	605.6	605.6	605.6	605.6	605.6	604.6	603.3	602.7	604.1	606.8
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3	2084.3
2.5°	2011.3	2005.4	2013.3	1991.6	2013.3	2005.4	2011.3	2025.1	2013.3	2021.2	2029.1
5°	1764.8	1755.0	1723.4	1697.8	1723.4	1755.0	1764.8	1806.3	1826.0	1861.5	1908.8
7.5°	1577.5	1569.6	1561.7	1545.9	1561.7	1569.6	1577.5	1589.3	1609.1	1640.6	1676.1
10°	1536.1	1538.1	1549.9	1547.9	1549.9	1538.1	1536.1	1532.1	1526.2	1532.1	1553.8
12.5°	1642.6	1660.3	1725.4	1721.5	1725.4	1660.3	1642.6	1563.7	1510.5	1500.6	1504.5
15°	1764.8	1770.8	1784.6	1786.5	1784.6	1770.8	1764.8	1733.3	1573.6	1504.5	1482.8
17.5°	1776.7	1778.6	1788.5	1788.5	1788.5	1778.6	1776.7	1762.9	1709.6	1616.9	1494.7
20°	1766.8	1770.8	1790.5	1794.4	1790.5	1770.8	1766.8	1749.1	1719.5	1686.0	1593.3
22.5°	1762.9	1770.8	1786.5	1784.6	1786.5	1770.8	1762.9	1735.3	1709.6	1686.0	1648.5
25°	1743.1	1743.1	1745.1	1747.1	1745.1	1743.1	1743.1	1721.5	1670.2	1664.3	1642.6
27.5°	1701.7	1705.7	1717.5	1715.5	1717.5	1705.7	1701.7	1693.8	1638.6	1632.7	1616.9
30°	1664.3	1660.3	1650.5	1642.6	1650.5	1660.3	1664.3	1652.4	1597.2	1581.4	1585.4
32.5°	1601.2	1591.3	1581.4	1575.5	1581.4	1591.3	1601.2	1597.2	1555.8	1534.1	1538.1
35°	1526.2	1528.2	1526.2	1520.3	1526.2	1528.2	1526.2	1530.2	1504.5	1484.8	1482.8
37.5°	1473.0	1476.9	1475.0	1467.1	1475.0	1476.9	1473.0	1469.0	1433.5	1427.6	1431.6
40°	1417.8	1419.7	1417.8	1411.9	1417.8	1419.7	1417.8	1409.9	1360.6	1362.6	1376.4
42.5°	1364.5	1362.6	1356.6	1352.7	1356.6	1362.6	1364.5	1352.7	1289.6	1283.7	1309.3
45°	1303.4	1305.4	1293.5	1287.6	1293.5	1305.4	1303.4	1295.5	1230.4	1214.7	1232.4
47.5°	1242.3	1242.3	1232.4	1226.5	1232.4	1242.3	1242.3	1232.4	1163.5	1147.7	1157.6
50°	1177.2	1175.3	1161.5	1159.5	1161.5	1175.3	1177.2	1171.4	1098.4	1084.6	1084.6
52.5°	1102.3	1102.3	1104.3	1108.3	1104.3	1102.3	1102.3	1104.3	1039.2	1025.4	1021.5
55°	1037.3	1039.2	1053.0	1057.0	1053.0	1039.2	1037.3	1037.3	978.1	964.3	956.4
57.5°	970.2	970.2	980.1	980.1	980.1	970.2	970.2	966.3	909.1	897.3	893.3
60°	893.3	897.3	905.1	903.2	905.1	897.3	893.3	889.4	840.1	832.2	818.4
62.5°	812.5	816.4	818.4	814.4	818.4	816.4	812.5	800.6	771.1	765.1	747.4
65°	727.7	731.6	733.6	729.6	733.6	731.6	727.7	721.8	700.1	690.2	674.4
67.5°	640.9	638.9	637.0	644.8	637.0	638.9	640.9	633.0	619.2	611.3	589.6
70°	552.2	552.2	550.2	554.1	550.2	552.2	552.2	546.2	538.4	532.4	512.7
72.5°	457.5	455.5	463.4	457.5	463.4	455.5	457.5	455.5	451.6	445.7	426.0
75°	364.8	368.8	364.8	370.7	364.8	368.8	364.8	366.8	364.8	360.9	347.1
77.5°	278.1	282.0	278.1	278.1	278.1	282.0	278.1	280.0	280.0	280.0	268.2
80°	197.2	195.2	195.2	193.3	195.2	195.2	197.2	197.2	199.2	195.2	191.3
82.5°	126.2	124.2	124.2	128.2	124.2	124.2	126.2	128.2	124.2	124.2	124.2
85°	69.0	71.0	67.0	67.0	67.0	71.0	69.0	65.1	69.0	69.0	67.0
87.5°	25.6	23.7	23.7	23.7	23.7	23.7	25.6	27.6	27.6	27.6	29.6
90°	15.5	15.5	15.5	15.5	15.5	15.5	15.5	20.6	27.4	30.9	26.5
92.5°	77.2	74.1	61.8	49.6	61.8	74.1	77.2	109.4	152.4	173.9	152.7
95°	262.2	252.9	215.6	178.5	215.6	252.9	262.2	344.3	453.8	508.5	429.4
97.5°	605.2	587.5	516.7	445.9	516.7	587.5	605.2	657.1	726.3	760.9	629.1
100°	849.8	828.7	744.4	660.0	744.4	828.7	849.8	846.1	841.1	838.5	692.3
102.5°	1058.8	1040.7	968.4	896.2	968.4	1040.7	1058.8	992.7	904.6	860.5	712.2
105°	1302.7	1292.9	1254.1	1215.2	1254.1	1292.9	1302.7	1154.5	956.8	858.0	714.5
107.5°	1429.5	1431.9	1441.2	1450.6	1441.2	1431.9	1429.5	1222.7	947.1	809.2	682.6
110°	1461.9	1472.1	1512.5	1553.0	1512.5	1472.1	1461.9	1230.8	922.7	768.6	654.4

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1441.2	1456.8	1518.9	1581.1	1518.9	1456.8	1441.2	1204.7	889.3	731.6	629.9
115°	1370.9	1392.4	1478.6	1564.8	1478.6	1392.4	1370.9	1143.1	839.3	687.3	601.7
117.5°	1273.8	1297.7	1393.3	1488.9	1393.3	1297.7	1273.8	1068.1	793.9	656.8	583.9
120°	1208.3	1231.5	1324.4	1417.3	1324.4	1231.5	1208.3	1020.4	769.9	644.6	578.0
122.5°	1143.0	1165.8	1257.4	1349.0	1257.4	1165.8	1143.0	973.8	748.1	635.3	574.8
125°	1056.4	1077.5	1161.8	1246.2	1161.8	1077.5	1056.4	912.6	721.0	625.1	572.3
127.5°	986.9	1004.6	1075.8	1147.0	1075.8	1004.6	986.9	863.4	698.9	616.5	570.8
130°	942.9	959.4	1025.1	1090.9	1025.1	959.4	942.9	833.1	686.6	613.3	571.7
132.5°	905.5	920.2	979.2	1038.1	979.2	920.2	905.5	807.2	676.1	610.5	572.3
135°	852.7	865.4	916.2	967.0	916.2	865.4	852.7	770.4	660.5	605.6	571.7
137.5°	813.7	824.1	865.7	907.2	865.7	824.1	813.7	744.1	651.3	604.8	575.2
140°	782.4	792.1	830.9	869.8	830.9	792.1	782.4	722.2	642.1	602.0	575.8
142.5°	760.5	768.9	802.2	835.6	802.2	768.9	760.5	707.7	637.2	602.0	577.9
145°	727.6	733.9	759.2	784.5	759.2	733.9	727.6	684.4	626.7	597.9	578.0
147.5°	699.9	705.1	726.1	747.1	726.1	705.1	699.9	665.8	620.6	597.9	581.9
150°	684.1	688.3	705.3	722.2	705.3	688.3	684.1	655.4	617.0	597.9	584.0
152.5°	671.5	674.7	687.5	700.4	687.5	674.7	671.5	646.9	614.3	597.9	585.4
155°	656.4	658.5	667.0	675.5	667.0	658.5	656.4	636.9	610.9	597.9	588.3
157.5°	643.4	644.8	650.9	656.8	650.9	644.8	643.4	628.2	608.0	597.9	591.3
160°	636.9	637.7	641.2	644.6	641.2	637.7	636.9	623.8	606.6	597.9	592.7
162.5°	630.8	631.6	634.9	638.1	634.9	631.6	630.8	619.9	605.2	597.9	594.2
165°	621.5	622.4	625.7	629.2	625.7	622.4	621.5	613.6	603.1	597.9	596.1
167.5°	617.4	617.8	619.2	620.7	619.2	617.8	617.4	612.3	605.4	602.0	600.5
170°	617.4	617.4	617.4	617.4	617.4	617.4	617.4	612.3	605.4	602.0	601.9
172.5°	614.2	613.9	612.6	611.3	612.6	613.9	614.2	610.1	604.7	602.0	602.0
175°	609.6	609.6	609.6	609.6	609.6	609.6	609.6	607.1	603.6	602.0	602.7
177.5°	608.9	608.5	607.1	605.6	607.1	608.5	608.9	606.8	604.1	602.7	603.3
180°	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2084.3	2084.3	2084.3	2084.3	2084.3
2.5°	2058.7	2068.5	2074.4	2082.3	2102.1
5°	1979.8	2017.3	2029.1	2058.7	2094.2
7.5°	1806.3	1920.6	1952.2	2023.2	2078.4
10°	1638.6	1753.0	1808.2	1975.8	2058.7
12.5°	1553.8	1620.9	1658.4	1893.0	2031.1
15°	1500.6	1547.9	1575.5	1782.6	1999.5
17.5°	1459.2	1492.7	1512.4	1674.1	1956.1
20°	1433.5	1449.3	1467.1	1595.2	1906.8
22.5°	1415.8	1405.9	1419.7	1540.0	1839.8
25°	1404.0	1366.5	1382.3	1496.6	1760.9
27.5°	1413.8	1331.0	1336.9	1457.2	1678.1
30°	1415.8	1287.6	1289.6	1415.8	1585.4
32.5°	1402.0	1242.3	1244.2	1364.5	1480.9
35°	1368.5	1189.0	1187.0	1305.4	1338.9
37.5°	1323.1	1131.9	1131.9	1240.3	1183.1
40°	1267.9	1074.7	1080.7	1155.6	1045.2
42.5°	1200.8	1013.6	1021.5	1043.2	942.6
45°	1128.0	954.4	960.4	881.5	863.7
47.5°	1047.1	893.3	895.3	731.6	838.1
50°	950.5	830.2	822.3	627.1	836.1
52.5°	865.7	761.2	737.5	567.9	759.2
55°	782.9	688.2	637.0	522.6	704.0
57.5°	709.9	593.6	544.3	469.3	692.2
60°	642.9	500.9	463.4	412.1	635.0
62.5°	587.7	431.9	424.0	372.7	575.8
65°	528.5	384.5	382.6	339.2	489.1
67.5°	471.3	353.0	351.0	307.6	372.7
70°	410.2	319.5	315.5	274.1	276.1
72.5°	347.1	282.0	278.1	246.5	228.8
75°	284.0	238.6	236.6	214.9	185.4
77.5°	222.8	189.3	193.3	173.5	136.1
80°	159.7	138.0	142.0	124.2	102.5
82.5°	106.5	90.7	94.7	78.9	69.0
85°	59.2	51.3	53.2	41.4	31.6
87.5°	27.6	23.7	23.7	15.8	9.9
90°	17.8	11.3	10.6	7.3	4.0
92.5°	110.3	78.5	71.6	43.9	16.3
95°	271.3	152.8	140.2	89.6	39.0
97.5°	365.5	167.8	156.7	112.0	67.4
100°	399.8	180.4	170.3	129.9	89.4
102.5°	415.5	193.1	183.6	145.9	108.2
105°	427.2	211.8	203.8	171.8	139.8
107.5°	429.3	239.4	231.9	202.1	172.4
110°	426.1	254.9	248.2	221.2	194.2



TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	426.2	273.5	267.1	241.5	215.8
115°	430.2	301.6	295.7	272.0	248.4
117.5°	438.2	328.8	323.4	301.9	280.4
120°	444.7	344.7	339.7	319.4	299.2
122.5°	454.0	363.3	358.2	337.8	317.4
125°	466.6	387.3	382.7	364.0	345.5
127.5°	479.2	410.5	405.7	387.0	368.3
130°	488.4	426.0	420.9	400.6	380.4
132.5°	495.9	438.6	433.5	413.2	393.0
135°	503.9	453.2	448.5	430.2	411.8
137.5°	516.2	471.9	467.4	449.1	430.9
140°	523.7	484.5	480.3	463.5	446.7
142.5°	529.9	493.8	489.9	474.4	458.9
145°	538.1	508.1	504.7	491.1	477.6
147.5°	549.9	525.9	522.7	509.5	496.3
150°	556.2	535.3	532.3	520.4	508.5
152.5°	560.2	541.4	539.1	530.2	521.1
155°	569.2	554.8	553.1	546.4	539.7
157.5°	578.1	568.2	566.6	560.0	553.5
160°	582.2	574.3	573.1	568.0	562.9
162.5°	586.6	580.9	579.9	576.1	572.3
165°	592.7	590.1	589.2	585.9	582.4
167.5°	597.6	595.4	595.1	593.4	591.8
170°	601.7	601.6	601.2	599.5	597.9
172.5°	602.0	602.0	601.9	601.6	601.2
175°	604.4	605.6	605.6	605.6	605.6
177.5°	604.6	605.6	605.6	605.6	605.6
180°	605.6	605.6	605.6	605.6	605.6

TEST NUMBER: P934393

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.39	14.33	14.28	15.24	16.39	16.23	17.17	17.12	18.07	19.23
	3H	13.88	14.72	14.77	15.63	16.81	17.58	18.42	18.48	19.34	20.52
	4H	14.07	14.86	14.98	15.79	16.97	18.03	18.83	18.95	19.75	20.94
	6H	14.19	14.93	15.12	15.85	17.05	18.32	19.06	19.25	19.98	21.19
	8H	14.20	14.89	15.13	15.84	17.04	18.40	19.10	19.34	20.04	21.24
	12H	14.17	14.83	15.11	15.77	17.00	18.44	19.11	19.38	20.05	21.27
4H	2H	14.44	15.23	15.36	16.15	17.34	16.65	17.44	17.57	18.36	19.55
	3H	15.47	16.13	16.40	17.09	18.29	18.16	18.83	19.09	19.78	20.98
	4H	15.75	16.35	16.69	17.30	18.53	18.70	19.30	19.64	20.25	21.48
	6H	15.88	16.40	16.83	17.37	18.60	19.07	19.59	20.02	20.56	21.79
	8H	15.89	16.37	16.84	17.34	18.58	19.18	19.66	20.13	20.63	21.87
	12H	15.86	16.30	16.83	17.28	18.53	19.24	19.68	20.21	20.66	21.91
8H	4H	16.21	16.70	17.17	17.66	18.90	18.83	19.31	19.78	20.28	21.52
	6H	16.48	16.88	17.46	17.88	19.13	19.27	19.67	20.25	20.68	21.92
	8H	16.52	16.87	17.51	17.87	19.13	19.42	19.78	20.41	20.77	22.03
	12H	16.51	16.82	17.50	17.81	19.11	19.53	19.84	20.52	20.83	22.13
12H	4H	16.22	16.66	17.20	17.64	18.89	18.80	19.23	19.77	20.22	21.46
	6H	16.54	16.89	17.53	17.89	19.15	19.27	19.62	20.26	20.62	21.88
	8H	16.61	16.92	17.60	17.91	19.22	19.43	19.75	20.43	20.73	22.04

END OF REPORT