

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934588

Luminaire Tested: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934588
REPORT IS A COMBINATION OF REPORTS P933703 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9804.8 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63	63	63	59
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	56	53	53	53	50
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	52	48	45	45	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	39	39	36
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	34	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	30	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	27	27	24
8	57	44	36	30	54	42	35	29	38	32	28	35	29	26	31	27	24	24	24	22
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21	21	21	19
10	49	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	19	19	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16364	16364	16364	16364
5°	16480	16518	16480	12988
10°	16364	16272	16364	11633
15°	16180	15919	16180	13292
20°	15835	15502	15835	13321
25°	15136	14892	15136	13038
30°	14235	14387	14235	12419
35°	12685	13747	12685	11737
40°	10564	12994	10564	11223
45°	9432	12113	9432	10631
50°	10013	11061	10013	10037
55°	9412	9928	9412	9694
60°	9691	8432	9691	8878
65°	8772	6970	8772	7792
70°	6058	5555	6058	6531
75°	5295	4106	5295	4917
80°	4238	2714	4238	2955
85°	2385	1438	2385	1222

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14466 cd/sqm

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.8	2.4
10°-20°	678.0	6.9
20°-30°	1048.0	10.7
30°-40°	1251.1	12.8
40°-50°	1258.4	12.8
50°-60°	1095.0	11.2
60°-70°	776.4	7.9
70°-80°	410.7	4.2
80°-90°	104.0	1.1
90°-100°	221.4	2.3
100°-110°	582.1	5.9
110°-120°	603.6	6.2
120°-130°	484.1	4.9
130°-140°	379.9	3.9
140°-150°	291.6	3.0
150°-160°	210.0	2.1
160°-170°	128.5	1.3
170°-180°	43.4	0.4
0°-30°	1964.7	20.0
0°-40°	3215.8	32.8
0°-60°	5569.2	56.8
0°-90°	6860.4	70.0
90°-120°	1407.0	14.4
90°-150°	2562.6	26.1
90°-180°	2944.0	30.0
0°-180°	9804.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2645	2645	2645	2645	2645	
5°	2658	2740	2658	2155	2658	252
15°	2538	2715	2538	2267	2538	714
25°	2235	2533	2235	2217	2235	1026
35°	1699	2260	1699	1930	1699	1051
45°	1096	1862	1096	1634	1096	878
55°	893	1374	893	1341	893	821
65°	621	828	621	926	621	593
75°	235	393	235	470	235	247
85°	40	100	40	85	40	54
90°	3	12	3	12	3	4
95°	29	134	29	134	29	32
105°	105	912	105	912	105	111
115°	186	1174	186	1174	186	184
125°	259	935	259	935	259	230
135°	309	725	309	725	309	239
145°	358	588	358	588	358	224
155°	405	507	405	507	405	186
165°	437	472	437	472	437	123
175°	454	457	454	457	454	43
180°	454	454	454	454	454	

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2
2.5°	2667.7	2667.7	2682.8	2687.7	2687.7	2680.2	2672.8	2680.2	2702.8	2710.3	2707.8
5°	2657.8	2677.8	2705.3	2710.3	2715.3	2712.8	2707.8	2712.8	2737.8	2742.9	2745.3
7.5°	2637.7	2675.2	2710.3	2717.8	2725.3	2717.8	2715.3	2720.3	2745.3	2750.3	2750.3
10°	2612.7	2665.3	2705.3	2710.3	2717.8	2710.3	2710.3	2720.3	2745.3	2750.3	2752.8
12.5°	2577.7	2650.3	2687.7	2692.8	2702.8	2700.3	2697.8	2707.8	2732.8	2737.8	2737.8
15°	2537.7	2622.7	2657.8	2662.8	2680.2	2675.2	2675.2	2685.3	2712.8	2720.3	2717.8
17.5°	2482.6	2587.7	2627.7	2635.2	2647.7	2645.2	2647.7	2657.8	2682.8	2687.7	2690.3
20°	2420.0	2540.1	2587.7	2595.2	2607.7	2607.7	2607.7	2620.2	2645.2	2655.2	2655.2
22.5°	2334.9	2490.0	2540.1	2545.2	2560.1	2560.1	2565.2	2582.6	2605.2	2607.7	2607.7
25°	2234.8	2435.0	2477.5	2492.6	2507.6	2515.1	2522.6	2532.6	2540.1	2537.7	2540.1
27.5°	2129.7	2364.9	2420.0	2430.0	2450.0	2457.5	2467.6	2470.0	2472.6	2480.1	2475.1
30°	2012.0	2267.3	2349.9	2359.9	2392.4	2397.5	2387.5	2392.4	2405.0	2410.0	2415.0
32.5°	1879.4	2122.2	2277.4	2299.8	2329.9	2314.9	2312.4	2319.9	2339.9	2339.9	2344.9
35°	1699.3	2009.6	2209.8	2229.8	2252.3	2234.8	2244.8	2247.3	2259.8	2267.3	2264.8
37.5°	1501.6	1912.0	2139.7	2154.7	2172.3	2149.7	2164.8	2172.3	2182.2	2177.3	2177.3
40°	1326.4	1759.3	2057.1	2067.1	2082.1	2064.6	2079.7	2084.7	2089.6	2084.7	2082.1
42.5°	1196.2	1591.6	1969.5	1982.1	1972.0	1984.5	1989.6	1999.6	1992.0	1982.1	1982.1
45°	1096.1	1546.6	1874.4	1889.5	1874.4	1894.5	1902.0	1902.0	1879.4	1874.4	1871.9
47.5°	1063.6	1456.5	1779.3	1779.3	1771.8	1796.9	1809.4	1791.9	1769.3	1761.8	1761.8
50°	1061.1	1356.4	1649.2	1639.2	1674.2	1704.3	1691.8	1674.2	1656.7	1629.2	1629.2
52.5°	963.5	1233.8	1481.6	1519.0	1574.1	1591.6	1571.6	1554.1	1524.1	1511.5	1501.6
55°	893.4	1106.1	1328.8	1404.0	1461.5	1484.0	1446.5	1429.0	1383.9	1376.5	1371.4
57.5°	878.4	920.9	1188.7	1283.9	1353.9	1351.4	1328.8	1296.3	1258.8	1251.3	1248.8
60°	805.9	665.6	1038.6	1151.2	1223.7	1216.2	1196.2	1166.2	1131.1	1126.2	1121.2
62.5°	730.7	483.0	868.4	996.1	1098.6	1096.1	1078.6	1033.5	1008.6	996.1	986.0
65°	620.7	405.4	618.1	828.3	976.0	981.0	943.5	911.0	883.5	868.4	865.9
67.5°	473.0	330.3	418.0	690.7	858.4	853.4	805.9	790.8	755.8	748.3	733.3
70°	350.3	220.3	290.3	560.5	743.2	730.7	693.3	675.7	643.2	625.6	615.7
72.5°	290.3	177.7	212.7	435.4	625.6	610.6	578.1	558.1	530.6	515.6	505.5
75°	235.3	187.7	162.7	322.8	508.0	498.0	468.0	447.9	425.5	405.4	407.9
77.5°	172.6	175.2	130.2	237.7	402.9	387.9	370.3	345.4	335.3	315.3	315.3
80°	130.2	137.6	97.6	162.7	290.3	290.3	275.3	257.7	240.3	230.2	230.2
82.5°	87.6	87.6	72.6	102.6	197.7	190.2	180.1	175.2	165.2	160.1	160.1
85°	40.0	50.1	45.1	62.6	107.6	112.6	112.6	107.6	105.1	100.1	102.6
87.5°	12.5	22.5	27.5	35.0	55.0	57.6	60.0	60.0	60.0	62.6	62.6
90°	3.1	5.5	8.0	8.6	13.4	19.9	23.2	20.6	15.4	11.5	11.5
92.5°	12.2	32.9	53.6	58.9	82.7	114.6	130.4	114.3	82.0	57.9	55.6
95°	29.3	67.1	105.1	114.6	203.5	322.1	381.4	340.4	258.2	196.6	189.6
97.5°	50.6	84.1	117.5	125.9	274.2	471.9	570.7	544.8	492.8	453.9	440.5
100°	67.0	97.4	127.8	135.4	299.8	519.2	628.9	630.7	634.6	637.4	621.7
102.5°	81.0	109.4	137.7	144.8	311.7	534.1	645.3	678.4	744.5	794.1	780.6
105°	104.9	128.9	152.8	158.8	320.4	535.8	643.5	717.6	865.8	977.0	969.7
107.5°	129.3	151.6	173.9	179.6	322.0	511.9	606.9	710.2	917.0	1072.1	1073.9
110°	145.7	165.8	186.1	191.1	319.6	490.8	576.4	692.0	923.2	1096.5	1104.1

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	161.9	181.1	200.4	205.2	319.7	472.4	548.7	667.0	903.6	1081.0	1092.6
115°	186.3	204.0	221.8	226.2	322.6	451.2	515.5	629.5	857.3	1028.2	1044.4
117.5°	210.3	226.5	242.6	246.6	328.6	438.0	492.6	595.4	801.1	955.3	973.3
120°	224.3	239.5	254.7	258.5	333.5	433.4	483.4	577.4	765.3	906.2	923.7
122.5°	238.1	253.4	268.7	272.5	340.5	431.1	476.4	561.0	730.3	857.2	874.4
125°	259.1	273.0	287.0	290.5	349.9	429.2	468.8	540.7	684.5	792.3	808.0
127.5°	276.2	290.3	304.4	307.9	359.4	428.1	462.4	524.2	647.5	740.1	753.4
130°	285.3	300.5	315.7	319.5	366.3	428.7	460.0	514.9	624.8	707.3	719.6
132.5°	294.8	310.0	325.2	328.9	371.9	429.2	457.9	507.1	605.4	679.2	690.2
135°	308.8	322.6	336.4	339.9	378.0	428.8	454.3	495.5	577.8	639.5	649.1
137.5°	323.1	336.8	350.4	353.9	387.1	431.4	453.6	488.4	558.0	610.2	618.0
140°	335.0	347.7	360.2	363.3	392.7	431.9	451.5	481.6	541.7	586.8	594.1
142.5°	344.1	355.7	367.4	370.3	397.4	433.4	451.5	477.9	530.7	570.3	576.6
145°	358.2	368.4	378.5	381.1	403.6	433.4	448.4	470.0	513.2	545.7	550.4
147.5°	372.2	382.1	392.0	394.5	412.4	436.4	448.4	465.4	499.4	524.9	528.9
150°	381.4	390.4	399.2	401.5	417.2	438.0	448.4	462.8	491.5	513.0	516.2
152.5°	390.8	397.6	404.4	406.0	420.1	439.0	448.4	460.7	485.2	503.6	505.9
155°	404.9	409.9	414.8	416.1	426.8	441.2	448.4	458.2	477.7	492.3	493.9
157.5°	415.2	420.0	425.0	426.1	433.5	443.5	448.4	456.0	471.2	482.5	483.6
160°	422.2	426.0	429.7	430.7	436.6	444.5	448.4	454.9	468.0	477.7	478.3
162.5°	429.2	432.1	434.9	435.6	439.9	445.6	448.4	454.0	464.9	473.1	473.7
165°	436.8	439.4	441.9	442.6	444.6	447.2	448.4	452.4	460.2	466.1	466.8
167.5°	443.8	445.0	446.3	446.6	448.2	450.4	451.5	454.1	459.2	463.0	463.3
170°	448.4	449.6	450.9	451.2	451.3	451.4	451.5	454.1	459.2	463.0	463.0
172.5°	450.9	451.2	451.4	451.5	451.5	451.5	451.5	453.5	457.5	460.6	460.4
175°	454.3	454.3	454.3	454.3	453.4	452.1	451.5	452.8	455.3	457.2	457.2
177.5°	454.3	454.3	454.3	454.3	453.6	452.6	452.1	453.1	455.1	456.6	456.3
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2
2.5°	2712.8	2705.3	2712.8	2707.8	2710.3	2702.8	2680.2	2672.8	2680.2	2687.7	2687.7
5°	2745.3	2740.3	2745.3	2745.3	2742.9	2737.8	2712.8	2707.8	2712.8	2715.3	2710.3
7.5°	2755.4	2747.9	2755.4	2750.3	2750.3	2745.3	2720.3	2715.3	2717.8	2725.3	2717.8
10°	2755.4	2747.9	2755.4	2752.8	2750.3	2745.3	2720.3	2710.3	2710.3	2717.8	2710.3
12.5°	2742.9	2737.8	2742.9	2737.8	2737.8	2732.8	2707.8	2697.8	2700.3	2702.8	2692.8
15°	2722.8	2715.3	2722.8	2717.8	2720.3	2712.8	2685.3	2675.2	2675.2	2680.2	2662.8
17.5°	2692.8	2682.8	2692.8	2690.3	2687.7	2682.8	2657.8	2647.7	2645.2	2647.7	2635.2
20°	2657.8	2650.3	2657.8	2655.2	2655.2	2645.2	2620.2	2607.7	2607.7	2607.7	2595.2
22.5°	2602.6	2595.2	2602.6	2607.7	2607.7	2605.2	2582.6	2565.2	2560.1	2560.1	2545.2
25°	2540.1	2532.6	2540.1	2540.1	2537.7	2540.1	2532.6	2522.6	2515.1	2507.6	2492.6
27.5°	2480.1	2475.1	2480.1	2475.1	2480.1	2472.6	2470.0	2467.6	2457.5	2450.0	2430.0
30°	2420.0	2415.0	2420.0	2415.0	2410.0	2405.0	2392.4	2387.5	2397.5	2392.4	2359.9
32.5°	2344.9	2339.9	2344.9	2344.9	2339.9	2339.9	2319.9	2312.4	2314.9	2329.9	2299.8
35°	2267.3	2259.8	2267.3	2264.8	2267.3	2259.8	2247.3	2244.8	2234.8	2252.3	2229.8
37.5°	2177.3	2169.7	2177.3	2177.3	2177.3	2182.2	2172.3	2164.8	2149.7	2172.3	2154.7
40°	2084.7	2074.6	2084.7	2082.1	2084.7	2089.6	2084.7	2079.7	2064.6	2082.1	2067.1
42.5°	1979.6	1977.0	1979.6	1982.1	1982.1	1992.0	1999.6	1989.6	1984.5	1972.0	1982.1
45°	1866.9	1862.0	1866.9	1871.9	1874.4	1879.4	1902.0	1902.0	1894.5	1874.4	1889.5
47.5°	1746.8	1734.3	1746.8	1761.8	1761.8	1769.3	1791.9	1809.4	1796.9	1771.8	1779.3
50°	1619.2	1621.7	1619.2	1629.2	1629.2	1656.7	1674.2	1691.8	1704.3	1674.2	1639.2
52.5°	1494.1	1491.5	1494.1	1501.6	1511.5	1524.1	1554.1	1571.6	1591.6	1574.1	1519.0
55°	1368.9	1373.9	1368.9	1371.4	1376.5	1383.9	1429.0	1446.5	1484.0	1461.5	1404.0
57.5°	1243.7	1236.2	1243.7	1248.8	1251.3	1258.8	1296.3	1328.8	1351.4	1353.9	1283.9
60°	1098.6	1088.6	1098.6	1121.2	1126.2	1131.1	1166.2	1196.2	1216.2	1223.7	1151.2
62.5°	971.0	953.5	971.0	986.0	996.1	1008.6	1033.5	1078.6	1096.1	1098.6	996.1
65°	835.8	828.3	835.8	865.9	868.4	883.5	911.0	943.5	981.0	976.0	828.3
67.5°	713.3	713.3	713.3	733.3	748.3	755.8	790.8	805.9	853.4	858.4	690.7
70°	600.6	598.1	600.6	615.7	625.6	643.2	675.7	693.3	730.7	743.2	560.5
72.5°	493.0	490.5	493.0	505.5	515.6	530.6	558.1	578.1	610.6	625.6	435.4
75°	397.9	392.9	397.9	407.9	405.4	425.5	447.9	468.0	498.0	508.0	322.8
77.5°	305.4	305.4	305.4	315.3	315.3	335.3	345.4	370.3	387.9	402.9	237.7
80°	227.8	225.2	227.8	230.2	230.2	240.3	257.7	275.3	290.3	290.3	162.7
82.5°	160.1	155.2	160.1	160.1	160.1	165.2	175.2	180.1	190.2	197.7	102.6
85°	100.1	100.1	100.1	102.6	100.1	105.1	107.6	112.6	112.6	107.6	62.6
87.5°	65.1	62.6	65.1	62.6	62.6	60.0	60.0	60.0	57.6	55.0	35.0
90°	11.5	11.5	11.5	11.5	11.5	15.4	20.6	23.2	19.9	13.4	8.6
92.5°	46.3	37.2	46.3	55.6	57.9	82.0	114.3	130.4	114.6	82.7	58.9
95°	161.7	133.8	161.7	189.6	196.6	258.2	340.4	381.4	322.1	203.5	114.6
97.5°	387.5	334.5	387.5	440.5	453.9	492.8	544.8	570.7	471.9	274.2	125.9
100°	558.4	495.1	558.4	621.7	637.4	634.6	630.7	628.9	519.2	299.8	135.4
102.5°	726.4	672.2	726.4	780.6	794.1	744.5	678.4	645.3	534.1	311.7	144.8
105°	940.6	911.5	940.6	969.7	977.0	865.8	717.6	643.5	535.8	320.4	158.8
107.5°	1080.9	1088.0	1080.9	1073.9	1072.1	917.0	710.2	606.9	511.9	322.0	179.6
110°	1134.4	1164.8	1134.4	1104.1	1096.5	923.2	692.0	576.4	490.8	319.6	191.1

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1139.2	1185.8	1139.2	1092.6	1081.0	903.6	667.0	548.7	472.4	319.7	205.2
115°	1109.0	1173.6	1109.0	1044.4	1028.2	857.3	629.5	515.5	451.2	322.6	226.2
117.5°	1045.0	1116.6	1045.0	973.3	955.3	801.1	595.4	492.6	438.0	328.6	246.6
120°	993.3	1063.0	993.3	923.7	906.2	765.3	577.4	483.4	433.4	333.5	258.5
122.5°	943.1	1011.7	943.1	874.4	857.2	730.3	561.0	476.4	431.1	340.5	272.5
125°	871.3	934.6	871.3	808.0	792.3	684.5	540.7	468.8	429.2	349.9	290.5
127.5°	806.8	860.3	806.8	753.4	740.1	647.5	524.2	462.4	428.1	359.4	307.9
130°	768.9	818.2	768.9	719.6	707.3	624.8	514.9	460.0	428.7	366.3	319.5
132.5°	734.4	778.5	734.4	690.2	679.2	605.4	507.1	457.9	429.2	371.9	328.9
135°	687.1	725.2	687.1	649.1	639.5	577.8	495.5	454.3	428.8	378.0	339.9
137.5°	649.3	680.4	649.3	618.0	610.2	558.0	488.4	453.6	431.4	387.1	353.9
140°	623.2	652.3	623.2	594.1	586.8	541.7	481.6	451.5	431.9	392.7	363.3
142.5°	601.7	626.7	601.7	576.6	570.3	530.7	477.9	451.5	433.4	397.4	370.3
145°	569.4	588.3	569.4	550.4	545.7	513.2	470.0	448.4	433.4	403.6	381.1
147.5°	544.6	560.2	544.6	528.9	524.9	499.4	465.4	448.4	436.4	412.4	394.5
150°	529.0	541.7	529.0	516.2	513.0	491.5	462.8	448.4	438.0	417.2	401.5
152.5°	515.6	525.2	515.6	505.9	503.6	485.2	460.7	448.4	439.0	420.1	406.0
155°	500.3	506.6	500.3	493.9	492.3	477.7	458.2	448.4	441.2	426.8	416.1
157.5°	488.2	492.6	488.2	483.6	482.5	471.2	456.0	448.4	443.5	433.5	426.1
160°	480.9	483.4	480.9	478.3	477.7	468.0	454.9	448.4	444.5	436.6	430.7
162.5°	476.1	478.6	476.1	473.7	473.1	464.9	454.0	448.4	445.6	439.9	435.6
165°	469.3	471.9	469.3	466.8	466.1	460.2	452.4	448.4	447.2	444.6	442.6
167.5°	464.4	465.5	464.4	463.3	463.0	459.2	454.1	451.5	450.4	448.2	446.6
170°	463.0	463.0	463.0	463.0	463.0	459.2	454.1	451.5	451.4	451.3	451.2
172.5°	459.4	458.5	459.4	460.4	460.6	457.5	453.5	451.5	451.5	451.5	451.5
175°	457.2	457.2	457.2	457.2	457.2	455.3	452.8	451.5	452.1	453.4	454.3
177.5°	455.3	454.3	455.3	456.3	456.6	455.1	453.1	452.1	452.6	453.6	454.3
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2
2.5°	2682.8	2667.7	2667.7	2642.8	2632.7	2625.2	2612.7	2575.1	2565.2	2555.1	2570.1
5°	2705.3	2677.8	2657.8	2612.7	2575.1	2560.1	2512.6	2422.5	2362.5	2317.4	2292.4
7.5°	2710.3	2675.2	2637.7	2567.6	2477.5	2437.5	2292.4	2127.2	2082.1	2042.1	2017.1
10°	2705.3	2665.3	2612.7	2507.6	2294.9	2224.8	2079.7	1972.0	1944.5	1937.0	1944.5
12.5°	2687.7	2650.3	2577.7	2402.5	2104.7	2057.1	1972.0	1909.5	1904.5	1917.0	1984.5
15°	2657.8	2622.7	2537.7	2262.4	1999.6	1964.5	1904.5	1882.0	1909.5	1997.0	2199.8
17.5°	2627.7	2587.7	2482.6	2124.7	1919.4	1894.5	1851.9	1897.0	2052.2	2169.7	2237.3
20°	2587.7	2540.1	2420.0	2024.6	1862.0	1839.4	1819.4	2022.1	2139.7	2182.2	2219.8
22.5°	2540.1	2490.0	2334.9	1954.5	1801.8	1784.4	1796.9	2092.2	2139.7	2169.7	2202.2
25°	2477.5	2435.0	2234.8	1899.4	1754.3	1734.3	1781.8	2084.7	2112.2	2119.7	2184.8
27.5°	2420.0	2364.9	2129.7	1849.4	1696.7	1689.2	1794.3	2052.2	2072.2	2079.7	2149.7
30°	2349.9	2267.3	2012.0	1796.9	1636.7	1634.2	1796.9	2012.0	2007.1	2027.1	2097.1
32.5°	2277.4	2122.2	1879.4	1731.8	1579.2	1576.6	1779.3	1952.0	1947.1	1974.6	2027.1
35°	2209.8	2009.6	1699.3	1656.7	1506.5	1509.1	1736.8	1882.0	1884.4	1909.5	1942.0
37.5°	2139.7	1912.0	1501.6	1574.1	1436.5	1436.5	1679.3	1816.9	1811.9	1819.4	1864.4
40°	2057.1	1759.3	1326.4	1466.5	1371.4	1363.9	1609.2	1746.8	1729.2	1726.8	1789.4
42.5°	1969.5	1591.6	1196.2	1323.9	1296.3	1286.3	1524.1	1661.7	1629.2	1636.7	1716.7
45°	1874.4	1546.6	1096.1	1118.6	1218.8	1211.2	1431.5	1564.1	1541.6	1561.6	1644.2
47.5°	1779.3	1456.5	1063.6	928.4	1136.2	1133.7	1328.8	1469.0	1456.5	1476.5	1564.1
50°	1649.2	1356.4	1061.1	795.8	1043.6	1053.5	1206.3	1376.5	1376.5	1393.9	1486.5
52.5°	1481.6	1233.8	963.5	720.8	936.0	966.0	1098.6	1296.3	1301.3	1318.9	1401.4
55°	1328.8	1106.1	893.4	663.2	808.3	873.4	993.5	1213.8	1223.7	1241.3	1316.3
57.5°	1188.7	920.9	878.4	595.6	690.7	753.3	900.9	1133.7	1138.6	1153.7	1226.3
60°	1038.6	665.6	805.9	523.1	588.1	635.7	815.8	1038.6	1056.1	1066.1	1128.7
62.5°	868.4	483.0	730.7	473.0	538.1	548.0	745.8	948.4	971.0	978.5	1016.1
65°	618.1	405.4	620.7	430.5	485.5	488.0	670.7	855.8	875.9	888.4	916.0
67.5°	418.0	330.3	473.0	390.4	445.5	447.9	598.1	748.3	775.8	785.8	803.3
70°	290.3	220.3	350.3	347.9	400.4	405.4	520.5	650.7	675.7	683.2	693.3
72.5°	212.7	177.7	290.3	312.9	352.9	357.9	440.4	540.5	565.6	573.1	578.1
75°	162.7	187.7	235.3	272.8	300.3	302.8	360.4	440.4	458.0	463.0	465.5
77.5°	130.2	175.2	172.6	220.3	245.2	240.3	282.8	340.4	355.4	355.4	355.4
80°	97.6	137.6	130.2	157.7	180.1	175.2	202.7	242.8	247.8	252.7	250.2
82.5°	72.6	87.6	87.6	100.1	120.1	115.2	135.2	157.7	157.7	157.7	162.7
85°	45.1	50.1	40.0	52.6	67.5	65.1	75.0	85.1	87.6	87.6	82.6
87.5°	27.5	22.5	12.5	20.0	30.1	30.1	35.0	37.6	35.0	35.0	35.0
90°	8.0	5.5	3.1	5.5	8.0	8.6	13.4	19.9	23.2	20.6	15.4
92.5°	53.6	32.9	12.2	32.9	53.6	58.9	82.7	114.6	130.4	114.3	82.0
95°	105.1	67.1	29.3	67.1	105.1	114.6	203.5	322.1	381.4	340.4	258.2
97.5°	117.5	84.1	50.6	84.1	117.5	125.9	274.2	471.9	570.7	544.8	492.8
100°	127.8	97.4	67.0	97.4	127.8	135.4	299.8	519.2	628.9	630.7	634.6
102.5°	137.7	109.4	81.0	109.4	137.7	144.8	311.7	534.1	645.3	678.4	744.5
105°	152.8	128.9	104.9	128.9	152.8	158.8	320.4	535.8	643.5	717.6	865.8
107.5°	173.9	151.6	129.3	151.6	173.9	179.6	322.0	511.9	606.9	710.2	917.0
110°	186.1	165.8	145.7	165.8	186.1	191.1	319.6	490.8	576.4	692.0	923.2

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	200.4	181.1	161.9	181.1	200.4	205.2	319.7	472.4	548.7	667.0	903.6
115°	221.8	204.0	186.3	204.0	221.8	226.2	322.6	451.2	515.5	629.5	857.3
117.5°	242.6	226.5	210.3	226.5	242.6	246.6	328.6	438.0	492.6	595.4	801.1
120°	254.7	239.5	224.3	239.5	254.7	258.5	333.5	433.4	483.4	577.4	765.3
122.5°	268.7	253.4	238.1	253.4	268.7	272.5	340.5	431.1	476.4	561.0	730.3
125°	287.0	273.0	259.1	273.0	287.0	290.5	349.9	429.2	468.8	540.7	684.5
127.5°	304.4	290.3	276.2	290.3	304.4	307.9	359.4	428.1	462.4	524.2	647.5
130°	315.7	300.5	285.3	300.5	315.7	319.5	366.3	428.7	460.0	514.9	624.8
132.5°	325.2	310.0	294.8	310.0	325.2	328.9	371.9	429.2	457.9	507.1	605.4
135°	336.4	322.6	308.8	322.6	336.4	339.9	378.0	428.8	454.3	495.5	577.8
137.5°	350.4	336.8	323.1	336.8	350.4	353.9	387.1	431.4	453.6	488.4	558.0
140°	360.2	347.7	335.0	347.7	360.2	363.3	392.7	431.9	451.5	481.6	541.7
142.5°	367.4	355.7	344.1	355.7	367.4	370.3	397.4	433.4	451.5	477.9	530.7
145°	378.5	368.4	358.2	368.4	378.5	381.1	403.6	433.4	448.4	470.0	513.2
147.5°	392.0	382.1	372.2	382.1	392.0	394.5	412.4	436.4	448.4	465.4	499.4
150°	399.2	390.4	381.4	390.4	399.2	401.5	417.2	438.0	448.4	462.8	491.5
152.5°	404.4	397.6	390.8	397.6	404.4	406.0	420.1	439.0	448.4	460.7	485.2
155°	414.8	409.9	404.9	409.9	414.8	416.1	426.8	441.2	448.4	458.2	477.7
157.5°	425.0	420.0	415.2	420.0	425.0	426.1	433.5	443.5	448.4	456.0	471.2
160°	429.7	426.0	422.2	426.0	429.7	430.7	436.6	444.5	448.4	454.9	468.0
162.5°	434.9	432.1	429.2	432.1	434.9	435.6	439.9	445.6	448.4	454.0	464.9
165°	441.9	439.4	436.8	439.4	441.9	442.6	444.6	447.2	448.4	452.4	460.2
167.5°	446.3	445.0	443.8	445.0	446.3	446.6	448.2	450.4	451.5	454.1	459.2
170°	450.9	449.6	448.4	449.6	450.9	451.2	451.3	451.4	451.5	454.1	459.2
172.5°	451.4	451.2	450.9	451.2	451.4	451.5	451.5	451.5	451.5	453.5	457.5
175°	454.3	454.3	454.3	454.3	454.3	454.3	453.4	452.1	451.5	452.8	455.3
177.5°	454.3	454.3	454.3	454.3	454.3	454.3	453.6	452.6	452.1	453.1	455.1
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2	2645.2
2.5°	2552.7	2545.2	2555.1	2527.6	2555.1	2545.2	2552.7	2570.1	2555.1	2565.2	2575.1
5°	2239.8	2227.3	2187.2	2154.7	2187.2	2227.3	2239.8	2292.4	2317.4	2362.5	2422.5
7.5°	2002.1	1992.0	1982.1	1962.0	1982.1	1992.0	2002.1	2017.1	2042.1	2082.1	2127.2
10°	1949.5	1952.0	1967.1	1964.5	1967.1	1952.0	1949.5	1944.5	1937.0	1944.5	1972.0
12.5°	2084.7	2107.2	2189.8	2184.8	2189.8	2107.2	2084.7	1984.5	1917.0	1904.5	1909.5
15°	2239.8	2247.3	2264.8	2267.3	2264.8	2247.3	2239.8	2199.8	1997.0	1909.5	1882.0
17.5°	2254.8	2257.3	2269.9	2269.9	2269.9	2257.3	2254.8	2237.3	2169.7	2052.2	1897.0
20°	2242.4	2247.3	2272.3	2277.4	2272.3	2247.3	2242.4	2219.8	2182.2	2139.7	2022.1
22.5°	2237.3	2247.3	2267.3	2264.8	2267.3	2247.3	2237.3	2202.2	2169.7	2139.7	2092.2
25°	2212.3	2212.3	2214.8	2217.3	2214.8	2212.3	2212.3	2184.8	2119.7	2112.2	2084.7
27.5°	2159.7	2164.8	2179.8	2177.3	2179.8	2164.8	2159.7	2149.7	2079.7	2072.2	2052.2
30°	2112.2	2107.2	2094.7	2084.7	2094.7	2107.2	2112.2	2097.1	2027.1	2007.1	2012.0
32.5°	2032.1	2019.6	2007.1	1999.6	2007.1	2019.6	2032.1	2027.1	1974.6	1947.1	1952.0
35°	1937.0	1939.5	1937.0	1929.5	1937.0	1939.5	1937.0	1942.0	1909.5	1884.4	1882.0
37.5°	1869.5	1874.4	1871.9	1862.0	1871.9	1874.4	1869.5	1864.4	1819.4	1811.9	1816.9
40°	1799.4	1801.8	1799.4	1791.9	1799.4	1801.8	1799.4	1789.4	1726.8	1729.2	1746.8
42.5°	1731.8	1729.2	1721.8	1716.7	1721.8	1729.2	1731.8	1716.7	1636.7	1629.2	1661.7
45°	1654.2	1656.7	1641.7	1634.2	1641.7	1656.7	1654.2	1644.2	1561.6	1541.6	1564.1
47.5°	1576.6	1576.6	1564.1	1556.6	1564.1	1576.6	1576.6	1564.1	1476.5	1456.5	1469.0
50°	1494.1	1491.5	1474.1	1471.5	1474.1	1491.5	1494.1	1486.5	1393.9	1376.5	1376.5
52.5°	1398.9	1398.9	1401.4	1406.4	1401.4	1398.9	1398.9	1401.4	1318.9	1301.3	1296.3
55°	1316.3	1318.9	1336.4	1341.4	1336.4	1318.9	1316.3	1316.3	1241.3	1223.7	1213.8
57.5°	1231.3	1231.3	1243.7	1243.7	1243.7	1231.3	1231.3	1226.3	1153.7	1138.6	1133.7
60°	1133.7	1138.6	1148.7	1146.2	1148.7	1138.6	1133.7	1128.7	1066.1	1056.1	1038.6
62.5°	1031.1	1036.1	1038.6	1033.5	1038.6	1036.1	1031.1	1016.1	978.5	971.0	948.4
65°	923.5	928.4	931.0	926.0	931.0	928.4	923.5	916.0	888.4	875.9	855.8
67.5°	813.4	810.8	808.3	818.4	808.3	810.8	813.4	803.3	785.8	775.8	748.3
70°	700.8	700.8	698.2	703.2	698.2	700.8	700.8	693.3	683.2	675.7	650.7
72.5°	580.6	578.1	588.1	580.6	588.1	578.1	580.6	578.1	573.1	565.6	540.5
75°	463.0	468.0	463.0	470.5	463.0	468.0	463.0	465.5	463.0	458.0	440.4
77.5°	352.9	357.9	352.9	352.9	352.9	357.9	352.9	355.4	355.4	355.4	340.4
80°	250.2	247.8	247.8	245.2	247.8	247.8	250.2	250.2	252.7	247.8	242.8
82.5°	160.1	157.7	157.7	162.7	157.7	157.7	160.1	162.7	157.7	157.7	157.7
85°	87.6	90.1	85.1	85.1	85.1	90.1	87.6	82.6	87.6	87.6	85.1
87.5°	32.5	30.1	30.1	30.1	30.1	30.1	32.5	35.0	35.0	35.0	37.6
90°	11.5	11.5	11.5	11.5	11.5	11.5	11.5	15.4	20.6	23.2	19.9
92.5°	57.9	55.6	46.3	37.2	46.3	55.6	57.9	82.0	114.3	130.4	114.6
95°	196.6	189.6	161.7	133.8	161.7	189.6	196.6	258.2	340.4	381.4	322.1
97.5°	453.9	440.5	387.5	334.5	387.5	440.5	453.9	492.8	544.8	570.7	471.9
100°	637.4	621.7	558.4	495.1	558.4	621.7	637.4	634.6	630.7	628.9	519.2
102.5°	794.1	780.6	726.4	672.2	726.4	780.6	794.1	744.5	678.4	645.3	534.1
105°	977.0	969.7	940.6	911.5	940.6	969.7	977.0	865.8	717.6	643.5	535.8
107.5°	1072.1	1073.9	1080.9	1088.0	1080.9	1073.9	1072.1	917.0	710.2	606.9	511.9
110°	1096.5	1104.1	1134.4	1164.8	1134.4	1104.1	1096.5	923.2	692.0	576.4	490.8

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1081.0	1092.6	1139.2	1185.8	1139.2	1092.6	1081.0	903.6	667.0	548.7	472.4
115°	1028.2	1044.4	1109.0	1173.6	1109.0	1044.4	1028.2	857.3	629.5	515.5	451.2
117.5°	955.3	973.3	1045.0	1116.6	1045.0	973.3	955.3	801.1	595.4	492.6	438.0
120°	906.2	923.7	993.3	1063.0	993.3	923.7	906.2	765.3	577.4	483.4	433.4
122.5°	857.2	874.4	943.1	1011.7	943.1	874.4	857.2	730.3	561.0	476.4	431.1
125°	792.3	808.0	871.3	934.6	871.3	808.0	792.3	684.5	540.7	468.8	429.2
127.5°	740.1	753.4	806.8	860.3	806.8	753.4	740.1	647.5	524.2	462.4	428.1
130°	707.3	719.6	768.9	818.2	768.9	719.6	707.3	624.8	514.9	460.0	428.7
132.5°	679.2	690.2	734.4	778.5	734.4	690.2	679.2	605.4	507.1	457.9	429.2
135°	639.5	649.1	687.1	725.2	687.1	649.1	639.5	577.8	495.5	454.3	428.8
137.5°	610.2	618.0	649.3	680.4	649.3	618.0	610.2	558.0	488.4	453.6	431.4
140°	586.8	594.1	623.2	652.3	623.2	594.1	586.8	541.7	481.6	451.5	431.9
142.5°	570.3	576.6	601.7	626.7	601.7	576.6	570.3	530.7	477.9	451.5	433.4
145°	545.7	550.4	569.4	588.3	569.4	550.4	545.7	513.2	470.0	448.4	433.4
147.5°	524.9	528.9	544.6	560.2	544.6	528.9	524.9	499.4	465.4	448.4	436.4
150°	513.0	516.2	529.0	541.7	529.0	516.2	513.0	491.5	462.8	448.4	438.0
152.5°	503.6	505.9	515.6	525.2	515.6	505.9	503.6	485.2	460.7	448.4	439.0
155°	492.3	493.9	500.3	506.6	500.3	493.9	492.3	477.7	458.2	448.4	441.2
157.5°	482.5	483.6	488.2	492.6	488.2	483.6	482.5	471.2	456.0	448.4	443.5
160°	477.7	478.3	480.9	483.4	480.9	478.3	477.7	468.0	454.9	448.4	444.5
162.5°	473.1	473.7	476.1	478.6	476.1	473.7	473.1	464.9	454.0	448.4	445.6
165°	466.1	466.8	469.3	471.9	469.3	466.8	466.1	460.2	452.4	448.4	447.2
167.5°	463.0	463.3	464.4	465.5	464.4	463.3	463.0	459.2	454.1	451.5	450.4
170°	463.0	463.0	463.0	463.0	463.0	463.0	463.0	459.2	454.1	451.5	451.4
172.5°	460.6	460.4	459.4	458.5	459.4	460.4	460.6	457.5	453.5	451.5	451.5
175°	457.2	457.2	457.2	457.2	457.2	457.2	457.2	455.3	452.8	451.5	452.1
177.5°	456.6	456.3	455.3	454.3	455.3	456.3	456.6	455.1	453.1	452.1	452.6
180°	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3	454.3

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2645.2	2645.2	2645.2	2645.2	2645.2
2.5°	2612.7	2625.2	2632.7	2642.8	2667.7
5°	2512.6	2560.1	2575.1	2612.7	2657.8
7.5°	2292.4	2437.5	2477.5	2567.6	2637.7
10°	2079.7	2224.8	2294.9	2507.6	2612.7
12.5°	1972.0	2057.1	2104.7	2402.5	2577.7
15°	1904.5	1964.5	1999.6	2262.4	2537.7
17.5°	1851.9	1894.5	1919.4	2124.7	2482.6
20°	1819.4	1839.4	1862.0	2024.6	2420.0
22.5°	1796.9	1784.4	1801.8	1954.5	2334.9
25°	1781.8	1734.3	1754.3	1899.4	2234.8
27.5°	1794.3	1689.2	1696.7	1849.4	2129.7
30°	1796.9	1634.2	1636.7	1796.9	2012.0
32.5°	1779.3	1576.6	1579.2	1731.8	1879.4
35°	1736.8	1509.1	1506.5	1656.7	1699.3
37.5°	1679.3	1436.5	1436.5	1574.1	1501.6
40°	1609.2	1363.9	1371.4	1466.5	1326.4
42.5°	1524.1	1286.3	1296.3	1323.9	1196.2
45°	1431.5	1211.2	1218.8	1118.6	1096.1
47.5°	1328.8	1133.7	1136.2	928.4	1063.6
50°	1206.3	1053.5	1043.6	795.8	1061.1
52.5°	1098.6	966.0	936.0	720.8	963.5
55°	993.5	873.4	808.3	663.2	893.4
57.5°	900.9	753.3	690.7	595.6	878.4
60°	815.8	635.7	588.1	523.1	805.9
62.5°	745.8	548.0	538.1	473.0	730.7
65°	670.7	488.0	485.5	430.5	620.7
67.5°	598.1	447.9	445.5	390.4	473.0
70°	520.5	405.4	400.4	347.9	350.3
72.5°	440.4	357.9	352.9	312.9	290.3
75°	360.4	302.8	300.3	272.8	235.3
77.5°	282.8	240.3	245.2	220.3	172.6
80°	202.7	175.2	180.1	157.7	130.2
82.5°	135.2	115.2	120.1	100.1	87.6
85°	75.0	65.1	67.5	52.6	40.0
87.5°	35.0	30.1	30.1	20.0	12.5
90°	13.4	8.6	8.0	5.5	3.1
92.5°	82.7	58.9	53.6	32.9	12.2
95°	203.5	114.6	105.1	67.1	29.3
97.5°	274.2	125.9	117.5	84.1	50.6
100°	299.8	135.4	127.8	97.4	67.0
102.5°	311.7	144.8	137.7	109.4	81.0
105°	320.4	158.8	152.8	128.9	104.9
107.5°	322.0	179.6	173.9	151.6	129.3
110°	319.6	191.1	186.1	165.8	145.7

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	319.7	205.2	200.4	181.1	161.9
115°	322.6	226.2	221.8	204.0	186.3
117.5°	328.6	246.6	242.6	226.5	210.3
120°	333.5	258.5	254.7	239.5	224.3
122.5°	340.5	272.5	268.7	253.4	238.1
125°	349.9	290.5	287.0	273.0	259.1
127.5°	359.4	307.9	304.4	290.3	276.2
130°	366.3	319.5	315.7	300.5	285.3
132.5°	371.9	328.9	325.2	310.0	294.8
135°	378.0	339.9	336.4	322.6	308.8
137.5°	387.1	353.9	350.4	336.8	323.1
140°	392.7	363.3	360.2	347.7	335.0
142.5°	397.4	370.3	367.4	355.7	344.1
145°	403.6	381.1	378.5	368.4	358.2
147.5°	412.4	394.5	392.0	382.1	372.2
150°	417.2	401.5	399.2	390.4	381.4
152.5°	420.1	406.0	404.4	397.6	390.8
155°	426.8	416.1	414.8	409.9	404.9
157.5°	433.5	426.1	425.0	420.0	415.2
160°	436.6	430.7	429.7	426.0	422.2
162.5°	439.9	435.6	434.9	432.1	429.2
165°	444.6	442.6	441.9	439.4	436.8
167.5°	448.2	446.6	446.3	445.0	443.8
170°	451.3	451.2	450.9	449.6	448.4
172.5°	451.5	451.5	451.4	451.2	450.9
175°	453.4	454.3	454.3	454.3	454.3
177.5°	453.6	454.3	454.3	454.3	454.3
180°	454.3	454.3	454.3	454.3	454.3

TEST NUMBER: P934588

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-6-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.18	17.26	16.94	18.04	19.00	19.00	20.08	19.77	20.87	21.82
	3H	16.67	17.64	17.45	18.43	19.42	20.36	21.33	21.14	22.13	23.11
	4H	16.87	17.79	17.67	18.59	19.59	20.82	21.73	21.61	22.53	23.53
	6H	17.00	17.84	17.81	18.66	19.67	21.11	21.95	21.92	22.77	23.78
	8H	17.01	17.81	17.83	18.64	19.66	21.19	21.99	22.01	22.82	23.84
	12H	16.99	17.75	17.81	18.58	19.62	21.24	22.00	22.06	22.83	23.86
4H	2H	17.24	18.15	18.04	18.95	19.95	19.44	20.35	20.24	21.16	22.15
	3H	18.28	19.04	19.10	19.88	20.89	20.96	21.72	21.78	22.56	23.57
	4H	18.57	19.26	19.40	20.10	21.14	21.50	22.19	22.33	23.03	24.07
	6H	18.71	19.30	19.55	20.17	21.21	21.88	22.47	22.72	23.34	24.38
	8H	18.72	19.27	19.56	20.13	21.19	21.99	22.54	22.83	23.40	24.46
	12H	18.69	19.20	19.56	20.07	21.14	22.05	22.55	22.92	23.43	24.50
8H	4H	19.04	19.60	19.89	20.45	21.51	21.64	22.20	22.49	23.06	24.11
	6H	19.31	19.77	20.18	20.67	21.73	22.09	22.55	22.96	23.45	24.50
	8H	19.35	19.76	20.24	20.66	21.73	22.24	22.65	23.12	23.54	24.62
	12H	19.35	19.71	20.24	20.59	21.72	22.35	22.71	23.23	23.59	24.72
12H	4H	19.06	19.56	19.92	20.44	21.50	21.62	22.12	22.48	23.00	24.06
	6H	19.37	19.78	20.26	20.68	21.75	22.08	22.49	22.97	23.39	24.46
	8H	19.45	19.81	20.34	20.70	21.82	22.25	22.62	23.14	23.50	24.63

END OF REPORT