

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936399

Luminaire Tested: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936399
REPORT IS A COMBINATION OF REPORTS P933446 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4904.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936399

CATALOG NUMBER: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P936399

CATALOG NUMBER: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	102	97	93	89	96	92	88	85	82	79	77	74	71	69	66	64	62
2	92	84	77	71	87	79	73	68	71	66	62	64	60	57	57	54	51
3	83	73	65	58	79	69	62	56	62	56	51	56	51	47	50	46	43
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	40	36
5	69	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31
6	64	51	42	35	60	48	40	34	43	37	32	39	33	29	35	30	27
7	59	45	37	31	55	43	35	30	39	32	27	35	30	25	32	27	23
8	54	41	33	27	51	39	31	26	36	29	24	32	26	22	29	24	21
9	51	37	29	24	48	36	28	23	32	26	21	29	24	20	26	22	18
10	47	34	26	21	45	33	25	21	30	23	19	27	22	18	24	20	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2796	2796	2796
5°	2731	3231	3759
10°	2476	4709	6231
15°	2103	6151	7525
20°	1712	7126	7669
25°	1428	7456	7513
30°	1203	7501	7499
35°	1063	7375	7693
40°	926	7210	7894
45°	838	7089	7924
50°	768	6980	7793
55°	735	6822	7447
60°	752	6519	6902
65°	780	6061	6152
70°	830	5282	5197
75°	916	4302	4056
80°	993	2980	2732
85°	864	1578	1399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7924 cd/sqm

TEST NUMBER: P936399

CATALOG NUMBER: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.5	1.2
10°-20°	259.2	5.3
20°-30°	453.3	9.2
30°-40°	583.6	11.9
40°-50°	651.8	13.3
50°-60°	624.3	12.7
60°-70°	494.7	10.1
70°-80°	290.9	5.9
80°-90°	81.7	1.7
90°-100°	105.7	2.2
100°-110°	278.0	5.7
110°-120°	288.2	5.9
120°-130°	231.2	4.7
130°-140°	181.4	3.7
140°-150°	139.2	2.8
150°-160°	100.3	2.0
160°-170°	61.4	1.3
170°-180°	20.7	0.4
0°-30°	771.0	15.7
0°-40°	1354.5	27.6
0°-60°	2630.6	53.6
0°-90°	3497.9	71.3
90°-120°	671.9	13.7
90°-150°	1223.8	25.0
90°-180°	1406.0	28.7
0°-180°	4904.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	452	452	452	452	452	
5°	440	472	532	602	624	41
15°	330	609	1026	1244	1284	92
25°	211	690	1222	1276	1278	97
35°	142	660	1151	1217	1265	89
45°	97	526	1017	1166	1218	75
55°	70	334	863	1003	1030	64
65°	55	177	641	721	731	55
75°	41	109	352	387	388	43
85°	14	33	87	96	97	15
90°	2	4	11	6	6	2
95°	14	55	182	94	64	16
105°	50	76	307	467	435	53
115°	89	108	246	491	560	88
125°	124	139	224	378	446	110
135°	148	162	217	305	346	114
145°	171	182	214	261	281	107
155°	193	199	214	235	242	89
165°	209	211	214	223	225	59
175°	217	217	216	218	218	21
180°	217	217	217	217	217	

TEST NUMBER: P936399

CATALOG NUMBER: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0	452.0
2.5°	452.0	452.0	454.9	456.4	459.3	460.8	463.7	466.6	475.3	476.7	479.7
5°	440.4	446.2	465.1	472.4	492.7	520.4	532.0	550.9	590.1	601.7	609.0
7.5°	423.0	436.0	482.6	494.2	545.1	617.7	648.3	689.0	751.5	782.0	806.7
10°	395.4	423.0	505.8	533.4	616.3	726.8	783.4	840.1	934.6	976.8	992.7
12.5°	364.8	409.9	530.5	568.3	687.5	848.8	917.2	979.7	1087.2	1144.0	1152.7
15°	329.9	391.0	553.8	609.0	763.1	950.6	1026.2	1103.3	1203.6	1244.3	1254.5
17.5°	299.4	376.5	575.6	633.7	821.2	1042.2	1119.3	1183.2	1264.6	1292.3	1299.5
20°	261.6	353.2	590.1	665.7	882.3	1109.1	1183.2	1232.7	1287.9	1305.3	1308.2
22.5°	234.0	328.5	598.8	677.3	923.0	1149.8	1212.3	1251.6	1289.4	1295.2	1296.6
25°	210.8	300.9	597.4	690.4	957.9	1174.5	1222.5	1251.6	1273.4	1276.3	1276.3
27.5°	189.0	270.4	591.6	693.3	984.0	1180.3	1218.1	1238.5	1248.7	1254.5	1254.5
30°	170.1	241.3	577.0	687.5	995.6	1174.5	1205.0	1215.2	1225.4	1234.1	1238.5
32.5°	155.5	213.7	555.2	675.9	997.1	1160.0	1181.8	1187.6	1202.1	1222.5	1229.8
35°	142.4	186.0	530.5	659.9	988.4	1136.7	1151.3	1157.1	1186.2	1216.7	1226.9
37.5°	129.4	165.7	498.6	632.3	975.3	1109.1	1119.3	1129.5	1174.5	1210.9	1222.5
40°	116.3	148.3	460.8	601.7	954.9	1075.6	1084.3	1100.3	1160.0	1202.1	1213.8
42.5°	106.1	133.7	420.1	569.8	928.8	1037.8	1050.9	1074.1	1142.5	1187.6	1200.7
45°	97.4	119.2	376.5	526.2	895.4	998.6	1017.4	1049.4	1122.2	1165.8	1177.4
47.5°	88.7	109.0	331.4	481.1	859.0	959.3	984.0	1020.4	1094.5	1136.7	1146.9
50°	81.4	98.8	286.3	433.1	819.8	917.2	946.2	984.0	1059.6	1098.8	1112.0
52.5°	75.6	90.1	244.2	385.2	774.7	873.6	907.0	946.2	1017.4	1055.2	1064.0
55°	69.8	82.8	207.9	334.3	728.2	827.0	863.4	901.2	970.9	1002.9	1008.7
57.5°	66.9	77.0	177.3	286.3	678.8	774.7	815.4	850.3	915.7	940.4	946.2
60°	62.5	72.7	154.1	245.6	625.0	725.3	760.2	795.1	850.3	870.6	875.0
62.5°	58.1	69.8	136.6	206.4	569.8	667.2	702.0	734.0	780.5	795.1	800.9
65°	55.2	66.9	123.5	177.3	513.1	606.1	641.0	668.6	706.4	720.9	723.8
67.5°	52.3	64.0	113.4	152.6	456.4	545.1	571.2	597.4	626.5	641.0	642.4
70°	48.0	61.0	104.7	135.2	398.3	475.3	497.1	524.7	548.0	555.2	559.6
72.5°	45.1	56.7	98.8	122.1	338.7	408.4	428.8	444.8	465.1	472.4	472.4
75°	40.7	50.9	93.0	109.0	277.6	334.3	351.7	367.7	383.7	386.6	382.3
77.5°	36.3	45.1	79.9	91.6	216.6	264.5	279.1	287.8	300.9	303.8	305.2
80°	30.5	39.2	62.5	71.2	157.0	194.8	204.9	212.2	223.8	223.8	226.7
82.5°	23.3	30.5	45.1	50.9	106.1	133.7	142.4	146.8	154.1	154.1	154.1
85°	14.5	18.9	29.1	33.4	64.0	81.4	87.2	88.7	94.5	95.9	95.9
87.5°	7.3	10.2	18.9	20.3	33.4	42.2	42.2	45.1	45.1	43.6	42.2
90°	1.5	2.6	3.8	4.1	6.4	9.5	11.0	9.8	7.4	5.5	5.5
92.5°	5.8	15.7	25.6	28.1	39.5	54.7	62.3	54.6	39.1	27.6	26.6
95°	14.0	32.1	50.2	54.7	97.2	153.8	182.1	162.5	123.3	93.9	90.6
97.5°	24.1	40.1	56.1	60.1	130.9	225.3	272.5	260.1	235.4	216.8	210.5
100°	32.1	46.5	61.0	64.6	143.2	248.0	300.3	301.2	303.0	304.4	296.8
102.5°	38.8	52.3	65.8	69.2	148.8	255.0	308.1	323.9	355.5	379.3	372.8
105°	50.1	61.5	73.0	75.9	153.0	255.8	307.3	342.6	413.5	466.6	463.1
107.5°	61.7	72.4	83.0	85.8	153.8	244.5	289.8	339.2	438.0	512.0	512.9
110°	69.6	79.3	88.9	91.3	152.6	234.4	275.3	330.5	440.9	523.6	527.2

TEST NUMBER: P936399

CATALOG NUMBER: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	77.3	86.5	95.6	98.0	152.6	225.6	262.0	318.5	431.5	516.2	521.7
115°	89.0	97.5	105.9	108.0	154.1	215.4	246.1	300.6	409.4	491.0	498.7
117.5°	100.5	108.1	115.8	117.7	156.9	209.1	235.3	284.4	382.6	456.2	464.7
120°	107.2	114.4	121.6	123.5	159.3	207.1	230.9	275.8	365.5	432.9	441.2
122.5°	113.7	121.0	128.3	130.1	162.6	205.9	227.5	267.9	348.7	409.4	417.6
125°	123.7	130.4	137.1	138.8	167.2	205.0	223.9	258.2	326.9	378.4	386.0
127.5°	131.9	138.6	145.4	147.0	171.6	204.5	220.8	250.3	309.3	353.5	359.9
130°	136.2	143.5	150.7	152.5	174.9	204.7	219.7	245.9	298.4	337.7	343.6
132.5°	140.8	148.1	155.2	157.1	177.6	205.0	218.7	242.2	289.1	324.3	329.6
135°	147.5	154.1	160.7	162.3	180.5	204.8	217.0	236.6	276.0	305.4	310.0
137.5°	154.4	160.9	167.3	169.0	184.9	206.1	216.7	233.3	266.6	291.5	295.2
140°	160.0	166.0	172.0	173.5	187.6	206.3	215.6	229.9	258.7	280.2	283.7
142.5°	164.3	169.9	175.5	176.8	189.7	207.0	215.6	228.2	253.5	272.4	275.4
145°	171.0	175.9	180.7	182.0	192.7	207.0	214.1	224.4	245.1	260.6	262.8
147.5°	177.7	182.5	187.2	188.4	197.0	208.4	214.1	222.3	238.5	250.7	252.5
150°	182.1	186.3	190.7	191.8	199.2	209.2	214.1	221.0	234.7	245.0	246.5
152.5°	186.6	189.8	193.1	193.9	200.7	209.7	214.1	220.0	231.7	240.5	241.7
155°	193.3	195.7	198.2	198.7	203.9	210.8	214.1	218.8	228.1	235.1	235.9
157.5°	198.3	200.6	202.9	203.5	207.1	211.8	214.1	217.7	225.0	230.4	231.0
160°	201.6	203.5	205.2	205.7	208.5	212.3	214.1	217.2	223.5	228.1	228.4
162.5°	204.9	206.3	207.7	208.0	210.1	212.8	214.1	216.8	222.0	226.0	226.3
165°	208.6	209.8	211.0	211.3	212.3	213.6	214.1	216.0	219.8	222.6	222.9
167.5°	211.9	212.5	213.1	213.3	214.1	215.1	215.6	216.9	219.3	221.1	221.2
170°	214.1	214.7	215.3	215.4	215.5	215.6	215.6	216.9	219.3	221.1	221.1
172.5°	215.3	215.4	215.6	215.6	215.6	215.6	215.6	216.6	218.5	220.0	219.9
175°	217.0	217.0	217.0	217.0	216.5	215.9	215.6	216.2	217.4	218.4	218.4
177.5°	217.0	217.0	217.0	217.0	216.6	216.1	215.9	216.4	217.3	218.1	218.0
180°	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0	217.0

TEST NUMBER: P936399

CATALOG NUMBER: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	452.0	452.0
2.5°	482.6	479.7
5°	620.6	623.6
7.5°	835.8	834.3
10°	1039.3	1052.3
12.5°	1187.6	1190.5
15°	1277.7	1283.5
17.5°	1312.6	1314.1
20°	1314.1	1311.2
22.5°	1298.1	1295.2
25°	1279.2	1277.7
27.5°	1261.7	1263.2
30°	1254.5	1258.8
32.5°	1254.5	1261.7
35°	1257.4	1264.6
37.5°	1255.9	1264.6
40°	1250.1	1260.3
42.5°	1234.1	1241.4
45°	1209.4	1218.1
47.5°	1177.4	1183.2
50°	1136.7	1142.5
52.5°	1085.8	1087.2
55°	1024.7	1030.5
57.5°	959.3	960.8
60°	886.6	891.0
62.5°	809.6	809.6
65°	728.2	731.1
67.5°	643.9	651.2
70°	558.1	559.6
72.5°	473.8	473.8
75°	386.6	388.1
77.5°	303.8	303.8
80°	225.3	226.7
82.5°	155.5	158.4
85°	97.4	97.4
87.5°	45.1	40.7
90°	5.5	5.5
92.5°	22.1	17.7
95°	77.2	64.0
97.5°	185.1	159.7
100°	266.7	236.4
102.5°	346.9	321.0
105°	449.2	435.3
107.5°	516.2	519.6
110°	541.8	556.3

TEST NUMBER: P936399

CATALOG NUMBER: SQ4-FB-025U-075D-B35-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	544.0	566.3
115°	529.6	560.5
117.5°	499.0	533.2
120°	474.4	507.7
122.5°	450.4	483.1
125°	416.1	446.3
127.5°	385.4	410.9
130°	367.2	390.7
132.5°	350.7	371.8
135°	328.1	346.3
137.5°	310.1	324.9
140°	297.6	311.5
142.5°	287.3	299.3
145°	271.9	281.0
147.5°	260.1	267.5
150°	252.6	258.7
152.5°	246.2	250.9
155°	238.9	242.0
157.5°	233.1	235.3
160°	229.7	230.9
162.5°	227.4	228.6
165°	224.1	225.4
167.5°	221.8	222.3
170°	221.1	221.1
172.5°	219.4	219.0
175°	218.4	218.4
177.5°	217.4	217.0
180°	217.0	217.0

(END OF REPORT)