

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934993

Luminaire Tested: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934993
REPORT IS A COMBINATION OF REPORTS P933720 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15053.3 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 124
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	56	56	56
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	49	47	47	47	47
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	40	40	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	35	35	35
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	30	30	30
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26	26	26	26
7	60	47	39	33	56	45	37	32	39	33	29	35	30	26	30	26	23	23	23	23
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	21	21	21
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	19	19	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16364	16364	16364	16364
5°	16487	16519	16487	12989
10°	16376	16272	16376	11634
15°	16199	15919	16199	13294
20°	15860	15502	15860	13321
25°	15166	14893	15166	13039
30°	14270	14387	14270	12419
35°	12721	13747	12721	11738
40°	10601	12994	10601	11223
45°	9471	12113	9471	10631
50°	10062	11062	10062	10037
55°	9467	9929	9467	9694
60°	9758	8433	9758	8879
65°	8847	6971	8847	7792
70°	6127	5555	6127	6532
75°	5371	4107	5371	4917
80°	4329	2715	4329	2957
85°	2483	1438	2483	1223

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14516 cd/sqm

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.4	2.1
10°-20°	904.0	6.0
20°-30°	1397.4	9.3
30°-40°	1668.2	11.1
40°-50°	1678.0	11.1
50°-60°	1460.0	9.7
60°-70°	1035.2	6.9
70°-80°	547.7	3.6
80°-90°	139.9	0.9
90°-100°	444.0	2.9
100°-110°	1167.3	7.8
110°-120°	1210.3	8.0
120°-130°	970.8	6.4
130°-140°	761.8	5.1
140°-150°	584.7	3.9
150°-160°	421.1	2.8
160°-170°	257.6	1.7
170°-180°	87.0	0.6
0°-30°	2619.7	17.4
0°-40°	4287.9	28.5
0°-60°	7425.9	49.3
0°-90°	9148.6	60.8
90°-120°	2821.6	18.7
90°-150°	5138.9	34.1
90°-180°	5905.0	39.2
0°-180°	15053.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3527	3527	3527	3527	3527	
5°	3544	3654	3544	2873	3544	336
15°	3384	3620	3384	3023	3384	952
25°	2980	3377	2980	2956	2980	1368
35°	2266	3013	2266	2573	2266	1402
45°	1462	2483	1462	2179	1462	1171
55°	1191	1832	1191	1789	1191	1095
65°	828	1104	828	1235	828	791
75°	314	524	314	627	314	330
85°	53	134	53	114	53	72
90°	6	23	6	23	6	7
95°	59	268	59	268	59	65
105°	210	1828	210	1828	210	223
115°	374	2354	374	2354	374	369
125°	520	1874	520	1874	520	461
135°	619	1454	619	1454	619	479
145°	718	1180	718	1180	718	450
155°	812	1016	812	1016	812	373
165°	876	946	876	946	876	247
175°	911	917	911	917	911	86
180°	911	911	911	911	911	

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3557.1	3557.1	3577.1	3583.8	3583.8	3573.9	3563.8	3573.9	3603.8	3613.9	3610.5
5°	3543.8	3570.5	3607.2	3613.9	3620.5	3617.2	3610.5	3617.2	3650.6	3657.3	3660.6
7.5°	3517.1	3567.2	3613.9	3623.8	3633.9	3623.8	3620.5	3627.2	3660.6	3667.2	3667.2
10°	3483.7	3553.8	3607.2	3613.9	3623.8	3613.9	3613.9	3627.2	3660.6	3667.2	3670.6
12.5°	3437.0	3533.7	3583.8	3590.5	3603.8	3600.5	3597.2	3610.5	3643.9	3650.6	3650.6
15°	3383.7	3497.0	3543.8	3550.5	3573.9	3567.2	3567.2	3580.5	3617.2	3627.2	3623.8
17.5°	3310.2	3450.3	3503.8	3513.7	3530.5	3527.1	3530.5	3543.8	3577.1	3583.8	3587.2
20°	3226.8	3386.9	3450.3	3460.4	3477.0	3477.0	3477.0	3493.7	3527.1	3540.4	3540.4
22.5°	3113.3	3320.3	3386.9	3393.6	3413.6	3413.6	3420.3	3443.7	3473.7	3477.0	3477.0
25°	2979.9	3246.8	3303.5	3323.5	3343.5	3353.6	3363.6	3377.0	3386.9	3383.7	3386.9
27.5°	2839.7	3153.3	3226.8	3240.1	3266.8	3276.9	3290.2	3293.5	3296.9	3306.8	3300.1
30°	2682.9	3023.3	3133.3	3146.7	3190.1	3196.7	3183.4	3190.1	3206.8	3213.5	3220.1
32.5°	2506.0	2829.7	3036.6	3066.7	3106.7	3086.7	3083.3	3093.3	3120.0	3120.0	3126.7
35°	2265.7	2679.6	2946.5	2973.2	3003.2	2979.9	2993.2	2996.6	3013.2	3023.3	3019.9
37.5°	2002.2	2549.4	2853.1	2873.1	2896.5	2866.4	2886.4	2896.5	2909.8	2903.1	2903.1
40°	1768.6	2345.8	2743.0	2756.3	2776.3	2752.9	2772.9	2779.6	2786.3	2779.6	2776.3
42.5°	1595.1	2122.3	2626.1	2642.8	2629.5	2646.1	2652.8	2666.1	2656.2	2642.8	2642.8
45°	1461.5	2062.2	2499.3	2519.3	2499.3	2526.0	2536.1	2536.1	2506.0	2499.3	2496.0
47.5°	1418.2	1942.0	2372.5	2372.5	2362.6	2395.9	2412.5	2389.2	2359.2	2349.1	2349.1
50°	1414.8	1808.6	2199.0	2185.7	2232.4	2272.4	2255.8	2232.4	2209.0	2172.4	2172.4
52.5°	1284.7	1645.0	1975.5	2025.5	2098.9	2122.3	2095.5	2072.2	2032.1	2015.5	2002.2
55°	1191.3	1475.0	1771.9	1872.0	1948.7	1978.8	1928.7	1905.3	1845.3	1835.3	1828.6
57.5°	1171.3	1228.0	1585.0	1711.8	1805.3	1801.9	1771.9	1728.6	1678.5	1668.4	1665.2
60°	1074.4	887.6	1384.8	1535.0	1631.7	1621.8	1595.1	1555.0	1508.3	1501.6	1495.0
62.5°	974.4	644.1	1157.9	1328.0	1464.9	1461.5	1438.2	1378.1	1344.8	1328.0	1314.7
65°	827.5	540.6	824.2	1104.5	1301.4	1308.0	1258.0	1214.7	1177.9	1157.9	1154.6
67.5°	630.6	440.4	557.3	921.0	1144.5	1137.8	1074.4	1054.4	1007.8	997.7	977.7
70°	467.2	293.6	387.1	747.5	991.0	974.4	924.3	901.0	857.6	834.3	820.8
72.5°	387.1	236.9	283.7	580.7	834.3	814.2	770.9	744.1	707.5	687.4	674.0
75°	313.6	250.2	216.9	430.5	677.4	664.1	624.0	597.3	567.2	540.6	543.9
77.5°	230.2	233.6	173.5	317.0	537.3	517.3	493.9	460.5	447.2	420.4	420.4
80°	173.5	183.5	130.2	216.9	387.1	387.1	367.1	343.7	320.4	307.0	307.0
82.5°	116.7	116.7	96.7	136.9	263.7	253.6	240.3	233.6	220.3	213.6	213.6
85°	53.3	66.8	60.0	83.4	143.5	150.2	150.2	143.5	140.1	133.5	136.9
87.5°	16.7	30.1	36.7	46.7	73.5	76.7	80.1	80.1	80.1	83.4	83.4
90°	6.1	11.0	16.0	17.2	26.9	39.9	46.4	41.3	31.0	23.3	23.3
92.5°	24.5	66.1	107.7	118.0	165.9	229.7	261.7	229.3	164.7	116.2	111.5
95°	58.7	134.8	210.8	229.8	408.1	645.8	764.7	682.4	517.7	394.3	380.3
97.5°	101.5	168.6	235.8	252.5	549.8	946.2	1144.4	1092.3	988.3	910.3	883.7
100°	134.5	195.3	256.3	271.4	601.4	1041.2	1261.1	1264.9	1272.5	1278.3	1246.5
102.5°	162.6	219.4	276.2	290.4	624.9	1071.1	1294.1	1360.4	1493.0	1592.5	1565.3
105°	210.3	258.4	306.4	318.5	642.5	1074.4	1290.5	1439.1	1736.2	1959.2	1944.6
107.5°	259.2	304.1	348.8	360.1	645.7	1026.6	1217.1	1424.4	1839.0	2150.0	2153.5
110°	292.3	332.7	373.1	383.3	640.8	984.2	1156.0	1387.7	1851.2	2198.9	2214.1

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	324.6	363.1	401.7	411.4	641.0	947.3	1100.4	1337.6	1812.0	2167.7	2191.1
115°	373.5	409.1	444.7	453.6	646.9	904.8	1033.7	1262.2	1719.2	2061.9	2094.4
117.5°	421.8	454.2	486.5	494.6	659.0	878.2	987.9	1194.0	1606.5	1915.8	1951.7
120°	449.9	480.3	510.7	518.3	668.7	869.3	969.5	1158.0	1534.8	1817.4	1852.3
122.5°	477.4	508.2	538.8	546.5	682.8	864.5	955.4	1125.1	1464.5	1719.0	1753.4
125°	519.6	547.6	575.5	582.5	701.7	860.7	940.2	1084.3	1372.5	1588.7	1620.5
127.5°	553.8	582.1	610.3	617.4	720.8	858.5	927.3	1051.1	1298.6	1484.2	1510.9
130°	572.2	602.5	633.0	640.6	734.6	859.9	922.5	1032.6	1253.0	1418.3	1443.0
132.5°	591.1	621.6	652.0	659.6	745.8	860.7	918.2	1016.8	1214.1	1362.0	1384.1
135°	619.2	646.9	674.7	681.6	758.0	859.9	910.9	993.5	1158.6	1282.5	1301.6
137.5°	648.0	675.4	702.8	709.7	776.4	865.2	909.6	979.4	1119.1	1223.8	1239.4
140°	671.9	697.1	722.3	728.7	787.5	866.1	905.3	965.7	1086.3	1176.8	1191.4
142.5°	690.2	713.6	736.9	742.8	797.0	869.3	905.3	958.3	1064.3	1143.8	1156.3
145°	718.3	738.7	759.0	764.2	809.2	869.3	899.2	942.6	1029.3	1094.3	1103.7
147.5°	746.4	766.2	786.1	791.1	827.2	875.2	899.2	933.3	1001.5	1052.7	1060.5
150°	764.7	782.7	800.6	805.1	836.4	878.3	899.2	928.0	985.6	1028.8	1035.2
152.5°	783.7	797.3	810.9	814.2	842.5	880.3	899.2	923.8	973.0	1009.9	1014.7
155°	811.8	821.8	831.9	834.5	856.0	884.8	899.2	918.8	957.9	987.3	990.4
157.5°	832.6	842.3	852.1	854.6	869.5	889.3	899.2	914.4	944.9	967.7	969.9
160°	846.7	854.3	861.9	863.7	875.6	891.3	899.2	912.2	938.4	957.9	959.2
162.5°	860.7	866.4	872.1	873.6	882.2	893.5	899.2	910.3	932.3	948.7	949.9
165°	876.0	881.1	886.3	887.6	891.4	896.7	899.2	907.1	922.9	934.7	936.0
167.5°	890.1	892.5	895.0	895.6	898.8	903.2	905.3	910.5	920.8	928.6	929.1
170°	899.2	901.7	904.2	904.8	905.0	905.2	905.3	910.5	920.8	928.6	928.6
172.5°	904.2	904.7	905.2	905.3	905.3	905.3	905.3	909.4	917.6	923.7	923.2
175°	910.9	910.9	910.9	910.9	909.0	906.5	905.3	907.9	913.1	917.0	917.0
177.5°	910.9	910.9	910.9	910.9	909.4	907.5	906.5	908.6	912.6	915.7	915.2
180°	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3617.2	3607.2	3617.2	3610.5	3613.9	3603.8	3573.9	3563.8	3573.9	3583.8	3583.8
5°	3660.6	3653.9	3660.6	3660.6	3657.3	3650.6	3617.2	3610.5	3617.2	3620.5	3613.9
7.5°	3673.9	3663.9	3673.9	3667.2	3667.2	3660.6	3627.2	3620.5	3623.8	3633.9	3623.8
10°	3673.9	3663.9	3673.9	3670.6	3667.2	3660.6	3627.2	3613.9	3613.9	3623.8	3613.9
12.5°	3657.3	3650.6	3657.3	3650.6	3650.6	3643.9	3610.5	3597.2	3600.5	3603.8	3590.5
15°	3630.6	3620.5	3630.6	3623.8	3627.2	3617.2	3580.5	3567.2	3567.2	3573.9	3550.5
17.5°	3590.5	3577.1	3590.5	3587.2	3583.8	3577.1	3543.8	3530.5	3527.1	3530.5	3513.7
20°	3543.8	3533.7	3543.8	3540.4	3540.4	3527.1	3493.7	3477.0	3477.0	3477.0	3460.4
22.5°	3470.3	3460.4	3470.3	3477.0	3477.0	3473.7	3443.7	3420.3	3413.6	3413.6	3393.6
25°	3386.9	3377.0	3386.9	3386.9	3383.7	3386.9	3377.0	3363.6	3353.6	3343.5	3323.5
27.5°	3306.8	3300.1	3306.8	3300.1	3306.8	3296.9	3293.5	3290.2	3276.9	3266.8	3240.1
30°	3226.8	3220.1	3226.8	3220.1	3213.5	3206.8	3190.1	3183.4	3196.7	3190.1	3146.7
32.5°	3126.7	3120.0	3126.7	3126.7	3120.0	3120.0	3093.3	3083.3	3086.7	3106.7	3066.7
35°	3023.3	3013.2	3023.3	3019.9	3023.3	3013.2	2996.6	2993.2	2979.9	3003.2	2973.2
37.5°	2903.1	2893.1	2903.1	2903.1	2903.1	2909.8	2896.5	2886.4	2866.4	2896.5	2873.1
40°	2779.6	2766.3	2779.6	2776.3	2779.6	2786.3	2779.6	2772.9	2752.9	2776.3	2756.3
42.5°	2639.5	2636.2	2639.5	2642.8	2642.8	2656.2	2666.1	2652.8	2646.1	2629.5	2642.8
45°	2489.4	2482.6	2489.4	2496.0	2499.3	2506.0	2536.1	2536.1	2526.0	2499.3	2519.3
47.5°	2329.1	2312.5	2329.1	2349.1	2349.1	2359.2	2389.2	2412.5	2395.9	2362.6	2372.5
50°	2158.9	2162.3	2158.9	2172.4	2172.4	2209.0	2232.4	2255.8	2272.4	2232.4	2185.7
52.5°	1992.1	1988.8	1992.1	2002.2	2015.5	2032.1	2072.2	2095.5	2122.3	2098.9	2025.5
55°	1825.3	1832.0	1825.3	1828.6	1835.3	1845.3	1905.3	1928.7	1978.8	1948.7	1872.0
57.5°	1658.5	1648.4	1658.5	1665.2	1668.4	1678.5	1728.6	1771.9	1801.9	1805.3	1711.8
60°	1464.9	1451.6	1464.9	1495.0	1501.6	1508.3	1555.0	1595.1	1621.8	1631.7	1535.0
62.5°	1294.7	1271.3	1294.7	1314.7	1328.0	1344.8	1378.1	1438.2	1461.5	1464.9	1328.0
65°	1114.5	1104.5	1114.5	1154.6	1157.9	1177.9	1214.7	1258.0	1308.0	1301.4	1104.5
67.5°	951.0	951.0	951.0	977.7	997.7	1007.8	1054.4	1074.4	1137.8	1144.5	921.0
70°	800.8	797.5	800.8	820.8	834.3	857.6	901.0	924.3	974.4	991.0	747.5
72.5°	657.4	654.0	657.4	674.0	687.4	707.5	744.1	770.9	814.2	834.3	580.7
75°	530.6	523.9	530.6	543.9	540.6	567.2	597.3	624.0	664.1	677.4	430.5
77.5°	407.1	407.1	407.1	420.4	420.4	447.2	460.5	493.9	517.3	537.3	317.0
80°	303.7	300.3	303.7	307.0	307.0	320.4	343.7	367.1	387.1	387.1	216.9
82.5°	213.6	206.9	213.6	213.6	213.6	220.3	233.6	240.3	253.6	263.7	136.9
85°	133.5	133.5	133.5	136.9	133.5	140.1	143.5	150.2	150.2	143.5	83.4
87.5°	86.8	83.4	86.8	83.4	83.4	80.1	80.1	80.1	76.7	73.5	46.7
90°	23.3	23.3	23.3	23.3	23.3	31.0	41.3	46.4	39.9	26.9	17.2
92.5°	93.1	74.5	93.1	111.5	116.2	164.7	229.3	261.7	229.7	165.9	118.0
95°	324.4	268.4	324.4	380.3	394.3	517.7	682.4	764.7	645.8	408.1	229.8
97.5°	777.1	670.6	777.1	883.7	910.3	988.3	1092.3	1144.4	946.2	549.8	252.5
100°	1119.7	992.8	1119.7	1246.5	1278.3	1272.5	1264.9	1261.1	1041.2	601.4	271.4
102.5°	1456.6	1348.0	1456.6	1565.3	1592.5	1493.0	1360.4	1294.1	1071.1	624.9	290.4
105°	1886.1	1827.7	1886.1	1944.6	1959.2	1736.2	1439.1	1290.5	1074.4	642.5	318.5
107.5°	2167.6	2181.7	2167.6	2153.5	2150.0	1839.0	1424.4	1217.1	1026.6	645.7	360.1
110°	2275.0	2335.8	2275.0	2214.1	2198.9	1851.2	1387.7	1156.0	984.2	640.8	383.3

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	2284.5	2377.9	2284.5	2191.1	2167.7	1812.0	1337.6	1100.4	947.3	641.0	411.4
115°	2223.9	2353.5	2223.9	2094.4	2061.9	1719.2	1262.2	1033.7	904.8	646.9	453.6
117.5°	2095.4	2239.2	2095.4	1951.7	1915.8	1606.5	1194.0	987.9	878.2	659.0	494.6
120°	1992.0	2131.6	1992.0	1852.3	1817.4	1534.8	1158.0	969.5	869.3	668.7	518.3
122.5°	1891.1	2028.9	1891.1	1753.4	1719.0	1464.5	1125.1	955.4	864.5	682.8	546.5
125°	1747.4	1874.3	1747.4	1620.5	1588.7	1372.5	1084.3	940.2	860.7	701.7	582.5
127.5°	1618.0	1725.1	1618.0	1510.9	1484.2	1298.6	1051.1	927.3	858.5	720.8	617.4
130°	1541.8	1640.7	1541.8	1443.0	1418.3	1253.0	1032.6	922.5	859.9	734.6	640.6
132.5°	1472.7	1561.2	1472.7	1384.1	1362.0	1214.1	1016.8	918.2	860.7	745.8	659.6
135°	1377.9	1454.3	1377.9	1301.6	1282.5	1158.6	993.5	910.9	859.9	758.0	681.6
137.5°	1301.9	1364.4	1301.9	1239.4	1223.8	1119.1	979.4	909.6	865.2	776.4	709.7
140°	1249.9	1308.2	1249.9	1191.4	1176.8	1086.3	965.7	905.3	866.1	787.5	728.7
142.5°	1206.6	1256.9	1206.6	1156.3	1143.8	1064.3	958.3	905.3	869.3	797.0	742.8
145°	1141.8	1179.8	1141.8	1103.7	1094.3	1029.3	942.6	899.2	869.3	809.2	764.2
147.5°	1092.0	1123.5	1092.0	1060.5	1052.7	1001.5	933.3	899.2	875.2	827.2	791.1
150°	1060.7	1086.3	1060.7	1035.2	1028.8	985.6	928.0	899.2	878.3	836.4	805.1
152.5°	1033.9	1053.2	1033.9	1014.7	1009.9	973.0	923.8	899.2	880.3	842.5	814.2
155°	1003.3	1016.0	1003.3	990.4	987.3	957.9	918.8	899.2	884.8	856.0	834.5
157.5°	978.9	987.9	978.9	969.9	967.7	944.9	914.4	899.2	889.3	869.5	854.6
160°	964.4	969.5	964.4	959.2	957.9	938.4	912.2	899.2	891.3	875.6	863.7
162.5°	954.8	959.8	954.8	949.9	948.7	932.3	910.3	899.2	893.5	882.2	873.6
165°	941.1	946.3	941.1	936.0	934.7	922.9	907.1	899.2	896.7	891.4	887.6
167.5°	931.3	933.4	931.3	929.1	928.6	920.8	910.5	905.3	903.2	898.8	895.6
170°	928.6	928.6	928.6	928.6	928.6	920.8	910.5	905.3	905.2	905.0	904.8
172.5°	921.3	919.4	921.3	923.2	923.7	917.6	909.4	905.3	905.3	905.3	905.3
175°	917.0	917.0	917.0	917.0	917.0	913.1	907.9	905.3	906.5	909.0	910.9
177.5°	913.0	910.9	913.0	915.2	915.7	912.6	908.6	906.5	907.5	909.4	910.9
180°	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3577.1	3557.1	3557.1	3523.8	3510.5	3500.4	3483.7	3433.6	3420.3	3406.9	3427.0
5°	3607.2	3570.5	3543.8	3483.7	3433.6	3413.6	3350.2	3230.1	3150.1	3089.9	3056.6
7.5°	3613.9	3567.2	3517.1	3423.7	3303.5	3250.2	3056.6	2836.3	2776.3	2722.9	2689.5
10°	3607.2	3553.8	3483.7	3343.5	3060.0	2966.5	2772.9	2629.5	2592.8	2582.7	2592.8
12.5°	3583.8	3533.7	3437.0	3203.4	2806.4	2743.0	2629.5	2546.0	2539.3	2556.1	2646.1
15°	3543.8	3497.0	3383.7	3016.6	2666.1	2619.5	2539.3	2509.4	2546.0	2662.9	2933.2
17.5°	3503.8	3450.3	3310.2	2833.1	2559.4	2526.0	2469.3	2529.4	2736.2	2893.1	2983.1
20°	3450.3	3386.9	3226.8	2699.6	2482.6	2452.6	2426.0	2696.2	2853.1	2909.8	2959.9
22.5°	3386.9	3320.3	3113.3	2606.1	2402.6	2379.2	2395.9	2789.7	2853.1	2893.1	2936.5
25°	3303.5	3246.8	2979.9	2532.7	2339.2	2312.5	2375.9	2779.6	2816.3	2826.4	2913.1
27.5°	3226.8	3153.3	2839.7	2466.0	2262.4	2252.4	2392.5	2736.2	2763.0	2772.9	2866.4
30°	3133.3	3023.3	2682.9	2395.9	2182.3	2179.0	2395.9	2682.9	2676.2	2702.9	2796.3
32.5°	3036.6	2829.7	2506.0	2309.1	2105.6	2102.3	2372.5	2602.7	2596.1	2632.8	2702.9
35°	2946.5	2679.6	2265.7	2209.0	2008.8	2012.1	2315.8	2509.4	2512.7	2546.0	2589.4
37.5°	2853.1	2549.4	2002.2	2098.9	1915.4	1915.4	2239.0	2422.6	2415.9	2426.0	2486.0
40°	2743.0	2345.8	1768.6	1955.4	1828.6	1818.6	2145.6	2329.1	2305.8	2302.5	2385.9
42.5°	2626.1	2122.3	1595.1	1765.2	1728.6	1715.1	2032.1	2215.7	2172.4	2182.3	2289.1
45°	2499.3	2062.2	1461.5	1491.6	1625.0	1615.1	1908.7	2085.6	2055.5	2082.2	2192.4
47.5°	2372.5	1942.0	1418.2	1238.0	1515.0	1511.6	1771.9	1958.8	1942.0	1968.7	2085.6
50°	2199.0	1808.6	1414.8	1061.1	1391.4	1404.9	1608.4	1835.3	1835.3	1858.6	1982.2
52.5°	1975.5	1645.0	1284.7	961.1	1248.0	1288.0	1464.9	1728.6	1735.2	1758.5	1868.7
55°	1771.9	1475.0	1191.3	884.2	1077.8	1164.6	1324.8	1618.4	1631.7	1655.1	1755.2
57.5°	1585.0	1228.0	1171.3	794.2	921.0	1004.4	1201.2	1511.6	1518.2	1538.4	1635.1
60°	1384.8	887.6	1074.4	697.4	784.2	847.6	1087.9	1384.8	1408.2	1421.5	1504.9
62.5°	1157.9	644.1	974.4	630.6	717.4	730.8	994.4	1264.6	1294.7	1304.8	1354.8
65°	824.2	540.6	827.5	574.0	647.3	650.7	894.3	1141.2	1167.9	1184.6	1221.3
67.5°	557.3	440.4	630.6	520.5	594.0	597.3	797.5	997.7	1034.4	1047.8	1071.2
70°	387.1	293.6	467.2	463.8	533.9	540.6	694.0	867.6	901.0	911.0	924.3
72.5°	283.7	236.9	387.1	417.1	470.5	477.2	587.3	720.8	754.1	764.2	770.9
75°	216.9	250.2	313.6	363.7	400.4	403.8	480.5	587.3	610.6	617.3	620.7
77.5°	173.5	233.6	230.2	293.6	327.1	320.4	377.0	453.9	473.9	473.9	473.9
80°	130.2	183.5	173.5	210.2	240.3	233.6	270.3	323.7	330.3	337.0	333.7
82.5°	96.7	116.7	116.7	133.5	160.1	153.5	180.2	210.2	210.2	210.2	216.9
85°	60.0	66.8	53.3	70.1	90.1	86.8	100.1	113.5	116.7	116.7	110.1
87.5°	36.7	30.1	16.7	26.7	40.0	40.0	46.7	50.1	46.7	46.7	46.7
90°	16.0	11.0	6.1	11.0	16.0	17.2	26.9	39.9	46.4	41.3	31.0
92.5°	107.7	66.1	24.5	66.1	107.7	118.0	165.9	229.7	261.7	229.3	164.7
95°	210.8	134.8	58.7	134.8	210.8	229.8	408.1	645.8	764.7	682.4	517.7
97.5°	235.8	168.6	101.5	168.6	235.8	252.5	549.8	946.2	1144.4	1092.3	988.3
100°	256.3	195.3	134.5	195.3	256.3	271.4	601.4	1041.2	1261.1	1264.9	1272.5
102.5°	276.2	219.4	162.6	219.4	276.2	290.4	624.9	1071.1	1294.1	1360.4	1493.0
105°	306.4	258.4	210.3	258.4	306.4	318.5	642.5	1074.4	1290.5	1439.1	1736.2
107.5°	348.8	304.1	259.2	304.1	348.8	360.1	645.7	1026.6	1217.1	1424.4	1839.0
110°	373.1	332.7	292.3	332.7	373.1	383.3	640.8	984.2	1156.0	1387.7	1851.2

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	401.7	363.1	324.6	363.1	401.7	411.4	641.0	947.3	1100.4	1337.6	1812.0
115°	444.7	409.1	373.5	409.1	444.7	453.6	646.9	904.8	1033.7	1262.2	1719.2
117.5°	486.5	454.2	421.8	454.2	486.5	494.6	659.0	878.2	987.9	1194.0	1606.5
120°	510.7	480.3	449.9	480.3	510.7	518.3	668.7	869.3	969.5	1158.0	1534.8
122.5°	538.8	508.2	477.4	508.2	538.8	546.5	682.8	864.5	955.4	1125.1	1464.5
125°	575.5	547.6	519.6	547.6	575.5	582.5	701.7	860.7	940.2	1084.3	1372.5
127.5°	610.3	582.1	553.8	582.1	610.3	617.4	720.8	858.5	927.3	1051.1	1298.6
130°	633.0	602.5	572.2	602.5	633.0	640.6	734.6	859.9	922.5	1032.6	1253.0
132.5°	652.0	621.6	591.1	621.6	652.0	659.6	745.8	860.7	918.2	1016.8	1214.1
135°	674.7	646.9	619.2	646.9	674.7	681.6	758.0	859.9	910.9	993.5	1158.6
137.5°	702.8	675.4	648.0	675.4	702.8	709.7	776.4	865.2	909.6	979.4	1119.1
140°	722.3	697.1	671.9	697.1	722.3	728.7	787.5	866.1	905.3	965.7	1086.3
142.5°	736.9	713.6	690.2	713.6	736.9	742.8	797.0	869.3	905.3	958.3	1064.3
145°	759.0	738.7	718.3	738.7	759.0	764.2	809.2	869.3	899.2	942.6	1029.3
147.5°	786.1	766.2	746.4	766.2	786.1	791.1	827.2	875.2	899.2	933.3	1001.5
150°	800.6	782.7	764.7	782.7	800.6	805.1	836.4	878.3	899.2	928.0	985.6
152.5°	810.9	797.3	783.7	797.3	810.9	814.2	842.5	880.3	899.2	923.8	973.0
155°	831.9	821.8	811.8	821.8	831.9	834.5	856.0	884.8	899.2	918.8	957.9
157.5°	852.1	842.3	832.6	842.3	852.1	854.6	869.5	889.3	899.2	914.4	944.9
160°	861.9	854.3	846.7	854.3	861.9	863.7	875.6	891.3	899.2	912.2	938.4
162.5°	872.1	866.4	860.7	866.4	872.1	873.6	882.2	893.5	899.2	910.3	932.3
165°	886.3	881.1	876.0	881.1	886.3	887.6	891.4	896.7	899.2	907.1	922.9
167.5°	895.0	892.5	890.1	892.5	895.0	895.6	898.8	903.2	905.3	910.5	920.8
170°	904.2	901.7	899.2	901.7	904.2	904.8	905.0	905.2	905.3	910.5	920.8
172.5°	905.2	904.7	904.2	904.7	905.2	905.3	905.3	905.3	905.3	909.4	917.6
175°	910.9	910.9	910.9	910.9	910.9	910.9	909.0	906.5	905.3	907.9	913.1
177.5°	910.9	910.9	910.9	910.9	910.9	910.9	909.4	907.5	906.5	908.6	912.6
180°	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3403.7	3393.6	3406.9	3370.2	3406.9	3393.6	3403.7	3427.0	3406.9	3420.3	3433.6
5°	2986.5	2969.8	2916.5	2873.1	2916.5	2969.8	2986.5	3056.6	3089.9	3150.1	3230.1
7.5°	2669.5	2656.2	2642.8	2616.2	2642.8	2656.2	2669.5	2689.5	2722.9	2776.3	2836.3
10°	2599.5	2602.7	2622.8	2619.5	2622.8	2602.7	2599.5	2592.8	2582.7	2592.8	2629.5
12.5°	2779.6	2809.7	2919.7	2913.1	2919.7	2809.7	2779.6	2646.1	2556.1	2539.3	2546.0
15°	2986.5	2996.6	3019.9	3023.3	3019.9	2996.6	2986.5	2933.2	2662.9	2546.0	2509.4
17.5°	3006.5	3009.9	3026.5	3026.5	3026.5	3009.9	3006.5	2983.1	2893.1	2736.2	2529.4
20°	2989.8	2996.6	3029.9	3036.6	3029.9	2996.6	2989.8	2959.9	2909.8	2853.1	2696.2
22.5°	2983.1	2996.6	3023.3	3019.9	3023.3	2996.6	2983.1	2936.5	2893.1	2853.1	2789.7
25°	2949.8	2949.8	2953.2	2956.5	2953.2	2949.8	2949.8	2913.1	2826.4	2816.3	2779.6
27.5°	2879.7	2886.4	2906.4	2903.1	2906.4	2886.4	2879.7	2866.4	2772.9	2763.0	2736.2
30°	2816.3	2809.7	2792.9	2779.6	2792.9	2809.7	2816.3	2796.3	2702.9	2676.2	2682.9
32.5°	2709.5	2692.9	2676.2	2666.1	2676.2	2692.9	2709.5	2702.9	2632.8	2596.1	2602.7
35°	2582.7	2586.1	2582.7	2572.8	2582.7	2586.1	2582.7	2589.4	2546.0	2512.7	2509.4
37.5°	2492.7	2499.3	2496.0	2482.6	2496.0	2499.3	2492.7	2486.0	2426.0	2415.9	2422.6
40°	2399.2	2402.6	2399.2	2389.2	2399.2	2402.6	2399.2	2385.9	2302.5	2305.8	2329.1
42.5°	2309.1	2305.8	2295.8	2289.1	2295.8	2305.8	2309.1	2289.1	2182.3	2172.4	2215.7
45°	2205.7	2209.0	2189.0	2179.0	2189.0	2209.0	2205.7	2192.4	2082.2	2055.5	2085.6
47.5°	2102.3	2102.3	2085.6	2075.5	2085.6	2102.3	2102.3	2085.6	1968.7	1942.0	1958.8
50°	1992.1	1988.8	1965.4	1962.1	1965.4	1988.8	1992.1	1982.2	1858.6	1835.3	1835.3
52.5°	1865.3	1865.3	1868.7	1875.4	1868.7	1865.3	1865.3	1868.7	1758.5	1735.2	1728.6
55°	1755.2	1758.5	1781.9	1788.6	1781.9	1758.5	1755.2	1755.2	1655.1	1631.7	1618.4
57.5°	1641.8	1641.8	1658.5	1658.5	1658.5	1641.8	1641.8	1635.1	1538.4	1518.2	1511.6
60°	1511.6	1518.2	1531.7	1528.3	1531.7	1518.2	1511.6	1504.9	1421.5	1408.2	1384.8
62.5°	1374.8	1381.5	1384.8	1378.1	1384.8	1381.5	1374.8	1354.8	1304.8	1294.7	1264.6
65°	1231.3	1238.0	1241.4	1234.7	1241.4	1238.0	1231.3	1221.3	1184.6	1167.9	1141.2
67.5°	1084.5	1081.1	1077.8	1091.2	1077.8	1081.1	1084.5	1071.2	1047.8	1034.4	997.7
70°	934.3	934.3	931.0	937.7	931.0	934.3	934.3	924.3	911.0	901.0	867.6
72.5°	774.2	770.9	784.2	774.2	784.2	770.9	774.2	770.9	764.2	754.1	720.8
75°	617.3	624.0	617.3	627.3	617.3	624.0	617.3	620.7	617.3	610.6	587.3
77.5°	470.5	477.2	470.5	470.5	470.5	477.2	470.5	473.9	473.9	473.9	453.9
80°	333.7	330.3	330.3	327.1	330.3	330.3	333.7	333.7	337.0	330.3	323.7
82.5°	213.6	210.2	210.2	216.9	210.2	210.2	213.6	216.9	210.2	210.2	210.2
85°	116.7	120.1	113.5	113.5	113.5	120.1	116.7	110.1	116.7	116.7	113.5
87.5°	43.4	40.0	40.0	40.0	40.0	40.0	43.4	46.7	46.7	46.7	50.1
90°	23.3	23.3	23.3	23.3	23.3	23.3	23.3	31.0	41.3	46.4	39.9
92.5°	116.2	111.5	93.1	74.5	93.1	111.5	116.2	164.7	229.3	261.7	229.7
95°	394.3	380.3	324.4	268.4	324.4	380.3	394.3	517.7	682.4	764.7	645.8
97.5°	910.3	883.7	777.1	670.6	777.1	883.7	910.3	988.3	1092.3	1144.4	946.2
100°	1278.3	1246.5	1119.7	992.8	1119.7	1246.5	1278.3	1272.5	1264.9	1261.1	1041.2
102.5°	1592.5	1565.3	1456.6	1348.0	1456.6	1565.3	1592.5	1493.0	1360.4	1294.1	1071.1
105°	1959.2	1944.6	1886.1	1827.7	1886.1	1944.6	1959.2	1736.2	1439.1	1290.5	1074.4
107.5°	2150.0	2153.5	2167.6	2181.7	2167.6	2153.5	2150.0	1839.0	1424.4	1217.1	1026.6
110°	2198.9	2214.1	2275.0	2335.8	2275.0	2214.1	2198.9	1851.2	1387.7	1156.0	984.2

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	2167.7	2191.1	2284.5	2377.9	2284.5	2191.1	2167.7	1812.0	1337.6	1100.4	947.3
115°	2061.9	2094.4	2223.9	2353.5	2223.9	2094.4	2061.9	1719.2	1262.2	1033.7	904.8
117.5°	1915.8	1951.7	2095.4	2239.2	2095.4	1951.7	1915.8	1606.5	1194.0	987.9	878.2
120°	1817.4	1852.3	1992.0	2131.6	1992.0	1852.3	1817.4	1534.8	1158.0	969.5	869.3
122.5°	1719.0	1753.4	1891.1	2028.9	1891.1	1753.4	1719.0	1464.5	1125.1	955.4	864.5
125°	1588.7	1620.5	1747.4	1874.3	1747.4	1620.5	1588.7	1372.5	1084.3	940.2	860.7
127.5°	1484.2	1510.9	1618.0	1725.1	1618.0	1510.9	1484.2	1298.6	1051.1	927.3	858.5
130°	1418.3	1443.0	1541.8	1640.7	1541.8	1443.0	1418.3	1253.0	1032.6	922.5	859.9
132.5°	1362.0	1384.1	1472.7	1561.2	1472.7	1384.1	1362.0	1214.1	1016.8	918.2	860.7
135°	1282.5	1301.6	1377.9	1454.3	1377.9	1301.6	1282.5	1158.6	993.5	910.9	859.9
137.5°	1223.8	1239.4	1301.9	1364.4	1301.9	1239.4	1223.8	1119.1	979.4	909.6	865.2
140°	1176.8	1191.4	1249.9	1308.2	1249.9	1191.4	1176.8	1086.3	965.7	905.3	866.1
142.5°	1143.8	1156.3	1206.6	1256.9	1206.6	1156.3	1143.8	1064.3	958.3	905.3	869.3
145°	1094.3	1103.7	1141.8	1179.8	1141.8	1103.7	1094.3	1029.3	942.6	899.2	869.3
147.5°	1052.7	1060.5	1092.0	1123.5	1092.0	1060.5	1052.7	1001.5	933.3	899.2	875.2
150°	1028.8	1035.2	1060.7	1086.3	1060.7	1035.2	1028.8	985.6	928.0	899.2	878.3
152.5°	1009.9	1014.7	1033.9	1053.2	1033.9	1014.7	1009.9	973.0	923.8	899.2	880.3
155°	987.3	990.4	1003.3	1016.0	1003.3	990.4	987.3	957.9	918.8	899.2	884.8
157.5°	967.7	969.9	978.9	987.9	978.9	969.9	967.7	944.9	914.4	899.2	889.3
160°	957.9	959.2	964.4	969.5	964.4	959.2	957.9	938.4	912.2	899.2	891.3
162.5°	948.7	949.9	954.8	959.8	954.8	949.9	948.7	932.3	910.3	899.2	893.5
165°	934.7	936.0	941.1	946.3	941.1	936.0	934.7	922.9	907.1	899.2	896.7
167.5°	928.6	929.1	931.3	933.4	931.3	929.1	928.6	920.8	910.5	905.3	903.2
170°	928.6	928.6	928.6	928.6	928.6	928.6	928.6	920.8	910.5	905.3	905.2
172.5°	923.7	923.2	921.3	919.4	921.3	923.2	923.7	917.6	909.4	905.3	905.3
175°	917.0	917.0	917.0	917.0	917.0	917.0	917.0	913.1	907.9	905.3	906.5
177.5°	915.7	915.2	913.0	910.9	913.0	915.2	915.7	912.6	908.6	906.5	907.5
180°	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9	910.9

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	3527.1	3527.1	3527.1	3527.1	3527.1
2.5°	3483.7	3500.4	3510.5	3523.8	3557.1
5°	3350.2	3413.6	3433.6	3483.7	3543.8
7.5°	3056.6	3250.2	3303.5	3423.7	3517.1
10°	2772.9	2966.5	3060.0	3343.5	3483.7
12.5°	2629.5	2743.0	2806.4	3203.4	3437.0
15°	2539.3	2619.5	2666.1	3016.6	3383.7
17.5°	2469.3	2526.0	2559.4	2833.1	3310.2
20°	2426.0	2452.6	2482.6	2699.6	3226.8
22.5°	2395.9	2379.2	2402.6	2606.1	3113.3
25°	2375.9	2312.5	2339.2	2532.7	2979.9
27.5°	2392.5	2252.4	2262.4	2466.0	2839.7
30°	2395.9	2179.0	2182.3	2395.9	2682.9
32.5°	2372.5	2102.3	2105.6	2309.1	2506.0
35°	2315.8	2012.1	2008.8	2209.0	2265.7
37.5°	2239.0	1915.4	1915.4	2098.9	2002.2
40°	2145.6	1818.6	1828.6	1955.4	1768.6
42.5°	2032.1	1715.1	1728.6	1765.2	1595.1
45°	1908.7	1615.1	1625.0	1491.6	1461.5
47.5°	1771.9	1511.6	1515.0	1238.0	1418.2
50°	1608.4	1404.9	1391.4	1061.1	1414.8
52.5°	1464.9	1288.0	1248.0	961.1	1284.7
55°	1324.8	1164.6	1077.8	884.2	1191.3
57.5°	1201.2	1004.4	921.0	794.2	1171.3
60°	1087.9	847.6	784.2	697.4	1074.4
62.5°	994.4	730.8	717.4	630.6	974.4
65°	894.3	650.7	647.3	574.0	827.5
67.5°	797.5	597.3	594.0	520.5	630.6
70°	694.0	540.6	533.9	463.8	467.2
72.5°	587.3	477.2	470.5	417.1	387.1
75°	480.5	403.8	400.4	363.7	313.6
77.5°	377.0	320.4	327.1	293.6	230.2
80°	270.3	233.6	240.3	210.2	173.5
82.5°	180.2	153.5	160.1	133.5	116.7
85°	100.1	86.8	90.1	70.1	53.3
87.5°	46.7	40.0	40.0	26.7	16.7
90°	26.9	17.2	16.0	11.0	6.1
92.5°	165.9	118.0	107.7	66.1	24.5
95°	408.1	229.8	210.8	134.8	58.7
97.5°	549.8	252.5	235.8	168.6	101.5
100°	601.4	271.4	256.3	195.3	134.5
102.5°	624.9	290.4	276.2	219.4	162.6
105°	642.5	318.5	306.4	258.4	210.3
107.5°	645.7	360.1	348.8	304.1	259.2
110°	640.8	383.3	373.1	332.7	292.3



TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	641.0	411.4	401.7	363.1	324.6
115°	646.9	453.6	444.7	409.1	373.5
117.5°	659.0	494.6	486.5	454.2	421.8
120°	668.7	518.3	510.7	480.3	449.9
122.5°	682.8	546.5	538.8	508.2	477.4
125°	701.7	582.5	575.5	547.6	519.6
127.5°	720.8	617.4	610.3	582.1	553.8
130°	734.6	640.6	633.0	602.5	572.2
132.5°	745.8	659.6	652.0	621.6	591.1
135°	758.0	681.6	674.7	646.9	619.2
137.5°	776.4	709.7	702.8	675.4	648.0
140°	787.5	728.7	722.3	697.1	671.9
142.5°	797.0	742.8	736.9	713.6	690.2
145°	809.2	764.2	759.0	738.7	718.3
147.5°	827.2	791.1	786.1	766.2	746.4
150°	836.4	805.1	800.6	782.7	764.7
152.5°	842.5	814.2	810.9	797.3	783.7
155°	856.0	834.5	831.9	821.8	811.8
157.5°	869.5	854.6	852.1	842.3	832.6
160°	875.6	863.7	861.9	854.3	846.7
162.5°	882.2	873.6	872.1	866.4	860.7
165°	891.4	887.6	886.3	881.1	876.0
167.5°	898.8	895.6	895.0	892.5	890.1
170°	905.0	904.8	904.2	901.7	899.2
172.5°	905.3	905.3	905.2	904.7	904.2
175°	909.0	910.9	910.9	910.9	910.9
177.5°	909.4	910.9	910.9	910.9	910.9
180°	910.9	910.9	910.9	910.9	910.9

TEST NUMBER: P934993

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-8-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.46	16.42	16.32	17.31	18.41	18.30	19.26	19.15	20.14	21.25
	3H	15.94	16.81	16.81	17.70	18.83	19.65	20.52	20.52	21.41	22.54
	4H	16.14	16.96	17.03	17.85	19.00	20.10	20.92	20.99	21.82	22.96
	6H	16.26	17.02	17.16	17.92	19.08	20.39	21.15	21.29	22.05	23.21
	8H	16.27	16.99	17.17	17.91	19.06	20.47	21.19	21.38	22.11	23.27
	12H	16.24	16.93	17.15	17.84	19.02	20.52	21.20	21.43	22.12	23.30
4H	2H	16.50	17.32	17.40	18.22	19.37	18.72	19.54	19.61	20.43	21.58
	3H	17.54	18.22	18.45	19.15	20.31	20.24	20.92	21.14	21.85	23.01
	4H	17.82	18.44	18.74	19.37	20.55	20.77	21.39	21.68	22.32	23.50
	6H	17.95	18.49	18.88	19.44	20.62	21.14	21.68	22.07	22.63	23.81
	8H	17.96	18.46	18.89	19.40	20.61	21.25	21.75	22.18	22.70	23.90
	12H	17.93	18.39	18.88	19.35	20.55	21.32	21.77	22.27	22.73	23.93
8H	4H	18.29	18.79	19.22	19.73	20.93	20.90	21.40	21.83	22.35	23.55
	6H	18.55	18.97	19.51	19.95	21.15	21.34	21.76	22.30	22.74	23.94
	8H	18.60	18.96	19.56	19.94	21.15	21.50	21.87	22.47	22.84	24.06
	12H	18.58	18.91	19.55	19.87	21.14	21.60	21.93	22.57	22.89	24.16
12H	4H	18.30	18.75	19.25	19.71	20.91	20.87	21.32	21.82	22.28	23.49
	6H	18.61	18.98	19.58	19.95	21.17	21.34	21.71	22.31	22.68	23.90
	8H	18.69	19.01	19.66	19.97	21.24	21.51	21.83	22.48	22.80	24.07