

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936500

Luminaire Tested: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936500
REPORT IS A COMBINATION OF REPORTS P933455 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8036.9 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936500

CATALOG NUMBER: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P936500

CATALOG NUMBER: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3695	3695	3695
5°	3610	4270	4967
10°	3274	6225	8234
15°	2783	8133	9943
20°	2266	9425	10133
25°	1890	9863	9927
30°	1594	9925	9908
35°	1409	9760	10164
40°	1228	9546	10429
45°	1112	9390	10470
50°	1020	9248	10296
55°	977	9041	9840
60°	1000	8645	9120
65°	1040	8041	8129
70°	1108	7012	6868
75°	1228	5717	5359
80°	1342	3964	3611
85°	1192	2104	1849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10470 cd/sqm

TEST NUMBER: P936500

CATALOG NUMBER: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.0	1.3
10°-20°	456.6	5.7
20°-30°	798.6	9.9
30°-40°	1028.1	12.8
40°-50°	1148.3	14.3
50°-60°	1099.8	13.7
60°-70°	871.6	10.8
70°-80°	512.5	6.4
80°-90°	143.5	1.8
90°-100°	141.0	1.8
100°-110°	370.6	4.6
110°-120°	384.3	4.8
120°-130°	308.3	3.8
130°-140°	241.9	3.0
140°-150°	185.7	2.3
150°-160°	133.7	1.7
160°-170°	81.8	1.0
170°-180°	27.6	0.3
0°-30°	1358.2	16.9
0°-40°	2386.3	29.7
0°-60°	4634.4	57.7
0°-90°	6162.0	76.7
90°-120°	895.9	11.1
90°-150°	1631.8	20.3
90°-180°	1875.0	23.3
0°-180°	8036.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	796	796	796	796	796	
5°	776	832	937	1060	1099	72
15°	581	1073	1808	2192	2261	162
25°	371	1216	2154	2248	2251	171
35°	251	1163	2028	2143	2228	157
45°	172	927	1793	2054	2146	133
55°	123	589	1521	1767	1816	112
65°	97	312	1129	1270	1288	96
75°	72	192	620	681	684	75
85°	26	59	154	169	172	27
90°	2	5	15	7	7	3
95°	19	73	243	125	85	21
105°	67	101	410	622	580	71
115°	119	144	328	655	747	117
125°	165	185	298	504	595	146
135°	197	216	289	407	462	152
145°	228	243	286	348	375	143
155°	258	265	286	314	323	118
165°	278	282	286	297	300	79
175°	289	289	288	291	291	27
180°	289	289	289	289	289	

TEST NUMBER: P936500

CATALOG NUMBER: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	796.4	796.4	796.4	796.4	796.4	796.4	796.4	796.4	796.4	796.4	796.4
2.5°	796.4	796.4	801.6	804.1	809.2	811.7	816.9	822.0	837.4	839.9	845.1
5°	775.9	786.1	819.5	832.3	868.1	916.8	937.2	970.6	1039.6	1060.2	1073.0
7.5°	745.2	768.2	850.2	870.6	960.3	1088.3	1142.1	1213.8	1323.9	1377.7	1421.2
10°	696.5	745.2	891.2	939.8	1085.8	1280.3	1380.2	1480.1	1646.5	1720.8	1748.9
12.5°	642.7	722.1	934.7	1001.3	1211.2	1495.5	1615.8	1726.0	1915.4	2015.3	2030.6
15°	581.3	688.9	975.7	1073.0	1344.4	1674.7	1807.9	1943.6	2120.3	2192.0	2209.9
17.5°	527.5	663.3	1014.1	1116.5	1446.8	1836.1	1971.8	2084.4	2227.8	2276.5	2289.4
20°	461.0	622.3	1039.6	1172.8	1554.4	1953.9	2084.4	2171.5	2268.8	2299.5	2304.7
22.5°	412.3	578.7	1055.0	1193.3	1626.1	2025.6	2135.7	2204.8	2271.4	2281.6	2284.2
25°	371.3	530.0	1052.4	1216.4	1687.5	2069.1	2153.6	2204.8	2243.2	2248.4	2248.4
27.5°	332.9	476.3	1042.3	1221.5	1733.6	2079.4	2145.9	2181.8	2199.7	2209.9	2209.9
30°	299.6	425.1	1016.6	1211.2	1754.1	2069.1	2122.9	2140.8	2158.7	2174.0	2181.8
32.5°	274.0	376.5	978.2	1190.7	1756.7	2043.5	2081.9	2092.2	2117.7	2153.6	2166.4
35°	251.0	327.8	934.7	1162.6	1741.3	2002.5	2028.1	2038.4	2089.6	2143.3	2161.3
37.5°	227.9	292.0	878.3	1114.0	1718.2	1953.9	1971.8	1989.7	2069.1	2133.1	2153.6
40°	204.8	261.2	811.7	1060.2	1682.4	1895.0	1910.3	1938.5	2043.5	2117.7	2138.2
42.5°	186.9	235.6	740.0	1003.8	1636.4	1828.4	1851.5	1892.4	2012.7	2092.2	2115.2
45°	171.6	210.0	663.3	926.9	1577.4	1759.2	1792.6	1848.9	1976.9	2053.7	2074.2
47.5°	156.2	192.1	583.8	847.6	1513.4	1690.1	1733.6	1797.7	1928.2	2002.5	2020.5
50°	143.4	174.1	504.5	763.1	1444.3	1615.8	1667.1	1733.6	1866.8	1936.0	1958.9
52.5°	133.1	158.7	430.2	678.6	1364.8	1539.0	1597.9	1667.1	1792.6	1859.1	1874.4
55°	122.9	145.9	366.2	589.0	1283.0	1457.1	1521.0	1587.7	1710.6	1766.9	1777.1
57.5°	117.8	135.8	312.4	504.5	1195.8	1364.8	1436.5	1498.1	1613.3	1656.8	1667.1
60°	110.1	128.0	271.4	432.8	1101.2	1277.8	1339.3	1400.7	1498.1	1533.9	1541.6
62.5°	102.4	122.9	240.7	363.7	1003.8	1175.4	1236.8	1293.2	1375.1	1400.7	1411.0
65°	97.3	117.8	217.6	312.4	904.0	1067.8	1129.3	1177.9	1244.5	1270.2	1275.3
67.5°	92.2	112.7	199.7	268.9	804.1	960.3	1006.4	1052.4	1103.7	1129.3	1131.9
70°	84.5	107.6	184.4	238.2	701.7	837.4	875.8	924.4	965.4	978.2	985.9
72.5°	79.4	99.9	174.1	215.1	596.6	719.6	755.4	783.6	819.5	832.3	832.3
75°	71.7	89.6	163.9	192.1	489.2	589.0	619.7	647.9	676.1	681.2	673.5
77.5°	64.1	79.4	140.8	161.3	381.6	466.1	491.7	507.0	530.0	535.2	537.8
80°	53.8	69.2	110.1	125.5	276.6	343.1	361.0	373.8	394.4	394.4	399.5
82.5°	41.0	53.8	79.4	89.6	186.9	235.6	251.0	258.6	271.4	271.4	271.4
85°	25.6	33.3	51.3	58.9	112.7	143.4	153.7	156.2	166.5	169.0	169.0
87.5°	12.8	17.9	33.3	35.9	58.9	74.2	74.2	79.4	79.4	76.8	74.2
90°	1.9	3.5	5.0	5.4	8.5	12.7	14.7	13.1	9.8	7.4	7.4
92.5°	7.8	20.9	34.2	37.5	52.7	73.0	83.0	72.8	52.3	36.9	35.5
95°	18.6	42.7	67.0	73.0	129.6	205.0	242.8	216.7	164.4	125.2	120.7
97.5°	32.3	53.6	74.8	80.1	174.5	300.4	363.4	346.9	313.9	289.1	280.6
100°	42.7	62.0	81.3	86.1	190.9	330.5	400.4	401.7	404.1	405.9	395.8
102.5°	51.6	69.7	87.7	92.2	198.5	340.1	411.0	432.0	474.0	505.6	497.0
105°	66.8	82.1	97.4	101.2	204.1	341.2	409.8	457.0	551.4	622.1	617.4
107.5°	82.3	96.5	110.8	114.3	205.0	326.0	386.4	452.2	583.9	682.7	683.8
110°	92.8	105.6	118.5	121.7	203.5	312.5	367.1	440.6	587.8	698.2	703.0

TEST NUMBER: P936500

CATALOG NUMBER: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	103.1	115.3	127.5	130.6	203.6	300.8	349.4	424.7	575.3	688.3	695.7
115°	118.6	129.8	141.2	144.0	205.4	287.3	328.2	400.8	545.9	654.8	665.0
117.5°	133.9	144.2	154.5	157.1	209.3	278.9	313.7	379.2	510.1	608.3	619.8
120°	142.8	152.5	162.2	164.6	212.4	276.1	307.9	367.6	487.3	577.0	588.1
122.5°	151.6	161.3	171.1	173.5	216.9	274.5	303.4	357.3	465.0	545.8	556.8
125°	165.0	173.9	182.8	185.0	222.9	273.4	298.5	344.3	435.9	504.5	514.5
127.5°	175.9	184.8	193.8	196.0	228.9	272.6	294.5	333.8	412.4	471.3	479.8
130°	181.7	191.4	201.0	203.4	233.2	273.1	292.9	327.9	397.9	450.3	458.1
132.5°	187.7	197.4	207.0	209.4	236.8	273.4	291.6	322.9	385.5	432.5	439.5
135°	196.6	205.4	214.2	216.5	240.7	273.1	289.2	315.5	367.9	407.3	413.3
137.5°	205.7	214.4	223.2	225.4	246.5	274.7	288.9	311.0	355.3	388.6	393.5
140°	213.3	221.3	229.4	231.4	250.1	275.0	287.5	306.7	345.0	373.6	378.3
142.5°	219.2	226.6	234.0	235.9	253.1	276.1	287.5	304.4	338.0	363.2	367.2
145°	228.1	234.6	241.0	242.6	257.0	276.1	285.6	299.3	326.8	347.5	350.5
147.5°	237.0	243.3	249.6	251.2	262.6	277.9	285.6	296.4	318.0	334.2	336.7
150°	242.8	248.5	254.2	255.6	265.6	278.9	285.6	294.7	313.0	326.6	328.7
152.5°	248.8	253.1	257.5	258.5	267.5	279.6	285.6	293.3	308.9	320.6	322.2
155°	257.8	261.0	264.1	264.9	271.8	281.0	285.6	291.8	304.2	313.5	314.4
157.5°	264.3	267.4	270.5	271.3	276.1	282.4	285.6	290.4	300.0	307.3	307.9
160°	268.8	271.2	273.6	274.2	278.0	283.0	285.6	289.7	298.0	304.2	304.6
162.5°	273.3	275.1	276.8	277.3	280.0	283.7	285.6	289.1	296.0	301.3	301.6
165°	278.2	279.8	281.5	281.9	283.1	284.8	285.6	288.1	293.0	296.8	297.2
167.5°	282.7	283.4	284.2	284.4	285.5	286.8	287.5	289.1	292.4	294.9	295.1
170°	285.6	286.3	287.1	287.3	287.4	287.5	287.5	289.1	292.4	294.9	294.9
172.5°	287.1	287.3	287.5	287.5	287.5	287.5	287.5	288.8	291.4	293.3	293.1
175°	289.2	289.2	289.2	289.2	288.7	287.9	287.5	288.3	289.9	291.2	291.2
177.5°	289.2	289.2	289.2	289.2	288.8	288.2	287.9	288.6	289.8	290.8	290.6
180°	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2

TEST NUMBER: P936500

CATALOG NUMBER: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	796.4	796.4
2.5°	850.2	845.1
5°	1093.4	1098.6
7.5°	1472.4	1469.9
10°	1830.9	1854.0
12.5°	2092.2	2097.3
15°	2250.9	2261.2
17.5°	2312.3	2314.9
20°	2314.9	2309.8
22.5°	2286.7	2281.6
25°	2253.5	2250.9
27.5°	2222.7	2225.3
30°	2209.9	2217.7
32.5°	2209.9	2222.7
35°	2215.0	2227.8
37.5°	2212.5	2227.8
40°	2202.2	2220.2
42.5°	2174.0	2186.8
45°	2130.5	2145.9
47.5°	2074.2	2084.4
50°	2002.5	2012.7
52.5°	1912.9	1915.4
55°	1805.3	1815.6
57.5°	1690.1	1692.6
60°	1562.0	1569.8
62.5°	1426.4	1426.4
65°	1283.0	1288.1
67.5°	1134.4	1147.2
70°	983.3	985.9
72.5°	834.8	834.8
75°	681.2	683.7
77.5°	535.2	535.2
80°	396.9	399.5
82.5°	274.0	279.2
85°	171.6	171.6
87.5°	79.4	71.7
90°	7.4	7.4
92.5°	29.6	23.6
95°	103.0	85.2
97.5°	246.7	212.9
100°	355.5	315.2
102.5°	462.5	428.0
105°	598.9	580.3
107.5°	688.3	692.7
110°	722.3	741.7



TEST NUMBER: P936500

CATALOG NUMBER: SQ4-FB-025U-100D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	725.4	755.0
115°	706.2	747.3
117.5°	665.4	711.1
120°	632.5	676.8
122.5°	600.5	644.2
125°	554.8	595.2
127.5°	513.8	547.8
130°	489.5	520.9
132.5°	467.6	495.7
135°	437.5	461.7
137.5°	413.4	433.2
140°	396.8	415.4
142.5°	383.1	399.0
145°	362.6	374.6
147.5°	346.7	356.8
150°	336.8	345.0
152.5°	328.3	334.4
155°	318.5	322.6
157.5°	310.9	313.7
160°	306.2	307.9
162.5°	303.2	304.8
165°	298.8	300.5
167.5°	295.7	296.4
170°	294.9	294.9
172.5°	292.5	292.0
175°	291.2	291.2
177.5°	289.9	289.2
180°	289.2	289.2

(END OF REPORT)