

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937083

Luminaire Tested: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937083
REPORT IS A COMBINATION OF REPORTS P933501 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4545.5 lumens
Efficiency: N/A
Efficacy: 132.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937083

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P937083

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35		
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35	29		
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29	23		
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24	19		
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20	16		
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	14		
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15	12		
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	10		
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12	9		
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10	8		
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1909	1909	1909
5°	1864	2205	2566
10°	1688	3211	4254
15°	1433	4192	5137
20°	1165	4855	5234
25°	971	5077	5128
30°	818	5104	5119
35°	721	5016	5250
40°	628	4902	5388
45°	567	4816	5409
50°	520	4739	5319
55°	495	4628	5083
60°	505	4419	4710
65°	523	4103	4199
70°	553	3571	3548
75°	607	2903	2769
80°	651	2008	1866
85°	547	1060	954

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5409 cd/sqm

TEST NUMBER: P937083

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.6	0.6
10°-20°	117.9	2.6
20°-30°	206.3	4.5
30°-40°	265.6	5.8
40°-50°	296.6	6.5
50°-60°	284.1	6.2
60°-70°	225.1	5.0
70°-80°	132.4	2.9
80°-90°	38.5	0.8
90°-100°	222.0	4.9
100°-110°	583.6	12.8
110°-120°	605.2	13.3
120°-130°	485.4	10.7
130°-140°	380.9	8.4
140°-150°	292.3	6.4
150°-160°	210.5	4.6
160°-170°	128.8	2.8
170°-180°	43.5	1.0
0°-30°	350.8	7.7
0°-40°	616.4	13.6
0°-60°	1197.1	26.3
0°-90°	1593.1	35.0
90°-120°	1410.8	31.0
90°-150°	2569.5	56.5
90°-180°	2952.0	64.9
0°-180°	4545.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	206	206	206	206	206	
5°	200	215	242	274	284	19
15°	150	277	467	566	584	42
25°	96	314	556	581	581	44
35°	65	300	524	554	575	40
45°	44	239	463	530	554	34
55°	32	152	393	456	469	29
65°	25	81	292	328	333	25
75°	18	50	160	176	177	19
85°	7	15	40	44	44	7
90°	3	9	23	12	12	3
95°	29	115	382	197	134	33
105°	105	159	645	980	914	111
115°	187	227	517	1031	1177	184
125°	260	291	470	794	937	231
135°	310	341	455	641	727	240
145°	359	382	450	547	590	225
155°	406	417	450	494	508	186
165°	438	444	450	467	473	124
175°	455	455	453	458	458	43
180°	455	455	455	455	455	

TEST NUMBER: P937083

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	205.7	205.7	205.7	205.7	205.7	205.7	205.7	205.7	205.7	205.7	205.7
2.5°	205.7	205.7	207.1	207.7	209.0	209.7	211.0	212.3	216.3	216.9	218.3
5°	200.5	203.1	211.7	214.9	224.2	236.8	242.1	250.7	268.6	273.8	277.2
7.5°	192.5	198.5	219.6	224.9	248.1	281.1	295.0	313.5	341.9	355.8	367.1
10°	179.9	192.5	230.2	242.8	280.4	330.7	356.5	382.4	425.4	444.5	451.8
12.5°	166.0	186.6	241.5	258.6	312.9	386.3	417.4	445.9	494.8	520.6	524.6
15°	150.2	178.0	252.0	277.2	347.3	432.6	467.0	502.1	547.7	566.2	570.8
17.5°	136.3	171.4	262.0	288.4	373.7	474.3	509.4	538.5	575.4	588.1	591.3
20°	119.1	160.7	268.6	303.0	401.5	504.7	538.5	560.9	586.1	594.0	595.3
22.5°	106.5	149.5	272.5	308.2	420.0	523.2	551.7	569.5	586.7	589.3	590.0
25°	95.9	137.0	271.8	314.2	435.9	534.4	556.3	569.5	579.5	580.8	580.8
27.5°	86.0	123.1	269.2	315.5	447.8	537.1	554.3	563.6	568.2	570.8	570.8
30°	77.4	109.8	262.6	312.9	453.1	534.4	548.3	552.9	557.6	561.6	563.6
32.5°	70.8	97.2	252.7	307.5	453.8	527.8	537.8	540.4	547.0	556.3	559.6
35°	64.8	84.7	241.5	300.3	449.8	517.3	523.9	526.5	539.7	553.6	558.3
37.5°	58.9	75.4	226.9	287.7	443.8	504.7	509.4	514.0	534.4	551.0	556.3
40°	52.9	67.4	209.7	273.8	434.6	489.5	493.5	500.7	527.8	547.0	552.4
42.5°	48.3	60.8	191.2	259.3	422.7	472.3	478.2	488.9	519.9	540.4	546.3
45°	44.3	54.2	171.4	239.4	407.4	454.4	463.0	477.6	510.6	530.5	535.8
47.5°	40.3	49.6	150.9	219.0	390.9	436.6	447.8	464.3	498.1	517.3	521.9
50°	37.1	45.0	130.3	197.1	373.1	417.4	430.6	447.8	482.3	500.1	506.0
52.5°	34.4	41.0	111.1	175.3	352.6	397.6	412.7	430.6	463.0	480.2	484.2
55°	31.7	37.7	94.6	152.1	331.4	376.4	392.9	410.1	441.8	456.4	459.1
57.5°	30.5	35.1	80.7	130.3	308.9	352.6	371.0	386.9	416.7	427.9	430.6
60°	28.4	33.0	70.1	111.8	284.5	330.1	346.0	361.9	386.9	396.2	398.2
62.5°	26.4	31.7	62.2	94.0	259.3	303.6	319.5	334.1	355.2	361.9	364.4
65°	25.1	30.5	56.2	80.7	233.5	275.8	291.7	304.3	321.4	328.0	329.4
67.5°	23.9	29.1	51.6	69.4	207.7	248.1	259.9	271.8	285.1	291.7	292.3
70°	21.8	27.8	47.6	61.5	181.2	216.3	226.2	238.8	249.4	252.7	254.7
72.5°	20.5	25.8	45.0	55.6	154.1	185.9	195.1	202.4	211.7	214.9	214.9
75°	18.5	23.2	42.3	49.6	126.3	152.1	160.0	167.3	174.6	175.9	173.9
77.5°	16.6	20.5	36.4	41.7	98.6	120.4	127.0	130.9	137.0	138.2	138.9
80°	13.9	17.8	28.4	32.4	71.5	88.6	93.3	96.5	101.9	101.9	103.2
82.5°	10.6	13.9	20.5	23.2	48.3	60.8	64.8	66.9	70.1	70.1	70.1
85°	6.6	8.6	13.2	15.2	29.1	37.1	39.7	40.3	43.0	43.7	43.7
87.5°	3.4	4.6	8.6	9.3	15.2	19.2	19.2	20.5	20.5	19.8	19.2
90°	3.1	5.5	8.0	8.6	13.5	20.0	23.3	20.7	15.5	11.6	11.6
92.5°	12.2	33.0	53.7	59.0	82.9	114.9	130.8	114.7	82.3	58.1	55.8
95°	29.4	67.4	105.5	115.0	204.1	322.9	382.4	341.2	258.8	197.1	190.1
97.5°	50.8	84.3	117.8	126.2	274.9	473.1	572.2	546.1	494.2	455.1	441.8
100°	67.2	97.6	128.1	135.7	300.6	520.6	630.5	632.4	636.3	639.1	623.3
102.5°	81.3	109.7	138.0	145.1	312.5	535.6	647.1	680.2	746.5	796.2	782.6
105°	105.1	129.2	153.2	159.2	321.2	537.3	645.2	719.6	868.2	979.6	972.3
107.5°	129.6	152.0	174.4	180.0	322.9	513.3	608.6	712.2	919.4	1074.9	1076.7
110°	146.1	166.3	186.6	191.7	320.4	492.1	578.0	693.8	925.6	1099.4	1107.0

TEST NUMBER: P937083

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	162.3	181.6	200.8	205.7	320.5	473.7	550.2	668.8	905.9	1083.8	1095.5
115°	186.7	204.5	222.3	226.8	323.5	452.4	516.9	631.1	859.6	1031.0	1047.1
117.5°	210.9	227.1	243.2	247.3	329.5	439.1	493.9	597.0	803.2	957.9	975.8
120°	225.0	240.2	255.4	259.2	334.4	434.6	484.7	579.0	767.4	908.7	926.1
122.5°	238.7	254.1	269.4	273.2	341.4	432.3	477.7	562.5	732.2	859.5	876.8
125°	259.8	273.8	287.8	291.3	350.9	430.4	470.1	542.2	686.4	794.4	810.3
127.5°	277.0	291.1	305.2	308.7	360.4	429.3	463.7	525.6	649.4	742.2	755.6
130°	286.1	301.3	316.5	320.4	367.3	429.9	461.3	516.4	626.5	709.1	721.5
132.5°	295.6	310.8	326.0	329.8	372.9	430.4	459.1	508.4	607.1	681.0	692.1
135°	309.6	323.4	337.3	340.8	379.0	430.0	455.4	496.7	579.4	641.3	650.9
137.5°	324.0	337.7	351.4	354.9	388.2	432.7	454.8	489.7	559.6	611.9	619.7
140°	335.9	348.6	361.2	364.3	393.8	433.1	452.7	482.8	543.1	588.3	595.6
142.5°	345.1	356.7	368.4	371.3	398.4	434.6	452.7	479.2	532.1	571.9	578.2
145°	359.1	369.4	379.5	382.1	404.6	434.6	449.6	471.3	514.6	547.1	551.9
147.5°	373.2	383.1	393.0	395.5	413.5	437.6	449.6	466.7	500.8	526.3	530.3
150°	382.4	391.3	400.3	402.6	418.3	439.2	449.6	464.0	492.8	514.4	517.6
152.5°	391.8	398.6	405.4	407.1	421.3	440.2	449.6	461.9	486.5	504.9	507.3
155°	405.9	411.0	415.9	417.2	428.0	442.4	449.6	459.4	478.9	493.6	495.2
157.5°	416.3	421.2	426.1	427.3	434.7	444.7	449.6	457.2	472.4	483.8	484.9
160°	423.3	427.1	430.9	431.9	437.8	445.7	449.6	456.1	469.2	479.0	479.6
162.5°	430.4	433.2	436.1	436.8	441.0	446.8	449.6	455.1	466.1	474.4	475.0
165°	438.0	440.5	443.1	443.8	445.8	448.3	449.6	453.6	461.4	467.4	468.1
167.5°	445.0	446.2	447.4	447.7	449.4	451.6	452.7	455.2	460.5	464.3	464.6
170°	449.6	450.8	452.1	452.4	452.5	452.6	452.7	455.2	460.5	464.3	464.3
172.5°	452.1	452.4	452.6	452.7	452.7	452.7	452.7	454.7	458.8	461.8	461.6
175°	455.4	455.4	455.4	455.4	454.5	453.3	452.7	454.0	456.5	458.5	458.5
177.5°	455.4	455.4	455.4	455.4	454.7	453.8	453.3	454.3	456.3	457.9	457.6
180°	455.4	455.4	455.4	455.4	455.4	455.4	455.4	455.4	455.4	455.4	455.4

TEST NUMBER: P937083

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	205.7	205.7
2.5°	219.6	218.3
5°	282.5	283.8
7.5°	380.3	379.7
10°	473.0	478.9
12.5°	540.4	541.7
15°	581.4	584.1
17.5°	597.3	598.0
20°	598.0	596.6
22.5°	590.7	589.3
25°	582.1	581.4
27.5°	574.1	574.8
30°	570.8	572.9
32.5°	570.8	574.1
35°	572.2	575.4
37.5°	571.5	575.4
40°	568.8	573.5
42.5°	561.6	564.9
45°	550.3	554.3
47.5°	535.8	538.5
50°	517.3	519.9
52.5°	494.1	494.8
55°	466.4	468.9
57.5°	436.6	437.2
60°	403.5	405.4
62.5°	368.5	368.5
65°	331.4	332.7
67.5°	293.0	296.3
70°	254.0	254.7
72.5°	215.6	215.6
75°	175.9	176.6
77.5°	138.2	138.2
80°	102.5	103.2
82.5°	70.8	72.1
85°	44.3	44.3
87.5°	20.5	18.5
90°	11.6	11.6
92.5°	46.5	37.3
95°	162.2	134.2
97.5°	388.6	335.3
100°	559.9	496.4
102.5°	728.3	673.9
105°	943.1	913.9
107.5°	1083.8	1090.9
110°	1137.4	1167.9



TEST NUMBER: P937083

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1142.3	1189.0
115°	1112.0	1176.8
117.5°	1047.7	1119.6
120°	996.0	1065.8
122.5°	945.6	1014.5
125°	873.7	937.1
127.5°	809.0	862.6
130°	771.0	820.4
132.5°	736.3	780.6
135°	689.0	727.2
137.5°	651.0	682.2
140°	624.9	654.1
142.5°	603.2	628.4
145°	570.9	589.9
147.5°	546.0	561.8
150°	530.4	543.2
152.5°	517.0	526.6
155°	501.6	508.0
157.5°	489.5	493.9
160°	482.2	484.7
162.5°	477.4	479.9
165°	470.6	473.2
167.5°	465.7	466.8
170°	464.3	464.3
172.5°	460.7	459.7
175°	458.5	458.5
177.5°	456.5	455.4
180°	455.4	455.4

TEST NUMBER: P937083

CATALOG NUMBER: SQ4-FB-075U-050D-B2750-1D-UNV-W2A-W-4-3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.69	2.45	2.76	3.53	5.00	14.83	15.59	15.90	16.67	18.13
	3H	2.39	3.07	3.47	4.16	5.64	16.64	17.33	17.72	18.41	19.90
	4H	2.68	3.33	3.77	4.42	5.91	17.27	17.93	18.36	19.01	20.50
	6H	2.93	3.53	4.03	4.62	6.12	17.69	18.29	18.78	19.38	20.88
	8H	2.99	3.57	4.10	4.67	6.17	17.80	18.37	18.90	19.47	20.97
	12H	3.01	3.55	4.11	4.65	6.17	17.85	18.40	18.96	19.50	21.02
4H	2H	8.87	9.52	9.96	10.60	12.10	15.09	15.74	16.19	16.83	18.32
	3H	10.43	10.97	11.53	12.08	13.59	17.11	17.66	18.22	18.77	20.27
	4H	10.52	11.02	11.63	12.12	13.65	17.86	18.37	18.97	19.47	20.99
	6H	10.52	10.95	11.64	12.08	13.60	18.38	18.82	19.50	19.94	21.46
	8H	10.50	10.90	11.61	12.02	13.55	18.54	18.94	19.65	20.06	21.59
	12H	10.45	10.81	11.58	11.94	13.48	18.62	18.98	19.75	20.11	21.65
8H	4H	11.94	12.35	13.06	13.46	15.00	17.92	18.32	19.03	19.44	20.97
	6H	12.18	12.52	13.32	13.67	15.20	18.53	18.86	19.67	20.02	21.55
	8H	12.20	12.49	13.34	13.63	15.18	18.74	19.03	19.88	20.17	21.72
	12H	12.16	12.42	13.31	13.56	15.14	18.87	19.13	20.02	20.26	21.85
12H	4H	12.08	12.44	13.21	13.57	15.11	17.86	18.23	19.00	19.36	20.90
	6H	12.44	12.73	13.58	13.87	15.42	18.51	18.80	19.65	19.94	21.49
	8H	12.50	12.76	13.65	13.89	15.48	18.73	18.99	19.88	20.12	21.71