

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P933979

Luminaire Tested: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P933979
REPORT IS A COMBINATION OF REPORTS P933677 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10781.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74		
1	103	99	95	91	98	94	90	87	85	82	80	77	75	73	69	68	66	62		
2	94	86	80	75	89	82	77	72	75	70	66	68	64	61	61	58	56	52		
3	86	76	68	62	81	72	66	60	66	60	56	60	55	52	54	51	48	44		
4	79	67	59	53	74	64	57	51	59	52	48	53	48	44	48	44	41	38		
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	36	33		
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	29		
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	26		
8	57	44	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23		
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	23	21		
10	50	37	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9504	9504	9504	9504
5°	9579	9594	9579	7544
10°	9518	9451	9518	6756
15°	9418	9246	9418	7721
20°	9225	9003	9225	7737
25°	8825	8650	8825	7573
30°	8308	8356	8308	7213
35°	7410	7984	7410	6817
40°	6178	7547	6178	6518
45°	5524	7035	5524	6175
50°	5873	6424	5873	5829
55°	5531	5766	5531	5630
60°	5708	4897	5708	5156
65°	5184	4048	5184	4526
70°	3598	3227	3598	3794
75°	3168	2385	3168	2856
80°	2572	1577	2572	1717
85°	1507	835	1507	710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8460 cd/sqm

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.4	2.6
10°-20°	787.5	7.3
20°-30°	1217.4	11.3
30°-40°	1453.3	13.5
40°-50°	1461.8	13.6
50°-60°	1271.9	11.8
60°-70°	901.8	8.4
70°-80°	477.1	4.4
80°-90°	120.5	1.1
90°-100°	211.5	2.0
100°-110°	556.0	5.2
110°-120°	576.5	5.3
120°-130°	462.4	4.3
130°-140°	362.8	3.4
140°-150°	278.5	2.6
150°-160°	200.6	1.9
160°-170°	122.7	1.1
170°-180°	41.5	0.4
0°-30°	2282.3	21.2
0°-40°	3735.6	34.6
0°-60°	6469.3	60.0
0°-90°	7968.7	73.9
90°-120°	1343.9	12.5
90°-150°	2447.6	22.7
90°-180°	2812.0	26.1
0°-180°	10781.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	3073	3073	3073	3073	3073	
5°	3087	3183	3087	2503	3087	293
15°	2948	3154	2948	2634	2948	829
25°	2596	2942	2596	2576	2596	1192
35°	1974	2625	1974	2241	1974	1221
45°	1273	2163	1273	1898	1273	1020
55°	1038	1596	1038	1558	1038	954
65°	721	962	721	1076	721	689
75°	273	456	273	546	273	287
85°	46	116	46	99	46	63
90°	3	11	3	11	3	4
95°	28	128	28	128	28	31
105°	100	870	100	870	100	106
115°	178	1121	178	1121	178	176
125°	248	893	248	893	248	220
135°	295	693	295	693	295	228
145°	342	562	342	562	342	214
155°	387	484	387	484	387	178
165°	417	451	417	451	417	118
175°	434	437	434	437	434	41
180°	434	434	434	434	434	

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8
2.5°	3099.0	3099.0	3116.4	3122.2	3122.2	3113.5	3104.8	3113.5	3139.7	3148.4	3145.5
5°	3087.3	3110.6	3142.6	3148.4	3154.2	3151.3	3145.5	3151.3	3180.4	3186.2	3189.1
7.5°	3064.1	3107.7	3148.4	3157.1	3165.8	3157.1	3154.2	3160.0	3189.1	3194.9	3194.9
10°	3035.0	3096.1	3142.6	3148.4	3157.1	3148.4	3148.4	3160.0	3189.1	3194.9	3197.8
12.5°	2994.3	3078.6	3122.2	3128.0	3139.7	3136.7	3133.8	3145.5	3174.5	3180.4	3180.4
15°	2947.8	3046.6	3087.3	3093.1	3113.5	3107.7	3107.7	3119.3	3151.3	3160.0	3157.1
17.5°	2883.8	3005.9	3052.4	3061.2	3075.7	3072.8	3075.7	3087.3	3116.4	3122.2	3125.1
20°	2811.2	2950.7	3005.9	3014.7	3029.2	3029.2	3029.2	3043.7	3072.8	3084.4	3084.4
22.5°	2712.3	2892.6	2950.7	2956.5	2974.0	2974.0	2979.8	3000.1	3026.3	3029.2	3029.2
25°	2596.0	2828.6	2878.0	2895.5	2912.9	2921.6	2930.4	2942.0	2950.7	2947.8	2950.7
27.5°	2473.9	2747.2	2811.2	2822.8	2846.0	2854.8	2866.4	2869.3	2872.2	2880.9	2875.1
30°	2337.2	2633.8	2729.8	2741.4	2779.2	2785.0	2773.4	2779.2	2793.7	2799.5	2805.4
32.5°	2183.2	2465.1	2645.5	2671.6	2706.5	2689.1	2686.2	2694.9	2718.1	2718.1	2724.0
35°	1973.9	2334.3	2567.0	2590.2	2616.4	2596.0	2607.7	2610.6	2625.1	2633.8	2630.9
37.5°	1744.2	2220.9	2485.5	2502.9	2523.3	2497.1	2514.6	2523.3	2534.9	2529.1	2529.1
40°	1540.7	2043.6	2389.6	2401.2	2418.6	2398.3	2415.7	2421.5	2427.3	2421.5	2418.6
42.5°	1389.5	1848.9	2287.8	2302.3	2290.7	2305.3	2311.1	2322.7	2314.0	2302.3	2302.3
45°	1273.3	1796.5	2177.3	2194.8	2177.3	2200.6	2209.3	2209.3	2183.2	2177.3	2174.4
47.5°	1235.5	1691.9	2066.9	2066.9	2058.2	2087.2	2101.8	2081.4	2055.2	2046.5	2046.5
50°	1232.6	1575.6	1915.7	1904.1	1944.8	1979.7	1965.1	1944.8	1924.4	1892.5	1892.5
52.5°	1119.2	1433.2	1720.9	1764.5	1828.5	1848.9	1825.6	1805.2	1770.4	1755.8	1744.2
55°	1037.8	1284.9	1543.6	1630.8	1697.7	1723.9	1680.2	1659.9	1607.6	1598.8	1593.0
57.5°	1020.4	1069.8	1380.8	1491.3	1572.7	1569.8	1543.6	1505.8	1462.2	1453.5	1450.6
60°	936.1	773.3	1206.4	1337.2	1421.5	1412.8	1389.5	1354.7	1314.0	1308.1	1302.3
62.5°	848.8	561.1	1008.7	1157.0	1276.2	1273.3	1252.9	1200.6	1171.5	1157.0	1145.4
65°	720.9	470.9	718.0	962.2	1133.7	1139.5	1095.9	1058.1	1026.2	1008.7	1005.8
67.5°	549.4	383.7	485.5	802.3	997.1	991.3	936.1	918.6	877.9	869.2	851.8
70°	407.0	255.8	337.2	651.2	863.4	848.8	805.2	784.9	747.1	726.8	715.1
72.5°	337.2	206.4	247.1	505.8	726.8	709.3	671.5	648.3	616.3	598.8	587.2
75°	273.3	218.0	189.0	375.0	590.1	578.5	543.6	520.4	494.2	470.9	473.8
77.5°	200.6	203.5	151.2	276.2	468.0	450.6	430.2	401.2	389.5	366.3	366.3
80°	151.2	159.9	113.4	189.0	337.2	337.2	319.8	299.4	279.1	267.4	267.4
82.5°	101.7	101.7	84.3	119.2	229.7	220.9	209.3	203.5	191.9	186.0	186.0
85°	46.5	58.1	52.3	72.7	125.0	130.8	130.8	125.0	122.1	116.3	119.2
87.5°	14.5	26.2	32.0	40.7	64.0	66.9	69.8	69.8	69.8	72.7	72.7
90°	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.7	14.7	11.0	11.0
92.5°	11.6	31.4	51.3	56.2	79.0	109.4	124.6	109.2	78.4	55.3	53.1
95°	27.9	64.1	100.4	109.5	194.4	307.7	364.2	325.0	246.6	187.8	181.1
97.5°	48.4	80.3	112.3	120.3	261.8	450.7	545.1	520.3	470.7	433.5	420.8
100°	64.1	93.0	122.0	129.3	286.4	495.9	600.7	602.5	606.1	608.8	593.7
102.5°	77.4	104.5	131.5	138.3	297.7	510.2	616.4	648.0	711.1	758.4	745.5
105°	100.2	123.1	145.9	151.6	306.0	511.7	614.6	685.4	826.9	933.1	926.2
107.5°	123.5	144.8	166.2	171.5	307.6	489.0	579.7	678.4	875.9	1024.0	1025.7
110°	139.1	158.4	177.7	182.6	305.2	468.8	550.6	661.0	881.7	1047.3	1054.6

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	154.7	173.0	191.4	195.9	305.3	451.2	524.1	637.1	863.0	1032.5	1043.6
115°	177.9	194.9	211.8	216.1	308.1	430.9	492.3	601.2	818.8	982.1	997.5
117.5°	200.9	216.3	231.7	235.6	313.9	418.3	470.5	568.8	765.2	912.5	929.7
120°	214.2	228.8	243.3	246.9	318.5	414.0	461.7	551.5	731.0	865.6	882.3
122.5°	227.4	242.1	256.6	260.3	325.2	411.7	455.0	535.9	697.5	818.7	835.1
125°	247.5	260.9	274.2	277.5	334.3	410.0	447.8	516.4	653.7	756.7	771.8
127.5°	263.8	277.2	290.7	294.1	343.3	408.9	441.7	500.6	618.5	706.9	719.7
130°	272.5	287.0	301.6	305.1	349.9	409.5	439.3	491.9	596.8	675.5	687.3
132.5°	281.6	296.0	310.6	314.1	355.2	410.0	437.3	484.3	578.3	648.7	659.3
135°	295.0	308.1	321.3	324.6	361.0	409.6	433.8	473.2	551.8	610.9	620.0
137.5°	308.6	321.7	334.7	338.0	369.8	412.1	433.2	466.5	532.9	582.9	590.3
140°	320.0	332.0	344.1	347.1	375.1	412.5	431.2	459.9	517.3	560.5	567.4
142.5°	328.7	339.8	351.0	353.8	379.6	414.0	431.2	456.4	506.9	544.8	550.8
145°	342.2	351.8	361.5	364.0	385.4	414.0	428.3	448.9	490.2	521.1	525.7
147.5°	355.5	364.9	374.4	376.7	393.9	416.9	428.3	444.6	477.0	501.4	505.1
150°	364.2	372.8	381.3	383.4	398.4	418.3	428.3	442.1	469.5	490.0	493.0
152.5°	373.3	379.8	386.1	387.8	401.3	419.3	428.3	440.0	463.5	481.0	483.3
155°	386.6	391.4	396.2	397.4	407.7	421.4	428.3	437.6	456.3	470.3	471.8
157.5°	396.5	401.2	405.9	407.1	414.2	423.5	428.3	435.6	450.0	460.9	461.9
160°	403.3	406.9	410.6	411.4	417.1	424.5	428.3	434.5	446.9	456.2	456.8
162.5°	410.0	412.7	415.4	416.1	420.2	425.6	428.3	433.5	444.0	451.8	452.4
165°	417.3	419.7	422.2	422.8	424.6	427.0	428.3	432.1	439.5	445.2	445.7
167.5°	423.9	425.1	426.3	426.6	428.1	430.1	431.2	433.6	438.6	442.3	442.5
170°	428.3	429.5	430.6	430.9	431.0	431.1	431.2	433.6	438.6	442.3	442.3
172.5°	430.6	430.9	431.1	431.2	431.2	431.2	431.2	433.1	437.0	439.9	439.7
175°	433.8	433.8	433.8	433.8	432.9	431.8	431.2	432.5	434.9	436.7	436.7
177.5°	433.8	433.8	433.8	433.8	433.1	432.3	431.8	432.8	434.7	436.1	435.9
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8
2.5°	3151.3	3142.6	3151.3	3145.5	3148.4	3139.7	3113.5	3104.8	3113.5	3122.2	3122.2
5°	3189.1	3183.3	3189.1	3189.1	3186.2	3180.4	3151.3	3145.5	3151.3	3154.2	3148.4
7.5°	3200.7	3192.0	3200.7	3194.9	3194.9	3189.1	3160.0	3154.2	3157.1	3165.8	3157.1
10°	3200.7	3192.0	3200.7	3197.8	3194.9	3189.1	3160.0	3148.4	3148.4	3157.1	3148.4
12.5°	3186.2	3180.4	3186.2	3180.4	3180.4	3174.5	3145.5	3133.8	3136.7	3139.7	3128.0
15°	3162.9	3154.2	3162.9	3157.1	3160.0	3151.3	3119.3	3107.7	3107.7	3113.5	3093.1
17.5°	3128.0	3116.4	3128.0	3125.1	3122.2	3116.4	3087.3	3075.7	3072.8	3075.7	3061.2
20°	3087.3	3078.6	3087.3	3084.4	3084.4	3072.8	3043.7	3029.2	3029.2	3029.2	3014.7
22.5°	3023.4	3014.7	3023.4	3029.2	3029.2	3026.3	3000.1	2979.8	2974.0	2974.0	2956.5
25°	2950.7	2942.0	2950.7	2950.7	2947.8	2950.7	2942.0	2930.4	2921.6	2912.9	2895.5
27.5°	2880.9	2875.1	2880.9	2875.1	2880.9	2872.2	2869.3	2866.4	2854.8	2846.0	2822.8
30°	2811.2	2805.4	2811.2	2805.4	2799.5	2793.7	2779.2	2773.4	2785.0	2779.2	2741.4
32.5°	2724.0	2718.1	2724.0	2724.0	2718.1	2718.1	2694.9	2686.2	2689.1	2706.5	2671.6
35°	2633.8	2625.1	2633.8	2630.9	2633.8	2625.1	2610.6	2607.7	2596.0	2616.4	2590.2
37.5°	2529.1	2520.4	2529.1	2529.1	2529.1	2534.9	2523.3	2514.6	2497.1	2523.3	2502.9
40°	2421.5	2409.9	2421.5	2418.6	2421.5	2427.3	2421.5	2415.7	2398.3	2418.6	2401.2
42.5°	2299.4	2296.5	2299.4	2302.3	2302.3	2314.0	2322.7	2311.1	2305.3	2290.7	2302.3
45°	2168.6	2162.8	2168.6	2174.4	2177.3	2183.2	2209.3	2209.3	2200.6	2177.3	2194.8
47.5°	2029.1	2014.6	2029.1	2046.5	2046.5	2055.2	2081.4	2101.8	2087.2	2058.2	2066.9
50°	1880.8	1883.7	1880.8	1892.5	1892.5	1924.4	1944.8	1965.1	1979.7	1944.8	1904.1
52.5°	1735.5	1732.6	1735.5	1744.2	1755.8	1770.4	1805.2	1825.6	1848.9	1828.5	1764.5
55°	1590.1	1595.9	1590.1	1593.0	1598.8	1607.6	1659.9	1680.2	1723.9	1697.7	1630.8
57.5°	1444.8	1436.1	1444.8	1450.6	1453.5	1462.2	1505.8	1543.6	1569.8	1572.7	1491.3
60°	1276.2	1264.5	1276.2	1302.3	1308.1	1314.0	1354.7	1389.5	1412.8	1421.5	1337.2
62.5°	1127.9	1107.6	1127.9	1145.4	1157.0	1171.5	1200.6	1252.9	1273.3	1276.2	1157.0
65°	970.9	962.2	970.9	1005.8	1008.7	1026.2	1058.1	1095.9	1139.5	1133.7	962.2
67.5°	828.5	828.5	828.5	851.8	869.2	877.9	918.6	936.1	991.3	997.1	802.3
70°	697.7	694.8	697.7	715.1	726.8	747.1	784.9	805.2	848.8	863.4	651.2
72.5°	572.7	569.8	572.7	587.2	598.8	616.3	648.3	671.5	709.3	726.8	505.8
75°	462.2	456.4	462.2	473.8	470.9	494.2	520.4	543.6	578.5	590.1	375.0
77.5°	354.7	354.7	354.7	366.3	366.3	389.5	401.2	430.2	450.6	468.0	276.2
80°	264.5	261.6	264.5	267.4	267.4	279.1	299.4	319.8	337.2	337.2	189.0
82.5°	186.0	180.2	186.0	186.0	186.0	191.9	203.5	209.3	220.9	229.7	119.2
85°	116.3	116.3	116.3	119.2	116.3	122.1	125.0	130.8	130.8	125.0	72.7
87.5°	75.6	72.7	75.6	72.7	72.7	69.8	69.8	69.8	66.9	64.0	40.7
90°	11.0	11.0	11.0	11.0	11.0	14.7	19.7	22.1	19.0	12.8	8.1
92.5°	44.4	35.6	44.4	53.1	55.3	78.4	109.2	124.6	109.4	79.0	56.2
95°	154.5	127.8	154.5	181.1	187.8	246.6	325.0	364.2	307.7	194.4	109.5
97.5°	370.2	319.4	370.2	420.8	433.5	470.7	520.3	545.1	450.7	261.8	120.3
100°	533.3	472.9	533.3	593.7	608.8	606.1	602.5	600.7	495.9	286.4	129.3
102.5°	693.7	642.0	693.7	745.5	758.4	711.1	648.0	616.4	510.2	297.7	138.3
105°	898.4	870.5	898.4	926.2	933.1	826.9	685.4	614.6	511.7	306.0	151.6
107.5°	1032.5	1039.2	1032.5	1025.7	1024.0	875.9	678.4	579.7	489.0	307.6	171.5
110°	1083.5	1112.5	1083.5	1054.6	1047.3	881.7	661.0	550.6	468.8	305.2	182.6

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1088.1	1132.6	1088.1	1043.6	1032.5	863.0	637.1	524.1	451.2	305.3	195.9
115°	1059.2	1120.9	1059.2	997.5	982.1	818.8	601.2	492.3	430.9	308.1	216.1
117.5°	998.1	1066.5	998.1	929.7	912.5	765.2	568.8	470.5	418.3	313.9	235.6
120°	948.7	1015.2	948.7	882.3	865.6	731.0	551.5	461.7	414.0	318.5	246.9
122.5°	900.8	966.4	900.8	835.1	818.7	697.5	535.9	455.0	411.7	325.2	260.3
125°	832.2	892.6	832.2	771.8	756.7	653.7	516.4	447.8	410.0	334.3	277.5
127.5°	770.6	821.6	770.6	719.7	706.9	618.5	500.6	441.7	408.9	343.3	294.1
130°	734.4	781.5	734.4	687.3	675.5	596.8	491.9	439.3	409.5	349.9	305.1
132.5°	701.5	743.6	701.5	659.3	648.7	578.3	484.3	437.3	410.0	355.2	314.1
135°	656.3	692.6	656.3	620.0	610.9	551.8	473.2	433.8	409.6	361.0	324.6
137.5°	620.1	649.9	620.1	590.3	582.9	532.9	466.5	433.2	412.1	369.8	338.0
140°	595.3	623.1	595.3	567.4	560.5	517.3	459.9	431.2	412.5	375.1	347.1
142.5°	574.7	598.6	574.7	550.8	544.8	506.9	456.4	431.2	414.0	379.6	353.8
145°	543.8	561.9	543.8	525.7	521.1	490.2	448.9	428.3	414.0	385.4	364.0
147.5°	520.2	535.2	520.2	505.1	501.4	477.0	444.6	428.3	416.9	393.9	376.7
150°	505.2	517.3	505.2	493.0	490.0	469.5	442.1	428.3	418.3	398.4	383.4
152.5°	492.4	501.7	492.4	483.3	481.0	463.5	440.0	428.3	419.3	401.3	387.8
155°	477.8	483.9	477.8	471.8	470.3	456.3	437.6	428.3	421.4	407.7	397.4
157.5°	466.3	470.5	466.3	461.9	460.9	450.0	435.6	428.3	423.5	414.2	407.1
160°	459.3	461.7	459.3	456.8	456.2	446.9	434.5	428.3	424.5	417.1	411.4
162.5°	454.8	457.1	454.8	452.4	451.8	444.0	433.5	428.3	425.6	420.2	416.1
165°	448.3	450.7	448.3	445.7	445.2	439.5	432.1	428.3	427.0	424.6	422.8
167.5°	443.5	444.6	443.5	442.5	442.3	438.6	433.6	431.2	430.1	428.1	426.6
170°	442.3	442.3	442.3	442.3	442.3	438.6	433.6	431.2	431.1	431.0	430.9
172.5°	438.8	437.9	438.8	439.7	439.9	437.0	433.1	431.2	431.2	431.2	431.2
175°	436.7	436.7	436.7	436.7	436.7	434.9	432.5	431.2	431.8	432.9	433.8
177.5°	434.9	433.8	434.9	435.9	436.1	434.7	432.8	431.8	432.3	433.1	433.8
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8
2.5°	3116.4	3099.0	3099.0	3069.9	3058.3	3049.5	3035.0	2991.4	2979.8	2968.1	2985.6
5°	3142.6	3110.6	3087.3	3035.0	2991.4	2974.0	2918.7	2814.1	2744.3	2692.0	2662.9
7.5°	3148.4	3107.7	3064.1	2982.7	2878.0	2831.5	2662.9	2471.0	2418.6	2372.1	2343.0
10°	3142.6	3096.1	3035.0	2912.9	2665.8	2584.4	2415.7	2290.7	2258.7	2250.0	2258.7
12.5°	3122.2	3078.6	2994.3	2790.8	2444.8	2389.6	2290.7	2218.0	2212.2	2226.8	2305.3
15°	3087.3	3046.6	2947.8	2628.0	2322.7	2282.0	2212.2	2186.1	2218.0	2319.8	2555.3
17.5°	3052.4	3005.9	2883.8	2468.0	2229.7	2200.6	2151.2	2203.5	2383.7	2520.4	2599.0
20°	3005.9	2950.7	2811.2	2351.8	2162.8	2136.6	2113.4	2348.9	2485.5	2534.9	2578.6
22.5°	2950.7	2892.6	2712.3	2270.4	2093.0	2072.7	2087.2	2430.3	2485.5	2520.4	2558.2
25°	2878.0	2828.6	2596.0	2206.4	2037.8	2014.6	2069.8	2421.5	2453.5	2462.2	2537.8
27.5°	2811.2	2747.2	2473.9	2148.3	1970.9	1962.2	2084.3	2383.7	2407.0	2415.7	2497.1
30°	2729.8	2633.8	2337.2	2087.2	1901.2	1898.3	2087.2	2337.2	2331.4	2354.7	2436.1
32.5°	2645.5	2465.1	2183.2	2011.6	1834.3	1831.4	2066.9	2267.5	2261.6	2293.6	2354.7
35°	2567.0	2334.3	1973.9	1924.4	1750.0	1752.9	2017.5	2186.1	2189.0	2218.0	2255.8
37.5°	2485.5	2220.9	1744.2	1828.5	1668.6	1668.6	1950.6	2110.5	2104.7	2113.4	2165.7
40°	2389.6	2043.6	1540.7	1703.5	1593.0	1584.3	1869.2	2029.1	2008.7	2005.8	2078.5
42.5°	2287.8	1848.9	1389.5	1537.8	1505.8	1494.2	1770.4	1930.2	1892.5	1901.2	1994.2
45°	2177.3	1796.5	1273.3	1299.4	1415.7	1407.0	1662.8	1816.9	1790.7	1814.0	1909.9
47.5°	2066.9	1691.9	1235.5	1078.5	1319.8	1316.9	1543.6	1706.4	1691.9	1715.1	1816.9
50°	1915.7	1575.6	1232.6	924.4	1212.2	1223.8	1401.2	1598.8	1598.8	1619.2	1726.8
52.5°	1720.9	1433.2	1119.2	837.2	1087.2	1122.1	1276.2	1505.8	1511.6	1532.0	1627.9
55°	1543.6	1284.9	1037.8	770.4	939.0	1014.5	1154.1	1409.9	1421.5	1441.9	1529.1
57.5°	1380.8	1069.8	1020.4	691.9	802.3	875.0	1046.5	1316.9	1322.7	1340.1	1424.4
60°	1206.4	773.3	936.1	607.6	683.1	738.4	947.7	1206.4	1226.8	1238.4	1311.1
62.5°	1008.7	561.1	848.8	549.4	625.0	636.6	866.3	1101.8	1127.9	1136.6	1180.2
65°	718.0	470.9	720.9	500.0	564.0	566.9	779.1	994.2	1017.4	1032.0	1064.0
67.5°	485.5	383.7	549.4	453.5	517.4	520.4	694.8	869.2	901.2	912.8	933.1
70°	337.2	255.8	407.0	404.1	465.1	470.9	604.7	755.8	784.9	793.6	805.2
72.5°	247.1	206.4	337.2	363.4	409.9	415.7	511.6	627.9	657.0	665.7	671.5
75°	189.0	218.0	273.3	316.9	348.8	351.7	418.6	511.6	532.0	537.8	540.7
77.5°	151.2	203.5	200.6	255.8	284.9	279.1	328.5	395.4	412.8	412.8	412.8
80°	113.4	159.9	151.2	183.1	209.3	203.5	235.5	282.0	287.8	293.6	290.7
82.5°	84.3	101.7	101.7	116.3	139.5	133.7	157.0	183.1	183.1	183.1	189.0
85°	52.3	58.1	46.5	61.0	78.5	75.6	87.2	98.8	101.7	101.7	95.9
87.5°	32.0	26.2	14.5	23.3	34.9	34.9	40.7	43.6	40.7	40.7	40.7
90°	7.6	5.2	2.9	5.2	7.6	8.1	12.8	19.0	22.1	19.7	14.7
92.5°	51.3	31.4	11.6	31.4	51.3	56.2	79.0	109.4	124.6	109.2	78.4
95°	100.4	64.1	27.9	64.1	100.4	109.5	194.4	307.7	364.2	325.0	246.6
97.5°	112.3	80.3	48.4	80.3	112.3	120.3	261.8	450.7	545.1	520.3	470.7
100°	122.0	93.0	64.1	93.0	122.0	129.3	286.4	495.9	600.7	602.5	606.1
102.5°	131.5	104.5	77.4	104.5	131.5	138.3	297.7	510.2	616.4	648.0	711.1
105°	145.9	123.1	100.2	123.1	145.9	151.6	306.0	511.7	614.6	685.4	826.9
107.5°	166.2	144.8	123.5	144.8	166.2	171.5	307.6	489.0	579.7	678.4	875.9
110°	177.7	158.4	139.1	158.4	177.7	182.6	305.2	468.8	550.6	661.0	881.7

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	191.4	173.0	154.7	173.0	191.4	195.9	305.3	451.2	524.1	637.1	863.0
115°	211.8	194.9	177.9	194.9	211.8	216.1	308.1	430.9	492.3	601.2	818.8
117.5°	231.7	216.3	200.9	216.3	231.7	235.6	313.9	418.3	470.5	568.8	765.2
120°	243.3	228.8	214.2	228.8	243.3	246.9	318.5	414.0	461.7	551.5	731.0
122.5°	256.6	242.1	227.4	242.1	256.6	260.3	325.2	411.7	455.0	535.9	697.5
125°	274.2	260.9	247.5	260.9	274.2	277.5	334.3	410.0	447.8	516.4	653.7
127.5°	290.7	277.2	263.8	277.2	290.7	294.1	343.3	408.9	441.7	500.6	618.5
130°	301.6	287.0	272.5	287.0	301.6	305.1	349.9	409.5	439.3	491.9	596.8
132.5°	310.6	296.0	281.6	296.0	310.6	314.1	355.2	410.0	437.3	484.3	578.3
135°	321.3	308.1	295.0	308.1	321.3	324.6	361.0	409.6	433.8	473.2	551.8
137.5°	334.7	321.7	308.6	321.7	334.7	338.0	369.8	412.1	433.2	466.5	532.9
140°	344.1	332.0	320.0	332.0	344.1	347.1	375.1	412.5	431.2	459.9	517.3
142.5°	351.0	339.8	328.7	339.8	351.0	353.8	379.6	414.0	431.2	456.4	506.9
145°	361.5	351.8	342.2	351.8	361.5	364.0	385.4	414.0	428.3	448.9	490.2
147.5°	374.4	364.9	355.5	364.9	374.4	376.7	393.9	416.9	428.3	444.6	477.0
150°	381.3	372.8	364.2	372.8	381.3	383.4	398.4	418.3	428.3	442.1	469.5
152.5°	386.1	379.8	373.3	379.8	386.1	387.8	401.3	419.3	428.3	440.0	463.5
155°	396.2	391.4	386.6	391.4	396.2	397.4	407.7	421.4	428.3	437.6	456.3
157.5°	405.9	401.2	396.5	401.2	405.9	407.1	414.2	423.5	428.3	435.6	450.0
160°	410.6	406.9	403.3	406.9	410.6	411.4	417.1	424.5	428.3	434.5	446.9
162.5°	415.4	412.7	410.0	412.7	415.4	416.1	420.2	425.6	428.3	433.5	444.0
165°	422.2	419.7	417.3	419.7	422.2	422.8	424.6	427.0	428.3	432.1	439.5
167.5°	426.3	425.1	423.9	425.1	426.3	426.6	428.1	430.1	431.2	433.6	438.6
170°	430.6	429.5	428.3	429.5	430.6	430.9	431.0	431.1	431.2	433.6	438.6
172.5°	431.1	430.9	430.6	430.9	431.1	431.2	431.2	431.2	431.2	433.1	437.0
175°	433.8	433.8	433.8	433.8	433.8	433.8	432.9	431.8	431.2	432.5	434.9
177.5°	433.8	433.8	433.8	433.8	433.8	433.8	433.1	432.3	431.8	432.8	434.7
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8	3072.8
2.5°	2965.2	2956.5	2968.1	2936.2	2968.1	2956.5	2965.2	2985.6	2968.1	2979.8	2991.4
5°	2601.9	2587.3	2540.7	2502.9	2540.7	2587.3	2601.9	2662.9	2692.0	2744.3	2814.1
7.5°	2325.6	2314.0	2302.3	2279.1	2302.3	2314.0	2325.6	2343.0	2372.1	2418.6	2471.0
10°	2264.6	2267.5	2284.9	2282.0	2284.9	2267.5	2264.6	2258.7	2250.0	2258.7	2290.7
12.5°	2421.5	2447.7	2543.6	2537.8	2543.6	2447.7	2421.5	2305.3	2226.8	2212.2	2218.0
15°	2601.9	2610.6	2630.9	2633.8	2630.9	2610.6	2601.9	2555.3	2319.8	2218.0	2186.1
17.5°	2619.3	2622.2	2636.7	2636.7	2636.7	2622.2	2619.3	2599.0	2520.4	2383.7	2203.5
20°	2604.8	2610.6	2639.7	2645.5	2639.7	2610.6	2604.8	2578.6	2534.9	2485.5	2348.9
22.5°	2599.0	2610.6	2633.8	2630.9	2633.8	2610.6	2599.0	2558.2	2520.4	2485.5	2430.3
25°	2569.9	2569.9	2572.8	2575.7	2572.8	2569.9	2569.9	2537.8	2462.2	2453.5	2421.5
27.5°	2508.7	2514.6	2532.0	2529.1	2532.0	2514.6	2508.7	2497.1	2415.7	2407.0	2383.7
30°	2453.5	2447.7	2433.2	2421.5	2433.2	2447.7	2453.5	2436.1	2354.7	2331.4	2337.2
32.5°	2360.5	2345.9	2331.4	2322.7	2331.4	2345.9	2360.5	2354.7	2293.6	2261.6	2267.5
35°	2250.0	2252.9	2250.0	2241.3	2250.0	2252.9	2250.0	2255.8	2218.0	2189.0	2186.1
37.5°	2171.5	2177.3	2174.4	2162.8	2174.4	2177.3	2171.5	2165.7	2113.4	2104.7	2110.5
40°	2090.1	2093.0	2090.1	2081.4	2090.1	2093.0	2090.1	2078.5	2005.8	2008.7	2029.1
42.5°	2011.6	2008.7	2000.0	1994.2	2000.0	2008.7	2011.6	1994.2	1901.2	1892.5	1930.2
45°	1921.5	1924.4	1907.0	1898.3	1907.0	1924.4	1921.5	1909.9	1814.0	1790.7	1816.9
47.5°	1831.4	1831.4	1816.9	1808.2	1816.9	1831.4	1831.4	1816.9	1715.1	1691.9	1706.4
50°	1735.5	1732.6	1712.2	1709.3	1712.2	1732.6	1735.5	1726.8	1619.2	1598.8	1598.8
52.5°	1625.0	1625.0	1627.9	1633.7	1627.9	1625.0	1625.0	1627.9	1532.0	1511.6	1505.8
55°	1529.1	1532.0	1552.3	1558.2	1552.3	1532.0	1529.1	1529.1	1441.9	1421.5	1409.9
57.5°	1430.2	1430.2	1444.8	1444.8	1444.8	1430.2	1430.2	1424.4	1340.1	1322.7	1316.9
60°	1316.9	1322.7	1334.3	1331.4	1334.3	1322.7	1316.9	1311.1	1238.4	1226.8	1206.4
62.5°	1197.7	1203.5	1206.4	1200.6	1206.4	1203.5	1197.7	1180.2	1136.6	1127.9	1101.8
65°	1072.7	1078.5	1081.4	1075.6	1081.4	1078.5	1072.7	1064.0	1032.0	1017.4	994.2
67.5°	944.8	941.9	939.0	950.6	939.0	941.9	944.8	933.1	912.8	901.2	869.2
70°	814.0	814.0	811.1	816.9	811.1	814.0	814.0	805.2	793.6	784.9	755.8
72.5°	674.4	671.5	683.1	674.4	683.1	671.5	674.4	671.5	665.7	657.0	627.9
75°	537.8	543.6	537.8	546.5	537.8	543.6	537.8	540.7	537.8	532.0	511.6
77.5°	409.9	415.7	409.9	409.9	409.9	415.7	409.9	412.8	412.8	412.8	395.4
80°	290.7	287.8	287.8	284.9	287.8	287.8	290.7	290.7	293.6	287.8	282.0
82.5°	186.0	183.1	183.1	189.0	183.1	183.1	186.0	189.0	183.1	183.1	183.1
85°	101.7	104.7	98.8	98.8	98.8	104.7	101.7	95.9	101.7	101.7	98.8
87.5°	37.8	34.9	34.9	34.9	34.9	34.9	37.8	40.7	40.7	40.7	43.6
90°	11.0	11.0	11.0	11.0	11.0	11.0	11.0	14.7	19.7	22.1	19.0
92.5°	55.3	53.1	44.4	35.6	44.4	53.1	55.3	78.4	109.2	124.6	109.4
95°	187.8	181.1	154.5	127.8	154.5	181.1	187.8	246.6	325.0	364.2	307.7
97.5°	433.5	420.8	370.2	319.4	370.2	420.8	433.5	470.7	520.3	545.1	450.7
100°	608.8	593.7	533.3	472.9	533.3	593.7	608.8	606.1	602.5	600.7	495.9
102.5°	758.4	745.5	693.7	642.0	693.7	745.5	758.4	711.1	648.0	616.4	510.2
105°	933.1	926.2	898.4	870.5	898.4	926.2	933.1	826.9	685.4	614.6	511.7
107.5°	1024.0	1025.7	1032.5	1039.2	1032.5	1025.7	1024.0	875.9	678.4	579.7	489.0
110°	1047.3	1054.6	1083.5	1112.5	1083.5	1054.6	1047.3	881.7	661.0	550.6	468.8

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1032.5	1043.6	1088.1	1132.6	1088.1	1043.6	1032.5	863.0	637.1	524.1	451.2
115°	982.1	997.5	1059.2	1120.9	1059.2	997.5	982.1	818.8	601.2	492.3	430.9
117.5°	912.5	929.7	998.1	1066.5	998.1	929.7	912.5	765.2	568.8	470.5	418.3
120°	865.6	882.3	948.7	1015.2	948.7	882.3	865.6	731.0	551.5	461.7	414.0
122.5°	818.7	835.1	900.8	966.4	900.8	835.1	818.7	697.5	535.9	455.0	411.7
125°	756.7	771.8	832.2	892.6	832.2	771.8	756.7	653.7	516.4	447.8	410.0
127.5°	706.9	719.7	770.6	821.6	770.6	719.7	706.9	618.5	500.6	441.7	408.9
130°	675.5	687.3	734.4	781.5	734.4	687.3	675.5	596.8	491.9	439.3	409.5
132.5°	648.7	659.3	701.5	743.6	701.5	659.3	648.7	578.3	484.3	437.3	410.0
135°	610.9	620.0	656.3	692.6	656.3	620.0	610.9	551.8	473.2	433.8	409.6
137.5°	582.9	590.3	620.1	649.9	620.1	590.3	582.9	532.9	466.5	433.2	412.1
140°	560.5	567.4	595.3	623.1	595.3	567.4	560.5	517.3	459.9	431.2	412.5
142.5°	544.8	550.8	574.7	598.6	574.7	550.8	544.8	506.9	456.4	431.2	414.0
145°	521.1	525.7	543.8	561.9	543.8	525.7	521.1	490.2	448.9	428.3	414.0
147.5°	501.4	505.1	520.2	535.2	520.2	505.1	501.4	477.0	444.6	428.3	416.9
150°	490.0	493.0	505.2	517.3	505.2	493.0	490.0	469.5	442.1	428.3	418.3
152.5°	481.0	483.3	492.4	501.7	492.4	483.3	481.0	463.5	440.0	428.3	419.3
155°	470.3	471.8	477.8	483.9	477.8	471.8	470.3	456.3	437.6	428.3	421.4
157.5°	460.9	461.9	466.3	470.5	466.3	461.9	460.9	450.0	435.6	428.3	423.5
160°	456.2	456.8	459.3	461.7	459.3	456.8	456.2	446.9	434.5	428.3	424.5
162.5°	451.8	452.4	454.8	457.1	454.8	452.4	451.8	444.0	433.5	428.3	425.6
165°	445.2	445.7	448.3	450.7	448.3	445.7	445.2	439.5	432.1	428.3	427.0
167.5°	442.3	442.5	443.5	444.6	443.5	442.5	442.3	438.6	433.6	431.2	430.1
170°	442.3	442.3	442.3	442.3	442.3	442.3	442.3	438.6	433.6	431.2	431.1
172.5°	439.9	439.7	438.8	437.9	438.8	439.7	439.9	437.0	433.1	431.2	431.2
175°	436.7	436.7	436.7	436.7	436.7	436.7	436.7	434.9	432.5	431.2	431.8
177.5°	436.1	435.9	434.9	433.8	434.9	435.9	436.1	434.7	432.8	431.8	432.3
180°	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	3072.8	3072.8	3072.8	3072.8	3072.8
2.5°	3035.0	3049.5	3058.3	3069.9	3099.0
5°	2918.7	2974.0	2991.4	3035.0	3087.3
7.5°	2662.9	2831.5	2878.0	2982.7	3064.1
10°	2415.7	2584.4	2665.8	2912.9	3035.0
12.5°	2290.7	2389.6	2444.8	2790.8	2994.3
15°	2212.2	2282.0	2322.7	2628.0	2947.8
17.5°	2151.2	2200.6	2229.7	2468.0	2883.8
20°	2113.4	2136.6	2162.8	2351.8	2811.2
22.5°	2087.2	2072.7	2093.0	2270.4	2712.3
25°	2069.8	2014.6	2037.8	2206.4	2596.0
27.5°	2084.3	1962.2	1970.9	2148.3	2473.9
30°	2087.2	1898.3	1901.2	2087.2	2337.2
32.5°	2066.9	1831.4	1834.3	2011.6	2183.2
35°	2017.5	1752.9	1750.0	1924.4	1973.9
37.5°	1950.6	1668.6	1668.6	1828.5	1744.2
40°	1869.2	1584.3	1593.0	1703.5	1540.7
42.5°	1770.4	1494.2	1505.8	1537.8	1389.5
45°	1662.8	1407.0	1415.7	1299.4	1273.3
47.5°	1543.6	1316.9	1319.8	1078.5	1235.5
50°	1401.2	1223.8	1212.2	924.4	1232.6
52.5°	1276.2	1122.1	1087.2	837.2	1119.2
55°	1154.1	1014.5	939.0	770.4	1037.8
57.5°	1046.5	875.0	802.3	691.9	1020.4
60°	947.7	738.4	683.1	607.6	936.1
62.5°	866.3	636.6	625.0	549.4	848.8
65°	779.1	566.9	564.0	500.0	720.9
67.5°	694.8	520.4	517.4	453.5	549.4
70°	604.7	470.9	465.1	404.1	407.0
72.5°	511.6	415.7	409.9	363.4	337.2
75°	418.6	351.7	348.8	316.9	273.3
77.5°	328.5	279.1	284.9	255.8	200.6
80°	235.5	203.5	209.3	183.1	151.2
82.5°	157.0	133.7	139.5	116.3	101.7
85°	87.2	75.6	78.5	61.0	46.5
87.5°	40.7	34.9	34.9	23.3	14.5
90°	12.8	8.1	7.6	5.2	2.9
92.5°	79.0	56.2	51.3	31.4	11.6
95°	194.4	109.5	100.4	64.1	27.9
97.5°	261.8	120.3	112.3	80.3	48.4
100°	286.4	129.3	122.0	93.0	64.1
102.5°	297.7	138.3	131.5	104.5	77.4
105°	306.0	151.6	145.9	123.1	100.2
107.5°	307.6	171.5	166.2	144.8	123.5
110°	305.2	182.6	177.7	158.4	139.1



TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	305.3	195.9	191.4	173.0	154.7
115°	308.1	216.1	211.8	194.9	177.9
117.5°	313.9	235.6	231.7	216.3	200.9
120°	318.5	246.9	243.3	228.8	214.2
122.5°	325.2	260.3	256.6	242.1	227.4
125°	334.3	277.5	274.2	260.9	247.5
127.5°	343.3	294.1	290.7	277.2	263.8
130°	349.9	305.1	301.6	287.0	272.5
132.5°	355.2	314.1	310.6	296.0	281.6
135°	361.0	324.6	321.3	308.1	295.0
137.5°	369.8	338.0	334.7	321.7	308.6
140°	375.1	347.1	344.1	332.0	320.0
142.5°	379.6	353.8	351.0	339.8	328.7
145°	385.4	364.0	361.5	351.8	342.2
147.5°	393.9	376.7	374.4	364.9	355.5
150°	398.4	383.4	381.3	372.8	364.2
152.5°	401.3	387.8	386.1	379.8	373.3
155°	407.7	397.4	396.2	391.4	386.6
157.5°	414.2	407.1	405.9	401.2	396.5
160°	417.1	411.4	410.6	406.9	403.3
162.5°	420.2	416.1	415.4	412.7	410.0
165°	424.6	422.8	422.2	419.7	417.3
167.5°	428.1	426.6	426.3	425.1	423.9
170°	431.0	430.9	430.6	429.5	428.3
172.5°	431.2	431.2	431.1	430.9	430.6
175°	432.9	433.8	433.8	433.8	433.8
177.5°	433.1	433.8	433.8	433.8	433.8
180°	433.8	433.8	433.8	433.8	433.8

TEST NUMBER: P933979

CATALOG NUMBER: SQ4-FA-025U-075D-B2750-1D-UNV-W2A-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.60	15.73	15.32	16.47	17.35	17.45	18.58	18.17	19.32	20.20
	3H	15.10	16.11	15.83	16.86	17.78	18.82	19.84	19.56	20.59	21.50
	4H	15.30	16.25	16.05	17.02	17.94	19.28	20.24	20.04	21.00	21.93
	6H	15.43	16.31	16.20	17.08	18.02	19.59	20.47	20.35	21.24	22.18
	8H	15.44	16.28	16.22	17.07	18.01	19.67	20.51	20.45	21.30	22.24
	12H	15.42	16.22	16.20	17.00	17.97	19.72	20.52	20.51	21.31	22.28
4H	2H	15.67	16.62	16.43	17.38	18.31	17.89	18.85	18.65	19.61	20.53
	3H	16.72	17.52	17.49	18.31	19.26	19.43	20.22	20.20	21.02	21.96
	4H	17.01	17.73	17.79	18.53	19.50	19.97	20.69	20.76	21.49	22.46
	6H	17.15	17.77	17.95	18.60	19.57	20.36	20.98	21.16	21.80	22.78
	8H	17.16	17.74	17.97	18.56	19.55	20.47	21.06	21.28	21.88	22.87
	12H	17.14	17.67	17.97	18.50	19.50	20.55	21.07	21.37	21.91	22.91
8H	4H	17.49	18.07	18.29	18.89	19.88	20.12	20.70	20.92	21.52	22.51
	6H	17.76	18.24	18.59	19.10	20.10	20.57	21.05	21.40	21.91	22.91
	8H	17.80	18.23	18.65	19.09	20.10	20.73	21.16	21.57	22.01	23.02
	12H	17.80	18.18	18.65	19.03	20.09	20.84	21.22	21.69	22.07	23.13
12H	4H	17.51	18.03	18.33	18.87	19.87	20.09	20.62	20.92	21.46	22.46
	6H	17.82	18.25	18.67	19.11	20.12	20.57	21.00	21.42	21.86	22.87
	8H	17.90	18.28	18.75	19.13	20.19	20.75	21.13	21.59	21.97	23.04

END OF REPORT