

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934394

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934394
REPORT IS A COMBINATION OF REPORTS P933696 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9171.6 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9504	9504	9504	9504
5°	9575	9593	9575	7543
10°	9511	9450	9511	6756
15°	9407	9245	9407	7720
20°	9210	9003	9210	7736
25°	8808	8649	8808	7572
30°	8288	8355	8288	7212
35°	7388	7984	7388	6817
40°	6156	7546	6156	6518
45°	5501	7035	5501	6174
50°	5844	6424	5844	5829
55°	5499	5767	5499	5630
60°	5668	4897	5668	5156
65°	5138	4049	5138	4526
70°	3558	3227	3558	3794
75°	3121	2385	3121	2856
80°	2515	1577	2515	1717
85°	1444	835	1444	710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8431 cd/sqm

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	2.0
10°-20°	525.0	5.7
20°-30°	811.5	8.8
30°-40°	968.8	10.6
40°-50°	974.5	10.6
50°-60°	847.9	9.2
60°-70°	601.2	6.6
70°-80°	318.1	3.5
80°-90°	81.5	0.9
90°-100°	290.1	3.2
100°-110°	762.7	8.3
110°-120°	790.9	8.6
120°-130°	634.4	6.9
130°-140°	497.8	5.4
140°-150°	382.1	4.2
150°-160°	275.1	3.0
160°-170°	168.3	1.8
170°-180°	56.9	0.6
0°-30°	1521.4	16.6
0°-40°	2490.2	27.2
0°-60°	4312.6	47.0
0°-90°	5313.4	57.9
90°-120°	1843.7	20.1
90°-150°	3357.9	36.6
90°-180°	3858.0	42.1
0°-180°	9171.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2048	2048	2048	2048	2048	
5°	2058	2122	2058	1668	2058	195
15°	1965	2103	1965	1756	1965	553
25°	1730	1961	1730	1717	1730	795
35°	1316	1750	1316	1494	1316	814
45°	849	1442	849	1265	849	680
55°	692	1064	692	1039	692	636
65°	481	642	481	717	481	459
75°	182	304	182	364	182	192
85°	31	78	31	66	31	42
90°	4	15	4	15	4	5
95°	38	175	38	175	38	43
105°	137	1194	137	1194	137	146
115°	244	1538	244	1538	244	241
125°	340	1225	340	1225	340	301
135°	405	950	405	950	405	313
145°	469	771	469	771	469	294
155°	530	664	530	664	530	244
165°	572	618	572	618	572	162
175°	595	599	595	599	595	56
180°	595	595	595	595	595	

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4
2.5°	2065.8	2065.8	2077.4	2081.3	2081.3	2075.5	2069.7	2075.5	2092.9	2098.8	2096.8
5°	2058.1	2073.6	2094.9	2098.8	2102.6	2100.7	2096.8	2100.7	2120.1	2124.0	2125.9
7.5°	2042.6	2071.6	2098.8	2104.6	2110.4	2104.6	2102.6	2106.5	2125.9	2129.8	2129.8
10°	2023.2	2063.9	2094.9	2098.8	2104.6	2098.8	2098.8	2106.5	2125.9	2129.8	2131.7
12.5°	1996.0	2052.2	2081.3	2085.2	2092.9	2091.0	2089.1	2096.8	2116.2	2120.1	2120.1
15°	1965.0	2030.9	2058.1	2061.9	2075.5	2071.6	2071.6	2079.4	2100.7	2106.5	2104.6
17.5°	1922.4	2003.8	2034.8	2040.6	2050.3	2048.4	2050.3	2058.1	2077.4	2081.3	2083.3
20°	1873.9	1967.0	2003.8	2009.6	2019.3	2019.3	2019.3	2029.0	2048.4	2056.1	2056.1
22.5°	1808.1	1928.2	1967.0	1970.8	1982.5	1982.5	1986.4	1999.9	2017.4	2019.3	2019.3
25°	1730.5	1885.6	1918.5	1930.2	1941.8	1947.6	1953.4	1961.2	1967.0	1965.0	1967.0
27.5°	1649.1	1831.3	1873.9	1881.7	1897.2	1903.0	1910.8	1912.7	1914.6	1920.5	1916.6
30°	1558.1	1755.7	1819.7	1827.4	1852.6	1856.5	1848.8	1852.6	1862.3	1866.2	1870.1
32.5°	1455.3	1643.3	1763.5	1780.9	1804.2	1792.6	1790.6	1796.4	1811.9	1811.9	1815.8
35°	1315.8	1556.1	1711.2	1726.7	1744.1	1730.5	1738.3	1740.2	1749.9	1755.7	1753.8
37.5°	1162.7	1480.5	1656.9	1668.5	1682.1	1664.6	1676.3	1682.1	1689.8	1686.0	1686.0
40°	1027.1	1362.3	1592.9	1600.7	1612.3	1598.8	1610.4	1614.3	1618.1	1614.3	1612.3
42.5°	926.4	1232.5	1525.1	1534.8	1527.0	1536.7	1540.6	1548.4	1542.6	1534.8	1534.8
45°	848.8	1197.6	1451.5	1463.1	1451.5	1467.0	1472.8	1472.8	1455.3	1451.5	1449.5
47.5°	823.6	1127.9	1377.8	1377.8	1372.0	1391.4	1401.1	1387.5	1370.1	1364.3	1364.3
50°	821.7	1050.4	1277.0	1269.3	1296.4	1319.7	1310.0	1296.4	1282.9	1261.5	1261.5
52.5°	746.1	955.4	1147.3	1176.3	1218.9	1232.5	1217.0	1203.4	1180.1	1170.5	1162.7
55°	691.9	856.6	1029.1	1087.2	1131.8	1149.2	1120.2	1106.6	1071.7	1065.9	1062.0
57.5°	680.2	713.2	920.6	994.2	1048.5	1046.5	1029.1	1003.9	974.8	969.0	967.1
60°	624.0	515.5	804.3	891.5	947.7	941.9	926.4	903.1	876.0	872.1	868.2
62.5°	565.9	374.0	672.5	771.3	850.8	848.8	835.3	800.4	781.0	771.3	763.6
65°	480.6	314.0	478.7	641.5	755.8	759.7	730.6	705.4	684.1	672.5	670.5
67.5°	366.3	255.8	323.6	534.9	664.7	660.9	624.0	612.4	585.3	579.5	567.8
70°	271.3	170.5	224.8	434.1	575.6	565.9	536.8	523.3	498.1	484.5	476.7
72.5°	224.8	137.6	164.7	337.2	484.5	472.9	447.7	432.2	410.9	399.2	391.5
75°	182.2	145.4	126.0	250.0	393.4	385.7	362.4	346.9	329.5	314.0	315.9
77.5°	133.7	135.7	100.8	184.1	312.0	300.4	286.8	267.4	259.7	244.2	244.2
80°	100.8	106.6	75.6	126.0	224.8	224.8	213.2	199.6	186.0	178.3	178.3
82.5°	67.8	67.8	56.2	79.5	153.1	147.3	139.5	135.7	127.9	124.0	124.0
85°	31.0	38.8	34.9	48.4	83.3	87.2	87.2	83.3	81.4	77.5	79.5
87.5°	9.7	17.4	21.3	27.1	42.6	44.6	46.5	46.5	46.5	48.4	48.4
90°	4.0	7.2	10.4	11.1	17.5	26.1	30.3	26.9	20.3	15.2	15.2
92.5°	16.0	43.1	70.3	77.1	108.4	150.1	170.9	149.8	107.6	75.9	72.9
95°	38.4	88.1	137.8	150.2	266.7	422.0	499.7	445.9	338.4	257.7	248.5
97.5°	66.3	110.1	154.0	164.9	359.2	618.2	747.8	713.8	645.7	594.8	577.3
100°	87.9	127.6	167.3	177.3	392.9	680.3	824.0	826.6	831.5	835.2	814.4
102.5°	106.3	143.4	180.4	189.7	408.3	699.9	845.6	889.0	975.6	1040.5	1022.8
105°	137.4	168.8	200.3	208.1	419.9	702.1	843.2	940.3	1134.6	1280.2	1270.6
107.5°	169.4	198.6	227.9	235.3	421.9	670.8	795.3	930.7	1201.7	1404.9	1407.2
110°	190.9	217.3	243.9	250.5	418.8	643.1	755.3	906.8	1209.6	1436.7	1446.7

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	212.1	237.3	262.5	268.8	418.9	619.0	719.0	873.9	1183.9	1416.4	1431.7
115°	244.1	267.3	290.6	296.4	422.8	591.3	675.5	824.8	1123.4	1347.3	1368.4
117.5°	275.6	296.7	317.8	323.2	430.6	573.8	645.5	780.2	1049.7	1251.9	1275.3
120°	294.0	313.9	333.8	338.8	437.0	568.0	633.5	756.6	1002.8	1187.5	1210.3
122.5°	311.9	332.0	352.0	357.1	446.1	564.9	624.3	735.2	957.0	1123.3	1145.7
125°	339.5	357.8	376.1	380.6	458.5	562.4	614.3	708.5	896.9	1038.2	1058.9
127.5°	361.9	380.3	398.7	403.4	470.9	561.0	605.9	686.8	848.6	969.9	987.3
130°	373.8	393.7	413.7	418.6	479.9	561.8	602.7	674.7	818.7	926.7	942.8
132.5°	386.2	406.1	426.1	431.0	487.3	562.4	600.0	664.4	793.3	889.9	904.4
135°	404.7	422.8	440.8	445.4	495.3	561.8	595.2	649.1	757.1	838.0	850.5
137.5°	423.5	441.4	459.3	463.8	507.3	565.3	594.4	640.0	731.3	799.7	809.9
140°	439.0	455.5	472.0	476.2	514.6	565.9	591.6	631.0	709.8	768.9	778.4
142.5°	451.0	466.2	481.5	485.3	520.7	567.9	591.6	626.2	695.5	747.4	755.6
145°	469.4	482.7	496.0	499.3	528.8	568.0	587.6	615.9	672.6	715.0	721.2
147.5°	487.7	500.7	513.7	516.9	540.4	571.9	587.6	609.9	654.4	687.8	692.9
150°	499.7	511.4	523.2	526.1	546.6	573.9	587.6	606.4	644.1	672.3	676.5
152.5°	512.1	521.0	529.8	532.1	550.6	575.3	587.6	603.7	635.8	659.9	663.1
155°	530.4	537.0	543.6	545.3	559.4	578.2	587.6	600.4	625.9	645.1	647.2
157.5°	544.0	550.4	556.8	558.4	568.1	581.1	587.6	597.5	617.3	632.3	633.7
160°	553.2	558.2	563.2	564.4	572.2	582.5	587.6	596.1	613.1	625.9	626.7
162.5°	562.4	566.2	569.9	570.8	576.5	583.9	587.6	594.8	609.2	620.0	620.7
165°	572.4	575.8	579.1	579.9	582.5	585.9	587.6	592.7	603.0	610.8	611.6
167.5°	581.6	583.1	584.8	585.2	587.3	590.1	591.6	595.0	601.7	606.8	607.2
170°	587.6	589.2	590.8	591.2	591.3	591.5	591.6	595.0	601.7	606.8	606.8
172.5°	590.8	591.2	591.5	591.6	591.6	591.6	591.6	594.3	599.6	603.6	603.3
175°	595.2	595.2	595.2	595.2	594.0	592.3	591.6	593.2	596.6	599.1	599.1
177.5°	595.2	595.2	595.2	595.2	594.2	592.9	592.3	593.7	596.3	598.4	598.0
180°	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4
2.5°	2100.7	2094.9	2100.7	2096.8	2098.8	2092.9	2075.5	2069.7	2075.5	2081.3	2081.3
5°	2125.9	2122.0	2125.9	2125.9	2124.0	2120.1	2100.7	2096.8	2100.7	2102.6	2098.8
7.5°	2133.6	2127.8	2133.6	2129.8	2129.8	2125.9	2106.5	2102.6	2104.6	2110.4	2104.6
10°	2133.6	2127.8	2133.6	2131.7	2129.8	2125.9	2106.5	2098.8	2098.8	2104.6	2098.8
12.5°	2124.0	2120.1	2124.0	2120.1	2120.1	2116.2	2096.8	2089.1	2091.0	2092.9	2085.2
15°	2108.4	2102.6	2108.4	2104.6	2106.5	2100.7	2079.4	2071.6	2071.6	2075.5	2061.9
17.5°	2085.2	2077.4	2085.2	2083.3	2081.3	2077.4	2058.1	2050.3	2048.4	2050.3	2040.6
20°	2058.1	2052.2	2058.1	2056.1	2056.1	2048.4	2029.0	2019.3	2019.3	2019.3	2009.6
22.5°	2015.4	2009.6	2015.4	2019.3	2019.3	2017.4	1999.9	1986.4	1982.5	1982.5	1970.8
25°	1967.0	1961.2	1967.0	1967.0	1965.0	1967.0	1961.2	1953.4	1947.6	1941.8	1930.2
27.5°	1920.5	1916.6	1920.5	1916.6	1920.5	1914.6	1912.7	1910.8	1903.0	1897.2	1881.7
30°	1873.9	1870.1	1873.9	1870.1	1866.2	1862.3	1852.6	1848.8	1856.5	1852.6	1827.4
32.5°	1815.8	1811.9	1815.8	1815.8	1811.9	1811.9	1796.4	1790.6	1792.6	1804.2	1780.9
35°	1755.7	1749.9	1755.7	1753.8	1755.7	1749.9	1740.2	1738.3	1730.5	1744.1	1726.7
37.5°	1686.0	1680.1	1686.0	1686.0	1686.0	1689.8	1682.1	1676.3	1664.6	1682.1	1668.5
40°	1614.3	1606.5	1614.3	1612.3	1614.3	1618.1	1614.3	1610.4	1598.8	1612.3	1600.7
42.5°	1532.9	1530.9	1532.9	1534.8	1534.8	1542.6	1548.4	1540.6	1536.7	1527.0	1534.8
45°	1445.7	1441.8	1445.7	1449.5	1451.5	1455.3	1472.8	1472.8	1467.0	1451.5	1463.1
47.5°	1352.6	1342.9	1352.6	1364.3	1364.3	1370.1	1387.5	1401.1	1391.4	1372.0	1377.8
50°	1253.8	1255.7	1253.8	1261.5	1261.5	1282.9	1296.4	1310.0	1319.7	1296.4	1269.3
52.5°	1156.9	1155.0	1156.9	1162.7	1170.5	1180.1	1203.4	1217.0	1232.5	1218.9	1176.3
55°	1060.1	1064.0	1060.1	1062.0	1065.9	1071.7	1106.6	1120.2	1149.2	1131.8	1087.2
57.5°	963.2	957.4	963.2	967.1	969.0	974.8	1003.9	1029.1	1046.5	1048.5	994.2
60°	850.8	843.0	850.8	868.2	872.1	876.0	903.1	926.4	941.9	947.7	891.5
62.5°	751.9	738.4	751.9	763.6	771.3	781.0	800.4	835.3	848.8	850.8	771.3
65°	647.3	641.5	647.3	670.5	672.5	684.1	705.4	730.6	759.7	755.8	641.5
67.5°	552.3	552.3	552.3	567.8	579.5	585.3	612.4	624.0	660.9	664.7	534.9
70°	465.1	463.2	465.1	476.7	484.5	498.1	523.3	536.8	565.9	575.6	434.1
72.5°	381.8	379.8	381.8	391.5	399.2	410.9	432.2	447.7	472.9	484.5	337.2
75°	308.1	304.3	308.1	315.9	314.0	329.5	346.9	362.4	385.7	393.4	250.0
77.5°	236.4	236.4	236.4	244.2	244.2	259.7	267.4	286.8	300.4	312.0	184.1
80°	176.4	174.4	176.4	178.3	178.3	186.0	199.6	213.2	224.8	224.8	126.0
82.5°	124.0	120.2	124.0	124.0	124.0	127.9	135.7	139.5	147.3	153.1	79.5
85°	77.5	77.5	77.5	79.5	77.5	81.4	83.3	87.2	87.2	83.3	48.4
87.5°	50.4	48.4	50.4	48.4	48.4	46.5	46.5	46.5	44.6	42.6	27.1
90°	15.2	15.2	15.2	15.2	15.2	20.3	26.9	30.3	26.1	17.5	11.1
92.5°	60.8	48.7	60.8	72.9	75.9	107.6	149.8	170.9	150.1	108.4	77.1
95°	211.9	175.4	211.9	248.5	257.7	338.4	445.9	499.7	422.0	266.7	150.2
97.5°	507.8	438.2	507.8	577.3	594.8	645.7	713.8	747.8	618.2	359.2	164.9
100°	731.6	648.6	731.6	814.4	835.2	831.5	826.6	824.0	680.3	392.9	177.3
102.5°	951.8	880.7	951.8	1022.8	1040.5	975.6	889.0	845.6	699.9	408.3	189.7
105°	1232.5	1194.3	1232.5	1270.6	1280.2	1134.6	940.3	843.2	702.1	419.9	208.1
107.5°	1416.4	1425.6	1416.4	1407.2	1404.9	1201.7	930.7	795.3	670.8	421.9	235.3
110°	1486.4	1526.3	1486.4	1446.7	1436.7	1209.6	906.8	755.3	643.1	418.8	250.5

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1492.7	1553.8	1492.7	1431.7	1416.4	1183.9	873.9	719.0	619.0	418.9	268.8
115°	1453.1	1537.8	1453.1	1368.4	1347.3	1123.4	824.8	675.5	591.3	422.8	296.4
117.5°	1369.3	1463.2	1369.3	1275.3	1251.9	1049.7	780.2	645.5	573.8	430.6	323.2
120°	1301.6	1392.8	1301.6	1210.3	1187.5	1002.8	756.6	633.5	568.0	437.0	338.8
122.5°	1235.8	1325.8	1235.8	1145.7	1123.3	957.0	735.2	624.3	564.9	446.1	357.1
125°	1141.8	1224.7	1141.8	1058.9	1038.2	896.9	708.5	614.3	562.4	458.5	380.6
127.5°	1057.3	1127.2	1057.3	987.3	969.9	848.6	686.8	605.9	561.0	470.9	403.4
130°	1007.5	1072.1	1007.5	942.8	926.7	818.7	674.7	602.7	561.8	479.9	418.6
132.5°	962.3	1020.2	962.3	904.4	889.9	793.3	664.4	600.0	562.4	487.3	431.0
135°	900.4	950.3	900.4	850.5	838.0	757.1	649.1	595.2	561.8	495.3	445.4
137.5°	850.8	891.6	850.8	809.9	799.7	731.3	640.0	594.4	565.3	507.3	463.8
140°	816.6	854.8	816.6	778.4	768.9	709.8	631.0	591.6	565.9	514.6	476.2
142.5°	788.4	821.2	788.4	755.6	747.4	695.5	626.2	591.6	567.9	520.7	485.3
145°	746.1	770.9	746.1	721.2	715.0	672.6	615.9	587.6	568.0	528.8	499.3
147.5°	713.6	734.2	713.6	692.9	687.8	654.4	609.9	587.6	571.9	540.4	516.9
150°	693.1	709.8	693.1	676.5	672.3	644.1	606.4	587.6	573.9	546.6	526.1
152.5°	675.7	688.3	675.7	663.1	659.9	635.8	603.7	587.6	575.3	550.6	532.1
155°	655.5	663.9	655.5	647.2	645.1	625.9	600.4	587.6	578.2	559.4	545.3
157.5°	639.6	645.5	639.6	633.7	632.3	617.3	597.5	587.6	581.1	568.1	558.4
160°	630.1	633.5	630.1	626.7	625.9	613.1	596.1	587.6	582.5	572.2	564.4
162.5°	623.9	627.1	623.9	620.7	620.0	609.2	594.8	587.6	583.9	576.5	570.8
165°	614.9	618.3	614.9	611.6	610.8	603.0	592.7	587.6	585.9	582.5	579.9
167.5°	608.5	610.0	608.5	607.2	606.8	601.7	595.0	591.6	590.1	587.3	585.2
170°	606.8	606.8	606.8	606.8	606.8	601.7	595.0	591.6	591.5	591.3	591.2
172.5°	602.0	600.8	602.0	603.3	603.6	599.6	594.3	591.6	591.6	591.6	591.6
175°	599.1	599.1	599.1	599.1	599.1	596.6	593.2	591.6	592.3	594.0	595.2
177.5°	596.6	595.2	596.6	598.0	598.4	596.3	593.7	592.3	592.9	594.2	595.2
180°	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4
2.5°	2077.4	2065.8	2065.8	2046.4	2038.7	2032.9	2023.2	1994.1	1986.4	1978.6	1990.2
5°	2094.9	2073.6	2058.1	2023.2	1994.1	1982.5	1945.7	1875.9	1829.4	1794.5	1775.1
7.5°	2098.8	2071.6	2042.6	1988.3	1918.5	1887.5	1775.1	1647.2	1612.3	1581.3	1561.9
10°	2094.9	2063.9	2023.2	1941.8	1777.0	1722.8	1610.4	1527.0	1505.7	1499.9	1505.7
12.5°	2081.3	2052.2	1996.0	1860.4	1629.8	1592.9	1527.0	1478.6	1474.7	1484.4	1536.7
15°	2058.1	2030.9	1965.0	1751.9	1548.4	1521.2	1474.7	1457.3	1478.6	1546.4	1703.4
17.5°	2034.8	2003.8	1922.4	1645.3	1486.3	1467.0	1434.0	1468.9	1589.1	1680.1	1732.5
20°	2003.8	1967.0	1873.9	1567.7	1441.8	1424.3	1408.8	1565.8	1656.9	1689.8	1718.9
22.5°	1967.0	1928.2	1808.1	1513.5	1395.3	1381.7	1391.4	1620.1	1656.9	1680.1	1705.3
25°	1918.5	1885.6	1730.5	1470.8	1358.4	1342.9	1379.8	1614.3	1635.6	1641.4	1691.8
27.5°	1873.9	1831.3	1649.1	1432.1	1313.9	1308.1	1389.4	1589.1	1604.6	1610.4	1664.6
30°	1819.7	1755.7	1558.1	1391.4	1267.4	1265.4	1391.4	1558.1	1554.2	1569.7	1623.9
32.5°	1763.5	1643.3	1455.3	1341.0	1222.8	1220.8	1377.8	1511.5	1507.7	1529.0	1569.7
35°	1711.2	1556.1	1315.8	1282.9	1166.6	1168.5	1344.9	1457.3	1459.2	1478.6	1503.8
37.5°	1656.9	1480.5	1162.7	1218.9	1112.4	1112.4	1300.3	1406.9	1403.0	1408.8	1443.7
40°	1592.9	1362.3	1027.1	1135.7	1062.0	1056.2	1246.0	1352.6	1339.1	1337.1	1385.6
42.5°	1525.1	1232.5	926.4	1025.2	1003.9	996.1	1180.1	1286.7	1261.5	1267.4	1329.4
45°	1451.5	1197.6	848.8	866.3	943.8	938.0	1108.5	1211.2	1193.7	1209.2	1273.2
47.5°	1377.8	1127.9	823.6	719.0	879.9	877.9	1029.1	1137.6	1127.9	1143.4	1211.2
50°	1277.0	1050.4	821.7	616.3	808.1	815.9	934.1	1065.9	1065.9	1079.5	1151.2
52.5°	1147.3	955.4	746.1	558.1	724.8	748.1	850.8	1003.9	1007.8	1021.3	1085.3
55°	1029.1	856.6	691.9	513.6	626.0	676.4	769.4	939.9	947.7	961.2	1019.4
57.5°	920.6	713.2	680.2	461.2	534.9	583.3	697.7	877.9	881.8	893.4	949.6
60°	804.3	515.5	624.0	405.0	455.4	492.3	631.8	804.3	817.8	825.6	874.0
62.5°	672.5	374.0	565.9	366.3	416.7	424.4	577.5	734.5	751.9	757.8	786.8
65°	478.7	314.0	480.6	333.3	376.0	377.9	519.4	662.8	678.3	688.0	709.3
67.5°	323.6	255.8	366.3	302.3	345.0	346.9	463.2	579.5	600.8	608.5	622.1
70°	224.8	170.5	271.3	269.4	310.1	314.0	403.1	503.9	523.3	529.1	536.8
72.5°	164.7	137.6	224.8	242.2	273.3	277.1	341.1	418.6	438.0	443.8	447.7
75°	126.0	145.4	182.2	211.2	232.6	234.5	279.1	341.1	354.7	358.5	360.5
77.5°	100.8	135.7	133.7	170.5	189.9	186.0	219.0	263.6	275.2	275.2	275.2
80°	75.6	106.6	100.8	122.1	139.5	135.7	157.0	188.0	191.9	195.7	193.8
82.5°	56.2	67.8	67.8	77.5	93.0	89.1	104.7	122.1	122.1	122.1	126.0
85°	34.9	38.8	31.0	40.7	52.3	50.4	58.1	65.9	67.8	67.8	64.0
87.5°	21.3	17.4	9.7	15.5	23.3	23.3	27.1	29.1	27.1	27.1	27.1
90°	10.4	7.2	4.0	7.2	10.4	11.1	17.5	26.1	30.3	26.9	20.3
92.5°	70.3	43.1	16.0	43.1	70.3	77.1	108.4	150.1	170.9	149.8	107.6
95°	137.8	88.1	38.4	88.1	137.8	150.2	266.7	422.0	499.7	445.9	338.4
97.5°	154.0	110.1	66.3	110.1	154.0	164.9	359.2	618.2	747.8	713.8	645.7
100°	167.3	127.6	87.9	127.6	167.3	177.3	392.9	680.3	824.0	826.6	831.5
102.5°	180.4	143.4	106.3	143.4	180.4	189.7	408.3	699.9	845.6	889.0	975.6
105°	200.3	168.8	137.4	168.8	200.3	208.1	419.9	702.1	843.2	940.3	1134.6
107.5°	227.9	198.6	169.4	198.6	227.9	235.3	421.9	670.8	795.3	930.7	1201.7
110°	243.9	217.3	190.9	217.3	243.9	250.5	418.8	643.1	755.3	906.8	1209.6

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	262.5	237.3	212.1	237.3	262.5	268.8	418.9	619.0	719.0	873.9	1183.9
115°	290.6	267.3	244.1	267.3	290.6	296.4	422.8	591.3	675.5	824.8	1123.4
117.5°	317.8	296.7	275.6	296.7	317.8	323.2	430.6	573.8	645.5	780.2	1049.7
120°	333.8	313.9	294.0	313.9	333.8	338.8	437.0	568.0	633.5	756.6	1002.8
122.5°	352.0	332.0	311.9	332.0	352.0	357.1	446.1	564.9	624.3	735.2	957.0
125°	376.1	357.8	339.5	357.8	376.1	380.6	458.5	562.4	614.3	708.5	896.9
127.5°	398.7	380.3	361.9	380.3	398.7	403.4	470.9	561.0	605.9	686.8	848.6
130°	413.7	393.7	373.8	393.7	413.7	418.6	479.9	561.8	602.7	674.7	818.7
132.5°	426.1	406.1	386.2	406.1	426.1	431.0	487.3	562.4	600.0	664.4	793.3
135°	440.8	422.8	404.7	422.8	440.8	445.4	495.3	561.8	595.2	649.1	757.1
137.5°	459.3	441.4	423.5	441.4	459.3	463.8	507.3	565.3	594.4	640.0	731.3
140°	472.0	455.5	439.0	455.5	472.0	476.2	514.6	565.9	591.6	631.0	709.8
142.5°	481.5	466.2	451.0	466.2	481.5	485.3	520.7	567.9	591.6	626.2	695.5
145°	496.0	482.7	469.4	482.7	496.0	499.3	528.8	568.0	587.6	615.9	672.6
147.5°	513.7	500.7	487.7	500.7	513.7	516.9	540.4	571.9	587.6	609.9	654.4
150°	523.2	511.4	499.7	511.4	523.2	526.1	546.6	573.9	587.6	606.4	644.1
152.5°	529.8	521.0	512.1	521.0	529.8	532.1	550.6	575.3	587.6	603.7	635.8
155°	543.6	537.0	530.4	537.0	543.6	545.3	559.4	578.2	587.6	600.4	625.9
157.5°	556.8	550.4	544.0	550.4	556.8	558.4	568.1	581.1	587.6	597.5	617.3
160°	563.2	558.2	553.2	558.2	563.2	564.4	572.2	582.5	587.6	596.1	613.1
162.5°	569.9	566.2	562.4	566.2	569.9	570.8	576.5	583.9	587.6	594.8	609.2
165°	579.1	575.8	572.4	575.8	579.1	579.9	582.5	585.9	587.6	592.7	603.0
167.5°	584.8	583.1	581.6	583.1	584.8	585.2	587.3	590.1	591.6	595.0	601.7
170°	590.8	589.2	587.6	589.2	590.8	591.2	591.3	591.5	591.6	595.0	601.7
172.5°	591.5	591.2	590.8	591.2	591.5	591.6	591.6	591.6	591.6	594.3	599.6
175°	595.2	595.2	595.2	595.2	595.2	595.2	594.0	592.3	591.6	593.2	596.6
177.5°	595.2	595.2	595.2	595.2	595.2	595.2	594.2	592.9	592.3	593.7	596.3
180°	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4	2048.4
2.5°	1976.7	1970.8	1978.6	1957.3	1978.6	1970.8	1976.7	1990.2	1978.6	1986.4	1994.1
5°	1734.4	1724.7	1693.7	1668.5	1693.7	1724.7	1734.4	1775.1	1794.5	1829.4	1875.9
7.5°	1550.3	1542.6	1534.8	1519.3	1534.8	1542.6	1550.3	1561.9	1581.3	1612.3	1647.2
10°	1509.6	1511.5	1523.2	1521.2	1523.2	1511.5	1509.6	1505.7	1499.9	1505.7	1527.0
12.5°	1614.3	1631.7	1695.7	1691.8	1695.7	1631.7	1614.3	1536.7	1484.4	1474.7	1478.6
15°	1734.4	1740.2	1753.8	1755.7	1753.8	1740.2	1734.4	1703.4	1546.4	1478.6	1457.3
17.5°	1746.0	1748.0	1757.7	1757.7	1757.7	1748.0	1746.0	1732.5	1680.1	1589.1	1468.9
20°	1736.4	1740.2	1759.6	1763.5	1759.6	1740.2	1736.4	1718.9	1689.8	1656.9	1565.8
22.5°	1732.5	1740.2	1755.7	1753.8	1755.7	1740.2	1732.5	1705.3	1680.1	1656.9	1620.1
25°	1713.1	1713.1	1715.0	1717.0	1715.0	1713.1	1713.1	1691.8	1641.4	1635.6	1614.3
27.5°	1672.4	1676.3	1687.9	1686.0	1687.9	1676.3	1672.4	1664.6	1610.4	1604.6	1589.1
30°	1635.6	1631.7	1622.0	1614.3	1622.0	1631.7	1635.6	1623.9	1569.7	1554.2	1558.1
32.5°	1573.6	1563.9	1554.2	1548.4	1554.2	1563.9	1573.6	1569.7	1529.0	1507.7	1511.5
35°	1499.9	1501.9	1499.9	1494.1	1499.9	1501.9	1499.9	1503.8	1478.6	1459.2	1457.3
37.5°	1447.6	1451.5	1449.5	1441.8	1449.5	1451.5	1447.6	1443.7	1408.8	1403.0	1406.9
40°	1393.3	1395.3	1393.3	1387.5	1393.3	1395.3	1393.3	1385.6	1337.1	1339.1	1352.6
42.5°	1341.0	1339.1	1333.2	1329.4	1333.2	1339.1	1341.0	1329.4	1267.4	1261.5	1286.7
45°	1280.9	1282.9	1271.2	1265.4	1271.2	1282.9	1280.9	1273.2	1209.2	1193.7	1211.2
47.5°	1220.8	1220.8	1211.2	1205.3	1211.2	1220.8	1220.8	1211.2	1143.4	1127.9	1137.6
50°	1156.9	1155.0	1141.5	1139.5	1141.5	1155.0	1156.9	1151.2	1079.5	1065.9	1065.9
52.5°	1083.3	1083.3	1085.3	1089.2	1085.3	1083.3	1083.3	1085.3	1021.3	1007.8	1003.9
55°	1019.4	1021.3	1034.9	1038.8	1034.9	1021.3	1019.4	1019.4	961.2	947.7	939.9
57.5°	953.5	953.5	963.2	963.2	963.2	953.5	953.5	949.6	893.4	881.8	877.9
60°	877.9	881.8	889.5	887.6	889.5	881.8	877.9	874.0	825.6	817.8	804.3
62.5°	798.5	802.3	804.3	800.4	804.3	802.3	798.5	786.8	757.8	751.9	734.5
65°	715.1	719.0	720.9	717.1	720.9	719.0	715.1	709.3	688.0	678.3	662.8
67.5°	629.8	627.9	626.0	633.7	626.0	627.9	629.8	622.1	608.5	600.8	579.5
70°	542.6	542.6	540.7	544.6	540.7	542.6	542.6	536.8	529.1	523.3	503.9
72.5°	449.6	447.7	455.4	449.6	455.4	447.7	449.6	447.7	443.8	438.0	418.6
75°	358.5	362.4	358.5	364.3	358.5	362.4	358.5	360.5	358.5	354.7	341.1
77.5°	273.3	277.1	273.3	273.3	273.3	277.1	273.3	275.2	275.2	275.2	263.6
80°	193.8	191.9	191.9	189.9	191.9	191.9	193.8	193.8	195.7	191.9	188.0
82.5°	124.0	122.1	122.1	126.0	122.1	122.1	124.0	126.0	122.1	122.1	122.1
85°	67.8	69.8	65.9	65.9	65.9	69.8	67.8	64.0	67.8	67.8	65.9
87.5°	25.2	23.3	23.3	23.3	23.3	23.3	25.2	27.1	27.1	27.1	29.1
90°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	20.3	26.9	30.3	26.1
92.5°	75.9	72.9	60.8	48.7	60.8	72.9	75.9	107.6	149.8	170.9	150.1
95°	257.7	248.5	211.9	175.4	211.9	248.5	257.7	338.4	445.9	499.7	422.0
97.5°	594.8	577.3	507.8	438.2	507.8	577.3	594.8	645.7	713.8	747.8	618.2
100°	835.2	814.4	731.6	648.6	731.6	814.4	835.2	831.5	826.6	824.0	680.3
102.5°	1040.5	1022.8	951.8	880.7	951.8	1022.8	1040.5	975.6	889.0	845.6	699.9
105°	1280.2	1270.6	1232.5	1194.3	1232.5	1270.6	1280.2	1134.6	940.3	843.2	702.1
107.5°	1404.9	1407.2	1416.4	1425.6	1416.4	1407.2	1404.9	1201.7	930.7	795.3	670.8
110°	1436.7	1446.7	1486.4	1526.3	1486.4	1446.7	1436.7	1209.6	906.8	755.3	643.1

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1416.4	1431.7	1492.7	1553.8	1492.7	1431.7	1416.4	1183.9	873.9	719.0	619.0
115°	1347.3	1368.4	1453.1	1537.8	1453.1	1368.4	1347.3	1123.4	824.8	675.5	591.3
117.5°	1251.9	1275.3	1369.3	1463.2	1369.3	1275.3	1251.9	1049.7	780.2	645.5	573.8
120°	1187.5	1210.3	1301.6	1392.8	1301.6	1210.3	1187.5	1002.8	756.6	633.5	568.0
122.5°	1123.3	1145.7	1235.8	1325.8	1235.8	1145.7	1123.3	957.0	735.2	624.3	564.9
125°	1038.2	1058.9	1141.8	1224.7	1141.8	1058.9	1038.2	896.9	708.5	614.3	562.4
127.5°	969.9	987.3	1057.3	1127.2	1057.3	987.3	969.9	848.6	686.8	605.9	561.0
130°	926.7	942.8	1007.5	1072.1	1007.5	942.8	926.7	818.7	674.7	602.7	561.8
132.5°	889.9	904.4	962.3	1020.2	962.3	904.4	889.9	793.3	664.4	600.0	562.4
135°	838.0	850.5	900.4	950.3	900.4	850.5	838.0	757.1	649.1	595.2	561.8
137.5°	799.7	809.9	850.8	891.6	850.8	809.9	799.7	731.3	640.0	594.4	565.3
140°	768.9	778.4	816.6	854.8	816.6	778.4	768.9	709.8	631.0	591.6	565.9
142.5°	747.4	755.6	788.4	821.2	788.4	755.6	747.4	695.5	626.2	591.6	567.9
145°	715.0	721.2	746.1	770.9	746.1	721.2	715.0	672.6	615.9	587.6	568.0
147.5°	687.8	692.9	713.6	734.2	713.6	692.9	687.8	654.4	609.9	587.6	571.9
150°	672.3	676.5	693.1	709.8	693.1	676.5	672.3	644.1	606.4	587.6	573.9
152.5°	659.9	663.1	675.7	688.3	675.7	663.1	659.9	635.8	603.7	587.6	575.3
155°	645.1	647.2	655.5	663.9	655.5	647.2	645.1	625.9	600.4	587.6	578.2
157.5°	632.3	633.7	639.6	645.5	639.6	633.7	632.3	617.3	597.5	587.6	581.1
160°	625.9	626.7	630.1	633.5	630.1	626.7	625.9	613.1	596.1	587.6	582.5
162.5°	620.0	620.7	623.9	627.1	623.9	620.7	620.0	609.2	594.8	587.6	583.9
165°	610.8	611.6	614.9	618.3	614.9	611.6	610.8	603.0	592.7	587.6	585.9
167.5°	606.8	607.2	608.5	610.0	608.5	607.2	606.8	601.7	595.0	591.6	590.1
170°	606.8	606.8	606.8	606.8	606.8	606.8	606.8	601.7	595.0	591.6	591.5
172.5°	603.6	603.3	602.0	600.8	602.0	603.3	603.6	599.6	594.3	591.6	591.6
175°	599.1	599.1	599.1	599.1	599.1	599.1	599.1	596.6	593.2	591.6	592.3
177.5°	598.4	598.0	596.6	595.2	596.6	598.0	598.4	596.3	593.7	592.3	592.9
180°	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	2048.4	2048.4	2048.4	2048.4	2048.4
2.5°	2023.2	2032.9	2038.7	2046.4	2065.8
5°	1945.7	1982.5	1994.1	2023.2	2058.1
7.5°	1775.1	1887.5	1918.5	1988.3	2042.6
10°	1610.4	1722.8	1777.0	1941.8	2023.2
12.5°	1527.0	1592.9	1629.8	1860.4	1996.0
15°	1474.7	1521.2	1548.4	1751.9	1965.0
17.5°	1434.0	1467.0	1486.3	1645.3	1922.4
20°	1408.8	1424.3	1441.8	1567.7	1873.9
22.5°	1391.4	1381.7	1395.3	1513.5	1808.1
25°	1379.8	1342.9	1358.4	1470.8	1730.5
27.5°	1389.4	1308.1	1313.9	1432.1	1649.1
30°	1391.4	1265.4	1267.4	1391.4	1558.1
32.5°	1377.8	1220.8	1222.8	1341.0	1455.3
35°	1344.9	1168.5	1166.6	1282.9	1315.8
37.5°	1300.3	1112.4	1112.4	1218.9	1162.7
40°	1246.0	1056.2	1062.0	1135.7	1027.1
42.5°	1180.1	996.1	1003.9	1025.2	926.4
45°	1108.5	938.0	943.8	866.3	848.8
47.5°	1029.1	877.9	879.9	719.0	823.6
50°	934.1	815.9	808.1	616.3	821.7
52.5°	850.8	748.1	724.8	558.1	746.1
55°	769.4	676.4	626.0	513.6	691.9
57.5°	697.7	583.3	534.9	461.2	680.2
60°	631.8	492.3	455.4	405.0	624.0
62.5°	577.5	424.4	416.7	366.3	565.9
65°	519.4	377.9	376.0	333.3	480.6
67.5°	463.2	346.9	345.0	302.3	366.3
70°	403.1	314.0	310.1	269.4	271.3
72.5°	341.1	277.1	273.3	242.2	224.8
75°	279.1	234.5	232.6	211.2	182.2
77.5°	219.0	186.0	189.9	170.5	133.7
80°	157.0	135.7	139.5	122.1	100.8
82.5°	104.7	89.1	93.0	77.5	67.8
85°	58.1	50.4	52.3	40.7	31.0
87.5°	27.1	23.3	23.3	15.5	9.7
90°	17.5	11.1	10.4	7.2	4.0
92.5°	108.4	77.1	70.3	43.1	16.0
95°	266.7	150.2	137.8	88.1	38.4
97.5°	359.2	164.9	154.0	110.1	66.3
100°	392.9	177.3	167.3	127.6	87.9
102.5°	408.3	189.7	180.4	143.4	106.3
105°	419.9	208.1	200.3	168.8	137.4
107.5°	421.9	235.3	227.9	198.6	169.4
110°	418.8	250.5	243.9	217.3	190.9

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	418.9	268.8	262.5	237.3	212.1
115°	422.8	296.4	290.6	267.3	244.1
117.5°	430.6	323.2	317.8	296.7	275.6
120°	437.0	338.8	333.8	313.9	294.0
122.5°	446.1	357.1	352.0	332.0	311.9
125°	458.5	380.6	376.1	357.8	339.5
127.5°	470.9	403.4	398.7	380.3	361.9
130°	479.9	418.6	413.7	393.7	373.8
132.5°	487.3	431.0	426.1	406.1	386.2
135°	495.3	445.4	440.8	422.8	404.7
137.5°	507.3	463.8	459.3	441.4	423.5
140°	514.6	476.2	472.0	455.5	439.0
142.5°	520.7	485.3	481.5	466.2	451.0
145°	528.8	499.3	496.0	482.7	469.4
147.5°	540.4	516.9	513.7	500.7	487.7
150°	546.6	526.1	523.2	511.4	499.7
152.5°	550.6	532.1	529.8	521.0	512.1
155°	559.4	545.3	543.6	537.0	530.4
157.5°	568.1	558.4	556.8	550.4	544.0
160°	572.2	564.4	563.2	558.2	553.2
162.5°	576.5	570.8	569.9	566.2	562.4
165°	582.5	579.9	579.1	575.8	572.4
167.5°	587.3	585.2	584.8	583.1	581.6
170°	591.3	591.2	590.8	589.2	587.6
172.5°	591.6	591.6	591.5	591.2	590.8
175°	594.0	595.2	595.2	595.2	595.2
177.5°	594.2	595.2	595.2	595.2	595.2
180°	595.2	595.2	595.2	595.2	595.2

TEST NUMBER: P934394

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.33	14.27	14.22	15.18	16.33	16.17	17.11	17.06	18.01	19.17
	3H	13.82	14.66	14.71	15.57	16.75	17.52	18.36	18.42	19.28	20.46
	4H	14.01	14.80	14.92	15.73	16.91	17.97	18.77	18.89	19.69	20.88
	6H	14.13	14.87	15.06	15.79	16.99	18.26	19.00	19.19	19.92	21.13
	8H	14.14	14.83	15.07	15.78	16.98	18.34	19.04	19.27	19.98	21.18
	12H	14.11	14.77	15.05	15.71	16.94	18.38	19.05	19.32	19.99	21.21
4H	2H	14.38	15.17	15.30	16.09	17.28	16.59	17.38	17.51	18.30	19.49
	3H	15.41	16.07	16.34	17.02	18.23	18.10	18.77	19.03	19.72	20.92
	4H	15.69	16.29	16.63	17.24	18.47	18.64	19.24	19.58	20.19	21.42
	6H	15.82	16.34	16.77	17.31	18.54	19.01	19.53	19.96	20.50	21.73
	8H	15.83	16.31	16.78	17.28	18.52	19.12	19.60	20.07	20.57	21.81
	12H	15.80	16.24	16.77	17.22	18.47	19.18	19.62	20.15	20.60	21.85
8H	4H	16.15	16.64	17.11	17.60	18.84	18.77	19.25	19.72	20.22	21.46
	6H	16.42	16.82	17.40	17.82	19.06	19.21	19.61	20.19	20.62	21.86
	8H	16.46	16.81	17.45	17.81	19.07	19.36	19.72	20.35	20.71	21.97
	12H	16.45	16.76	17.44	17.75	19.05	19.47	19.78	20.46	20.77	22.07
12H	4H	16.16	16.60	17.14	17.58	18.83	18.74	19.17	19.71	20.16	21.40
	6H	16.48	16.83	17.47	17.83	19.09	19.21	19.56	20.20	20.56	21.82
	8H	16.55	16.86	17.54	17.85	19.16	19.37	19.69	20.37	20.67	21.98

END OF REPORT