

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934579

Luminaire Tested: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934579
REPORT IS A COMBINATION OF REPORTS P933701 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19272.4 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 168
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63	63	63	59
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	56	53	53	53	50
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	52	48	45	45	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	39	39	36
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	34	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	30	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	27	27	24
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	31	27	24	24	24	22
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21	21	21	19
10	49	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	19	19	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16083	16083	16083	16083
5°	16209	16235	16209	12766
10°	16107	15992	16107	11433
15°	15937	15645	15937	13064
20°	15610	15235	15610	13092
25°	14934	14636	14934	12814
30°	14058	14139	14058	12205
35°	12539	13511	12539	11536
40°	10454	12771	10454	11030
45°	9347	11904	9347	10448
50°	9938	10871	9938	9865
55°	9359	9758	9359	9527
60°	9659	8287	9659	8726
65°	8772	6851	8772	7658
70°	6089	5460	6089	6419
75°	5359	4036	5359	4833
80°	4351	2668	4351	2905
85°	2550	1413	2550	1201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14316 cd/sqm

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	469.4	2.4
10°-20°	1332.6	6.9
20°-30°	2060.0	10.7
30°-40°	2459.2	12.8
40°-50°	2473.6	12.8
50°-60°	2152.4	11.2
60°-70°	1526.1	7.9
70°-80°	807.4	4.2
80°-90°	204.5	1.1
90°-100°	435.1	2.3
100°-110°	1144.1	5.9
110°-120°	1186.3	6.2
120°-130°	951.5	4.9
130°-140°	746.6	3.9
140°-150°	573.1	3.0
150°-160°	412.7	2.1
160°-170°	252.5	1.3
170°-180°	85.3	0.4
0°-30°	3862.0	20.0
0°-40°	6321.2	32.8
0°-60°	10947.2	56.8
0°-90°	13485.1	70.0
90°-120°	2765.5	14.3
90°-150°	5036.8	26.1
90°-180°	5787.0	30.0
0°-180°	19272.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5200	5200	5200	5200	5200	
5°	5224	5387	5224	4236	5224	496
15°	4988	5337	4988	4457	4988	1403
25°	4393	4978	4393	4358	4393	2017
35°	3340	4442	3340	3793	3340	2066
45°	2155	3660	2155	3212	2155	1726
55°	1756	2701	1756	2637	1756	1614
65°	1220	1628	1220	1820	1220	1166
75°	462	772	462	925	462	486
85°	79	197	79	167	79	106
90°	6	23	6	23	6	8
95°	58	263	58	263	58	64
105°	206	1792	206	1792	206	219
115°	366	2307	366	2307	366	362
125°	509	1837	509	1837	509	452
135°	607	1425	607	1425	607	470
145°	704	1156	704	1156	704	441
155°	796	996	796	996	796	366
165°	859	928	859	928	859	242
175°	893	899	893	899	893	85
180°	893	893	893	893	893	

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5243.9	5243.9	5273.4	5283.3	5283.3	5268.5	5253.7	5268.5	5312.7	5327.6	5322.6
5°	5224.2	5263.6	5317.7	5327.6	5337.3	5332.4	5322.6	5332.4	5381.6	5391.5	5396.4
7.5°	5184.8	5258.7	5327.6	5342.3	5357.0	5342.3	5337.3	5347.2	5396.4	5406.2	5406.2
10°	5135.7	5239.0	5317.7	5327.6	5342.3	5327.6	5327.6	5347.2	5396.4	5406.2	5411.2
12.5°	5066.8	5209.4	5283.3	5293.1	5312.7	5307.8	5302.9	5322.6	5371.7	5381.6	5381.6
15°	4988.1	5155.4	5224.2	5234.1	5268.5	5258.7	5258.7	5278.3	5332.4	5347.2	5342.3
17.5°	4879.9	5086.5	5165.2	5180.0	5204.5	5199.7	5204.5	5224.2	5273.4	5283.3	5288.1
20°	4756.9	4993.0	5086.5	5101.2	5125.8	5125.8	5125.8	5150.4	5199.7	5219.3	5219.3
22.5°	4589.7	4894.6	4993.0	5002.9	5032.4	5032.4	5042.2	5076.6	5120.9	5125.8	5125.8
25°	4392.9	4786.4	4870.0	4899.6	4929.1	4943.8	4958.6	4978.2	4993.0	4988.1	4993.0
27.5°	4186.3	4648.7	4756.9	4776.6	4815.9	4830.7	4850.3	4855.3	4860.2	4874.9	4865.2
30°	3955.1	4456.8	4619.1	4638.8	4702.8	4712.6	4693.0	4702.8	4727.4	4737.2	4747.0
32.5°	3694.3	4171.5	4476.5	4520.8	4579.8	4550.3	4545.4	4560.1	4599.5	4599.5	4609.3
35°	3340.1	3950.1	4343.6	4383.0	4427.3	4392.9	4412.5	4417.5	4442.1	4456.8	4451.9
37.5°	2951.6	3758.3	4205.9	4235.5	4269.9	4225.6	4255.2	4269.9	4289.6	4279.7	4279.7
40°	2607.2	3458.2	4043.6	4063.3	4092.8	4058.4	4087.9	4097.7	4107.6	4097.7	4092.8
42.5°	2351.4	3128.6	3871.4	3896.1	3876.4	3900.9	3910.8	3930.5	3915.7	3896.1	3896.1
45°	2154.6	3040.0	3684.5	3714.0	3684.5	3723.9	3738.6	3738.6	3694.3	3684.5	3679.6
47.5°	2090.7	2863.0	3497.6	3497.6	3482.8	3532.0	3556.6	3522.1	3477.9	3463.1	3463.1
50°	2085.8	2666.2	3241.8	3222.1	3290.9	3350.0	3325.4	3290.9	3256.5	3202.4	3202.4
52.5°	1893.9	2425.2	2912.1	2986.0	3094.2	3128.6	3089.3	3054.9	2995.8	2971.2	2951.6
55°	1756.1	2174.3	2612.1	2759.7	2872.8	2917.1	2843.3	2808.8	2720.4	2705.5	2695.8
57.5°	1726.7	1810.3	2336.6	2523.6	2661.3	2656.4	2612.1	2548.2	2474.3	2459.6	2454.7
60°	1584.0	1308.5	2041.5	2262.8	2405.5	2390.7	2351.4	2292.4	2223.5	2213.7	2203.8
62.5°	1436.4	949.4	1707.0	1957.9	2159.5	2154.6	2120.2	2031.6	1982.5	1957.9	1938.2
65°	1220.0	796.9	1215.0	1628.3	1918.5	1928.3	1854.6	1790.6	1736.4	1707.0	1702.0
67.5°	929.8	649.3	821.5	1357.7	1687.3	1677.4	1584.0	1554.5	1485.6	1470.8	1441.3
70°	688.7	432.9	570.6	1101.9	1461.0	1436.4	1362.6	1328.2	1264.3	1229.8	1210.1
72.5°	570.6	349.2	418.1	855.9	1229.8	1200.3	1136.3	1097.0	1042.8	1013.4	993.7
75°	462.4	368.9	319.8	634.6	998.6	978.9	919.9	880.5	836.2	796.9	801.8
77.5°	339.4	344.4	255.8	467.3	792.0	762.5	728.0	678.9	659.2	619.9	619.9
80°	255.8	270.5	191.9	319.8	570.6	570.6	541.1	506.7	472.3	452.5	452.5
82.5°	172.2	172.2	142.6	201.6	388.7	373.8	354.2	344.4	324.7	314.8	314.8
85°	78.7	98.4	88.6	123.0	211.5	221.3	221.3	211.5	206.6	196.8	201.6
87.5°	24.6	44.3	54.1	68.9	108.2	113.2	118.0	118.0	118.0	123.0	123.0
90°	6.0	10.8	15.6	16.8	26.4	39.1	45.5	40.5	30.3	22.8	22.8
92.5°	23.9	64.6	105.4	115.6	162.5	225.1	256.4	224.7	161.3	113.9	109.3
95°	57.6	132.1	206.7	225.3	400.0	633.0	749.5	668.8	507.5	386.4	372.7
97.5°	99.4	165.2	231.0	247.5	538.9	927.3	1121.6	1070.6	968.6	892.2	866.1
100°	131.8	191.5	251.1	266.0	589.3	1020.5	1236.1	1239.7	1247.2	1252.8	1221.7
102.5°	159.4	215.0	270.6	284.6	612.5	1049.8	1268.4	1333.3	1463.3	1560.8	1534.1
105°	206.1	253.2	300.3	312.1	629.7	1053.1	1264.8	1410.5	1701.8	1920.3	1905.9
107.5°	254.1	298.0	342.0	352.9	633.0	1006.3	1192.9	1396.1	1802.5	2107.3	2110.8
110°	286.4	326.1	365.8	375.7	628.1	964.7	1133.1	1360.2	1814.5	2155.2	2170.1

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	318.1	355.9	393.7	403.2	628.3	928.4	1078.5	1311.0	1775.9	2124.6	2147.5
115°	366.1	401.0	435.9	444.6	634.1	886.8	1013.2	1237.1	1685.0	2020.9	2052.7
117.5°	413.4	445.1	476.7	484.7	645.8	860.8	968.2	1170.4	1574.5	1877.7	1912.9
120°	441.0	470.8	500.6	508.0	655.4	852.0	950.3	1135.0	1504.3	1781.3	1815.5
122.5°	467.9	498.1	528.1	535.7	669.3	847.4	936.4	1102.7	1435.4	1684.8	1718.5
125°	509.3	536.7	564.2	571.0	687.9	843.6	921.5	1062.8	1345.3	1557.2	1588.3
127.5°	542.8	570.5	598.3	605.1	706.4	841.4	908.9	1030.2	1272.8	1454.8	1481.0
130°	560.9	590.7	620.5	627.9	720.0	842.7	904.2	1012.1	1228.1	1390.0	1414.3
132.5°	579.4	609.2	639.1	646.5	731.0	843.6	899.9	996.6	1189.9	1334.9	1356.6
135°	607.0	634.1	661.2	668.0	742.9	842.8	892.7	973.7	1135.7	1257.1	1275.8
137.5°	635.1	662.0	689.0	695.6	761.0	848.1	891.6	960.0	1096.9	1199.5	1214.8
140°	658.4	683.2	708.0	714.2	771.9	848.8	887.3	946.4	1064.7	1153.4	1167.7
142.5°	676.5	699.3	722.3	728.0	781.1	851.9	887.3	939.3	1043.1	1121.0	1133.3
145°	704.0	723.9	743.9	748.9	793.1	851.9	881.4	923.8	1008.8	1072.5	1081.8
147.5°	731.6	751.0	770.5	775.3	810.7	857.9	881.4	914.8	981.7	1031.8	1039.5
150°	749.5	767.1	784.7	789.1	819.9	860.9	881.4	909.6	966.0	1008.3	1014.6
152.5°	768.1	781.4	794.8	798.1	825.9	862.9	881.4	905.5	953.7	989.8	994.6
155°	795.6	805.5	815.4	817.8	839.1	867.3	881.4	900.6	938.9	967.6	970.7
157.5°	816.1	825.7	835.2	837.6	852.2	871.7	881.4	896.3	926.1	948.5	950.7
160°	829.9	837.3	844.8	846.6	858.2	873.7	881.4	894.2	919.7	938.9	940.1
162.5°	843.6	849.2	854.9	856.2	864.6	875.8	881.4	892.2	913.7	929.9	931.0
165°	858.6	863.7	868.7	870.0	873.7	878.9	881.4	889.2	904.6	916.1	917.4
167.5°	872.4	874.7	877.1	877.7	880.9	885.2	887.3	892.4	902.5	910.1	910.7
170°	881.4	883.7	886.2	886.7	886.9	887.2	887.3	892.4	902.5	910.1	910.1
172.5°	886.2	886.6	887.2	887.3	887.3	887.3	887.3	891.3	899.3	905.3	904.9
175°	892.7	892.7	892.7	892.7	890.9	888.5	887.3	889.8	895.0	898.7	898.7
177.5°	892.7	892.7	892.7	892.7	891.4	889.5	888.6	890.6	894.6	897.6	897.0
180°	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5332.4	5317.7	5332.4	5322.6	5327.6	5312.7	5268.5	5253.7	5268.5	5283.3	5283.3
5°	5396.4	5386.6	5396.4	5396.4	5391.5	5381.6	5332.4	5322.6	5332.4	5337.3	5327.6
7.5°	5416.0	5401.3	5416.0	5406.2	5406.2	5396.4	5347.2	5337.3	5342.3	5357.0	5342.3
10°	5416.0	5401.3	5416.0	5411.2	5406.2	5396.4	5347.2	5327.6	5327.6	5342.3	5327.6
12.5°	5391.5	5381.6	5391.5	5381.6	5381.6	5371.7	5322.6	5302.9	5307.8	5312.7	5293.1
15°	5352.1	5337.3	5352.1	5342.3	5347.2	5332.4	5278.3	5258.7	5258.7	5268.5	5234.1
17.5°	5293.1	5273.4	5293.1	5288.1	5283.3	5273.4	5224.2	5204.5	5199.7	5204.5	5180.0
20°	5224.2	5209.4	5224.2	5219.3	5219.3	5199.7	5150.4	5125.8	5125.8	5125.8	5101.2
22.5°	5116.0	5101.2	5116.0	5125.8	5125.8	5120.9	5076.6	5042.2	5032.4	5032.4	5002.9
25°	4993.0	4978.2	4993.0	4993.0	4988.1	4993.0	4978.2	4958.6	4943.8	4929.1	4899.6
27.5°	4874.9	4865.2	4874.9	4865.2	4874.9	4860.2	4855.3	4850.3	4830.7	4815.9	4776.6
30°	4756.9	4747.0	4756.9	4747.0	4737.2	4727.4	4702.8	4693.0	4712.6	4702.8	4638.8
32.5°	4609.3	4599.5	4609.3	4609.3	4599.5	4599.5	4560.1	4545.4	4550.3	4579.8	4520.8
35°	4456.8	4442.1	4456.8	4451.9	4456.8	4442.1	4417.5	4412.5	4392.9	4427.3	4383.0
37.5°	4279.7	4265.0	4279.7	4279.7	4279.7	4289.6	4269.9	4255.2	4225.6	4269.9	4235.5
40°	4097.7	4078.0	4097.7	4092.8	4097.7	4107.6	4097.7	4087.9	4058.4	4092.8	4063.3
42.5°	3891.1	3886.2	3891.1	3896.1	3896.1	3915.7	3930.5	3910.8	3900.9	3876.4	3896.1
45°	3669.7	3659.9	3669.7	3679.6	3684.5	3694.3	3738.6	3738.6	3723.9	3684.5	3714.0
47.5°	3433.7	3409.0	3433.7	3463.1	3463.1	3477.9	3522.1	3556.6	3532.0	3482.8	3497.6
50°	3182.8	3187.6	3182.8	3202.4	3202.4	3256.5	3290.9	3325.4	3350.0	3290.9	3222.1
52.5°	2936.7	2931.9	2936.7	2951.6	2971.2	2995.8	3054.9	3089.3	3128.6	3094.2	2986.0
55°	2690.8	2700.7	2690.8	2695.8	2705.5	2720.4	2808.8	2843.3	2917.1	2872.8	2759.7
57.5°	2444.9	2430.1	2444.9	2454.7	2459.6	2474.3	2548.2	2612.1	2656.4	2661.3	2523.6
60°	2159.5	2139.8	2159.5	2203.8	2213.7	2223.5	2292.4	2351.4	2390.7	2405.5	2262.8
62.5°	1908.6	1874.2	1908.6	1938.2	1957.9	1982.5	2031.6	2120.2	2154.6	2159.5	1957.9
65°	1643.0	1628.3	1643.0	1702.0	1707.0	1736.4	1790.6	1854.6	1928.3	1918.5	1628.3
67.5°	1401.9	1401.9	1401.9	1441.3	1470.8	1485.6	1554.5	1584.0	1677.4	1687.3	1357.7
70°	1180.6	1175.7	1180.6	1210.1	1229.8	1264.3	1328.2	1362.6	1436.4	1461.0	1101.9
72.5°	969.1	964.2	969.1	993.7	1013.4	1042.8	1097.0	1136.3	1200.3	1229.8	855.9
75°	782.2	772.3	782.2	801.8	796.9	836.2	880.5	919.9	978.9	998.6	634.6
77.5°	600.1	600.1	600.1	619.9	619.9	659.2	678.9	728.0	762.5	792.0	467.3
80°	447.7	442.7	447.7	452.5	452.5	472.3	506.7	541.1	570.6	570.6	319.8
82.5°	314.8	304.9	314.8	314.8	314.8	324.7	344.4	354.2	373.8	388.7	201.6
85°	196.8	196.8	196.8	201.6	196.8	206.6	211.5	221.3	221.3	211.5	123.0
87.5°	127.9	123.0	127.9	123.0	123.0	118.0	118.0	118.0	113.2	108.2	68.9
90°	22.8	22.8	22.8	22.8	22.8	30.3	40.5	45.5	39.1	26.4	16.8
92.5°	91.2	73.1	91.2	109.3	113.9	161.3	224.7	256.4	225.1	162.5	115.6
95°	317.8	263.0	317.8	372.7	386.4	507.5	668.8	749.5	633.0	400.0	225.3
97.5°	761.6	657.3	761.6	866.1	892.2	968.6	1070.6	1121.6	927.3	538.9	247.5
100°	1097.4	973.1	1097.4	1221.7	1252.8	1247.2	1239.7	1236.1	1020.5	589.3	266.0
102.5°	1427.6	1321.1	1427.6	1534.1	1560.8	1463.3	1333.3	1268.4	1049.8	612.5	284.6
105°	1848.8	1791.5	1848.8	1905.9	1920.3	1701.8	1410.5	1264.8	1053.1	629.7	312.1
107.5°	2124.5	2138.4	2124.5	2110.8	2107.3	1802.5	1396.1	1192.9	1006.3	633.0	352.9
110°	2229.7	2289.4	2229.7	2170.1	2155.2	1814.5	1360.2	1133.1	964.7	628.1	375.7

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	2239.2	2330.7	2239.2	2147.5	2124.6	1775.9	1311.0	1078.5	928.4	628.3	403.2
115°	2179.8	2306.8	2179.8	2052.7	2020.9	1685.0	1237.1	1013.2	886.8	634.1	444.6
117.5°	2053.8	2194.7	2053.8	1912.9	1877.7	1574.5	1170.4	968.2	860.8	645.8	484.7
120°	1952.4	2089.3	1952.4	1815.5	1781.3	1504.3	1135.0	950.3	852.0	655.4	508.0
122.5°	1853.6	1988.6	1853.6	1718.5	1684.8	1435.4	1102.7	936.4	847.4	669.3	535.7
125°	1712.6	1837.0	1712.6	1588.3	1557.2	1345.3	1062.8	921.5	843.6	687.9	571.0
127.5°	1585.9	1690.8	1585.9	1481.0	1454.8	1272.8	1030.2	908.9	841.4	706.4	605.1
130°	1511.3	1608.2	1511.3	1414.3	1390.0	1228.1	1012.1	904.2	842.7	720.0	627.9
132.5°	1443.4	1530.2	1443.4	1356.6	1334.9	1189.9	996.6	899.9	843.6	731.0	646.5
135°	1350.6	1425.4	1350.6	1275.8	1257.1	1135.7	973.7	892.7	842.8	742.9	668.0
137.5°	1276.1	1337.3	1276.1	1214.8	1199.5	1096.9	960.0	891.6	848.1	761.0	695.6
140°	1224.9	1282.2	1224.9	1167.7	1153.4	1064.7	946.4	887.3	848.8	771.9	714.2
142.5°	1182.7	1231.9	1182.7	1133.3	1121.0	1043.1	939.3	887.3	851.9	781.1	728.0
145°	1119.1	1156.4	1119.1	1081.8	1072.5	1008.8	923.8	881.4	851.9	793.1	748.9
147.5°	1070.4	1101.3	1070.4	1039.5	1031.8	981.7	914.8	881.4	857.9	810.7	775.3
150°	1039.6	1064.7	1039.6	1014.6	1008.3	966.0	909.6	881.4	860.9	819.9	789.1
152.5°	1013.5	1032.4	1013.5	994.6	989.8	953.7	905.5	881.4	862.9	825.9	798.1
155°	983.3	995.8	983.3	970.7	967.6	938.9	900.6	881.4	867.3	839.1	817.8
157.5°	959.4	968.2	959.4	950.7	948.5	926.1	896.3	881.4	871.7	852.2	837.6
160°	945.3	950.3	945.3	940.1	938.9	919.7	894.2	881.4	873.7	858.2	846.6
162.5°	935.9	940.7	935.9	931.0	929.9	913.7	892.2	881.4	875.8	864.6	856.2
165°	922.5	927.5	922.5	917.4	916.1	904.6	889.2	881.4	878.9	873.7	870.0
167.5°	912.8	914.9	912.8	910.7	910.1	902.5	892.4	887.3	885.2	880.9	877.7
170°	910.1	910.1	910.1	910.1	910.1	902.5	892.4	887.3	887.2	886.9	886.7
172.5°	903.0	901.2	903.0	904.9	905.3	899.3	891.3	887.3	887.3	887.3	887.3
175°	898.7	898.7	898.7	898.7	898.7	895.0	889.8	887.3	888.5	890.9	892.7
177.5°	894.9	892.7	894.9	897.0	897.6	894.6	890.6	888.6	889.5	891.4	892.7
180°	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5273.4	5243.9	5243.9	5194.7	5175.0	5160.3	5135.7	5061.9	5042.2	5022.5	5052.1
5°	5317.7	5263.6	5224.2	5135.7	5061.9	5032.4	4938.9	4761.8	4643.7	4555.2	4506.0
7.5°	5327.6	5258.7	5184.8	5047.1	4870.0	4791.3	4506.0	4181.3	4092.8	4014.1	3964.9
10°	5317.7	5239.0	5135.7	4929.1	4510.9	4373.2	4087.9	3876.4	3822.2	3807.5	3822.2
12.5°	5283.3	5209.4	5066.8	4722.4	4137.0	4043.6	3876.4	3753.3	3743.5	3768.2	3900.9
15°	5224.2	5155.4	4988.1	4446.9	3930.5	3861.6	3743.5	3699.3	3753.3	3925.5	4324.0
17.5°	5165.2	5086.5	4879.9	4176.4	3773.1	3723.9	3640.2	3728.8	4033.8	4265.0	4397.8
20°	5086.5	4993.0	4756.9	3979.7	3659.9	3615.6	3576.3	3974.7	4205.9	4289.6	4363.3
22.5°	4993.0	4894.6	4589.7	3841.9	3541.9	3507.4	3532.0	4112.4	4205.9	4265.0	4328.9
25°	4870.0	4786.4	4392.9	3733.7	3448.4	3409.0	3502.5	4097.7	4151.8	4166.6	4294.5
27.5°	4756.9	4648.7	4186.3	3635.3	3335.2	3320.5	3527.1	4033.8	4073.1	4087.9	4225.6
30°	4619.1	4456.8	3955.1	3532.0	3217.2	3212.2	3532.0	3955.1	3945.2	3984.5	4122.3
32.5°	4476.5	4171.5	3694.3	3404.1	3104.0	3099.2	3497.6	3836.9	3827.2	3881.2	3984.5
35°	4343.6	3950.1	3340.1	3256.5	2961.4	2966.3	3414.0	3699.3	3704.2	3753.3	3817.3
37.5°	4205.9	3758.3	2951.6	3094.2	2823.7	2823.7	3300.8	3571.3	3561.6	3576.3	3664.9
40°	4043.6	3458.2	2607.2	2882.7	2695.8	2680.9	3163.1	3433.7	3399.2	3394.3	3517.3
42.5°	3871.4	3128.6	2351.4	2602.2	2548.2	2528.5	2995.8	3266.4	3202.4	3217.2	3374.5
45°	3684.5	3040.0	2154.6	2198.9	2395.7	2380.9	2813.8	3074.5	3030.3	3069.6	3231.9
47.5°	3497.6	2863.0	2090.7	1825.0	2233.4	2228.4	2612.1	2887.6	2863.0	2902.3	3074.5
50°	3241.8	2666.2	2085.8	1564.4	2051.3	2070.9	2371.0	2705.5	2705.5	2740.0	2922.0
52.5°	2912.1	2425.2	1893.9	1416.8	1839.7	1898.9	2159.5	2548.2	2558.0	2592.5	2754.8
55°	2612.1	2174.3	1756.1	1303.6	1588.9	1716.8	1952.9	2385.8	2405.5	2439.9	2587.5
57.5°	2336.6	1810.3	1726.7	1170.7	1357.7	1480.7	1770.9	2228.4	2238.3	2267.8	2410.4
60°	2041.5	1308.5	1584.0	1028.1	1156.0	1249.5	1603.7	2041.5	2075.9	2095.6	2218.5
62.5°	1707.0	949.4	1436.4	929.8	1057.7	1077.3	1465.9	1864.4	1908.6	1923.4	1997.2
65°	1215.0	796.9	1220.0	846.1	954.4	959.2	1318.3	1682.4	1721.7	1746.3	1800.4
67.5°	821.5	649.3	929.8	767.4	875.6	880.5	1175.7	1470.8	1524.9	1544.7	1579.1
70°	570.6	432.9	688.7	683.7	787.1	796.9	1023.2	1279.0	1328.2	1342.9	1362.6
72.5°	418.1	349.2	570.6	614.9	693.6	703.5	865.8	1062.5	1111.7	1126.5	1136.3
75°	319.8	368.9	462.4	536.1	590.3	595.3	708.3	865.8	900.2	910.1	914.9
77.5°	255.8	344.4	339.4	432.9	482.1	472.3	555.9	669.0	698.6	698.6	698.6
80°	191.9	270.5	255.8	309.9	354.2	344.4	398.5	477.1	487.0	496.8	492.0
82.5°	142.6	172.2	172.2	196.8	236.1	226.3	265.6	309.9	309.9	309.9	319.8
85°	88.6	98.4	78.7	103.3	132.8	127.9	147.6	167.2	172.2	172.2	162.3
87.5°	54.1	44.3	24.6	39.3	59.0	59.0	68.9	73.7	68.9	68.9	68.9
90°	15.6	10.8	6.0	10.8	15.6	16.8	26.4	39.1	45.5	40.5	30.3
92.5°	105.4	64.6	23.9	64.6	105.4	115.6	162.5	225.1	256.4	224.7	161.3
95°	206.7	132.1	57.6	132.1	206.7	225.3	400.0	633.0	749.5	668.8	507.5
97.5°	231.0	165.2	99.4	165.2	231.0	247.5	538.9	927.3	1121.6	1070.6	968.6
100°	251.1	191.5	131.8	191.5	251.1	266.0	589.3	1020.5	1236.1	1239.7	1247.2
102.5°	270.6	215.0	159.4	215.0	270.6	284.6	612.5	1049.8	1268.4	1333.3	1463.3
105°	300.3	253.2	206.1	253.2	300.3	312.1	629.7	1053.1	1264.8	1410.5	1701.8
107.5°	342.0	298.0	254.1	298.0	342.0	352.9	633.0	1006.3	1192.9	1396.1	1802.5
110°	365.8	326.1	286.4	326.1	365.8	375.7	628.1	964.7	1133.1	1360.2	1814.5

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	393.7	355.9	318.1	355.9	393.7	403.2	628.3	928.4	1078.5	1311.0	1775.9
115°	435.9	401.0	366.1	401.0	435.9	444.6	634.1	886.8	1013.2	1237.1	1685.0
117.5°	476.7	445.1	413.4	445.1	476.7	484.7	645.8	860.8	968.2	1170.4	1574.5
120°	500.6	470.8	441.0	470.8	500.6	508.0	655.4	852.0	950.3	1135.0	1504.3
122.5°	528.1	498.1	467.9	498.1	528.1	535.7	669.3	847.4	936.4	1102.7	1435.4
125°	564.2	536.7	509.3	536.7	564.2	571.0	687.9	843.6	921.5	1062.8	1345.3
127.5°	598.3	570.5	542.8	570.5	598.3	605.1	706.4	841.4	908.9	1030.2	1272.8
130°	620.5	590.7	560.9	590.7	620.5	627.9	720.0	842.7	904.2	1012.1	1228.1
132.5°	639.1	609.2	579.4	609.2	639.1	646.5	731.0	843.6	899.9	996.6	1189.9
135°	661.2	634.1	607.0	634.1	661.2	668.0	742.9	842.8	892.7	973.7	1135.7
137.5°	689.0	662.0	635.1	662.0	689.0	695.6	761.0	848.1	891.6	960.0	1096.9
140°	708.0	683.2	658.4	683.2	708.0	714.2	771.9	848.8	887.3	946.4	1064.7
142.5°	722.3	699.3	676.5	699.3	722.3	728.0	781.1	851.9	887.3	939.3	1043.1
145°	743.9	723.9	704.0	723.9	743.9	748.9	793.1	851.9	881.4	923.8	1008.8
147.5°	770.5	751.0	731.6	751.0	770.5	775.3	810.7	857.9	881.4	914.8	981.7
150°	784.7	767.1	749.5	767.1	784.7	789.1	819.9	860.9	881.4	909.6	966.0
152.5°	794.8	781.4	768.1	781.4	794.8	798.1	825.9	862.9	881.4	905.5	953.7
155°	815.4	805.5	795.6	805.5	815.4	817.8	839.1	867.3	881.4	900.6	938.9
157.5°	835.2	825.7	816.1	825.7	835.2	837.6	852.2	871.7	881.4	896.3	926.1
160°	844.8	837.3	829.9	837.3	844.8	846.6	858.2	873.7	881.4	894.2	919.7
162.5°	854.9	849.2	843.6	849.2	854.9	856.2	864.6	875.8	881.4	892.2	913.7
165°	868.7	863.7	858.6	863.7	868.7	870.0	873.7	878.9	881.4	889.2	904.6
167.5°	877.1	874.7	872.4	874.7	877.1	877.7	880.9	885.2	887.3	892.4	902.5
170°	886.2	883.7	881.4	883.7	886.2	886.7	886.9	887.2	887.3	892.4	902.5
172.5°	887.2	886.6	886.2	886.6	887.2	887.3	887.3	887.3	887.3	891.3	899.3
175°	892.7	892.7	892.7	892.7	892.7	892.7	890.9	888.5	887.3	889.8	895.0
177.5°	892.7	892.7	892.7	892.7	892.7	892.7	891.4	889.5	888.6	890.6	894.6
180°	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5017.6	5002.9	5022.5	4968.5	5022.5	5002.9	5017.6	5052.1	5022.5	5042.2	5061.9
5°	4402.7	4378.1	4299.4	4235.5	4299.4	4378.1	4402.7	4506.0	4555.2	4643.7	4761.8
7.5°	3935.4	3915.7	3896.1	3856.7	3896.1	3915.7	3935.4	3964.9	4014.1	4092.8	4181.3
10°	3832.1	3836.9	3866.5	3861.6	3866.5	3836.9	3832.1	3822.2	3807.5	3822.2	3876.4
12.5°	4097.7	4142.0	4304.3	4294.5	4304.3	4142.0	4097.7	3900.9	3768.2	3743.5	3753.3
15°	4402.7	4417.5	4451.9	4456.8	4451.9	4417.5	4402.7	4324.0	3925.5	3753.3	3699.3
17.5°	4432.2	4437.1	4461.8	4461.8	4461.8	4437.1	4432.2	4397.8	4265.0	4033.8	3728.8
20°	4407.6	4417.5	4466.7	4476.5	4466.7	4417.5	4407.6	4363.3	4289.6	4205.9	3974.7
22.5°	4397.8	4417.5	4456.8	4451.9	4456.8	4417.5	4397.8	4328.9	4265.0	4205.9	4112.4
25°	4348.6	4348.6	4353.5	4358.5	4353.5	4348.6	4348.6	4294.5	4166.6	4151.8	4097.7
27.5°	4245.3	4255.2	4284.6	4279.7	4284.6	4255.2	4245.3	4225.6	4087.9	4073.1	4033.8
30°	4151.8	4142.0	4117.4	4097.7	4117.4	4142.0	4151.8	4122.3	3984.5	3945.2	3955.1
32.5°	3994.4	3969.8	3945.2	3930.5	3945.2	3969.8	3994.4	3984.5	3881.2	3827.2	3836.9
35°	3807.5	3812.4	3807.5	3792.8	3807.5	3812.4	3807.5	3817.3	3753.3	3704.2	3699.3
37.5°	3674.6	3684.5	3679.6	3659.9	3679.6	3684.5	3674.6	3664.9	3576.3	3561.6	3571.3
40°	3536.9	3541.9	3536.9	3522.1	3536.9	3541.9	3536.9	3517.3	3394.3	3399.2	3433.7
42.5°	3404.1	3399.2	3384.4	3374.5	3384.4	3399.2	3404.1	3374.5	3217.2	3202.4	3266.4
45°	3251.6	3256.5	3227.0	3212.2	3227.0	3256.5	3251.6	3231.9	3069.6	3030.3	3074.5
47.5°	3099.2	3099.2	3074.5	3059.7	3074.5	3099.2	3099.2	3074.5	2902.3	2863.0	2887.6
50°	2936.7	2931.9	2897.4	2892.5	2897.4	2931.9	2936.7	2922.0	2740.0	2705.5	2705.5
52.5°	2749.8	2749.8	2754.8	2764.6	2754.8	2749.8	2749.8	2754.8	2592.5	2558.0	2548.2
55°	2587.5	2592.5	2626.9	2636.7	2626.9	2592.5	2587.5	2587.5	2439.9	2405.5	2385.8
57.5°	2420.3	2420.3	2444.9	2444.9	2444.9	2420.3	2420.3	2410.4	2267.8	2238.3	2228.4
60°	2228.4	2238.3	2258.0	2253.0	2258.0	2238.3	2228.4	2218.5	2095.6	2075.9	2041.5
62.5°	2026.8	2036.5	2041.5	2031.6	2041.5	2036.5	2026.8	1997.2	1923.4	1908.6	1864.4
65°	1815.2	1825.0	1830.0	1820.1	1830.0	1825.0	1815.2	1800.4	1746.3	1721.7	1682.4
67.5°	1598.8	1593.8	1588.9	1608.5	1588.9	1593.8	1598.8	1579.1	1544.7	1524.9	1470.8
70°	1377.3	1377.3	1372.5	1382.3	1372.5	1377.3	1377.3	1362.6	1342.9	1328.2	1279.0
72.5°	1141.3	1136.3	1156.0	1141.3	1156.0	1136.3	1141.3	1136.3	1126.5	1111.7	1062.5
75°	910.1	919.9	910.1	924.8	910.1	919.9	910.1	914.9	910.1	900.2	865.8
77.5°	693.6	703.5	693.6	693.6	693.6	703.5	693.6	698.6	698.6	698.6	669.0
80°	492.0	487.0	487.0	482.1	487.0	487.0	492.0	492.0	496.8	487.0	477.1
82.5°	314.8	309.9	309.9	319.8	309.9	309.9	314.8	319.8	309.9	309.9	309.9
85°	172.2	177.1	167.2	167.2	167.2	177.1	172.2	162.3	172.2	172.2	167.2
87.5°	64.0	59.0	59.0	59.0	59.0	59.0	64.0	68.9	68.9	68.9	73.7
90°	22.8	22.8	22.8	22.8	22.8	22.8	22.8	30.3	40.5	45.5	39.1
92.5°	113.9	109.3	91.2	73.1	91.2	109.3	113.9	161.3	224.7	256.4	225.1
95°	386.4	372.7	317.8	263.0	317.8	372.7	386.4	507.5	668.8	749.5	633.0
97.5°	892.2	866.1	761.6	657.3	761.6	866.1	892.2	968.6	1070.6	1121.6	927.3
100°	1252.8	1221.7	1097.4	973.1	1097.4	1221.7	1252.8	1247.2	1239.7	1236.1	1020.5
102.5°	1560.8	1534.1	1427.6	1321.1	1427.6	1534.1	1560.8	1463.3	1333.3	1268.4	1049.8
105°	1920.3	1905.9	1848.8	1791.5	1848.8	1905.9	1920.3	1701.8	1410.5	1264.8	1053.1
107.5°	2107.3	2110.8	2124.5	2138.4	2124.5	2110.8	2107.3	1802.5	1396.1	1192.9	1006.3
110°	2155.2	2170.1	2229.7	2289.4	2229.7	2170.1	2155.2	1814.5	1360.2	1133.1	964.7

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	2124.6	2147.5	2239.2	2330.7	2239.2	2147.5	2124.6	1775.9	1311.0	1078.5	928.4
115°	2020.9	2052.7	2179.8	2306.8	2179.8	2052.7	2020.9	1685.0	1237.1	1013.2	886.8
117.5°	1877.7	1912.9	2053.8	2194.7	2053.8	1912.9	1877.7	1574.5	1170.4	968.2	860.8
120°	1781.3	1815.5	1952.4	2089.3	1952.4	1815.5	1781.3	1504.3	1135.0	950.3	852.0
122.5°	1684.8	1718.5	1853.6	1988.6	1853.6	1718.5	1684.8	1435.4	1102.7	936.4	847.4
125°	1557.2	1588.3	1712.6	1837.0	1712.6	1588.3	1557.2	1345.3	1062.8	921.5	843.6
127.5°	1454.8	1481.0	1585.9	1690.8	1585.9	1481.0	1454.8	1272.8	1030.2	908.9	841.4
130°	1390.0	1414.3	1511.3	1608.2	1511.3	1414.3	1390.0	1228.1	1012.1	904.2	842.7
132.5°	1334.9	1356.6	1443.4	1530.2	1443.4	1356.6	1334.9	1189.9	996.6	899.9	843.6
135°	1257.1	1275.8	1350.6	1425.4	1350.6	1275.8	1257.1	1135.7	973.7	892.7	842.8
137.5°	1199.5	1214.8	1276.1	1337.3	1276.1	1214.8	1199.5	1096.9	960.0	891.6	848.1
140°	1153.4	1167.7	1224.9	1282.2	1224.9	1167.7	1153.4	1064.7	946.4	887.3	848.8
142.5°	1121.0	1133.3	1182.7	1231.9	1182.7	1133.3	1121.0	1043.1	939.3	887.3	851.9
145°	1072.5	1081.8	1119.1	1156.4	1119.1	1081.8	1072.5	1008.8	923.8	881.4	851.9
147.5°	1031.8	1039.5	1070.4	1101.3	1070.4	1039.5	1031.8	981.7	914.8	881.4	857.9
150°	1008.3	1014.6	1039.6	1064.7	1039.6	1014.6	1008.3	966.0	909.6	881.4	860.9
152.5°	989.8	994.6	1013.5	1032.4	1013.5	994.6	989.8	953.7	905.5	881.4	862.9
155°	967.6	970.7	983.3	995.8	983.3	970.7	967.6	938.9	900.6	881.4	867.3
157.5°	948.5	950.7	959.4	968.2	959.4	950.7	948.5	926.1	896.3	881.4	871.7
160°	938.9	940.1	945.3	950.3	945.3	940.1	938.9	919.7	894.2	881.4	873.7
162.5°	929.9	931.0	935.9	940.7	935.9	931.0	929.9	913.7	892.2	881.4	875.8
165°	916.1	917.4	922.5	927.5	922.5	917.4	916.1	904.6	889.2	881.4	878.9
167.5°	910.1	910.7	912.8	914.9	912.8	910.7	910.1	902.5	892.4	887.3	885.2
170°	910.1	910.1	910.1	910.1	910.1	910.1	910.1	902.5	892.4	887.3	887.2
172.5°	905.3	904.9	903.0	901.2	903.0	904.9	905.3	899.3	891.3	887.3	887.3
175°	898.7	898.7	898.7	898.7	898.7	898.7	898.7	895.0	889.8	887.3	888.5
177.5°	897.6	897.0	894.9	892.7	894.9	897.0	897.6	894.6	890.6	888.6	889.5
180°	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	5199.7	5199.7	5199.7	5199.7	5199.7
2.5°	5135.7	5160.3	5175.0	5194.7	5243.9
5°	4938.9	5032.4	5061.9	5135.7	5224.2
7.5°	4506.0	4791.3	4870.0	5047.1	5184.8
10°	4087.9	4373.2	4510.9	4929.1	5135.7
12.5°	3876.4	4043.6	4137.0	4722.4	5066.8
15°	3743.5	3861.6	3930.5	4446.9	4988.1
17.5°	3640.2	3723.9	3773.1	4176.4	4879.9
20°	3576.3	3615.6	3659.9	3979.7	4756.9
22.5°	3532.0	3507.4	3541.9	3841.9	4589.7
25°	3502.5	3409.0	3448.4	3733.7	4392.9
27.5°	3527.1	3320.5	3335.2	3635.3	4186.3
30°	3532.0	3212.2	3217.2	3532.0	3955.1
32.5°	3497.6	3099.2	3104.0	3404.1	3694.3
35°	3414.0	2966.3	2961.4	3256.5	3340.1
37.5°	3300.8	2823.7	2823.7	3094.2	2951.6
40°	3163.1	2680.9	2695.8	2882.7	2607.2
42.5°	2995.8	2528.5	2548.2	2602.2	2351.4
45°	2813.8	2380.9	2395.7	2198.9	2154.6
47.5°	2612.1	2228.4	2233.4	1825.0	2090.7
50°	2371.0	2070.9	2051.3	1564.4	2085.8
52.5°	2159.5	1898.9	1839.7	1416.8	1893.9
55°	1952.9	1716.8	1588.9	1303.6	1756.1
57.5°	1770.9	1480.7	1357.7	1170.7	1726.7
60°	1603.7	1249.5	1156.0	1028.1	1584.0
62.5°	1465.9	1077.3	1057.7	929.8	1436.4
65°	1318.3	959.2	954.4	846.1	1220.0
67.5°	1175.7	880.5	875.6	767.4	929.8
70°	1023.2	796.9	787.1	683.7	688.7
72.5°	865.8	703.5	693.6	614.9	570.6
75°	708.3	595.3	590.3	536.1	462.4
77.5°	555.9	472.3	482.1	432.9	339.4
80°	398.5	344.4	354.2	309.9	255.8
82.5°	265.6	226.3	236.1	196.8	172.2
85°	147.6	127.9	132.8	103.3	78.7
87.5°	68.9	59.0	59.0	39.3	24.6
90°	26.4	16.8	15.6	10.8	6.0
92.5°	162.5	115.6	105.4	64.6	23.9
95°	400.0	225.3	206.7	132.1	57.6
97.5°	538.9	247.5	231.0	165.2	99.4
100°	589.3	266.0	251.1	191.5	131.8
102.5°	612.5	284.6	270.6	215.0	159.4
105°	629.7	312.1	300.3	253.2	206.1
107.5°	633.0	352.9	342.0	298.0	254.1
110°	628.1	375.7	365.8	326.1	286.4

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	628.3	403.2	393.7	355.9	318.1
115°	634.1	444.6	435.9	401.0	366.1
117.5°	645.8	484.7	476.7	445.1	413.4
120°	655.4	508.0	500.6	470.8	441.0
122.5°	669.3	535.7	528.1	498.1	467.9
125°	687.9	571.0	564.2	536.7	509.3
127.5°	706.4	605.1	598.3	570.5	542.8
130°	720.0	627.9	620.5	590.7	560.9
132.5°	731.0	646.5	639.1	609.2	579.4
135°	742.9	668.0	661.2	634.1	607.0
137.5°	761.0	695.6	689.0	662.0	635.1
140°	771.9	714.2	708.0	683.2	658.4
142.5°	781.1	728.0	722.3	699.3	676.5
145°	793.1	748.9	743.9	723.9	704.0
147.5°	810.7	775.3	770.5	751.0	731.6
150°	819.9	789.1	784.7	767.1	749.5
152.5°	825.9	798.1	794.8	781.4	768.1
155°	839.1	817.8	815.4	805.5	795.6
157.5°	852.2	837.6	835.2	825.7	816.1
160°	858.2	846.6	844.8	837.3	829.9
162.5°	864.6	856.2	854.9	849.2	843.6
165°	873.7	870.0	868.7	863.7	858.6
167.5°	880.9	877.7	877.1	874.7	872.4
170°	886.9	886.7	886.2	883.7	881.4
172.5°	887.3	887.3	887.2	886.6	886.2
175°	890.9	892.7	892.7	892.7	892.7
177.5°	891.4	892.7	892.7	892.7	892.7
180°	892.7	892.7	892.7	892.7	892.7

TEST NUMBER: P934579

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.13	17.20	16.89	17.99	18.95	18.98	20.06	19.75	20.84	21.80
	3H	16.62	17.59	17.40	18.38	19.37	20.35	21.31	21.13	22.11	23.10
	4H	16.82	17.73	17.62	18.54	19.53	20.81	21.72	21.60	22.52	23.52
	6H	16.95	17.79	17.76	18.61	19.62	21.11	21.95	21.92	22.76	23.77
	8H	16.96	17.76	17.78	18.59	19.60	21.19	21.99	22.01	22.83	23.84
	12H	16.94	17.70	17.76	18.53	19.56	21.24	22.00	22.07	22.83	23.87
4H	2H	17.19	18.10	17.99	18.91	19.90	19.42	20.33	20.21	21.13	22.13
	3H	18.24	19.00	19.05	19.84	20.85	20.95	21.71	21.76	22.55	23.56
	4H	18.53	19.22	19.35	20.05	21.09	21.49	22.18	22.31	23.02	24.06
	6H	18.66	19.26	19.50	20.12	21.17	21.87	22.47	22.71	23.33	24.38
	8H	18.67	19.23	19.52	20.09	21.15	21.99	22.54	22.83	23.40	24.46
	12H	18.65	19.15	19.52	20.03	21.09	22.06	22.56	22.92	23.44	24.50
8H	4H	19.00	19.56	19.85	20.41	21.47	21.63	22.19	22.48	23.04	24.10
	6H	19.27	19.73	20.14	20.63	21.69	22.08	22.54	22.95	23.44	24.50
	8H	19.31	19.72	20.20	20.62	21.69	22.24	22.65	23.12	23.54	24.62
	12H	19.31	19.67	20.20	20.55	21.68	22.35	22.71	23.24	23.60	24.73
12H	4H	19.02	19.52	19.88	20.40	21.46	21.60	22.11	22.47	22.98	24.05
	6H	19.33	19.74	20.22	20.64	21.71	22.08	22.49	22.96	23.38	24.46
	8H	19.41	19.77	20.30	20.66	21.79	22.25	22.62	23.14	23.50	24.63

END OF REPORT