

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934984

Luminaire Tested: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934984
REPORT IS A COMBINATION OF REPORTS P933718 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7397.4 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66
1	100	96	92	88	94	90	86	83	79	76	74	68	66	65	59	57	56	56	56	51
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	49	47	47	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	40	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	35	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	30	30	27
6	65	52	44	38	60	49	42	36	44	37	33	38	33	30	33	29	26	26	26	24
7	60	47	39	33	56	45	37	32	39	33	29	35	30	26	30	26	23	23	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	21	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	19	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16084	16084	16084	16084
5°	16186	16237	16186	12766
10°	16060	15994	16060	11434
15°	15868	15647	15868	13065
20°	15518	15236	15518	13093
25°	14820	14637	14820	12815
30°	13925	14141	13925	12206
35°	12397	13512	12397	11537
40°	10311	12771	10311	11030
45°	9195	11906	9195	10449
50°	9747	10872	9747	9866
55°	9146	9759	9146	9528
60°	9392	8289	9392	8727
65°	8475	6851	8475	7659
70°	5829	5461	5829	6420
75°	5057	4037	5057	4833
80°	3992	2669	3992	2905
85°	2178	1413	2178	1200

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14120 cd/sqm

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.5	2.1
10°-20°	444.2	6.0
20°-30°	686.7	9.3
30°-40°	819.8	11.1
40°-50°	824.6	11.1
50°-60°	717.5	9.7
60°-70°	508.7	6.9
70°-80°	269.2	3.6
80°-90°	68.7	0.9
90°-100°	218.2	2.9
100°-110°	573.6	7.8
110°-120°	594.7	8.0
120°-130°	477.1	6.4
130°-140°	374.3	5.1
140°-150°	287.3	3.9
150°-160°	206.9	2.8
160°-170°	126.6	1.7
170°-180°	42.8	0.6
0°-30°	1287.4	17.4
0°-40°	2107.2	28.5
0°-60°	3649.3	49.3
0°-90°	4495.9	60.8
90°-120°	1386.5	18.7
90°-150°	2525.2	34.1
90°-180°	2901.0	39.2
0°-180°	7397.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1733	1733	1733	1733	1733	
5°	1742	1796	1742	1412	1742	165
15°	1663	1779	1663	1486	1663	468
25°	1464	1660	1464	1453	1464	672
35°	1114	1481	1114	1264	1114	689
45°	718	1220	718	1071	718	575
55°	586	900	586	879	586	538
65°	407	543	407	607	407	389
75°	154	258	154	308	154	162
85°	26	66	26	56	26	35
90°	3	11	3	11	3	4
95°	29	132	29	132	29	32
105°	103	898	103	898	103	110
115°	184	1156	184	1156	184	181
125°	255	921	255	921	255	227
135°	304	715	304	715	304	235
145°	353	580	353	580	353	221
155°	399	499	399	499	399	183
165°	430	465	430	465	430	121
175°	448	451	448	451	448	42
180°	448	448	448	448	448	

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3
2.5°	1748.1	1748.1	1758.0	1761.3	1761.3	1756.3	1751.4	1756.3	1771.0	1776.0	1774.3
5°	1741.5	1754.7	1772.7	1776.0	1779.3	1777.6	1774.3	1777.6	1794.0	1797.3	1798.9
7.5°	1728.4	1753.0	1776.0	1780.9	1785.8	1780.9	1779.3	1782.6	1798.9	1802.2	1802.2
10°	1712.0	1746.4	1772.7	1776.0	1780.9	1776.0	1776.0	1782.6	1798.9	1802.2	1803.9
12.5°	1689.1	1736.6	1761.3	1764.5	1771.0	1769.4	1767.7	1774.3	1790.7	1794.0	1794.0
15°	1662.8	1718.6	1741.5	1744.8	1756.3	1753.0	1753.0	1759.6	1777.6	1782.6	1780.9
17.5°	1626.8	1695.7	1721.8	1726.8	1735.0	1733.3	1735.0	1741.5	1758.0	1761.3	1762.8
20°	1585.8	1664.5	1695.7	1700.5	1708.7	1708.7	1708.7	1717.0	1733.3	1739.9	1739.9
22.5°	1530.0	1631.7	1664.5	1667.7	1677.5	1677.5	1680.8	1692.4	1707.1	1708.7	1708.7
25°	1464.4	1595.6	1623.5	1633.3	1643.1	1648.1	1653.0	1659.5	1664.5	1662.8	1664.5
27.5°	1395.6	1549.6	1585.8	1592.3	1605.4	1610.4	1616.9	1618.5	1620.2	1625.1	1621.8
30°	1318.4	1485.7	1539.8	1546.4	1567.7	1570.9	1564.5	1567.7	1575.9	1579.2	1582.5
32.5°	1231.5	1390.6	1492.3	1507.0	1526.8	1516.9	1515.2	1520.2	1533.2	1533.2	1536.5
35°	1113.5	1316.8	1448.0	1461.2	1475.9	1464.4	1470.9	1472.6	1480.8	1485.7	1484.1
37.5°	983.9	1252.8	1402.0	1411.9	1423.4	1408.6	1418.5	1423.4	1430.0	1426.7	1426.7
40°	869.1	1152.8	1348.0	1354.6	1364.4	1352.9	1362.7	1366.0	1369.3	1366.0	1364.4
42.5°	783.8	1042.9	1290.6	1298.8	1292.2	1300.4	1303.7	1310.3	1305.3	1298.8	1298.8
45°	718.2	1013.5	1228.2	1238.1	1228.2	1241.4	1246.3	1246.3	1231.5	1228.2	1226.7
47.5°	696.9	954.4	1165.9	1165.9	1161.1	1177.4	1185.6	1174.1	1159.4	1154.5	1154.5
50°	695.3	888.8	1080.6	1074.1	1097.1	1116.8	1108.5	1097.1	1085.6	1067.5	1067.5
52.5°	631.3	808.4	970.8	995.4	1031.5	1042.9	1029.9	1018.3	998.7	990.5	983.9
55°	585.5	724.8	870.7	920.0	957.7	972.4	947.9	936.3	906.9	901.9	898.7
57.5°	575.6	603.5	779.0	841.3	887.1	885.6	870.7	849.4	824.8	820.0	818.3
60°	528.0	436.2	680.5	754.4	801.8	797.0	783.8	764.2	741.2	737.9	734.7
62.5°	478.9	316.5	569.0	652.6	719.9	718.2	706.8	677.2	660.9	652.6	646.1
65°	406.7	265.7	405.0	542.8	639.5	642.8	618.2	596.9	578.9	569.0	567.3
67.5°	309.9	216.5	273.8	452.6	562.5	559.2	528.0	518.2	495.3	490.3	480.5
70°	229.6	144.3	190.2	367.3	487.0	478.9	454.3	442.7	421.4	410.0	403.4
72.5°	190.2	116.5	139.3	285.4	410.0	400.1	378.8	365.7	347.7	337.8	331.2
75°	154.2	123.0	106.6	211.5	332.9	326.4	306.7	293.5	278.8	265.7	267.3
77.5°	113.2	114.8	85.3	155.8	264.1	254.2	242.7	226.3	219.8	206.6	206.6
80°	85.3	90.2	64.0	106.6	190.2	190.2	180.4	168.9	157.5	150.9	150.9
82.5°	57.4	57.4	47.6	67.2	129.6	124.6	118.0	114.8	108.2	104.9	104.9
85°	26.3	32.8	29.6	41.0	70.5	73.8	73.8	70.5	68.9	65.6	67.2
87.5°	8.2	14.7	18.0	23.0	36.0	37.7	39.3	39.3	39.3	41.0	41.0
90°	3.0	5.4	7.8	8.4	13.3	19.7	22.9	20.3	15.2	11.4	11.4
92.5°	12.0	32.5	52.8	57.9	81.5	112.9	128.6	112.7	80.9	57.1	54.8
95°	28.9	66.3	103.7	113.0	200.6	317.3	375.8	335.3	254.4	193.7	186.8
97.5°	49.9	82.8	115.8	124.0	270.2	464.9	562.3	536.7	485.7	447.3	434.2
100°	66.1	95.9	125.9	133.3	295.4	511.6	619.7	621.5	625.3	628.1	612.5
102.5°	79.9	107.8	135.7	142.6	307.1	526.4	636.0	668.5	733.6	782.5	769.1
105°	103.3	126.9	150.6	156.5	315.7	528.0	634.1	707.2	853.2	962.7	955.5
107.5°	127.3	149.4	171.4	176.9	317.3	504.5	598.1	699.9	903.6	1056.4	1058.1
110°	143.6	163.5	183.4	188.4	314.9	483.6	568.0	681.9	909.6	1080.4	1087.9

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	159.5	178.5	197.4	202.1	315.0	465.5	540.7	657.3	890.3	1065.1	1076.7
115°	183.5	201.0	218.5	222.9	317.9	444.6	507.9	620.3	844.8	1013.2	1029.1
117.5°	207.3	223.2	239.1	243.0	323.8	431.5	485.4	586.7	789.3	941.4	959.0
120°	221.1	236.0	251.0	254.8	328.6	427.1	476.4	569.0	754.2	893.0	910.2
122.5°	234.6	249.7	264.7	268.5	335.5	424.8	469.5	552.8	719.6	844.7	861.6
125°	255.3	269.1	282.9	286.2	344.9	423.0	462.0	532.9	674.5	780.7	796.3
127.5°	272.2	286.0	299.9	303.4	354.2	421.9	455.7	516.6	638.2	729.4	742.5
130°	281.2	296.1	311.0	314.8	361.0	422.5	453.3	507.5	615.7	696.9	709.0
132.5°	290.5	305.4	320.4	324.1	366.5	423.0	451.2	499.6	596.6	669.3	680.1
135°	304.3	317.8	331.5	334.9	372.5	422.6	447.6	488.2	569.4	630.2	639.6
137.5°	318.4	331.9	345.4	348.7	381.5	425.2	447.0	481.3	549.9	601.4	609.0
140°	330.1	342.5	354.9	358.0	387.0	425.6	444.9	474.5	533.7	578.2	585.4
142.5°	339.2	350.6	362.0	364.9	391.6	427.1	444.9	470.9	523.0	562.0	568.2
145°	352.9	363.0	373.0	375.5	397.6	427.1	441.9	463.2	505.7	537.7	542.3
147.5°	366.8	376.5	386.2	388.7	406.4	430.0	441.9	458.6	492.2	517.3	521.1
150°	375.8	384.6	393.4	395.6	411.0	431.6	441.9	456.0	484.3	505.5	508.6
152.5°	385.1	391.8	398.5	400.1	414.1	432.6	441.9	454.0	478.1	496.2	498.6
155°	398.9	403.9	408.7	410.0	420.6	434.8	441.9	451.5	470.6	485.1	486.6
157.5°	409.1	414.0	418.8	420.0	427.2	437.0	441.9	449.3	464.2	475.5	476.6
160°	416.0	419.8	423.5	424.4	430.2	438.0	441.9	448.3	461.1	470.7	471.3
162.5°	423.0	425.8	428.6	429.3	433.4	439.1	441.9	447.3	458.0	466.2	466.8
165°	430.4	432.9	435.5	436.1	438.1	440.6	441.9	445.7	453.5	459.3	460.0
167.5°	437.3	438.5	439.7	440.0	441.7	443.8	444.9	447.4	452.5	456.3	456.6
170°	441.9	443.0	444.3	444.6	444.7	444.8	444.9	447.4	452.5	456.3	456.3
172.5°	444.3	444.6	444.8	444.9	444.9	444.9	444.9	446.9	450.9	453.9	453.7
175°	447.6	447.6	447.6	447.6	446.7	445.4	444.9	446.1	448.6	450.6	450.6
177.5°	447.6	447.6	447.6	447.6	446.9	445.9	445.4	446.4	448.5	450.0	449.7
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3
2.5°	1777.6	1772.7	1777.6	1774.3	1776.0	1771.0	1756.3	1751.4	1756.3	1761.3	1761.3
5°	1798.9	1795.7	1798.9	1798.9	1797.3	1794.0	1777.6	1774.3	1777.6	1779.3	1776.0
7.5°	1805.4	1800.6	1805.4	1802.2	1802.2	1798.9	1782.6	1779.3	1780.9	1785.8	1780.9
10°	1805.4	1800.6	1805.4	1803.9	1802.2	1798.9	1782.6	1776.0	1776.0	1780.9	1776.0
12.5°	1797.3	1794.0	1797.3	1794.0	1794.0	1790.7	1774.3	1767.7	1769.4	1771.0	1764.5
15°	1784.1	1779.3	1784.1	1780.9	1782.6	1777.6	1759.6	1753.0	1753.0	1756.3	1744.8
17.5°	1764.5	1758.0	1764.5	1762.8	1761.3	1758.0	1741.5	1735.0	1733.3	1735.0	1726.8
20°	1741.5	1736.6	1741.5	1739.9	1739.9	1733.3	1717.0	1708.7	1708.7	1708.7	1700.5
22.5°	1705.4	1700.5	1705.4	1708.7	1708.7	1707.1	1692.4	1680.8	1677.5	1677.5	1667.7
25°	1664.5	1659.5	1664.5	1664.5	1662.8	1664.5	1659.5	1653.0	1648.1	1643.1	1633.3
27.5°	1625.1	1621.8	1625.1	1621.8	1625.1	1620.2	1618.5	1616.9	1610.4	1605.4	1592.3
30°	1585.8	1582.5	1585.8	1582.5	1579.2	1575.9	1567.7	1564.5	1570.9	1567.7	1546.4
32.5°	1536.5	1533.2	1536.5	1536.5	1533.2	1533.2	1520.2	1515.2	1516.9	1526.8	1507.0
35°	1485.7	1480.8	1485.7	1484.1	1485.7	1480.8	1472.6	1470.9	1464.4	1475.9	1461.2
37.5°	1426.7	1421.7	1426.7	1426.7	1426.7	1430.0	1423.4	1418.5	1408.6	1423.4	1411.9
40°	1366.0	1359.4	1366.0	1364.4	1366.0	1369.3	1366.0	1362.7	1352.9	1364.4	1354.6
42.5°	1297.1	1295.5	1297.1	1298.8	1298.8	1305.3	1310.3	1303.7	1300.4	1292.2	1298.8
45°	1223.4	1220.1	1223.4	1226.7	1228.2	1231.5	1246.3	1246.3	1241.4	1228.2	1238.1
47.5°	1144.6	1136.4	1144.6	1154.5	1154.5	1159.4	1174.1	1185.6	1177.4	1161.1	1165.9
50°	1061.0	1062.6	1061.0	1067.5	1067.5	1085.6	1097.1	1108.5	1116.8	1097.1	1074.1
52.5°	979.0	977.3	979.0	983.9	990.5	998.7	1018.3	1029.9	1042.9	1031.5	995.4
55°	897.0	900.3	897.0	898.7	901.9	906.9	936.3	947.9	972.4	957.7	920.0
57.5°	815.0	810.1	815.0	818.3	820.0	824.8	849.4	870.7	885.6	887.1	841.3
60°	719.9	713.4	719.9	734.7	737.9	741.2	764.2	783.8	797.0	801.8	754.4
62.5°	636.2	624.8	636.2	646.1	652.6	660.9	677.2	706.8	718.2	719.9	652.6
65°	547.7	542.8	547.7	567.3	569.0	578.9	596.9	618.2	642.8	639.5	542.8
67.5°	467.3	467.3	467.3	480.5	490.3	495.3	518.2	528.0	559.2	562.5	452.6
70°	393.6	392.0	393.6	403.4	410.0	421.4	442.7	454.3	478.9	487.0	367.3
72.5°	323.1	321.4	323.1	331.2	337.8	347.7	365.7	378.8	400.1	410.0	285.4
75°	260.8	257.5	260.8	267.3	265.7	278.8	293.5	306.7	326.4	332.9	211.5
77.5°	200.1	200.1	200.1	206.6	206.6	219.8	226.3	242.7	254.2	264.1	155.8
80°	149.2	147.6	149.2	150.9	150.9	157.5	168.9	180.4	190.2	190.2	106.6
82.5°	104.9	101.6	104.9	104.9	104.9	108.2	114.8	118.0	124.6	129.6	67.2
85°	65.6	65.6	65.6	67.2	65.6	68.9	70.5	73.8	73.8	70.5	41.0
87.5°	42.6	41.0	42.6	41.0	41.0	39.3	39.3	39.3	37.7	36.0	23.0
90°	11.4	11.4	11.4	11.4	11.4	15.2	20.3	22.9	19.7	13.3	8.4
92.5°	45.7	36.6	45.7	54.8	57.1	80.9	112.7	128.6	112.9	81.5	57.9
95°	159.4	131.9	159.4	186.8	193.7	254.4	335.3	375.8	317.3	200.6	113.0
97.5°	381.9	329.6	381.9	434.2	447.3	485.7	536.7	562.3	464.9	270.2	124.0
100°	550.2	487.8	550.2	612.5	628.1	625.3	621.5	619.7	511.6	295.4	133.3
102.5°	715.7	662.3	715.7	769.1	782.5	733.6	668.5	636.0	526.4	307.1	142.6
105°	926.8	898.2	926.8	955.5	962.7	853.2	707.2	634.1	528.0	315.7	156.5
107.5°	1065.1	1072.1	1065.1	1058.1	1056.4	903.6	699.9	598.1	504.5	317.3	176.9
110°	1117.8	1147.8	1117.8	1087.9	1080.4	909.6	681.9	568.0	483.6	314.9	188.4

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1122.6	1168.5	1122.6	1076.7	1065.1	890.3	657.3	540.7	465.5	315.0	202.1
115°	1092.8	1156.5	1092.8	1029.1	1013.2	844.8	620.3	507.9	444.6	317.9	222.9
117.5°	1029.7	1100.3	1029.7	959.0	941.4	789.3	586.7	485.4	431.5	323.8	243.0
120°	978.8	1047.4	978.8	910.2	893.0	754.2	569.0	476.4	427.1	328.6	254.8
122.5°	929.3	997.0	929.3	861.6	844.7	719.6	552.8	469.5	424.8	335.5	268.5
125°	858.6	920.9	858.6	796.3	780.7	674.5	532.9	462.0	423.0	344.9	286.2
127.5°	795.1	847.7	795.1	742.5	729.4	638.2	516.6	455.7	421.9	354.2	303.4
130°	757.7	806.2	757.7	709.0	696.9	615.7	507.5	453.3	422.5	361.0	314.8
132.5°	723.6	767.2	723.6	680.1	669.3	596.6	499.6	451.2	423.0	366.5	324.1
135°	677.1	714.6	677.1	639.6	630.2	569.4	488.2	447.6	422.6	372.5	334.9
137.5°	639.7	670.5	639.7	609.0	601.4	549.9	481.3	447.0	425.2	381.5	348.7
140°	614.2	642.8	614.2	585.4	578.2	533.7	474.5	444.9	425.6	387.0	358.0
142.5°	592.8	617.5	592.8	568.2	562.0	523.0	470.9	444.9	427.1	391.6	364.9
145°	561.1	579.8	561.1	542.3	537.7	505.7	463.2	441.9	427.1	397.6	375.5
147.5°	536.6	552.1	536.6	521.1	517.3	492.2	458.6	441.9	430.0	406.4	388.7
150°	521.2	533.8	521.2	508.6	505.5	484.3	456.0	441.9	431.6	411.0	395.6
152.5°	508.0	517.5	508.0	498.6	496.2	478.1	454.0	441.9	432.6	414.1	400.1
155°	492.9	499.2	492.9	486.6	485.1	470.6	451.5	441.9	434.8	420.6	410.0
157.5°	481.0	485.4	481.0	476.6	475.5	464.2	449.3	441.9	437.0	427.2	420.0
160°	473.8	476.4	473.8	471.3	470.7	461.1	448.3	441.9	438.0	430.2	424.4
162.5°	469.2	471.6	469.2	466.8	466.2	458.0	447.3	441.9	439.1	433.4	429.3
165°	462.5	465.0	462.5	460.0	459.3	453.5	445.7	441.9	440.6	438.1	436.1
167.5°	457.7	458.7	457.7	456.6	456.3	452.5	447.4	444.9	443.8	441.7	440.0
170°	456.3	456.3	456.3	456.3	456.3	452.5	447.4	444.9	444.8	444.7	444.6
172.5°	452.7	451.7	452.7	453.7	453.9	450.9	446.9	444.9	444.9	444.9	444.9
175°	450.6	450.6	450.6	450.6	450.6	448.6	446.1	444.9	445.4	446.7	447.6
177.5°	448.6	447.6	448.6	449.7	450.0	448.5	446.4	445.4	445.9	446.9	447.6
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3
2.5°	1758.0	1748.1	1748.1	1731.7	1725.1	1720.2	1712.0	1687.4	1680.8	1674.3	1684.1
5°	1772.7	1754.7	1741.5	1712.0	1687.4	1677.5	1646.4	1587.4	1548.1	1518.5	1502.1
7.5°	1776.0	1753.0	1728.4	1682.5	1623.5	1597.2	1502.1	1393.9	1364.4	1338.1	1321.7
10°	1772.7	1746.4	1712.0	1643.1	1503.8	1457.9	1362.7	1292.2	1274.1	1269.3	1274.1
12.5°	1761.3	1736.6	1689.1	1574.2	1379.1	1348.0	1292.2	1251.2	1248.0	1256.1	1300.4
15°	1741.5	1718.6	1662.8	1482.5	1310.3	1287.3	1248.0	1233.1	1251.2	1308.6	1441.5
17.5°	1721.8	1695.7	1626.8	1392.3	1257.8	1241.4	1213.5	1243.0	1344.7	1421.7	1466.0
20°	1695.7	1664.5	1585.8	1326.7	1220.1	1205.3	1192.2	1325.0	1402.0	1430.0	1454.6
22.5°	1664.5	1631.7	1530.0	1280.7	1180.7	1169.2	1177.4	1370.9	1402.0	1421.7	1443.0
25°	1623.5	1595.6	1464.4	1244.7	1149.5	1136.4	1167.5	1366.0	1384.0	1389.0	1431.6
27.5°	1585.8	1549.6	1395.6	1211.8	1111.8	1106.9	1175.8	1344.7	1357.8	1362.7	1408.6
30°	1539.8	1485.7	1318.4	1177.4	1072.5	1070.8	1177.4	1318.4	1315.1	1328.3	1374.2
32.5°	1492.3	1390.6	1231.5	1134.8	1034.8	1033.1	1165.9	1279.1	1275.8	1293.8	1328.3
35°	1448.0	1316.8	1113.5	1085.6	987.2	988.9	1138.1	1233.1	1234.8	1251.2	1272.5
37.5°	1402.0	1252.8	983.9	1031.5	941.3	941.3	1100.3	1190.5	1187.2	1192.2	1221.7
40°	1348.0	1152.8	869.1	961.0	898.7	893.7	1054.5	1144.6	1133.1	1131.5	1172.5
42.5°	1290.6	1042.9	783.8	867.4	849.4	842.9	998.7	1088.9	1067.5	1072.5	1124.9
45°	1228.2	1013.5	718.2	733.0	798.6	793.7	938.0	1024.9	1010.2	1023.3	1077.4
47.5°	1165.9	954.4	696.9	608.4	744.5	742.8	870.7	962.6	954.4	967.5	1024.9
50°	1080.6	888.8	695.3	521.5	683.8	690.4	790.4	901.9	901.9	913.4	974.0
52.5°	970.8	808.4	631.3	472.3	613.3	633.0	719.9	849.4	852.7	864.3	918.3
55°	870.7	724.8	585.5	434.6	529.7	572.3	651.1	795.4	801.8	813.4	862.6
57.5°	779.0	603.5	575.6	390.3	452.6	493.6	590.3	742.8	746.1	756.0	803.5
60°	680.5	436.2	528.0	342.7	385.4	416.5	534.6	680.5	692.1	698.6	739.5
62.5°	569.0	316.5	478.9	309.9	352.5	359.1	488.7	621.5	636.2	641.2	665.8
65°	405.0	265.7	406.7	282.1	318.1	319.8	439.4	560.9	573.9	582.2	600.2
67.5°	273.8	216.5	309.9	255.8	291.9	293.5	392.0	490.3	508.3	514.9	526.4
70°	190.2	144.3	229.6	227.9	262.4	265.7	341.1	426.4	442.7	447.7	454.3
72.5°	139.3	116.5	190.2	204.9	231.2	234.5	288.6	354.2	370.6	375.5	378.8
75°	106.6	123.0	154.2	178.8	196.8	198.5	236.1	288.6	300.1	303.4	305.0
77.5°	85.3	114.8	113.2	144.3	160.7	157.5	185.3	223.1	232.9	232.9	232.9
80°	64.0	90.2	85.3	103.3	118.0	114.8	132.8	159.1	162.3	165.6	164.0
82.5°	47.6	57.4	57.4	65.6	78.7	75.4	88.6	103.3	103.3	103.3	106.6
85°	29.6	32.8	26.3	34.4	44.3	42.6	49.2	55.7	57.4	57.4	54.1
87.5°	18.0	14.7	8.2	13.1	19.7	19.7	23.0	24.6	23.0	23.0	23.0
90°	7.8	5.4	3.0	5.4	7.8	8.4	13.3	19.7	22.9	20.3	15.2
92.5°	52.8	32.5	12.0	32.5	52.8	57.9	81.5	112.9	128.6	112.7	80.9
95°	103.7	66.3	28.9	66.3	103.7	113.0	200.6	317.3	375.8	335.3	254.4
97.5°	115.8	82.8	49.9	82.8	115.8	124.0	270.2	464.9	562.3	536.7	485.7
100°	125.9	95.9	66.1	95.9	125.9	133.3	295.4	511.6	619.7	621.5	625.3
102.5°	135.7	107.8	79.9	107.8	135.7	142.6	307.1	526.4	636.0	668.5	733.6
105°	150.6	126.9	103.3	126.9	150.6	156.5	315.7	528.0	634.1	707.2	853.2
107.5°	171.4	149.4	127.3	149.4	171.4	176.9	317.3	504.5	598.1	699.9	903.6
110°	183.4	163.5	143.6	163.5	183.4	188.4	314.9	483.6	568.0	681.9	909.6

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	197.4	178.5	159.5	178.5	197.4	202.1	315.0	465.5	540.7	657.3	890.3
115°	218.5	201.0	183.5	201.0	218.5	222.9	317.9	444.6	507.9	620.3	844.8
117.5°	239.1	223.2	207.3	223.2	239.1	243.0	323.8	431.5	485.4	586.7	789.3
120°	251.0	236.0	221.1	236.0	251.0	254.8	328.6	427.1	476.4	569.0	754.2
122.5°	264.7	249.7	234.6	249.7	264.7	268.5	335.5	424.8	469.5	552.8	719.6
125°	282.9	269.1	255.3	269.1	282.9	286.2	344.9	423.0	462.0	532.9	674.5
127.5°	299.9	286.0	272.2	286.0	299.9	303.4	354.2	421.9	455.7	516.6	638.2
130°	311.0	296.1	281.2	296.1	311.0	314.8	361.0	422.5	453.3	507.5	615.7
132.5°	320.4	305.4	290.5	305.4	320.4	324.1	366.5	423.0	451.2	499.6	596.6
135°	331.5	317.8	304.3	317.8	331.5	334.9	372.5	422.6	447.6	488.2	569.4
137.5°	345.4	331.9	318.4	331.9	345.4	348.7	381.5	425.2	447.0	481.3	549.9
140°	354.9	342.5	330.1	342.5	354.9	358.0	387.0	425.6	444.9	474.5	533.7
142.5°	362.0	350.6	339.2	350.6	362.0	364.9	391.6	427.1	444.9	470.9	523.0
145°	373.0	363.0	352.9	363.0	373.0	375.5	397.6	427.1	441.9	463.2	505.7
147.5°	386.2	376.5	366.8	376.5	386.2	388.7	406.4	430.0	441.9	458.6	492.2
150°	393.4	384.6	375.8	384.6	393.4	395.6	411.0	431.6	441.9	456.0	484.3
152.5°	398.5	391.8	385.1	391.8	398.5	400.1	414.1	432.6	441.9	454.0	478.1
155°	408.7	403.9	398.9	403.9	408.7	410.0	420.6	434.8	441.9	451.5	470.6
157.5°	418.8	414.0	409.1	414.0	418.8	420.0	427.2	437.0	441.9	449.3	464.2
160°	423.5	419.8	416.0	419.8	423.5	424.4	430.2	438.0	441.9	448.3	461.1
162.5°	428.6	425.8	423.0	425.8	428.6	429.3	433.4	439.1	441.9	447.3	458.0
165°	435.5	432.9	430.4	432.9	435.5	436.1	438.1	440.6	441.9	445.7	453.5
167.5°	439.7	438.5	437.3	438.5	439.7	440.0	441.7	443.8	444.9	447.4	452.5
170°	444.3	443.0	441.9	443.0	444.3	444.6	444.7	444.8	444.9	447.4	452.5
172.5°	444.8	444.6	444.3	444.6	444.8	444.9	444.9	444.9	444.9	446.9	450.9
175°	447.6	447.6	447.6	447.6	447.6	447.6	446.7	445.4	444.9	446.1	448.6
177.5°	447.6	447.6	447.6	447.6	447.6	447.6	446.9	445.9	445.4	446.4	448.5
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3	1733.3
2.5°	1672.7	1667.7	1674.3	1656.2	1674.3	1667.7	1672.7	1684.1	1674.3	1680.8	1687.4
5°	1467.6	1459.5	1433.2	1411.9	1433.2	1459.5	1467.6	1502.1	1518.5	1548.1	1587.4
7.5°	1311.9	1305.3	1298.8	1285.7	1298.8	1305.3	1311.9	1321.7	1338.1	1364.4	1393.9
10°	1277.4	1279.1	1289.0	1287.3	1289.0	1279.1	1277.4	1274.1	1269.3	1274.1	1292.2
12.5°	1366.0	1380.7	1434.9	1431.6	1434.9	1380.7	1366.0	1300.4	1256.1	1248.0	1251.2
15°	1467.6	1472.6	1484.1	1485.7	1484.1	1472.6	1467.6	1441.5	1308.6	1251.2	1233.1
17.5°	1477.5	1479.2	1487.3	1487.3	1487.3	1479.2	1477.5	1466.0	1421.7	1344.7	1243.0
20°	1469.3	1472.6	1489.0	1492.3	1489.0	1472.6	1469.3	1454.6	1430.0	1402.0	1325.0
22.5°	1466.0	1472.6	1485.7	1484.1	1485.7	1472.6	1466.0	1443.0	1421.7	1402.0	1370.9
25°	1449.6	1449.6	1451.3	1452.9	1451.3	1449.6	1449.6	1431.6	1389.0	1384.0	1366.0
27.5°	1415.2	1418.5	1428.3	1426.7	1428.3	1418.5	1415.2	1408.6	1362.7	1357.8	1344.7
30°	1384.0	1380.7	1372.6	1366.0	1372.6	1380.7	1384.0	1374.2	1328.3	1315.1	1318.4
32.5°	1331.6	1323.4	1315.1	1310.3	1315.1	1323.4	1331.6	1328.3	1293.8	1275.8	1279.1
35°	1269.3	1270.8	1269.3	1264.4	1269.3	1270.8	1269.3	1272.5	1251.2	1234.8	1233.1
37.5°	1225.0	1228.2	1226.7	1220.1	1226.7	1228.2	1225.0	1221.7	1192.2	1187.2	1190.5
40°	1179.1	1180.7	1179.1	1174.1	1179.1	1180.7	1179.1	1172.5	1131.5	1133.1	1144.6
42.5°	1134.8	1133.1	1128.2	1124.9	1128.2	1133.1	1134.8	1124.9	1072.5	1067.5	1088.9
45°	1083.9	1085.6	1075.8	1070.8	1075.8	1085.6	1083.9	1077.4	1023.3	1010.2	1024.9
47.5°	1033.1	1033.1	1024.9	1020.0	1024.9	1033.1	1033.1	1024.9	967.5	954.4	962.6
50°	979.0	977.3	965.9	964.3	965.9	977.3	979.0	974.0	913.4	901.9	901.9
52.5°	916.7	916.7	918.3	921.6	918.3	916.7	916.7	918.3	864.3	852.7	849.4
55°	862.6	864.3	875.7	879.0	875.7	864.3	862.6	862.6	813.4	801.8	795.4
57.5°	806.8	806.8	815.0	815.0	815.0	806.8	806.8	803.5	756.0	746.1	742.8
60°	742.8	746.1	752.7	751.1	752.7	746.1	742.8	739.5	698.6	692.1	680.5
62.5°	675.6	678.9	680.5	677.2	680.5	678.9	675.6	665.8	641.2	636.2	621.5
65°	605.1	608.4	610.0	606.8	610.0	608.4	605.1	600.2	582.2	573.9	560.9
67.5°	532.9	531.3	529.7	536.2	529.7	531.3	532.9	526.4	514.9	508.3	490.3
70°	459.1	459.1	457.6	460.8	457.6	459.1	459.1	454.3	447.7	442.7	426.4
72.5°	380.4	378.8	385.4	380.4	385.4	378.8	380.4	378.8	375.5	370.6	354.2
75°	303.4	306.7	303.4	308.3	303.4	306.7	303.4	305.0	303.4	300.1	288.6
77.5°	231.2	234.5	231.2	231.2	231.2	234.5	231.2	232.9	232.9	232.9	223.1
80°	164.0	162.3	162.3	160.7	162.3	162.3	164.0	164.0	165.6	162.3	159.1
82.5°	104.9	103.3	103.3	106.6	103.3	103.3	104.9	106.6	103.3	103.3	103.3
85°	57.4	59.0	55.7	55.7	55.7	59.0	57.4	54.1	57.4	57.4	55.7
87.5°	21.3	19.7	19.7	19.7	19.7	19.7	21.3	23.0	23.0	23.0	24.6
90°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	15.2	20.3	22.9	19.7
92.5°	57.1	54.8	45.7	36.6	45.7	54.8	57.1	80.9	112.7	128.6	112.9
95°	193.7	186.8	159.4	131.9	159.4	186.8	193.7	254.4	335.3	375.8	317.3
97.5°	447.3	434.2	381.9	329.6	381.9	434.2	447.3	485.7	536.7	562.3	464.9
100°	628.1	612.5	550.2	487.8	550.2	612.5	628.1	625.3	621.5	619.7	511.6
102.5°	782.5	769.1	715.7	662.3	715.7	769.1	782.5	733.6	668.5	636.0	526.4
105°	962.7	955.5	926.8	898.2	926.8	955.5	962.7	853.2	707.2	634.1	528.0
107.5°	1056.4	1058.1	1065.1	1072.1	1065.1	1058.1	1056.4	903.6	699.9	598.1	504.5
110°	1080.4	1087.9	1117.8	1147.8	1117.8	1087.9	1080.4	909.6	681.9	568.0	483.6

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1065.1	1076.7	1122.6	1168.5	1122.6	1076.7	1065.1	890.3	657.3	540.7	465.5
115°	1013.2	1029.1	1092.8	1156.5	1092.8	1029.1	1013.2	844.8	620.3	507.9	444.6
117.5°	941.4	959.0	1029.7	1100.3	1029.7	959.0	941.4	789.3	586.7	485.4	431.5
120°	893.0	910.2	978.8	1047.4	978.8	910.2	893.0	754.2	569.0	476.4	427.1
122.5°	844.7	861.6	929.3	997.0	929.3	861.6	844.7	719.6	552.8	469.5	424.8
125°	780.7	796.3	858.6	920.9	858.6	796.3	780.7	674.5	532.9	462.0	423.0
127.5°	729.4	742.5	795.1	847.7	795.1	742.5	729.4	638.2	516.6	455.7	421.9
130°	696.9	709.0	757.7	806.2	757.7	709.0	696.9	615.7	507.5	453.3	422.5
132.5°	669.3	680.1	723.6	767.2	723.6	680.1	669.3	596.6	499.6	451.2	423.0
135°	630.2	639.6	677.1	714.6	677.1	639.6	630.2	569.4	488.2	447.6	422.6
137.5°	601.4	609.0	639.7	670.5	639.7	609.0	601.4	549.9	481.3	447.0	425.2
140°	578.2	585.4	614.2	642.8	614.2	585.4	578.2	533.7	474.5	444.9	425.6
142.5°	562.0	568.2	592.8	617.5	592.8	568.2	562.0	523.0	470.9	444.9	427.1
145°	537.7	542.3	561.1	579.8	561.1	542.3	537.7	505.7	463.2	441.9	427.1
147.5°	517.3	521.1	536.6	552.1	536.6	521.1	517.3	492.2	458.6	441.9	430.0
150°	505.5	508.6	521.2	533.8	521.2	508.6	505.5	484.3	456.0	441.9	431.6
152.5°	496.2	498.6	508.0	517.5	508.0	498.6	496.2	478.1	454.0	441.9	432.6
155°	485.1	486.6	492.9	499.2	492.9	486.6	485.1	470.6	451.5	441.9	434.8
157.5°	475.5	476.6	481.0	485.4	481.0	476.6	475.5	464.2	449.3	441.9	437.0
160°	470.7	471.3	473.8	476.4	473.8	471.3	470.7	461.1	448.3	441.9	438.0
162.5°	466.2	466.8	469.2	471.6	469.2	466.8	466.2	458.0	447.3	441.9	439.1
165°	459.3	460.0	462.5	465.0	462.5	460.0	459.3	453.5	445.7	441.9	440.6
167.5°	456.3	456.6	457.7	458.7	457.7	456.6	456.3	452.5	447.4	444.9	443.8
170°	456.3	456.3	456.3	456.3	456.3	456.3	456.3	452.5	447.4	444.9	444.8
172.5°	453.9	453.7	452.7	451.7	452.7	453.7	453.9	450.9	446.9	444.9	444.9
175°	450.6	450.6	450.6	450.6	450.6	450.6	450.6	448.6	446.1	444.9	445.4
177.5°	450.0	449.7	448.6	447.6	448.6	449.7	450.0	448.5	446.4	445.4	445.9
180°	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1733.3	1733.3	1733.3	1733.3	1733.3
2.5°	1712.0	1720.2	1725.1	1731.7	1748.1
5°	1646.4	1677.5	1687.4	1712.0	1741.5
7.5°	1502.1	1597.2	1623.5	1682.5	1728.4
10°	1362.7	1457.9	1503.8	1643.1	1712.0
12.5°	1292.2	1348.0	1379.1	1574.2	1689.1
15°	1248.0	1287.3	1310.3	1482.5	1662.8
17.5°	1213.5	1241.4	1257.8	1392.3	1626.8
20°	1192.2	1205.3	1220.1	1326.7	1585.8
22.5°	1177.4	1169.2	1180.7	1280.7	1530.0
25°	1167.5	1136.4	1149.5	1244.7	1464.4
27.5°	1175.8	1106.9	1111.8	1211.8	1395.6
30°	1177.4	1070.8	1072.5	1177.4	1318.4
32.5°	1165.9	1033.1	1034.8	1134.8	1231.5
35°	1138.1	988.9	987.2	1085.6	1113.5
37.5°	1100.3	941.3	941.3	1031.5	983.9
40°	1054.5	893.7	898.7	961.0	869.1
42.5°	998.7	842.9	849.4	867.4	783.8
45°	938.0	793.7	798.6	733.0	718.2
47.5°	870.7	742.8	744.5	608.4	696.9
50°	790.4	690.4	683.8	521.5	695.3
52.5°	719.9	633.0	613.3	472.3	631.3
55°	651.1	572.3	529.7	434.6	585.5
57.5°	590.3	493.6	452.6	390.3	575.6
60°	534.6	416.5	385.4	342.7	528.0
62.5°	488.7	359.1	352.5	309.9	478.9
65°	439.4	319.8	318.1	282.1	406.7
67.5°	392.0	293.5	291.9	255.8	309.9
70°	341.1	265.7	262.4	227.9	229.6
72.5°	288.6	234.5	231.2	204.9	190.2
75°	236.1	198.5	196.8	178.8	154.2
77.5°	185.3	157.5	160.7	144.3	113.2
80°	132.8	114.8	118.0	103.3	85.3
82.5°	88.6	75.4	78.7	65.6	57.4
85°	49.2	42.6	44.3	34.4	26.3
87.5°	23.0	19.7	19.7	13.1	8.2
90°	13.3	8.4	7.8	5.4	3.0
92.5°	81.5	57.9	52.8	32.5	12.0
95°	200.6	113.0	103.7	66.3	28.9
97.5°	270.2	124.0	115.8	82.8	49.9
100°	295.4	133.3	125.9	95.9	66.1
102.5°	307.1	142.6	135.7	107.8	79.9
105°	315.7	156.5	150.6	126.9	103.3
107.5°	317.3	176.9	171.4	149.4	127.3
110°	314.9	188.4	183.4	163.5	143.6



TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	315.0	202.1	197.4	178.5	159.5
115°	317.9	222.9	218.5	201.0	183.5
117.5°	323.8	243.0	239.1	223.2	207.3
120°	328.6	254.8	251.0	236.0	221.1
122.5°	335.5	268.5	264.7	249.7	234.6
125°	344.9	286.2	282.9	269.1	255.3
127.5°	354.2	303.4	299.9	286.0	272.2
130°	361.0	314.8	311.0	296.1	281.2
132.5°	366.5	324.1	320.4	305.4	290.5
135°	372.5	334.9	331.5	317.8	304.3
137.5°	381.5	348.7	345.4	331.9	318.4
140°	387.0	358.0	354.9	342.5	330.1
142.5°	391.6	364.9	362.0	350.6	339.2
145°	397.6	375.5	373.0	363.0	352.9
147.5°	406.4	388.7	386.2	376.5	366.8
150°	411.0	395.6	393.4	384.6	375.8
152.5°	414.1	400.1	398.5	391.8	385.1
155°	420.6	410.0	408.7	403.9	398.9
157.5°	427.2	420.0	418.8	414.0	409.1
160°	430.2	424.4	423.5	419.8	416.0
162.5°	433.4	429.3	428.6	425.8	423.0
165°	438.1	436.1	435.5	432.9	430.4
167.5°	441.7	440.0	439.7	438.5	437.3
170°	444.7	444.6	444.3	443.0	441.9
172.5°	444.9	444.9	444.8	444.6	444.3
175°	446.7	447.6	447.6	447.6	447.6
177.5°	446.9	447.6	447.6	447.6	447.6
180°	447.6	447.6	447.6	447.6	447.6

TEST NUMBER: P934984

CATALOG NUMBER: SQ4-FA-075U-125D-B2750-1D-UNV-W2A-W-4-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.38	16.35	16.24	17.23	18.34	18.18	19.15	19.04	20.03	21.14
	3H	15.87	16.74	16.74	17.63	18.76	19.52	20.39	20.40	21.28	22.42
	4H	16.07	16.88	16.95	17.78	18.93	19.97	20.79	20.85	21.68	22.83
	6H	16.19	16.95	17.09	17.85	19.01	20.25	21.01	21.15	21.91	23.07
	8H	16.19	16.91	17.10	17.83	18.99	20.32	21.04	21.23	21.96	23.12
	12H	16.17	16.85	17.08	17.77	18.95	20.36	21.05	21.27	21.96	23.14
4H	2H	16.42	17.24	17.31	18.14	19.28	18.61	19.42	19.50	20.32	21.47
	3H	17.46	18.14	18.36	19.07	20.23	20.11	20.79	21.01	21.72	22.88
	4H	17.74	18.36	18.65	19.28	20.47	20.64	21.26	21.55	22.18	23.37
	6H	17.87	18.41	18.80	19.35	20.54	21.00	21.54	21.93	22.48	23.67
	8H	17.88	18.38	18.81	19.32	20.52	21.10	21.61	22.04	22.55	23.75
	12H	17.85	18.30	18.80	19.26	20.47	21.16	21.61	22.11	22.57	23.78
8H	4H	18.20	18.70	19.13	19.64	20.84	20.77	21.27	21.70	22.21	23.41
	6H	18.46	18.88	19.42	19.86	21.06	21.20	21.62	22.16	22.60	23.80
	8H	18.51	18.87	19.47	19.85	21.06	21.35	21.72	22.32	22.69	23.91
	12H	18.49	18.82	19.47	19.78	21.05	21.45	21.77	22.42	22.74	24.00
12H	4H	18.21	18.66	19.16	19.62	20.82	20.74	21.19	21.69	22.15	23.36
	6H	18.52	18.89	19.49	19.86	21.08	21.20	21.57	22.17	22.54	23.76
	8H	18.59	18.92	19.56	19.88	21.15	21.36	21.69	22.33	22.65	23.92