

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937600

Luminaire Tested: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937600
REPORT IS A COMBINATION OF REPORTS P933582 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12453.6 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 98.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937600

CATALOG NUMBER: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P937600

CATALOG NUMBER: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	90	86	83	86	82	78	75	66	64	62	52	50	49	39	38	37
2	86	78	72	67	77	71	66	61	58	54	50	45	42	40	34	32	30
3	78	68	61	55	70	62	56	50	50	46	42	39	36	33	29	27	25
4	71	60	52	46	64	55	48	42	44	39	35	35	31	28	26	23	21
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	42	34	29	49	39	32	27	32	26	22	25	21	18	19	16	14
8	51	38	31	25	46	35	28	23	29	23	20	23	19	16	17	14	12
9	47	35	27	22	42	32	25	21	26	21	17	21	17	14	16	13	11
10	44	32	24	20	40	29	23	18	24	19	15	19	15	12	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2796	2796	2796
5°	2732	3232	3759
10°	2478	4711	6232
15°	2106	6156	7525
20°	1714	7133	7669
25°	1430	7465	7513
30°	1206	7512	7499
35°	1066	7387	7693
40°	929	7225	7893
45°	841	7106	7924
50°	772	6999	7793
55°	739	6843	7447
60°	757	6542	6902
65°	787	6086	6152
70°	839	5307	5197
75°	930	4327	4056
80°	1015	3001	2733
85°	904	1592	1398

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7924 cd/sqm

TEST NUMBER: P937600

CATALOG NUMBER: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	0.6
10°-20°	345.6	2.8
20°-30°	604.4	4.9
30°-40°	778.1	6.2
40°-50°	869.1	7.0
50°-60°	832.4	6.7
60°-70°	659.6	5.3
70°-80°	387.9	3.1
80°-90°	112.3	0.9
90°-100°	585.5	4.7
100°-110°	1539.2	12.4
110°-120°	1596.0	12.8
120°-130°	1280.2	10.3
130°-140°	1004.5	8.1
140°-150°	771.0	6.2
150°-160°	555.2	4.5
160°-170°	339.7	2.7
170°-180°	114.8	0.9
0°-30°	1028.0	8.3
0°-40°	1806.0	14.5
0°-60°	3507.5	28.2
0°-90°	4667.4	37.5
90°-120°	3720.7	29.9
90°-150°	6776.4	54.4
90°-180°	7786.0	62.5
0°-180°	12453.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	603	603	603	603	603	
5°	587	630	709	802	831	54
15°	440	812	1368	1659	1711	122
25°	281	921	1630	1702	1704	129
35°	190	880	1535	1622	1686	119
45°	130	702	1357	1554	1624	100
55°	93	446	1151	1337	1374	85
65°	74	236	855	961	975	73
75°	54	145	469	516	517	57
85°	19	45	116	128	130	21
90°	8	23	61	31	31	8
95°	77	303	1008	520	354	86
105°	277	420	1702	2584	2410	294
115°	492	598	1363	2719	3104	486
125°	685	768	1240	2095	2472	608
135°	817	899	1201	1691	1918	632
145°	947	1008	1186	1443	1556	593
155°	1070	1100	1186	1302	1340	492
165°	1155	1170	1186	1233	1248	326
175°	1201	1201	1194	1209	1209	114
180°	1201	1201	1201	1201	1201	

TEST NUMBER: P937600

CATALOG NUMBER: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7	602.7
2.5°	602.7	602.7	606.6	608.5	612.4	614.3	618.2	622.1	633.7	635.7	639.5
5°	587.2	595.0	620.2	629.8	657.0	693.8	709.3	734.5	786.8	802.3	812.0
7.5°	564.0	581.4	643.4	658.9	726.8	823.6	864.3	918.6	1001.9	1042.6	1075.6
10°	527.1	564.0	674.4	711.2	821.7	969.0	1044.6	1120.3	1246.2	1302.4	1323.8
12.5°	486.4	546.5	707.4	757.8	916.7	1131.9	1223.0	1306.3	1449.7	1525.3	1536.9
15°	439.9	521.3	738.4	812.0	1017.4	1267.5	1368.3	1471.0	1604.8	1659.0	1672.6
17.5°	399.2	501.9	767.4	845.0	1095.0	1389.6	1492.4	1577.6	1686.2	1723.0	1732.7
20°	348.8	470.9	786.8	887.6	1176.5	1478.8	1577.6	1643.5	1717.2	1740.4	1744.3
22.5°	312.0	438.0	798.5	903.1	1230.7	1533.1	1616.4	1668.7	1719.1	1726.9	1728.8
25°	281.0	401.2	796.5	920.6	1277.2	1566.0	1630.0	1668.7	1697.8	1701.7	1701.7
27.5°	251.9	360.5	788.8	924.4	1312.1	1573.8	1624.1	1651.3	1664.8	1672.6	1672.6
30°	226.7	321.7	769.4	916.7	1327.6	1566.0	1606.7	1620.3	1633.8	1645.5	1651.3
32.5°	207.4	284.9	740.3	901.2	1329.6	1546.6	1575.7	1583.4	1602.8	1630.0	1639.6
35°	189.9	248.1	707.4	879.9	1317.9	1515.6	1535.0	1542.7	1581.5	1622.2	1635.8
37.5°	172.5	220.9	664.7	843.0	1300.5	1478.8	1492.4	1505.9	1566.0	1614.5	1630.0
40°	155.0	197.7	614.3	802.3	1273.4	1434.2	1445.8	1467.2	1546.6	1602.8	1618.3
42.5°	141.5	178.3	560.1	759.7	1238.5	1383.8	1401.3	1432.3	1523.4	1583.4	1600.9
45°	129.8	158.9	501.9	701.6	1193.9	1331.5	1356.7	1399.3	1496.2	1554.4	1569.9
47.5°	118.2	145.4	441.9	641.5	1145.5	1279.2	1312.1	1360.6	1459.4	1515.6	1529.2
50°	108.5	131.8	381.8	577.5	1093.0	1223.0	1261.7	1312.1	1412.9	1465.2	1482.7
52.5°	100.8	120.2	325.6	513.6	1033.0	1164.8	1209.4	1261.7	1356.7	1407.1	1418.7
55°	93.0	110.5	277.1	445.7	970.9	1102.8	1151.3	1201.7	1294.7	1337.3	1345.1
57.5°	89.1	102.7	236.4	381.8	905.0	1033.0	1087.2	1133.8	1221.0	1254.0	1261.7
60°	83.3	96.9	205.4	327.5	833.3	967.1	1013.6	1060.1	1133.8	1161.0	1166.8
62.5°	77.5	93.0	182.2	275.2	759.7	889.5	936.1	978.7	1040.7	1060.1	1067.8
65°	73.6	89.1	164.7	236.4	684.1	808.1	854.7	891.5	941.9	961.2	965.1
67.5°	69.8	85.3	151.2	203.5	608.5	726.8	761.6	796.5	835.3	854.7	856.6
70°	64.0	81.4	139.5	180.2	531.0	633.7	662.8	699.6	730.6	740.3	746.1
72.5°	60.1	75.6	131.8	162.8	451.6	544.6	571.7	593.0	620.2	629.8	629.8
75°	54.3	67.8	124.0	145.4	370.2	445.7	469.0	490.3	511.6	515.5	509.7
77.5°	48.4	60.1	106.6	122.1	288.8	352.7	372.1	383.7	401.2	405.0	407.0
80°	40.7	52.3	83.3	95.0	209.3	259.7	273.3	282.9	298.5	298.5	302.3
82.5°	31.0	40.7	60.1	67.8	141.5	178.3	189.9	195.7	205.4	205.4	205.4
85°	19.4	25.2	38.8	44.6	85.3	108.5	116.3	118.2	126.0	127.9	127.9
87.5°	9.7	13.6	25.2	27.1	44.6	56.2	56.2	60.1	60.1	58.1	56.2
90°	8.0	14.5	20.9	22.6	35.5	52.6	61.2	54.5	40.8	30.6	30.6
92.5°	32.3	87.1	142.0	155.6	218.7	302.9	345.0	302.3	217.2	153.2	147.1
95°	77.4	177.7	278.0	303.1	538.2	851.7	1008.4	899.9	682.8	520.0	501.6
97.5°	133.8	222.3	310.9	332.9	725.0	1247.7	1509.0	1440.4	1303.2	1200.3	1165.2
100°	177.3	257.6	337.9	357.9	792.9	1373.0	1663.0	1668.0	1678.0	1685.6	1643.7
102.5°	214.4	289.2	364.2	382.9	824.0	1412.3	1706.5	1793.9	1968.8	2099.9	2064.1
105°	277.3	340.7	404.1	420.0	847.2	1416.9	1701.7	1897.6	2289.6	2583.5	2564.3
107.5°	341.8	400.9	460.0	474.8	851.6	1353.8	1605.0	1878.3	2425.0	2835.0	2839.7
110°	385.3	438.7	492.1	505.4	845.1	1297.9	1524.3	1830.0	2441.1	2899.5	2919.6

TEST NUMBER: P937600

CATALOG NUMBER: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	428.0	478.9	529.8	542.5	845.4	1249.1	1451.0	1763.8	2389.3	2858.5	2889.3
115°	492.5	539.4	586.4	598.2	853.1	1193.1	1363.1	1664.5	2267.1	2719.0	2761.7
117.5°	556.2	598.8	641.5	652.1	869.0	1158.1	1302.6	1574.5	2118.4	2526.3	2573.7
120°	593.3	633.4	673.6	683.5	881.9	1146.3	1278.5	1527.0	2023.9	2396.5	2442.6
122.5°	629.6	670.1	710.6	720.6	900.4	1140.0	1259.9	1483.6	1931.1	2266.8	2312.2
125°	685.2	722.1	759.0	768.2	925.4	1135.0	1239.7	1429.9	1810.0	2095.1	2136.9
127.5°	730.3	767.5	804.9	814.2	950.4	1132.1	1222.9	1386.1	1712.4	1957.2	1992.5
130°	754.5	794.6	834.7	844.8	968.6	1133.8	1216.4	1361.6	1652.2	1870.2	1902.7
132.5°	779.5	819.6	859.7	869.8	983.4	1135.0	1210.8	1340.8	1600.9	1795.9	1825.1
135°	816.6	853.1	889.7	898.8	999.6	1133.9	1201.1	1310.0	1527.8	1691.2	1716.4
137.5°	854.5	890.6	926.8	935.9	1023.7	1140.9	1199.4	1291.5	1475.7	1613.8	1634.4
140°	885.9	919.2	952.5	960.9	1038.5	1142.1	1193.8	1273.4	1432.5	1551.8	1571.0
142.5°	910.1	940.9	971.7	979.4	1050.9	1146.1	1193.8	1263.7	1403.4	1508.2	1524.8
145°	947.2	974.0	1001.0	1007.7	1067.1	1146.2	1185.8	1242.9	1357.2	1442.9	1455.4
147.5°	984.2	1010.4	1036.5	1043.1	1090.7	1154.1	1185.8	1230.7	1320.7	1388.1	1398.5
150°	1008.4	1032.1	1055.7	1061.6	1103.0	1158.1	1185.8	1223.8	1299.7	1356.7	1365.1
152.5°	1033.4	1051.4	1069.3	1073.7	1111.1	1160.9	1185.8	1218.2	1283.1	1331.7	1338.1
155°	1070.5	1083.7	1097.0	1100.3	1128.8	1166.8	1185.8	1211.5	1263.2	1301.9	1306.0
157.5°	1097.9	1110.8	1123.7	1126.9	1146.5	1172.7	1185.8	1205.8	1245.9	1276.1	1279.0
160°	1116.5	1126.6	1136.5	1139.1	1154.7	1175.4	1185.8	1203.0	1237.4	1263.2	1264.9
162.5°	1135.0	1142.5	1150.1	1151.9	1163.2	1178.2	1185.8	1200.3	1229.3	1251.1	1252.7
165°	1155.1	1161.9	1168.7	1170.5	1175.6	1182.4	1185.8	1196.1	1217.0	1232.6	1234.3
167.5°	1173.7	1176.9	1180.1	1180.9	1185.2	1190.9	1193.8	1200.6	1214.3	1224.4	1225.1
170°	1185.8	1189.0	1192.3	1193.0	1193.3	1193.6	1193.8	1200.6	1214.3	1224.4	1224.4
172.5°	1192.3	1192.9	1193.6	1193.8	1193.8	1193.8	1193.8	1199.2	1210.0	1218.0	1217.5
175°	1201.1	1201.1	1201.1	1201.1	1198.7	1195.5	1193.8	1197.2	1204.0	1209.1	1209.1
177.5°	1201.1	1201.1	1201.1	1201.1	1199.2	1196.7	1195.5	1198.2	1203.5	1207.6	1206.9
180°	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1	1201.1

TEST NUMBER: P937600

CATALOG NUMBER: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	602.7	602.7
2.5°	643.4	639.5
5°	827.5	831.4
7.5°	1114.4	1112.5
10°	1385.8	1403.2
12.5°	1583.4	1587.3
15°	1703.6	1711.4
17.5°	1750.1	1752.0
20°	1752.0	1748.2
22.5°	1730.7	1726.9
25°	1705.5	1703.6
27.5°	1682.3	1684.2
30°	1672.6	1678.4
32.5°	1672.6	1682.3
35°	1676.5	1686.2
37.5°	1674.5	1686.2
40°	1666.8	1680.3
42.5°	1645.5	1655.1
45°	1612.5	1624.1
47.5°	1569.9	1577.6
50°	1515.6	1523.4
52.5°	1447.8	1449.7
55°	1366.4	1374.1
57.5°	1279.2	1281.1
60°	1182.3	1188.1
62.5°	1079.5	1079.5
65°	970.9	974.8
67.5°	858.5	868.2
70°	744.2	746.1
72.5°	631.8	631.8
75°	515.5	517.4
77.5°	405.0	405.0
80°	300.4	302.3
82.5°	207.4	211.2
85°	129.8	129.8
87.5°	60.1	54.3
90°	30.6	30.6
92.5°	122.8	98.4
95°	427.7	353.9
97.5°	1024.7	884.3
100°	1476.5	1309.1
102.5°	1920.8	1777.4
105°	2487.2	2410.2
107.5°	2858.4	2877.0
110°	2999.8	3080.1

TEST NUMBER: P937600

CATALOG NUMBER: SQ4-FB-100U-075D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3012.4	3135.7
115°	2932.6	3103.5
117.5°	2763.2	2952.7
120°	2626.8	2810.9
122.5°	2493.8	2675.4
125°	2304.2	2471.5
127.5°	2133.6	2274.8
130°	2033.2	2163.6
132.5°	1942.0	2058.7
135°	1817.1	1917.7
137.5°	1716.8	1799.2
140°	1648.0	1725.0
142.5°	1591.1	1657.4
145°	1505.6	1555.7
147.5°	1440.0	1481.6
150°	1398.8	1432.5
152.5°	1363.5	1388.9
155°	1322.9	1339.7
157.5°	1290.8	1302.6
160°	1271.7	1278.5
162.5°	1259.1	1265.6
165°	1241.1	1247.9
167.5°	1228.0	1230.9
170°	1224.4	1224.4
172.5°	1214.9	1212.4
175°	1209.1	1209.1
177.5°	1204.0	1201.1
180°	1201.1	1201.1

(END OF REPORT)