

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937984

Luminaire Tested: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937984
REPORT IS A COMBINATION OF REPORTS P933598 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7180.2 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937984

CATALOG NUMBER: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P937984

CATALOG NUMBER: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	103	103	103	103	93	93	93	93		74	74	74		56	56	56		40	40	40
1	94	89	85	82	84	80	77	74		64	62	60		49	47	46		35	34	33
2	85	77	71	66	76	70	65	60		55	52	49		42	40	38		30	29	27
3	77	68	60	54	69	61	55	50		49	44	40		37	34	31		26	24	23
4	70	59	52	46	63	54	47	42		43	38	34		33	29	26		23	21	19
5	64	53	45	39	57	48	41	35		38	33	29		29	25	23		21	18	16
6	59	47	39	33	53	42	35	30		34	29	25		26	22	19		19	16	14
7	54	42	34	29	49	38	31	26		31	25	22		23	20	17		17	14	12
8	50	38	30	25	45	34	28	23		28	23	19		21	18	15		15	13	11
9	47	34	27	22	42	31	25	20		25	20	17		19	16	13		14	12	10
10	43	31	24	19	39	28	22	18		23	18	15		18	14	12		13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2797	2797	2797
5°	2729	3230	3759
10°	2473	4704	6232
15°	2099	6142	7524
20°	1707	7112	7668
25°	1422	7437	7513
30°	1198	7478	7499
35°	1058	7348	7692
40°	919	7181	7893
45°	831	7056	7923
50°	761	6943	7792
55°	726	6780	7447
60°	742	6473	6902
65°	767	6011	6152
70°	812	5232	5198
75°	889	4255	4056
80°	950	2940	2734
85°	803	1551	1398

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7923 cd/sqm

TEST NUMBER: P937984

CATALOG NUMBER: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	0.5
10°-20°	172.8	2.4
20°-30°	302.2	4.2
30°-40°	389.0	5.4
40°-50°	434.5	6.1
50°-60°	416.2	5.8
60°-70°	329.8	4.6
70°-80°	193.9	2.7
80°-90°	56.7	0.8
90°-100°	364.4	5.1
100°-110°	958.0	13.3
110°-120°	993.4	13.8
120°-130°	796.8	11.1
130°-140°	625.2	8.7
140°-150°	479.9	6.7
150°-160°	345.6	4.8
160°-170°	211.4	2.9
170°-180°	71.4	1.0
0°-30°	514.0	7.2
0°-40°	903.0	12.6
0°-60°	1753.7	24.4
0°-90°	2334.2	32.5
90°-120°	2315.8	32.3
90°-150°	4217.6	58.7
90°-180°	4846.0	67.5
0°-180°	7180.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	301	301	301	301	301	
5°	294	315	355	401	416	27
15°	220	406	684	830	856	61
25°	140	460	815	851	852	65
35°	95	440	767	811	843	59
45°	65	351	678	777	812	50
55°	46	223	576	669	687	42
65°	37	118	427	481	487	37
75°	27	73	234	258	259	28
85°	10	22	58	64	65	10
90°	5	14	38	19	19	5
95°	48	189	628	324	220	53
105°	173	261	1059	1608	1500	183
115°	306	372	848	1692	1932	303
125°	426	478	772	1304	1538	379
135°	508	559	748	1053	1194	393
145°	590	627	738	898	968	369
155°	666	685	738	810	834	306
165°	719	728	738	767	777	203
175°	748	748	743	752	752	71
180°	748	748	748	748	748	

TEST NUMBER: P937984

CATALOG NUMBER: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4	301.4
2.5°	301.4	301.4	303.3	304.3	306.2	307.2	309.1	311.0	316.9	317.8	319.8
5°	293.6	297.5	310.1	314.9	328.5	346.9	354.7	367.3	393.4	401.2	406.0
7.5°	282.0	290.7	321.7	329.5	363.4	411.8	432.2	459.3	501.0	521.3	537.8
10°	263.6	282.0	337.2	355.6	410.9	484.5	522.3	560.1	623.1	651.2	661.8
12.5°	243.2	273.3	353.7	378.9	458.3	565.9	611.4	653.1	724.8	762.6	768.4
15°	220.0	260.7	369.2	406.0	508.7	633.7	684.1	735.5	802.3	829.5	836.2
17.5°	199.6	251.0	383.7	422.5	547.5	694.8	746.1	788.8	843.0	861.4	866.3
20°	174.4	235.5	393.4	443.8	588.2	739.3	788.8	821.7	858.5	870.2	872.1
22.5°	156.0	219.0	399.2	451.6	615.3	766.5	808.1	834.3	859.5	863.4	864.3
25°	140.5	200.6	398.3	460.3	638.6	783.0	814.9	834.3	848.8	850.8	850.8
27.5°	126.0	180.2	394.4	462.2	656.0	786.8	812.0	825.6	832.4	836.2	836.2
30°	113.4	160.9	384.7	458.3	663.8	783.0	803.3	810.1	816.9	822.7	825.6
32.5°	103.7	142.4	370.2	450.6	664.7	773.3	787.8	791.7	801.4	814.9	819.8
35°	95.0	124.0	353.7	439.9	658.9	757.8	767.4	771.3	790.7	811.1	817.8
37.5°	86.2	110.5	332.4	421.5	650.2	739.3	746.1	752.9	783.0	807.2	814.9
40°	77.5	98.8	307.2	401.2	636.6	717.1	722.9	733.5	773.3	801.4	809.1
42.5°	70.7	89.1	280.0	379.8	619.2	691.9	700.6	716.1	761.6	791.7	800.4
45°	64.9	79.5	251.0	350.8	596.9	665.7	678.3	699.6	748.1	777.1	784.9
47.5°	59.1	72.7	220.9	320.7	572.7	639.5	656.0	680.2	729.7	757.8	764.5
50°	54.3	65.9	190.9	288.8	546.5	611.4	630.8	656.0	706.4	732.6	741.3
52.5°	50.4	60.1	162.8	256.8	516.5	582.4	604.7	630.8	678.3	703.5	709.3
55°	46.5	55.2	138.6	222.9	485.5	551.4	575.6	600.8	647.3	668.6	672.5
57.5°	44.6	51.4	118.2	190.9	452.5	516.5	543.6	566.9	610.5	626.9	630.8
60°	41.7	48.4	102.7	163.8	416.7	483.5	506.8	530.0	566.9	580.4	583.3
62.5°	38.8	46.5	91.1	137.6	379.8	444.8	468.0	489.3	520.4	530.0	533.9
65°	36.8	44.6	82.4	118.2	342.1	404.1	427.3	445.7	470.9	480.6	482.6
67.5°	34.9	42.6	75.6	101.7	304.3	363.4	380.8	398.3	417.6	427.3	428.3
70°	32.0	40.7	69.8	90.1	265.5	316.9	331.4	349.8	365.3	370.2	373.1
72.5°	30.0	37.8	65.9	81.4	225.8	272.3	285.9	296.5	310.1	314.9	314.9
75°	27.1	33.9	62.0	72.7	185.1	222.9	234.5	245.2	255.8	257.8	254.8
77.5°	24.2	30.0	53.3	61.0	144.4	176.4	186.0	191.9	200.6	202.5	203.5
80°	20.3	26.2	41.7	47.5	104.7	129.8	136.6	141.5	149.2	149.2	151.2
82.5°	15.5	20.3	30.0	33.9	70.7	89.1	95.0	97.9	102.7	102.7	102.7
85°	9.7	12.6	19.4	22.3	42.6	54.3	58.1	59.1	63.0	64.0	64.0
87.5°	4.8	6.8	12.6	13.6	22.3	28.1	28.1	30.0	30.0	29.1	28.1
90°	5.0	9.0	13.1	14.1	22.1	32.8	38.1	33.8	25.4	19.1	19.1
92.5°	20.1	54.2	88.3	96.8	136.1	188.6	214.7	188.2	135.2	95.3	91.6
95°	48.2	110.6	173.1	188.7	335.0	530.0	627.6	560.1	425.0	323.6	312.1
97.5°	83.2	138.3	193.4	207.2	451.2	776.5	939.2	896.4	811.1	747.0	725.2
100°	110.4	160.4	210.3	222.8	493.5	854.5	1035.0	1038.1	1044.4	1049.0	1023.0
102.5°	133.4	180.0	226.6	238.3	512.9	879.1	1062.1	1116.6	1225.4	1307.0	1284.7
105°	172.6	212.1	251.6	261.4	527.3	881.9	1059.1	1181.1	1425.0	1608.0	1595.9
107.5°	212.7	249.5	286.3	295.5	530.0	842.6	998.9	1169.1	1509.3	1764.5	1767.4
110°	239.8	273.1	306.2	314.5	526.0	807.9	948.7	1139.0	1519.4	1804.7	1817.2

TEST NUMBER: P937984

CATALOG NUMBER: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	266.4	298.1	329.7	337.6	526.1	777.4	903.1	1097.8	1487.1	1779.1	1798.3
115°	306.5	335.8	365.0	372.3	531.0	742.5	848.4	1035.9	1411.0	1692.3	1718.8
117.5°	346.2	372.8	399.3	405.9	540.9	720.8	810.8	979.9	1318.4	1572.3	1601.8
120°	369.3	394.3	419.3	425.5	548.9	713.5	795.7	950.4	1259.6	1491.6	1520.3
122.5°	391.9	417.1	442.3	448.6	560.5	709.6	784.2	923.5	1201.9	1410.8	1439.1
125°	426.5	449.4	472.4	478.1	576.0	706.4	771.6	889.9	1126.5	1303.9	1330.0
127.5°	454.6	477.7	500.9	506.7	591.5	704.6	761.1	862.6	1065.8	1218.1	1240.1
130°	469.6	494.6	519.6	525.8	602.9	705.7	757.1	847.5	1028.3	1164.0	1184.2
132.5°	485.2	510.2	535.2	541.4	612.1	706.4	753.6	834.5	996.4	1117.8	1136.0
135°	508.2	531.0	553.7	559.4	622.1	705.7	747.6	815.4	951.0	1052.6	1068.3
137.5°	531.8	554.3	576.8	582.5	637.1	710.1	746.5	803.8	918.4	1004.4	1017.2
140°	551.4	572.1	592.8	598.1	646.4	710.9	743.0	792.5	891.6	965.8	977.8
142.5°	566.4	585.6	604.8	609.6	654.1	713.4	743.0	786.5	873.5	938.7	948.9
145°	589.5	606.2	623.0	627.1	664.1	713.4	738.0	773.6	844.7	898.1	905.9
147.5°	612.6	628.9	645.2	649.2	678.8	718.2	738.0	766.0	822.0	864.0	870.5
150°	627.6	642.4	657.1	660.8	686.5	720.8	738.0	761.6	808.9	844.4	849.6
152.5°	643.2	654.4	665.5	668.3	691.6	722.5	738.0	758.1	798.6	828.8	832.8
155°	666.3	674.5	682.8	684.8	702.5	726.2	738.0	754.1	786.1	810.3	812.9
157.5°	683.3	691.4	699.3	701.4	713.6	729.9	738.0	750.5	775.5	794.2	796.0
160°	694.9	701.1	707.4	708.9	718.6	731.5	738.0	748.6	770.1	786.1	787.2
162.5°	706.4	711.1	715.8	717.0	723.9	733.3	738.0	747.0	765.1	778.7	779.7
165°	718.9	723.2	727.4	728.5	731.7	735.9	738.0	744.5	757.4	767.1	768.1
167.5°	730.5	732.5	734.5	735.0	737.7	741.3	743.0	747.3	755.7	762.1	762.6
170°	738.0	740.0	742.1	742.5	742.7	742.9	743.0	747.3	755.7	762.1	762.1
172.5°	742.1	742.4	742.9	743.0	743.0	743.0	743.0	746.3	753.0	758.0	757.7
175°	747.6	747.6	747.6	747.6	746.0	744.0	743.0	745.2	749.3	752.5	752.5
177.5°	747.6	747.6	747.6	747.6	746.4	744.8	744.0	745.6	749.0	751.6	751.1
180°	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6	747.6

TEST NUMBER: P937984

CATALOG NUMBER: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	301.4	301.4
2.5°	321.7	319.8
5°	413.8	415.7
7.5°	557.2	556.2
10°	692.8	701.6
12.5°	791.7	793.6
15°	851.8	855.6
17.5°	875.0	876.0
20°	876.0	874.0
22.5°	865.3	863.4
25°	852.7	851.8
27.5°	841.1	842.1
30°	836.2	839.2
32.5°	836.2	841.1
35°	838.2	843.0
37.5°	837.2	843.0
40°	833.3	840.1
42.5°	822.7	827.5
45°	806.2	812.0
47.5°	784.9	788.8
50°	757.8	761.6
52.5°	723.8	724.8
55°	683.1	687.0
57.5°	639.5	640.5
60°	591.1	594.0
62.5°	539.7	539.7
65°	485.5	487.4
67.5°	429.3	434.1
70°	372.1	373.1
72.5°	315.9	315.9
75°	257.8	258.7
77.5°	202.5	202.5
80°	150.2	151.2
82.5°	103.7	105.6
85°	64.9	64.9
87.5°	30.0	27.1
90°	19.1	19.1
92.5°	76.4	61.2
95°	266.2	220.3
97.5°	637.8	550.4
100°	918.9	814.7
102.5°	1195.5	1106.3
105°	1548.1	1500.1
107.5°	1779.0	1790.6
110°	1867.1	1917.0

TEST NUMBER: P937984

CATALOG NUMBER: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1874.9	1951.7
115°	1825.2	1931.6
117.5°	1719.8	1837.7
120°	1634.8	1749.4
122.5°	1552.0	1665.1
125°	1434.0	1538.2
127.5°	1327.9	1415.8
130°	1265.4	1346.6
132.5°	1208.6	1281.3
135°	1130.9	1193.5
137.5°	1068.5	1119.8
140°	1025.7	1073.7
142.5°	990.2	1031.5
145°	937.1	968.3
147.5°	896.2	922.1
150°	870.6	891.6
152.5°	848.6	864.4
155°	823.4	833.8
157.5°	803.4	810.8
160°	791.5	795.7
162.5°	783.7	787.7
165°	772.4	776.7
167.5°	764.3	766.1
170°	762.1	762.1
172.5°	756.1	754.6
175°	752.5	752.5
177.5°	749.3	747.6
180°	747.6	747.6

TEST NUMBER: P937984

CATALOG NUMBER: SQ4-FB-125U-075D-B2750-1D-UNV-W2A-W-4-3500K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.70	3.45	3.79	4.54	6.04	15.84	16.59	16.93	17.68	19.17
	3H	3.40	4.07	4.49	5.17	6.68	17.66	18.32	18.75	19.42	20.94
	4H	3.69	4.33	4.80	5.43	6.95	18.28	18.92	19.39	20.02	21.54
	6H	3.93	4.52	5.05	5.62	7.16	18.70	19.28	19.81	20.39	21.92
	8H	4.00	4.56	5.12	5.68	7.20	18.81	19.37	19.93	20.48	22.01
	12H	4.01	4.54	5.14	5.66	7.21	18.86	19.39	19.99	20.51	22.06
4H	2H	9.88	10.51	10.99	11.61	13.13	16.10	16.74	17.22	17.84	19.36
	3H	11.44	11.97	12.56	13.09	14.63	18.12	18.65	19.24	19.78	21.31
	4H	11.53	12.02	12.65	13.13	14.69	18.87	19.36	20.00	20.48	22.03
	6H	11.53	11.95	12.66	13.09	14.64	19.39	19.81	20.53	20.95	22.50
	8H	11.50	11.90	12.64	13.03	14.59	19.54	19.94	20.68	21.07	22.63
	12H	11.46	11.81	12.60	12.95	14.52	19.62	19.98	20.77	21.12	22.69
8H	4H	12.95	13.34	14.08	14.47	16.04	18.92	19.32	20.06	20.45	22.01
	6H	13.19	13.51	14.34	14.69	16.24	19.54	19.86	20.69	21.03	22.59
	8H	13.20	13.49	14.36	14.64	16.22	19.75	20.03	20.91	21.18	22.76
	12H	13.17	13.42	14.33	14.57	16.18	19.88	20.13	21.04	21.28	22.89
12H	4H	13.09	13.44	14.23	14.58	16.15	18.87	19.23	20.02	20.37	21.94
	6H	13.44	13.73	14.60	14.88	16.46	19.52	19.80	20.68	20.95	22.53
	8H	13.50	13.75	14.67	14.90	16.52	19.73	19.98	20.90	21.13	22.75