

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934180

Luminaire Tested: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934180
REPORT IS A COMBINATION OF REPORTS P933685 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16060.2 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 148.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	86	86	86	86	86	83
1	105	101	97	93	101	97	93	90	89	87	84	83	80	78	76	75	73	73	73	70
2	96	88	82	76	92	85	79	74	78	74	70	73	69	66	67	64	62	62	62	59
3	88	78	70	64	84	75	68	62	69	63	59	64	60	56	60	56	52	52	52	50
4	80	69	60	54	77	66	59	53	62	55	50	57	52	48	53	49	45	45	45	43
5	74	61	53	46	70	59	51	45	55	49	43	52	46	41	48	43	39	39	39	37
6	68	55	47	40	65	53	45	40	50	43	38	47	41	36	44	39	35	35	35	32
7	63	50	42	36	60	48	41	35	45	39	34	42	37	32	40	35	31	31	31	29
8	59	46	37	32	56	44	36	31	41	35	30	39	33	29	37	31	28	28	28	26
9	55	42	34	28	52	40	33	28	38	32	27	36	30	26	34	29	25	25	25	23
10	51	38	31	26	49	37	30	25	35	29	24	33	28	24	31	26	23	23	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15850	15850	15850	15850
5°	15975	16000	15975	12581
10°	15874	15761	15874	11268
15°	15707	15419	15707	12876
20°	15385	15015	15385	12902
25°	14718	14425	14718	12629
30°	13855	13935	13855	12029
35°	12358	13316	12358	11369
40°	10303	12586	10303	10870
45°	9212	11732	9212	10297
50°	9794	10714	9794	9722
55°	9223	9617	9223	9390
60°	9520	8168	9520	8600
65°	8645	6752	8645	7547
70°	6000	5381	6000	6326
75°	5282	3977	5282	4763
80°	4288	2629	4288	2863
85°	2511	1393	2511	1184

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 14110 cd/sqm

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	462.6	2.9
10°-20°	1313.4	8.2
20°-30°	2030.3	12.6
30°-40°	2423.7	15.1
40°-50°	2437.9	15.2
50°-60°	2121.3	13.2
60°-70°	1504.0	9.4
70°-80°	795.7	5.0
80°-90°	199.8	1.2
90°-100°	208.4	1.3
100°-110°	547.9	3.4
110°-120°	568.1	3.5
120°-130°	455.7	2.8
130°-140°	357.6	2.2
140°-150°	274.5	1.7
150°-160°	197.7	1.2
160°-170°	120.9	0.8
170°-180°	40.9	0.3
0°-30°	3806.2	23.7
0°-40°	6229.9	38.8
0°-60°	10789.0	67.2
0°-90°	13288.6	82.7
90°-120°	1324.5	8.2
90°-150°	2412.2	15.0
90°-180°	2772.0	17.3
0°-180°	16060.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5124	5124	5124	5124	5124	
5°	5149	5309	5149	4174	5149	488
15°	4916	5260	4916	4392	4916	1383
25°	4329	4906	4329	4296	4329	1988
35°	3292	4378	3292	3738	3292	2037
45°	2123	3607	2123	3166	2123	1701
55°	1731	2662	1731	2599	1731	1590
65°	1202	1605	1202	1794	1202	1149
75°	456	761	456	912	456	479
85°	78	194	78	165	78	105
90°	3	11	3	11	3	6
95°	28	126	28	126	28	31
105°	99	858	99	858	99	105
115°	175	1105	175	1105	175	173
125°	244	880	244	880	244	217
135°	291	683	291	683	291	225
145°	337	554	337	554	337	211
155°	381	477	381	477	381	175
165°	411	444	411	444	411	116
175°	428	430	428	430	428	41
180°	428	428	428	428	428	

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	5168.2	5168.2	5197.2	5206.9	5206.9	5192.3	5177.8	5192.3	5236.0	5250.6	5245.7
5°	5148.7	5187.6	5240.8	5250.6	5260.2	5255.4	5245.7	5255.4	5303.9	5313.6	5318.4
7.5°	5109.9	5182.7	5250.6	5265.1	5279.6	5265.1	5260.2	5270.0	5318.4	5328.1	5328.1
10°	5061.5	5163.3	5240.8	5250.6	5265.1	5250.6	5250.6	5270.0	5318.4	5328.1	5333.0
12.5°	4993.6	5134.2	5206.9	5216.6	5236.0	5231.1	5226.3	5245.7	5294.1	5303.9	5303.9
15°	4916.1	5080.9	5148.7	5158.4	5192.3	5182.7	5182.7	5202.1	5255.4	5270.0	5265.1
17.5°	4809.4	5013.0	5090.5	5105.1	5129.3	5124.5	5129.3	5148.7	5197.2	5206.9	5211.7
20°	4688.2	4920.8	5013.0	5027.5	5051.8	5051.8	5051.8	5076.0	5124.5	5143.9	5143.9
22.5°	4523.4	4823.9	4920.8	4930.6	4959.7	4959.7	4969.3	5003.2	5046.9	5051.8	5051.8
25°	4329.4	4717.2	4799.6	4828.8	4857.9	4872.4	4886.9	4906.3	4920.8	4916.1	4920.8
27.5°	4125.8	4581.5	4688.2	4707.6	4746.3	4760.9	4780.3	4785.1	4790.0	4804.5	4794.9
30°	3897.9	4392.4	4552.4	4571.8	4634.8	4644.5	4625.2	4634.8	4659.1	4668.8	4678.4
32.5°	3640.9	4111.3	4411.8	4455.5	4513.6	4484.6	4479.7	4494.2	4533.0	4533.0	4542.7
35°	3291.9	3893.1	4280.9	4319.7	4363.3	4329.4	4348.8	4353.7	4377.9	4392.4	4387.6
37.5°	2908.9	3704.0	4145.2	4174.3	4208.2	4164.6	4193.7	4208.2	4227.6	4217.9	4217.9
40°	2569.5	3408.2	3985.2	4004.6	4033.6	3999.7	4028.9	4038.5	4048.2	4038.5	4033.6
42.5°	2317.4	3083.4	3815.5	3839.8	3820.4	3844.5	3854.3	3873.7	3859.2	3839.8	3839.8
45°	2123.4	2996.1	3631.3	3660.3	3631.3	3670.1	3684.6	3684.6	3640.9	3631.3	3626.4
47.5°	2060.5	2821.6	3447.1	3447.1	3432.5	3481.0	3505.2	3471.2	3427.7	3413.1	3413.1
50°	2055.6	2627.7	3195.0	3175.6	3243.4	3301.6	3277.4	3243.4	3209.5	3156.2	3156.2
52.5°	1866.5	2390.2	2870.1	2942.8	3049.5	3083.4	3044.6	3010.7	2952.5	2928.3	2908.9
55°	1730.7	2142.9	2574.4	2719.8	2831.3	2874.9	2802.3	2768.3	2681.1	2666.5	2656.8
57.5°	1701.7	1784.1	2302.9	2487.1	2622.8	2618.0	2574.4	2511.4	2438.6	2424.1	2419.2
60°	1561.1	1289.6	2012.0	2230.1	2370.8	2356.2	2317.4	2259.2	2191.3	2181.7	2172.0
62.5°	1415.7	935.7	1682.3	1929.6	2128.3	2123.4	2089.5	2002.3	1953.8	1929.6	1910.2
65°	1202.3	785.4	1197.5	1604.8	1890.8	1900.4	1827.8	1764.7	1711.4	1682.3	1677.5
67.5°	916.3	639.9	809.6	1338.1	1662.9	1653.2	1561.1	1532.0	1464.1	1449.6	1420.5
70°	678.7	426.6	562.4	1086.0	1439.9	1415.7	1342.9	1309.0	1246.0	1212.0	1192.6
72.5°	562.4	344.2	412.1	843.6	1212.0	1183.0	1119.9	1081.2	1027.8	998.7	979.4
75°	455.7	363.6	315.2	625.4	984.1	964.7	906.6	867.8	824.2	785.4	790.3
77.5°	334.5	339.4	252.1	460.6	780.5	751.5	717.5	669.1	649.7	610.9	610.9
80°	252.1	266.6	189.1	315.2	562.4	562.4	533.3	499.4	465.5	446.0	446.0
82.5°	169.7	169.7	140.6	198.7	383.1	368.4	349.1	339.4	320.0	310.3	310.3
85°	77.5	96.9	87.3	121.2	208.5	218.1	218.1	208.5	203.6	194.0	198.7
87.5°	24.3	43.6	53.3	67.9	106.7	111.5	116.3	116.3	116.3	121.2	121.2
90°	2.9	5.2	7.4	8.0	12.6	18.7	21.8	19.4	14.5	10.9	10.9
92.5°	11.5	30.9	50.5	55.4	77.8	107.8	122.8	107.6	77.3	54.5	52.3
95°	27.5	63.2	98.9	107.9	191.6	303.2	359.0	320.3	243.0	185.1	178.5
97.5°	47.7	79.2	110.7	118.5	258.0	444.2	537.2	512.7	463.9	427.3	414.8
100°	63.1	91.7	120.2	127.4	282.3	488.8	592.0	593.8	597.4	600.0	585.1
102.5°	76.3	102.9	129.6	136.3	293.4	502.8	607.5	638.6	700.8	747.5	734.7
105°	98.7	121.3	143.8	149.5	301.6	504.3	605.8	675.5	815.0	919.7	912.8
107.5°	121.7	142.7	163.8	169.0	303.1	481.9	571.3	668.6	863.2	1009.2	1010.9
110°	137.1	156.1	175.1	179.9	300.8	462.0	542.6	651.4	869.0	1032.2	1039.3

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	152.4	170.5	188.6	193.1	300.9	444.6	516.6	627.9	850.5	1017.6	1028.5
115°	175.3	192.1	208.8	213.0	303.7	424.7	485.2	592.5	807.0	967.9	983.1
117.5°	198.0	213.2	228.3	232.2	309.3	412.3	463.7	560.6	754.2	899.3	916.2
120°	211.2	225.5	239.8	243.3	313.9	408.0	455.1	543.5	720.5	853.1	869.5
122.5°	224.1	238.6	252.9	256.5	320.5	405.8	448.5	528.1	687.4	806.9	823.0
125°	243.9	257.1	270.3	273.5	329.5	404.1	441.3	508.9	644.2	745.8	760.7
127.5°	260.0	273.2	286.5	289.8	338.4	403.0	435.3	493.4	609.6	696.7	709.3
130°	268.5	282.9	297.2	300.7	344.9	403.6	433.0	484.8	588.2	665.7	677.4
132.5°	277.5	291.8	306.1	309.6	350.1	404.1	431.0	477.3	569.9	639.4	649.8
135°	290.7	303.7	316.7	319.9	355.8	403.7	427.6	466.3	543.9	602.0	611.0
137.5°	304.2	317.1	329.9	333.1	364.4	406.2	427.0	459.7	525.2	574.4	581.8
140°	315.3	327.2	339.1	342.1	369.7	406.5	425.0	453.2	509.9	552.4	559.2
142.5°	323.9	334.9	345.9	348.7	374.1	408.0	425.0	449.8	499.6	536.9	542.8
145°	337.2	346.8	356.3	358.7	379.8	408.0	422.1	442.5	483.1	513.6	518.1
147.5°	350.4	359.7	369.0	371.3	388.2	410.8	422.1	438.2	470.1	494.1	497.8
150°	359.0	367.4	375.8	377.9	392.6	412.3	422.1	435.7	462.7	482.9	485.9
152.5°	367.9	374.3	380.6	382.2	395.5	413.2	422.1	433.7	456.8	474.1	476.4
155°	381.0	385.7	390.5	391.6	401.8	415.3	422.1	431.3	449.7	463.5	465.0
157.5°	390.8	395.4	400.0	401.2	408.2	417.4	422.1	429.3	443.5	454.2	455.2
160°	397.5	401.0	404.6	405.5	411.0	418.4	422.1	428.2	440.4	449.6	450.2
162.5°	404.1	406.7	409.4	410.1	414.1	419.4	422.1	427.3	437.6	445.3	445.9
165°	411.2	413.6	416.1	416.7	418.5	420.9	422.1	425.8	433.2	438.7	439.3
167.5°	417.8	419.0	420.1	420.4	421.9	423.9	425.0	427.4	432.2	435.9	436.1
170°	422.1	423.3	424.4	424.7	424.8	424.9	425.0	427.4	432.2	435.9	435.9
172.5°	424.4	424.7	424.9	425.0	425.0	425.0	425.0	426.9	430.7	433.6	433.4
175°	427.6	427.6	427.6	427.6	426.7	425.5	425.0	426.2	428.6	430.4	430.4
177.5°	427.6	427.6	427.6	427.6	426.9	426.0	425.5	426.5	428.4	429.8	429.6
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	5255.4	5240.8	5255.4	5245.7	5250.6	5236.0	5192.3	5177.8	5192.3	5206.9	5206.9
5°	5318.4	5308.7	5318.4	5318.4	5313.6	5303.9	5255.4	5245.7	5255.4	5260.2	5250.6
7.5°	5337.8	5323.3	5337.8	5328.1	5328.1	5318.4	5270.0	5260.2	5265.1	5279.6	5265.1
10°	5337.8	5323.3	5337.8	5333.0	5328.1	5318.4	5270.0	5250.6	5250.6	5265.1	5250.6
12.5°	5313.6	5303.9	5313.6	5303.9	5303.9	5294.1	5245.7	5226.3	5231.1	5236.0	5216.6
15°	5274.8	5260.2	5274.8	5265.1	5270.0	5255.4	5202.1	5182.7	5182.7	5192.3	5158.4
17.5°	5216.6	5197.2	5216.6	5211.7	5206.9	5197.2	5148.7	5129.3	5124.5	5129.3	5105.1
20°	5148.7	5134.2	5148.7	5143.9	5143.9	5124.5	5076.0	5051.8	5051.8	5051.8	5027.5
22.5°	5042.1	5027.5	5042.1	5051.8	5051.8	5046.9	5003.2	4969.3	4959.7	4959.7	4930.6
25°	4920.8	4906.3	4920.8	4920.8	4916.1	4920.8	4906.3	4886.9	4872.4	4857.9	4828.8
27.5°	4804.5	4794.9	4804.5	4794.9	4804.5	4790.0	4785.1	4780.3	4760.9	4746.3	4707.6
30°	4688.2	4678.4	4688.2	4678.4	4668.8	4659.1	4634.8	4625.2	4644.5	4634.8	4571.8
32.5°	4542.7	4533.0	4542.7	4542.7	4533.0	4533.0	4494.2	4479.7	4484.6	4513.6	4455.5
35°	4392.4	4377.9	4392.4	4387.6	4392.4	4377.9	4353.7	4348.8	4329.4	4363.3	4319.7
37.5°	4217.9	4203.3	4217.9	4217.9	4217.9	4227.6	4208.2	4193.7	4164.6	4208.2	4174.3
40°	4038.5	4019.1	4038.5	4033.6	4038.5	4048.2	4038.5	4028.9	3999.7	4033.6	4004.6
42.5°	3834.9	3830.0	3834.9	3839.8	3839.8	3859.2	3873.7	3854.3	3844.5	3820.4	3839.8
45°	3616.7	3607.0	3616.7	3626.4	3631.3	3640.9	3684.6	3684.6	3670.1	3631.3	3660.3
47.5°	3384.0	3359.8	3384.0	3413.1	3413.1	3427.7	3471.2	3505.2	3481.0	3432.5	3447.1
50°	3136.8	3141.6	3136.8	3156.2	3156.2	3209.5	3243.4	3277.4	3301.6	3243.4	3175.6
52.5°	2894.3	2889.5	2894.3	2908.9	2928.3	2952.5	3010.7	3044.6	3083.4	3049.5	2942.8
55°	2651.9	2661.7	2651.9	2656.8	2666.5	2681.1	2768.3	2802.3	2874.9	2831.3	2719.8
57.5°	2409.6	2394.9	2409.6	2419.2	2424.1	2438.6	2511.4	2574.4	2618.0	2622.8	2487.1
60°	2128.3	2108.9	2128.3	2172.0	2181.7	2191.3	2259.2	2317.4	2356.2	2370.8	2230.1
62.5°	1881.1	1847.2	1881.1	1910.2	1929.6	1953.8	2002.3	2089.5	2123.4	2128.3	1929.6
65°	1619.3	1604.8	1619.3	1677.5	1682.3	1711.4	1764.7	1827.8	1900.4	1890.8	1604.8
67.5°	1381.7	1381.7	1381.7	1420.5	1449.6	1464.1	1532.0	1561.1	1653.2	1662.9	1338.1
70°	1163.6	1158.7	1163.6	1192.6	1212.0	1246.0	1309.0	1342.9	1415.7	1439.9	1086.0
72.5°	955.1	950.2	955.1	979.4	998.7	1027.8	1081.2	1119.9	1183.0	1212.0	843.6
75°	770.9	761.1	770.9	790.3	785.4	824.2	867.8	906.6	964.7	984.1	625.4
77.5°	591.4	591.4	591.4	610.9	610.9	649.7	669.1	717.5	751.5	780.5	460.6
80°	441.2	436.3	441.2	446.0	446.0	465.5	499.4	533.3	562.4	562.4	315.2
82.5°	310.3	300.5	310.3	310.3	310.3	320.0	339.4	349.1	368.4	383.1	198.7
85°	194.0	194.0	194.0	198.7	194.0	203.6	208.5	218.1	218.1	208.5	121.2
87.5°	126.1	121.2	126.1	121.2	121.2	116.3	116.3	116.3	111.5	106.7	67.9
90°	10.9	10.9	10.9	10.9	10.9	14.5	19.4	21.8	18.7	12.6	8.0
92.5°	43.7	35.0	43.7	52.3	54.5	77.3	107.6	122.8	107.8	77.8	55.4
95°	152.2	126.0	152.2	178.5	185.1	243.0	320.3	359.0	303.2	191.6	107.9
97.5°	364.8	314.8	364.8	414.8	427.3	463.9	512.7	537.2	444.2	258.0	118.5
100°	525.6	466.0	525.6	585.1	600.0	597.4	593.8	592.0	488.8	282.3	127.4
102.5°	683.7	632.7	683.7	734.7	747.5	700.8	638.6	607.5	502.8	293.4	136.3
105°	885.4	858.0	885.4	912.8	919.7	815.0	675.5	605.8	504.3	301.6	149.5
107.5°	1017.6	1024.1	1017.6	1010.9	1009.2	863.2	668.6	571.3	481.9	303.1	169.0
110°	1067.9	1096.4	1067.9	1039.3	1032.2	869.0	651.4	542.6	462.0	300.8	179.9

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1072.4	1116.2	1072.4	1028.5	1017.6	850.5	627.9	516.6	444.6	300.9	193.1
115°	1043.9	1104.7	1043.9	983.1	967.9	807.0	592.5	485.2	424.7	303.7	213.0
117.5°	983.6	1051.1	983.6	916.2	899.3	754.2	560.6	463.7	412.3	309.3	232.2
120°	935.0	1000.6	935.0	869.5	853.1	720.5	543.5	455.1	408.0	313.9	243.3
122.5°	887.8	952.4	887.8	823.0	806.9	687.4	528.1	448.5	405.8	320.5	256.5
125°	820.2	879.7	820.2	760.7	745.8	644.2	508.9	441.3	404.1	329.5	273.5
127.5°	759.5	809.7	759.5	709.3	696.7	609.6	493.4	435.3	403.0	338.4	289.8
130°	723.8	770.2	723.8	677.4	665.7	588.2	484.8	433.0	403.6	344.9	300.7
132.5°	691.3	732.9	691.3	649.8	639.4	569.9	477.3	431.0	404.1	350.1	309.6
135°	646.8	682.6	646.8	611.0	602.0	543.9	466.3	427.6	403.7	355.8	319.9
137.5°	611.1	640.5	611.1	581.8	574.4	525.2	459.7	427.0	406.2	364.4	333.1
140°	586.7	614.1	586.7	559.2	552.4	509.9	453.2	425.0	406.5	369.7	342.1
142.5°	566.4	590.0	566.4	542.8	536.9	499.6	449.8	425.0	408.0	374.1	348.7
145°	535.9	553.8	535.9	518.1	513.6	483.1	442.5	422.1	408.0	379.8	358.7
147.5°	512.6	527.4	512.6	497.8	494.1	470.1	438.2	422.1	410.8	388.2	371.3
150°	497.9	509.9	497.9	485.9	482.9	462.7	435.7	422.1	412.3	392.6	377.9
152.5°	485.3	494.4	485.3	476.4	474.1	456.8	433.7	422.1	413.2	395.5	382.2
155°	470.9	476.9	470.9	465.0	463.5	449.7	431.3	422.1	415.3	401.8	391.6
157.5°	459.5	463.7	459.5	455.2	454.2	443.5	429.3	422.1	417.4	408.2	401.2
160°	452.7	455.1	452.7	450.2	449.6	440.4	428.2	422.1	418.4	411.0	405.5
162.5°	448.2	450.5	448.2	445.9	445.3	437.6	427.3	422.1	419.4	414.1	410.1
165°	441.8	444.2	441.8	439.3	438.7	433.2	425.8	422.1	420.9	418.5	416.7
167.5°	437.1	438.2	437.1	436.1	435.9	432.2	427.4	425.0	423.9	421.9	420.4
170°	435.9	435.9	435.9	435.9	435.9	432.2	427.4	425.0	424.9	424.8	424.7
172.5°	432.4	431.6	432.4	433.4	433.6	430.7	426.9	425.0	425.0	425.0	425.0
175°	430.4	430.4	430.4	430.4	430.4	428.6	426.2	425.0	425.5	426.7	427.6
177.5°	428.6	427.6	428.6	429.6	429.8	428.4	426.5	425.5	426.0	426.9	427.6
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	5197.2	5168.2	5168.2	5119.7	5100.3	5085.8	5061.5	4988.7	4969.3	4950.0	4979.1
5°	5240.8	5187.6	5148.7	5061.5	4988.7	4959.7	4867.5	4693.0	4576.6	4489.4	4440.9
7.5°	5250.6	5182.7	5109.9	4974.2	4799.6	4722.1	4440.9	4120.9	4033.6	3956.1	3907.6
10°	5240.8	5163.3	5061.5	4857.9	4445.7	4310.0	4028.9	3820.4	3767.0	3752.5	3767.0
12.5°	5206.9	5134.2	4993.6	4654.2	4077.3	3985.2	3820.4	3699.1	3689.5	3713.7	3844.5
15°	5148.7	5080.9	4916.1	4382.7	3873.7	3805.8	3689.5	3645.8	3699.1	3868.8	4261.5
17.5°	5090.5	5013.0	4809.4	4116.0	3718.6	3670.1	3587.6	3674.9	3975.5	4203.3	4334.3
20°	5013.0	4920.8	4688.2	3922.2	3607.0	3563.4	3524.6	3917.3	4145.2	4227.6	4300.3
22.5°	4920.8	4823.9	4523.4	3786.4	3490.7	3456.7	3481.0	4053.0	4145.2	4203.3	4266.4
25°	4799.6	4717.2	4329.4	3679.7	3398.6	3359.8	3451.8	4038.5	4091.8	4106.4	4232.5
27.5°	4688.2	4581.5	4125.8	3582.8	3287.0	3272.5	3476.1	3975.5	4014.2	4028.9	4164.6
30°	4552.4	4392.4	3897.9	3481.0	3170.7	3165.8	3481.0	3897.9	3888.2	3927.0	4062.8
32.5°	4411.8	4111.3	3640.9	3354.9	3059.2	3054.4	3447.1	3781.5	3771.9	3825.2	3927.0
35°	4280.9	3893.1	3291.9	3209.5	2918.6	2923.4	3364.7	3645.8	3650.7	3699.1	3762.1
37.5°	4145.2	3704.0	2908.9	3049.5	2782.9	2782.9	3253.1	3519.7	3510.1	3524.6	3611.9
40°	3985.2	3408.2	2569.5	2841.0	2656.8	2642.2	3117.4	3384.0	3350.0	3345.3	3466.5
42.5°	3815.5	3083.4	2317.4	2564.7	2511.4	2492.0	2952.5	3219.2	3156.2	3170.7	3325.8
45°	3631.3	2996.1	2123.4	2167.1	2361.0	2346.5	2773.1	3030.1	2986.5	3025.2	3185.2
47.5°	3447.1	2821.6	2060.5	1798.6	2201.1	2196.2	2574.4	2845.9	2821.6	2860.4	3030.1
50°	3195.0	2627.7	2055.6	1541.8	2021.6	2041.0	2336.8	2666.5	2666.5	2700.5	2879.8
52.5°	2870.1	2390.2	1866.5	1396.3	1813.2	1871.4	2128.3	2511.4	2521.0	2555.0	2715.0
55°	2574.4	2142.9	1730.7	1284.8	1565.9	1692.0	1924.7	2351.3	2370.8	2404.7	2550.1
57.5°	2302.9	1784.1	1701.7	1153.8	1338.1	1459.3	1745.4	2196.2	2206.0	2235.0	2375.6
60°	2012.0	1289.6	1561.1	1013.3	1139.3	1231.5	1580.5	2012.0	2045.9	2065.3	2186.5
62.5°	1682.3	935.7	1415.7	916.3	1042.4	1061.8	1444.7	1837.4	1881.1	1895.6	1968.4
65°	1197.5	785.4	1202.3	833.9	940.6	945.4	1299.3	1658.1	1696.8	1721.1	1774.4
67.5°	809.6	639.9	916.3	756.3	862.9	867.8	1158.7	1449.6	1502.9	1522.4	1556.3
70°	562.4	426.6	678.7	673.8	775.7	785.4	1008.4	1260.5	1309.0	1323.5	1342.9
72.5°	412.1	344.2	562.4	606.0	683.6	693.3	853.3	1047.2	1095.7	1110.2	1119.9
75°	315.2	363.6	455.7	528.4	581.8	586.7	698.1	853.3	887.2	896.9	901.7
77.5°	252.1	339.4	334.5	426.6	475.1	465.5	547.9	659.3	688.5	688.5	688.5
80°	189.1	266.6	252.1	305.4	349.1	339.4	392.7	470.2	480.0	489.6	484.9
82.5°	140.6	169.7	169.7	194.0	232.7	223.0	261.8	305.4	305.4	305.4	315.2
85°	87.3	96.9	77.5	101.8	130.9	126.1	145.4	164.8	169.7	169.7	160.0
87.5°	53.3	43.6	24.3	38.8	58.2	58.2	67.9	72.7	67.9	67.9	67.9
90°	7.4	5.2	2.9	5.2	7.4	8.0	12.6	18.7	21.8	19.4	14.5
92.5°	50.5	30.9	11.5	30.9	50.5	55.4	77.8	107.8	122.8	107.6	77.3
95°	98.9	63.2	27.5	63.2	98.9	107.9	191.6	303.2	359.0	320.3	243.0
97.5°	110.7	79.2	47.7	79.2	110.7	118.5	258.0	444.2	537.2	512.7	463.9
100°	120.2	91.7	63.1	91.7	120.2	127.4	282.3	488.8	592.0	593.8	597.4
102.5°	129.6	102.9	76.3	102.9	129.6	136.3	293.4	502.8	607.5	638.6	700.8
105°	143.8	121.3	98.7	121.3	143.8	149.5	301.6	504.3	605.8	675.5	815.0
107.5°	163.8	142.7	121.7	142.7	163.8	169.0	303.1	481.9	571.3	668.6	863.2
110°	175.1	156.1	137.1	156.1	175.1	179.9	300.8	462.0	542.6	651.4	869.0

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	188.6	170.5	152.4	170.5	188.6	193.1	300.9	444.6	516.6	627.9	850.5
115°	208.8	192.1	175.3	192.1	208.8	213.0	303.7	424.7	485.2	592.5	807.0
117.5°	228.3	213.2	198.0	213.2	228.3	232.2	309.3	412.3	463.7	560.6	754.2
120°	239.8	225.5	211.2	225.5	239.8	243.3	313.9	408.0	455.1	543.5	720.5
122.5°	252.9	238.6	224.1	238.6	252.9	256.5	320.5	405.8	448.5	528.1	687.4
125°	270.3	257.1	243.9	257.1	270.3	273.5	329.5	404.1	441.3	508.9	644.2
127.5°	286.5	273.2	260.0	273.2	286.5	289.8	338.4	403.0	435.3	493.4	609.6
130°	297.2	282.9	268.5	282.9	297.2	300.7	344.9	403.6	433.0	484.8	588.2
132.5°	306.1	291.8	277.5	291.8	306.1	309.6	350.1	404.1	431.0	477.3	569.9
135°	316.7	303.7	290.7	303.7	316.7	319.9	355.8	403.7	427.6	466.3	543.9
137.5°	329.9	317.1	304.2	317.1	329.9	333.1	364.4	406.2	427.0	459.7	525.2
140°	339.1	327.2	315.3	327.2	339.1	342.1	369.7	406.5	425.0	453.2	509.9
142.5°	345.9	334.9	323.9	334.9	345.9	348.7	374.1	408.0	425.0	449.8	499.6
145°	356.3	346.8	337.2	346.8	356.3	358.7	379.8	408.0	422.1	442.5	483.1
147.5°	369.0	359.7	350.4	359.7	369.0	371.3	388.2	410.8	422.1	438.2	470.1
150°	375.8	367.4	359.0	367.4	375.8	377.9	392.6	412.3	422.1	435.7	462.7
152.5°	380.6	374.3	367.9	374.3	380.6	382.2	395.5	413.2	422.1	433.7	456.8
155°	390.5	385.7	381.0	385.7	390.5	391.6	401.8	415.3	422.1	431.3	449.7
157.5°	400.0	395.4	390.8	395.4	400.0	401.2	408.2	417.4	422.1	429.3	443.5
160°	404.6	401.0	397.5	401.0	404.6	405.5	411.0	418.4	422.1	428.2	440.4
162.5°	409.4	406.7	404.1	406.7	409.4	410.1	414.1	419.4	422.1	427.3	437.6
165°	416.1	413.6	411.2	413.6	416.1	416.7	418.5	420.9	422.1	425.8	433.2
167.5°	420.1	419.0	417.8	419.0	420.1	420.4	421.9	423.9	425.0	427.4	432.2
170°	424.4	423.3	422.1	423.3	424.4	424.7	424.8	424.9	425.0	427.4	432.2
172.5°	424.9	424.7	424.4	424.7	424.9	425.0	425.0	425.0	425.0	426.9	430.7
175°	427.6	427.6	427.6	427.6	427.6	427.6	426.7	425.5	425.0	426.2	428.6
177.5°	427.6	427.6	427.6	427.6	427.6	427.6	426.9	426.0	425.5	426.5	428.4
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	4945.1	4930.6	4950.0	4896.7	4950.0	4930.6	4945.1	4979.1	4950.0	4969.3	4988.7
5°	4339.1	4314.9	4237.2	4174.3	4237.2	4314.9	4339.1	4440.9	4489.4	4576.6	4693.0
7.5°	3878.5	3859.2	3839.8	3801.0	3839.8	3859.2	3878.5	3907.6	3956.1	4033.6	4120.9
10°	3776.7	3781.5	3810.6	3805.8	3810.6	3781.5	3776.7	3767.0	3752.5	3767.0	3820.4
12.5°	4038.5	4082.1	4242.1	4232.5	4242.1	4082.1	4038.5	3844.5	3713.7	3689.5	3699.1
15°	4339.1	4353.7	4387.6	4392.4	4387.6	4353.7	4339.1	4261.5	3868.8	3699.1	3645.8
17.5°	4368.2	4373.0	4397.3	4397.3	4397.3	4373.0	4368.2	4334.3	4203.3	3975.5	3674.9
20°	4343.9	4353.7	4402.2	4411.8	4402.2	4353.7	4343.9	4300.3	4227.6	4145.2	3917.3
22.5°	4334.3	4353.7	4392.4	4387.6	4392.4	4353.7	4334.3	4266.4	4203.3	4145.2	4053.0
25°	4285.8	4285.8	4290.6	4295.5	4290.6	4285.8	4285.8	4232.5	4106.4	4091.8	4038.5
27.5°	4184.0	4193.7	4222.7	4217.9	4222.7	4193.7	4184.0	4164.6	4028.9	4014.2	3975.5
30°	4091.8	4082.1	4057.9	4038.5	4057.9	4082.1	4091.8	4062.8	3927.0	3888.2	3897.9
32.5°	3936.7	3912.4	3888.2	3873.7	3888.2	3912.4	3936.7	3927.0	3825.2	3771.9	3781.5
35°	3752.5	3757.4	3752.5	3738.0	3752.5	3757.4	3752.5	3762.1	3699.1	3650.7	3645.8
37.5°	3621.6	3631.3	3626.4	3607.0	3626.4	3631.3	3621.6	3611.9	3524.6	3510.1	3519.7
40°	3485.8	3490.7	3485.8	3471.2	3485.8	3490.7	3485.8	3466.5	3345.3	3350.0	3384.0
42.5°	3354.9	3350.0	3335.5	3325.8	3335.5	3350.0	3354.9	3325.8	3170.7	3156.2	3219.2
45°	3204.6	3209.5	3180.3	3165.8	3180.3	3209.5	3204.6	3185.2	3025.2	2986.5	3030.1
47.5°	3054.4	3054.4	3030.1	3015.5	3030.1	3054.4	3054.4	3030.1	2860.4	2821.6	2845.9
50°	2894.3	2889.5	2855.5	2850.7	2855.5	2889.5	2894.3	2879.8	2700.5	2666.5	2666.5
52.5°	2710.1	2710.1	2715.0	2724.6	2715.0	2710.1	2710.1	2715.0	2555.0	2521.0	2511.4
55°	2550.1	2555.0	2588.9	2598.7	2588.9	2555.0	2550.1	2550.1	2404.7	2370.8	2351.3
57.5°	2385.3	2385.3	2409.6	2409.6	2409.6	2385.3	2385.3	2375.6	2235.0	2206.0	2196.2
60°	2196.2	2206.0	2225.3	2220.5	2225.3	2206.0	2196.2	2186.5	2065.3	2045.9	2012.0
62.5°	1997.5	2007.1	2012.0	2002.3	2012.0	2007.1	1997.5	1968.4	1895.6	1881.1	1837.4
65°	1789.0	1798.6	1803.5	1793.8	1803.5	1798.6	1789.0	1774.4	1721.1	1696.8	1658.1
67.5°	1575.7	1570.8	1565.9	1585.3	1565.9	1570.8	1575.7	1556.3	1522.4	1502.9	1449.6
70°	1357.4	1357.4	1352.7	1362.3	1352.7	1357.4	1357.4	1342.9	1323.5	1309.0	1260.5
72.5°	1124.8	1119.9	1139.3	1124.8	1139.3	1119.9	1124.8	1119.9	1110.2	1095.7	1047.2
75°	896.9	906.6	896.9	911.5	896.9	906.6	896.9	901.7	896.9	887.2	853.3
77.5°	683.6	693.3	683.6	683.6	683.6	693.3	683.6	688.5	688.5	688.5	659.3
80°	484.9	480.0	480.0	475.1	480.0	480.0	484.9	484.9	489.6	480.0	470.2
82.5°	310.3	305.4	305.4	315.2	305.4	305.4	310.3	315.2	305.4	305.4	305.4
85°	169.7	174.6	164.8	164.8	164.8	174.6	169.7	160.0	169.7	169.7	164.8
87.5°	63.0	58.2	58.2	58.2	58.2	58.2	63.0	67.9	67.9	67.9	72.7
90°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	14.5	19.4	21.8	18.7
92.5°	54.5	52.3	43.7	35.0	43.7	52.3	54.5	77.3	107.6	122.8	107.8
95°	185.1	178.5	152.2	126.0	152.2	178.5	185.1	243.0	320.3	359.0	303.2
97.5°	427.3	414.8	364.8	314.8	364.8	414.8	427.3	463.9	512.7	537.2	444.2
100°	600.0	585.1	525.6	466.0	525.6	585.1	600.0	597.4	593.8	592.0	488.8
102.5°	747.5	734.7	683.7	632.7	683.7	734.7	747.5	700.8	638.6	607.5	502.8
105°	919.7	912.8	885.4	858.0	885.4	912.8	919.7	815.0	675.5	605.8	504.3
107.5°	1009.2	1010.9	1017.6	1024.1	1017.6	1010.9	1009.2	863.2	668.6	571.3	481.9
110°	1032.2	1039.3	1067.9	1096.4	1067.9	1039.3	1032.2	869.0	651.4	542.6	462.0

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1017.6	1028.5	1072.4	1116.2	1072.4	1028.5	1017.6	850.5	627.9	516.6	444.6
115°	967.9	983.1	1043.9	1104.7	1043.9	983.1	967.9	807.0	592.5	485.2	424.7
117.5°	899.3	916.2	983.6	1051.1	983.6	916.2	899.3	754.2	560.6	463.7	412.3
120°	853.1	869.5	935.0	1000.6	935.0	869.5	853.1	720.5	543.5	455.1	408.0
122.5°	806.9	823.0	887.8	952.4	887.8	823.0	806.9	687.4	528.1	448.5	405.8
125°	745.8	760.7	820.2	879.7	820.2	760.7	745.8	644.2	508.9	441.3	404.1
127.5°	696.7	709.3	759.5	809.7	759.5	709.3	696.7	609.6	493.4	435.3	403.0
130°	665.7	677.4	723.8	770.2	723.8	677.4	665.7	588.2	484.8	433.0	403.6
132.5°	639.4	649.8	691.3	732.9	691.3	649.8	639.4	569.9	477.3	431.0	404.1
135°	602.0	611.0	646.8	682.6	646.8	611.0	602.0	543.9	466.3	427.6	403.7
137.5°	574.4	581.8	611.1	640.5	611.1	581.8	574.4	525.2	459.7	427.0	406.2
140°	552.4	559.2	586.7	614.1	586.7	559.2	552.4	509.9	453.2	425.0	406.5
142.5°	536.9	542.8	566.4	590.0	566.4	542.8	536.9	499.6	449.8	425.0	408.0
145°	513.6	518.1	535.9	553.8	535.9	518.1	513.6	483.1	442.5	422.1	408.0
147.5°	494.1	497.8	512.6	527.4	512.6	497.8	494.1	470.1	438.2	422.1	410.8
150°	482.9	485.9	497.9	509.9	497.9	485.9	482.9	462.7	435.7	422.1	412.3
152.5°	474.1	476.4	485.3	494.4	485.3	476.4	474.1	456.8	433.7	422.1	413.2
155°	463.5	465.0	470.9	476.9	470.9	465.0	463.5	449.7	431.3	422.1	415.3
157.5°	454.2	455.2	459.5	463.7	459.5	455.2	454.2	443.5	429.3	422.1	417.4
160°	449.6	450.2	452.7	455.1	452.7	450.2	449.6	440.4	428.2	422.1	418.4
162.5°	445.3	445.9	448.2	450.5	448.2	445.9	445.3	437.6	427.3	422.1	419.4
165°	438.7	439.3	441.8	444.2	441.8	439.3	438.7	433.2	425.8	422.1	420.9
167.5°	435.9	436.1	437.1	438.2	437.1	436.1	435.9	432.2	427.4	425.0	423.9
170°	435.9	435.9	435.9	435.9	435.9	435.9	435.9	432.2	427.4	425.0	424.9
172.5°	433.6	433.4	432.4	431.6	432.4	433.4	433.6	430.7	426.9	425.0	425.0
175°	430.4	430.4	430.4	430.4	430.4	430.4	430.4	428.6	426.2	425.0	425.5
177.5°	429.8	429.6	428.6	427.6	428.6	429.6	429.8	428.4	426.5	425.5	426.0
180°	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6	427.6

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	5124.5	5124.5	5124.5	5124.5	5124.5
2.5°	5061.5	5085.8	5100.3	5119.7	5168.2
5°	4867.5	4959.7	4988.7	5061.5	5148.7
7.5°	4440.9	4722.1	4799.6	4974.2	5109.9
10°	4028.9	4310.0	4445.7	4857.9	5061.5
12.5°	3820.4	3985.2	4077.3	4654.2	4993.6
15°	3689.5	3805.8	3873.7	4382.7	4916.1
17.5°	3587.6	3670.1	3718.6	4116.0	4809.4
20°	3524.6	3563.4	3607.0	3922.2	4688.2
22.5°	3481.0	3456.7	3490.7	3786.4	4523.4
25°	3451.8	3359.8	3398.6	3679.7	4329.4
27.5°	3476.1	3272.5	3287.0	3582.8	4125.8
30°	3481.0	3165.8	3170.7	3481.0	3897.9
32.5°	3447.1	3054.4	3059.2	3354.9	3640.9
35°	3364.7	2923.4	2918.6	3209.5	3291.9
37.5°	3253.1	2782.9	2782.9	3049.5	2908.9
40°	3117.4	2642.2	2656.8	2841.0	2569.5
42.5°	2952.5	2492.0	2511.4	2564.7	2317.4
45°	2773.1	2346.5	2361.0	2167.1	2123.4
47.5°	2574.4	2196.2	2201.1	1798.6	2060.5
50°	2336.8	2041.0	2021.6	1541.8	2055.6
52.5°	2128.3	1871.4	1813.2	1396.3	1866.5
55°	1924.7	1692.0	1565.9	1284.8	1730.7
57.5°	1745.4	1459.3	1338.1	1153.8	1701.7
60°	1580.5	1231.5	1139.3	1013.3	1561.1
62.5°	1444.7	1061.8	1042.4	916.3	1415.7
65°	1299.3	945.4	940.6	833.9	1202.3
67.5°	1158.7	867.8	862.9	756.3	916.3
70°	1008.4	785.4	775.7	673.8	678.7
72.5°	853.3	693.3	683.6	606.0	562.4
75°	698.1	586.7	581.8	528.4	455.7
77.5°	547.9	465.5	475.1	426.6	334.5
80°	392.7	339.4	349.1	305.4	252.1
82.5°	261.8	223.0	232.7	194.0	169.7
85°	145.4	126.1	130.9	101.8	77.5
87.5°	67.9	58.2	58.2	38.8	24.3
90°	12.6	8.0	7.4	5.2	2.9
92.5°	77.8	55.4	50.5	30.9	11.5
95°	191.6	107.9	98.9	63.2	27.5
97.5°	258.0	118.5	110.7	79.2	47.7
100°	282.3	127.4	120.2	91.7	63.1
102.5°	293.4	136.3	129.6	102.9	76.3
105°	301.6	149.5	143.8	121.3	98.7
107.5°	303.1	169.0	163.8	142.7	121.7
110°	300.8	179.9	175.1	156.1	137.1



TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	300.9	193.1	188.6	170.5	152.4
115°	303.7	213.0	208.8	192.1	175.3
117.5°	309.3	232.2	228.3	213.2	198.0
120°	313.9	243.3	239.8	225.5	211.2
122.5°	320.5	256.5	252.9	238.6	224.1
125°	329.5	273.5	270.3	257.1	243.9
127.5°	338.4	289.8	286.5	273.2	260.0
130°	344.9	300.7	297.2	282.9	268.5
132.5°	350.1	309.6	306.1	291.8	277.5
135°	355.8	319.9	316.7	303.7	290.7
137.5°	364.4	333.1	329.9	317.1	304.2
140°	369.7	342.1	339.1	327.2	315.3
142.5°	374.1	348.7	345.9	334.9	323.9
145°	379.8	358.7	356.3	346.8	337.2
147.5°	388.2	371.3	369.0	359.7	350.4
150°	392.6	377.9	375.8	367.4	359.0
152.5°	395.5	382.2	380.6	374.3	367.9
155°	401.8	391.6	390.5	385.7	381.0
157.5°	408.2	401.2	400.0	395.4	390.8
160°	411.0	405.5	404.6	401.0	397.5
162.5°	414.1	410.1	409.4	406.7	404.1
165°	418.5	416.7	416.1	413.6	411.2
167.5°	421.9	420.4	420.1	419.0	417.8
170°	424.8	424.7	424.4	423.3	422.1
172.5°	425.0	425.0	424.9	424.7	424.4
175°	426.7	427.6	427.6	427.6	427.6
177.5°	426.9	427.6	427.6	427.6	427.6
180°	427.6	427.6	427.6	427.6	427.6

TEST NUMBER: P934180

CATALOG NUMBER: SQ4-FA-025U-125D-B2750-1D-UNV-W2A-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.02	18.28	17.64	18.91	19.62	19.87	21.13	20.49	21.76	22.47
	3H	17.53	18.66	18.16	19.30	20.04	21.26	22.39	21.88	23.02	23.77
	4H	17.74	18.81	18.39	19.45	20.21	21.72	22.79	22.37	23.44	24.20
	6H	17.88	18.86	18.54	19.52	20.30	22.03	23.02	22.69	23.68	24.45
	8H	17.89	18.83	18.56	19.51	20.29	22.12	23.06	22.79	23.74	24.52
	12H	17.87	18.77	18.55	19.44	20.25	22.18	23.07	22.86	23.75	24.55
4H	2H	18.11	19.17	18.76	19.82	20.58	20.33	21.40	20.98	22.04	22.81
	3H	19.17	20.06	19.83	20.75	21.53	21.88	22.77	22.54	23.45	24.23
	4H	19.46	20.27	20.14	20.96	21.77	22.43	23.23	23.11	23.92	24.74
	6H	19.61	20.31	20.31	21.03	21.85	22.82	23.52	23.52	24.24	25.06
	8H	19.63	20.28	20.33	20.99	21.83	22.94	23.59	23.64	24.31	25.14
	12H	19.61	20.20	20.34	20.94	21.78	23.02	23.61	23.74	24.35	25.18
8H	4H	19.95	20.61	20.66	21.32	22.15	22.58	23.24	23.29	23.95	24.78
	6H	20.23	20.77	20.97	21.53	22.36	23.04	23.58	23.78	24.34	25.18
	8H	20.28	20.76	21.03	21.52	22.37	23.20	23.68	23.95	24.44	25.29
	12H	20.28	20.70	21.03	21.45	22.37	23.32	23.75	24.07	24.50	25.41
12H	4H	19.98	20.57	20.70	21.30	22.14	22.57	23.15	23.29	23.89	24.73
	6H	20.29	20.78	21.04	21.54	22.39	23.04	23.53	23.79	24.28	25.14
	8H	20.38	20.81	21.13	21.55	22.47	23.22	23.65	23.97	24.40	25.31