

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934390

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934390
REPORT IS A COMBINATION OF REPORTS P933695 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6779.5 lumens
Efficiency: N/A
Efficacy: 124.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9367	9367	9367	9367
5°	9433	9455	9433	7435
10°	9367	9314	9367	6659
15°	9262	9112	9262	7609
20°	9064	8873	9064	7625
25°	8664	8524	8664	7463
30°	8148	8235	8148	7109
35°	7261	7869	7261	6719
40°	6046	7438	6046	6424
45°	5399	6933	5399	6085
50°	5732	6332	5732	5745
55°	5387	5683	5387	5548
60°	5547	4827	5547	5082
65°	5021	3990	5021	4460
70°	3468	3180	3468	3738
75°	3031	2351	3031	2815
80°	2425	1554	2425	1692
85°	1365	823	1365	700

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8280 cd/sqm

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.7	2.0
10°-20°	388.1	5.7
20°-30°	599.9	8.8
30°-40°	716.1	10.6
40°-50°	720.3	10.6
50°-60°	626.8	9.2
60°-70°	444.4	6.6
70°-80°	235.1	3.5
80°-90°	60.2	0.9
90°-100°	214.4	3.2
100°-110°	563.8	8.3
110°-120°	584.6	8.6
120°-130°	468.9	6.9
130°-140°	367.9	5.4
140°-150°	282.4	4.2
150°-160°	203.4	3.0
160°-170°	124.4	1.8
170°-180°	42.0	0.6
0°-30°	1124.6	16.6
0°-40°	1840.8	27.2
0°-60°	3187.9	47.0
0°-90°	3927.6	57.9
90°-120°	1362.8	20.1
90°-150°	2482.0	36.6
90°-180°	2852.0	42.1
0°-180°	6779.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1514	1514	1514	1514	1514	
5°	1521	1569	1521	1233	1521	144
15°	1453	1554	1453	1298	1453	409
25°	1279	1450	1279	1269	1279	587
35°	973	1294	973	1104	973	602
45°	627	1066	627	935	627	503
55°	511	786	511	768	511	470
65°	355	474	355	530	355	340
75°	135	225	135	269	135	142
85°	23	57	23	49	23	31
90°	3	11	3	11	3	3
95°	28	130	28	130	28	31
105°	102	883	102	883	102	108
115°	180	1137	180	1137	180	178
125°	251	905	251	905	251	223
135°	299	702	299	702	299	231
145°	347	570	347	570	347	217
155°	392	491	392	491	392	180
165°	423	457	423	457	423	119
175°	440	443	440	443	440	42
180°	440	440	440	440	440	

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1527.0	1527.0	1535.6	1538.5	1538.5	1534.2	1529.9	1534.2	1547.1	1551.4	1550.0
5°	1521.3	1532.8	1548.5	1551.4	1554.3	1552.8	1550.0	1552.8	1567.2	1570.0	1571.5
7.5°	1509.9	1531.3	1551.4	1555.7	1560.0	1555.7	1554.3	1557.1	1571.5	1574.3	1574.3
10°	1495.5	1525.6	1548.5	1551.4	1555.7	1551.4	1551.4	1557.1	1571.5	1574.3	1575.8
12.5°	1475.5	1517.0	1538.5	1541.4	1547.1	1545.7	1544.2	1550.0	1564.3	1567.2	1567.2
15°	1452.6	1501.3	1521.3	1524.2	1534.2	1531.3	1531.3	1537.1	1552.8	1557.1	1555.7
17.5°	1421.0	1481.2	1504.1	1508.4	1515.6	1514.2	1515.6	1521.3	1535.6	1538.5	1539.9
20°	1385.2	1454.0	1481.2	1485.5	1492.7	1492.7	1492.7	1499.8	1514.2	1519.9	1519.9
22.5°	1336.5	1425.3	1454.0	1456.9	1465.4	1465.4	1468.3	1478.3	1491.2	1492.7	1492.7
25°	1279.2	1393.8	1418.2	1426.8	1435.4	1439.7	1444.0	1449.7	1454.0	1452.6	1454.0
27.5°	1219.1	1353.7	1385.2	1391.0	1402.4	1406.7	1412.4	1413.9	1415.3	1419.6	1416.7
30°	1151.7	1297.8	1345.1	1350.8	1369.5	1372.3	1366.6	1369.5	1376.6	1379.5	1382.4
32.5°	1075.8	1214.8	1303.6	1316.5	1333.7	1325.1	1323.6	1327.9	1339.4	1339.4	1342.3
35°	972.7	1150.3	1264.9	1276.4	1289.2	1279.2	1285.0	1286.4	1293.5	1297.8	1296.4
37.5°	859.5	1094.4	1224.8	1233.4	1243.4	1230.5	1239.1	1243.4	1249.1	1246.3	1246.3
40°	759.2	1007.0	1177.5	1183.2	1191.8	1181.8	1190.4	1193.3	1196.1	1193.3	1191.8
42.5°	684.7	911.1	1127.4	1134.5	1128.8	1136.0	1138.8	1144.6	1140.3	1134.5	1134.5
45°	627.4	885.3	1072.9	1081.5	1072.9	1084.4	1088.7	1088.7	1075.8	1072.9	1071.5
47.5°	608.8	833.7	1018.5	1018.5	1014.2	1028.5	1035.7	1025.7	1012.8	1008.5	1008.5
50°	607.4	776.4	944.0	938.3	958.3	975.5	968.4	958.3	948.3	932.6	932.6
52.5°	551.5	706.2	848.0	869.5	901.0	911.1	899.6	889.6	872.4	865.2	859.5
55°	511.4	633.2	760.7	803.6	836.6	849.5	828.0	818.0	792.2	787.9	785.0
57.5°	502.8	527.2	680.4	734.9	775.0	773.6	760.7	742.0	720.5	716.2	714.8
60°	461.3	381.0	594.5	658.9	700.5	696.2	684.7	667.5	647.5	644.6	641.8
62.5°	418.3	276.5	497.1	570.1	628.9	627.4	617.4	591.6	577.3	570.1	564.4
65°	355.3	232.1	353.8	474.2	558.7	561.5	540.1	521.4	505.7	497.1	495.6
67.5°	270.7	189.1	239.2	395.4	491.3	488.5	461.3	452.7	432.6	428.3	419.7
70°	200.5	126.1	166.2	320.9	425.5	418.3	396.8	386.8	368.2	358.1	352.4
72.5°	166.2	101.7	121.8	249.3	358.1	349.5	330.9	319.4	303.7	295.1	289.4
75°	134.7	107.4	93.1	184.8	290.8	285.1	267.9	256.4	243.5	232.1	233.5
77.5°	98.8	100.3	74.5	136.1	230.6	222.0	212.0	197.7	192.0	180.5	180.5
80°	74.5	78.8	55.9	93.1	166.2	166.2	157.6	147.5	137.5	131.8	131.8
82.5°	50.1	50.1	41.5	58.7	113.2	108.9	103.1	100.3	94.5	91.7	91.7
85°	22.9	28.6	25.8	35.8	61.6	64.5	64.5	61.6	60.2	57.3	58.7
87.5°	7.2	12.9	15.8	20.1	31.5	32.9	34.4	34.4	34.4	35.8	35.8
90°	3.0	5.3	7.7	8.3	13.0	19.3	22.4	20.0	14.9	11.2	11.2
92.5°	11.8	31.9	52.0	57.0	80.1	111.0	126.3	110.7	79.5	56.1	53.9
95°	28.4	65.0	101.8	111.0	197.1	312.0	369.4	329.7	250.1	190.4	183.6
97.5°	49.0	81.5	113.8	122.0	265.6	457.1	552.8	527.6	477.3	439.6	426.7
100°	64.9	94.4	123.8	131.1	290.4	502.9	609.1	610.9	614.6	617.4	602.1
102.5°	78.5	106.0	133.4	140.3	301.9	517.3	625.0	657.0	721.1	769.2	756.1
105°	101.6	124.8	148.0	153.9	310.3	518.9	623.2	695.0	838.6	946.3	939.2
107.5°	125.2	146.9	168.5	173.9	311.9	495.8	587.8	687.9	888.2	1038.4	1040.1
110°	141.1	160.6	180.2	185.1	309.5	475.4	558.3	670.2	894.2	1062.1	1069.4

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	156.8	175.4	194.1	198.7	309.6	457.5	531.5	646.1	875.2	1047.0	1058.2
115°	180.4	197.6	214.8	219.1	312.5	437.0	499.3	609.7	830.4	995.9	1011.5
117.5°	203.7	219.4	234.9	238.8	318.3	424.2	477.1	576.7	775.9	925.3	942.7
120°	217.3	232.0	246.7	250.4	323.0	419.8	468.2	559.2	741.3	877.7	894.6
122.5°	230.6	245.4	260.2	264.0	329.8	417.5	461.5	543.4	707.4	830.3	846.9
125°	251.0	264.4	278.0	281.3	338.9	415.7	454.1	523.7	663.0	767.3	782.6
127.5°	267.5	281.2	294.8	298.2	348.1	414.7	447.9	507.7	627.1	716.8	729.7
130°	276.4	291.1	305.8	309.4	354.8	415.2	445.5	498.7	605.2	685.0	697.0
132.5°	285.5	300.3	315.0	318.6	360.2	415.7	443.5	491.2	586.4	657.8	668.5
135°	299.1	312.5	325.8	329.2	366.1	415.3	440.0	479.9	559.6	619.4	628.7
137.5°	313.0	326.2	339.4	342.7	374.9	417.8	439.3	473.0	540.4	591.0	598.6
140°	324.5	336.7	348.9	351.9	380.4	418.3	437.3	466.4	524.7	568.3	575.4
142.5°	333.3	344.6	355.8	358.7	384.9	419.8	437.3	462.9	514.0	552.4	558.5
145°	347.0	356.8	366.6	369.1	390.9	419.8	434.3	455.2	497.1	528.5	533.1
147.5°	360.5	370.1	379.7	382.1	399.5	422.7	434.3	450.8	483.7	508.4	512.3
150°	369.4	378.1	386.7	388.9	404.1	424.2	434.3	448.3	476.1	496.9	499.9
152.5°	378.5	385.1	391.6	393.3	406.9	425.2	434.3	446.2	470.0	487.7	490.0
155°	392.1	397.0	401.8	403.0	413.4	427.4	434.3	443.8	462.7	476.8	478.4
157.5°	402.2	406.8	411.6	412.8	419.9	429.6	434.3	441.7	456.4	467.4	468.4
160°	408.9	412.6	416.2	417.1	422.9	430.5	434.3	440.6	453.2	462.7	463.3
162.5°	415.7	418.5	421.3	421.9	426.0	431.6	434.3	439.7	450.3	458.2	458.8
165°	423.1	425.5	428.0	428.7	430.6	433.1	434.3	438.2	445.7	451.4	452.1
167.5°	429.8	431.0	432.2	432.5	434.1	436.2	437.3	439.8	444.7	448.5	448.8
170°	434.3	435.5	436.7	437.0	437.1	437.2	437.3	439.8	444.7	448.5	448.5
172.5°	436.7	437.0	437.2	437.3	437.3	437.3	437.3	439.2	443.1	446.1	445.9
175°	440.0	440.0	440.0	440.0	439.1	437.9	437.3	438.5	441.0	442.8	442.8
177.5°	440.0	440.0	440.0	440.0	439.3	438.3	437.9	438.8	440.8	442.3	442.0
180°	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1552.8	1548.5	1552.8	1550.0	1551.4	1547.1	1534.2	1529.9	1534.2	1538.5	1538.5
5°	1571.5	1568.6	1571.5	1571.5	1570.0	1567.2	1552.8	1550.0	1552.8	1554.3	1551.4
7.5°	1577.2	1572.9	1577.2	1574.3	1574.3	1571.5	1557.1	1554.3	1555.7	1560.0	1555.7
10°	1577.2	1572.9	1577.2	1575.8	1574.3	1571.5	1557.1	1551.4	1551.4	1555.7	1551.4
12.5°	1570.0	1567.2	1570.0	1567.2	1567.2	1564.3	1550.0	1544.2	1545.7	1547.1	1541.4
15°	1558.6	1554.3	1558.6	1555.7	1557.1	1552.8	1537.1	1531.3	1531.3	1534.2	1524.2
17.5°	1541.4	1535.6	1541.4	1539.9	1538.5	1535.6	1521.3	1515.6	1514.2	1515.6	1508.4
20°	1521.3	1517.0	1521.3	1519.9	1519.9	1514.2	1499.8	1492.7	1492.7	1492.7	1485.5
22.5°	1489.8	1485.5	1489.8	1492.7	1492.7	1491.2	1478.3	1468.3	1465.4	1465.4	1456.9
25°	1454.0	1449.7	1454.0	1454.0	1452.6	1454.0	1449.7	1444.0	1439.7	1435.4	1426.8
27.5°	1419.6	1416.7	1419.6	1416.7	1419.6	1415.3	1413.9	1412.4	1406.7	1402.4	1391.0
30°	1385.2	1382.4	1385.2	1382.4	1379.5	1376.6	1369.5	1366.6	1372.3	1369.5	1350.8
32.5°	1342.3	1339.4	1342.3	1342.3	1339.4	1339.4	1327.9	1323.6	1325.1	1333.7	1316.5
35°	1297.8	1293.5	1297.8	1296.4	1297.8	1293.5	1286.4	1285.0	1279.2	1289.2	1276.4
37.5°	1246.3	1242.0	1246.3	1246.3	1246.3	1249.1	1243.4	1239.1	1230.5	1243.4	1233.4
40°	1193.3	1187.5	1193.3	1191.8	1193.3	1196.1	1193.3	1190.4	1181.8	1191.8	1183.2
42.5°	1133.1	1131.7	1133.1	1134.5	1134.5	1140.3	1144.6	1138.8	1136.0	1128.8	1134.5
45°	1068.6	1065.8	1068.6	1071.5	1072.9	1075.8	1088.7	1088.7	1084.4	1072.9	1081.5
47.5°	999.9	992.7	999.9	1008.5	1008.5	1012.8	1025.7	1035.7	1028.5	1014.2	1018.5
50°	926.8	928.3	926.8	932.6	932.6	948.3	958.3	968.4	975.5	958.3	938.3
52.5°	855.2	853.8	855.2	859.5	865.2	872.4	889.6	899.6	911.1	901.0	869.5
55°	783.6	786.4	783.6	785.0	787.9	792.2	818.0	828.0	849.5	836.6	803.6
57.5°	712.0	707.7	712.0	714.8	716.2	720.5	742.0	760.7	773.6	775.0	734.9
60°	628.9	623.1	628.9	641.8	644.6	647.5	667.5	684.7	696.2	700.5	658.9
62.5°	555.8	545.8	555.8	564.4	570.1	577.3	591.6	617.4	627.4	628.9	570.1
65°	478.5	474.2	478.5	495.6	497.1	505.7	521.4	540.1	561.5	558.7	474.2
67.5°	408.3	408.3	408.3	419.7	428.3	432.6	452.7	461.3	488.5	491.3	395.4
70°	343.8	342.4	343.8	352.4	358.1	368.2	386.8	396.8	418.3	425.5	320.9
72.5°	282.2	280.8	282.2	289.4	295.1	303.7	319.4	330.9	349.5	358.1	249.3
75°	227.8	224.9	227.8	233.5	232.1	243.5	256.4	267.9	285.1	290.8	184.8
77.5°	174.8	174.8	174.8	180.5	180.5	192.0	197.7	212.0	222.0	230.6	136.1
80°	130.4	128.9	130.4	131.8	131.8	137.5	147.5	157.6	166.2	166.2	93.1
82.5°	91.7	88.8	91.7	91.7	91.7	94.5	100.3	103.1	108.9	113.2	58.7
85°	57.3	57.3	57.3	58.7	57.3	60.2	61.6	64.5	64.5	61.6	35.8
87.5°	37.2	35.8	37.2	35.8	35.8	34.4	34.4	34.4	32.9	31.5	20.1
90°	11.2	11.2	11.2	11.2	11.2	14.9	20.0	22.4	19.3	13.0	8.3
92.5°	44.9	36.0	44.9	53.9	56.1	79.5	110.7	126.3	111.0	80.1	57.0
95°	156.6	129.6	156.6	183.6	190.4	250.1	329.7	369.4	312.0	197.1	111.0
97.5°	375.3	323.9	375.3	426.7	439.6	477.3	527.6	552.8	457.1	265.6	122.0
100°	540.8	479.5	540.8	602.1	617.4	614.6	610.9	609.1	502.9	290.4	131.1
102.5°	703.5	651.0	703.5	756.1	769.2	721.1	657.0	625.0	517.3	301.9	140.3
105°	911.1	882.8	911.1	939.2	946.3	838.6	695.0	623.2	518.9	310.3	153.9
107.5°	1046.9	1053.7	1046.9	1040.1	1038.4	888.2	687.9	587.8	495.8	311.9	173.9
110°	1098.7	1128.1	1098.7	1069.4	1062.1	894.2	670.2	558.3	475.4	309.5	185.1

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1103.4	1148.5	1103.4	1058.2	1047.0	875.2	646.1	531.5	457.5	309.6	198.7
115°	1074.1	1136.7	1074.1	1011.5	995.9	830.4	609.7	499.3	437.0	312.5	219.1
117.5°	1012.1	1081.5	1012.1	942.7	925.3	775.9	576.7	477.1	424.2	318.3	238.8
120°	962.1	1029.6	962.1	894.6	877.7	741.3	559.2	468.2	419.8	323.0	250.4
122.5°	913.5	979.9	913.5	846.9	830.3	707.4	543.4	461.5	417.5	329.8	264.0
125°	843.9	905.2	843.9	782.6	767.3	663.0	523.7	454.1	415.7	338.9	281.3
127.5°	781.5	833.2	781.5	729.7	716.8	627.1	507.7	447.9	414.7	348.1	298.2
130°	744.7	792.5	744.7	697.0	685.0	605.2	498.7	445.5	415.2	354.8	309.4
132.5°	711.3	754.1	711.3	668.5	657.8	586.4	491.2	443.5	415.7	360.2	318.6
135°	665.5	702.4	665.5	628.7	619.4	559.6	479.9	440.0	415.3	366.1	329.2
137.5°	628.9	659.0	628.9	598.6	591.0	540.4	473.0	439.3	417.8	374.9	342.7
140°	603.6	631.8	603.6	575.4	568.3	524.7	466.4	437.3	418.3	380.4	351.9
142.5°	582.7	607.0	582.7	558.5	552.4	514.0	462.9	437.3	419.8	384.9	358.7
145°	551.5	569.8	551.5	533.1	528.5	497.1	455.2	434.3	419.8	390.9	369.1
147.5°	527.4	542.6	527.4	512.3	508.4	483.7	450.8	434.3	422.7	399.5	382.1
150°	512.4	524.7	512.4	499.9	496.9	476.1	448.3	434.3	424.2	404.1	388.9
152.5°	499.4	508.7	499.4	490.0	487.7	470.0	446.2	434.3	425.2	406.9	393.3
155°	484.6	490.7	484.6	478.4	476.8	462.7	443.8	434.3	427.4	413.4	403.0
157.5°	472.8	477.1	472.8	468.4	467.4	456.4	441.7	434.3	429.6	419.9	412.8
160°	465.8	468.2	465.8	463.3	462.7	453.2	440.6	434.3	430.5	422.9	417.1
162.5°	461.2	463.6	461.2	458.8	458.2	450.3	439.7	434.3	431.6	426.0	421.9
165°	454.6	457.1	454.6	452.1	451.4	445.7	438.2	434.3	433.1	430.6	428.7
167.5°	449.8	450.9	449.8	448.8	448.5	444.7	439.8	437.3	436.2	434.1	432.5
170°	448.5	448.5	448.5	448.5	448.5	444.7	439.8	437.3	437.2	437.1	437.0
172.5°	444.9	444.1	444.9	445.9	446.1	443.1	439.2	437.3	437.3	437.3	437.3
175°	442.8	442.8	442.8	442.8	442.8	441.0	438.5	437.3	437.9	439.1	440.0
177.5°	441.0	440.0	441.0	442.0	442.3	440.8	438.8	437.9	438.3	439.3	440.0
180°	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1535.6	1527.0	1527.0	1512.7	1507.0	1502.7	1495.5	1474.0	1468.3	1462.6	1471.2
5°	1548.5	1532.8	1521.3	1495.5	1474.0	1465.4	1438.2	1386.7	1352.3	1326.5	1312.2
7.5°	1551.4	1531.3	1509.9	1469.7	1418.2	1395.3	1312.2	1217.6	1191.8	1168.9	1154.6
10°	1548.5	1525.6	1495.5	1435.4	1313.6	1273.5	1190.4	1128.8	1113.1	1108.8	1113.1
12.5°	1538.5	1517.0	1475.5	1375.2	1204.7	1177.5	1128.8	1093.0	1090.1	1097.3	1136.0
15°	1521.3	1501.3	1452.6	1295.0	1144.6	1124.5	1090.1	1077.2	1093.0	1143.1	1259.2
17.5°	1504.1	1481.2	1421.0	1216.2	1098.7	1084.4	1060.0	1085.8	1174.6	1242.0	1280.7
20°	1481.2	1454.0	1385.2	1158.9	1065.8	1052.9	1041.4	1157.5	1224.8	1249.1	1270.6
22.5°	1454.0	1425.3	1336.5	1118.8	1031.4	1021.4	1028.5	1197.6	1224.8	1242.0	1260.6
25°	1418.2	1393.8	1279.2	1087.3	1004.2	992.7	1019.9	1193.3	1209.0	1213.3	1250.6
27.5°	1385.2	1353.7	1219.1	1058.6	971.2	966.9	1027.1	1174.6	1186.1	1190.4	1230.5
30°	1345.1	1297.8	1151.7	1028.5	936.9	935.4	1028.5	1151.7	1148.9	1160.3	1200.4
32.5°	1303.6	1214.8	1075.8	991.3	903.9	902.5	1018.5	1117.4	1114.5	1130.2	1160.3
35°	1264.9	1150.3	972.7	948.3	862.4	863.8	994.2	1077.2	1078.7	1093.0	1111.6
37.5°	1224.8	1094.4	859.5	901.0	822.3	822.3	961.2	1040.0	1037.1	1041.4	1067.2
40°	1177.5	1007.0	759.2	839.4	785.0	780.7	921.1	999.9	989.9	988.4	1024.2
42.5°	1127.4	911.1	684.7	757.8	742.0	736.3	872.4	951.2	932.6	936.9	982.7
45°	1072.9	885.3	627.4	640.3	697.6	693.3	819.4	895.3	882.4	893.9	941.2
47.5°	1018.5	833.7	608.8	531.5	650.4	648.9	760.7	840.9	833.7	845.2	895.3
50°	944.0	776.4	607.4	455.5	597.4	603.1	690.5	787.9	787.9	797.9	850.9
52.5°	848.0	706.2	551.5	412.6	535.8	552.9	628.9	742.0	744.9	754.9	802.2
55°	760.7	633.2	511.4	379.6	462.7	499.9	568.7	694.8	700.5	710.5	753.5
57.5°	680.4	527.2	502.8	340.9	395.4	431.2	515.7	648.9	651.8	660.4	701.9
60°	594.5	381.0	461.3	299.4	336.6	363.9	467.0	594.5	604.5	610.2	646.1
62.5°	497.1	276.5	418.3	270.7	308.0	313.7	426.9	542.9	555.8	560.1	581.6
65°	353.8	232.1	355.3	246.4	277.9	279.3	383.9	489.9	501.4	508.5	524.3
67.5°	239.2	189.1	270.7	223.5	255.0	256.4	342.4	428.3	444.1	449.8	459.8
70°	166.2	126.1	200.5	199.1	229.2	232.1	298.0	372.4	386.8	391.1	396.8
72.5°	121.8	101.7	166.2	179.1	202.0	204.8	252.1	309.4	323.7	328.0	330.9
75°	93.1	107.4	134.7	156.1	171.9	173.3	206.3	252.1	262.1	265.0	266.4
77.5°	74.5	100.3	98.8	126.1	140.4	137.5	161.9	194.8	203.4	203.4	203.4
80°	55.9	78.8	74.5	90.2	103.1	100.3	116.0	139.0	141.8	144.7	143.2
82.5°	41.5	50.1	50.1	57.3	68.8	65.9	77.4	90.2	90.2	90.2	93.1
85°	25.8	28.6	22.9	30.1	38.7	37.2	43.0	48.7	50.1	50.1	47.3
87.5°	15.8	12.9	7.2	11.5	17.2	17.2	20.1	21.5	20.1	20.1	20.1
90°	7.7	5.3	3.0	5.3	7.7	8.3	13.0	19.3	22.4	20.0	14.9
92.5°	52.0	31.9	11.8	31.9	52.0	57.0	80.1	111.0	126.3	110.7	79.5
95°	101.8	65.0	28.4	65.0	101.8	111.0	197.1	312.0	369.4	329.7	250.1
97.5°	113.8	81.5	49.0	81.5	113.8	122.0	265.6	457.1	552.8	527.6	477.3
100°	123.8	94.4	64.9	94.4	123.8	131.1	290.4	502.9	609.1	610.9	614.6
102.5°	133.4	106.0	78.5	106.0	133.4	140.3	301.9	517.3	625.0	657.0	721.1
105°	148.0	124.8	101.6	124.8	148.0	153.9	310.3	518.9	623.2	695.0	838.6
107.5°	168.5	146.9	125.2	146.9	168.5	173.9	311.9	495.8	587.8	687.9	888.2
110°	180.2	160.6	141.1	160.6	180.2	185.1	309.5	475.4	558.3	670.2	894.2

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	194.1	175.4	156.8	175.4	194.1	198.7	309.6	457.5	531.5	646.1	875.2
115°	214.8	197.6	180.4	197.6	214.8	219.1	312.5	437.0	499.3	609.7	830.4
117.5°	234.9	219.4	203.7	219.4	234.9	238.8	318.3	424.2	477.1	576.7	775.9
120°	246.7	232.0	217.3	232.0	246.7	250.4	323.0	419.8	468.2	559.2	741.3
122.5°	260.2	245.4	230.6	245.4	260.2	264.0	329.8	417.5	461.5	543.4	707.4
125°	278.0	264.4	251.0	264.4	278.0	281.3	338.9	415.7	454.1	523.7	663.0
127.5°	294.8	281.2	267.5	281.2	294.8	298.2	348.1	414.7	447.9	507.7	627.1
130°	305.8	291.1	276.4	291.1	305.8	309.4	354.8	415.2	445.5	498.7	605.2
132.5°	315.0	300.3	285.5	300.3	315.0	318.6	360.2	415.7	443.5	491.2	586.4
135°	325.8	312.5	299.1	312.5	325.8	329.2	366.1	415.3	440.0	479.9	559.6
137.5°	339.4	326.2	313.0	326.2	339.4	342.7	374.9	417.8	439.3	473.0	540.4
140°	348.9	336.7	324.5	336.7	348.9	351.9	380.4	418.3	437.3	466.4	524.7
142.5°	355.8	344.6	333.3	344.6	355.8	358.7	384.9	419.8	437.3	462.9	514.0
145°	366.6	356.8	347.0	356.8	366.6	369.1	390.9	419.8	434.3	455.2	497.1
147.5°	379.7	370.1	360.5	370.1	379.7	382.1	399.5	422.7	434.3	450.8	483.7
150°	386.7	378.1	369.4	378.1	386.7	388.9	404.1	424.2	434.3	448.3	476.1
152.5°	391.6	385.1	378.5	385.1	391.6	393.3	406.9	425.2	434.3	446.2	470.0
155°	401.8	397.0	392.1	397.0	401.8	403.0	413.4	427.4	434.3	443.8	462.7
157.5°	411.6	406.8	402.2	406.8	411.6	412.8	419.9	429.6	434.3	441.7	456.4
160°	416.2	412.6	408.9	412.6	416.2	417.1	422.9	430.5	434.3	440.6	453.2
162.5°	421.3	418.5	415.7	418.5	421.3	421.9	426.0	431.6	434.3	439.7	450.3
165°	428.0	425.5	423.1	425.5	428.0	428.7	430.6	433.1	434.3	438.2	445.7
167.5°	432.2	431.0	429.8	431.0	432.2	432.5	434.1	436.2	437.3	439.8	444.7
170°	436.7	435.5	434.3	435.5	436.7	437.0	437.1	437.2	437.3	439.8	444.7
172.5°	437.2	437.0	436.7	437.0	437.2	437.3	437.3	437.3	437.3	439.2	443.1
175°	440.0	440.0	440.0	440.0	440.0	440.0	439.1	437.9	437.3	438.5	441.0
177.5°	440.0	440.0	440.0	440.0	440.0	440.0	439.3	438.3	437.9	438.8	440.8
180°	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1461.1	1456.9	1462.6	1446.8	1462.6	1456.9	1461.1	1471.2	1462.6	1468.3	1474.0
5°	1282.1	1274.9	1252.0	1233.4	1252.0	1274.9	1282.1	1312.2	1326.5	1352.3	1386.7
7.5°	1146.0	1140.3	1134.5	1123.1	1134.5	1140.3	1146.0	1154.6	1168.9	1191.8	1217.6
10°	1115.9	1117.4	1125.9	1124.5	1125.9	1117.4	1115.9	1113.1	1108.8	1113.1	1128.8
12.5°	1193.3	1206.2	1253.4	1250.6	1253.4	1206.2	1193.3	1136.0	1097.3	1090.1	1093.0
15°	1282.1	1286.4	1296.4	1297.8	1296.4	1286.4	1282.1	1259.2	1143.1	1093.0	1077.2
17.5°	1290.7	1292.1	1299.3	1299.3	1299.3	1292.1	1290.7	1280.7	1242.0	1174.6	1085.8
20°	1283.5	1286.4	1300.7	1303.6	1300.7	1286.4	1283.5	1270.6	1249.1	1224.8	1157.5
22.5°	1280.7	1286.4	1297.8	1296.4	1297.8	1286.4	1280.7	1260.6	1242.0	1224.8	1197.6
25°	1266.3	1266.3	1267.8	1269.2	1267.8	1266.3	1266.3	1250.6	1213.3	1209.0	1193.3
27.5°	1236.2	1239.1	1247.7	1246.3	1247.7	1239.1	1236.2	1230.5	1190.4	1186.1	1174.6
30°	1209.0	1206.2	1199.0	1193.3	1199.0	1206.2	1209.0	1200.4	1160.3	1148.9	1151.7
32.5°	1163.2	1156.0	1148.9	1144.6	1148.9	1156.0	1163.2	1160.3	1130.2	1114.5	1117.4
35°	1108.8	1110.2	1108.8	1104.5	1108.8	1110.2	1108.8	1111.6	1093.0	1078.7	1077.2
37.5°	1070.1	1072.9	1071.5	1065.8	1071.5	1072.9	1070.1	1067.2	1041.4	1037.1	1040.0
40°	1030.0	1031.4	1030.0	1025.7	1030.0	1031.4	1030.0	1024.2	988.4	989.9	999.9
42.5°	991.3	989.9	985.6	982.7	985.6	989.9	991.3	982.7	936.9	932.6	951.2
45°	946.9	948.3	939.7	935.4	939.7	948.3	946.9	941.2	893.9	882.4	895.3
47.5°	902.5	902.5	895.3	891.0	895.3	902.5	902.5	895.3	845.2	833.7	840.9
50°	855.2	853.8	843.7	842.3	843.7	853.8	855.2	850.9	797.9	787.9	787.9
52.5°	800.8	800.8	802.2	805.1	802.2	800.8	800.8	802.2	754.9	744.9	742.0
55°	753.5	754.9	765.0	767.8	765.0	754.9	753.5	753.5	710.5	700.5	694.8
57.5°	704.8	704.8	712.0	712.0	712.0	704.8	704.8	701.9	660.4	651.8	648.9
60°	648.9	651.8	657.5	656.1	657.5	651.8	648.9	646.1	610.2	604.5	594.5
62.5°	590.2	593.1	594.5	591.6	594.5	593.1	590.2	581.6	560.1	555.8	542.9
65°	528.6	531.5	532.9	530.0	532.9	531.5	528.6	524.3	508.5	501.4	489.9
67.5°	465.6	464.1	462.7	468.4	462.7	464.1	465.6	459.8	449.8	444.1	428.3
70°	401.1	401.1	399.7	402.5	399.7	401.1	401.1	396.8	391.1	386.8	372.4
72.5°	332.3	330.9	336.6	332.3	336.6	330.9	332.3	330.9	328.0	323.7	309.4
75°	265.0	267.9	265.0	269.3	265.0	267.9	265.0	266.4	265.0	262.1	252.1
77.5°	202.0	204.8	202.0	202.0	202.0	204.8	202.0	203.4	203.4	203.4	194.8
80°	143.2	141.8	141.8	140.4	141.8	141.8	143.2	143.2	144.7	141.8	139.0
82.5°	91.7	90.2	90.2	93.1	90.2	90.2	91.7	93.1	90.2	90.2	90.2
85°	50.1	51.6	48.7	48.7	48.7	51.6	50.1	47.3	50.1	50.1	48.7
87.5°	18.6	17.2	17.2	17.2	17.2	17.2	18.6	20.1	20.1	20.1	21.5
90°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	14.9	20.0	22.4	19.3
92.5°	56.1	53.9	44.9	36.0	44.9	53.9	56.1	79.5	110.7	126.3	111.0
95°	190.4	183.6	156.6	129.6	156.6	183.6	190.4	250.1	329.7	369.4	312.0
97.5°	439.6	426.7	375.3	323.9	375.3	426.7	439.6	477.3	527.6	552.8	457.1
100°	617.4	602.1	540.8	479.5	540.8	602.1	617.4	614.6	610.9	609.1	502.9
102.5°	769.2	756.1	703.5	651.0	703.5	756.1	769.2	721.1	657.0	625.0	517.3
105°	946.3	939.2	911.1	882.8	911.1	939.2	946.3	838.6	695.0	623.2	518.9
107.5°	1038.4	1040.1	1046.9	1053.7	1046.9	1040.1	1038.4	888.2	687.9	587.8	495.8
110°	1062.1	1069.4	1098.7	1128.1	1098.7	1069.4	1062.1	894.2	670.2	558.3	475.4

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1047.0	1058.2	1103.4	1148.5	1103.4	1058.2	1047.0	875.2	646.1	531.5	457.5
115°	995.9	1011.5	1074.1	1136.7	1074.1	1011.5	995.9	830.4	609.7	499.3	437.0
117.5°	925.3	942.7	1012.1	1081.5	1012.1	942.7	925.3	775.9	576.7	477.1	424.2
120°	877.7	894.6	962.1	1029.6	962.1	894.6	877.7	741.3	559.2	468.2	419.8
122.5°	830.3	846.9	913.5	979.9	913.5	846.9	830.3	707.4	543.4	461.5	417.5
125°	767.3	782.6	843.9	905.2	843.9	782.6	767.3	663.0	523.7	454.1	415.7
127.5°	716.8	729.7	781.5	833.2	781.5	729.7	716.8	627.1	507.7	447.9	414.7
130°	685.0	697.0	744.7	792.5	744.7	697.0	685.0	605.2	498.7	445.5	415.2
132.5°	657.8	668.5	711.3	754.1	711.3	668.5	657.8	586.4	491.2	443.5	415.7
135°	619.4	628.7	665.5	702.4	665.5	628.7	619.4	559.6	479.9	440.0	415.3
137.5°	591.0	598.6	628.9	659.0	628.9	598.6	591.0	540.4	473.0	439.3	417.8
140°	568.3	575.4	603.6	631.8	603.6	575.4	568.3	524.7	466.4	437.3	418.3
142.5°	552.4	558.5	582.7	607.0	582.7	558.5	552.4	514.0	462.9	437.3	419.8
145°	528.5	533.1	551.5	569.8	551.5	533.1	528.5	497.1	455.2	434.3	419.8
147.5°	508.4	512.3	527.4	542.6	527.4	512.3	508.4	483.7	450.8	434.3	422.7
150°	496.9	499.9	512.4	524.7	512.4	499.9	496.9	476.1	448.3	434.3	424.2
152.5°	487.7	490.0	499.4	508.7	499.4	490.0	487.7	470.0	446.2	434.3	425.2
155°	476.8	478.4	484.6	490.7	484.6	478.4	476.8	462.7	443.8	434.3	427.4
157.5°	467.4	468.4	472.8	477.1	472.8	468.4	467.4	456.4	441.7	434.3	429.6
160°	462.7	463.3	465.8	468.2	465.8	463.3	462.7	453.2	440.6	434.3	430.5
162.5°	458.2	458.8	461.2	463.6	461.2	458.8	458.2	450.3	439.7	434.3	431.6
165°	451.4	452.1	454.6	457.1	454.6	452.1	451.4	445.7	438.2	434.3	433.1
167.5°	448.5	448.8	449.8	450.9	449.8	448.8	448.5	444.7	439.8	437.3	436.2
170°	448.5	448.5	448.5	448.5	448.5	448.5	448.5	444.7	439.8	437.3	437.2
172.5°	446.1	445.9	444.9	444.1	444.9	445.9	446.1	443.1	439.2	437.3	437.3
175°	442.8	442.8	442.8	442.8	442.8	442.8	442.8	441.0	438.5	437.3	437.9
177.5°	442.3	442.0	441.0	440.0	441.0	442.0	442.3	440.8	438.8	437.9	438.3
180°	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1495.5	1502.7	1507.0	1512.7	1527.0
5°	1438.2	1465.4	1474.0	1495.5	1521.3
7.5°	1312.2	1395.3	1418.2	1469.7	1509.9
10°	1190.4	1273.5	1313.6	1435.4	1495.5
12.5°	1128.8	1177.5	1204.7	1375.2	1475.5
15°	1090.1	1124.5	1144.6	1295.0	1452.6
17.5°	1060.0	1084.4	1098.7	1216.2	1421.0
20°	1041.4	1052.9	1065.8	1158.9	1385.2
22.5°	1028.5	1021.4	1031.4	1118.8	1336.5
25°	1019.9	992.7	1004.2	1087.3	1279.2
27.5°	1027.1	966.9	971.2	1058.6	1219.1
30°	1028.5	935.4	936.9	1028.5	1151.7
32.5°	1018.5	902.5	903.9	991.3	1075.8
35°	994.2	863.8	862.4	948.3	972.7
37.5°	961.2	822.3	822.3	901.0	859.5
40°	921.1	780.7	785.0	839.4	759.2
42.5°	872.4	736.3	742.0	757.8	684.7
45°	819.4	693.3	697.6	640.3	627.4
47.5°	760.7	648.9	650.4	531.5	608.8
50°	690.5	603.1	597.4	455.5	607.4
52.5°	628.9	552.9	535.8	412.6	551.5
55°	568.7	499.9	462.7	379.6	511.4
57.5°	515.7	431.2	395.4	340.9	502.8
60°	467.0	363.9	336.6	299.4	461.3
62.5°	426.9	313.7	308.0	270.7	418.3
65°	383.9	279.3	277.9	246.4	355.3
67.5°	342.4	256.4	255.0	223.5	270.7
70°	298.0	232.1	229.2	199.1	200.5
72.5°	252.1	204.8	202.0	179.1	166.2
75°	206.3	173.3	171.9	156.1	134.7
77.5°	161.9	137.5	140.4	126.1	98.8
80°	116.0	100.3	103.1	90.2	74.5
82.5°	77.4	65.9	68.8	57.3	50.1
85°	43.0	37.2	38.7	30.1	22.9
87.5°	20.1	17.2	17.2	11.5	7.2
90°	13.0	8.3	7.7	5.3	3.0
92.5°	80.1	57.0	52.0	31.9	11.8
95°	197.1	111.0	101.8	65.0	28.4
97.5°	265.6	122.0	113.8	81.5	49.0
100°	290.4	131.1	123.8	94.4	64.9
102.5°	301.9	140.3	133.4	106.0	78.5
105°	310.3	153.9	148.0	124.8	101.6
107.5°	311.9	173.9	168.5	146.9	125.2
110°	309.5	185.1	180.2	160.6	141.1

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	309.6	198.7	194.1	175.4	156.8
115°	312.5	219.1	214.8	197.6	180.4
117.5°	318.3	238.8	234.9	219.4	203.7
120°	323.0	250.4	246.7	232.0	217.3
122.5°	329.8	264.0	260.2	245.4	230.6
125°	338.9	281.3	278.0	264.4	251.0
127.5°	348.1	298.2	294.8	281.2	267.5
130°	354.8	309.4	305.8	291.1	276.4
132.5°	360.2	318.6	315.0	300.3	285.5
135°	366.1	329.2	325.8	312.5	299.1
137.5°	374.9	342.7	339.4	326.2	313.0
140°	380.4	351.9	348.9	336.7	324.5
142.5°	384.9	358.7	355.8	344.6	333.3
145°	390.9	369.1	366.6	356.8	347.0
147.5°	399.5	382.1	379.7	370.1	360.5
150°	404.1	388.9	386.7	378.1	369.4
152.5°	406.9	393.3	391.6	385.1	378.5
155°	413.4	403.0	401.8	397.0	392.1
157.5°	419.9	412.8	411.6	406.8	402.2
160°	422.9	417.1	416.2	412.6	408.9
162.5°	426.0	421.9	421.3	418.5	415.7
165°	430.6	428.7	428.0	425.5	423.1
167.5°	434.1	432.5	432.2	431.0	429.8
170°	437.1	437.0	436.7	435.5	434.3
172.5°	437.3	437.3	437.2	437.0	436.7
175°	439.1	440.0	440.0	440.0	440.0
177.5°	439.3	440.0	440.0	440.0	440.0
180°	440.0	440.0	440.0	440.0	440.0

TEST NUMBER: P934390

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.28	14.21	14.16	15.12	16.27	16.10	17.04	16.99	17.95	19.10
	3H	13.76	14.60	14.66	15.52	16.70	17.45	18.29	18.35	19.21	20.39
	4H	13.95	14.75	14.87	15.67	16.86	17.90	18.69	18.81	19.61	20.80
	6H	14.08	14.81	15.00	15.74	16.94	18.19	18.92	19.11	19.85	21.05
	8H	14.08	14.78	15.01	15.72	16.92	18.26	18.96	19.19	19.90	21.10
	12H	14.05	14.72	14.99	15.66	16.88	18.30	18.97	19.24	19.90	21.13
4H	2H	14.32	15.11	15.24	16.03	17.22	16.52	17.31	17.44	18.24	19.42
	3H	15.35	16.01	16.28	16.97	18.17	18.03	18.69	18.96	19.65	20.85
	4H	15.63	16.24	16.57	17.18	18.41	18.56	19.17	19.50	20.11	21.34
	6H	15.76	16.28	16.71	17.25	18.48	18.93	19.45	19.88	20.42	21.65
	8H	15.77	16.25	16.72	17.22	18.46	19.04	19.52	19.99	20.49	21.73
	12H	15.74	16.18	16.71	17.16	18.41	19.10	19.54	20.07	20.52	21.77
8H	4H	16.09	16.58	17.05	17.54	18.78	18.69	19.18	19.65	20.14	21.39
	6H	16.36	16.76	17.34	17.76	19.00	19.13	19.53	20.11	20.54	21.78
	8H	16.40	16.75	17.39	17.75	19.01	19.28	19.64	20.27	20.63	21.89
	12H	16.39	16.70	17.38	17.69	18.99	19.38	19.70	20.38	20.69	21.99
12H	4H	16.10	16.54	17.07	17.52	18.77	18.66	19.10	19.64	20.08	21.33
	6H	16.42	16.77	17.41	17.77	19.03	19.13	19.48	20.12	20.48	21.74
	8H	16.49	16.80	17.48	17.79	19.09	19.29	19.61	20.29	20.59	21.90

END OF REPORT