

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938298

Luminaire Tested: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938298
REPORT IS A COMBINATION OF REPORTS P933629 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7405.1 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938298

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P938298

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	30	30	21
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	26	25	24	24	24	17
2	83	75	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	20	20	14
3	75	66	59	53	66	59	53	48	45	40	37	32	29	27	20	18	17	17	17	12
4	69	58	50	45	60	52	45	40	39	35	31	28	25	23	17	16	14	14	14	10
5	63	51	44	38	55	46	39	34	35	30	27	25	22	19	15	14	12	12	12	8
6	57	46	38	32	51	41	34	29	31	26	23	22	19	17	14	12	11	11	11	7
7	53	41	33	28	47	37	30	25	28	23	20	20	17	14	12	11	9	9	9	6
8	49	37	30	24	43	33	27	22	25	21	17	18	15	13	11	9	8	8	8	5
9	45	34	26	21	40	30	24	19	23	18	15	17	13	11	10	9	7	7	7	5
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	6	6	6	4

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1875	1875	1875
5°	1831	2166	2522
10°	1659	3156	4180
15°	1408	4120	5048
20°	1146	4772	5144
25°	954	4989	5040
30°	804	5017	5031
35°	709	4929	5160
40°	617	4818	5295
45°	557	4733	5316
50°	510	4658	5228
55°	487	4548	4996
60°	496	4343	4630
65°	515	4032	4126
70°	543	3510	3487
75°	597	2854	2720
80°	641	1973	1835
85°	538	1044	937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5316 cd/sqm

TEST NUMBER: P938298

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.2	0.4
10°-20°	115.9	1.6
20°-30°	202.7	2.7
30°-40°	261.0	3.5
40°-50°	291.5	3.9
50°-60°	279.2	3.8
60°-70°	221.2	3.0
70°-80°	130.1	1.8
80°-90°	39.6	0.5
90°-100°	439.0	5.9
100°-110°	1154.1	15.6
110°-120°	1196.6	16.2
120°-130°	959.8	13.0
130°-140°	753.1	10.2
140°-150°	578.1	7.8
150°-160°	416.3	5.6
160°-170°	254.7	3.4
170°-180°	86.1	1.2
0°-30°	344.8	4.7
0°-40°	605.8	8.2
0°-60°	1176.5	15.9
0°-90°	1567.4	21.2
90°-120°	2789.6	37.7
90°-150°	5080.6	68.6
90°-180°	5838.0	78.8
0°-180°	7405.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	202	202	202	202	202	
5°	197	211	238	269	279	18
15°	148	272	459	556	574	41
25°	94	309	547	571	571	43
35°	64	295	515	544	566	40
45°	44	235	455	521	545	34
55°	31	150	386	449	461	28
65°	25	79	287	322	327	24
75°	18	49	157	173	174	19
85°	6	15	39	43	44	7
90°	6	17	46	23	23	5
95°	58	227	756	390	265	64
105°	208	315	1276	1937	1807	220
115°	369	448	1022	2039	2327	365
125°	514	576	930	1571	1853	456
135°	612	674	900	1268	1438	474
145°	710	755	889	1082	1166	445
155°	803	825	889	976	1004	369
165°	866	878	889	924	936	244
175°	900	900	895	907	907	85
180°	900	900	900	900	900	

TEST NUMBER: P938298

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	202.1	202.1	202.1	202.1	202.1	202.1	202.1	202.1	202.1	202.1	202.1
2.5°	202.1	202.1	203.5	204.1	205.4	206.1	207.4	208.6	212.6	213.2	214.5
5°	197.0	199.6	208.0	211.2	220.4	232.8	237.9	246.4	264.0	269.1	272.4
7.5°	189.1	195.1	215.8	221.0	243.8	276.3	289.9	308.1	336.0	349.7	360.8
10°	176.8	189.1	226.3	238.6	275.6	325.0	350.4	375.8	418.0	436.8	444.0
12.5°	163.2	183.3	237.3	254.2	307.5	379.7	410.2	438.2	486.2	511.6	515.5
15°	147.6	174.9	247.7	272.4	341.3	425.1	458.9	493.4	538.3	556.4	561.0
17.5°	133.9	168.4	257.5	283.4	367.3	466.1	500.6	529.2	565.5	577.9	581.1
20°	117.1	157.9	264.0	297.8	394.6	496.0	529.2	551.3	576.0	583.7	585.1
22.5°	104.7	146.9	267.8	302.9	412.8	514.2	542.2	559.7	576.6	579.2	579.8
25°	94.3	134.6	267.2	308.8	428.4	525.2	546.7	559.7	569.5	570.7	570.7
27.5°	84.5	120.9	264.5	310.1	440.1	527.8	544.8	553.9	558.4	561.0	561.0
30°	76.1	107.9	258.0	307.5	445.3	525.2	538.9	543.4	548.0	551.9	553.9
32.5°	69.6	95.5	248.4	302.2	445.9	518.7	528.5	531.1	537.6	546.7	549.9
35°	63.7	83.2	237.3	295.2	442.1	508.3	514.8	517.4	530.4	544.1	548.6
37.5°	57.8	74.1	223.0	282.8	436.1	496.0	500.6	505.1	525.2	541.5	546.7
40°	52.0	66.3	206.1	269.1	427.1	481.0	485.0	492.1	518.7	537.6	542.8
42.5°	47.5	59.8	187.9	254.8	415.4	464.2	470.0	480.4	511.0	531.1	536.9
45°	43.5	53.3	168.4	235.3	400.4	446.6	455.0	469.4	501.8	521.3	526.6
47.5°	39.6	48.7	148.3	215.2	384.2	429.1	440.1	456.3	489.5	508.3	512.9
50°	36.4	44.2	128.1	193.7	366.7	410.2	423.2	440.1	473.9	491.5	497.3
52.5°	33.8	40.3	109.2	172.3	346.5	390.7	405.6	423.2	455.0	471.9	475.9
55°	31.2	37.0	92.9	149.5	325.7	369.9	386.1	403.0	434.2	448.6	451.2
57.5°	29.9	34.5	79.3	128.1	303.6	346.5	364.6	380.2	409.5	420.5	423.2
60°	27.9	32.5	68.9	109.9	279.6	324.4	340.0	355.6	380.2	389.3	391.4
62.5°	26.0	31.2	61.1	92.3	254.8	298.4	314.0	328.3	349.0	355.6	358.1
65°	24.7	29.9	55.2	79.3	229.5	271.0	286.6	299.0	315.9	322.4	323.7
67.5°	23.4	28.6	50.7	68.2	204.1	243.8	255.4	267.2	280.1	286.6	287.3
70°	21.4	27.3	46.8	60.5	178.1	212.6	222.3	234.7	245.1	248.4	250.3
72.5°	20.2	25.4	44.2	54.7	151.5	182.7	191.8	198.9	208.0	211.2	211.2
75°	18.2	22.8	41.6	48.7	124.1	149.5	157.3	164.4	171.6	172.9	170.9
77.5°	16.3	20.2	35.8	41.0	96.9	118.3	124.8	128.7	134.6	135.9	136.5
80°	13.7	17.5	27.9	31.9	70.3	87.1	91.7	94.9	100.1	100.1	101.5
82.5°	10.4	13.7	20.2	22.8	47.5	59.8	63.7	65.7	68.9	68.9	68.9
85°	6.5	8.4	13.0	14.9	28.6	36.4	39.1	39.6	42.2	42.9	42.9
87.5°	3.3	4.6	8.4	9.1	14.9	18.9	18.9	20.2	20.2	19.5	18.9
90°	6.0	10.9	15.7	17.0	26.6	39.5	45.9	40.8	30.6	23.0	23.0
92.5°	24.1	65.2	106.4	116.7	164.0	227.0	258.6	226.6	162.8	114.8	110.3
95°	58.0	133.2	208.4	227.2	403.5	638.6	756.1	674.7	511.9	389.8	376.0
97.5°	100.3	166.7	233.0	249.6	543.5	935.5	1131.4	1080.0	977.0	899.9	873.6
100°	132.9	193.1	253.3	268.3	594.5	1029.4	1246.8	1250.6	1258.1	1263.8	1232.4
102.5°	160.8	217.0	273.1	287.1	617.9	1058.9	1279.5	1345.0	1476.1	1574.4	1547.6
105°	207.9	255.5	303.0	314.9	635.2	1062.2	1275.8	1422.7	1716.6	1937.0	1922.6
107.5°	256.3	300.6	345.0	356.0	638.5	1015.0	1203.3	1408.2	1818.1	2125.6	2129.1
110°	288.9	328.9	369.0	379.0	633.6	973.1	1142.8	1372.0	1830.2	2174.0	2189.0

TEST NUMBER: P938298

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	320.9	359.1	397.3	406.8	633.8	936.5	1087.9	1322.4	1791.4	2143.1	2166.2
115°	369.3	404.5	439.6	448.5	639.6	894.6	1022.0	1247.9	1699.7	2038.6	2070.7
117.5°	417.1	449.0	481.0	489.0	651.6	868.3	976.7	1180.5	1588.3	1894.1	1929.7
120°	444.8	474.9	504.9	512.5	661.1	859.4	958.5	1144.8	1517.4	1796.8	1831.3
122.5°	472.0	502.3	532.8	540.3	675.1	854.9	944.7	1112.4	1447.9	1699.5	1733.5
125°	513.8	541.4	569.1	576.0	693.8	851.0	929.6	1072.0	1357.0	1570.7	1602.1
127.5°	547.6	575.5	603.4	610.4	712.5	848.7	916.9	1039.3	1283.9	1467.5	1493.9
130°	565.7	595.7	625.8	633.3	726.3	850.1	912.0	1020.9	1238.8	1402.1	1426.6
132.5°	584.4	614.5	644.6	652.1	737.3	851.0	907.8	1005.2	1200.3	1346.5	1368.4
135°	612.2	639.6	667.0	673.8	749.4	850.1	900.5	982.2	1145.5	1267.9	1286.8
137.5°	640.6	667.7	694.9	701.7	767.5	855.4	899.3	968.3	1106.4	1210.0	1225.4
140°	664.2	689.2	714.2	720.5	778.7	856.3	895.1	954.7	1073.9	1163.4	1177.8
142.5°	682.4	705.4	728.5	734.3	787.9	859.3	895.1	947.5	1052.2	1130.8	1143.2
145°	710.2	730.3	750.4	755.4	800.0	859.4	889.1	931.9	1017.5	1081.8	1091.2
147.5°	737.9	757.6	777.1	782.1	817.7	865.3	889.1	922.8	990.1	1040.7	1048.5
150°	756.1	773.8	791.5	795.9	826.9	868.3	889.1	917.5	974.4	1017.2	1023.5
152.5°	774.8	788.3	801.7	805.0	833.0	870.4	889.1	913.4	962.0	998.5	1003.2
155°	802.6	812.6	822.5	825.0	846.3	874.8	889.1	908.4	947.1	976.1	979.3
157.5°	823.2	832.9	842.4	844.9	859.6	879.3	889.1	904.1	934.1	956.7	958.9
160°	837.0	844.6	852.1	854.0	865.7	881.3	889.1	901.9	927.7	947.0	948.3
162.5°	851.0	856.6	862.2	863.7	872.1	883.4	889.1	899.9	921.7	938.0	939.2
165°	866.1	871.1	876.3	877.5	881.4	886.5	889.1	896.8	912.4	924.0	925.3
167.5°	879.9	882.4	884.8	885.4	888.6	892.9	895.1	900.2	910.4	918.0	918.6
170°	889.1	891.5	893.9	894.5	894.7	895.0	895.1	900.2	910.4	918.0	918.0
172.5°	893.9	894.4	895.0	895.1	895.1	895.1	895.1	899.1	907.2	913.2	912.7
175°	900.5	900.5	900.5	900.5	898.7	896.2	895.1	897.6	902.7	906.6	906.6
177.5°	900.5	900.5	900.5	900.5	899.1	897.3	896.3	898.4	902.3	905.3	904.8
180°	900.5	900.5	900.5	900.5	900.5	900.5	900.5	900.5	900.5	900.5	900.5

TEST NUMBER: P938298

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	202.1	202.1
2.5°	215.8	214.5
5°	277.6	278.9
7.5°	373.7	373.2
10°	464.8	470.6
12.5°	531.1	532.4
15°	571.4	574.0
17.5°	587.0	587.7
20°	587.7	586.3
22.5°	580.5	579.2
25°	572.1	571.4
27.5°	564.2	564.9
30°	561.0	563.0
32.5°	561.0	564.2
35°	562.3	565.5
37.5°	561.6	565.5
40°	559.0	563.6
42.5°	551.9	555.1
45°	540.8	544.8
47.5°	526.6	529.2
50°	508.3	511.0
52.5°	485.6	486.2
55°	458.3	460.9
57.5°	429.1	429.7
60°	396.5	398.5
62.5°	362.1	362.1
65°	325.7	326.9
67.5°	288.0	291.2
70°	249.6	250.3
72.5°	211.9	211.9
75°	172.9	173.5
77.5°	135.9	135.9
80°	100.8	101.5
82.5°	69.6	70.8
85°	43.5	43.5
87.5°	20.2	18.2
90°	23.0	23.0
92.5°	92.0	73.7
95°	320.6	265.3
97.5°	768.3	663.0
100°	1107.0	981.5
102.5°	1440.1	1332.7
105°	1864.8	1807.1
107.5°	2143.0	2157.0
110°	2249.1	2309.3

TEST NUMBER: P938298

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2258.6	2351.0
115°	2198.8	2326.9
117.5°	2071.7	2213.8
120°	1969.4	2107.5
122.5°	1869.8	2005.9
125°	1727.5	1853.0
127.5°	1599.7	1705.5
130°	1524.3	1622.1
132.5°	1455.9	1543.5
135°	1362.3	1437.8
137.5°	1287.2	1348.9
140°	1235.6	1293.3
142.5°	1192.9	1242.5
145°	1128.9	1166.5
147.5°	1079.7	1110.9
150°	1048.7	1073.9
152.5°	1022.3	1041.3
155°	991.9	1004.5
157.5°	967.7	976.7
160°	953.4	958.5
162.5°	944.0	948.8
165°	930.4	935.6
167.5°	920.7	922.9
170°	918.0	918.0
172.5°	910.9	909.0
175°	906.6	906.6
177.5°	902.6	900.5
180°	900.5	900.5

(END OF REPORT)