

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937885

Luminaire Tested: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937885
REPORT IS A COMBINATION OF REPORTS P933597 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6320.2 lumens
Efficiency: N/A
Efficacy: 132.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 47.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937885

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P937885

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	84	80	81	78	75	72	60	58	56	44	42	41	28	28	27
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22
3	76	66	59	54	67	59	53	48	46	42	38	33	30	28	22	20	19
4	69	58	51	45	61	52	46	41	40	36	32	29	26	24	19	17	16
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13
6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	12
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9
9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8
10	42	31	24	19	38	28	21	17	22	17	14	16	13	10	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1848	1848	1848
5°	1805	2135	2485
10°	1635	3110	4120
15°	1388	4061	4975
20°	1129	4702	5070
25°	940	4917	4968
30°	792	4944	4958
35°	698	4858	5085
40°	609	4748	5218
45°	549	4666	5239
50°	503	4589	5153
55°	481	4483	4923
60°	489	4280	4563
65°	508	3974	4067
70°	536	3459	3437
75°	590	2812	2681
80°	632	1943	1808
85°	530	1028	924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5239 cd/sqm

TEST NUMBER: P937885

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.8	0.4
10°-20°	114.2	1.8
20°-30°	199.8	3.2
30°-40°	257.2	4.1
40°-50°	287.3	4.5
50°-60°	275.2	4.4
60°-70°	218.1	3.5
70°-80°	128.2	2.0
80°-90°	38.4	0.6
90°-100°	359.1	5.7
100°-110°	944.2	14.9
110°-120°	979.0	15.5
120°-130°	785.3	12.4
130°-140°	616.2	9.7
140°-150°	472.9	7.5
150°-160°	340.6	5.4
160°-170°	208.4	3.3
170°-180°	70.4	1.1
0°-30°	339.8	5.4
0°-40°	597.0	9.4
0°-60°	1159.5	18.3
0°-90°	1544.2	24.4
90°-120°	2282.3	36.1
90°-150°	4156.6	65.8
90°-180°	4776.0	75.6
0°-180°	6320.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	199	199	199	199	199	
5°	194	208	234	265	275	18
15°	145	268	452	548	566	40
25°	93	304	539	562	563	43
35°	63	291	507	536	557	39
45°	43	232	448	514	537	33
55°	31	147	381	442	454	28
65°	24	78	282	318	322	24
75°	18	48	155	170	171	19
85°	6	15	38	42	43	7
90°	5	14	38	19	19	5
95°	48	186	619	319	217	53
105°	170	258	1044	1585	1478	180
115°	302	367	836	1668	1904	298
125°	420	471	760	1285	1516	373
135°	501	551	737	1037	1176	388
145°	581	618	727	885	954	364
155°	657	675	727	799	822	302
165°	708	718	727	756	765	200
175°	737	737	732	742	742	70
180°	737	737	737	737	737	

TEST NUMBER: P937885

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	199.2	199.2	199.2	199.2	199.2	199.2	199.2	199.2	199.2	199.2	199.2
2.5°	199.2	199.2	200.5	201.1	202.5	203.1	204.4	205.6	209.5	210.1	211.4
5°	194.2	196.7	205.0	208.2	217.2	229.4	234.5	242.9	260.1	265.2	268.5
7.5°	186.4	192.2	212.7	217.8	240.3	272.3	285.7	303.7	331.2	344.7	355.5
10°	174.3	186.4	223.0	235.1	271.6	320.3	345.3	370.3	412.0	430.5	437.6
12.5°	160.8	180.7	233.9	250.5	303.0	374.2	404.3	431.9	479.2	504.2	508.1
15°	145.4	172.4	244.1	268.5	336.4	419.0	452.3	486.3	530.5	548.4	552.8
17.5°	132.0	166.0	253.7	279.3	361.9	459.4	493.4	521.5	557.3	569.6	572.7
20°	115.4	155.7	260.1	293.5	388.9	488.9	521.5	543.3	567.7	575.3	576.6
22.5°	103.1	144.8	264.0	298.5	406.8	506.7	534.3	551.6	568.2	570.8	571.5
25°	92.9	132.6	263.3	304.4	422.2	517.6	538.8	551.6	561.3	562.5	562.5
27.5°	83.3	119.2	260.7	305.6	433.8	520.2	536.9	545.9	550.4	552.8	552.8
30°	75.0	106.4	254.3	303.0	438.8	517.6	531.1	535.6	540.1	544.0	545.9
32.5°	68.6	94.2	244.8	297.9	439.5	511.2	520.9	523.4	529.8	538.8	542.0
35°	62.7	82.0	233.9	290.9	435.7	501.0	507.4	510.0	522.8	536.2	540.7
37.5°	57.0	73.1	219.7	278.7	429.8	488.9	493.4	497.8	517.6	533.7	538.8
40°	51.3	65.3	203.1	265.2	421.0	474.1	478.0	484.9	511.2	529.8	535.0
42.5°	46.8	58.9	185.2	251.2	409.4	457.4	463.2	473.5	503.6	523.4	529.2
45°	42.9	52.5	166.0	231.9	394.6	440.2	448.5	462.6	494.6	513.8	518.9
47.5°	39.1	48.0	146.1	212.1	378.7	422.9	433.8	449.7	482.5	501.0	505.5
50°	35.9	43.5	126.3	190.9	361.4	404.3	417.0	433.8	467.1	484.4	490.1
52.5°	33.3	39.7	107.6	169.8	341.5	385.1	399.8	417.0	448.5	465.1	469.0
55°	30.8	36.5	91.6	147.4	321.0	364.5	380.6	397.2	427.9	442.1	444.6
57.5°	29.5	34.0	78.1	126.3	299.2	341.5	359.4	374.7	403.6	414.5	417.0
60°	27.5	32.0	67.9	108.3	275.5	319.7	335.1	350.5	374.7	383.7	385.7
62.5°	25.6	30.8	60.3	91.0	251.2	294.0	309.4	323.6	344.0	350.5	353.0
65°	24.4	29.5	54.4	78.1	226.1	267.1	282.5	294.7	311.3	317.7	319.1
67.5°	23.1	28.2	49.9	67.2	201.1	240.3	251.7	263.3	276.1	282.5	283.2
70°	21.1	26.9	46.1	59.6	175.5	209.5	219.1	231.3	241.5	244.8	246.7
72.5°	19.9	25.0	43.5	53.9	149.3	180.0	189.0	196.1	205.0	208.2	208.2
75°	18.0	22.4	41.0	48.0	122.3	147.4	155.0	162.1	169.1	170.4	168.5
77.5°	16.0	19.9	35.2	40.4	95.5	116.6	123.0	126.8	132.6	133.9	134.6
80°	13.5	17.3	27.5	31.4	69.2	85.9	90.3	93.5	98.7	98.7	100.0
82.5°	10.2	13.5	19.9	22.4	46.8	58.9	62.7	64.7	67.9	67.9	67.9
85°	6.4	8.3	12.8	14.7	28.2	35.9	38.5	39.1	41.6	42.3	42.3
87.5°	3.2	4.5	8.3	9.0	14.7	18.6	18.6	19.9	19.9	19.2	18.6
90°	5.0	8.9	12.9	13.8	21.8	32.3	37.5	33.3	25.0	18.8	18.8
92.5°	19.8	53.4	87.0	95.4	134.2	185.8	211.6	185.5	133.2	94.0	90.2
95°	47.5	109.0	170.6	185.9	330.1	522.4	618.6	552.0	418.9	319.0	307.6
97.5°	82.0	136.3	190.6	204.2	444.6	765.2	925.6	883.5	799.3	736.2	714.7
100°	108.8	158.1	207.2	219.6	486.4	842.1	1020.0	1023.1	1029.3	1033.9	1008.2
102.5°	131.5	177.4	223.4	234.8	505.5	866.4	1046.8	1100.4	1207.7	1288.1	1266.1
105°	170.1	209.0	247.9	257.7	519.7	869.1	1043.8	1164.0	1404.4	1584.7	1572.9
107.5°	209.6	245.9	282.2	291.3	522.4	830.5	984.5	1152.2	1487.5	1739.0	1741.8
110°	236.4	269.1	301.8	310.0	518.4	796.2	935.0	1122.5	1497.4	1778.6	1790.9

TEST NUMBER: P937885

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	262.5	293.8	324.9	332.7	518.5	766.2	890.1	1081.9	1465.6	1753.4	1772.3
115°	302.1	330.9	359.7	366.9	523.3	731.8	836.1	1020.9	1390.6	1667.8	1694.0
117.5°	341.2	367.4	393.6	400.0	533.1	710.4	799.0	965.8	1299.4	1549.6	1578.6
120°	364.0	388.6	413.2	419.3	541.0	703.2	784.2	936.7	1241.4	1470.0	1498.3
122.5°	386.2	411.0	435.9	442.1	552.4	699.3	772.9	910.1	1184.6	1390.4	1418.3
125°	420.3	442.9	465.6	471.2	567.7	696.2	760.5	877.1	1110.2	1285.0	1310.7
127.5°	448.0	470.8	493.6	499.4	582.9	694.4	750.1	850.1	1050.4	1200.5	1222.2
130°	462.8	487.4	512.1	518.2	594.2	695.5	746.1	835.2	1013.4	1147.1	1167.1
132.5°	478.2	502.8	527.4	533.6	603.3	696.2	742.7	822.4	982.0	1101.7	1119.5
135°	500.9	523.3	545.7	551.3	613.1	695.5	736.8	803.6	937.2	1037.4	1052.9
137.5°	524.1	546.3	568.5	574.1	627.9	699.8	735.7	792.2	905.1	989.9	1002.5
140°	543.4	563.8	584.3	589.4	637.1	700.6	732.3	781.1	878.7	951.8	963.7
142.5°	558.2	577.1	596.0	600.8	644.6	703.1	732.3	775.2	860.8	925.1	935.2
145°	581.0	597.4	614.0	618.1	654.5	703.1	727.3	762.4	832.5	885.1	892.8
147.5°	603.8	619.8	635.8	639.8	669.0	707.8	727.3	754.9	810.1	851.5	857.9
150°	618.6	633.1	647.6	651.2	676.6	710.4	727.3	750.6	797.2	832.2	837.3
152.5°	633.9	644.9	655.9	658.7	681.6	712.0	727.3	747.2	787.0	816.8	820.7
155°	656.7	664.8	672.9	674.9	692.4	715.7	727.3	743.2	774.8	798.6	801.1
157.5°	673.5	681.4	689.2	691.2	703.3	719.3	727.3	739.6	764.3	782.7	784.5
160°	684.8	690.9	697.2	698.7	708.2	720.9	727.3	737.8	758.9	774.8	775.8
162.5°	696.2	700.8	705.5	706.6	713.5	722.7	727.3	736.2	754.1	767.4	768.4
165°	708.5	712.7	716.9	718.0	721.1	725.2	727.3	733.7	746.4	756.0	757.0
167.5°	720.0	721.9	723.9	724.4	727.0	730.6	732.3	736.5	744.8	751.1	751.6
170°	727.3	729.3	731.3	731.8	732.0	732.2	732.3	736.5	744.8	751.1	751.1
172.5°	731.3	731.7	732.2	732.3	732.3	732.3	732.3	735.5	742.1	747.1	746.7
175°	736.8	736.8	736.8	736.8	735.3	733.2	732.3	734.4	738.5	741.7	741.7
177.5°	736.8	736.8	736.8	736.8	735.6	734.0	733.2	734.9	738.2	740.7	740.2
180°	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8	736.8

TEST NUMBER: P937885

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	199.2	199.2
2.5°	212.7	211.4
5°	273.6	274.8
7.5°	368.3	367.8
10°	458.1	463.8
12.5°	523.4	524.7
15°	563.2	565.7
17.5°	578.5	579.2
20°	579.2	577.9
22.5°	572.1	570.8
25°	563.8	563.2
27.5°	556.1	556.8
30°	552.8	554.9
32.5°	552.8	556.1
35°	554.2	557.3
37.5°	553.5	557.3
40°	550.9	555.4
42.5°	544.0	547.1
45°	533.0	536.9
47.5°	518.9	521.5
50°	501.0	503.6
52.5°	478.6	479.2
55°	451.7	454.2
57.5°	422.9	423.4
60°	390.8	392.7
62.5°	356.9	356.9
65°	321.0	322.2
67.5°	283.8	287.0
70°	246.0	246.7
72.5°	208.9	208.9
75°	170.4	171.0
77.5°	133.9	133.9
80°	99.3	100.0
82.5°	68.6	69.8
85°	42.9	42.9
87.5°	19.9	18.0
90°	18.8	18.8
92.5°	75.3	60.4
95°	262.3	217.1
97.5°	628.6	542.4
100°	905.6	803.0
102.5°	1178.2	1090.3
105°	1525.7	1478.4
107.5°	1753.3	1764.7
110°	1840.1	1889.3



TEST NUMBER: P937885

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1847.8	1923.5
115°	1798.8	1903.7
117.5°	1694.9	1811.2
120°	1611.2	1724.2
122.5°	1529.6	1641.1
125°	1413.3	1516.0
127.5°	1308.7	1395.4
130°	1247.1	1327.2
132.5°	1191.2	1262.8
135°	1114.6	1176.3
137.5°	1053.1	1103.6
140°	1010.9	1058.1
142.5°	975.9	1016.6
145°	923.6	954.3
147.5°	883.3	908.8
150°	858.1	878.7
152.5°	836.3	852.0
155°	811.5	821.8
157.5°	791.8	799.0
160°	780.0	784.2
162.5°	772.4	776.3
165°	761.2	765.4
167.5°	753.3	755.0
170°	751.1	751.1
172.5°	745.2	743.7
175°	741.7	741.7
177.5°	738.5	736.8
180°	736.8	736.8

TEST NUMBER: P937885

CATALOG NUMBER: SQ4-FB-125U-050D-B2750-1D-UNV-W2A-W-4-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.11	0.80	1.25	1.93	3.53	13.25	13.94	14.40	15.07	16.67
	3H	0.80	1.42	1.95	2.56	4.17	15.06	15.68	16.21	16.82	18.43
	4H	1.09	1.68	2.25	2.82	4.44	15.69	16.27	16.85	17.42	19.03
	6H	1.34	1.87	2.50	3.02	4.65	16.10	16.64	17.27	17.78	19.41
	8H	1.40	1.91	2.57	3.07	4.69	16.21	16.72	17.38	17.88	19.50
	12H	1.41	1.90	2.59	3.05	4.69	16.26	16.75	17.44	17.90	19.54
4H	2H	7.28	7.87	8.45	9.01	10.62	13.50	14.09	14.67	15.24	16.85
	3H	8.83	9.32	10.01	10.49	12.12	15.52	16.01	16.69	17.18	18.80
	4H	8.92	9.37	10.10	10.53	12.17	16.27	16.72	17.44	17.88	19.52
	6H	8.92	9.31	10.10	10.49	12.12	16.78	17.17	17.97	18.35	19.99
	8H	8.89	9.26	10.07	10.43	12.08	16.94	17.30	18.12	18.47	20.12
	12H	8.84	9.17	10.04	10.35	12.01	17.01	17.34	18.21	18.52	20.18
8H	4H	10.34	10.70	11.52	11.87	13.52	16.31	16.67	17.49	17.85	19.50
	6H	10.57	10.87	11.78	12.09	13.74	16.92	17.22	18.12	18.44	20.08
	8H	10.59	10.85	11.80	12.04	13.71	17.13	17.39	18.34	18.58	20.25
	12H	10.55	10.78	11.76	11.97	13.67	17.26	17.49	18.47	18.68	20.38
12H	4H	10.47	10.80	11.67	11.98	13.64	16.26	16.59	17.45	17.77	19.42
	6H	10.83	11.09	12.03	12.28	13.95	16.90	17.16	18.11	18.36	20.02
	8H	10.89	11.12	12.10	12.31	14.01	17.12	17.35	18.33	18.54	20.23