

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934391

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934391
REPORT IS A COMBINATION OF REPORTS P933695 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6630.4 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

Luminous Intensity Polar Plot



TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9161	9161	9161	9161
5°	9226	9247	9226	7271
10°	9161	9109	9161	6513
15°	9058	8912	9058	7442
20°	8865	8678	8865	7457
25°	8474	8337	8474	7299
30°	7969	8054	7969	6952
35°	7101	7696	7101	6571
40°	5913	7274	5913	6283
45°	5280	6781	5280	5952
50°	5605	6192	5605	5619
55°	5269	5558	5269	5426
60°	5425	4720	5425	4971
65°	4910	3902	4910	4362
70°	3392	3110	3392	3657
75°	2963	2299	2963	2753
80°	2373	1520	2373	1655
85°	1335	804	1335	684

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8098 cd/sqm

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.7	2.0
10°-20°	379.5	5.7
20°-30°	586.7	8.8
30°-40°	700.4	10.6
40°-50°	704.5	10.6
50°-60°	613.0	9.2
60°-70°	434.6	6.6
70°-80°	229.9	3.5
80°-90°	58.9	0.9
90°-100°	209.7	3.2
100°-110°	551.4	8.3
110°-120°	571.7	8.6
120°-130°	458.6	6.9
130°-140°	359.8	5.4
140°-150°	276.2	4.2
150°-160°	198.9	3.0
160°-170°	121.7	1.8
170°-180°	41.1	0.6
0°-30°	1099.9	16.6
0°-40°	1800.3	27.2
0°-60°	3117.8	47.0
0°-90°	3841.2	57.9
90°-120°	1332.8	20.1
90°-150°	2427.4	36.6
90°-180°	2789.0	42.1
0°-180°	6630.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1481	1481	1481	1481	1481	
5°	1488	1534	1488	1206	1488	141
15°	1421	1520	1421	1269	1421	400
25°	1251	1418	1251	1241	1251	574
35°	951	1265	951	1080	951	589
45°	614	1042	614	915	614	492
55°	500	769	500	751	500	460
65°	347	464	347	518	347	332
75°	132	220	132	263	132	138
85°	22	56	22	48	22	30
90°	3	11	3	11	3	3
95°	28	127	28	127	28	31
105°	99	863	99	863	99	105
115°	176	1112	176	1112	176	174
125°	246	885	246	885	246	218
135°	292	687	292	687	292	226
145°	339	557	339	557	339	213
155°	384	480	384	480	384	176
165°	414	447	414	447	414	117
175°	430	433	430	433	430	41
180°	430	430	430	430	430	

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9
2.5°	1493.5	1493.5	1501.9	1504.7	1504.7	1500.5	1496.3	1500.5	1513.1	1517.3	1515.9
5°	1487.9	1499.1	1514.5	1517.3	1520.1	1518.7	1515.9	1518.7	1532.7	1535.5	1536.9
7.5°	1476.7	1497.7	1517.3	1521.5	1525.7	1521.5	1520.1	1522.9	1536.9	1539.7	1539.7
10°	1462.6	1492.1	1514.5	1517.3	1521.5	1517.3	1517.3	1522.9	1536.9	1539.7	1541.1
12.5°	1443.0	1483.7	1504.7	1507.5	1513.1	1511.7	1510.3	1515.9	1529.9	1532.7	1532.7
15°	1420.6	1468.2	1487.9	1490.7	1500.5	1497.7	1497.7	1503.3	1518.7	1522.9	1521.5
17.5°	1389.8	1448.6	1471.1	1475.3	1482.3	1480.9	1482.3	1487.9	1501.9	1504.7	1506.1
20°	1354.8	1422.0	1448.6	1452.8	1459.8	1459.8	1459.8	1466.8	1480.9	1486.5	1486.5
22.5°	1307.1	1394.0	1422.0	1424.8	1433.2	1433.2	1436.0	1445.8	1458.4	1459.8	1459.8
25°	1251.1	1363.2	1387.0	1395.4	1403.8	1408.0	1412.2	1417.8	1422.0	1420.6	1422.0
27.5°	1192.3	1323.9	1354.8	1360.4	1371.6	1375.8	1381.4	1382.8	1384.2	1388.4	1385.6
30°	1126.4	1269.3	1315.5	1321.1	1339.4	1342.2	1336.6	1339.4	1346.4	1349.2	1352.0
32.5°	1052.2	1188.0	1274.9	1287.5	1304.3	1295.9	1294.5	1298.7	1309.9	1309.9	1312.7
35°	951.3	1125.0	1237.1	1248.3	1260.9	1251.1	1256.7	1258.1	1265.1	1269.3	1267.9
37.5°	840.6	1070.4	1197.9	1206.3	1216.1	1203.5	1211.9	1216.1	1221.7	1218.9	1218.9
40°	742.5	984.9	1151.6	1157.2	1165.6	1155.8	1164.2	1167.0	1169.8	1167.0	1165.6
42.5°	669.7	891.0	1102.6	1109.6	1104.0	1111.0	1113.8	1119.4	1115.2	1109.6	1109.6
45°	613.6	865.8	1049.3	1057.8	1049.3	1060.6	1064.8	1064.8	1052.2	1049.3	1047.9
47.5°	595.4	815.4	996.1	996.1	991.9	1005.9	1012.9	1003.1	990.5	986.3	986.3
50°	594.0	759.3	923.3	917.7	937.3	954.1	947.1	937.3	927.5	912.1	912.1
52.5°	539.4	690.7	829.4	850.4	881.2	891.0	879.8	870.0	853.2	846.2	840.6
55°	500.2	619.2	743.9	786.0	818.2	830.8	809.8	800.0	774.8	770.6	767.7
57.5°	491.8	515.6	665.5	718.7	757.9	756.5	743.9	725.7	704.7	700.5	699.1
60°	451.1	372.7	581.4	644.5	685.1	680.9	669.7	652.9	633.3	630.4	627.6
62.5°	409.1	270.4	486.1	557.6	615.0	613.6	603.8	578.6	564.6	557.6	552.0
65°	347.4	227.0	346.0	463.7	546.4	549.2	528.2	510.0	494.6	486.1	484.7
67.5°	264.8	184.9	234.0	386.7	480.5	477.7	451.1	442.7	423.1	418.9	410.5
70°	196.1	123.3	162.5	313.8	416.1	409.1	388.1	378.3	360.1	350.2	344.6
72.5°	162.5	99.5	119.1	243.8	350.2	341.8	323.6	312.4	297.0	288.6	283.0
75°	131.7	105.1	91.1	180.7	284.4	278.8	262.0	250.8	238.2	227.0	228.4
77.5°	96.7	98.1	72.9	133.1	225.6	217.2	207.3	193.3	187.7	176.5	176.5
80°	72.9	77.1	54.6	91.1	162.5	162.5	154.1	144.3	134.5	128.9	128.9
82.5°	49.0	49.0	40.6	57.4	110.7	106.5	100.9	98.1	92.5	89.7	89.7
85°	22.4	28.0	25.2	35.0	60.2	63.0	63.0	60.2	58.8	56.0	57.4
87.5°	7.0	12.6	15.4	19.6	30.8	32.2	33.6	33.6	33.6	35.0	35.0
90°	2.9	5.2	7.6	8.1	12.7	18.9	21.9	19.5	14.6	10.9	10.9
92.5°	11.6	31.2	50.8	55.8	78.4	108.5	123.6	108.3	77.7	54.8	52.7
95°	27.7	63.6	99.6	108.5	192.8	305.1	361.3	322.4	244.6	186.2	179.6
97.5°	47.9	79.7	111.3	119.3	259.7	447.0	540.6	516.0	466.8	429.9	417.3
100°	63.5	92.3	121.0	128.2	284.0	491.8	595.7	597.5	601.1	603.8	588.9
102.5°	76.8	103.7	130.5	137.2	295.2	505.9	611.3	642.6	705.3	752.2	739.4
105°	99.4	122.1	144.8	150.5	303.5	507.5	609.5	679.8	820.1	925.5	918.6
107.5°	122.4	143.6	164.8	170.1	305.0	484.9	574.9	672.8	868.6	1015.5	1017.2
110°	138.0	157.1	176.2	181.0	302.7	464.9	546.0	655.5	874.5	1038.7	1045.9

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	153.4	171.6	189.8	194.4	302.8	447.5	519.8	631.9	855.9	1023.9	1035.0
115°	176.4	193.2	210.1	214.3	305.6	427.4	488.3	596.3	812.1	974.0	989.3
117.5°	199.2	214.5	229.8	233.6	311.3	414.9	466.6	564.0	758.9	905.0	922.0
120°	212.5	226.9	241.3	244.9	315.9	410.6	457.9	547.0	725.0	858.4	875.0
122.5°	225.6	240.0	254.5	258.2	322.5	408.3	451.3	531.4	691.8	812.0	828.3
125°	245.5	258.6	271.9	275.2	331.5	406.6	444.1	512.2	648.4	750.5	765.4
127.5°	261.6	275.0	288.3	291.7	340.4	405.5	438.0	496.5	613.4	701.1	713.7
130°	270.3	284.7	299.1	302.6	347.0	406.1	435.7	487.7	591.9	670.0	681.6
132.5°	279.3	293.6	308.0	311.6	352.3	406.6	433.7	480.4	573.5	643.3	653.8
135°	292.5	305.6	318.7	321.9	358.1	406.2	430.3	469.3	547.3	605.8	614.9
137.5°	306.1	319.1	331.9	335.2	366.7	408.6	429.6	462.6	528.6	578.1	585.4
140°	317.4	329.3	341.2	344.2	372.0	409.1	427.7	456.2	513.1	555.8	562.7
142.5°	326.0	337.0	348.0	350.8	376.4	410.6	427.7	452.7	502.7	540.2	546.2
145°	339.3	348.9	358.6	361.0	382.3	410.6	424.8	445.2	486.1	516.9	521.4
147.5°	352.6	361.9	371.4	373.7	390.7	413.4	424.8	440.8	473.1	497.3	501.0
150°	361.3	369.8	378.2	380.3	395.2	414.9	424.8	438.4	465.6	486.0	488.9
152.5°	370.1	376.6	383.0	384.6	398.0	415.8	424.8	436.4	459.6	477.0	479.2
155°	383.5	388.3	392.9	394.1	404.3	418.0	424.8	434.0	452.5	466.3	467.8
157.5°	393.3	397.9	402.6	403.7	410.7	420.1	424.8	432.0	446.4	457.1	458.1
160°	399.9	403.5	407.0	408.0	413.6	421.0	424.8	430.9	443.3	452.5	453.1
162.5°	406.6	409.3	412.0	412.6	416.7	422.1	424.8	430.0	440.4	448.1	448.7
165°	413.8	416.2	418.6	419.3	421.1	423.6	424.8	428.5	435.9	441.5	442.2
167.5°	420.4	421.5	422.7	423.0	424.6	426.7	427.7	430.1	435.0	438.6	438.9
170°	424.8	425.9	427.1	427.4	427.5	427.6	427.7	430.1	435.0	438.6	438.6
172.5°	427.1	427.4	427.6	427.7	427.7	427.7	427.7	429.5	433.4	436.3	436.1
175°	430.3	430.3	430.3	430.3	429.5	428.2	427.7	428.9	431.3	433.1	433.1
177.5°	430.3	430.3	430.3	430.3	429.6	428.7	428.2	429.2	431.1	432.5	432.3
180°	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9
2.5°	1518.7	1514.5	1518.7	1515.9	1517.3	1513.1	1500.5	1496.3	1500.5	1504.7	1504.7
5°	1536.9	1534.1	1536.9	1536.9	1535.5	1532.7	1518.7	1515.9	1518.7	1520.1	1517.3
7.5°	1542.5	1538.3	1542.5	1539.7	1539.7	1536.9	1522.9	1520.1	1521.5	1525.7	1521.5
10°	1542.5	1538.3	1542.5	1541.1	1539.7	1536.9	1522.9	1517.3	1517.3	1521.5	1517.3
12.5°	1535.5	1532.7	1535.5	1532.7	1532.7	1529.9	1515.9	1510.3	1511.7	1513.1	1507.5
15°	1524.3	1520.1	1524.3	1521.5	1522.9	1518.7	1503.3	1497.7	1497.7	1500.5	1490.7
17.5°	1507.5	1501.9	1507.5	1506.1	1504.7	1501.9	1487.9	1482.3	1480.9	1482.3	1475.3
20°	1487.9	1483.7	1487.9	1486.5	1486.5	1480.9	1466.8	1459.8	1459.8	1459.8	1452.8
22.5°	1457.0	1452.8	1457.0	1459.8	1459.8	1458.4	1445.8	1436.0	1433.2	1433.2	1424.8
25°	1422.0	1417.8	1422.0	1422.0	1420.6	1422.0	1417.8	1412.2	1408.0	1403.8	1395.4
27.5°	1388.4	1385.6	1388.4	1385.6	1388.4	1384.2	1382.8	1381.4	1375.8	1371.6	1360.4
30°	1354.8	1352.0	1354.8	1352.0	1349.2	1346.4	1339.4	1336.6	1342.2	1339.4	1321.1
32.5°	1312.7	1309.9	1312.7	1312.7	1309.9	1309.9	1298.7	1294.5	1295.9	1304.3	1287.5
35°	1269.3	1265.1	1269.3	1267.9	1269.3	1265.1	1258.1	1256.7	1251.1	1260.9	1248.3
37.5°	1218.9	1214.7	1218.9	1218.9	1218.9	1221.7	1216.1	1211.9	1203.5	1216.1	1206.3
40°	1167.0	1161.4	1167.0	1165.6	1167.0	1169.8	1167.0	1164.2	1155.8	1165.6	1157.2
42.5°	1108.2	1106.8	1108.2	1109.6	1109.6	1115.2	1119.4	1113.8	1111.0	1104.0	1109.6
45°	1045.1	1042.3	1045.1	1047.9	1049.3	1052.2	1064.8	1064.8	1060.6	1049.3	1057.8
47.5°	977.9	970.9	977.9	986.3	986.3	990.5	1003.1	1012.9	1005.9	991.9	996.1
50°	906.4	907.8	906.4	912.1	912.1	927.5	937.3	947.1	954.1	937.3	917.7
52.5°	836.4	835.0	836.4	840.6	846.2	853.2	870.0	879.8	891.0	881.2	850.4
55°	766.3	769.1	766.3	767.7	770.6	774.8	800.0	809.8	830.8	818.2	786.0
57.5°	696.3	692.1	696.3	699.1	700.5	704.7	725.7	743.9	756.5	757.9	718.7
60°	615.0	609.4	615.0	627.6	630.4	633.3	652.9	669.7	680.9	685.1	644.5
62.5°	543.6	533.8	543.6	552.0	557.6	564.6	578.6	603.8	613.6	615.0	557.6
65°	467.9	463.7	467.9	484.7	486.1	494.6	510.0	528.2	549.2	546.4	463.7
67.5°	399.3	399.3	399.3	410.5	418.9	423.1	442.7	451.1	477.7	480.5	386.7
70°	336.2	334.8	336.2	344.6	350.2	360.1	378.3	388.1	409.1	416.1	313.8
72.5°	276.0	274.6	276.0	283.0	288.6	297.0	312.4	323.6	341.8	350.2	243.8
75°	222.8	220.0	222.8	228.4	227.0	238.2	250.8	262.0	278.8	284.4	180.7
77.5°	170.9	170.9	170.9	176.5	176.5	187.7	193.3	207.3	217.2	225.6	133.1
80°	127.5	126.1	127.5	128.9	128.9	134.5	144.3	154.1	162.5	162.5	91.1
82.5°	89.7	86.9	89.7	89.7	89.7	92.5	98.1	100.9	106.5	110.7	57.4
85°	56.0	56.0	56.0	57.4	56.0	58.8	60.2	63.0	63.0	60.2	35.0
87.5°	36.4	35.0	36.4	35.0	35.0	33.6	33.6	33.6	32.2	30.8	19.6
90°	10.9	10.9	10.9	10.9	10.9	14.6	19.5	21.9	18.9	12.7	8.1
92.5°	43.9	35.2	43.9	52.7	54.8	77.7	108.3	123.6	108.5	78.4	55.8
95°	153.2	126.7	153.2	179.6	186.2	244.6	322.4	361.3	305.1	192.8	108.5
97.5°	367.1	316.8	367.1	417.3	429.9	466.8	516.0	540.6	447.0	259.7	119.3
100°	528.9	469.0	528.9	588.9	603.8	601.1	597.5	595.7	491.8	284.0	128.2
102.5°	688.1	636.7	688.1	739.4	752.2	705.3	642.6	611.3	505.9	295.2	137.2
105°	891.0	863.4	891.0	918.6	925.5	820.1	679.8	609.5	507.5	303.5	150.5
107.5°	1023.9	1030.6	1023.9	1017.2	1015.5	868.6	672.8	574.9	484.9	305.0	170.1
110°	1074.6	1103.3	1074.6	1045.9	1038.7	874.5	655.5	546.0	464.9	302.7	181.0

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1079.1	1123.2	1079.1	1035.0	1023.9	855.9	631.9	519.8	447.5	302.8	194.4
115°	1050.5	1111.7	1050.5	989.3	974.0	812.1	596.3	488.3	427.4	305.6	214.3
117.5°	989.9	1057.8	989.9	922.0	905.0	758.9	564.0	466.6	414.9	311.3	233.6
120°	940.9	1006.9	940.9	875.0	858.4	725.0	547.0	457.9	410.6	315.9	244.9
122.5°	893.4	958.4	893.4	828.3	812.0	691.8	531.4	451.3	408.3	322.5	258.2
125°	825.4	885.3	825.4	765.4	750.5	648.4	512.2	444.1	406.6	331.5	275.2
127.5°	764.3	814.9	764.3	713.7	701.1	613.4	496.5	438.0	405.5	340.4	291.7
130°	728.3	775.0	728.3	681.6	670.0	591.9	487.7	435.7	406.1	347.0	302.6
132.5°	695.6	737.5	695.6	653.8	643.3	573.5	480.4	433.7	406.6	352.3	311.6
135°	650.9	687.0	650.9	614.9	605.8	547.3	469.3	430.3	406.2	358.1	321.9
137.5°	615.0	644.6	615.0	585.4	578.1	528.6	462.6	429.6	408.6	366.7	335.2
140°	590.3	617.9	590.3	562.7	555.8	513.1	456.2	427.7	409.1	372.0	344.2
142.5°	569.9	593.7	569.9	546.2	540.2	502.7	452.7	427.7	410.6	376.4	350.8
145°	539.4	557.3	539.4	521.4	516.9	486.1	445.2	424.8	410.6	382.3	361.0
147.5°	515.8	530.7	515.8	501.0	497.3	473.1	440.8	424.8	413.4	390.7	373.7
150°	501.1	513.1	501.1	488.9	486.0	465.6	438.4	424.8	414.9	395.2	380.3
152.5°	488.4	497.5	488.4	479.2	477.0	459.6	436.4	424.8	415.8	398.0	384.6
155°	473.9	479.9	473.9	467.8	466.3	452.5	434.0	424.8	418.0	404.3	394.1
157.5°	462.4	466.6	462.4	458.1	457.1	446.4	432.0	424.8	420.1	410.7	403.7
160°	455.5	457.9	455.5	453.1	452.5	443.3	430.9	424.8	421.0	413.6	408.0
162.5°	451.0	453.4	451.0	448.7	448.1	440.4	430.0	424.8	422.1	416.7	412.6
165°	444.6	447.0	444.6	442.2	441.5	435.9	428.5	424.8	423.6	421.1	419.3
167.5°	439.9	440.9	439.9	438.9	438.6	435.0	430.1	427.7	426.7	424.6	423.0
170°	438.6	438.6	438.6	438.6	438.6	435.0	430.1	427.7	427.6	427.5	427.4
172.5°	435.2	434.3	435.2	436.1	436.3	433.4	429.5	427.7	427.7	427.7	427.7
175°	433.1	433.1	433.1	433.1	433.1	431.3	428.9	427.7	428.2	429.5	430.3
177.5°	431.3	430.3	431.3	432.3	432.5	431.1	429.2	428.2	428.7	429.6	430.3
180°	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9
2.5°	1501.9	1493.5	1493.5	1479.5	1473.9	1469.6	1462.6	1441.6	1436.0	1430.4	1438.8
5°	1514.5	1499.1	1487.9	1462.6	1441.6	1433.2	1406.6	1356.2	1322.5	1297.3	1283.3
7.5°	1517.3	1497.7	1476.7	1437.4	1387.0	1364.6	1283.3	1190.9	1165.6	1143.2	1129.2
10°	1514.5	1492.1	1462.6	1403.8	1284.7	1245.5	1164.2	1104.0	1088.6	1084.4	1088.6
12.5°	1504.7	1483.7	1443.0	1345.0	1178.2	1151.6	1104.0	1069.0	1066.2	1073.2	1111.0
15°	1487.9	1468.2	1420.6	1266.5	1119.4	1099.8	1066.2	1053.6	1069.0	1118.0	1231.5
17.5°	1471.1	1448.6	1389.8	1189.4	1074.6	1060.6	1036.7	1062.0	1148.8	1214.7	1252.5
20°	1448.6	1422.0	1354.8	1133.4	1042.3	1029.7	1018.5	1132.0	1197.9	1221.7	1242.7
22.5°	1422.0	1394.0	1307.1	1094.2	1008.7	998.9	1005.9	1171.2	1197.9	1214.7	1232.9
25°	1387.0	1363.2	1251.1	1063.4	982.1	970.9	997.5	1167.0	1182.4	1186.6	1223.1
27.5°	1354.8	1323.9	1192.3	1035.3	949.9	945.7	1004.5	1148.8	1160.0	1164.2	1203.5
30°	1315.5	1269.3	1126.4	1005.9	916.3	914.9	1005.9	1126.4	1123.6	1134.8	1174.0
32.5°	1274.9	1188.0	1052.2	969.5	884.0	882.6	996.1	1092.8	1090.0	1105.4	1134.8
35°	1237.1	1125.0	951.3	927.5	843.4	844.8	972.3	1053.6	1055.0	1069.0	1087.2
37.5°	1197.9	1070.4	840.6	881.2	804.2	804.2	940.1	1017.1	1014.3	1018.5	1043.7
40°	1151.6	984.9	742.5	821.0	767.7	763.5	900.8	977.9	968.1	966.7	1001.7
42.5°	1102.6	891.0	669.7	741.1	725.7	720.1	853.2	930.3	912.1	916.3	961.1
45°	1049.3	865.8	613.6	626.2	682.3	678.1	801.4	875.6	863.0	874.2	920.5
47.5°	996.1	815.4	595.4	519.8	636.1	634.7	743.9	822.4	815.4	826.6	875.6
50°	923.3	759.3	594.0	445.5	584.2	589.8	675.3	770.6	770.6	780.4	832.2
52.5°	829.4	690.7	539.4	403.5	524.0	540.8	615.0	725.7	728.5	738.3	784.6
55°	743.9	619.2	500.2	371.3	452.5	488.9	556.2	679.5	685.1	694.9	736.9
57.5°	665.5	515.6	491.8	333.4	386.7	421.7	504.4	634.7	637.5	645.9	686.5
60°	581.4	372.7	451.1	292.8	329.2	355.9	456.7	581.4	591.2	596.8	631.9
62.5°	486.1	270.4	409.1	264.8	301.2	306.8	417.5	531.0	543.6	547.8	568.8
65°	346.0	227.0	347.4	241.0	271.8	273.2	375.5	479.1	490.4	497.4	512.8
67.5°	234.0	184.9	264.8	218.6	249.4	250.8	334.8	418.9	434.3	439.9	449.7
70°	162.5	123.3	196.1	194.7	224.2	227.0	291.4	364.3	378.3	382.5	388.1
72.5°	119.1	99.5	162.5	175.1	197.5	200.3	246.6	302.6	316.6	320.8	323.6
75°	91.1	105.1	131.7	152.7	168.1	169.5	201.7	246.6	256.4	259.2	260.6
77.5°	72.9	98.1	96.7	123.3	137.3	134.5	158.3	190.5	198.9	198.9	198.9
80°	54.6	77.1	72.9	88.3	100.9	98.1	113.5	135.9	138.7	141.5	140.1
82.5°	40.6	49.0	49.0	56.0	67.2	64.4	75.7	88.3	88.3	88.3	91.1
85°	25.2	28.0	22.4	29.4	37.8	36.4	42.0	47.6	49.0	49.0	46.2
87.5°	15.4	12.6	7.0	11.2	16.8	16.8	19.6	21.0	19.6	19.6	19.6
90°	7.6	5.2	2.9	5.2	7.6	8.1	12.7	18.9	21.9	19.5	14.6
92.5°	50.8	31.2	11.6	31.2	50.8	55.8	78.4	108.5	123.6	108.3	77.7
95°	99.6	63.6	27.7	63.6	99.6	108.5	192.8	305.1	361.3	322.4	244.6
97.5°	111.3	79.7	47.9	79.7	111.3	119.3	259.7	447.0	540.6	516.0	466.8
100°	121.0	92.3	63.5	92.3	121.0	128.2	284.0	491.8	595.7	597.5	601.1
102.5°	130.5	103.7	76.8	103.7	130.5	137.2	295.2	505.9	611.3	642.6	705.3
105°	144.8	122.1	99.4	122.1	144.8	150.5	303.5	507.5	609.5	679.8	820.1
107.5°	164.8	143.6	122.4	143.6	164.8	170.1	305.0	484.9	574.9	672.8	868.6
110°	176.2	157.1	138.0	157.1	176.2	181.0	302.7	464.9	546.0	655.5	874.5

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	189.8	171.6	153.4	171.6	189.8	194.4	302.8	447.5	519.8	631.9	855.9
115°	210.1	193.2	176.4	193.2	210.1	214.3	305.6	427.4	488.3	596.3	812.1
117.5°	229.8	214.5	199.2	214.5	229.8	233.6	311.3	414.9	466.6	564.0	758.9
120°	241.3	226.9	212.5	226.9	241.3	244.9	315.9	410.6	457.9	547.0	725.0
122.5°	254.5	240.0	225.6	240.0	254.5	258.2	322.5	408.3	451.3	531.4	691.8
125°	271.9	258.6	245.5	258.6	271.9	275.2	331.5	406.6	444.1	512.2	648.4
127.5°	288.3	275.0	261.6	275.0	288.3	291.7	340.4	405.5	438.0	496.5	613.4
130°	299.1	284.7	270.3	284.7	299.1	302.6	347.0	406.1	435.7	487.7	591.9
132.5°	308.0	293.6	279.3	293.6	308.0	311.6	352.3	406.6	433.7	480.4	573.5
135°	318.7	305.6	292.5	305.6	318.7	321.9	358.1	406.2	430.3	469.3	547.3
137.5°	331.9	319.1	306.1	319.1	331.9	335.2	366.7	408.6	429.6	462.6	528.6
140°	341.2	329.3	317.4	329.3	341.2	344.2	372.0	409.1	427.7	456.2	513.1
142.5°	348.0	337.0	326.0	337.0	348.0	350.8	376.4	410.6	427.7	452.7	502.7
145°	358.6	348.9	339.3	348.9	358.6	361.0	382.3	410.6	424.8	445.2	486.1
147.5°	371.4	361.9	352.6	361.9	371.4	373.7	390.7	413.4	424.8	440.8	473.1
150°	378.2	369.8	361.3	369.8	378.2	380.3	395.2	414.9	424.8	438.4	465.6
152.5°	383.0	376.6	370.1	376.6	383.0	384.6	398.0	415.8	424.8	436.4	459.6
155°	392.9	388.3	383.5	388.3	392.9	394.1	404.3	418.0	424.8	434.0	452.5
157.5°	402.6	397.9	393.3	397.9	402.6	403.7	410.7	420.1	424.8	432.0	446.4
160°	407.0	403.5	399.9	403.5	407.0	408.0	413.6	421.0	424.8	430.9	443.3
162.5°	412.0	409.3	406.6	409.3	412.0	412.6	416.7	422.1	424.8	430.0	440.4
165°	418.6	416.2	413.8	416.2	418.6	419.3	421.1	423.6	424.8	428.5	435.9
167.5°	422.7	421.5	420.4	421.5	422.7	423.0	424.6	426.7	427.7	430.1	435.0
170°	427.1	425.9	424.8	425.9	427.1	427.4	427.5	427.6	427.7	430.1	435.0
172.5°	427.6	427.4	427.1	427.4	427.6	427.7	427.7	427.7	427.7	429.5	433.4
175°	430.3	430.3	430.3	430.3	430.3	430.3	429.5	428.2	427.7	428.9	431.3
177.5°	430.3	430.3	430.3	430.3	430.3	430.3	429.6	428.7	428.2	429.2	431.1
180°	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9	1480.9
2.5°	1429.0	1424.8	1430.4	1415.0	1430.4	1424.8	1429.0	1438.8	1430.4	1436.0	1441.6
5°	1253.9	1246.9	1224.5	1206.3	1224.5	1246.9	1253.9	1283.3	1297.3	1322.5	1356.2
7.5°	1120.8	1115.2	1109.6	1098.4	1109.6	1115.2	1120.8	1129.2	1143.2	1165.6	1190.9
10°	1091.4	1092.8	1101.2	1099.8	1101.2	1092.8	1091.4	1088.6	1084.4	1088.6	1104.0
12.5°	1167.0	1179.6	1225.9	1223.1	1225.9	1179.6	1167.0	1111.0	1073.2	1066.2	1069.0
15°	1253.9	1258.1	1267.9	1269.3	1267.9	1258.1	1253.9	1231.5	1118.0	1069.0	1053.6
17.5°	1262.3	1263.7	1270.7	1270.7	1270.7	1263.7	1262.3	1252.5	1214.7	1148.8	1062.0
20°	1255.3	1258.1	1272.1	1274.9	1272.1	1258.1	1255.3	1242.7	1221.7	1197.9	1132.0
22.5°	1252.5	1258.1	1269.3	1267.9	1269.3	1258.1	1252.5	1232.9	1214.7	1197.9	1171.2
25°	1238.5	1238.5	1239.9	1241.3	1239.9	1238.5	1238.5	1223.1	1186.6	1182.4	1167.0
27.5°	1209.1	1211.9	1220.3	1218.9	1220.3	1211.9	1209.1	1203.5	1164.2	1160.0	1148.8
30°	1182.4	1179.6	1172.6	1167.0	1172.6	1179.6	1182.4	1174.0	1134.8	1123.6	1126.4
32.5°	1137.6	1130.6	1123.6	1119.4	1123.6	1130.6	1137.6	1134.8	1105.4	1090.0	1092.8
35°	1084.4	1085.8	1084.4	1080.2	1084.4	1085.8	1084.4	1087.2	1069.0	1055.0	1053.6
37.5°	1046.5	1049.3	1047.9	1042.3	1047.9	1049.3	1046.5	1043.7	1018.5	1014.3	1017.1
40°	1007.3	1008.7	1007.3	1003.1	1007.3	1008.7	1007.3	1001.7	966.7	968.1	977.9
42.5°	969.5	968.1	963.9	961.1	963.9	968.1	969.5	961.1	916.3	912.1	930.3
45°	926.1	927.5	919.1	914.9	919.1	927.5	926.1	920.5	874.2	863.0	875.6
47.5°	882.6	882.6	875.6	871.4	875.6	882.6	882.6	875.6	826.6	815.4	822.4
50°	836.4	835.0	825.2	823.8	825.2	835.0	836.4	832.2	780.4	770.6	770.6
52.5°	783.2	783.2	784.6	787.4	784.6	783.2	783.2	784.6	738.3	728.5	725.7
55°	736.9	738.3	748.1	750.9	748.1	738.3	736.9	736.9	694.9	685.1	679.5
57.5°	689.3	689.3	696.3	696.3	696.3	689.3	689.3	686.5	645.9	637.5	634.7
60°	634.7	637.5	643.1	641.7	643.1	637.5	634.7	631.9	596.8	591.2	581.4
62.5°	577.2	580.0	581.4	578.6	581.4	580.0	577.2	568.8	547.8	543.6	531.0
65°	517.0	519.8	521.2	518.4	521.2	519.8	517.0	512.8	497.4	490.4	479.1
67.5°	455.3	453.9	452.5	458.1	452.5	453.9	455.3	449.7	439.9	434.3	418.9
70°	392.3	392.3	390.9	393.7	390.9	392.3	392.3	388.1	382.5	378.3	364.3
72.5°	325.0	323.6	329.2	325.0	329.2	323.6	325.0	323.6	320.8	316.6	302.6
75°	259.2	262.0	259.2	263.4	259.2	262.0	259.2	260.6	259.2	256.4	246.6
77.5°	197.5	200.3	197.5	197.5	197.5	200.3	197.5	198.9	198.9	198.9	190.5
80°	140.1	138.7	138.7	137.3	138.7	138.7	140.1	140.1	141.5	138.7	135.9
82.5°	89.7	88.3	88.3	91.1	88.3	88.3	89.7	91.1	88.3	88.3	88.3
85°	49.0	50.4	47.6	47.6	47.6	50.4	49.0	46.2	49.0	49.0	47.6
87.5°	18.2	16.8	16.8	16.8	16.8	16.8	18.2	19.6	19.6	19.6	21.0
90°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	14.6	19.5	21.9	18.9
92.5°	54.8	52.7	43.9	35.2	43.9	52.7	54.8	77.7	108.3	123.6	108.5
95°	186.2	179.6	153.2	126.7	153.2	179.6	186.2	244.6	322.4	361.3	305.1
97.5°	429.9	417.3	367.1	316.8	367.1	417.3	429.9	466.8	516.0	540.6	447.0
100°	603.8	588.9	528.9	469.0	528.9	588.9	603.8	601.1	597.5	595.7	491.8
102.5°	752.2	739.4	688.1	636.7	688.1	739.4	752.2	705.3	642.6	611.3	505.9
105°	925.5	918.6	891.0	863.4	891.0	918.6	925.5	820.1	679.8	609.5	507.5
107.5°	1015.5	1017.2	1023.9	1030.6	1023.9	1017.2	1015.5	868.6	672.8	574.9	484.9
110°	1038.7	1045.9	1074.6	1103.3	1074.6	1045.9	1038.7	874.5	655.5	546.0	464.9

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1023.9	1035.0	1079.1	1123.2	1079.1	1035.0	1023.9	855.9	631.9	519.8	447.5
115°	974.0	989.3	1050.5	1111.7	1050.5	989.3	974.0	812.1	596.3	488.3	427.4
117.5°	905.0	922.0	989.9	1057.8	989.9	922.0	905.0	758.9	564.0	466.6	414.9
120°	858.4	875.0	940.9	1006.9	940.9	875.0	858.4	725.0	547.0	457.9	410.6
122.5°	812.0	828.3	893.4	958.4	893.4	828.3	812.0	691.8	531.4	451.3	408.3
125°	750.5	765.4	825.4	885.3	825.4	765.4	750.5	648.4	512.2	444.1	406.6
127.5°	701.1	713.7	764.3	814.9	764.3	713.7	701.1	613.4	496.5	438.0	405.5
130°	670.0	681.6	728.3	775.0	728.3	681.6	670.0	591.9	487.7	435.7	406.1
132.5°	643.3	653.8	695.6	737.5	695.6	653.8	643.3	573.5	480.4	433.7	406.6
135°	605.8	614.9	650.9	687.0	650.9	614.9	605.8	547.3	469.3	430.3	406.2
137.5°	578.1	585.4	615.0	644.6	615.0	585.4	578.1	528.6	462.6	429.6	408.6
140°	555.8	562.7	590.3	617.9	590.3	562.7	555.8	513.1	456.2	427.7	409.1
142.5°	540.2	546.2	569.9	593.7	569.9	546.2	540.2	502.7	452.7	427.7	410.6
145°	516.9	521.4	539.4	557.3	539.4	521.4	516.9	486.1	445.2	424.8	410.6
147.5°	497.3	501.0	515.8	530.7	515.8	501.0	497.3	473.1	440.8	424.8	413.4
150°	486.0	488.9	501.1	513.1	501.1	488.9	486.0	465.6	438.4	424.8	414.9
152.5°	477.0	479.2	488.4	497.5	488.4	479.2	477.0	459.6	436.4	424.8	415.8
155°	466.3	467.8	473.9	479.9	473.9	467.8	466.3	452.5	434.0	424.8	418.0
157.5°	457.1	458.1	462.4	466.6	462.4	458.1	457.1	446.4	432.0	424.8	420.1
160°	452.5	453.1	455.5	457.9	455.5	453.1	452.5	443.3	430.9	424.8	421.0
162.5°	448.1	448.7	451.0	453.4	451.0	448.7	448.1	440.4	430.0	424.8	422.1
165°	441.5	442.2	444.6	447.0	444.6	442.2	441.5	435.9	428.5	424.8	423.6
167.5°	438.6	438.9	439.9	440.9	439.9	438.9	438.6	435.0	430.1	427.7	426.7
170°	438.6	438.6	438.6	438.6	438.6	438.6	438.6	435.0	430.1	427.7	427.6
172.5°	436.3	436.1	435.2	434.3	435.2	436.1	436.3	433.4	429.5	427.7	427.7
175°	433.1	433.1	433.1	433.1	433.1	433.1	433.1	431.3	428.9	427.7	428.2
177.5°	432.5	432.3	431.3	430.3	431.3	432.3	432.5	431.1	429.2	428.2	428.7
180°	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1480.9	1480.9	1480.9	1480.9	1480.9
2.5°	1462.6	1469.6	1473.9	1479.5	1493.5
5°	1406.6	1433.2	1441.6	1462.6	1487.9
7.5°	1283.3	1364.6	1387.0	1437.4	1476.7
10°	1164.2	1245.5	1284.7	1403.8	1462.6
12.5°	1104.0	1151.6	1178.2	1345.0	1443.0
15°	1066.2	1099.8	1119.4	1266.5	1420.6
17.5°	1036.7	1060.6	1074.6	1189.4	1389.8
20°	1018.5	1029.7	1042.3	1133.4	1354.8
22.5°	1005.9	998.9	1008.7	1094.2	1307.1
25°	997.5	970.9	982.1	1063.4	1251.1
27.5°	1004.5	945.7	949.9	1035.3	1192.3
30°	1005.9	914.9	916.3	1005.9	1126.4
32.5°	996.1	882.6	884.0	969.5	1052.2
35°	972.3	844.8	843.4	927.5	951.3
37.5°	940.1	804.2	804.2	881.2	840.6
40°	900.8	763.5	767.7	821.0	742.5
42.5°	853.2	720.1	725.7	741.1	669.7
45°	801.4	678.1	682.3	626.2	613.6
47.5°	743.9	634.7	636.1	519.8	595.4
50°	675.3	589.8	584.2	445.5	594.0
52.5°	615.0	540.8	524.0	403.5	539.4
55°	556.2	488.9	452.5	371.3	500.2
57.5°	504.4	421.7	386.7	333.4	491.8
60°	456.7	355.9	329.2	292.8	451.1
62.5°	417.5	306.8	301.2	264.8	409.1
65°	375.5	273.2	271.8	241.0	347.4
67.5°	334.8	250.8	249.4	218.6	264.8
70°	291.4	227.0	224.2	194.7	196.1
72.5°	246.6	200.3	197.5	175.1	162.5
75°	201.7	169.5	168.1	152.7	131.7
77.5°	158.3	134.5	137.3	123.3	96.7
80°	113.5	98.1	100.9	88.3	72.9
82.5°	75.7	64.4	67.2	56.0	49.0
85°	42.0	36.4	37.8	29.4	22.4
87.5°	19.6	16.8	16.8	11.2	7.0
90°	12.7	8.1	7.6	5.2	2.9
92.5°	78.4	55.8	50.8	31.2	11.6
95°	192.8	108.5	99.6	63.6	27.7
97.5°	259.7	119.3	111.3	79.7	47.9
100°	284.0	128.2	121.0	92.3	63.5
102.5°	295.2	137.2	130.5	103.7	76.8
105°	303.5	150.5	144.8	122.1	99.4
107.5°	305.0	170.1	164.8	143.6	122.4
110°	302.7	181.0	176.2	157.1	138.0



TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	302.8	194.4	189.8	171.6	153.4
115°	305.6	214.3	210.1	193.2	176.4
117.5°	311.3	233.6	229.8	214.5	199.2
120°	315.9	244.9	241.3	226.9	212.5
122.5°	322.5	258.2	254.5	240.0	225.6
125°	331.5	275.2	271.9	258.6	245.5
127.5°	340.4	291.7	288.3	275.0	261.6
130°	347.0	302.6	299.1	284.7	270.3
132.5°	352.3	311.6	308.0	293.6	279.3
135°	358.1	321.9	318.7	305.6	292.5
137.5°	366.7	335.2	331.9	319.1	306.1
140°	372.0	344.2	341.2	329.3	317.4
142.5°	376.4	350.8	348.0	337.0	326.0
145°	382.3	361.0	358.6	348.9	339.3
147.5°	390.7	373.7	371.4	361.9	352.6
150°	395.2	380.3	378.2	369.8	361.3
152.5°	398.0	384.6	383.0	376.6	370.1
155°	404.3	394.1	392.9	388.3	383.5
157.5°	410.7	403.7	402.6	397.9	393.3
160°	413.6	408.0	407.0	403.5	399.9
162.5°	416.7	412.6	412.0	409.3	406.6
165°	421.1	419.3	418.6	416.2	413.8
167.5°	424.6	423.0	422.7	421.5	420.4
170°	427.5	427.4	427.1	425.9	424.8
172.5°	427.7	427.7	427.6	427.4	427.1
175°	429.5	430.3	430.3	430.3	430.3
177.5°	429.6	430.3	430.3	430.3	430.3
180°	430.3	430.3	430.3	430.3	430.3

TEST NUMBER: P934391

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-6-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.20	14.14	14.09	15.04	16.20	16.02	16.96	16.91	17.87	19.02
	3H	13.68	14.52	14.58	15.44	16.62	17.37	18.21	18.27	19.13	20.31
	4H	13.88	14.67	14.79	15.59	16.78	17.82	18.61	18.73	19.54	20.72
	6H	14.00	14.73	14.93	15.66	16.86	18.11	18.84	19.03	19.77	20.97
	8H	14.00	14.70	14.94	15.65	16.85	18.18	18.88	19.12	19.83	21.03
	12H	13.98	14.64	14.92	15.58	16.81	18.22	18.89	19.16	19.83	21.05
4H	2H	14.24	15.04	15.16	15.96	17.14	16.44	17.24	17.36	18.16	19.35
	3H	15.27	15.94	16.20	16.89	18.09	17.95	18.62	18.88	19.57	20.77
	4H	15.55	16.16	16.49	17.11	18.33	18.48	19.09	19.42	20.04	21.26
	6H	15.68	16.20	16.64	17.18	18.40	18.85	19.37	19.81	20.34	21.57
	8H	15.69	16.18	16.65	17.14	18.38	18.96	19.45	19.92	20.41	21.65
	12H	15.66	16.10	16.64	17.08	18.33	19.02	19.46	19.99	20.44	21.69
8H	4H	16.01	16.50	16.97	17.46	18.71	18.62	19.10	19.57	20.07	21.31
	6H	16.28	16.68	17.26	17.69	18.93	19.05	19.46	20.04	20.46	21.70
	8H	16.32	16.68	17.31	17.67	18.93	19.21	19.56	20.20	20.56	21.81
	12H	16.31	16.62	17.30	17.61	18.92	19.31	19.62	20.30	20.61	21.91
12H	4H	16.02	16.46	17.00	17.44	18.69	18.58	19.02	19.56	20.00	21.25
	6H	16.34	16.69	17.33	17.69	18.95	19.05	19.41	20.04	20.40	21.66
	8H	16.41	16.72	17.40	17.71	19.02	19.22	19.53	20.21	20.52	21.82

END OF REPORT