

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934396

Luminaire Tested: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934396
REPORT IS A COMBINATION OF REPORTS P933696 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8840.4 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

Luminous Intensity Polar Plot



TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	95	91	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	57	60	55	50	51	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9160	9160	9160	9160
5°	9229	9247	9229	7271
10°	9167	9109	9167	6512
15°	9068	8911	9068	7441
20°	8878	8678	8878	7457
25°	8489	8336	8489	7299
30°	7988	8053	7988	6952
35°	7121	7695	7121	6570
40°	5934	7274	5934	6282
45°	5302	6780	5302	5951
50°	5633	6192	5633	5619
55°	5300	5558	5300	5426
60°	5463	4721	5463	4970
65°	4953	3902	4953	4362
70°	3430	3110	3430	3656
75°	3008	2299	3008	2753
80°	2423	1520	2423	1655
85°	1393	805	1393	684

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 8126 cd/sqm

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.2	2.0
10°-20°	506.0	5.7
20°-30°	782.2	8.8
30°-40°	933.8	10.6
40°-50°	939.3	10.6
50°-60°	817.3	9.2
60°-70°	579.5	6.6
70°-80°	306.6	3.5
80°-90°	78.5	0.9
90°-100°	279.6	3.2
100°-110°	735.2	8.3
110°-120°	762.3	8.6
120°-130°	611.4	6.9
130°-140°	479.8	5.4
140°-150°	368.3	4.2
150°-160°	265.2	3.0
160°-170°	162.3	1.8
170°-180°	54.8	0.6
0°-30°	1466.5	16.6
0°-40°	2400.3	27.2
0°-60°	4156.8	47.0
0°-90°	5121.5	57.9
90°-120°	1777.1	20.1
90°-150°	3236.6	36.6
90°-180°	3719.0	42.1
0°-180°	8840.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1974	1974	1974	1974	1974	
5°	1984	2045	1984	1608	1984	188
15°	1894	2027	1894	1692	1894	533
25°	1668	1890	1668	1655	1668	766
35°	1268	1687	1268	1440	1268	785
45°	818	1390	818	1220	818	655
55°	667	1026	667	1001	667	613
65°	463	618	463	691	463	443
75°	176	293	176	351	176	185
85°	30	75	30	64	30	40
90°	4	15	4	15	4	4
95°	37	169	37	169	37	41
105°	132	1151	132	1151	132	140
115°	235	1482	235	1482	235	232
125°	327	1180	327	1180	327	291
135°	390	916	390	916	390	302
145°	452	743	452	743	452	283
155°	511	640	511	640	511	235
165°	552	596	552	596	552	156
175°	574	578	574	578	574	54
180°	574	574	574	574	574	

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1991.2	1991.2	2002.4	2006.1	2006.1	2000.5	1994.9	2000.5	2017.3	2023.0	2021.1
5°	1983.7	1998.7	2019.2	2023.0	2026.7	2024.8	2021.1	2024.8	2043.5	2047.2	2049.1
7.5°	1968.8	1996.8	2023.0	2028.6	2034.2	2028.6	2026.7	2030.4	2049.1	2052.8	2052.8
10°	1950.1	1989.3	2019.2	2023.0	2028.6	2023.0	2023.0	2030.4	2049.1	2052.8	2054.7
12.5°	1923.9	1978.1	2006.1	2009.9	2017.3	2015.5	2013.6	2021.1	2039.8	2043.5	2043.5
15°	1894.1	1957.6	1983.7	1987.5	2000.5	1996.8	1996.8	2004.3	2024.8	2030.4	2028.6
17.5°	1853.0	1931.4	1961.3	1966.9	1976.3	1974.4	1976.3	1983.7	2002.4	2006.1	2008.0
20°	1806.3	1895.9	1931.4	1937.0	1946.4	1946.4	1946.4	1955.7	1974.4	1981.9	1981.9
22.5°	1742.8	1858.6	1895.9	1899.7	1910.9	1910.9	1914.6	1927.7	1944.5	1946.4	1946.4
25°	1668.0	1817.5	1849.2	1860.4	1871.6	1877.2	1882.9	1890.3	1895.9	1894.1	1895.9
27.5°	1589.6	1765.2	1806.3	1813.7	1828.7	1834.3	1841.8	1843.6	1845.5	1851.1	1847.4
30°	1501.8	1692.3	1754.0	1761.4	1785.7	1789.5	1782.0	1785.7	1795.1	1798.8	1802.5
32.5°	1402.8	1584.0	1699.8	1716.6	1739.0	1727.8	1725.9	1731.5	1746.5	1746.5	1750.2
35°	1268.3	1499.9	1649.4	1664.3	1681.1	1668.0	1675.5	1677.4	1686.7	1692.3	1690.4
37.5°	1120.7	1427.1	1597.0	1608.3	1621.3	1604.5	1615.7	1621.3	1628.8	1625.1	1625.1
40°	990.0	1313.1	1535.4	1542.9	1554.1	1541.0	1552.2	1556.0	1559.7	1556.0	1554.1
42.5°	892.9	1188.0	1470.0	1479.4	1471.9	1481.2	1485.0	1492.4	1486.8	1479.4	1479.4
45°	818.2	1154.3	1399.0	1410.2	1399.0	1414.0	1419.6	1419.6	1402.8	1399.0	1397.2
47.5°	793.9	1087.2	1328.1	1328.1	1322.5	1341.1	1350.5	1337.4	1320.6	1315.0	1315.0
50°	792.0	1012.5	1230.9	1223.4	1249.6	1272.0	1262.7	1249.6	1236.5	1216.0	1216.0
52.5°	719.2	920.9	1105.9	1133.8	1174.9	1188.0	1173.0	1159.9	1137.5	1128.2	1120.7
55°	666.9	825.7	991.9	1047.9	1090.9	1107.7	1079.7	1066.6	1033.0	1027.4	1023.7
57.5°	655.7	687.4	887.3	958.3	1010.6	1008.7	991.9	967.6	939.6	934.0	932.1
60°	601.5	496.9	775.2	859.3	913.5	907.8	892.9	870.5	844.3	840.6	836.9
62.5°	545.5	360.5	648.2	743.5	820.1	818.2	805.1	771.5	752.8	743.5	736.0
65°	463.3	302.6	461.4	618.3	728.5	732.3	704.2	680.0	659.4	648.2	646.3
67.5°	353.1	246.6	312.0	515.6	640.7	637.0	601.5	590.3	564.1	558.5	547.3
70°	261.5	164.4	216.7	418.4	554.8	545.5	517.4	504.4	480.1	467.0	459.5
72.5°	216.7	132.6	158.8	325.0	467.0	455.8	431.5	416.6	396.0	384.8	377.3
75°	175.6	140.1	121.4	241.0	379.2	371.7	349.3	334.4	317.6	302.6	304.5
77.5°	128.9	130.8	97.1	177.5	300.7	289.5	276.5	257.8	250.3	235.4	235.4
80°	97.1	102.7	72.9	121.4	216.7	216.7	205.5	192.4	179.3	171.9	171.9
82.5°	65.4	65.4	54.2	76.6	147.6	142.0	134.5	130.8	123.3	119.6	119.6
85°	29.9	37.4	33.6	46.7	80.3	84.1	84.1	80.3	78.5	74.7	76.6
87.5°	9.3	16.8	20.5	26.2	41.1	43.0	44.8	44.8	44.8	46.7	46.7
90°	3.8	6.9	10.0	10.7	16.9	25.1	29.2	26.0	19.5	14.7	14.7
92.5°	15.4	41.6	67.8	74.3	104.5	144.7	164.8	144.4	103.7	73.1	70.2
95°	37.0	84.9	132.8	144.8	257.0	406.8	481.7	429.8	326.2	248.4	239.6
97.5°	63.9	106.1	148.4	159.0	346.2	595.9	720.8	688.0	622.4	573.3	556.5
100°	84.7	123.0	161.3	170.9	378.7	655.8	794.3	796.7	801.5	805.0	785.0
102.5°	102.5	138.2	173.9	182.9	393.6	674.6	815.1	856.9	940.4	1002.9	985.8
105°	132.4	162.7	193.1	200.6	404.7	676.8	812.8	906.4	1093.6	1234.0	1224.8
107.5°	163.3	191.5	219.7	226.8	406.7	646.6	766.5	897.1	1158.3	1354.1	1356.4
110°	184.0	209.5	235.1	241.4	403.7	619.9	728.1	874.0	1165.9	1384.8	1394.5

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	204.5	228.7	253.0	259.1	403.8	596.6	693.0	842.4	1141.2	1365.2	1380.0
115°	235.3	257.7	280.1	285.7	407.5	569.9	651.1	795.0	1082.8	1298.6	1319.0
117.5°	265.6	286.0	306.4	311.5	415.1	553.1	622.1	752.1	1011.8	1206.6	1229.2
120°	283.4	302.5	321.8	326.5	421.2	547.5	610.6	729.3	966.6	1144.6	1166.6
122.5°	300.7	320.0	339.3	344.2	430.0	544.5	601.8	708.6	922.4	1082.7	1104.4
125°	327.3	344.8	362.5	366.9	442.0	542.1	592.2	682.9	864.5	1000.7	1020.7
127.5°	348.8	366.6	384.3	388.8	453.9	540.7	584.0	662.0	817.9	934.8	951.7
130°	360.3	379.5	398.7	403.5	462.6	541.5	580.9	650.3	789.1	893.2	908.8
132.5°	372.3	391.4	410.7	415.4	469.7	542.1	578.3	640.4	764.7	857.8	871.7
135°	390.0	407.5	424.9	429.3	477.4	541.5	573.7	625.7	729.7	807.7	819.8
137.5°	408.2	425.4	442.7	447.0	488.9	544.9	572.9	616.9	704.9	770.8	780.6
140°	423.1	439.1	455.0	459.0	496.0	545.5	570.2	608.2	684.2	741.1	750.3
142.5°	434.7	449.3	464.1	467.7	501.9	547.4	570.2	603.6	670.3	720.4	728.3
145°	452.4	465.2	478.1	481.3	509.7	547.5	566.4	593.7	648.3	689.2	695.2
147.5°	470.1	482.6	495.1	498.2	520.9	551.2	566.4	587.9	630.7	663.0	667.9
150°	481.7	493.0	504.3	507.1	526.9	553.2	566.4	584.5	620.8	648.0	652.0
152.5°	493.6	502.2	510.7	512.9	530.7	554.5	566.4	581.9	612.8	636.1	639.1
155°	511.3	517.6	524.0	525.6	539.2	557.3	566.4	578.7	603.3	621.8	623.8
157.5°	524.3	530.5	536.7	538.3	547.6	560.1	566.4	575.9	595.1	609.4	610.8
160°	533.2	538.1	542.8	544.1	551.5	561.4	566.4	574.6	590.9	603.3	604.1
162.5°	542.1	545.7	549.3	550.2	555.6	562.8	566.4	573.3	587.2	597.6	598.3
165°	551.7	555.0	558.2	559.0	561.4	564.7	566.4	571.3	581.2	588.7	589.5
167.5°	560.6	562.1	563.7	564.0	566.1	568.8	570.2	573.5	580.0	584.9	585.2
170°	566.4	567.9	569.5	569.8	569.9	570.1	570.2	573.5	580.0	584.9	584.9
172.5°	569.5	569.8	570.1	570.2	570.2	570.2	570.2	572.8	578.0	581.8	581.5
175°	573.7	573.7	573.7	573.7	572.5	571.0	570.2	571.8	575.1	577.5	577.5
177.5°	573.7	573.7	573.7	573.7	572.7	571.5	571.0	572.3	574.8	576.7	576.4
180°	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	2024.8	2019.2	2024.8	2021.1	2023.0	2017.3	2000.5	1994.9	2000.5	2006.1	2006.1
5°	2049.1	2045.4	2049.1	2049.1	2047.2	2043.5	2024.8	2021.1	2024.8	2026.7	2023.0
7.5°	2056.6	2051.0	2056.6	2052.8	2052.8	2049.1	2030.4	2026.7	2028.6	2034.2	2028.6
10°	2056.6	2051.0	2056.6	2054.7	2052.8	2049.1	2030.4	2023.0	2023.0	2028.6	2023.0
12.5°	2047.2	2043.5	2047.2	2043.5	2043.5	2039.8	2021.1	2013.6	2015.5	2017.3	2009.9
15°	2032.3	2026.7	2032.3	2028.6	2030.4	2024.8	2004.3	1996.8	1996.8	2000.5	1987.5
17.5°	2009.9	2002.4	2009.9	2008.0	2006.1	2002.4	1983.7	1976.3	1974.4	1976.3	1966.9
20°	1983.7	1978.1	1983.7	1981.9	1981.9	1974.4	1955.7	1946.4	1946.4	1946.4	1937.0
22.5°	1942.6	1937.0	1942.6	1946.4	1946.4	1944.5	1927.7	1914.6	1910.9	1910.9	1899.7
25°	1895.9	1890.3	1895.9	1895.9	1894.1	1895.9	1890.3	1882.9	1877.2	1871.6	1860.4
27.5°	1851.1	1847.4	1851.1	1847.4	1851.1	1845.5	1843.6	1841.8	1834.3	1828.7	1813.7
30°	1806.3	1802.5	1806.3	1802.5	1798.8	1795.1	1785.7	1782.0	1789.5	1785.7	1761.4
32.5°	1750.2	1746.5	1750.2	1750.2	1746.5	1746.5	1731.5	1725.9	1727.8	1739.0	1716.6
35°	1692.3	1686.7	1692.3	1690.4	1692.3	1686.7	1677.4	1675.5	1668.0	1681.1	1664.3
37.5°	1625.1	1619.5	1625.1	1625.1	1625.1	1628.8	1621.3	1615.7	1604.5	1621.3	1608.3
40°	1556.0	1548.5	1556.0	1554.1	1556.0	1559.7	1556.0	1552.2	1541.0	1554.1	1542.9
42.5°	1477.5	1475.6	1477.5	1479.4	1479.4	1486.8	1492.4	1485.0	1481.2	1471.9	1479.4
45°	1393.4	1389.7	1393.4	1397.2	1399.0	1402.8	1419.6	1419.6	1414.0	1399.0	1410.2
47.5°	1303.8	1294.4	1303.8	1315.0	1315.0	1320.6	1337.4	1350.5	1341.1	1322.5	1328.1
50°	1208.5	1210.4	1208.5	1216.0	1216.0	1236.5	1249.6	1262.7	1272.0	1249.6	1223.4
52.5°	1115.1	1113.3	1115.1	1120.7	1128.2	1137.5	1159.9	1173.0	1188.0	1174.9	1133.8
55°	1021.8	1025.5	1021.8	1023.7	1027.4	1033.0	1066.6	1079.7	1107.7	1090.9	1047.9
57.5°	928.4	922.8	928.4	932.1	934.0	939.6	967.6	991.9	1008.7	1010.6	958.3
60°	820.1	812.6	820.1	836.9	840.6	844.3	870.5	892.9	907.8	913.5	859.3
62.5°	724.8	711.7	724.8	736.0	743.5	752.8	771.5	805.1	818.2	820.1	743.5
65°	623.9	618.3	623.9	646.3	648.2	659.4	680.0	704.2	732.3	728.5	618.3
67.5°	532.4	532.4	532.4	547.3	558.5	564.1	590.3	601.5	637.0	640.7	515.6
70°	448.3	446.5	448.3	459.5	467.0	480.1	504.4	517.4	545.5	554.8	418.4
72.5°	368.0	366.1	368.0	377.3	384.8	396.0	416.6	431.5	455.8	467.0	325.0
75°	297.0	293.3	297.0	304.5	302.6	317.6	334.4	349.3	371.7	379.2	241.0
77.5°	227.9	227.9	227.9	235.4	235.4	250.3	257.8	276.5	289.5	300.7	177.5
80°	170.0	168.1	170.0	171.9	171.9	179.3	192.4	205.5	216.7	216.7	121.4
82.5°	119.6	115.8	119.6	119.6	119.6	123.3	130.8	134.5	142.0	147.6	76.6
85°	74.7	74.7	74.7	76.6	74.7	78.5	80.3	84.1	84.1	80.3	46.7
87.5°	48.6	46.7	48.6	46.7	46.7	44.8	44.8	44.8	43.0	41.1	26.2
90°	14.7	14.7	14.7	14.7	14.7	19.5	26.0	29.2	25.1	16.9	10.7
92.5°	58.6	47.0	58.6	70.2	73.1	103.7	144.4	164.8	144.7	104.5	74.3
95°	204.3	169.1	204.3	239.6	248.4	326.2	429.8	481.7	406.8	257.0	144.8
97.5°	489.4	422.4	489.4	556.5	573.3	622.4	688.0	720.8	595.9	346.2	159.0
100°	705.2	625.2	705.2	785.0	805.0	801.5	796.7	794.3	655.8	378.7	170.9
102.5°	917.4	848.9	917.4	985.8	1002.9	940.4	856.9	815.1	674.6	393.6	182.9
105°	1188.0	1151.2	1188.0	1224.8	1234.0	1093.6	906.4	812.8	676.8	404.7	200.6
107.5°	1365.2	1374.1	1365.2	1356.4	1354.1	1158.3	897.1	766.5	646.6	406.7	226.8
110°	1432.8	1471.1	1432.8	1394.5	1384.8	1165.9	874.0	728.1	619.9	403.7	241.4



TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	1438.8	1497.7	1438.8	1380.0	1365.2	1141.2	842.4	693.0	596.6	403.8	259.1
115°	1400.6	1482.3	1400.6	1319.0	1298.6	1082.8	795.0	651.1	569.9	407.5	285.7
117.5°	1319.8	1410.3	1319.8	1229.2	1206.6	1011.8	752.1	622.1	553.1	415.1	311.5
120°	1254.5	1342.5	1254.5	1166.6	1144.6	966.6	729.3	610.6	547.5	421.2	326.5
122.5°	1191.1	1277.9	1191.1	1104.4	1082.7	922.4	708.6	601.8	544.5	430.0	344.2
125°	1100.5	1180.5	1100.5	1020.7	1000.7	864.5	682.9	592.2	542.1	442.0	366.9
127.5°	1019.1	1086.5	1019.1	951.7	934.8	817.9	662.0	584.0	540.7	453.9	388.8
130°	971.1	1033.4	971.1	908.8	893.2	789.1	650.3	580.9	541.5	462.6	403.5
132.5°	927.6	983.3	927.6	871.7	857.8	764.7	640.4	578.3	542.1	469.7	415.4
135°	867.9	916.0	867.9	819.8	807.7	729.7	625.7	573.7	541.5	477.4	429.3
137.5°	820.1	859.4	820.1	780.6	770.8	704.9	616.9	572.9	544.9	488.9	447.0
140°	787.1	823.9	787.1	750.3	741.1	684.2	608.2	570.2	545.5	496.0	459.0
142.5°	759.9	791.6	759.9	728.3	720.4	670.3	603.6	570.2	547.4	501.9	467.7
145°	719.2	743.1	719.2	695.2	689.2	648.3	593.7	566.4	547.5	509.7	481.3
147.5°	687.8	707.7	687.8	667.9	663.0	630.7	587.9	566.4	551.2	520.9	498.2
150°	668.1	684.2	668.1	652.0	648.0	620.8	584.5	566.4	553.2	526.9	507.1
152.5°	651.3	663.4	651.3	639.1	636.1	612.8	581.9	566.4	554.5	530.7	512.9
155°	631.9	639.9	631.9	623.8	621.8	603.3	578.7	566.4	557.3	539.2	525.6
157.5°	616.5	622.1	616.5	610.8	609.4	595.1	575.9	566.4	560.1	547.6	538.3
160°	607.4	610.6	607.4	604.1	603.3	590.9	574.6	566.4	561.4	551.5	544.1
162.5°	601.4	604.5	601.4	598.3	597.6	587.2	573.3	566.4	562.8	555.6	550.2
165°	592.7	596.0	592.7	589.5	588.7	581.2	571.3	566.4	564.7	561.4	559.0
167.5°	586.6	588.0	586.6	585.2	584.9	580.0	573.5	570.2	568.8	566.1	564.0
170°	584.9	584.9	584.9	584.9	584.9	580.0	573.5	570.2	570.1	569.9	569.8
172.5°	580.3	579.1	580.3	581.5	581.8	578.0	572.8	570.2	570.2	570.2	570.2
175°	577.5	577.5	577.5	577.5	577.5	575.1	571.8	570.2	571.0	572.5	573.7
177.5°	575.1	573.7	575.1	576.4	576.7	574.8	572.3	571.0	571.5	572.7	573.7
180°	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	2002.4	1991.2	1991.2	1972.5	1965.0	1959.4	1950.1	1922.1	1914.6	1907.1	1918.3
5°	2019.2	1998.7	1983.7	1950.1	1922.1	1910.9	1875.4	1808.1	1763.3	1729.7	1711.0
7.5°	2023.0	1996.8	1968.8	1916.5	1849.2	1819.3	1711.0	1587.7	1554.1	1524.2	1505.5
10°	2019.2	1989.3	1950.1	1871.6	1712.9	1660.6	1552.2	1471.9	1451.3	1445.7	1451.3
12.5°	2006.1	1978.1	1923.9	1793.2	1570.9	1535.4	1471.9	1425.2	1421.5	1430.8	1481.2
15°	1983.7	1957.6	1894.1	1688.6	1492.4	1466.3	1421.5	1404.6	1425.2	1490.6	1641.9
17.5°	1961.3	1931.4	1853.0	1585.8	1432.7	1414.0	1382.2	1415.9	1531.7	1619.5	1669.9
20°	1931.4	1895.9	1806.3	1511.1	1389.7	1372.9	1357.9	1509.3	1597.0	1628.8	1656.8
22.5°	1895.9	1858.6	1742.8	1458.8	1344.9	1331.8	1341.1	1561.6	1597.0	1619.5	1643.7
25°	1849.2	1817.5	1668.0	1417.7	1309.4	1294.4	1329.9	1556.0	1576.5	1582.1	1630.7
27.5°	1806.3	1765.2	1589.6	1380.4	1266.4	1260.8	1339.3	1531.7	1546.6	1552.2	1604.5
30°	1754.0	1692.3	1501.8	1341.1	1221.6	1219.7	1341.1	1501.8	1498.0	1513.0	1565.3
32.5°	1699.8	1584.0	1402.8	1292.6	1178.6	1176.7	1328.1	1456.9	1453.2	1473.8	1513.0
35°	1649.4	1499.9	1268.3	1236.5	1124.4	1126.3	1296.3	1404.6	1406.5	1425.2	1449.5
37.5°	1597.0	1427.1	1120.7	1174.9	1072.2	1072.2	1253.3	1356.1	1352.3	1357.9	1391.6
40°	1535.4	1313.1	990.0	1094.6	1023.7	1018.1	1201.0	1303.8	1290.7	1288.8	1335.5
42.5°	1470.0	1188.0	892.9	988.2	967.6	960.2	1137.5	1240.3	1216.0	1221.6	1281.4
45°	1399.0	1154.3	818.2	835.0	909.7	904.1	1068.5	1167.4	1150.6	1165.5	1227.2
47.5°	1328.1	1087.2	793.9	693.0	848.1	846.2	991.9	1096.5	1087.2	1102.1	1167.4
50°	1230.9	1012.5	792.0	594.0	779.0	786.4	900.4	1027.4	1027.4	1040.5	1109.6
52.5°	1105.9	920.9	719.2	538.0	698.6	721.0	820.1	967.6	971.4	984.4	1046.1
55°	991.9	825.7	666.9	495.0	603.4	651.9	741.6	906.0	913.5	926.5	982.6
57.5°	887.3	687.4	655.7	444.6	515.6	562.3	672.5	846.2	849.9	861.1	915.3
60°	775.2	496.9	601.5	390.4	439.0	474.5	609.0	775.2	788.3	795.8	842.5
62.5°	648.2	360.5	545.5	353.1	401.6	409.1	556.7	708.0	724.8	730.4	758.4
65°	461.4	302.6	463.3	321.3	362.4	364.3	500.6	638.9	653.8	663.1	683.7
67.5°	312.0	246.6	353.1	291.4	332.5	334.4	446.5	558.5	579.1	586.6	599.6
70°	216.7	164.4	261.5	259.7	298.9	302.6	388.5	485.7	504.4	510.0	517.4
72.5°	158.8	132.6	216.7	233.5	263.4	267.1	328.8	403.5	422.2	427.8	431.5
75°	121.4	140.1	175.6	203.6	224.2	226.0	269.0	328.8	341.8	345.6	347.4
77.5°	97.1	130.8	128.9	164.4	183.1	179.3	211.1	254.0	265.3	265.3	265.3
80°	72.9	102.7	97.1	117.7	134.5	130.8	151.3	181.2	184.9	188.7	186.8
82.5°	54.2	65.4	65.4	74.7	89.7	85.9	100.9	117.7	117.7	117.7	121.4
85°	33.6	37.4	29.9	39.2	50.4	48.6	56.0	63.5	65.4	65.4	61.6
87.5°	20.5	16.8	9.3	14.9	22.4	22.4	26.2	28.0	26.2	26.2	26.2
90°	10.0	6.9	3.8	6.9	10.0	10.7	16.9	25.1	29.2	26.0	19.5
92.5°	67.8	41.6	15.4	41.6	67.8	74.3	104.5	144.7	164.8	144.4	103.7
95°	132.8	84.9	37.0	84.9	132.8	144.8	257.0	406.8	481.7	429.8	326.2
97.5°	148.4	106.1	63.9	106.1	148.4	159.0	346.2	595.9	720.8	688.0	622.4
100°	161.3	123.0	84.7	123.0	161.3	170.9	378.7	655.8	794.3	796.7	801.5
102.5°	173.9	138.2	102.5	138.2	173.9	182.9	393.6	674.6	815.1	856.9	940.4
105°	193.1	162.7	132.4	162.7	193.1	200.6	404.7	676.8	812.8	906.4	1093.6
107.5°	219.7	191.5	163.3	191.5	219.7	226.8	406.7	646.6	766.5	897.1	1158.3
110°	235.1	209.5	184.0	209.5	235.1	241.4	403.7	619.9	728.1	874.0	1165.9

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	253.0	228.7	204.5	228.7	253.0	259.1	403.8	596.6	693.0	842.4	1141.2
115°	280.1	257.7	235.3	257.7	280.1	285.7	407.5	569.9	651.1	795.0	1082.8
117.5°	306.4	286.0	265.6	286.0	306.4	311.5	415.1	553.1	622.1	752.1	1011.8
120°	321.8	302.5	283.4	302.5	321.8	326.5	421.2	547.5	610.6	729.3	966.6
122.5°	339.3	320.0	300.7	320.0	339.3	344.2	430.0	544.5	601.8	708.6	922.4
125°	362.5	344.8	327.3	344.8	362.5	366.9	442.0	542.1	592.2	682.9	864.5
127.5°	384.3	366.6	348.8	366.6	384.3	388.8	453.9	540.7	584.0	662.0	817.9
130°	398.7	379.5	360.3	379.5	398.7	403.5	462.6	541.5	580.9	650.3	789.1
132.5°	410.7	391.4	372.3	391.4	410.7	415.4	469.7	542.1	578.3	640.4	764.7
135°	424.9	407.5	390.0	407.5	424.9	429.3	477.4	541.5	573.7	625.7	729.7
137.5°	442.7	425.4	408.2	425.4	442.7	447.0	488.9	544.9	572.9	616.9	704.9
140°	455.0	439.1	423.1	439.1	455.0	459.0	496.0	545.5	570.2	608.2	684.2
142.5°	464.1	449.3	434.7	449.3	464.1	467.7	501.9	547.4	570.2	603.6	670.3
145°	478.1	465.2	452.4	465.2	478.1	481.3	509.7	547.5	566.4	593.7	648.3
147.5°	495.1	482.6	470.1	482.6	495.1	498.2	520.9	551.2	566.4	587.9	630.7
150°	504.3	493.0	481.7	493.0	504.3	507.1	526.9	553.2	566.4	584.5	620.8
152.5°	510.7	502.2	493.6	502.2	510.7	512.9	530.7	554.5	566.4	581.9	612.8
155°	524.0	517.6	511.3	517.6	524.0	525.6	539.2	557.3	566.4	578.7	603.3
157.5°	536.7	530.5	524.3	530.5	536.7	538.3	547.6	560.1	566.4	575.9	595.1
160°	542.8	538.1	533.2	538.1	542.8	544.1	551.5	561.4	566.4	574.6	590.9
162.5°	549.3	545.7	542.1	545.7	549.3	550.2	555.6	562.8	566.4	573.3	587.2
165°	558.2	555.0	551.7	555.0	558.2	559.0	561.4	564.7	566.4	571.3	581.2
167.5°	563.7	562.1	560.6	562.1	563.7	564.0	566.1	568.8	570.2	573.5	580.0
170°	569.5	567.9	566.4	567.9	569.5	569.8	569.9	570.1	570.2	573.5	580.0
172.5°	570.1	569.8	569.5	569.8	570.1	570.2	570.2	570.2	570.2	572.8	578.0
175°	573.7	573.7	573.7	573.7	573.7	573.7	572.5	571.0	570.2	571.8	575.1
177.5°	573.7	573.7	573.7	573.7	573.7	573.7	572.7	571.5	571.0	572.3	574.8
180°	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1905.3	1899.7	1907.1	1886.6	1907.1	1899.7	1905.3	1918.3	1907.1	1914.6	1922.1
5°	1671.8	1662.4	1632.5	1608.3	1632.5	1662.4	1671.8	1711.0	1729.7	1763.3	1808.1
7.5°	1494.3	1486.8	1479.4	1464.4	1479.4	1486.8	1494.3	1505.5	1524.2	1554.1	1587.7
10°	1455.1	1456.9	1468.2	1466.3	1468.2	1456.9	1455.1	1451.3	1445.7	1451.3	1471.9
12.5°	1556.0	1572.8	1634.4	1630.7	1634.4	1572.8	1556.0	1481.2	1430.8	1421.5	1425.2
15°	1671.8	1677.4	1690.4	1692.3	1690.4	1677.4	1671.8	1641.9	1490.6	1425.2	1404.6
17.5°	1683.0	1684.8	1694.2	1694.2	1694.2	1684.8	1683.0	1669.9	1619.5	1531.7	1415.9
20°	1673.6	1677.4	1696.1	1699.8	1696.1	1677.4	1673.6	1656.8	1628.8	1597.0	1509.3
22.5°	1669.9	1677.4	1692.3	1690.4	1692.3	1677.4	1669.9	1643.7	1619.5	1597.0	1561.6
25°	1651.2	1651.2	1653.1	1655.0	1653.1	1651.2	1651.2	1630.7	1582.1	1576.5	1556.0
27.5°	1612.0	1615.7	1626.9	1625.1	1626.9	1615.7	1612.0	1604.5	1552.2	1546.6	1531.7
30°	1576.5	1572.8	1563.4	1556.0	1563.4	1572.8	1576.5	1565.3	1513.0	1498.0	1501.8
32.5°	1516.7	1507.4	1498.0	1492.4	1498.0	1507.4	1516.7	1513.0	1473.8	1453.2	1456.9
35°	1445.7	1447.6	1445.7	1440.1	1445.7	1447.6	1445.7	1449.5	1425.2	1406.5	1404.6
37.5°	1395.3	1399.0	1397.2	1389.7	1397.2	1399.0	1395.3	1391.6	1357.9	1352.3	1356.1
40°	1343.0	1344.9	1343.0	1337.4	1343.0	1344.9	1343.0	1335.5	1288.8	1290.7	1303.8
42.5°	1292.6	1290.7	1285.1	1281.4	1285.1	1290.7	1292.6	1281.4	1221.6	1216.0	1240.3
45°	1234.7	1236.5	1225.3	1219.7	1225.3	1236.5	1234.7	1227.2	1165.5	1150.6	1167.4
47.5°	1176.7	1176.7	1167.4	1161.8	1167.4	1176.7	1176.7	1167.4	1102.1	1087.2	1096.5
50°	1115.1	1113.3	1100.3	1098.4	1100.3	1113.3	1115.1	1109.6	1040.5	1027.4	1027.4
52.5°	1044.2	1044.2	1046.1	1049.8	1046.1	1044.2	1044.2	1046.1	984.4	971.4	967.6
55°	982.6	984.4	997.5	1001.2	997.5	984.4	982.6	982.6	926.5	913.5	906.0
57.5°	919.1	919.1	928.4	928.4	928.4	919.1	919.1	915.3	861.1	849.9	846.2
60°	846.2	849.9	857.4	855.5	857.4	849.9	846.2	842.5	795.8	788.3	775.2
62.5°	769.6	773.4	775.2	771.5	775.2	773.4	769.6	758.4	730.4	724.8	708.0
65°	689.3	693.0	694.9	691.2	694.9	693.0	689.3	683.7	663.1	653.8	638.9
67.5°	607.1	605.2	603.4	610.8	603.4	605.2	607.1	599.6	586.6	579.1	558.5
70°	523.0	523.0	521.2	524.9	521.2	523.0	523.0	517.4	510.0	504.4	485.7
72.5°	433.4	431.5	439.0	433.4	439.0	431.5	433.4	431.5	427.8	422.2	403.5
75°	345.6	349.3	345.6	351.2	345.6	349.3	345.6	347.4	345.6	341.8	328.8
77.5°	263.4	267.1	263.4	263.4	263.4	267.1	263.4	265.3	265.3	265.3	254.0
80°	186.8	184.9	184.9	183.1	184.9	184.9	186.8	186.8	188.7	184.9	181.2
82.5°	119.6	117.7	117.7	121.4	117.7	117.7	119.6	121.4	117.7	117.7	117.7
85°	65.4	67.2	63.5	63.5	63.5	67.2	65.4	61.6	65.4	65.4	63.5
87.5°	24.3	22.4	22.4	22.4	22.4	22.4	24.3	26.2	26.2	26.2	28.0
90°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	19.5	26.0	29.2	25.1
92.5°	73.1	70.2	58.6	47.0	58.6	70.2	73.1	103.7	144.4	164.8	144.7
95°	248.4	239.6	204.3	169.1	204.3	239.6	248.4	326.2	429.8	481.7	406.8
97.5°	573.3	556.5	489.4	422.4	489.4	556.5	573.3	622.4	688.0	720.8	595.9
100°	805.0	785.0	705.2	625.2	705.2	785.0	805.0	801.5	796.7	794.3	655.8
102.5°	1002.9	985.8	917.4	848.9	917.4	985.8	1002.9	940.4	856.9	815.1	674.6
105°	1234.0	1224.8	1188.0	1151.2	1188.0	1224.8	1234.0	1093.6	906.4	812.8	676.8
107.5°	1354.1	1356.4	1365.2	1374.1	1365.2	1356.4	1354.1	1158.3	897.1	766.5	646.6
110°	1384.8	1394.5	1432.8	1471.1	1432.8	1394.5	1384.8	1165.9	874.0	728.1	619.9

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	1365.2	1380.0	1438.8	1497.7	1438.8	1380.0	1365.2	1141.2	842.4	693.0	596.6
115°	1298.6	1319.0	1400.6	1482.3	1400.6	1319.0	1298.6	1082.8	795.0	651.1	569.9
117.5°	1206.6	1229.2	1319.8	1410.3	1319.8	1229.2	1206.6	1011.8	752.1	622.1	553.1
120°	1144.6	1166.6	1254.5	1342.5	1254.5	1166.6	1144.6	966.6	729.3	610.6	547.5
122.5°	1082.7	1104.4	1191.1	1277.9	1191.1	1104.4	1082.7	922.4	708.6	601.8	544.5
125°	1000.7	1020.7	1100.5	1180.5	1100.5	1020.7	1000.7	864.5	682.9	592.2	542.1
127.5°	934.8	951.7	1019.1	1086.5	1019.1	951.7	934.8	817.9	662.0	584.0	540.7
130°	893.2	908.8	971.1	1033.4	971.1	908.8	893.2	789.1	650.3	580.9	541.5
132.5°	857.8	871.7	927.6	983.3	927.6	871.7	857.8	764.7	640.4	578.3	542.1
135°	807.7	819.8	867.9	916.0	867.9	819.8	807.7	729.7	625.7	573.7	541.5
137.5°	770.8	780.6	820.1	859.4	820.1	780.6	770.8	704.9	616.9	572.9	544.9
140°	741.1	750.3	787.1	823.9	787.1	750.3	741.1	684.2	608.2	570.2	545.5
142.5°	720.4	728.3	759.9	791.6	759.9	728.3	720.4	670.3	603.6	570.2	547.4
145°	689.2	695.2	719.2	743.1	719.2	695.2	689.2	648.3	593.7	566.4	547.5
147.5°	663.0	667.9	687.8	707.7	687.8	667.9	663.0	630.7	587.9	566.4	551.2
150°	648.0	652.0	668.1	684.2	668.1	652.0	648.0	620.8	584.5	566.4	553.2
152.5°	636.1	639.1	651.3	663.4	651.3	639.1	636.1	612.8	581.9	566.4	554.5
155°	621.8	623.8	631.9	639.9	631.9	623.8	621.8	603.3	578.7	566.4	557.3
157.5°	609.4	610.8	616.5	622.1	616.5	610.8	609.4	595.1	575.9	566.4	560.1
160°	603.3	604.1	607.4	610.6	607.4	604.1	603.3	590.9	574.6	566.4	561.4
162.5°	597.6	598.3	601.4	604.5	601.4	598.3	597.6	587.2	573.3	566.4	562.8
165°	588.7	589.5	592.7	596.0	592.7	589.5	588.7	581.2	571.3	566.4	564.7
167.5°	584.9	585.2	586.6	588.0	586.6	585.2	584.9	580.0	573.5	570.2	568.8
170°	584.9	584.9	584.9	584.9	584.9	584.9	584.9	580.0	573.5	570.2	570.1
172.5°	581.8	581.5	580.3	579.1	580.3	581.5	581.8	578.0	572.8	570.2	570.2
175°	577.5	577.5	577.5	577.5	577.5	577.5	577.5	575.1	571.8	570.2	571.0
177.5°	576.7	576.4	575.1	573.7	575.1	576.4	576.7	574.8	572.3	571.0	571.5
180°	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	1974.4	1974.4	1974.4	1974.4	1974.4
2.5°	1950.1	1959.4	1965.0	1972.5	1991.2
5°	1875.4	1910.9	1922.1	1950.1	1983.7
7.5°	1711.0	1819.3	1849.2	1916.5	1968.8
10°	1552.2	1660.6	1712.9	1871.6	1950.1
12.5°	1471.9	1535.4	1570.9	1793.2	1923.9
15°	1421.5	1466.3	1492.4	1688.6	1894.1
17.5°	1382.2	1414.0	1432.7	1585.8	1853.0
20°	1357.9	1372.9	1389.7	1511.1	1806.3
22.5°	1341.1	1331.8	1344.9	1458.8	1742.8
25°	1329.9	1294.4	1309.4	1417.7	1668.0
27.5°	1339.3	1260.8	1266.4	1380.4	1589.6
30°	1341.1	1219.7	1221.6	1341.1	1501.8
32.5°	1328.1	1176.7	1178.6	1292.6	1402.8
35°	1296.3	1126.3	1124.4	1236.5	1268.3
37.5°	1253.3	1072.2	1072.2	1174.9	1120.7
40°	1201.0	1018.1	1023.7	1094.6	990.0
42.5°	1137.5	960.2	967.6	988.2	892.9
45°	1068.5	904.1	909.7	835.0	818.2
47.5°	991.9	846.2	848.1	693.0	793.9
50°	900.4	786.4	779.0	594.0	792.0
52.5°	820.1	721.0	698.6	538.0	719.2
55°	741.6	651.9	603.4	495.0	666.9
57.5°	672.5	562.3	515.6	444.6	655.7
60°	609.0	474.5	439.0	390.4	601.5
62.5°	556.7	409.1	401.6	353.1	545.5
65°	500.6	364.3	362.4	321.3	463.3
67.5°	446.5	334.4	332.5	291.4	353.1
70°	388.5	302.6	298.9	259.7	261.5
72.5°	328.8	267.1	263.4	233.5	216.7
75°	269.0	226.0	224.2	203.6	175.6
77.5°	211.1	179.3	183.1	164.4	128.9
80°	151.3	130.8	134.5	117.7	97.1
82.5°	100.9	85.9	89.7	74.7	65.4
85°	56.0	48.6	50.4	39.2	29.9
87.5°	26.2	22.4	22.4	14.9	9.3
90°	16.9	10.7	10.0	6.9	3.8
92.5°	104.5	74.3	67.8	41.6	15.4
95°	257.0	144.8	132.8	84.9	37.0
97.5°	346.2	159.0	148.4	106.1	63.9
100°	378.7	170.9	161.3	123.0	84.7
102.5°	393.6	182.9	173.9	138.2	102.5
105°	404.7	200.6	193.1	162.7	132.4
107.5°	406.7	226.8	219.7	191.5	163.3
110°	403.7	241.4	235.1	209.5	184.0



TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	403.8	259.1	253.0	228.7	204.5
115°	407.5	285.7	280.1	257.7	235.3
117.5°	415.1	311.5	306.4	286.0	265.6
120°	421.2	326.5	321.8	302.5	283.4
122.5°	430.0	344.2	339.3	320.0	300.7
125°	442.0	366.9	362.5	344.8	327.3
127.5°	453.9	388.8	384.3	366.6	348.8
130°	462.6	403.5	398.7	379.5	360.3
132.5°	469.7	415.4	410.7	391.4	372.3
135°	477.4	429.3	424.9	407.5	390.0
137.5°	488.9	447.0	442.7	425.4	408.2
140°	496.0	459.0	455.0	439.1	423.1
142.5°	501.9	467.7	464.1	449.3	434.7
145°	509.7	481.3	478.1	465.2	452.4
147.5°	520.9	498.2	495.1	482.6	470.1
150°	526.9	507.1	504.3	493.0	481.7
152.5°	530.7	512.9	510.7	502.2	493.6
155°	539.2	525.6	524.0	517.6	511.3
157.5°	547.6	538.3	536.7	530.5	524.3
160°	551.5	544.1	542.8	538.1	533.2
162.5°	555.6	550.2	549.3	545.7	542.1
165°	561.4	559.0	558.2	555.0	551.7
167.5°	566.1	564.0	563.7	562.1	560.6
170°	569.9	569.8	569.5	567.9	566.4
172.5°	570.2	570.2	570.1	569.8	569.5
175°	572.5	573.7	573.7	573.7	573.7
177.5°	572.7	573.7	573.7	573.7	573.7
180°	573.7	573.7	573.7	573.7	573.7

TEST NUMBER: P934396

CATALOG NUMBER: SQ4-FA-050U-075D-B2750-1D-UNV-W2A-W-8-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.20	14.14	14.09	15.05	16.20	16.04	16.98	16.93	17.89	19.04
	3H	13.69	14.53	14.59	15.44	16.62	17.40	18.24	18.29	19.15	20.33
	4H	13.88	14.68	14.80	15.60	16.79	17.85	18.64	18.76	19.56	20.75
	6H	14.01	14.74	14.93	15.66	16.87	18.14	18.87	19.06	19.80	21.00
	8H	14.01	14.71	14.94	15.65	16.85	18.21	18.91	19.15	19.86	21.06
	12H	13.98	14.65	14.92	15.58	16.81	18.26	18.92	19.19	19.86	21.08
4H	2H	14.25	15.04	15.17	15.96	17.15	16.46	17.25	17.38	18.18	19.36
	3H	15.28	15.94	16.21	16.90	18.10	17.98	18.64	18.91	19.59	20.79
	4H	15.56	16.17	16.50	17.11	18.34	18.51	19.11	19.45	20.06	21.29
	6H	15.69	16.21	16.65	17.18	18.41	18.88	19.40	19.83	20.37	21.60
	8H	15.70	16.19	16.65	17.15	18.39	18.99	19.48	19.95	20.44	21.68
	12H	15.67	16.11	16.64	17.09	18.34	19.05	19.49	20.03	20.47	21.72
8H	4H	16.02	16.51	16.98	17.47	18.72	18.64	19.13	19.59	20.09	21.33
	6H	16.29	16.69	17.27	17.70	18.94	19.08	19.48	20.06	20.49	21.73
	8H	16.33	16.69	17.32	17.68	18.94	19.23	19.59	20.23	20.59	21.84
	12H	16.32	16.63	17.31	17.62	18.93	19.34	19.65	20.33	20.64	21.95
12H	4H	16.03	16.47	17.01	17.45	18.70	18.61	19.05	19.58	20.03	21.28
	6H	16.35	16.71	17.34	17.70	18.96	19.08	19.43	20.07	20.43	21.69
	8H	16.42	16.73	17.41	17.72	19.03	19.24	19.56	20.24	20.55	21.85

END OF REPORT