

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934581

Luminaire Tested: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P934581
REPORT IS A COMBINATION OF REPORTS P933701 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I
Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18576.3 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 168
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

Luminous Intensity Polar Plot



TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	65	63
2	93	86	79	74	88	81	76	71	73	68	65	65	62	59	58	56	53
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	52	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	49	37	30	25	47	35	28	24	32	26	22	30	25	21	27	23	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15502	15502	15502	15502
5°	15623	15649	15623	12305
10°	15525	15414	15525	11020
15°	15362	15081	15362	12592
20°	15047	14685	15047	12619
25°	14395	14108	14395	12351
30°	13550	13629	13550	11765
35°	12086	13023	12086	11119
40°	10076	12309	10076	10632
45°	9009	11474	9009	10071
50°	9579	10479	9579	9508
55°	9021	9406	9021	9183
60°	9311	7988	9311	8411
65°	8455	6604	8455	7381
70°	5869	5262	5869	6188
75°	5166	3890	5166	4658
80°	4194	2572	4194	2801
85°	2456	1362	2456	1158

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 20°

Vertical Angle: 45°

Luminance: 13799 cd/sqm

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.4	2.4
10°-20°	1284.5	6.9
20°-30°	1985.6	10.7
30°-40°	2370.4	12.8
40°-50°	2384.3	12.8
50°-60°	2074.6	11.2
60°-70°	1470.9	7.9
70°-80°	778.2	4.2
80°-90°	197.1	1.1
90°-100°	419.4	2.3
100°-110°	1102.8	5.9
110°-120°	1143.4	6.2
120°-130°	917.2	4.9
130°-140°	719.7	3.9
140°-150°	552.4	3.0
150°-160°	397.8	2.1
160°-170°	243.4	1.3
170°-180°	82.2	0.4
0°-30°	3722.5	20.0
0°-40°	6092.9	32.8
0°-60°	10551.8	56.8
0°-90°	12998.0	70.0
90°-120°	2665.6	14.3
90°-150°	4854.8	26.1
90°-180°	5578.0	30.0
0°-180°	18576.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	5012	5012	5012	5012	5012	
5°	5036	5192	5036	4082	5036	478
15°	4808	5145	4808	4296	4808	1353
25°	4234	4798	4234	4201	4234	1944
35°	3220	4282	3220	3656	3220	1992
45°	2077	3528	2077	3096	2077	1664
55°	1693	2603	1693	2542	1693	1555
65°	1176	1570	1176	1754	1176	1124
75°	446	744	446	891	446	469
85°	76	190	76	161	76	102
90°	6	22	6	22	6	8
95°	56	254	56	254	56	62
105°	199	1727	199	1727	199	211
115°	353	2224	353	2224	353	348
125°	491	1771	491	1771	491	436
135°	585	1374	585	1374	585	453
145°	679	1115	679	1115	679	425
155°	767	960	767	960	767	352
165°	828	894	828	894	828	234
175°	860	866	860	866	860	82
180°	860	860	860	860	860	

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8
2.5°	5054.5	5054.5	5082.9	5092.4	5092.4	5078.2	5064.0	5078.2	5120.8	5135.1	5130.4
5°	5035.5	5073.5	5125.6	5135.1	5144.6	5139.8	5130.4	5139.8	5187.2	5196.8	5201.4
7.5°	4997.6	5068.7	5135.1	5149.3	5163.5	5149.3	5144.6	5154.1	5201.4	5211.0	5211.0
10°	4950.2	5049.8	5125.6	5135.1	5149.3	5135.1	5135.1	5154.1	5201.4	5211.0	5215.7
12.5°	4883.8	5021.3	5092.4	5101.9	5120.8	5116.1	5111.4	5130.4	5177.7	5187.2	5187.2
15°	4808.0	4969.2	5035.5	5045.0	5078.2	5068.7	5068.7	5087.7	5139.8	5154.1	5149.3
17.5°	4703.6	4902.8	4978.6	4992.9	5016.5	5011.8	5016.5	5035.5	5082.9	5092.4	5097.1
20°	4585.1	4812.6	4902.8	4916.9	4940.7	4940.7	4940.7	4964.4	5011.8	5030.8	5030.8
22.5°	4423.9	4717.8	4812.6	4822.1	4850.6	4850.6	4860.1	4893.2	4935.9	4940.7	4940.7
25°	4234.2	4613.5	4694.1	4722.6	4751.1	4765.3	4779.5	4798.4	4812.6	4808.0	4812.6
27.5°	4035.1	4480.8	4585.1	4604.1	4642.0	4656.2	4675.1	4679.9	4684.7	4698.9	4689.4
30°	3812.2	4295.8	4452.3	4471.2	4532.9	4542.4	4523.5	4532.9	4556.6	4566.1	4575.6
32.5°	3560.9	4020.9	4314.8	4357.5	4414.4	4386.0	4381.2	4395.4	4433.3	4433.3	4442.9
35°	3219.5	3807.5	4186.7	4224.7	4267.4	4234.2	4253.2	4257.9	4281.6	4295.8	4291.1
37.5°	2845.0	3622.5	4054.0	4082.5	4115.7	4073.0	4101.5	4115.7	4134.6	4125.1	4125.1
40°	2513.0	3333.3	3897.6	3916.5	3944.9	3911.8	3940.3	3949.7	3959.2	3949.7	3944.9
42.5°	2266.4	3015.6	3731.6	3755.3	3736.4	3760.0	3769.5	3788.5	3774.3	3755.3	3755.3
45°	2076.7	2930.2	3551.4	3579.8	3551.4	3589.4	3603.6	3603.6	3560.9	3551.4	3546.7
47.5°	2015.2	2759.6	3371.3	3371.3	3357.0	3404.4	3428.2	3394.9	3352.3	3338.0	3338.0
50°	2010.4	2569.9	3124.7	3105.7	3172.1	3229.0	3205.3	3172.1	3138.9	3086.8	3086.8
52.5°	1825.5	2337.6	2807.0	2878.1	2982.4	3015.6	2977.7	2944.5	2887.6	2863.9	2845.0
55°	1692.7	2095.8	2517.8	2660.0	2769.0	2811.7	2740.6	2707.4	2622.1	2607.8	2598.4
57.5°	1664.3	1744.9	2252.2	2432.4	2565.1	2560.5	2517.8	2456.1	2385.0	2370.8	2366.0
60°	1526.8	1261.3	1967.8	2181.1	2318.7	2304.4	2266.4	2209.6	2143.2	2133.7	2124.2
62.5°	1384.6	915.1	1645.3	1887.1	2081.5	2076.7	2043.6	1958.2	1910.9	1887.1	1868.2
65°	1175.9	768.1	1171.1	1569.5	1849.2	1858.7	1787.6	1725.9	1673.7	1645.3	1640.6
67.5°	896.2	625.9	791.8	1308.6	1626.4	1616.8	1526.8	1498.3	1431.9	1417.7	1389.2
70°	663.8	417.2	550.0	1062.1	1408.2	1384.6	1313.4	1280.2	1218.6	1185.3	1166.4
72.5°	550.0	336.6	403.0	825.0	1185.3	1156.9	1095.3	1057.4	1005.2	976.8	957.8
75°	445.7	355.6	308.2	611.7	962.5	943.5	886.6	848.7	806.0	768.1	772.9
77.5°	327.2	331.9	246.6	450.5	763.4	735.0	701.7	654.4	635.4	597.5	597.5
80°	246.6	260.8	184.9	308.2	550.0	550.0	521.5	488.4	455.2	436.2	436.2
82.5°	166.0	166.0	137.5	194.4	374.6	360.3	341.4	331.9	313.0	303.5	303.5
85°	75.8	94.8	85.4	118.5	203.9	213.3	213.3	203.9	199.1	189.7	194.4
87.5°	23.7	42.7	52.1	66.4	104.3	109.1	113.8	113.8	113.8	118.5	118.5
90°	5.8	10.4	15.0	16.2	25.4	37.7	43.9	39.0	29.2	21.9	21.9
92.5°	23.1	62.3	101.6	111.4	156.6	217.0	247.1	216.6	155.5	109.7	105.4
95°	55.5	127.3	199.2	217.2	385.6	610.2	722.4	644.6	489.1	372.5	359.2
97.5°	95.8	159.2	222.7	238.5	519.4	893.8	1081.1	1032.0	933.6	859.9	834.8
100°	127.0	184.6	242.0	256.4	568.1	983.6	1191.4	1195.0	1202.2	1207.6	1177.6
102.5°	153.6	207.3	260.9	274.3	590.4	1011.9	1222.6	1285.2	1410.4	1504.4	1478.7
105°	198.7	244.1	289.4	300.8	606.9	1015.1	1219.2	1359.5	1640.3	1850.9	1837.1
107.5°	244.9	287.2	329.6	340.2	610.1	970.0	1149.8	1345.7	1737.4	2031.2	2034.5
110°	276.1	314.3	352.6	362.1	605.4	929.9	1092.1	1311.1	1748.9	2077.3	2091.7

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	306.6	343.1	379.5	388.6	605.6	894.9	1039.5	1263.6	1711.7	2047.9	2069.9
115°	352.9	386.5	420.1	428.5	611.2	854.8	976.6	1192.4	1624.1	1948.0	1978.6
117.5°	398.4	429.0	459.5	467.2	622.5	829.7	933.3	1128.1	1517.7	1809.9	1843.8
120°	425.1	453.8	482.5	489.7	631.8	821.3	916.0	1094.0	1449.9	1717.0	1749.9
122.5°	451.0	480.1	509.0	516.3	645.1	816.8	902.6	1062.9	1383.5	1623.9	1656.4
125°	490.9	517.3	543.8	550.4	663.0	813.1	888.2	1024.4	1296.7	1500.9	1530.9
127.5°	523.2	549.9	576.7	583.3	680.9	811.0	876.1	993.0	1226.8	1402.2	1427.5
130°	540.6	569.4	598.0	605.2	694.0	812.3	871.5	975.6	1183.8	1339.8	1363.2
132.5°	558.4	587.2	616.0	623.2	704.6	813.1	867.4	960.6	1147.0	1286.7	1307.6
135°	585.1	611.2	637.4	643.9	716.1	812.4	860.5	938.6	1094.6	1211.7	1229.7
137.5°	612.1	638.1	664.1	670.5	733.5	817.4	859.4	925.3	1057.3	1156.2	1171.0
140°	634.7	658.6	682.4	688.4	744.0	818.2	855.3	912.2	1026.3	1111.7	1125.6
142.5°	652.0	674.1	696.2	701.7	752.9	821.2	855.3	905.3	1005.5	1080.5	1092.4
145°	678.6	697.8	717.0	721.9	764.5	821.2	849.6	890.5	972.4	1033.8	1042.7
147.5°	705.2	723.8	742.6	747.3	781.4	826.9	849.6	881.8	946.2	994.5	1002.0
150°	722.4	739.4	756.4	760.6	790.3	829.8	849.6	876.7	931.1	971.9	978.0
152.5°	740.4	753.2	766.1	769.2	796.0	831.7	849.6	872.8	919.2	954.1	958.7
155°	766.9	776.4	786.0	788.3	808.8	835.9	849.6	868.1	905.0	932.7	935.7
157.5°	786.6	795.9	805.0	807.3	821.5	840.2	849.6	864.0	892.6	914.2	916.3
160°	799.9	807.1	814.3	816.0	827.2	842.1	849.6	861.9	886.5	905.0	906.2
162.5°	813.1	818.6	824.0	825.3	833.4	844.1	849.6	859.9	880.7	896.3	897.4
165°	827.6	832.5	837.3	838.5	842.2	847.1	849.6	857.0	871.9	883.0	884.2
167.5°	840.9	843.1	845.5	846.0	849.1	853.2	855.3	860.1	869.9	877.2	877.8
170°	849.6	851.8	854.1	854.7	854.9	855.2	855.3	860.1	869.9	877.2	877.2
172.5°	854.1	854.6	855.2	855.3	855.3	855.3	855.3	859.1	866.8	872.6	872.2
175°	860.5	860.5	860.5	860.5	858.7	856.4	855.3	857.7	862.6	866.3	866.3
177.5°	860.5	860.5	860.5	860.5	859.2	857.4	856.5	858.4	862.3	865.2	864.6
180°	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8
2.5°	5139.8	5125.6	5139.8	5130.4	5135.1	5120.8	5078.2	5064.0	5078.2	5092.4	5092.4
5°	5201.4	5192.0	5201.4	5201.4	5196.8	5187.2	5139.8	5130.4	5139.8	5144.6	5135.1
7.5°	5220.4	5206.2	5220.4	5211.0	5211.0	5201.4	5154.1	5144.6	5149.3	5163.5	5149.3
10°	5220.4	5206.2	5220.4	5215.7	5211.0	5201.4	5154.1	5135.1	5135.1	5149.3	5135.1
12.5°	5196.8	5187.2	5196.8	5187.2	5187.2	5177.7	5130.4	5111.4	5116.1	5120.8	5101.9
15°	5158.8	5144.6	5158.8	5149.3	5154.1	5139.8	5087.7	5068.7	5068.7	5078.2	5045.0
17.5°	5101.9	5082.9	5101.9	5097.1	5092.4	5082.9	5035.5	5016.5	5011.8	5016.5	4992.9
20°	5035.5	5021.3	5035.5	5030.8	5030.8	5011.8	4964.4	4940.7	4940.7	4940.7	4916.9
22.5°	4931.2	4916.9	4931.2	4940.7	4940.7	4935.9	4893.2	4860.1	4850.6	4850.6	4822.1
25°	4812.6	4798.4	4812.6	4812.6	4808.0	4812.6	4798.4	4779.5	4765.3	4751.1	4722.6
27.5°	4698.9	4689.4	4698.9	4689.4	4698.9	4684.7	4679.9	4675.1	4656.2	4642.0	4604.1
30°	4585.1	4575.6	4585.1	4575.6	4566.1	4556.6	4532.9	4523.5	4542.4	4532.9	4471.2
32.5°	4442.9	4433.3	4442.9	4442.9	4433.3	4433.3	4395.4	4381.2	4386.0	4414.4	4357.5
35°	4295.8	4281.6	4295.8	4291.1	4295.8	4281.6	4257.9	4253.2	4234.2	4267.4	4224.7
37.5°	4125.1	4110.9	4125.1	4125.1	4125.1	4134.6	4115.7	4101.5	4073.0	4115.7	4082.5
40°	3949.7	3930.7	3949.7	3944.9	3949.7	3959.2	3949.7	3940.3	3911.8	3944.9	3916.5
42.5°	3750.6	3745.8	3750.6	3755.3	3755.3	3774.3	3788.5	3769.5	3760.0	3736.4	3755.3
45°	3537.2	3527.7	3537.2	3546.7	3551.4	3560.9	3603.6	3603.6	3589.4	3551.4	3579.8
47.5°	3309.6	3285.9	3309.6	3338.0	3338.0	3352.3	3394.9	3428.2	3404.4	3357.0	3371.3
50°	3067.8	3072.5	3067.8	3086.8	3086.8	3138.9	3172.1	3205.3	3229.0	3172.1	3105.7
52.5°	2830.7	2826.0	2830.7	2845.0	2863.9	2887.6	2944.5	2977.7	3015.6	2982.4	2878.1
55°	2593.6	2603.2	2593.6	2598.4	2607.8	2622.1	2707.4	2740.6	2811.7	2769.0	2660.0
57.5°	2356.6	2342.3	2356.6	2366.0	2370.8	2385.0	2456.1	2517.8	2560.5	2565.1	2432.4
60°	2081.5	2062.6	2081.5	2124.2	2133.7	2143.2	2209.6	2266.4	2304.4	2318.7	2181.1
62.5°	1839.7	1806.5	1839.7	1868.2	1887.1	1910.9	1958.2	2043.6	2076.7	2081.5	1887.1
65°	1583.7	1569.5	1583.7	1640.6	1645.3	1673.7	1725.9	1787.6	1858.7	1849.2	1569.5
67.5°	1351.3	1351.3	1351.3	1389.2	1417.7	1431.9	1498.3	1526.8	1616.8	1626.4	1308.6
70°	1138.0	1133.2	1138.0	1166.4	1185.3	1218.6	1280.2	1313.4	1384.6	1408.2	1062.1
72.5°	934.1	929.3	934.1	957.8	976.8	1005.2	1057.4	1095.3	1156.9	1185.3	825.0
75°	753.9	744.4	753.9	772.9	768.1	806.0	848.7	886.6	943.5	962.5	611.7
77.5°	578.4	578.4	578.4	597.5	597.5	635.4	654.4	701.7	735.0	763.4	450.5
80°	431.5	426.7	431.5	436.2	436.2	455.2	488.4	521.5	550.0	550.0	308.2
82.5°	303.5	293.9	303.5	303.5	303.5	313.0	331.9	341.4	360.3	374.6	194.4
85°	189.7	189.7	189.7	194.4	189.7	199.1	203.9	213.3	213.3	203.9	118.5
87.5°	123.3	118.5	123.3	118.5	118.5	113.8	113.8	113.8	109.1	104.3	66.4
90°	21.9	21.9	21.9	21.9	21.9	29.2	39.0	43.9	37.7	25.4	16.2
92.5°	87.9	70.4	87.9	105.4	109.7	155.5	216.6	247.1	217.0	156.6	111.4
95°	306.4	253.5	306.4	359.2	372.5	489.1	644.6	722.4	610.2	385.6	217.2
97.5°	734.1	633.5	734.1	834.8	859.9	933.6	1032.0	1081.1	893.8	519.4	238.5
100°	1057.8	937.9	1057.8	1177.6	1207.6	1202.2	1195.0	1191.4	983.6	568.1	256.4
102.5°	1376.1	1273.4	1376.1	1478.7	1504.4	1410.4	1285.2	1222.6	1011.9	590.4	274.3
105°	1782.0	1726.8	1782.0	1837.1	1850.9	1640.3	1359.5	1219.2	1015.1	606.9	300.8
107.5°	2047.8	2061.2	2047.8	2034.5	2031.2	1737.4	1345.7	1149.8	970.0	610.1	340.2
110°	2149.1	2206.7	2149.1	2091.7	2077.3	1748.9	1311.1	1092.1	929.9	605.4	362.1

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	2158.3	2246.6	2158.3	2069.9	2047.9	1711.7	1263.6	1039.5	894.9	605.6	388.6
115°	2101.0	2223.5	2101.0	1978.6	1948.0	1624.1	1192.4	976.6	854.8	611.2	428.5
117.5°	1979.6	2115.4	1979.6	1843.8	1809.9	1517.7	1128.1	933.3	829.7	622.5	467.2
120°	1881.9	2013.8	1881.9	1749.9	1717.0	1449.9	1094.0	916.0	821.3	631.8	489.7
122.5°	1786.6	1916.8	1786.6	1656.4	1623.9	1383.5	1062.9	902.6	816.8	645.1	516.3
125°	1650.8	1770.7	1650.8	1530.9	1500.9	1296.7	1024.4	888.2	813.1	663.0	550.4
127.5°	1528.6	1629.7	1528.6	1427.5	1402.2	1226.8	993.0	876.1	811.0	680.9	583.3
130°	1456.7	1550.1	1456.7	1363.2	1339.8	1183.8	975.6	871.5	812.3	694.0	605.2
132.5°	1391.3	1475.0	1391.3	1307.6	1286.7	1147.0	960.6	867.4	813.1	704.6	623.2
135°	1301.8	1373.9	1301.8	1229.7	1211.7	1094.6	938.6	860.5	812.4	716.1	643.9
137.5°	1230.0	1289.0	1230.0	1171.0	1156.2	1057.3	925.3	859.4	817.4	733.5	670.5
140°	1180.7	1235.9	1180.7	1125.6	1111.7	1026.3	912.2	855.3	818.2	744.0	688.4
142.5°	1139.9	1187.4	1139.9	1092.4	1080.5	1005.5	905.3	855.3	821.2	752.9	701.7
145°	1078.7	1114.6	1078.7	1042.7	1033.8	972.4	890.5	849.6	821.2	764.5	721.9
147.5°	1031.7	1061.5	1031.7	1002.0	994.5	946.2	881.8	849.6	826.9	781.4	747.3
150°	1002.1	1026.3	1002.1	978.0	971.9	931.1	876.7	849.6	829.8	790.3	760.6
152.5°	976.9	995.1	976.9	958.7	954.1	919.2	872.8	849.6	831.7	796.0	769.2
155°	947.8	959.9	947.8	935.7	932.7	905.0	868.1	849.6	835.9	808.8	788.3
157.5°	924.8	933.3	924.8	916.3	914.2	892.6	864.0	849.6	840.2	821.5	807.3
160°	911.1	916.0	911.1	906.2	905.0	886.5	861.9	849.6	842.1	827.2	816.0
162.5°	902.1	906.7	902.1	897.4	896.3	880.7	859.9	849.6	844.1	833.4	825.3
165°	889.2	894.0	889.2	884.2	883.0	871.9	857.0	849.6	847.1	842.2	838.5
167.5°	879.8	881.9	879.8	877.8	877.2	869.9	860.1	855.3	853.2	849.1	846.0
170°	877.2	877.2	877.2	877.2	877.2	869.9	860.1	855.3	855.2	854.9	854.7
172.5°	870.4	868.6	870.4	872.2	872.6	866.8	859.1	855.3	855.3	855.3	855.3
175°	866.3	866.3	866.3	866.3	866.3	862.6	857.7	855.3	856.4	858.7	860.5
177.5°	862.5	860.5	862.5	864.6	865.2	862.3	858.4	856.5	857.4	859.2	860.5
180°	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8
2.5°	5082.9	5054.5	5054.5	5007.1	4988.1	4973.9	4950.2	4879.0	4860.1	4841.1	4869.6
5°	5125.6	5073.5	5035.5	4950.2	4879.0	4850.6	4760.5	4589.8	4476.0	4390.6	4343.3
7.5°	5135.1	5068.7	4997.6	4864.8	4694.1	4618.3	4343.3	4030.3	3944.9	3869.1	3821.6
10°	5125.6	5049.8	4950.2	4751.1	4348.0	4215.2	3940.3	3736.4	3684.2	3670.0	3684.2
12.5°	5092.4	5021.3	4883.8	4551.8	3987.6	3897.6	3736.4	3617.8	3608.3	3632.0	3760.0
15°	5035.5	4969.2	4808.0	4286.3	3788.5	3722.1	3608.3	3565.6	3617.8	3783.7	4167.8
17.5°	4978.6	4902.8	4703.6	4025.5	3636.8	3589.4	3508.8	3594.1	3888.1	4110.9	4239.0
20°	4902.8	4812.6	4585.1	3835.9	3527.7	3485.0	3447.1	3831.2	4054.0	4134.6	4205.7
22.5°	4812.6	4717.8	4423.9	3703.1	3414.0	3380.7	3404.4	3963.9	4054.0	4110.9	4172.6
25°	4694.1	4613.5	4234.2	3598.8	3323.8	3285.9	3375.9	3949.7	4001.8	4016.1	4139.4
27.5°	4585.1	4480.8	4035.1	3504.0	3214.7	3200.5	3399.7	3888.1	3926.0	3940.3	4073.0
30°	4452.3	4295.8	3812.2	3404.4	3101.0	3096.2	3404.4	3812.2	3802.7	3840.6	3973.4
32.5°	4314.8	4020.9	3560.9	3281.1	2991.9	2987.2	3371.3	3698.4	3688.9	3741.0	3840.6
35°	4186.7	3807.5	3219.5	3138.9	2854.4	2859.2	3290.7	3565.6	3570.4	3617.8	3679.4
37.5°	4054.0	3622.5	2845.0	2982.4	2721.7	2721.7	3181.6	3442.4	3432.9	3447.1	3532.5
40°	3897.6	3333.3	2513.0	2778.6	2598.4	2584.1	3048.9	3309.6	3276.4	3271.7	3390.2
42.5°	3731.6	3015.6	2266.4	2508.3	2456.1	2437.2	2887.6	3148.4	3086.8	3101.0	3252.7
45°	3551.4	2930.2	2076.7	2119.4	2309.1	2294.9	2712.1	2963.5	2920.8	2958.7	3115.2
47.5°	3371.3	2759.6	2015.2	1759.1	2152.7	2147.9	2517.8	2783.3	2759.6	2797.5	2963.5
50°	3124.7	2569.9	2010.4	1507.8	1977.2	1996.1	2285.4	2607.8	2607.8	2641.1	2816.5
52.5°	2807.0	2337.6	1825.5	1365.6	1773.3	1830.3	2081.5	2456.1	2465.6	2498.8	2655.3
55°	2517.8	2095.8	1692.7	1256.5	1531.5	1654.8	1882.4	2299.6	2318.7	2351.8	2494.1
57.5°	2252.2	1744.9	1664.3	1128.5	1308.6	1427.2	1707.0	2147.9	2157.4	2185.8	2323.3
60°	1967.8	1261.3	1526.8	991.0	1114.3	1204.4	1545.8	1967.8	2000.9	2019.9	2138.4
62.5°	1645.3	915.1	1384.6	896.2	1019.5	1038.4	1413.0	1797.0	1839.7	1853.9	1925.1
65°	1171.1	768.1	1175.9	815.6	919.9	924.6	1270.7	1621.6	1659.5	1683.3	1735.4
67.5°	791.8	625.9	896.2	739.6	844.0	848.7	1133.2	1417.7	1469.8	1488.9	1522.0
70°	550.0	417.2	663.8	659.0	758.7	768.1	986.2	1232.8	1280.2	1294.4	1313.4
72.5°	403.0	336.6	550.0	592.7	668.6	678.1	834.5	1024.1	1071.6	1085.8	1095.3
75°	308.2	355.6	445.7	516.8	569.0	573.8	682.8	834.5	867.7	877.2	881.9
77.5°	246.6	331.9	327.2	417.2	464.7	455.2	535.8	644.8	673.3	673.3	673.3
80°	184.9	260.8	246.6	298.7	341.4	331.9	384.1	459.9	469.4	478.9	474.2
82.5°	137.5	166.0	166.0	189.7	227.6	218.1	256.0	298.7	298.7	298.7	308.2
85°	85.4	94.8	75.8	99.6	128.1	123.3	142.2	161.2	166.0	166.0	156.4
87.5°	52.1	42.7	23.7	37.9	56.9	56.9	66.4	71.1	66.4	66.4	66.4
90°	15.0	10.4	5.8	10.4	15.0	16.2	25.4	37.7	43.9	39.0	29.2
92.5°	101.6	62.3	23.1	62.3	101.6	111.4	156.6	217.0	247.1	216.6	155.5
95°	199.2	127.3	55.5	127.3	199.2	217.2	385.6	610.2	722.4	644.6	489.1
97.5°	222.7	159.2	95.8	159.2	222.7	238.5	519.4	893.8	1081.1	1032.0	933.6
100°	242.0	184.6	127.0	184.6	242.0	256.4	568.1	983.6	1191.4	1195.0	1202.2
102.5°	260.9	207.3	153.6	207.3	260.9	274.3	590.4	1011.9	1222.6	1285.2	1410.4
105°	289.4	244.1	198.7	244.1	289.4	300.8	606.9	1015.1	1219.2	1359.5	1640.3
107.5°	329.6	287.2	244.9	287.2	329.6	340.2	610.1	970.0	1149.8	1345.7	1737.4
110°	352.6	314.3	276.1	314.3	352.6	362.1	605.4	929.9	1092.1	1311.1	1748.9

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	379.5	343.1	306.6	343.1	379.5	388.6	605.6	894.9	1039.5	1263.6	1711.7
115°	420.1	386.5	352.9	386.5	420.1	428.5	611.2	854.8	976.6	1192.4	1624.1
117.5°	459.5	429.0	398.4	429.0	459.5	467.2	622.5	829.7	933.3	1128.1	1517.7
120°	482.5	453.8	425.1	453.8	482.5	489.7	631.8	821.3	916.0	1094.0	1449.9
122.5°	509.0	480.1	451.0	480.1	509.0	516.3	645.1	816.8	902.6	1062.9	1383.5
125°	543.8	517.3	490.9	517.3	543.8	550.4	663.0	813.1	888.2	1024.4	1296.7
127.5°	576.7	549.9	523.2	549.9	576.7	583.3	680.9	811.0	876.1	993.0	1226.8
130°	598.0	569.4	540.6	569.4	598.0	605.2	694.0	812.3	871.5	975.6	1183.8
132.5°	616.0	587.2	558.4	587.2	616.0	623.2	704.6	813.1	867.4	960.6	1147.0
135°	637.4	611.2	585.1	611.2	637.4	643.9	716.1	812.4	860.5	938.6	1094.6
137.5°	664.1	638.1	612.1	638.1	664.1	670.5	733.5	817.4	859.4	925.3	1057.3
140°	682.4	658.6	634.7	658.6	682.4	688.4	744.0	818.2	855.3	912.2	1026.3
142.5°	696.2	674.1	652.0	674.1	696.2	701.7	752.9	821.2	855.3	905.3	1005.5
145°	717.0	697.8	678.6	697.8	717.0	721.9	764.5	821.2	849.6	890.5	972.4
147.5°	742.6	723.8	705.2	723.8	742.6	747.3	781.4	826.9	849.6	881.8	946.2
150°	756.4	739.4	722.4	739.4	756.4	760.6	790.3	829.8	849.6	876.7	931.1
152.5°	766.1	753.2	740.4	753.2	766.1	769.2	796.0	831.7	849.6	872.8	919.2
155°	786.0	776.4	766.9	776.4	786.0	788.3	808.8	835.9	849.6	868.1	905.0
157.5°	805.0	795.9	786.6	795.9	805.0	807.3	821.5	840.2	849.6	864.0	892.6
160°	814.3	807.1	799.9	807.1	814.3	816.0	827.2	842.1	849.6	861.9	886.5
162.5°	824.0	818.6	813.1	818.6	824.0	825.3	833.4	844.1	849.6	859.9	880.7
165°	837.3	832.5	827.6	832.5	837.3	838.5	842.2	847.1	849.6	857.0	871.9
167.5°	845.5	843.1	840.9	843.1	845.5	846.0	849.1	853.2	855.3	860.1	869.9
170°	854.1	851.8	849.6	851.8	854.1	854.7	854.9	855.2	855.3	860.1	869.9
172.5°	855.2	854.6	854.1	854.6	855.2	855.3	855.3	855.3	855.3	859.1	866.8
175°	860.5	860.5	860.5	860.5	860.5	860.5	858.7	856.4	855.3	857.7	862.6
177.5°	860.5	860.5	860.5	860.5	860.5	860.5	859.2	857.4	856.5	858.4	862.3
180°	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8	5011.8
2.5°	4836.3	4822.1	4841.1	4789.0	4841.1	4822.1	4836.3	4869.6	4841.1	4860.1	4879.0
5°	4243.7	4220.0	4144.1	4082.5	4144.1	4220.0	4243.7	4343.3	4390.6	4476.0	4589.8
7.5°	3793.3	3774.3	3755.3	3717.4	3755.3	3774.3	3793.3	3821.6	3869.1	3944.9	4030.3
10°	3693.7	3698.4	3726.8	3722.1	3726.8	3698.4	3693.7	3684.2	3670.0	3684.2	3736.4
12.5°	3949.7	3992.4	4148.8	4139.4	4148.8	3992.4	3949.7	3760.0	3632.0	3608.3	3617.8
15°	4243.7	4257.9	4291.1	4295.8	4291.1	4257.9	4243.7	4167.8	3783.7	3617.8	3565.6
17.5°	4272.1	4276.9	4300.6	4300.6	4300.6	4276.9	4272.1	4239.0	4110.9	3888.1	3594.1
20°	4248.4	4257.9	4305.4	4314.8	4305.4	4257.9	4248.4	4205.7	4134.6	4054.0	3831.2
22.5°	4239.0	4257.9	4295.8	4291.1	4295.8	4257.9	4239.0	4172.6	4110.9	4054.0	3963.9
25°	4191.5	4191.5	4196.3	4201.0	4196.3	4191.5	4191.5	4139.4	4016.1	4001.8	3949.7
27.5°	4091.9	4101.5	4129.9	4125.1	4129.9	4101.5	4091.9	4073.0	3940.3	3926.0	3888.1
30°	4001.8	3992.4	3968.7	3949.7	3968.7	3992.4	4001.8	3973.4	3840.6	3802.7	3812.2
32.5°	3850.1	3826.4	3802.7	3788.5	3802.7	3826.4	3850.1	3840.6	3741.0	3688.9	3698.4
35°	3670.0	3674.7	3670.0	3655.8	3670.0	3674.7	3670.0	3679.4	3617.8	3570.4	3565.6
37.5°	3541.9	3551.4	3546.7	3527.7	3546.7	3551.4	3541.9	3532.5	3447.1	3432.9	3442.4
40°	3409.2	3414.0	3409.2	3394.9	3409.2	3414.0	3409.2	3390.2	3271.7	3276.4	3309.6
42.5°	3281.1	3276.4	3262.2	3252.7	3262.2	3276.4	3281.1	3252.7	3101.0	3086.8	3148.4
45°	3134.1	3138.9	3110.4	3096.2	3110.4	3138.9	3134.1	3115.2	2958.7	2920.8	2963.5
47.5°	2987.2	2987.2	2963.5	2949.2	2963.5	2987.2	2987.2	2963.5	2797.5	2759.6	2783.3
50°	2830.7	2826.0	2792.8	2788.0	2792.8	2826.0	2830.7	2816.5	2641.1	2607.8	2607.8
52.5°	2650.5	2650.5	2655.3	2664.7	2655.3	2650.5	2650.5	2655.3	2498.8	2465.6	2456.1
55°	2494.1	2498.8	2532.0	2541.5	2532.0	2498.8	2494.1	2494.1	2351.8	2318.7	2299.6
57.5°	2332.9	2332.9	2356.6	2356.6	2356.6	2332.9	2332.9	2323.3	2185.8	2157.4	2147.9
60°	2147.9	2157.4	2176.4	2171.6	2176.4	2157.4	2147.9	2138.4	2019.9	2000.9	1967.8
62.5°	1953.6	1963.0	1967.8	1958.2	1967.8	1963.0	1953.6	1925.1	1853.9	1839.7	1797.0
65°	1749.7	1759.1	1763.9	1754.3	1763.9	1759.1	1749.7	1735.4	1683.3	1659.5	1621.6
67.5°	1541.0	1536.2	1531.5	1550.4	1531.5	1536.2	1541.0	1522.0	1488.9	1469.8	1417.7
70°	1327.6	1327.6	1322.9	1332.4	1322.9	1327.6	1327.6	1313.4	1294.4	1280.2	1232.8
72.5°	1100.1	1095.3	1114.3	1100.1	1114.3	1095.3	1100.1	1095.3	1085.8	1071.6	1024.1
75°	877.2	886.6	877.2	891.4	877.2	886.6	877.2	881.9	877.2	867.7	834.5
77.5°	668.6	678.1	668.6	668.6	668.6	678.1	668.6	673.3	673.3	673.3	644.8
80°	474.2	469.4	469.4	464.7	469.4	469.4	474.2	474.2	478.9	469.4	459.9
82.5°	303.5	298.7	298.7	308.2	298.7	298.7	303.5	308.2	298.7	298.7	298.7
85°	166.0	170.7	161.2	161.2	161.2	170.7	166.0	156.4	166.0	166.0	161.2
87.5°	61.6	56.9	56.9	56.9	56.9	56.9	61.6	66.4	66.4	66.4	71.1
90°	21.9	21.9	21.9	21.9	21.9	21.9	21.9	29.2	39.0	43.9	37.7
92.5°	109.7	105.4	87.9	70.4	87.9	105.4	109.7	155.5	216.6	247.1	217.0
95°	372.5	359.2	306.4	253.5	306.4	359.2	372.5	489.1	644.6	722.4	610.2
97.5°	859.9	834.8	734.1	633.5	734.1	834.8	859.9	933.6	1032.0	1081.1	893.8
100°	1207.6	1177.6	1057.8	937.9	1057.8	1177.6	1207.6	1202.2	1195.0	1191.4	983.6
102.5°	1504.4	1478.7	1376.1	1273.4	1376.1	1478.7	1504.4	1410.4	1285.2	1222.6	1011.9
105°	1850.9	1837.1	1782.0	1726.8	1782.0	1837.1	1850.9	1640.3	1359.5	1219.2	1015.1
107.5°	2031.2	2034.5	2047.8	2061.2	2047.8	2034.5	2031.2	1737.4	1345.7	1149.8	970.0
110°	2077.3	2091.7	2149.1	2206.7	2149.1	2091.7	2077.3	1748.9	1311.1	1092.1	929.9

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	2047.9	2069.9	2158.3	2246.6	2158.3	2069.9	2047.9	1711.7	1263.6	1039.5	894.9
115°	1948.0	1978.6	2101.0	2223.5	2101.0	1978.6	1948.0	1624.1	1192.4	976.6	854.8
117.5°	1809.9	1843.8	1979.6	2115.4	1979.6	1843.8	1809.9	1517.7	1128.1	933.3	829.7
120°	1717.0	1749.9	1881.9	2013.8	1881.9	1749.9	1717.0	1449.9	1094.0	916.0	821.3
122.5°	1623.9	1656.4	1786.6	1916.8	1786.6	1656.4	1623.9	1383.5	1062.9	902.6	816.8
125°	1500.9	1530.9	1650.8	1770.7	1650.8	1530.9	1500.9	1296.7	1024.4	888.2	813.1
127.5°	1402.2	1427.5	1528.6	1629.7	1528.6	1427.5	1402.2	1226.8	993.0	876.1	811.0
130°	1339.8	1363.2	1456.7	1550.1	1456.7	1363.2	1339.8	1183.8	975.6	871.5	812.3
132.5°	1286.7	1307.6	1391.3	1475.0	1391.3	1307.6	1286.7	1147.0	960.6	867.4	813.1
135°	1211.7	1229.7	1301.8	1373.9	1301.8	1229.7	1211.7	1094.6	938.6	860.5	812.4
137.5°	1156.2	1171.0	1230.0	1289.0	1230.0	1171.0	1156.2	1057.3	925.3	859.4	817.4
140°	1111.7	1125.6	1180.7	1235.9	1180.7	1125.6	1111.7	1026.3	912.2	855.3	818.2
142.5°	1080.5	1092.4	1139.9	1187.4	1139.9	1092.4	1080.5	1005.5	905.3	855.3	821.2
145°	1033.8	1042.7	1078.7	1114.6	1078.7	1042.7	1033.8	972.4	890.5	849.6	821.2
147.5°	994.5	1002.0	1031.7	1061.5	1031.7	1002.0	994.5	946.2	881.8	849.6	826.9
150°	971.9	978.0	1002.1	1026.3	1002.1	978.0	971.9	931.1	876.7	849.6	829.8
152.5°	954.1	958.7	976.9	995.1	976.9	958.7	954.1	919.2	872.8	849.6	831.7
155°	932.7	935.7	947.8	959.9	947.8	935.7	932.7	905.0	868.1	849.6	835.9
157.5°	914.2	916.3	924.8	933.3	924.8	916.3	914.2	892.6	864.0	849.6	840.2
160°	905.0	906.2	911.1	916.0	911.1	906.2	905.0	886.5	861.9	849.6	842.1
162.5°	896.3	897.4	902.1	906.7	902.1	897.4	896.3	880.7	859.9	849.6	844.1
165°	883.0	884.2	889.2	894.0	889.2	884.2	883.0	871.9	857.0	849.6	847.1
167.5°	877.2	877.8	879.8	881.9	879.8	877.8	877.2	869.9	860.1	855.3	853.2
170°	877.2	877.2	877.2	877.2	877.2	877.2	877.2	869.9	860.1	855.3	855.2
172.5°	872.6	872.2	870.4	868.6	870.4	872.2	872.6	866.8	859.1	855.3	855.3
175°	866.3	866.3	866.3	866.3	866.3	866.3	866.3	862.6	857.7	855.3	856.4
177.5°	865.2	864.6	862.5	860.5	862.5	864.6	865.2	862.3	858.4	856.5	857.4
180°	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
0°	5011.8	5011.8	5011.8	5011.8	5011.8
2.5°	4950.2	4973.9	4988.1	5007.1	5054.5
5°	4760.5	4850.6	4879.0	4950.2	5035.5
7.5°	4343.3	4618.3	4694.1	4864.8	4997.6
10°	3940.3	4215.2	4348.0	4751.1	4950.2
12.5°	3736.4	3897.6	3987.6	4551.8	4883.8
15°	3608.3	3722.1	3788.5	4286.3	4808.0
17.5°	3508.8	3589.4	3636.8	4025.5	4703.6
20°	3447.1	3485.0	3527.7	3835.9	4585.1
22.5°	3404.4	3380.7	3414.0	3703.1	4423.9
25°	3375.9	3285.9	3323.8	3598.8	4234.2
27.5°	3399.7	3200.5	3214.7	3504.0	4035.1
30°	3404.4	3096.2	3101.0	3404.4	3812.2
32.5°	3371.3	2987.2	2991.9	3281.1	3560.9
35°	3290.7	2859.2	2854.4	3138.9	3219.5
37.5°	3181.6	2721.7	2721.7	2982.4	2845.0
40°	3048.9	2584.1	2598.4	2778.6	2513.0
42.5°	2887.6	2437.2	2456.1	2508.3	2266.4
45°	2712.1	2294.9	2309.1	2119.4	2076.7
47.5°	2517.8	2147.9	2152.7	1759.1	2015.2
50°	2285.4	1996.1	1977.2	1507.8	2010.4
52.5°	2081.5	1830.3	1773.3	1365.6	1825.5
55°	1882.4	1654.8	1531.5	1256.5	1692.7
57.5°	1707.0	1427.2	1308.6	1128.5	1664.3
60°	1545.8	1204.4	1114.3	991.0	1526.8
62.5°	1413.0	1038.4	1019.5	896.2	1384.6
65°	1270.7	924.6	919.9	815.6	1175.9
67.5°	1133.2	848.7	844.0	739.6	896.2
70°	986.2	768.1	758.7	659.0	663.8
72.5°	834.5	678.1	668.6	592.7	550.0
75°	682.8	573.8	569.0	516.8	445.7
77.5°	535.8	455.2	464.7	417.2	327.2
80°	384.1	331.9	341.4	298.7	246.6
82.5°	256.0	218.1	227.6	189.7	166.0
85°	142.2	123.3	128.1	99.6	75.8
87.5°	66.4	56.9	56.9	37.9	23.7
90°	25.4	16.2	15.0	10.4	5.8
92.5°	156.6	111.4	101.6	62.3	23.1
95°	385.6	217.2	199.2	127.3	55.5
97.5°	519.4	238.5	222.7	159.2	95.8
100°	568.1	256.4	242.0	184.6	127.0
102.5°	590.4	274.3	260.9	207.3	153.6
105°	606.9	300.8	289.4	244.1	198.7
107.5°	610.1	340.2	329.6	287.2	244.9
110°	605.4	362.1	352.6	314.3	276.1

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CANDELA DISTRIBUTION (continued):

	330°	337.5°	340°	350°	360°
112.5°	605.6	388.6	379.5	343.1	306.6
115°	611.2	428.5	420.1	386.5	352.9
117.5°	622.5	467.2	459.5	429.0	398.4
120°	631.8	489.7	482.5	453.8	425.1
122.5°	645.1	516.3	509.0	480.1	451.0
125°	663.0	550.4	543.8	517.3	490.9
127.5°	680.9	583.3	576.7	549.9	523.2
130°	694.0	605.2	598.0	569.4	540.6
132.5°	704.6	623.2	616.0	587.2	558.4
135°	716.1	643.9	637.4	611.2	585.1
137.5°	733.5	670.5	664.1	638.1	612.1
140°	744.0	688.4	682.4	658.6	634.7
142.5°	752.9	701.7	696.2	674.1	652.0
145°	764.5	721.9	717.0	697.8	678.6
147.5°	781.4	747.3	742.6	723.8	705.2
150°	790.3	760.6	756.4	739.4	722.4
152.5°	796.0	769.2	766.1	753.2	740.4
155°	808.8	788.3	786.0	776.4	766.9
157.5°	821.5	807.3	805.0	795.9	786.6
160°	827.2	816.0	814.3	807.1	799.9
162.5°	833.4	825.3	824.0	818.6	813.1
165°	842.2	838.5	837.3	832.5	827.6
167.5°	849.1	846.0	845.5	843.1	840.9
170°	854.9	854.7	854.1	851.8	849.6
172.5°	855.3	855.3	855.2	854.6	854.1
175°	858.7	860.5	860.5	860.5	860.5
177.5°	859.2	860.5	860.5	860.5	860.5
180°	860.5	860.5	860.5	860.5	860.5

TEST NUMBER: P934581

CATALOG NUMBER: SQ4-FA-050U-125D-B2750-1D-UNV-W2A-W-12-5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.00	17.08	16.77	17.86	18.82	18.85	19.93	19.62	20.71	21.67
	3H	16.50	17.46	17.27	18.26	19.24	20.22	21.19	21.00	21.98	22.97
	4H	16.70	17.61	17.49	18.41	19.41	20.68	21.59	21.48	22.40	23.39
	6H	16.83	17.67	17.63	18.48	19.49	20.98	21.82	21.79	22.63	23.64
	8H	16.83	17.63	17.65	18.47	19.48	21.06	21.86	21.88	22.70	23.71
	12H	16.81	17.57	17.63	18.40	19.44	21.11	21.88	21.94	22.70	23.74
4H	2H	17.07	17.98	17.86	18.78	19.78	19.29	20.20	20.09	21.00	22.00
	3H	18.11	18.87	18.92	19.71	20.72	20.82	21.58	21.63	22.42	23.43
	4H	18.40	19.09	19.22	19.93	20.97	21.36	22.05	22.19	22.89	23.93
	6H	18.53	19.13	19.38	19.99	21.04	21.74	22.34	22.59	23.20	24.25
	8H	18.54	19.10	19.39	19.96	21.02	21.86	22.42	22.70	23.27	24.33
	12H	18.52	19.02	19.39	19.90	20.97	21.93	22.43	22.80	23.31	24.37
8H	4H	18.87	19.43	19.72	20.29	21.34	21.50	22.06	22.35	22.92	23.97
	6H	19.14	19.60	20.02	20.50	21.56	21.95	22.41	22.83	23.31	24.37
	8H	19.19	19.60	20.07	20.49	21.57	22.11	22.52	23.00	23.41	24.49
	12H	19.18	19.54	20.07	20.43	21.56	22.22	22.58	23.11	23.47	24.60
12H	4H	18.89	19.39	19.75	20.27	21.33	21.48	21.98	22.34	22.86	23.92
	6H	19.21	19.62	20.09	20.51	21.58	21.95	22.36	22.84	23.26	24.33
	8H	19.28	19.64	20.17	20.53	21.66	22.13	22.49	23.01	23.37	24.50

END OF REPORT