

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936803

Luminaire Tested: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936803
REPORT IS A COMBINATION OF REPORTS P933478 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6300.1 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	98	94	89	86	91	87	83	80	75	72	69	63	61	59	53	51	50
2	89	81	74	69	82	75	70	65	65	60	56	55	51	49	45	43	41
3	81	71	63	57	74	66	59	53	56	51	47	48	44	40	40	37	34
4	73	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29
5	67	55	46	40	62	51	44	38	44	38	33	37	33	29	31	28	25
6	62	49	40	34	57	46	38	32	39	33	29	33	29	25	28	24	21
7	57	44	36	30	52	41	34	28	35	29	25	30	25	22	25	22	19
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15
10	46	33	25	20	42	31	24	19	27	21	17	23	18	15	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2756	2756	2756
5°	2691	3185	3704
10°	2440	4641	6141
15°	2073	6062	7416
20°	1687	7024	7558
25°	1407	7348	7405
30°	1186	7392	7390
35°	1048	7268	7582
40°	913	7105	7780
45°	826	6987	7810
50°	757	6880	7680
55°	725	6723	7339
60°	741	6425	6802
65°	769	5973	6063
70°	818	5205	5122
75°	902	4241	3998
80°	980	2938	2694
85°	853	1557	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7810 cd/sqm

TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.6	0.9
10°-20°	255.4	4.1
20°-30°	446.8	7.1
30°-40°	575.1	9.1
40°-50°	642.4	10.2
50°-60°	615.2	9.8
60°-70°	487.6	7.7
70°-80°	286.7	4.6
80°-90°	81.3	1.3
90°-100°	214.4	3.4
100°-110°	563.8	8.9
110°-120°	584.6	9.3
120°-130°	468.9	7.4
130°-140°	367.9	5.8
140°-150°	282.4	4.5
150°-160°	203.4	3.2
160°-170°	124.4	2.0
170°-180°	42.0	0.7
0°-30°	759.8	12.1
0°-40°	1335.0	21.2
0°-60°	2592.6	41.2
0°-90°	3448.2	54.7
90°-120°	1362.8	21.6
90°-150°	2482.0	39.4
90°-180°	2852.0	45.3
0°-180°	6300.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	446	446	446	446	446	
5°	434	466	524	593	614	40
15°	325	600	1011	1226	1265	90
25°	208	680	1205	1258	1259	96
35°	140	650	1135	1199	1246	88
45°	96	519	1003	1149	1200	74
55°	69	330	851	988	1016	63
65°	54	175	632	710	720	54
75°	40	107	347	381	382	42
85°	14	33	86	94	96	15
90°	3	8	22	11	11	3
95°	28	111	369	190	130	31
105°	102	154	623	946	883	108
115°	180	219	499	996	1137	178
125°	251	281	454	767	905	223
135°	299	329	440	619	702	231
145°	347	369	434	528	570	217
155°	392	403	434	477	491	180
165°	423	429	434	451	457	119
175°	440	440	437	443	443	42
180°	440	440	440	440	440	

TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5
2.5°	445.5	445.5	448.4	449.8	452.7	454.1	457.0	459.8	468.4	469.9	472.7
5°	434.0	439.8	458.4	465.6	485.6	512.8	524.3	542.9	581.6	593.1	600.2
7.5°	416.9	429.8	475.6	487.0	537.2	608.8	638.9	679.0	740.6	770.7	795.0
10°	389.6	416.9	498.5	525.7	607.4	716.2	772.1	828.0	921.1	962.6	978.4
12.5°	359.6	404.0	522.9	560.1	677.6	836.6	903.9	965.5	1071.5	1127.5	1136.1
15°	325.2	385.3	545.8	600.2	752.1	936.9	1011.3	1087.4	1186.2	1226.3	1236.3
17.5°	295.1	371.0	567.3	624.6	809.4	1027.1	1103.1	1166.2	1246.4	1273.6	1280.8
20°	257.8	348.1	581.6	656.1	869.5	1093.1	1166.2	1214.9	1269.3	1286.5	1289.3
22.5°	230.6	323.7	590.2	667.5	909.6	1133.2	1194.8	1233.5	1270.7	1276.5	1277.9
25°	207.7	296.5	588.8	680.4	944.0	1157.6	1204.8	1233.5	1255.0	1257.8	1257.8
27.5°	186.2	266.4	583.0	683.3	969.8	1163.3	1200.5	1220.6	1230.6	1236.3	1236.3
30°	167.6	237.8	568.7	677.6	981.3	1157.6	1187.6	1197.7	1207.7	1216.3	1220.6
32.5°	153.3	210.6	547.2	666.1	982.7	1143.2	1164.7	1170.4	1184.8	1204.8	1212.0
35°	140.4	183.4	522.9	650.4	974.1	1120.3	1134.6	1140.4	1169.0	1199.1	1209.1
37.5°	127.5	163.3	491.3	623.1	961.2	1093.1	1103.1	1113.1	1157.6	1193.4	1204.8
40°	114.6	146.1	454.1	593.1	941.2	1060.0	1068.6	1084.4	1143.2	1184.8	1196.2
42.5°	104.6	131.8	414.0	561.5	915.4	1022.8	1035.7	1058.6	1126.0	1170.4	1183.3
45°	96.0	117.5	371.0	518.6	882.4	984.1	1002.8	1034.3	1106.0	1149.0	1160.4
47.5°	87.4	107.4	326.6	474.2	846.6	945.4	969.8	1005.6	1078.7	1120.3	1130.3
50°	80.2	97.4	282.2	426.9	807.9	903.9	932.6	969.8	1044.3	1083.0	1096.0
52.5°	74.5	88.8	240.7	379.6	763.5	860.9	893.9	932.6	1002.8	1040.0	1048.6
55°	68.8	81.7	204.8	329.5	717.7	815.1	850.9	888.2	956.9	988.4	994.2
57.5°	65.9	75.9	174.8	282.2	669.0	763.5	803.6	838.0	902.5	926.8	932.6
60°	61.6	71.6	151.8	242.1	616.0	714.8	749.2	783.6	838.0	858.1	862.4
62.5°	57.3	68.8	134.7	203.4	561.5	657.5	691.9	723.4	769.3	783.6	789.3
65°	54.4	65.9	121.8	174.8	505.7	597.4	631.7	658.9	696.2	710.5	713.4
67.5°	51.6	63.0	111.7	150.4	449.8	537.2	563.0	588.8	617.4	631.7	633.2
70°	47.3	60.2	103.1	133.2	392.5	468.4	489.9	517.1	540.1	547.2	551.5
72.5°	44.4	55.9	97.4	120.3	333.8	402.5	422.6	438.3	458.4	465.6	465.6
75°	40.1	50.1	91.7	107.4	273.6	329.5	346.7	362.4	378.2	381.0	376.7
77.5°	35.8	44.4	78.8	90.2	213.4	260.7	275.0	283.6	296.5	299.4	300.8
80°	30.1	38.7	61.6	70.2	154.7	192.0	202.0	209.1	220.6	220.6	223.5
82.5°	22.9	30.1	44.4	50.1	104.6	131.8	140.4	144.7	151.8	151.8	151.8
85°	14.3	18.6	28.6	32.9	63.0	80.2	86.0	87.4	93.1	94.5	94.5
87.5°	7.2	10.0	18.6	20.1	32.9	41.5	41.5	44.4	44.4	43.0	41.5
90°	3.0	5.3	7.7	8.3	13.0	19.3	22.4	20.0	14.9	11.2	11.2
92.5°	11.8	31.9	52.0	57.0	80.1	111.0	126.3	110.7	79.5	56.1	53.9
95°	28.4	65.0	101.8	111.0	197.1	312.0	369.4	329.7	250.1	190.4	183.6
97.5°	49.0	81.5	113.8	122.0	265.6	457.1	552.8	527.6	477.3	439.6	426.7
100°	64.9	94.4	123.8	131.1	290.4	502.9	609.1	610.9	614.6	617.4	602.1
102.5°	78.5	106.0	133.4	140.3	301.9	517.3	625.0	657.0	721.1	769.2	756.1
105°	101.6	124.8	148.0	153.9	310.3	518.9	623.2	695.0	838.6	946.3	939.2
107.5°	125.2	146.9	168.5	173.9	311.9	495.8	587.8	687.9	888.2	1038.4	1040.1
110°	141.1	160.6	180.2	185.1	309.5	475.4	558.3	670.2	894.2	1062.1	1069.4

TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	156.8	175.4	194.1	198.7	309.6	457.5	531.5	646.1	875.2	1047.0	1058.2
115°	180.4	197.6	214.8	219.1	312.5	437.0	499.3	609.7	830.4	995.9	1011.5
117.5°	203.7	219.4	234.9	238.8	318.3	424.2	477.1	576.7	775.9	925.3	942.7
120°	217.3	232.0	246.7	250.4	323.0	419.8	468.2	559.2	741.3	877.7	894.6
122.5°	230.6	245.4	260.2	264.0	329.8	417.5	461.5	543.4	707.4	830.3	846.9
125°	251.0	264.4	278.0	281.3	338.9	415.7	454.1	523.7	663.0	767.3	782.6
127.5°	267.5	281.2	294.8	298.2	348.1	414.7	447.9	507.7	627.1	716.8	729.7
130°	276.4	291.1	305.8	309.4	354.8	415.2	445.5	498.7	605.2	685.0	697.0
132.5°	285.5	300.3	315.0	318.6	360.2	415.7	443.5	491.2	586.4	657.8	668.5
135°	299.1	312.5	325.8	329.2	366.1	415.3	440.0	479.9	559.6	619.4	628.7
137.5°	313.0	326.2	339.4	342.7	374.9	417.8	439.3	473.0	540.4	591.0	598.6
140°	324.5	336.7	348.9	351.9	380.4	418.3	437.3	466.4	524.7	568.3	575.4
142.5°	333.3	344.6	355.8	358.7	384.9	419.8	437.3	462.9	514.0	552.4	558.5
145°	347.0	356.8	366.6	369.1	390.9	419.8	434.3	455.2	497.1	528.5	533.1
147.5°	360.5	370.1	379.7	382.1	399.5	422.7	434.3	450.8	483.7	508.4	512.3
150°	369.4	378.1	386.7	388.9	404.1	424.2	434.3	448.3	476.1	496.9	499.9
152.5°	378.5	385.1	391.6	393.3	406.9	425.2	434.3	446.2	470.0	487.7	490.0
155°	392.1	397.0	401.8	403.0	413.4	427.4	434.3	443.8	462.7	476.8	478.4
157.5°	402.2	406.8	411.6	412.8	419.9	429.6	434.3	441.7	456.4	467.4	468.4
160°	408.9	412.6	416.2	417.1	422.9	430.5	434.3	440.6	453.2	462.7	463.3
162.5°	415.7	418.5	421.3	421.9	426.0	431.6	434.3	439.7	450.3	458.2	458.8
165°	423.1	425.5	428.0	428.7	430.6	433.1	434.3	438.2	445.7	451.4	452.1
167.5°	429.8	431.0	432.2	432.5	434.1	436.2	437.3	439.8	444.7	448.5	448.8
170°	434.3	435.5	436.7	437.0	437.1	437.2	437.3	439.8	444.7	448.5	448.5
172.5°	436.7	437.0	437.2	437.3	437.3	437.3	437.3	439.2	443.1	446.1	445.9
175°	440.0	440.0	440.0	440.0	439.1	437.9	437.3	438.5	441.0	442.8	442.8
177.5°	440.0	440.0	440.0	440.0	439.3	438.3	437.9	438.8	440.8	442.3	442.0
180°	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0

TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	445.5	445.5
2.5°	475.6	472.7
5°	611.7	614.5
7.5°	823.7	822.3
10°	1024.2	1037.1
12.5°	1170.4	1173.3
15°	1259.3	1265.0
17.5°	1293.6	1295.1
20°	1295.1	1292.2
22.5°	1279.3	1276.5
25°	1260.7	1259.3
27.5°	1243.5	1244.9
30°	1236.3	1240.6
32.5°	1236.3	1243.5
35°	1239.2	1246.4
37.5°	1237.8	1246.4
40°	1232.0	1242.1
42.5°	1216.3	1223.5
45°	1191.9	1200.5
47.5°	1160.4	1166.2
50°	1120.3	1126.0
52.5°	1070.1	1071.5
55°	1009.9	1015.6
57.5°	945.4	946.9
60°	873.8	878.1
62.5°	797.9	797.9
65°	717.7	720.5
67.5°	634.6	641.8
70°	550.1	551.5
72.5°	467.0	467.0
75°	381.0	382.5
77.5°	299.4	299.4
80°	222.0	223.5
82.5°	153.3	156.1
85°	96.0	96.0
87.5°	44.4	40.1
90°	11.2	11.2
92.5°	44.9	36.0
95°	156.6	129.6
97.5°	375.3	323.9
100°	540.8	479.5
102.5°	703.5	651.0
105°	911.1	882.8
107.5°	1046.9	1053.7
110°	1098.7	1128.1

TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1103.4	1148.5
115°	1074.1	1136.7
117.5°	1012.1	1081.5
120°	962.1	1029.6
122.5°	913.5	979.9
125°	843.9	905.2
127.5°	781.5	833.2
130°	744.7	792.5
132.5°	711.3	754.1
135°	665.5	702.4
137.5°	628.9	659.0
140°	603.6	631.8
142.5°	582.7	607.0
145°	551.5	569.8
147.5°	527.4	542.6
150°	512.4	524.7
152.5°	499.4	508.7
155°	484.6	490.7
157.5°	472.8	477.1
160°	465.8	468.2
162.5°	461.2	463.6
165°	454.6	457.1
167.5°	449.8	450.9
170°	448.5	448.5
172.5°	444.9	444.1
175°	442.8	442.8
177.5°	441.0	440.0
180°	440.0	440.0

(END OF REPORT)