

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936804

Luminaire Tested: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936804
REPORT IS A COMBINATION OF REPORTS P933486 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8400.2 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936804

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P936804

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	98	94	89	86	91	87	83	80	75	72	69	63	61	59	53	51	50
2	89	81	74	69	82	75	70	65	65	60	56	55	51	49	45	43	41
3	81	71	63	57	74	66	59	53	56	51	47	48	44	40	40	37	34
4	73	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29
5	67	55	46	40	62	51	44	38	44	38	33	37	33	29	31	28	25
6	62	49	40	34	57	46	38	32	39	33	29	33	29	25	28	24	21
7	57	44	36	30	52	41	34	28	35	29	25	30	25	22	25	22	19
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15
10	46	33	25	20	42	31	24	19	27	21	17	23	18	15	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2756	2756	2756
5°	2692	3186	3704
10°	2442	4643	6142
15°	2076	6067	7416
20°	1690	7030	7558
25°	1410	7357	7405
30°	1189	7403	7391
35°	1051	7280	7582
40°	916	7121	7779
45°	829	7004	7810
50°	761	6898	7681
55°	729	6744	7340
60°	746	6447	6802
65°	776	5997	6063
70°	826	5230	5123
75°	916	4264	3998
80°	1000	2957	2694
85°	890	1569	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7810 cd/sqm

TEST NUMBER: P936804

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	0.9
10°-20°	340.6	4.1
20°-30°	595.7	7.1
30°-40°	766.8	9.1
40°-50°	856.5	10.2
50°-60°	820.4	9.8
60°-70°	650.1	7.7
70°-80°	382.3	4.6
80°-90°	108.4	1.3
90°-100°	285.9	3.4
100°-110°	751.7	8.9
110°-120°	779.4	9.3
120°-130°	625.2	7.4
130°-140°	490.6	5.8
140°-150°	376.5	4.5
150°-160°	271.2	3.2
160°-170°	165.9	2.0
170°-180°	56.1	0.7
0°-30°	1013.1	12.1
0°-40°	1780.0	21.2
0°-60°	3456.9	41.2
0°-90°	4597.7	54.7
90°-120°	1817.1	21.6
90°-150°	3309.4	39.4
90°-180°	3802.0	45.3
0°-180°	8400.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	594	594	594	594	594	
5°	579	621	699	791	819	53
15°	434	800	1349	1635	1687	121
25°	277	907	1606	1677	1679	128
35°	187	867	1513	1599	1662	117
45°	128	691	1337	1532	1601	99
55°	92	439	1135	1318	1354	84
65°	73	233	842	947	961	72
75°	54	143	462	508	510	56
85°	19	44	115	126	128	20
90°	4	11	30	15	15	5
95°	38	148	492	254	173	42
105°	135	205	831	1262	1177	144
115°	241	292	666	1328	1516	238
125°	335	375	606	1023	1207	297
135°	399	439	587	826	937	309
145°	463	492	579	705	760	290
155°	523	537	579	636	654	240
165°	564	572	579	602	609	159
175°	587	587	583	590	590	56
180°	587	587	587	587	587	

TEST NUMBER: P936804

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	594.0	594.0	594.0	594.0	594.0	594.0	594.0	594.0	594.0	594.0	594.0
2.5°	594.0	594.0	597.8	599.7	603.6	605.5	609.3	613.1	624.6	626.5	630.3
5°	578.7	586.4	611.2	620.8	647.5	683.8	699.1	723.9	775.5	790.7	800.3
7.5°	555.8	573.0	634.1	649.4	716.2	811.8	851.9	905.3	987.5	1027.6	1060.0
10°	519.5	555.8	664.7	701.0	809.8	955.0	1029.5	1104.1	1228.2	1283.6	1304.6
12.5°	479.4	538.6	697.2	746.8	903.4	1115.5	1205.3	1287.4	1428.8	1503.3	1514.7
15°	433.6	513.8	727.7	800.3	1002.8	1249.2	1348.6	1449.8	1581.6	1635.1	1648.4
17.5°	393.5	494.7	756.4	832.8	1079.1	1369.6	1470.8	1554.8	1661.8	1698.1	1707.6
20°	343.8	464.1	775.5	874.8	1159.5	1457.4	1554.8	1619.8	1692.4	1715.3	1719.1
22.5°	307.5	431.7	786.9	890.1	1212.9	1510.9	1593.0	1644.6	1694.3	1701.9	1703.8
25°	277.0	395.4	785.0	907.2	1258.8	1543.4	1606.4	1644.6	1673.3	1677.1	1677.1
27.5°	248.3	355.3	777.4	911.1	1293.2	1551.0	1600.7	1627.4	1640.8	1648.4	1648.4
30°	223.5	317.1	758.3	903.4	1308.4	1543.4	1583.5	1596.9	1610.2	1621.7	1627.4
32.5°	204.4	280.8	729.6	888.2	1310.4	1524.3	1552.9	1560.6	1579.7	1606.4	1616.0
35°	187.2	244.5	697.2	867.1	1298.9	1493.7	1512.8	1520.5	1558.7	1598.8	1612.1
37.5°	170.0	217.7	655.1	830.8	1281.7	1457.4	1470.8	1484.2	1543.4	1591.1	1606.4
40°	152.8	194.8	605.5	790.7	1255.0	1413.5	1425.0	1446.0	1524.3	1579.7	1594.9
42.5°	139.4	175.7	552.0	748.7	1220.6	1363.8	1381.0	1411.6	1501.4	1560.6	1577.8
45°	128.0	156.6	494.7	691.4	1176.7	1312.3	1337.1	1379.1	1474.6	1531.9	1547.2
47.5°	116.5	143.2	435.5	632.2	1128.9	1260.7	1293.2	1340.9	1438.3	1493.7	1507.1
50°	107.0	129.9	376.3	569.2	1077.2	1205.3	1243.5	1293.2	1392.5	1444.1	1461.2
52.5°	99.3	118.4	320.9	506.2	1018.0	1148.0	1191.9	1243.5	1337.1	1386.8	1398.2
55°	91.7	108.9	273.1	439.3	956.9	1086.9	1134.6	1184.3	1276.0	1318.0	1325.6
57.5°	87.9	101.2	233.0	376.3	892.0	1018.0	1071.5	1117.4	1203.4	1235.9	1243.5
60°	82.1	95.5	202.5	322.8	821.3	953.1	998.9	1044.8	1117.4	1144.2	1149.9
62.5°	76.4	91.7	179.5	271.2	748.7	876.7	922.5	964.6	1025.7	1044.8	1052.4
65°	72.6	87.9	162.4	233.0	674.2	796.5	842.3	878.6	928.3	947.4	951.2
67.5°	68.8	84.0	149.0	200.5	599.7	716.2	750.6	785.0	823.2	842.3	844.2
70°	63.0	80.2	137.5	177.6	523.3	624.6	653.2	689.5	720.1	729.6	735.4
72.5°	59.2	74.5	129.9	160.4	445.0	536.7	563.4	584.5	611.2	620.8	620.8
75°	53.5	66.8	122.2	143.2	364.8	439.3	462.2	483.2	504.2	508.1	502.3
77.5°	47.8	59.2	105.0	120.3	284.6	347.6	366.7	378.2	395.4	399.2	401.1
80°	40.1	51.6	82.1	93.6	206.3	255.9	269.3	278.9	294.1	294.1	298.0
82.5°	30.6	40.1	59.2	66.8	139.4	175.7	187.2	192.9	202.5	202.5	202.5
85°	19.1	24.8	38.2	43.9	84.0	107.0	114.6	116.5	124.2	126.1	126.1
87.5°	9.5	13.4	24.8	26.7	43.9	55.4	55.4	59.2	59.2	57.3	55.4
90°	3.9	7.1	10.2	11.0	17.3	25.7	29.9	26.5	20.0	15.0	15.0
92.5°	15.8	42.5	69.3	76.0	106.9	147.9	168.5	147.6	106.0	74.8	71.8
95°	37.8	86.8	135.8	148.0	262.8	415.9	492.5	439.5	333.5	253.9	245.0
97.5°	65.3	108.5	151.7	162.5	354.0	609.3	737.0	703.5	636.4	586.2	569.0
100°	86.6	125.8	164.9	174.8	387.3	670.5	812.1	814.6	819.5	823.1	802.7
102.5°	104.8	141.3	177.8	187.0	402.4	689.8	833.4	876.1	961.5	1025.5	1008.0
105°	135.4	166.4	197.4	205.1	413.8	692.0	831.0	926.7	1118.2	1261.7	1252.3
107.5°	166.9	195.8	224.6	231.9	415.8	661.1	783.8	917.3	1184.3	1384.6	1386.9
110°	188.1	214.2	240.4	246.9	412.8	633.8	744.4	893.7	1192.1	1416.0	1425.8

TEST NUMBER: P936804

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	209.0	233.9	258.7	264.9	412.8	610.1	708.6	861.3	1166.8	1395.9	1411.0
115°	240.6	263.5	286.4	292.1	416.7	582.7	665.7	812.9	1107.1	1327.8	1348.7
117.5°	271.6	292.4	313.2	318.5	424.4	565.6	636.1	769.0	1034.6	1233.8	1256.9
120°	289.7	309.3	329.0	333.9	430.7	559.8	624.4	745.7	988.3	1170.4	1192.8
122.5°	307.4	327.2	347.0	351.9	439.7	556.8	615.3	724.6	943.2	1107.0	1129.2
125°	334.6	352.6	370.6	375.1	451.9	554.3	605.5	698.3	883.9	1023.2	1043.6
127.5°	356.7	374.8	393.0	397.6	464.1	552.8	597.2	676.9	836.3	955.9	973.0
130°	368.4	388.0	407.7	412.6	473.0	553.7	594.0	665.0	806.9	913.3	929.2
132.5°	380.7	400.2	419.9	424.8	480.3	554.3	591.3	654.8	781.9	877.1	891.3
135°	398.8	416.7	434.4	438.9	488.1	553.7	586.6	639.8	746.1	825.9	838.2
137.5°	417.3	435.0	452.7	457.1	499.9	557.1	585.8	630.8	720.7	788.2	798.2
140°	432.6	448.9	465.2	469.3	507.2	557.7	583.0	621.9	699.5	757.8	767.2
142.5°	444.5	459.5	474.5	478.3	513.2	559.7	583.0	617.1	685.4	736.6	744.7
145°	462.6	475.7	488.9	492.1	521.1	559.8	579.1	607.0	662.9	704.7	710.8
147.5°	480.7	493.4	506.2	509.4	532.6	563.6	579.1	601.1	644.9	677.9	682.9
150°	492.5	504.0	515.6	518.5	538.7	565.6	579.1	597.6	634.8	662.6	666.7
152.5°	504.7	513.5	522.2	524.4	542.6	567.0	579.1	595.0	626.6	650.4	653.5
155°	522.8	529.3	535.8	537.4	551.3	569.8	579.1	591.7	616.8	635.7	637.8
157.5°	536.1	542.4	548.7	550.4	559.9	572.7	579.1	588.9	608.4	623.1	624.6
160°	545.2	550.2	555.0	556.3	563.9	574.1	579.1	587.5	604.2	616.8	617.7
162.5°	554.3	558.0	561.6	562.6	568.1	575.5	579.1	586.2	600.4	611.0	611.8
165°	564.1	567.5	570.7	571.6	574.1	577.4	579.1	584.2	594.3	601.9	602.8
167.5°	573.2	574.7	576.3	576.7	578.8	581.6	583.0	586.4	593.1	598.0	598.4
170°	579.1	580.6	582.3	582.6	582.7	582.9	583.0	586.4	593.1	598.0	598.0
172.5°	582.3	582.6	582.9	583.0	583.0	583.0	583.0	585.7	591.0	594.9	594.6
175°	586.6	586.6	586.6	586.6	585.4	583.8	583.0	584.7	588.0	590.5	590.5
177.5°	586.6	586.6	586.6	586.6	585.6	584.4	583.8	585.1	587.7	589.7	589.3
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P936804

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	594.0	594.0
2.5°	634.1	630.3
5°	815.6	819.4
7.5°	1098.3	1096.4
10°	1365.7	1382.9
12.5°	1560.6	1564.4
15°	1679.0	1686.6
17.5°	1724.8	1726.7
20°	1726.7	1722.9
22.5°	1705.7	1701.9
25°	1680.9	1679.0
27.5°	1658.0	1659.9
30°	1648.4	1654.2
32.5°	1648.4	1658.0
35°	1652.2	1661.8
37.5°	1650.3	1661.8
40°	1642.7	1656.1
42.5°	1621.7	1631.2
45°	1589.2	1600.7
47.5°	1547.2	1554.8
50°	1493.7	1501.4
52.5°	1426.9	1428.8
55°	1346.6	1354.3
57.5°	1260.7	1262.6
60°	1165.2	1170.9
62.5°	1063.9	1063.9
65°	956.9	960.7
67.5°	846.1	855.7
70°	733.4	735.4
72.5°	622.7	622.7
75°	508.1	510.0
77.5°	399.2	399.2
80°	296.0	298.0
82.5°	204.4	208.2
85°	128.0	128.0
87.5°	59.2	53.5
90°	15.0	15.0
92.5°	59.9	48.0
95°	208.9	172.9
97.5°	500.4	431.9
100°	721.0	639.3
102.5°	938.0	868.0
105°	1214.7	1177.0
107.5°	1395.9	1405.0
110°	1465.0	1504.2

TEST NUMBER: P936804

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1471.2	1531.3
115°	1432.1	1515.6
117.5°	1349.5	1442.0
120°	1282.8	1372.7
122.5°	1217.9	1306.6
125°	1125.3	1207.0
127.5°	1042.0	1111.0
130°	992.9	1056.6
132.5°	948.4	1005.4
135°	887.4	936.6
137.5°	838.5	878.7
140°	804.8	842.4
142.5°	777.0	809.4
145°	735.4	759.8
147.5°	703.3	723.6
150°	683.1	699.5
152.5°	665.9	678.3
155°	646.1	654.3
157.5°	630.4	636.1
160°	621.0	624.4
162.5°	614.9	618.1
165°	606.0	609.4
167.5°	599.7	601.2
170°	598.0	598.0
172.5°	593.3	592.1
175°	590.5	590.5
177.5°	588.0	586.6
180°	586.6	586.6

(END OF REPORT)