

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937101

Luminaire Tested: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937101
REPORT IS A COMBINATION OF REPORTS P933493 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13206.7 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 103.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937101

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P937101

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1848	1848	1848
5°	1807	2137	2485
10°	1639	3116	4119
15°	1394	4072	4974
20°	1135	4720	5069
25°	947	4940	4966
30°	799	4973	4957
35°	707	4891	5085
40°	617	4786	5217
45°	558	4708	5238
50°	513	4639	5151
55°	492	4537	4923
60°	504	4340	4562
65°	526	4039	4067
70°	561	3525	3436
75°	624	2876	2681
80°	687	1997	1807
85°	622	1062	924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5238 cd/sqm

TEST NUMBER: P937101

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	0.6
10°-20°	342.6	2.6
20°-30°	599.3	4.5
30°-40°	771.5	5.8
40°-50°	861.7	6.5
50°-60°	825.3	6.2
60°-70°	654.1	5.0
70°-80°	384.6	2.9
80°-90°	111.9	0.8
90°-100°	645.1	4.9
100°-110°	1695.9	12.8
110°-120°	1758.4	13.3
120°-130°	1410.5	10.7
130°-140°	1106.7	8.4
140°-150°	849.4	6.4
150°-160°	611.7	4.6
160°-170°	374.3	2.8
170°-180°	126.5	1.0
0°-30°	1019.2	7.7
0°-40°	1790.7	13.6
0°-60°	3477.7	26.3
0°-90°	4628.2	35.0
90°-120°	4099.3	31.0
90°-150°	7466.0	56.5
90°-180°	8578.0	65.0
0°-180°	13206.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	582	624	703	796	824	54
15°	436	805	1357	1645	1697	121
25°	279	913	1616	1687	1689	128
35°	188	872	1522	1608	1672	118
45°	129	696	1345	1541	1610	100
55°	92	442	1141	1326	1362	84
65°	73	234	848	953	967	72
75°	54	144	465	511	513	56
85°	19	44	115	127	129	20
90°	9	25	68	34	34	9
95°	85	334	1111	573	390	95
105°	306	463	1875	2846	2656	324
115°	543	659	1502	2996	3419	536
125°	755	846	1366	2308	2723	670
135°	900	990	1323	1863	2113	696
145°	1044	1110	1306	1590	1714	654
155°	1179	1212	1306	1434	1476	542
165°	1273	1290	1306	1358	1375	359
175°	1323	1323	1315	1332	1332	126
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P937101

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6
2.5°	597.6	597.6	601.5	603.4	607.2	609.1	613.0	616.8	628.4	630.3	634.1
5°	582.3	589.9	614.9	624.5	651.4	687.9	703.3	728.3	780.1	795.5	805.2
7.5°	559.2	576.4	637.9	653.3	720.6	816.7	857.0	910.9	993.5	1033.8	1066.4
10°	522.7	559.2	668.7	705.3	814.7	960.8	1035.7	1110.7	1235.6	1291.4	1312.5
12.5°	482.3	541.9	701.4	751.3	908.9	1122.2	1212.6	1295.2	1437.4	1512.3	1523.8
15°	436.2	516.9	732.1	805.2	1008.9	1256.7	1356.7	1458.5	1591.1	1644.9	1658.4
17.5°	395.8	497.7	760.9	837.8	1085.7	1377.8	1479.6	1564.2	1671.8	1708.3	1717.9
20°	345.9	467.0	780.1	880.1	1166.4	1466.2	1564.2	1629.5	1702.6	1725.6	1729.4
22.5°	309.4	434.2	791.7	895.5	1220.2	1520.0	1602.6	1654.5	1704.5	1712.1	1714.0
25°	278.7	397.8	789.8	912.8	1266.3	1552.6	1616.1	1654.5	1683.3	1687.2	1687.2
27.5°	249.8	357.5	782.0	916.6	1300.9	1560.4	1610.3	1637.2	1650.6	1658.4	1658.4
30°	224.8	319.0	762.9	908.9	1316.3	1552.6	1593.0	1606.5	1619.9	1631.4	1637.2
32.5°	205.6	282.5	734.0	893.5	1318.2	1533.4	1562.3	1569.9	1589.1	1616.1	1625.7
35°	188.3	246.0	701.4	872.4	1306.7	1502.7	1521.9	1529.6	1568.0	1608.4	1621.8
37.5°	171.0	219.1	659.1	835.9	1289.3	1466.2	1479.6	1493.0	1552.6	1600.7	1616.1
40°	153.8	196.0	609.1	795.5	1262.5	1422.0	1433.6	1454.7	1533.4	1589.1	1604.5
42.5°	140.3	176.8	555.3	753.3	1227.9	1372.0	1389.3	1420.1	1510.3	1569.9	1587.2
45°	128.7	157.6	497.7	695.6	1183.7	1320.1	1345.1	1387.4	1483.5	1541.1	1556.5
47.5°	117.2	144.1	438.2	636.0	1135.7	1268.2	1300.9	1348.9	1446.9	1502.7	1516.2
50°	107.6	130.6	378.6	572.6	1083.7	1212.6	1251.0	1300.9	1400.9	1452.7	1470.0
52.5°	99.9	119.2	322.8	509.2	1024.2	1154.9	1199.1	1251.0	1345.1	1395.1	1406.6
55°	92.3	109.5	274.8	442.0	962.7	1093.4	1141.4	1191.4	1283.6	1325.9	1333.6
57.5°	88.4	101.8	234.5	378.6	897.4	1024.2	1078.0	1124.1	1210.6	1243.3	1251.0
60°	82.6	96.1	203.7	324.8	826.3	958.9	1005.0	1051.1	1124.1	1151.1	1156.8
62.5°	76.9	92.3	180.6	272.8	753.3	882.0	928.2	970.4	1031.9	1051.1	1058.8
65°	73.1	88.4	163.3	234.5	678.3	801.3	847.5	883.9	933.9	953.1	956.9
67.5°	69.1	84.5	149.8	201.8	603.4	720.6	755.2	789.8	828.2	847.5	849.4
70°	63.4	80.7	138.4	178.7	526.5	628.4	657.2	693.7	724.5	734.0	739.8
72.5°	59.6	75.0	130.6	161.4	447.7	540.0	566.9	588.0	614.9	624.5	624.5
75°	53.8	67.2	123.0	144.1	367.0	442.0	465.0	486.2	507.3	511.1	505.4
77.5°	48.0	59.6	105.7	121.1	286.3	349.7	368.9	380.5	397.8	401.6	403.5
80°	40.4	51.9	82.6	94.2	207.5	257.5	270.9	280.6	296.0	296.0	299.8
82.5°	30.8	40.4	59.6	67.2	140.3	176.8	188.3	194.1	203.7	203.7	203.7
85°	19.2	25.0	38.4	44.2	84.5	107.6	115.3	117.2	124.9	126.8	126.8
87.5°	9.6	13.5	25.0	26.9	44.2	55.8	55.8	59.6	59.6	57.7	55.8
90°	8.9	15.9	23.0	24.8	39.1	58.1	67.5	60.0	45.0	33.7	33.7
92.5°	35.5	95.9	156.3	171.4	240.9	333.7	380.1	333.1	239.2	168.7	162.1
95°	85.3	195.8	306.4	334.0	593.0	938.4	1111.0	991.5	752.3	572.8	552.5
97.5°	147.5	245.0	342.5	366.8	798.8	1374.6	1662.6	1586.9	1435.7	1322.4	1283.7
100°	195.4	283.8	372.3	394.3	873.6	1512.6	1832.2	1837.7	1848.8	1857.1	1811.0
102.5°	236.3	318.8	401.2	421.8	907.9	1556.1	1880.2	1976.5	2169.1	2313.6	2274.1
105°	305.5	375.4	445.2	462.7	933.4	1561.0	1874.9	2090.8	2522.6	2846.5	2825.3
107.5°	376.6	441.7	506.8	523.1	938.2	1491.6	1768.3	2069.5	2671.8	3123.5	3128.7
110°	424.5	483.3	542.2	556.9	931.0	1430.0	1679.5	2016.2	2689.6	3194.6	3216.6

TEST NUMBER: P937101

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	471.6	527.6	583.7	597.7	931.4	1376.3	1598.7	1943.2	2632.5	3149.3	3183.2
115°	542.6	594.3	646.1	658.9	939.9	1314.6	1501.8	1833.8	2497.7	2995.6	3042.7
117.5°	612.8	659.8	706.7	718.4	957.4	1275.9	1435.2	1734.8	2333.9	2783.3	2835.6
120°	653.7	697.9	742.0	753.1	971.6	1262.9	1408.5	1682.2	2229.7	2640.4	2691.1
122.5°	693.6	738.2	782.8	794.0	992.1	1256.1	1388.1	1634.6	2127.6	2497.4	2547.5
125°	754.9	795.6	836.3	846.4	1019.6	1250.5	1365.9	1575.4	1994.1	2308.2	2354.4
127.5°	804.7	845.7	886.8	897.0	1047.2	1247.2	1347.3	1527.1	1886.7	2156.4	2195.3
130°	831.3	875.5	919.7	930.7	1067.2	1249.1	1340.2	1500.2	1820.3	2060.4	2096.3
132.5°	858.8	903.0	947.2	958.2	1083.4	1250.5	1333.9	1477.2	1763.8	1978.8	2010.9
135°	899.7	939.9	980.2	990.2	1101.3	1249.3	1323.3	1443.3	1683.3	1863.3	1891.0
137.5°	941.4	981.3	1021.2	1031.1	1128.0	1257.0	1321.5	1423.0	1625.9	1778.0	1800.7
140°	976.0	1012.7	1049.4	1058.6	1144.2	1258.3	1315.3	1403.0	1578.2	1709.6	1730.8
142.5°	1002.7	1036.7	1070.6	1079.1	1157.8	1262.8	1315.3	1392.3	1546.2	1661.7	1679.9
145°	1043.5	1073.1	1102.7	1110.2	1175.6	1262.8	1306.4	1369.4	1495.3	1589.8	1603.6
147.5°	1084.4	1113.2	1142.1	1149.2	1201.7	1271.5	1306.4	1356.0	1455.0	1529.3	1540.8
150°	1111.0	1137.1	1163.2	1169.7	1215.2	1276.1	1306.4	1348.3	1431.9	1494.7	1503.9
152.5°	1138.6	1158.3	1178.0	1183.0	1224.1	1279.0	1306.4	1342.2	1413.6	1467.2	1474.1
155°	1179.4	1194.0	1208.6	1212.3	1243.7	1285.5	1306.4	1334.9	1391.7	1434.3	1439.0
157.5°	1209.6	1223.8	1238.1	1241.6	1263.2	1292.0	1306.4	1328.5	1372.7	1405.9	1409.1
160°	1230.0	1241.1	1252.2	1255.0	1272.2	1295.0	1306.4	1325.3	1363.3	1391.7	1393.6
162.5°	1250.5	1258.8	1267.0	1269.1	1281.5	1298.1	1306.4	1322.4	1354.4	1378.4	1380.2
165°	1272.7	1280.2	1287.6	1289.5	1295.2	1302.7	1306.4	1317.9	1340.7	1357.9	1359.8
167.5°	1293.1	1296.6	1300.2	1301.1	1305.9	1312.2	1315.3	1322.8	1337.8	1349.0	1349.8
170°	1306.4	1310.0	1313.6	1314.5	1314.7	1315.1	1315.3	1322.8	1337.8	1349.0	1349.0
172.5°	1313.5	1314.3	1315.1	1315.3	1315.3	1315.3	1315.3	1321.2	1333.1	1342.0	1341.3
175°	1323.3	1323.3	1323.3	1323.3	1320.7	1317.1	1315.3	1319.0	1326.6	1332.2	1332.2
177.5°	1323.3	1323.3	1323.3	1323.3	1321.2	1318.5	1317.1	1320.1	1326.0	1330.4	1329.6
180°	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3

TEST NUMBER: P937101

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	597.6	597.6
2.5°	637.9	634.1
5°	820.5	824.4
7.5°	1104.9	1103.0
10°	1374.0	1391.2
12.5°	1569.9	1573.7
15°	1689.1	1696.7
17.5°	1735.2	1737.1
20°	1737.1	1733.3
22.5°	1715.9	1712.1
25°	1691.0	1689.1
27.5°	1667.9	1669.9
30°	1658.4	1664.1
32.5°	1658.4	1667.9
35°	1662.2	1671.8
37.5°	1660.3	1671.8
40°	1652.5	1666.0
42.5°	1631.4	1641.1
45°	1598.8	1610.3
47.5°	1556.5	1564.2
50°	1502.7	1510.3
52.5°	1435.5	1437.4
55°	1354.8	1362.4
57.5°	1268.2	1270.1
60°	1172.2	1177.9
62.5°	1070.4	1070.4
65°	962.7	966.6
67.5°	851.3	860.8
70°	737.9	739.8
72.5°	626.5	626.5
75°	511.1	513.0
77.5°	401.6	401.6
80°	297.9	299.8
82.5°	205.6	209.4
85°	128.7	128.7
87.5°	59.6	53.8
90°	33.7	33.7
92.5°	135.2	108.4
95°	471.2	389.9
97.5°	1129.0	974.3
100°	1626.7	1442.3
102.5°	2116.2	1958.3
105°	2740.4	2655.5
107.5°	3149.2	3169.7
110°	3305.1	3393.5

TEST NUMBER: P937101

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3319.0	3454.8
115°	3231.0	3419.3
117.5°	3044.3	3253.2
120°	2894.0	3096.9
122.5°	2747.5	2947.7
125°	2538.7	2723.0
127.5°	2350.8	2506.3
130°	2240.0	2383.8
132.5°	2139.6	2268.3
135°	2002.0	2112.8
137.5°	1891.5	1982.3
140°	1815.7	1900.5
142.5°	1753.0	1826.0
145°	1658.8	1714.0
147.5°	1586.5	1632.4
150°	1541.1	1578.2
152.5°	1502.2	1530.2
155°	1457.5	1476.0
157.5°	1422.2	1435.2
160°	1401.1	1408.5
162.5°	1387.2	1394.4
165°	1367.3	1374.8
167.5°	1353.0	1356.2
170°	1349.0	1349.0
172.5°	1338.5	1335.8
175°	1332.2	1332.2
177.5°	1326.5	1323.3
180°	1323.3	1323.3

(END OF REPORT)