

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936697

Luminaire Tested: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936697
REPORT IS A COMBINATION OF REPORTS P933461 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10481.6 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 85.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936697

CATALOG NUMBER: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P936697

CATALOG NUMBER: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	43	42
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	39	37	35
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16
8	51	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1876	1876	1876
5°	1833	2168	2521
10°	1663	3161	4179
15°	1414	4132	5047
20°	1152	4789	5143
25°	961	5012	5039
30°	811	5046	5029
35°	717	4963	5159
40°	626	4856	5294
45°	567	4777	5315
50°	520	4707	5227
55°	499	4603	4995
60°	511	4404	4629
65°	533	4099	4126
70°	568	3577	3486
75°	633	2918	2720
80°	697	2027	1833
85°	632	1077	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5315 cd/sqm

TEST NUMBER: P936697

CATALOG NUMBER: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.4	0.7
10°-20°	347.6	3.3
20°-30°	608.1	5.8
30°-40°	782.8	7.5
40°-50°	874.3	8.3
50°-60°	837.4	8.0
60°-70°	663.6	6.3
70°-80°	390.2	3.7
80°-90°	111.8	1.1
90°-100°	435.1	4.2
100°-110°	1144.1	10.9
110°-120°	1186.3	11.3
120°-130°	951.5	9.1
130°-140°	746.6	7.1
140°-150°	573.1	5.5
150°-160°	412.7	3.9
160°-170°	252.5	2.4
170°-180°	85.3	0.8
0°-30°	1034.2	9.9
0°-40°	1816.9	17.3
0°-60°	3528.6	33.7
0°-90°	4694.3	44.8
90°-120°	2765.5	26.4
90°-150°	5036.8	48.1
90°-180°	5787.0	55.2
0°-180°	10481.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	606	606	606	606	606	
5°	591	634	714	807	836	55
15°	443	817	1377	1669	1722	123
25°	283	926	1640	1712	1714	130
35°	191	885	1544	1632	1696	119
45°	131	706	1365	1564	1634	101
55°	94	448	1158	1345	1382	85
65°	74	238	860	967	981	73
75°	55	146	472	519	520	57
85°	20	45	117	129	131	21
90°	6	17	46	23	23	6
95°	58	225	750	386	263	64
105°	206	312	1265	1920	1792	219
115°	366	445	1013	2021	2307	362
125°	509	571	922	1557	1837	452
135°	607	668	893	1257	1425	470
145°	704	749	881	1072	1156	441
155°	796	818	881	968	996	366
165°	859	870	881	916	928	242
175°	893	893	887	899	899	85
180°	893	893	893	893	893	

TEST NUMBER: P936697

CATALOG NUMBER: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4	606.4
2.5°	606.4	606.4	610.3	612.2	616.1	618.0	622.0	625.9	637.6	639.5	643.4
5°	590.8	598.6	623.9	633.6	661.0	698.0	713.6	739.0	791.6	807.2	817.0
7.5°	567.3	584.9	647.3	662.9	731.2	828.7	869.6	924.2	1008.1	1048.9	1082.1
10°	530.3	567.3	678.5	715.6	826.7	974.9	1050.9	1126.9	1253.7	1310.3	1331.7
12.5°	489.3	549.8	711.6	762.3	922.2	1138.7	1230.3	1314.2	1458.4	1534.5	1546.1
15°	442.6	524.5	742.8	817.0	1023.7	1275.1	1376.6	1479.9	1614.5	1669.0	1682.7
17.5°	401.7	504.9	772.1	850.1	1101.7	1398.0	1501.3	1587.1	1696.3	1733.3	1743.1
20°	351.0	473.8	791.6	893.0	1183.5	1487.7	1587.1	1653.4	1727.5	1750.9	1754.8
22.5°	314.0	440.6	803.3	908.6	1238.1	1542.3	1626.1	1678.8	1729.5	1737.2	1739.2
25°	282.8	403.6	801.4	926.2	1284.9	1575.4	1639.7	1678.8	1708.0	1711.9	1711.9
27.5°	253.5	362.7	793.5	930.0	1320.0	1583.2	1633.9	1661.2	1674.8	1682.7	1682.7
30°	228.1	323.6	774.0	922.2	1335.6	1575.4	1616.4	1630.1	1643.6	1655.3	1661.2
32.5°	208.6	286.6	744.8	906.6	1337.5	1555.9	1585.2	1592.9	1612.4	1639.7	1649.5
35°	191.1	249.6	711.6	885.2	1325.9	1524.7	1544.2	1552.0	1591.0	1632.0	1645.6
37.5°	173.5	222.3	668.8	848.2	1308.2	1487.7	1501.3	1514.9	1575.4	1624.1	1639.7
40°	156.0	198.8	618.0	807.2	1281.0	1442.8	1454.6	1476.0	1555.9	1612.4	1628.0
42.5°	142.3	179.4	563.5	764.3	1245.9	1392.2	1409.7	1440.9	1532.5	1592.9	1610.5
45°	130.6	159.9	504.9	705.8	1201.1	1339.4	1364.8	1407.8	1505.2	1563.7	1579.3
47.5°	118.9	146.2	444.6	645.4	1152.3	1286.8	1320.0	1368.7	1468.1	1524.7	1538.4
50°	109.2	132.6	384.1	581.0	1099.6	1230.3	1269.3	1320.0	1421.4	1474.0	1491.6
52.5°	101.4	120.9	327.5	516.7	1039.3	1171.8	1216.7	1269.3	1364.8	1415.5	1427.2
55°	93.6	111.1	278.8	448.5	976.8	1109.4	1158.1	1208.8	1302.4	1345.4	1353.1
57.5°	89.7	103.3	237.9	384.1	910.6	1039.3	1093.8	1140.6	1228.3	1261.5	1269.3
60°	83.8	97.5	206.7	329.6	838.4	973.0	1019.8	1066.5	1140.6	1167.9	1173.7
62.5°	78.0	93.6	183.2	276.8	764.3	895.0	941.8	984.6	1047.0	1066.5	1074.3
65°	74.1	89.7	165.7	237.9	688.3	813.1	859.9	896.9	947.6	967.1	970.9
67.5°	70.2	85.8	152.0	204.7	612.2	731.2	766.3	801.4	840.3	859.9	861.8
70°	64.3	81.9	140.4	181.3	534.2	637.6	666.9	703.9	735.1	744.8	750.7
72.5°	60.5	76.1	132.6	163.8	454.3	547.9	575.2	596.6	623.9	633.6	633.6
75°	54.6	68.2	124.8	146.2	372.4	448.5	471.8	493.3	514.7	518.6	512.8
77.5°	48.7	60.5	107.3	122.9	290.5	354.8	374.3	386.0	403.6	407.5	409.4
80°	41.0	52.6	83.8	95.5	210.6	261.2	274.9	284.7	300.3	300.3	304.2
82.5°	31.2	41.0	60.5	68.2	142.3	179.4	191.1	196.9	206.7	206.7	206.7
85°	19.5	25.4	39.0	44.9	85.8	109.2	117.0	118.9	126.7	128.7	128.7
87.5°	9.8	13.7	25.4	27.3	44.9	56.6	56.6	60.5	60.5	58.5	56.6
90°	6.0	10.8	15.6	16.8	26.4	39.1	45.5	40.5	30.3	22.8	22.8
92.5°	23.9	64.6	105.4	115.6	162.5	225.1	256.4	224.7	161.3	113.9	109.3
95°	57.6	132.1	206.7	225.3	400.0	633.0	749.5	668.8	507.5	386.4	372.7
97.5°	99.4	165.2	231.0	247.5	538.9	927.3	1121.6	1070.6	968.6	892.2	866.1
100°	131.8	191.5	251.1	266.0	589.3	1020.5	1236.1	1239.7	1247.2	1252.8	1221.7
102.5°	159.4	215.0	270.6	284.6	612.5	1049.8	1268.4	1333.3	1463.3	1560.8	1534.1
105°	206.1	253.2	300.3	312.1	629.7	1053.1	1264.8	1410.5	1701.8	1920.3	1905.9
107.5°	254.1	298.0	342.0	352.9	633.0	1006.3	1192.9	1396.1	1802.5	2107.3	2110.8
110°	286.4	326.1	365.8	375.7	628.1	964.7	1133.1	1360.2	1814.5	2155.2	2170.1

TEST NUMBER: P936697

CATALOG NUMBER: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	318.1	355.9	393.7	403.2	628.3	928.4	1078.5	1311.0	1775.9	2124.6	2147.5
115°	366.1	401.0	435.9	444.6	634.1	886.8	1013.2	1237.1	1685.0	2020.9	2052.7
117.5°	413.4	445.1	476.7	484.7	645.8	860.8	968.2	1170.4	1574.5	1877.7	1912.9
120°	441.0	470.8	500.6	508.0	655.4	852.0	950.3	1135.0	1504.3	1781.3	1815.5
122.5°	467.9	498.1	528.1	535.7	669.3	847.4	936.4	1102.7	1435.4	1684.8	1718.5
125°	509.3	536.7	564.2	571.0	687.9	843.6	921.5	1062.8	1345.3	1557.2	1588.3
127.5°	542.8	570.5	598.3	605.1	706.4	841.4	908.9	1030.2	1272.8	1454.8	1481.0
130°	560.9	590.7	620.5	627.9	720.0	842.7	904.2	1012.1	1228.1	1390.0	1414.3
132.5°	579.4	609.2	639.1	646.5	731.0	843.6	899.9	996.6	1189.9	1334.9	1356.6
135°	607.0	634.1	661.2	668.0	742.9	842.8	892.7	973.7	1135.7	1257.1	1275.8
137.5°	635.1	662.0	689.0	695.6	761.0	848.1	891.6	960.0	1096.9	1199.5	1214.8
140°	658.4	683.2	708.0	714.2	771.9	848.8	887.3	946.4	1064.7	1153.4	1167.7
142.5°	676.5	699.3	722.3	728.0	781.1	851.9	887.3	939.3	1043.1	1121.0	1133.3
145°	704.0	723.9	743.9	748.9	793.1	851.9	881.4	923.8	1008.8	1072.5	1081.8
147.5°	731.6	751.0	770.5	775.3	810.7	857.9	881.4	914.8	981.7	1031.8	1039.5
150°	749.5	767.1	784.7	789.1	819.9	860.9	881.4	909.6	966.0	1008.3	1014.6
152.5°	768.1	781.4	794.8	798.1	825.9	862.9	881.4	905.5	953.7	989.8	994.6
155°	795.6	805.5	815.4	817.8	839.1	867.3	881.4	900.6	938.9	967.6	970.7
157.5°	816.1	825.7	835.2	837.6	852.2	871.7	881.4	896.3	926.1	948.5	950.7
160°	829.9	837.3	844.8	846.6	858.2	873.7	881.4	894.2	919.7	938.9	940.1
162.5°	843.6	849.2	854.9	856.2	864.6	875.8	881.4	892.2	913.7	929.9	931.0
165°	858.6	863.7	868.7	870.0	873.7	878.9	881.4	889.2	904.6	916.1	917.4
167.5°	872.4	874.7	877.1	877.7	880.9	885.2	887.3	892.4	902.5	910.1	910.7
170°	881.4	883.7	886.2	886.7	886.9	887.2	887.3	892.4	902.5	910.1	910.1
172.5°	886.2	886.6	887.2	887.3	887.3	887.3	887.3	891.3	899.3	905.3	904.9
175°	892.7	892.7	892.7	892.7	890.9	888.5	887.3	889.8	895.0	898.7	898.7
177.5°	892.7	892.7	892.7	892.7	891.4	889.5	888.6	890.6	894.6	897.6	897.0
180°	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7

TEST NUMBER: P936697

CATALOG NUMBER: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	606.4	606.4
2.5°	647.3	643.4
5°	832.6	836.4
7.5°	1121.1	1119.2
10°	1394.1	1411.6
12.5°	1592.9	1596.8
15°	1713.9	1721.6
17.5°	1760.7	1762.6
20°	1762.6	1758.7
22.5°	1741.1	1737.2
25°	1715.8	1713.9
27.5°	1692.4	1694.4
30°	1682.7	1688.5
32.5°	1682.7	1692.4
35°	1686.5	1696.3
37.5°	1684.6	1696.3
40°	1676.8	1690.4
42.5°	1655.3	1665.1
45°	1622.2	1633.9
47.5°	1579.3	1587.1
50°	1524.7	1532.5
52.5°	1456.5	1458.4
55°	1374.6	1382.4
57.5°	1286.8	1288.8
60°	1189.4	1195.2
62.5°	1086.1	1086.1
65°	976.8	980.7
67.5°	863.8	873.5
70°	748.7	750.7
72.5°	635.7	635.7
75°	518.6	520.5
77.5°	407.5	407.5
80°	302.2	304.2
82.5°	208.6	212.5
85°	130.6	130.6
87.5°	60.5	54.6
90°	22.8	22.8
92.5°	91.2	73.1
95°	317.8	263.0
97.5°	761.6	657.3
100°	1097.4	973.1
102.5°	1427.6	1321.1
105°	1848.8	1791.5
107.5°	2124.5	2138.4
110°	2229.7	2289.4

TEST NUMBER: P936697

CATALOG NUMBER: SQ4-FB-050U-050D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2239.2	2330.7
115°	2179.8	2306.8
117.5°	2053.8	2194.7
120°	1952.4	2089.3
122.5°	1853.6	1988.6
125°	1712.6	1837.0
127.5°	1585.9	1690.8
130°	1511.3	1608.2
132.5°	1443.4	1530.2
135°	1350.6	1425.4
137.5°	1276.1	1337.3
140°	1224.9	1282.2
142.5°	1182.7	1231.9
145°	1119.1	1156.4
147.5°	1070.4	1101.3
150°	1039.6	1064.7
152.5°	1013.5	1032.4
155°	983.3	995.8
157.5°	959.4	968.2
160°	945.3	950.3
162.5°	935.9	940.7
165°	922.5	927.5
167.5°	912.8	914.9
170°	910.1	910.1
172.5°	903.0	901.2
175°	898.7	898.7
177.5°	894.9	892.7
180°	892.7	892.7

(END OF REPORT)