

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937402

Luminaire Tested: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937402
REPORT IS A COMBINATION OF REPORTS P933504 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6749.0 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937402

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P937402

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63
1	99	94	90	86	92	88	84	81	76	73	71	65	63	61	55	53	52
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43
3	81	71	63	57	75	66	59	54	57	52	47	49	45	41	41	38	36
4	74	62	54	48	68	58	51	45	50	45	40	43	39	35	36	33	30
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	33	29	26
6	62	49	41	35	57	46	38	33	40	34	29	34	29	26	29	25	22
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17
9	49	36	28	23	46	34	27	22	30	24	20	26	21	17	22	18	15
10	46	33	26	21	43	31	24	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4663	4663	4663
5°	4551	5385	6268
10°	4123	7845	10392
15°	3500	10242	12548
20°	2847	11860	12788
25°	2372	12403	12529
30°	1997	12471	12506
35°	1762	12254	12828
40°	1534	11975	13162
45°	1387	11767	13214
50°	1269	11578	12995
55°	1211	11306	12419
60°	1236	10796	11510
65°	1280	10024	10260
70°	1353	8726	8668
75°	1486	7096	6765
80°	1587	4905	4558
85°	1333	2586	2333

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 13214 cd/sqm

TEST NUMBER: P937402

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.0
10°-20°	288.1	4.3
20°-30°	504.0	7.5
30°-40°	648.8	9.6
40°-50°	724.6	10.7
50°-60°	694.0	10.3
60°-70°	550.0	8.1
70°-80°	323.4	4.8
80°-90°	91.5	1.4
90°-100°	215.0	3.2
100°-110°	565.3	8.4
110°-120°	586.1	8.7
120°-130°	470.2	7.0
130°-140°	368.9	5.5
140°-150°	283.1	4.2
150°-160°	203.9	3.0
160°-170°	124.8	1.8
170°-180°	42.2	0.6
0°-30°	857.1	12.7
0°-40°	1505.8	22.3
0°-60°	2924.5	43.3
0°-90°	3889.5	57.6
90°-120°	1366.5	20.2
90°-150°	2488.7	36.9
90°-180°	2860.0	42.4
0°-180°	6749.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	490	525	591	669	693	45
15°	367	677	1141	1383	1427	102
25°	234	768	1359	1419	1420	108
35°	158	734	1280	1353	1406	99
45°	108	585	1131	1296	1354	84
55°	78	372	960	1115	1146	71
65°	61	197	713	802	813	61
75°	45	121	391	430	432	47
85°	16	37	97	107	108	17
90°	3	8	22	11	11	4
95°	28	111	370	191	130	32
105°	102	154	625	949	885	108
115°	181	220	501	998	1140	179
125°	252	282	455	769	908	223
135°	300	330	441	621	704	232
145°	348	370	436	530	571	218
155°	393	404	436	478	492	181
165°	424	430	436	453	458	120
175°	441	441	438	444	444	42
180°	441	441	441	441	441	

TEST NUMBER: P937402

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	502.5	502.5	502.5	502.5	502.5	502.5	502.5	502.5	502.5	502.5	502.5
2.5°	502.5	502.5	505.8	507.4	510.6	512.3	515.5	518.8	528.4	530.0	533.3
5°	489.6	496.1	517.1	525.2	547.8	578.5	591.4	612.4	656.1	669.0	677.1
7.5°	470.2	484.8	536.5	549.4	605.9	686.7	720.7	766.0	835.4	869.3	896.8
10°	439.5	470.2	562.3	593.1	685.1	807.9	871.0	934.0	1039.0	1085.9	1103.7
12.5°	405.6	455.7	589.8	631.8	764.4	943.7	1019.7	1089.2	1208.7	1271.8	1281.4
15°	366.8	434.7	615.7	677.1	848.3	1056.8	1140.8	1226.5	1338.1	1383.2	1394.6
17.5°	332.9	418.6	639.9	704.6	913.0	1158.6	1244.3	1315.4	1405.9	1436.6	1444.6
20°	290.9	392.7	656.1	740.1	980.9	1233.0	1315.4	1370.3	1431.7	1451.1	1454.4
22.5°	260.1	365.2	665.7	753.0	1026.1	1278.2	1347.7	1391.3	1433.4	1439.9	1441.4
25°	234.4	334.5	664.2	767.5	1064.9	1305.7	1359.1	1391.3	1415.6	1418.8	1418.8
27.5°	210.1	300.5	657.7	770.8	1094.0	1312.2	1354.2	1376.8	1388.1	1394.6	1394.6
30°	189.1	268.3	641.6	764.4	1106.9	1305.7	1339.6	1350.9	1362.2	1372.0	1376.8
32.5°	173.0	237.5	617.3	751.4	1108.6	1289.5	1313.8	1320.2	1336.4	1359.1	1367.1
35°	158.3	206.9	589.8	733.6	1098.8	1263.7	1279.8	1286.3	1318.6	1352.6	1363.8
37.5°	143.8	184.2	554.3	703.0	1084.3	1233.0	1244.3	1255.6	1305.7	1346.1	1359.1
40°	129.3	164.8	512.3	669.0	1061.7	1195.8	1205.5	1223.3	1289.5	1336.4	1349.3
42.5°	117.9	148.7	467.0	633.5	1032.5	1153.8	1168.3	1194.2	1270.1	1320.2	1334.8
45°	108.3	132.6	418.6	584.9	995.4	1110.2	1131.2	1166.7	1247.5	1296.0	1308.9
47.5°	98.6	121.2	368.4	534.9	955.0	1066.5	1094.0	1134.4	1216.8	1263.7	1275.0
50°	90.5	109.9	318.3	481.5	911.4	1019.7	1052.0	1094.0	1178.0	1221.6	1236.2
52.5°	84.0	100.2	271.5	428.2	861.3	971.1	1008.4	1052.0	1131.2	1173.2	1182.9
55°	77.5	92.1	231.1	371.7	809.6	919.5	959.9	1001.9	1079.4	1115.0	1121.5
57.5°	74.3	85.7	197.1	318.3	754.6	861.3	906.6	945.4	1018.0	1045.5	1052.0
60°	69.5	80.8	171.3	273.1	694.9	806.4	845.2	883.9	945.4	968.0	972.8
62.5°	64.7	77.5	151.9	229.5	633.5	741.7	780.5	816.0	867.8	883.9	890.3
65°	61.4	74.3	137.3	197.1	570.4	673.8	712.6	743.4	785.4	801.5	804.8
67.5°	58.2	71.1	126.1	169.7	507.4	605.9	635.1	664.2	696.5	712.6	714.2
70°	53.3	67.9	116.3	150.3	442.7	528.4	552.7	583.3	609.2	617.3	622.2
72.5°	50.1	63.0	109.9	135.7	376.6	454.1	476.7	494.5	517.1	525.2	525.2
75°	45.3	56.5	103.4	121.2	308.7	371.7	391.1	408.8	426.6	429.8	425.0
77.5°	40.4	50.1	88.9	101.8	240.8	294.1	310.3	319.9	334.5	337.7	339.3
80°	33.9	43.6	69.5	79.2	174.5	216.5	227.9	235.9	248.9	248.9	252.1
82.5°	25.9	33.9	50.1	56.5	117.9	148.7	158.3	163.2	171.3	171.3	171.3
85°	16.1	21.0	32.3	37.1	71.1	90.5	96.9	98.6	105.0	106.7	106.7
87.5°	8.1	11.3	21.0	22.6	37.1	46.9	46.9	50.1	50.1	48.5	46.9
90°	3.0	5.3	7.7	8.3	13.1	19.4	22.5	20.1	15.0	11.3	11.3
92.5°	11.8	32.0	52.0	57.1	80.3	111.3	126.7	111.1	79.7	56.2	54.1
95°	28.5	65.3	102.2	111.4	197.7	312.8	370.3	330.4	250.7	190.9	184.1
97.5°	49.2	81.7	114.1	122.2	266.3	458.2	554.2	529.0	478.6	440.8	427.9
100°	65.1	94.5	124.1	131.4	291.2	504.2	610.7	612.5	616.3	619.0	603.7
102.5°	78.8	106.3	133.7	140.6	302.6	518.8	626.8	658.9	723.0	771.2	758.0
105°	101.8	125.1	148.4	154.2	311.1	520.4	625.0	697.0	840.9	948.8	941.7
107.5°	125.5	147.3	168.9	174.4	312.8	497.2	589.4	689.8	890.5	1041.1	1042.9
110°	141.5	161.1	180.8	185.7	310.4	476.6	559.8	672.0	896.5	1064.8	1072.2

TEST NUMBER: P937402

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	157.2	175.9	194.5	199.2	310.5	458.8	532.9	647.8	877.5	1049.7	1061.1
115°	180.9	198.1	215.4	219.6	313.3	438.2	500.6	611.3	832.6	998.5	1014.2
117.5°	204.3	219.9	235.6	239.5	319.2	425.3	478.4	578.3	777.9	927.8	945.2
120°	217.9	232.6	247.3	251.1	323.8	421.0	469.5	560.8	743.3	880.1	897.0
122.5°	231.2	246.1	260.9	264.6	330.6	418.7	462.7	544.8	709.2	832.5	849.2
125°	251.6	265.2	278.8	282.1	339.9	416.9	455.3	525.2	664.8	769.4	784.8
127.5°	268.3	281.9	295.6	299.0	349.1	415.8	449.1	509.1	629.0	718.8	731.8
130°	277.1	291.8	306.6	310.3	355.7	416.4	446.7	500.1	606.8	686.8	698.8
132.5°	286.3	301.0	315.7	319.4	361.2	416.9	444.6	492.4	588.0	659.6	670.3
135°	299.9	313.2	326.7	330.0	367.1	416.5	441.1	481.1	561.2	621.1	630.4
137.5°	313.8	327.1	340.4	343.7	376.0	419.1	440.5	474.3	542.0	592.7	600.2
140°	325.4	337.6	349.8	352.9	381.4	419.4	438.4	467.7	526.0	569.8	576.9
142.5°	334.2	345.5	356.8	359.7	385.9	421.0	438.4	464.1	515.4	553.9	560.0
145°	347.8	357.7	367.6	370.1	391.8	421.0	435.5	456.5	498.4	529.9	534.5
147.5°	361.5	371.0	380.7	383.1	400.5	423.8	435.5	452.0	485.0	509.8	513.6
150°	370.3	379.0	387.7	389.9	405.1	425.4	435.5	449.4	477.3	498.2	501.3
152.5°	379.5	386.1	392.7	394.3	408.1	426.3	435.5	447.4	471.2	489.1	491.3
155°	393.2	398.0	402.8	404.1	414.6	428.5	435.5	444.9	463.8	478.1	479.6
157.5°	403.2	408.0	412.8	413.9	421.1	430.7	435.5	442.8	457.5	468.6	469.7
160°	410.0	413.7	417.3	418.3	424.0	431.7	435.5	441.8	454.5	463.9	464.5
162.5°	416.9	419.6	422.4	423.1	427.2	432.7	435.5	440.8	451.4	459.5	460.0
165°	424.2	426.7	429.2	429.8	431.8	434.2	435.5	439.3	446.9	452.7	453.3
167.5°	431.0	432.1	433.4	433.7	435.3	437.4	438.4	440.9	446.0	449.7	450.0
170°	435.5	436.6	437.9	438.2	438.2	438.3	438.4	440.9	446.0	449.7	449.7
172.5°	437.9	438.2	438.3	438.4	438.4	438.4	438.4	440.4	444.4	447.3	447.1
175°	441.1	441.1	441.1	441.1	440.3	439.0	438.4	439.7	442.2	444.1	444.1
177.5°	441.1	441.1	441.1	441.1	440.4	439.5	439.0	440.0	442.0	443.5	443.2
180°	441.1	441.1	441.1	441.1	441.1	441.1	441.1	441.1	441.1	441.1	441.1

TEST NUMBER: P937402

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	502.5	502.5
2.5°	536.5	533.3
5°	690.0	693.2
7.5°	929.2	927.6
10°	1155.4	1170.0
12.5°	1320.2	1323.4
15°	1420.5	1426.9
17.5°	1459.2	1460.9
20°	1460.9	1457.6
22.5°	1443.0	1439.9
25°	1422.0	1420.5
27.5°	1402.6	1404.2
30°	1394.6	1399.5
32.5°	1394.6	1402.6
35°	1397.8	1405.9
37.5°	1396.2	1405.9
40°	1389.7	1401.0
42.5°	1372.0	1380.0
45°	1344.4	1354.2
47.5°	1308.9	1315.4
50°	1263.7	1270.1
52.5°	1207.1	1208.7
55°	1139.2	1145.7
57.5°	1066.5	1068.2
60°	985.8	990.6
62.5°	900.1	900.1
65°	809.6	812.8
67.5°	715.9	724.0
70°	620.6	622.2
72.5°	526.8	526.8
75°	429.8	431.5
77.5°	337.7	337.7
80°	250.5	252.1
82.5°	173.0	176.1
85°	108.3	108.3
87.5°	50.1	45.3
90°	11.3	11.3
92.5°	45.1	36.1
95°	157.1	130.0
97.5°	376.4	324.8
100°	542.2	480.7
102.5°	705.4	652.7
105°	913.5	885.2
107.5°	1049.7	1056.6
110°	1101.7	1131.2

TEST NUMBER: P937402

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1106.4	1151.6
115°	1077.0	1139.8
117.5°	1014.8	1084.4
120°	964.6	1032.3
122.5°	915.8	982.6
125°	846.2	907.6
127.5°	783.6	835.4
130°	746.7	794.6
132.5°	713.2	756.1
135°	667.4	704.3
137.5°	630.5	660.8
140°	605.3	633.5
142.5°	584.3	608.6
145°	552.9	571.4
147.5°	528.9	544.2
150°	513.7	526.1
152.5°	500.7	510.1
155°	485.8	492.0
157.5°	474.1	478.4
160°	467.0	469.5
162.5°	462.4	464.8
165°	455.8	458.3
167.5°	451.0	452.1
170°	449.7	449.7
172.5°	446.2	445.2
175°	444.1	444.1
177.5°	442.2	441.1
180°	441.1	441.1

(END OF REPORT)