

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936897

Luminaire Tested: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936897
REPORT IS A COMBINATION OF REPORTS P933463 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15031.1 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 135.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936897

CATALOG NUMBER: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P936897

CATALOG NUMBER: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20					20				20
RC	80				70				50					30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	100	95	91	87	93	89	85	82	78	75	72	67	65	63	58	56	55	50
2	90	82	75	70	84	77	71	66	67	63	59	58	55	52	50	48	45	41
3	82	72	64	57	76	67	60	54	59	53	49	51	47	43	44	40	38	34
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32	28
5	68	56	47	41	63	52	44	39	46	40	35	40	35	31	34	30	27	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	23	21
7	58	45	36	30	54	42	34	29	37	31	26	32	27	23	28	24	21	18
8	53	40	32	26	50	38	30	25	34	27	23	29	24	20	25	21	18	16
9	50	37	29	23	46	35	27	22	31	24	20	27	22	18	23	19	16	14
10	46	33	26	21	43	32	25	20	28	22	18	25	20	16	21	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3695	3695	3695
5°	3611	4271	4966
10°	3276	6228	8233
15°	2785	8138	9941
20°	2269	9433	10132
25°	1893	9874	9926
30°	1597	9939	9907
35°	1413	9777	10163
40°	1232	9564	10428
45°	1117	9410	10469
50°	1025	9272	10295
55°	983	9069	9839
60°	1007	8674	9119
65°	1049	8073	8128
70°	1120	7046	6867
75°	1247	5750	5359
80°	1371	3993	3611
85°	1244	2121	1849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10469 cd/sqm

TEST NUMBER: P936897

CATALOG NUMBER: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.5	1.0
10°-20°	684.8	4.6
20°-30°	1197.8	8.0
30°-40°	1541.9	10.3
40°-50°	1722.3	11.5
50°-60°	1649.5	11.0
60°-70°	1307.3	8.7
70°-80°	768.7	5.1
80°-90°	217.0	1.4
90°-100°	435.1	2.9
100°-110°	1144.1	7.6
110°-120°	1186.3	7.9
120°-130°	951.5	6.3
130°-140°	746.6	5.0
140°-150°	573.1	3.8
150°-160°	412.7	2.7
160°-170°	252.5	1.7
170°-180°	85.3	0.6
0°-30°	2037.1	13.6
0°-40°	3579.0	23.8
0°-60°	6950.9	46.2
0°-90°	9243.8	61.5
90°-120°	2765.5	18.4
90°-150°	5036.8	33.5
90°-180°	5787.0	38.5
0°-180°	15031.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1194	1194	1194	1194	1194	
5°	1164	1248	1406	1590	1648	107
15°	872	1609	2712	3288	3391	243
25°	557	1824	3230	3372	3376	257
35°	376	1744	3042	3215	3341	235
45°	257	1390	2688	3080	3218	199
55°	184	883	2281	2650	2723	168
65°	146	469	1694	1905	1932	145
75°	108	288	930	1022	1026	113
85°	38	88	230	254	257	41
90°	6	17	46	23	23	8
95°	58	225	750	386	263	64
105°	206	312	1265	1920	1792	219
115°	366	445	1013	2021	2307	362
125°	509	571	922	1557	1837	452
135°	607	668	893	1257	1425	470
145°	704	749	881	1072	1156	441
155°	796	818	881	968	996	366
165°	859	870	881	916	928	242
175°	893	893	887	899	899	85
180°	893	893	893	893	893	

TEST NUMBER: P936897

CATALOG NUMBER: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5
2.5°	1194.5	1194.5	1202.1	1206.0	1213.7	1217.5	1225.2	1232.9	1255.9	1259.8	1267.5
5°	1163.8	1179.1	1229.1	1248.3	1302.0	1375.0	1405.7	1455.6	1559.3	1590.0	1609.2
7.5°	1117.6	1152.2	1275.1	1305.8	1440.2	1632.3	1713.0	1820.5	1985.7	2066.3	2131.6
10°	1044.7	1117.6	1336.5	1409.5	1628.5	1920.4	2070.2	2220.0	2469.6	2580.9	2623.2
12.5°	964.1	1083.1	1401.9	1501.8	1816.7	2242.9	2423.5	2588.7	2872.9	3022.7	3045.7
15°	871.8	1033.1	1463.3	1609.2	2016.4	2511.8	2711.6	2915.1	3180.2	3287.6	3314.6
17.5°	791.2	994.8	1520.9	1674.5	2170.0	2753.8	2957.4	3126.4	3341.4	3414.4	3433.7
20°	691.3	933.3	1559.3	1759.0	2331.3	2930.4	3126.4	3256.9	3402.8	3449.0	3456.6
22.5°	618.3	868.0	1582.4	1789.7	2438.9	3038.0	3203.1	3306.9	3406.7	3422.1	3425.9
25°	556.9	795.1	1578.5	1824.3	2531.0	3103.3	3230.1	3306.9	3364.5	3372.1	3372.1
27.5°	499.3	714.3	1563.2	1832.0	2600.2	3118.6	3218.5	3272.3	3299.2	3314.6	3314.6
30°	449.3	637.6	1524.7	1816.7	2630.9	3103.3	3183.9	3210.9	3237.7	3260.8	3272.3
32.5°	411.0	564.5	1467.2	1786.0	2634.7	3064.9	3122.5	3137.9	3176.3	3230.1	3249.3
35°	376.4	491.6	1401.9	1743.7	2611.6	3003.4	3041.9	3057.2	3134.0	3214.7	3241.6
37.5°	341.9	437.9	1317.4	1670.7	2577.2	2930.4	2957.4	2984.2	3103.3	3199.3	3230.1
40°	307.3	391.8	1217.5	1590.0	2523.4	2842.2	2865.1	2907.4	3064.9	3176.3	3207.0
42.5°	280.3	353.4	1110.0	1505.5	2454.2	2742.3	2776.9	2838.3	3018.8	3137.9	3172.4
45°	257.4	314.9	994.8	1390.3	2365.9	2638.6	2688.5	2773.0	2965.0	3080.3	3111.0
47.5°	234.3	288.1	875.7	1271.3	2269.9	2534.9	2600.2	2696.1	2892.1	3003.4	3030.4
50°	215.1	261.1	756.6	1144.6	2166.2	2423.5	2500.3	2600.2	2799.9	2903.6	2938.2
52.5°	199.7	238.1	645.3	1017.8	2047.1	2308.3	2396.6	2500.3	2688.5	2788.4	2811.5
55°	184.4	218.9	549.2	883.3	1924.2	2185.4	2281.4	2381.2	2565.6	2650.1	2665.4
57.5°	176.6	203.6	468.6	756.6	1793.6	2047.1	2154.7	2246.8	2419.7	2484.9	2500.3
60°	165.1	192.1	407.1	649.0	1651.5	1916.5	2008.7	2100.9	2246.8	2300.6	2312.1
62.5°	153.6	184.4	361.0	545.4	1505.5	1762.9	1855.1	1939.6	2062.5	2100.9	2116.2
65°	145.9	176.6	326.5	468.6	1355.8	1601.6	1693.7	1766.8	1866.6	1905.0	1912.7
67.5°	138.3	169.0	299.6	403.3	1206.0	1440.2	1509.4	1578.5	1655.3	1693.7	1697.6
70°	126.7	161.3	276.6	357.2	1052.3	1255.9	1313.6	1386.5	1448.0	1467.2	1478.7
72.5°	119.1	149.8	261.1	322.6	894.9	1079.3	1133.1	1175.3	1229.1	1248.3	1248.3
75°	107.6	134.4	245.8	288.1	733.5	883.3	929.5	971.7	1014.0	1021.6	1010.1
77.5°	96.0	119.1	211.2	242.0	572.3	699.0	737.4	760.5	795.1	802.7	806.6
80°	80.6	103.7	165.1	188.2	414.8	514.6	541.6	560.8	591.5	591.5	599.1
82.5°	61.4	80.6	119.1	134.4	280.3	353.4	376.4	387.9	407.1	407.1	407.1
85°	38.4	49.9	76.8	88.4	169.0	215.1	230.4	234.3	249.6	253.5	253.5
87.5°	19.2	26.8	49.9	53.8	88.4	111.3	111.3	119.1	119.1	115.2	111.3
90°	6.0	10.8	15.6	16.8	26.4	39.1	45.5	40.5	30.3	22.8	22.8
92.5°	23.9	64.6	105.4	115.6	162.5	225.1	256.4	224.7	161.3	113.9	109.3
95°	57.6	132.1	206.7	225.3	400.0	633.0	749.5	668.8	507.5	386.4	372.7
97.5°	99.4	165.2	231.0	247.5	538.9	927.3	1121.6	1070.6	968.6	892.2	866.1
100°	131.8	191.5	251.1	266.0	589.3	1020.5	1236.1	1239.7	1247.2	1252.8	1221.7
102.5°	159.4	215.0	270.6	284.6	612.5	1049.8	1268.4	1333.3	1463.3	1560.8	1534.1
105°	206.1	253.2	300.3	312.1	629.7	1053.1	1264.8	1410.5	1701.8	1920.3	1905.9
107.5°	254.1	298.0	342.0	352.9	633.0	1006.3	1192.9	1396.1	1802.5	2107.3	2110.8
110°	286.4	326.1	365.8	375.7	628.1	964.7	1133.1	1360.2	1814.5	2155.2	2170.1

TEST NUMBER: P936897

CATALOG NUMBER: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	318.1	355.9	393.7	403.2	628.3	928.4	1078.5	1311.0	1775.9	2124.6	2147.5
115°	366.1	401.0	435.9	444.6	634.1	886.8	1013.2	1237.1	1685.0	2020.9	2052.7
117.5°	413.4	445.1	476.7	484.7	645.8	860.8	968.2	1170.4	1574.5	1877.7	1912.9
120°	441.0	470.8	500.6	508.0	655.4	852.0	950.3	1135.0	1504.3	1781.3	1815.5
122.5°	467.9	498.1	528.1	535.7	669.3	847.4	936.4	1102.7	1435.4	1684.8	1718.5
125°	509.3	536.7	564.2	571.0	687.9	843.6	921.5	1062.8	1345.3	1557.2	1588.3
127.5°	542.8	570.5	598.3	605.1	706.4	841.4	908.9	1030.2	1272.8	1454.8	1481.0
130°	560.9	590.7	620.5	627.9	720.0	842.7	904.2	1012.1	1228.1	1390.0	1414.3
132.5°	579.4	609.2	639.1	646.5	731.0	843.6	899.9	996.6	1189.9	1334.9	1356.6
135°	607.0	634.1	661.2	668.0	742.9	842.8	892.7	973.7	1135.7	1257.1	1275.8
137.5°	635.1	662.0	689.0	695.6	761.0	848.1	891.6	960.0	1096.9	1199.5	1214.8
140°	658.4	683.2	708.0	714.2	771.9	848.8	887.3	946.4	1064.7	1153.4	1167.7
142.5°	676.5	699.3	722.3	728.0	781.1	851.9	887.3	939.3	1043.1	1121.0	1133.3
145°	704.0	723.9	743.9	748.9	793.1	851.9	881.4	923.8	1008.8	1072.5	1081.8
147.5°	731.6	751.0	770.5	775.3	810.7	857.9	881.4	914.8	981.7	1031.8	1039.5
150°	749.5	767.1	784.7	789.1	819.9	860.9	881.4	909.6	966.0	1008.3	1014.6
152.5°	768.1	781.4	794.8	798.1	825.9	862.9	881.4	905.5	953.7	989.8	994.6
155°	795.6	805.5	815.4	817.8	839.1	867.3	881.4	900.6	938.9	967.6	970.7
157.5°	816.1	825.7	835.2	837.6	852.2	871.7	881.4	896.3	926.1	948.5	950.7
160°	829.9	837.3	844.8	846.6	858.2	873.7	881.4	894.2	919.7	938.9	940.1
162.5°	843.6	849.2	854.9	856.2	864.6	875.8	881.4	892.2	913.7	929.9	931.0
165°	858.6	863.7	868.7	870.0	873.7	878.9	881.4	889.2	904.6	916.1	917.4
167.5°	872.4	874.7	877.1	877.7	880.9	885.2	887.3	892.4	902.5	910.1	910.7
170°	881.4	883.7	886.2	886.7	886.9	887.2	887.3	892.4	902.5	910.1	910.1
172.5°	886.2	886.6	887.2	887.3	887.3	887.3	887.3	891.3	899.3	905.3	904.9
175°	892.7	892.7	892.7	892.7	890.9	888.5	887.3	889.8	895.0	898.7	898.7
177.5°	892.7	892.7	892.7	892.7	891.4	889.5	888.6	890.6	894.6	897.6	897.0
180°	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7	892.7

TEST NUMBER: P936897

CATALOG NUMBER: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1194.5	1194.5
2.5°	1275.1	1267.5
5°	1640.0	1647.7
7.5°	2208.4	2204.6
10°	2746.1	2780.6
12.5°	3137.9	3145.6
15°	3376.0	3391.4
17.5°	3468.1	3472.0
20°	3472.0	3464.4
22.5°	3429.8	3422.1
25°	3379.9	3376.0
27.5°	3333.7	3337.6
30°	3314.6	3326.1
32.5°	3314.6	3333.7
35°	3322.2	3341.4
37.5°	3318.3	3341.4
40°	3303.0	3329.9
42.5°	3260.8	3280.0
45°	3195.5	3218.5
47.5°	3111.0	3126.4
50°	3003.4	3018.8
52.5°	2869.0	2872.9
55°	2707.7	2723.1
57.5°	2534.9	2538.7
60°	2342.8	2354.4
62.5°	2139.3	2139.3
65°	1924.2	1931.9
67.5°	1701.5	1720.7
70°	1474.8	1478.7
72.5°	1252.0	1252.0
75°	1021.6	1025.5
77.5°	802.7	802.7
80°	595.4	599.1
82.5°	411.0	418.6
85°	257.4	257.4
87.5°	119.1	107.6
90°	22.8	22.8
92.5°	91.2	73.1
95°	317.8	263.0
97.5°	761.6	657.3
100°	1097.4	973.1
102.5°	1427.6	1321.1
105°	1848.8	1791.5
107.5°	2124.5	2138.4
110°	2229.7	2289.4

TEST NUMBER: P936897

CATALOG NUMBER: SQ4-FB-050U-100D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2239.2	2330.7
115°	2179.8	2306.8
117.5°	2053.8	2194.7
120°	1952.4	2089.3
122.5°	1853.6	1988.6
125°	1712.6	1837.0
127.5°	1585.9	1690.8
130°	1511.3	1608.2
132.5°	1443.4	1530.2
135°	1350.6	1425.4
137.5°	1276.1	1337.3
140°	1224.9	1282.2
142.5°	1182.7	1231.9
145°	1119.1	1156.4
147.5°	1070.4	1101.3
150°	1039.6	1064.7
152.5°	1013.5	1032.4
155°	983.3	995.8
157.5°	959.4	968.2
160°	945.3	950.3
162.5°	935.9	940.7
165°	922.5	927.5
167.5°	912.8	914.9
170°	910.1	910.1
172.5°	903.0	901.2
175°	898.7	898.7
177.5°	894.9	892.7
180°	892.7	892.7

(END OF REPORT)