

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937702

Luminaire Tested: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937702
REPORT IS A COMBINATION OF REPORTS P933567 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6875.0 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937702

CATALOG NUMBER: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P937702

CATALOG NUMBER: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	84	88	84	80	77	69	67	65	56	55	53	44	43	42
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34
3	79	69	62	56	72	63	57	52	53	48	44	43	39	36	33	31	29
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24
5	66	54	46	39	60	49	42	37	41	36	31	33	29	26	26	23	21
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	20	18
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16
8	51	39	31	26	47	36	29	24	30	24	20	25	20	17	19	16	14
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3641	3641	3641
5°	3554	4205	4895
10°	3220	6127	8115
15°	2733	7998	9798
20°	2222	9262	9986
25°	1852	9684	9783
30°	1559	9738	9765
35°	1377	9569	10018
40°	1197	9350	10278
45°	1082	9189	10319
50°	991	9041	10148
55°	945	8829	9697
60°	964	8430	8988
65°	998	7829	8011
70°	1056	6814	6768
75°	1158	5541	5282
80°	1240	3828	3558
85°	1043	2020	1821

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10319 cd/sqm

TEST NUMBER: P937702

CATALOG NUMBER: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	0.7
10°-20°	225.0	3.3
20°-30°	393.5	5.7
30°-40°	506.6	7.4
40°-50°	565.9	8.2
50°-60°	542.0	7.9
60°-70°	429.5	6.2
70°-80°	252.6	3.7
80°-90°	72.4	1.1
90°-100°	288.5	4.2
100°-110°	758.5	11.0
110°-120°	786.5	11.4
120°-130°	630.8	9.2
130°-140°	495.0	7.2
140°-150°	379.9	5.5
150°-160°	273.6	4.0
160°-170°	167.4	2.4
170°-180°	56.6	0.8
0°-30°	669.3	9.7
0°-40°	1175.9	17.1
0°-60°	2283.7	33.2
0°-90°	3038.2	44.2
90°-120°	1833.5	26.7
90°-150°	3339.2	48.6
90°-180°	3837.0	55.8
0°-180°	6875.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	392	392	392	392	392	
5°	382	410	462	522	541	35
15°	286	529	891	1080	1114	80
25°	183	599	1061	1108	1109	84
35°	124	573	999	1056	1098	77
45°	84	457	883	1012	1058	65
55°	60	290	750	871	895	55
65°	48	154	556	626	635	48
75°	35	95	305	336	337	37
85°	13	29	76	83	84	13
90°	4	11	30	15	15	4
95°	38	149	497	256	174	42
105°	137	207	839	1273	1188	145
115°	243	295	672	1340	1529	240
125°	338	379	611	1032	1218	300
135°	402	443	592	833	945	311
145°	467	496	584	711	767	292
155°	528	542	584	642	660	242
165°	569	577	584	607	615	161
175°	592	592	588	596	596	56
180°	592	592	592	592	592	

TEST NUMBER: P937702

CATALOG NUMBER: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	392.4	392.4	392.4	392.4	392.4	392.4	392.4	392.4	392.4	392.4	392.4
2.5°	392.4	392.4	395.0	396.2	398.7	400.0	402.5	405.0	412.7	413.9	416.4
5°	382.4	387.4	403.8	410.1	427.7	451.7	461.8	478.3	512.4	522.4	528.7
7.5°	367.2	378.6	419.0	429.1	473.2	536.3	562.8	598.1	652.4	678.9	700.3
10°	343.2	367.2	439.1	463.1	535.0	631.0	680.2	729.3	811.4	847.9	861.9
12.5°	316.8	355.8	460.6	493.4	596.9	737.0	796.3	850.5	943.9	993.1	1000.6
15°	286.4	339.4	480.7	528.7	662.5	825.3	890.9	957.8	1044.9	1080.2	1089.0
17.5°	260.0	326.8	499.7	550.2	713.0	904.8	971.6	1027.2	1097.9	1121.8	1128.1
20°	227.1	306.7	512.4	578.0	766.0	962.8	1027.2	1070.1	1118.0	1133.2	1135.7
22.5°	203.1	285.2	519.9	588.0	801.2	998.2	1052.4	1086.5	1119.3	1124.3	1125.6
25°	183.0	261.2	518.7	599.4	831.6	1019.6	1061.2	1086.5	1105.4	1107.9	1107.9
27.5°	164.1	234.7	513.6	601.9	854.2	1024.6	1057.5	1075.1	1083.9	1089.0	1089.0
30°	147.6	209.4	501.0	596.9	864.4	1019.6	1046.1	1054.9	1063.8	1071.3	1075.1
32.5°	135.0	185.5	482.1	586.8	865.6	1007.0	1025.9	1030.9	1043.5	1061.2	1067.6
35°	123.7	161.5	460.6	572.9	858.1	986.8	999.4	1004.5	1029.7	1056.2	1065.0
37.5°	112.3	143.8	432.8	548.9	846.7	962.8	971.6	980.5	1019.6	1051.2	1061.2
40°	100.9	128.7	400.0	522.4	829.0	933.8	941.3	955.3	1007.0	1043.5	1053.7
42.5°	92.2	116.1	364.7	494.7	806.3	900.9	912.3	932.6	991.9	1030.9	1042.3
45°	84.5	103.4	326.8	456.8	777.3	866.9	883.3	911.1	974.2	1012.0	1022.1
47.5°	77.0	94.6	287.7	417.7	745.8	832.9	854.2	885.9	950.2	986.8	995.6
50°	70.7	85.9	248.6	376.1	711.7	796.3	821.5	854.2	920.0	953.9	965.3
52.5°	65.6	78.2	212.0	334.4	672.6	758.4	787.4	821.5	883.3	916.1	923.7
55°	60.5	71.9	180.5	290.2	632.2	718.0	749.6	782.3	843.0	870.7	875.7
57.5°	58.1	66.8	153.9	248.6	589.3	672.6	707.9	738.2	794.9	816.4	821.5
60°	54.2	63.1	133.8	213.3	542.6	629.6	660.0	690.3	738.2	755.9	759.6
62.5°	50.5	60.5	118.6	179.2	494.7	579.2	609.5	637.3	677.7	690.3	695.3
65°	47.9	58.1	107.2	153.9	445.4	526.2	556.5	580.4	613.3	625.9	628.4
67.5°	45.5	55.5	98.5	132.5	396.2	473.2	495.9	518.7	543.9	556.5	557.7
70°	41.6	53.0	90.8	117.4	345.7	412.7	431.6	455.5	475.7	482.1	485.8
72.5°	39.2	49.2	85.9	106.0	294.0	354.6	372.3	386.1	403.8	410.1	410.1
75°	35.3	44.1	80.8	94.6	241.0	290.2	305.4	319.3	333.1	335.7	331.9
77.5°	31.5	39.2	69.4	79.5	188.0	229.7	242.3	249.8	261.2	263.8	265.0
80°	26.5	34.1	54.2	61.8	136.3	169.1	177.9	184.2	194.3	194.3	196.8
82.5°	20.2	26.5	39.2	44.1	92.2	116.1	123.7	127.5	133.8	133.8	133.8
85°	12.6	16.4	25.2	29.0	55.5	70.7	75.7	77.0	82.0	83.3	83.3
87.5°	6.3	8.8	16.4	17.7	29.0	36.6	36.6	39.2	39.2	37.8	36.6
90°	4.0	7.2	10.3	11.1	17.5	26.0	30.2	26.8	20.2	15.1	15.1
92.5°	15.9	42.9	69.9	76.7	107.8	149.3	170.0	149.0	107.0	75.4	72.5
95°	38.1	87.6	137.0	149.4	265.2	419.6	496.9	443.4	336.4	256.2	247.2
97.5°	65.9	109.5	153.2	164.1	357.3	614.8	743.6	709.8	642.1	591.4	574.1
100°	87.4	126.9	166.5	176.4	390.8	676.6	819.5	822.0	826.8	830.6	809.9
102.5°	105.6	142.6	179.4	188.7	406.2	696.0	841.0	884.0	970.2	1034.7	1017.1
105°	136.7	167.9	199.1	206.9	417.5	698.2	838.6	935.1	1128.2	1273.1	1263.7
107.5°	168.5	197.6	226.7	234.0	419.6	667.1	790.8	925.6	1195.0	1397.1	1399.4
110°	189.9	216.2	242.5	249.1	416.4	639.6	751.1	901.7	1202.9	1428.8	1438.7

TEST NUMBER: P937702

CATALOG NUMBER: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	211.0	236.0	261.0	267.3	416.6	615.5	715.0	869.1	1177.3	1408.5	1423.7
115°	242.7	265.8	288.9	294.7	420.4	588.0	671.7	820.2	1117.2	1339.9	1360.9
117.5°	274.1	295.1	316.1	321.4	428.2	570.7	642.0	775.9	1043.9	1244.9	1268.2
120°	292.3	312.1	331.9	336.8	434.5	564.9	630.0	752.4	997.3	1181.0	1203.7
122.5°	310.3	330.2	350.2	355.2	443.7	561.8	620.8	731.1	951.6	1117.0	1139.3
125°	337.7	355.8	374.0	378.6	456.0	559.2	610.9	704.6	891.9	1032.4	1053.0
127.5°	359.8	378.2	396.6	401.2	468.3	557.8	602.6	683.0	843.8	964.5	981.8
130°	371.8	391.6	411.3	416.3	477.3	558.8	599.5	671.1	814.2	921.6	937.6
132.5°	384.1	403.9	423.6	428.6	484.6	559.2	596.6	660.7	788.8	885.0	899.4
135°	402.4	420.4	438.4	442.9	492.6	558.8	591.9	645.6	752.8	833.3	845.7
137.5°	421.1	438.9	456.7	461.2	504.4	562.2	591.0	636.4	727.1	795.2	805.4
140°	436.5	453.0	469.4	473.5	511.8	562.8	588.3	627.4	705.8	764.7	774.1
142.5°	448.5	463.7	478.8	482.7	517.9	564.8	588.3	622.7	691.5	743.2	751.4
145°	466.7	480.0	493.2	496.5	525.8	564.9	584.4	612.5	668.8	711.0	717.2
147.5°	485.0	497.9	510.7	514.0	537.5	568.7	584.4	606.5	650.8	684.1	689.2
150°	496.9	508.5	520.2	523.1	543.6	570.8	584.4	603.1	640.4	668.5	672.6
152.5°	509.2	518.0	526.9	529.1	547.5	572.0	584.4	600.3	632.2	656.2	659.3
155°	527.5	534.0	540.6	542.2	556.3	575.0	584.4	597.1	622.5	641.5	643.6
157.5°	541.0	547.4	553.7	555.3	565.0	577.9	584.4	594.2	614.0	628.8	630.2
160°	550.2	555.1	560.0	561.3	569.0	579.2	584.4	592.9	609.8	622.5	623.3
162.5°	559.2	563.0	566.7	567.7	573.2	580.6	584.4	591.5	605.8	616.5	617.2
165°	569.2	572.5	575.9	576.7	579.3	582.6	584.4	589.5	599.7	607.4	608.2
167.5°	578.3	580.0	581.6	582.0	584.1	586.8	588.3	591.6	598.3	603.4	603.8
170°	584.4	585.9	587.5	587.9	588.0	588.2	588.3	591.6	598.3	603.4	603.4
172.5°	587.5	587.9	588.2	588.3	588.3	588.3	588.3	591.0	596.2	600.2	599.9
175°	591.9	591.9	591.9	591.9	590.7	589.0	588.3	590.0	593.3	595.8	595.8
177.5°	591.9	591.9	591.9	591.9	591.0	589.7	589.0	590.4	593.1	595.1	594.7
180°	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9	591.9

TEST NUMBER: P937702

CATALOG NUMBER: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	392.4	392.4
2.5°	419.0	416.4
5°	538.8	541.4
7.5°	725.6	724.3
10°	902.3	913.6
12.5°	1030.9	1033.5
15°	1109.2	1114.2
17.5°	1139.5	1140.7
20°	1140.7	1138.2
22.5°	1126.9	1124.3
25°	1110.5	1109.2
27.5°	1095.3	1096.5
30°	1089.0	1092.8
32.5°	1089.0	1095.3
35°	1091.6	1097.9
37.5°	1090.2	1097.9
40°	1085.3	1094.0
42.5°	1071.3	1077.6
45°	1049.9	1057.5
47.5°	1022.1	1027.2
50°	986.8	991.9
52.5°	942.6	943.9
55°	889.6	894.6
57.5°	832.9	834.1
60°	769.7	773.6
62.5°	702.9	702.9
65°	632.2	634.7
67.5°	559.1	565.4
70°	484.6	485.8
72.5°	411.4	411.4
75°	335.7	336.9
77.5°	263.8	263.8
80°	195.6	196.8
82.5°	135.0	137.5
85°	84.5	84.5
87.5°	39.2	35.3
90°	15.1	15.1
92.5°	60.5	48.4
95°	210.8	174.4
97.5°	504.9	435.8
100°	727.5	645.1
102.5°	946.5	875.9
105°	1225.6	1187.7
107.5°	1408.5	1417.7
110°	1478.2	1517.8

TEST NUMBER: P937702

CATALOG NUMBER: SQ4-FB-100U-100D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1484.5	1545.2
115°	1445.1	1529.3
117.5°	1361.6	1455.0
120°	1294.4	1385.1
122.5°	1228.9	1318.4
125°	1135.4	1217.9
127.5°	1051.5	1121.0
130°	1001.9	1066.2
132.5°	956.9	1014.5
135°	895.3	945.0
137.5°	846.0	886.6
140°	812.1	850.0
142.5°	784.1	816.7
145°	741.9	766.7
147.5°	709.7	730.1
150°	689.2	705.8
152.5°	671.8	684.4
155°	651.9	660.2
157.5°	636.1	642.0
160°	626.7	630.0
162.5°	620.5	623.6
165°	611.6	614.9
167.5°	605.1	606.5
170°	603.4	603.4
172.5°	598.7	597.4
175°	595.8	595.8
177.5°	593.3	591.9
180°	591.9	591.9

(END OF REPORT)