

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937803

Luminaire Tested: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937803
REPORT IS A COMBINATION OF REPORTS P933576 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11590.8 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937803

CATALOG NUMBER: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P937803

CATALOG NUMBER: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56
1	97	93	89	85	90	86	82	79	72	70	67	60	58	57	49	48	47
2	88	80	74	68	81	74	69	64	63	59	55	52	49	46	42	40	38
3	80	70	62	56	73	65	58	53	55	50	45	46	42	39	37	34	32
4	73	62	53	47	67	57	50	44	48	43	38	40	36	32	33	30	27
5	67	54	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23
6	61	49	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20
7	56	44	35	30	52	40	33	28	34	29	24	29	24	21	24	20	17
8	52	39	31	26	48	37	29	24	31	25	21	26	22	18	22	18	15
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	20	16	14
10	45	33	25	20	41	30	24	19	26	21	17	22	18	15	18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4554	5389	6269
10°	4129	7854	10393
15°	3509	10258	12549
20°	2855	11884	12790
25°	2381	12433	12529
30°	2006	12509	12506
35°	1774	12298	12829
40°	1545	12025	13163
45°	1397	11823	13215
50°	1281	11641	12996
55°	1225	11377	12420
60°	1253	10873	11511
65°	1303	10107	10260
70°	1384	8808	8668
75°	1528	7177	6764
80°	1657	4971	4559
85°	1449	2632	2333

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 13215 cd/sqm

TEST NUMBER: P937803

CATALOG NUMBER: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.5	0.8
10°-20°	432.2	3.7
20°-30°	756.0	6.5
30°-40°	973.2	8.4
40°-50°	1087.0	9.4
50°-60°	1041.1	9.0
60°-70°	825.1	7.1
70°-80°	485.2	4.2
80°-90°	138.2	1.2
90°-100°	432.8	3.7
100°-110°	1137.7	9.8
110°-120°	1179.7	10.2
120°-130°	946.3	8.2
130°-140°	742.5	6.4
140°-150°	569.9	4.9
150°-160°	410.4	3.5
160°-170°	251.1	2.2
170°-180°	84.8	0.7
0°-30°	1285.7	11.1
0°-40°	2259.0	19.5
0°-60°	4387.1	37.8
0°-90°	5835.6	50.3
90°-120°	2750.2	23.7
90°-150°	5008.9	43.2
90°-180°	5755.0	49.7
0°-180°	11590.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	754	754	754	754	754	
5°	734	788	887	1004	1040	68
15°	550	1016	1712	2075	2140	153
25°	352	1151	2039	2128	2131	162
35°	238	1100	1920	2029	2109	148
45°	162	878	1697	1944	2031	126
55°	116	558	1440	1673	1719	106
65°	92	296	1069	1202	1219	91
75°	68	182	587	645	647	71
85°	24	56	145	160	162	26
90°	6	17	45	23	23	7
95°	57	224	745	384	262	64
105°	205	310	1258	1910	1782	217
115°	364	442	1008	2010	2294	360
125°	506	568	916	1549	1827	450
135°	604	664	888	1250	1418	467
145°	700	745	876	1066	1150	439
155°	791	813	876	962	990	364
165°	854	865	876	911	922	241
175°	888	888	882	894	894	84
180°	888	888	888	888	888	

TEST NUMBER: P937803

CATALOG NUMBER: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	753.9	753.9	753.9	753.9	753.9	753.9	753.9	753.9	753.9	753.9	753.9
2.5°	753.9	753.9	758.7	761.1	766.0	768.5	773.3	778.1	792.6	795.1	800.0
5°	734.5	744.2	775.7	787.9	821.8	867.8	887.2	918.7	984.2	1003.6	1015.7
7.5°	705.5	727.2	804.8	824.2	909.1	1030.3	1081.2	1149.1	1253.2	1304.1	1345.4
10°	659.3	705.5	843.6	889.7	1027.9	1212.1	1306.6	1401.2	1558.8	1629.0	1655.7
12.5°	608.4	683.6	884.8	947.8	1146.6	1415.7	1529.6	1633.8	1813.3	1907.8	1922.3
15°	550.3	652.1	923.6	1015.7	1272.6	1585.4	1711.5	1839.9	2007.2	2075.0	2092.0
17.5°	499.4	627.8	960.0	1056.9	1369.7	1738.1	1866.5	1973.2	2109.0	2155.1	2167.2
20°	436.3	589.0	984.2	1110.3	1471.5	1849.6	1973.2	2055.6	2147.8	2176.8	2181.7
22.5°	390.3	547.9	998.7	1129.7	1539.4	1917.4	2021.7	2087.2	2150.2	2159.9	2162.3
25°	351.5	501.8	996.4	1151.4	1597.5	1958.7	2038.7	2087.2	2123.5	2128.4	2128.4
27.5°	315.2	450.9	986.6	1156.3	1641.2	1968.4	2031.4	2065.4	2082.3	2092.0	2092.0
30°	283.6	402.4	962.4	1146.6	1660.6	1958.7	2009.6	2026.6	2043.5	2058.1	2065.4
32.5°	259.4	356.3	926.0	1127.2	1662.9	1934.4	1970.8	1980.5	2004.7	2038.7	2050.8
35°	237.6	310.3	884.8	1100.5	1648.4	1895.7	1919.9	1929.6	1978.1	2029.0	2046.0
37.5°	215.7	276.4	831.5	1054.5	1626.6	1849.6	1866.5	1883.5	1958.7	2019.3	2038.7
40°	194.0	247.2	768.5	1003.6	1592.7	1793.9	1808.4	1835.0	1934.4	2004.7	2024.1
42.5°	177.0	223.0	700.6	950.2	1549.0	1730.8	1752.6	1791.4	1905.3	1980.5	2002.3
45°	162.4	198.7	627.8	877.5	1493.2	1665.3	1696.8	1750.2	1871.4	1944.2	1963.6
47.5°	147.8	181.8	552.7	802.4	1432.7	1599.9	1641.2	1701.7	1825.4	1895.7	1912.7
50°	135.7	164.8	477.6	722.4	1367.2	1529.6	1578.1	1641.2	1767.2	1832.6	1854.4
52.5°	126.1	150.3	407.2	642.4	1292.0	1456.9	1512.6	1578.1	1696.8	1759.9	1774.5
55°	116.3	138.2	346.7	557.5	1214.5	1379.3	1439.9	1503.0	1619.3	1672.7	1682.3
57.5°	111.5	128.4	295.8	477.6	1132.1	1292.0	1359.9	1418.1	1527.2	1568.4	1578.1
60°	104.2	121.2	257.0	409.7	1042.4	1209.6	1267.9	1326.0	1418.1	1452.1	1459.3
62.5°	96.9	116.3	227.9	344.2	950.2	1112.7	1170.8	1224.2	1301.8	1326.0	1335.7
65°	92.2	111.5	206.1	295.8	855.7	1010.9	1069.0	1115.1	1178.1	1202.3	1207.2
67.5°	87.3	106.7	189.1	254.5	761.1	909.1	952.7	996.4	1044.8	1069.0	1071.5
70°	80.0	101.8	174.6	225.5	664.2	792.6	829.0	875.1	913.9	926.0	933.3
72.5°	75.2	94.5	164.8	203.6	564.8	681.2	715.1	741.7	775.7	787.9	787.9
75°	67.9	84.8	155.2	181.8	463.0	557.5	586.7	613.3	639.9	644.8	637.6
77.5°	60.6	75.2	133.3	152.7	361.2	441.2	465.5	480.0	501.8	506.6	509.1
80°	50.9	65.4	104.2	118.8	261.8	324.8	341.8	353.9	373.3	373.3	378.2
82.5°	38.8	50.9	75.2	84.8	177.0	223.0	237.6	244.9	257.0	257.0	257.0
85°	24.3	31.5	48.5	55.8	106.7	135.7	145.4	147.8	157.6	160.0	160.0
87.5°	12.1	17.0	31.5	33.9	55.8	70.3	70.3	75.2	75.2	72.8	70.3
90°	5.9	10.7	15.5	16.7	26.3	39.0	45.3	40.2	30.2	22.6	22.6
92.5°	23.9	64.4	104.9	115.0	161.7	223.9	255.0	223.5	160.4	113.2	108.7
95°	57.2	131.3	205.5	224.0	397.9	629.5	745.4	665.2	504.6	384.3	370.6
97.5°	98.9	164.4	229.8	246.1	535.9	922.2	1115.4	1064.7	963.3	887.2	861.2
100°	131.1	190.4	249.7	264.5	586.1	1014.8	1229.2	1232.9	1240.4	1245.9	1215.0
102.5°	158.5	213.9	269.2	283.1	609.2	1044.0	1261.4	1326.0	1455.2	1552.2	1525.7
105°	204.9	251.8	298.7	310.5	626.3	1047.3	1257.8	1402.7	1692.4	1909.6	1895.4
107.5°	252.6	296.3	340.1	351.0	629.4	1000.6	1186.3	1388.4	1792.4	2095.6	2099.0
110°	284.8	324.2	363.8	373.6	624.7	959.4	1126.7	1352.6	1804.4	2143.2	2158.0

TEST NUMBER: P937803

CATALOG NUMBER: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	316.4	354.0	391.6	401.0	624.9	923.3	1072.5	1303.7	1766.1	2112.8	2135.6
115°	364.0	398.7	433.4	442.1	630.6	881.8	1007.5	1230.2	1675.7	2009.8	2041.4
117.5°	411.1	442.6	474.2	482.0	642.2	856.0	962.8	1163.9	1565.8	1867.3	1902.4
120°	438.5	468.2	497.8	505.3	651.9	847.3	945.0	1128.6	1495.9	1771.4	1805.4
122.5°	465.4	495.3	525.2	532.7	665.5	842.7	931.3	1096.7	1427.4	1675.5	1709.1
125°	506.4	533.7	561.1	567.8	684.1	839.0	916.4	1056.9	1337.9	1548.6	1579.6
127.5°	539.9	567.4	595.0	601.8	702.5	836.8	903.9	1024.5	1265.8	1446.7	1472.8
130°	557.7	587.4	617.0	624.5	716.1	838.1	899.1	1006.5	1221.3	1382.4	1406.4
132.5°	576.2	605.9	635.5	642.9	726.9	839.0	894.9	991.1	1183.3	1327.5	1349.1
135°	603.6	630.6	657.6	664.4	738.9	838.1	887.8	968.3	1129.3	1250.1	1268.7
137.5°	631.5	658.3	685.1	691.8	756.7	843.4	886.6	954.7	1090.8	1192.9	1208.1
140°	654.8	679.5	704.1	710.2	767.6	844.1	882.4	941.2	1058.8	1147.0	1161.2
142.5°	672.7	695.5	718.3	724.0	776.8	847.2	882.4	934.1	1037.3	1114.8	1127.0
145°	700.1	720.0	739.8	744.8	788.7	847.3	876.5	918.7	1003.2	1066.5	1075.8
147.5°	727.5	746.8	766.1	771.0	806.1	853.0	876.5	909.7	976.2	1026.1	1033.7
150°	745.4	762.9	780.3	784.7	815.3	856.1	876.5	904.6	960.6	1002.8	1009.0
152.5°	763.9	777.2	790.4	793.7	821.3	858.1	876.5	900.5	948.4	984.3	989.0
155°	791.3	801.1	810.8	813.3	834.4	862.5	876.5	895.6	933.7	962.3	965.4
157.5°	811.6	821.1	830.6	833.0	847.5	866.9	876.5	891.3	921.0	943.3	945.4
160°	825.2	832.7	840.1	841.9	853.5	868.9	876.5	889.2	914.6	933.7	934.9
162.5°	839.0	844.5	850.0	851.5	859.8	871.0	876.5	887.2	908.7	924.7	925.9
165°	853.9	858.8	863.9	865.1	869.0	874.0	876.5	884.1	899.5	911.1	912.3
167.5°	867.5	869.9	872.3	872.9	876.0	880.3	882.4	887.5	897.5	905.1	905.6
170°	876.5	878.9	881.3	881.8	882.0	882.3	882.4	887.5	897.5	905.1	905.1
172.5°	881.3	881.8	882.3	882.4	882.4	882.4	882.4	886.4	894.4	900.3	899.8
175°	887.8	887.8	887.8	887.8	886.0	883.6	882.4	884.9	890.0	893.8	893.8
177.5°	887.8	887.8	887.8	887.8	886.4	884.6	883.7	885.7	889.6	892.5	892.0
180°	887.8	887.8	887.8	887.8	887.8	887.8	887.8	887.8	887.8	887.8	887.8

TEST NUMBER: P937803

CATALOG NUMBER: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	753.9	753.9
2.5°	804.8	800.0
5°	1035.1	1040.0
7.5°	1393.9	1391.4
10°	1733.2	1755.1
12.5°	1980.5	1985.3
15°	2130.8	2140.5
17.5°	2189.0	2191.4
20°	2191.4	2186.6
22.5°	2164.7	2159.9
25°	2133.2	2130.8
27.5°	2104.2	2106.5
30°	2092.0	2099.3
32.5°	2092.0	2104.2
35°	2096.9	2109.0
37.5°	2094.4	2109.0
40°	2084.8	2101.7
42.5°	2058.1	2070.2
45°	2016.9	2031.4
47.5°	1963.6	1973.2
50°	1895.7	1905.3
52.5°	1810.8	1813.3
55°	1709.0	1718.7
57.5°	1599.9	1602.3
60°	1478.7	1486.0
62.5°	1350.3	1350.3
65°	1214.5	1219.3
67.5°	1073.9	1086.0
70°	930.8	933.3
72.5°	790.3	790.3
75°	644.8	647.2
77.5°	506.6	506.6
80°	375.7	378.2
82.5°	259.4	264.2
85°	162.4	162.4
87.5°	75.2	67.9
90°	22.6	22.6
92.5°	90.6	72.7
95°	316.1	261.6
97.5°	757.4	653.6
100°	1091.3	967.6
102.5°	1419.7	1313.8
105°	1838.5	1781.6
107.5°	2112.8	2126.6
110°	2217.4	2276.7

TEST NUMBER: P937803

CATALOG NUMBER: SQ4-FB-100U-125D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2226.7	2317.8
115°	2167.7	2294.0
117.5°	2042.5	2182.6
120°	1941.6	2077.7
122.5°	1843.3	1977.6
125°	1703.1	1826.8
127.5°	1577.2	1681.5
130°	1502.9	1599.2
132.5°	1435.5	1521.8
135°	1343.1	1417.5
137.5°	1269.0	1329.9
140°	1218.2	1275.1
142.5°	1176.1	1225.1
145°	1113.0	1150.0
147.5°	1064.4	1095.2
150°	1033.9	1058.8
152.5°	1007.8	1026.6
155°	977.8	990.2
157.5°	954.1	962.8
160°	940.0	945.0
162.5°	930.6	935.4
165°	917.4	922.3
167.5°	907.7	909.8
170°	905.1	905.1
172.5°	898.0	896.2
175°	893.8	893.8
177.5°	889.9	887.8
180°	887.8	887.8

(END OF REPORT)