

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938097

Luminaire Tested: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938097
REPORT IS A COMBINATION OF REPORTS P933591 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23787.0 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 193.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938097

CATALOG NUMBER: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P938097

CATALOG NUMBER: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	90	86	83	86	82	79	76	67	65	62	53	51	50	40	39	38
2	86	78	72	67	78	71	66	61	58	54	51	46	43	41	35	33	31
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26
4	71	60	52	46	64	55	48	42	45	40	35	35	32	29	27	24	22
5	65	53	45	39	59	49	41	36	40	34	30	31	27	24	24	21	19
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	43	35	29	50	39	32	27	32	26	23	25	21	18	19	16	14
8	51	38	31	25	46	35	28	23	29	24	20	23	19	16	18	15	13
9	47	35	27	22	43	32	25	21	26	21	17	21	17	14	16	13	11
10	44	32	25	20	40	29	23	18	24	19	16	19	15	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3695	3695	3695
5°	3611	4271	4966
10°	3276	6228	8233
15°	2785	8138	9941
20°	2269	9433	10132
25°	1893	9874	9926
30°	1597	9939	9907
35°	1413	9777	10163
40°	1232	9564	10428
45°	1117	9410	10469
50°	1025	9272	10295
55°	983	9069	9839
60°	1007	8674	9119
65°	1049	8073	8128
70°	1120	7046	6867
75°	1247	5750	5359
80°	1371	3993	3611
85°	1244	2121	1849

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10469 cd/sqm

TEST NUMBER: P938097

CATALOG NUMBER: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.5	0.6
10°-20°	684.8	2.9
20°-30°	1197.8	5.0
30°-40°	1541.9	6.5
40°-50°	1722.3	7.2
50°-60°	1649.5	6.9
60°-70°	1307.3	5.5
70°-80°	768.7	3.2
80°-90°	222.1	0.9
90°-100°	1093.2	4.6
100°-110°	2874.0	12.1
110°-120°	2980.0	12.5
120°-130°	2390.3	10.0
130°-140°	1875.6	7.9
140°-150°	1439.6	6.1
150°-160°	1036.7	4.4
160°-170°	634.3	2.7
170°-180°	214.3	0.9
0°-30°	2037.1	8.6
0°-40°	3579.0	15.0
0°-60°	6950.9	29.2
0°-90°	9248.9	38.9
90°-120°	6947.2	29.2
90°-150°	12652.7	53.2
90°-180°	14538.0	61.1
0°-180°	23787.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1194	1194	1194	1194	1194	
5°	1164	1248	1406	1590	1648	107
15°	872	1609	2712	3288	3391	243
25°	557	1824	3230	3372	3376	257
35°	376	1744	3042	3215	3341	235
45°	257	1390	2688	3080	3218	199
55°	184	883	2281	2650	2723	168
65°	146	469	1694	1905	1932	145
75°	108	288	930	1022	1026	113
85°	38	88	230	254	257	41
90°	15	42	114	57	57	15
95°	144	566	1883	971	661	160
105°	518	784	3177	4824	4500	549
115°	920	1117	2545	5077	5795	908
125°	1279	1434	2315	3912	4615	1136
135°	1525	1678	2243	3158	3581	1180
145°	1768	1881	2214	2694	2905	1108
155°	1999	2054	2214	2431	2502	918
165°	2157	2185	2214	2301	2330	609
175°	2243	2243	2229	2258	2258	213
180°	2243	2243	2243	2243	2243	

TEST NUMBER: P938097

CATALOG NUMBER: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5
2.5°	1194.5	1194.5	1202.1	1206.0	1213.7	1217.5	1225.2	1232.9	1255.9	1259.8	1267.5
5°	1163.8	1179.1	1229.1	1248.3	1302.0	1375.0	1405.7	1455.6	1559.3	1590.0	1609.2
7.5°	1117.6	1152.2	1275.1	1305.8	1440.2	1632.3	1713.0	1820.5	1985.7	2066.3	2131.6
10°	1044.7	1117.6	1336.5	1409.5	1628.5	1920.4	2070.2	2220.0	2469.6	2580.9	2623.2
12.5°	964.1	1083.1	1401.9	1501.8	1816.7	2242.9	2423.5	2588.7	2872.9	3022.7	3045.7
15°	871.8	1033.1	1463.3	1609.2	2016.4	2511.8	2711.6	2915.1	3180.2	3287.6	3314.6
17.5°	791.2	994.8	1520.9	1674.5	2170.0	2753.8	2957.4	3126.4	3341.4	3414.4	3433.7
20°	691.3	933.3	1559.3	1759.0	2331.3	2930.4	3126.4	3256.9	3402.8	3449.0	3456.6
22.5°	618.3	868.0	1582.4	1789.7	2438.9	3038.0	3203.1	3306.9	3406.7	3422.1	3425.9
25°	556.9	795.1	1578.5	1824.3	2531.0	3103.3	3230.1	3306.9	3364.5	3372.1	3372.1
27.5°	499.3	714.3	1563.2	1832.0	2600.2	3118.6	3218.5	3272.3	3299.2	3314.6	3314.6
30°	449.3	637.6	1524.7	1816.7	2630.9	3103.3	3183.9	3210.9	3237.7	3260.8	3272.3
32.5°	411.0	564.5	1467.2	1786.0	2634.7	3064.9	3122.5	3137.9	3176.3	3230.1	3249.3
35°	376.4	491.6	1401.9	1743.7	2611.6	3003.4	3041.9	3057.2	3134.0	3214.7	3241.6
37.5°	341.9	437.9	1317.4	1670.7	2577.2	2930.4	2957.4	2984.2	3103.3	3199.3	3230.1
40°	307.3	391.8	1217.5	1590.0	2523.4	2842.2	2865.1	2907.4	3064.9	3176.3	3207.0
42.5°	280.3	353.4	1110.0	1505.5	2454.2	2742.3	2776.9	2838.3	3018.8	3137.9	3172.4
45°	257.4	314.9	994.8	1390.3	2365.9	2638.6	2688.5	2773.0	2965.0	3080.3	3111.0
47.5°	234.3	288.1	875.7	1271.3	2269.9	2534.9	2600.2	2696.1	2892.1	3003.4	3030.4
50°	215.1	261.1	756.6	1144.6	2166.2	2423.5	2500.3	2600.2	2799.9	2903.6	2938.2
52.5°	199.7	238.1	645.3	1017.8	2047.1	2308.3	2396.6	2500.3	2688.5	2788.4	2811.5
55°	184.4	218.9	549.2	883.3	1924.2	2185.4	2281.4	2381.2	2565.6	2650.1	2665.4
57.5°	176.6	203.6	468.6	756.6	1793.6	2047.1	2154.7	2246.8	2419.7	2484.9	2500.3
60°	165.1	192.1	407.1	649.0	1651.5	1916.5	2008.7	2100.9	2246.8	2300.6	2312.1
62.5°	153.6	184.4	361.0	545.4	1505.5	1762.9	1855.1	1939.6	2062.5	2100.9	2116.2
65°	145.9	176.6	326.5	468.6	1355.8	1601.6	1693.7	1766.8	1866.6	1905.0	1912.7
67.5°	138.3	169.0	299.6	403.3	1206.0	1440.2	1509.4	1578.5	1655.3	1693.7	1697.6
70°	126.7	161.3	276.6	357.2	1052.3	1255.9	1313.6	1386.5	1448.0	1467.2	1478.7
72.5°	119.1	149.8	261.1	322.6	894.9	1079.3	1133.1	1175.3	1229.1	1248.3	1248.3
75°	107.6	134.4	245.8	288.1	733.5	883.3	929.5	971.7	1014.0	1021.6	1010.1
77.5°	96.0	119.1	211.2	242.0	572.3	699.0	737.4	760.5	795.1	802.7	806.6
80°	80.6	103.7	165.1	188.2	414.8	514.6	541.6	560.8	591.5	591.5	599.1
82.5°	61.4	80.6	119.1	134.4	280.3	353.4	376.4	387.9	407.1	407.1	407.1
85°	38.4	49.9	76.8	88.4	169.0	215.1	230.4	234.3	249.6	253.5	253.5
87.5°	19.2	26.8	49.9	53.8	88.4	111.3	111.3	119.1	119.1	115.2	111.3
90°	15.0	27.0	39.1	42.2	66.2	98.3	114.3	101.6	76.3	57.2	57.2
92.5°	60.2	162.5	264.9	290.5	408.4	565.6	644.2	564.5	405.3	286.0	274.6
95°	144.5	331.8	519.1	565.9	1004.9	1590.2	1882.9	1680.1	1274.8	970.8	936.3
97.5°	249.8	415.0	580.3	621.6	1353.6	2329.6	2817.6	2689.5	2433.3	2241.1	2175.5
100°	331.1	481.0	630.8	668.3	1480.5	2563.6	3105.1	3114.5	3133.2	3147.2	3069.1
102.5°	400.4	540.2	679.9	714.9	1538.8	2637.1	3186.4	3349.5	3676.0	3920.9	3854.0
105°	517.7	636.1	754.6	784.2	1581.9	2645.5	3177.3	3543.1	4275.0	4823.9	4787.9
107.5°	638.2	748.6	858.9	886.5	1589.9	2527.8	2996.7	3507.1	4527.8	5293.5	5302.2
110°	719.5	819.1	918.8	943.7	1577.8	2423.4	2846.1	3416.8	4558.0	5413.9	5451.4

TEST NUMBER: P938097

CATALOG NUMBER: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	799.2	894.2	989.2	1012.9	1578.3	2332.3	2709.2	3293.2	4461.2	5337.2	5394.7
115°	919.6	1007.2	1094.9	1116.8	1592.9	2227.7	2545.2	3107.8	4232.9	5076.8	5156.5
117.5°	1038.6	1118.1	1197.8	1217.6	1622.5	2162.3	2432.3	2940.0	3955.5	4717.0	4805.5
120°	1107.8	1182.7	1257.7	1276.4	1646.6	2140.3	2387.1	2851.1	3778.9	4474.7	4560.7
122.5°	1175.5	1251.1	1326.7	1345.6	1681.2	2128.8	2352.5	2770.3	3605.7	4232.4	4317.2
125°	1279.4	1348.3	1417.2	1434.4	1727.9	2119.2	2314.8	2669.7	3379.5	3911.8	3989.9
127.5°	1363.7	1433.2	1502.8	1520.2	1774.5	2113.7	2283.3	2587.9	3197.3	3654.4	3720.3
130°	1408.8	1483.7	1558.6	1577.3	1808.6	2117.1	2271.2	2542.5	3085.0	3491.9	3552.7
132.5°	1455.4	1530.3	1605.3	1624.0	1836.3	2119.2	2260.7	2503.5	2989.2	3353.4	3408.0
135°	1524.7	1592.9	1661.2	1678.2	1866.4	2117.3	2242.7	2446.0	2852.7	3157.8	3204.8
137.5°	1595.5	1663.0	1730.5	1747.4	1911.4	2130.2	2239.6	2411.6	2755.4	3013.2	3051.7
140°	1654.1	1716.3	1778.5	1794.1	1939.1	2132.4	2229.1	2377.5	2674.5	2897.3	2933.3
142.5°	1699.2	1756.8	1814.4	1828.7	1962.1	2140.1	2229.1	2359.5	2620.5	2816.1	2847.0
145°	1768.5	1818.7	1868.9	1881.4	1992.3	2140.1	2214.1	2320.8	2534.1	2694.1	2717.6
147.5°	1837.7	1886.5	1935.4	1947.6	2036.5	2154.9	2214.1	2298.0	2465.9	2591.8	2611.2
150°	1882.9	1927.1	1971.2	1982.3	2059.5	2162.5	2214.1	2285.0	2426.8	2533.1	2548.8
152.5°	1929.6	1963.0	1996.5	2004.9	2074.6	2167.6	2214.1	2274.6	2395.7	2486.5	2498.4
155°	1998.8	2023.6	2048.3	2054.5	2107.7	2178.6	2214.1	2262.2	2358.5	2430.7	2438.6
157.5°	2050.0	2074.0	2098.2	2104.2	2140.8	2189.6	2214.1	2251.5	2326.4	2382.6	2388.1
160°	2084.6	2103.3	2122.1	2126.8	2155.8	2194.7	2214.1	2246.1	2310.4	2358.5	2361.7
162.5°	2119.2	2133.3	2147.3	2150.8	2171.9	2200.0	2214.1	2241.2	2295.4	2336.0	2339.0
165°	2156.8	2169.5	2182.2	2185.4	2195.0	2207.7	2214.1	2233.4	2272.2	2301.3	2304.5
167.5°	2191.5	2197.5	2203.5	2205.0	2213.0	2223.8	2229.1	2241.8	2267.2	2286.3	2287.6
170°	2214.1	2220.1	2226.1	2227.5	2228.0	2228.7	2229.1	2241.8	2267.2	2286.3	2286.3
172.5°	2226.1	2227.4	2228.8	2229.1	2229.1	2229.1	2229.1	2239.2	2259.2	2274.2	2273.1
175°	2242.7	2242.7	2242.7	2242.7	2238.1	2232.1	2229.1	2235.5	2248.2	2257.7	2257.7
177.5°	2242.7	2242.7	2242.7	2242.7	2239.2	2234.4	2232.1	2237.1	2247.1	2254.7	2253.3
180°	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7	2242.7



TEST NUMBER: P938097

CATALOG NUMBER: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1194.5	1194.5
2.5°	1275.1	1267.5
5°	1640.0	1647.7
7.5°	2208.4	2204.6
10°	2746.1	2780.6
12.5°	3137.9	3145.6
15°	3376.0	3391.4
17.5°	3468.1	3472.0
20°	3472.0	3464.4
22.5°	3429.8	3422.1
25°	3379.9	3376.0
27.5°	3333.7	3337.6
30°	3314.6	3326.1
32.5°	3314.6	3333.7
35°	3322.2	3341.4
37.5°	3318.3	3341.4
40°	3303.0	3329.9
42.5°	3260.8	3280.0
45°	3195.5	3218.5
47.5°	3111.0	3126.4
50°	3003.4	3018.8
52.5°	2869.0	2872.9
55°	2707.7	2723.1
57.5°	2534.9	2538.7
60°	2342.8	2354.4
62.5°	2139.3	2139.3
65°	1924.2	1931.9
67.5°	1701.5	1720.7
70°	1474.8	1478.7
72.5°	1252.0	1252.0
75°	1021.6	1025.5
77.5°	802.7	802.7
80°	595.4	599.1
82.5°	411.0	418.6
85°	257.4	257.4
87.5°	119.1	107.6
90°	57.2	57.2
92.5°	229.1	183.6
95°	798.6	660.8
97.5°	1913.3	1651.1
100°	2756.7	2444.3
102.5°	3586.4	3318.8
105°	4644.1	4500.3
107.5°	5337.0	5371.7
110°	5601.2	5751.0

TEST NUMBER: P938097

CATALOG NUMBER: SQ4-FB-125U-100D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5624.8	5854.9
115°	5475.6	5794.7
117.5°	5159.3	5513.2
120°	4904.5	5248.3
122.5°	4656.3	4995.5
125°	4302.3	4614.7
127.5°	3983.8	4247.4
130°	3796.3	4039.8
132.5°	3626.0	3844.0
135°	3392.7	3580.6
137.5°	3205.5	3359.4
140°	3077.2	3221.0
142.5°	2970.8	3094.5
145°	2811.2	2904.9
147.5°	2688.8	2766.4
150°	2611.7	2674.6
152.5°	2545.9	2593.3
155°	2470.1	2501.5
157.5°	2410.2	2432.3
160°	2374.4	2387.1
162.5°	2351.0	2363.0
165°	2317.2	2330.0
167.5°	2292.9	2298.3
170°	2286.3	2286.3
172.5°	2268.3	2263.7
175°	2257.7	2257.7
177.5°	2248.0	2242.7
180°	2242.7	2242.7

(END OF REPORT)