

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938300

Luminaire Tested: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938300
REPORT IS A COMBINATION OF REPORTS P933645 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14809.3 lumens
Efficiency: N/A
Efficacy: 133.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 111.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938300

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P938300

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	30	30	21
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	26	25	24	24	24	17
2	83	75	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	20	20	14
3	75	66	59	53	66	59	53	48	45	40	37	32	29	27	20	18	17	17	17	12
4	69	58	50	45	60	52	45	40	39	35	31	28	25	23	17	16	14	14	14	10
5	63	51	44	38	55	46	39	34	35	30	27	25	22	19	15	14	12	12	12	8
6	57	46	38	32	51	41	34	29	31	26	23	22	19	17	14	12	11	11	11	7
7	53	41	33	28	47	37	30	25	28	23	20	20	17	14	12	11	9	9	9	6
8	49	37	30	24	43	33	27	22	25	21	17	18	15	13	11	9	8	8	8	5
9	45	34	26	21	40	30	24	19	23	18	15	16	13	11	10	9	7	7	7	5
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	6	6	6	4

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1875	1875	1875
5°	1832	2168	2521
10°	1662	3160	4179
15°	1413	4128	5046
20°	1150	4784	5143
25°	959	5006	5039
30°	808	5037	5029
35°	715	4954	5159
40°	623	4845	5294
45°	564	4765	5314
50°	518	4694	5226
55°	496	4589	4994
60°	508	4388	4628
65°	528	4081	4126
70°	563	3559	3486
75°	623	2902	2720
80°	681	2012	1832
85°	606	1068	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5314 cd/sqm

TEST NUMBER: P938300

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	0.4
10°-20°	231.7	1.6
20°-30°	405.3	2.7
30°-40°	521.8	3.5
40°-50°	582.8	3.9
50°-60°	558.2	3.8
60°-70°	442.4	3.0
70°-80°	260.1	1.8
80°-90°	79.1	0.5
90°-100°	877.9	5.9
100°-110°	2308.1	15.6
110°-120°	2393.2	16.2
120°-130°	1919.7	13.0
130°-140°	1506.3	10.2
140°-150°	1156.1	7.8
150°-160°	832.6	5.6
160°-170°	509.4	3.4
170°-180°	172.1	1.2
0°-30°	689.4	4.7
0°-40°	1211.2	8.2
0°-60°	2352.2	15.9
0°-90°	3133.9	21.2
90°-120°	5579.2	37.7
90°-150°	10161.3	68.6
90°-180°	11675.0	78.8
0°-180°	14809.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	404	404	404	404	404	
5°	394	422	476	538	558	36
15°	295	545	918	1112	1148	82
25°	188	617	1093	1141	1142	87
35°	127	590	1029	1088	1131	80
45°	87	470	910	1042	1089	67
55°	62	299	772	897	922	57
65°	49	158	573	645	654	49
75°	36	98	314	346	347	38
85°	13	30	78	86	87	14
90°	12	34	92	46	46	11
95°	116	454	1512	780	531	129
105°	416	630	2552	3874	3614	441
115°	739	897	2044	4077	4654	729
125°	1027	1152	1859	3142	3706	912
135°	1224	1348	1801	2536	2876	947
145°	1420	1511	1778	2164	2333	890
155°	1605	1650	1778	1952	2009	738
165°	1732	1755	1778	1848	1871	489
175°	1801	1801	1790	1813	1813	171
180°	1801	1801	1801	1801	1801	

TEST NUMBER: P938300

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	404.2	404.2	404.2	404.2	404.2	404.2	404.2	404.2	404.2	404.2	404.2
2.5°	404.2	404.2	406.8	408.1	410.7	412.0	414.6	417.3	425.0	426.3	428.9
5°	393.8	399.0	415.9	422.4	440.6	465.3	475.7	492.5	527.7	538.1	544.6
7.5°	378.2	389.9	431.5	441.9	487.4	552.3	579.7	616.1	671.9	699.2	721.3
10°	353.5	378.2	452.3	477.0	551.1	649.8	700.6	751.3	835.7	873.4	887.7
12.5°	326.3	366.5	474.4	508.1	614.7	759.0	820.2	876.0	972.2	1022.9	1030.6
15°	295.1	349.6	495.2	544.6	682.4	850.0	917.6	986.4	1076.2	1112.5	1121.6
17.5°	267.7	336.6	514.7	566.7	734.3	931.9	1000.8	1058.0	1130.7	1155.4	1161.9
20°	233.9	315.8	527.7	595.3	789.0	991.7	1058.0	1102.1	1151.6	1167.2	1169.8
22.5°	209.2	293.7	535.5	605.6	825.3	1028.1	1083.9	1119.1	1152.8	1158.1	1159.3
25°	188.5	269.0	534.2	617.3	856.5	1050.2	1093.0	1119.1	1138.6	1141.2	1141.2
27.5°	169.0	241.8	529.0	620.0	879.9	1055.3	1089.2	1107.4	1116.5	1121.6	1121.6
30°	152.0	215.8	516.0	614.7	890.3	1050.2	1077.4	1086.5	1095.6	1103.5	1107.4
32.5°	139.1	191.1	496.5	604.4	891.6	1037.1	1056.7	1061.8	1074.8	1093.0	1099.5
35°	127.3	166.4	474.4	590.0	883.8	1016.4	1029.4	1034.6	1060.6	1087.9	1096.9
37.5°	115.7	148.2	445.8	565.4	872.1	991.7	1000.8	1009.9	1050.2	1082.7	1093.0
40°	104.0	132.6	412.0	538.1	853.9	961.8	969.6	983.9	1037.1	1074.8	1085.3
42.5°	94.9	119.6	375.6	509.5	830.5	928.0	939.7	960.5	1021.6	1061.8	1073.6
45°	87.1	106.6	336.6	470.4	800.6	892.9	909.8	938.4	1003.4	1042.4	1052.7
47.5°	79.3	97.5	296.3	430.2	768.1	857.9	879.9	912.4	978.7	1016.4	1025.5
50°	72.8	88.4	256.0	387.3	733.0	820.2	846.1	879.9	947.5	982.6	994.3
52.5°	67.5	80.6	218.3	344.4	692.7	781.1	811.1	846.1	909.8	943.6	951.4
55°	62.4	74.1	185.9	298.9	651.2	739.5	772.0	805.8	868.2	896.8	902.0
57.5°	59.8	68.9	158.5	256.0	607.0	692.7	729.2	760.4	818.8	840.9	846.1
60°	55.9	65.0	137.8	219.7	558.9	648.6	679.8	711.0	760.4	778.5	782.5
62.5°	52.0	62.4	122.2	184.6	509.5	596.6	627.7	656.4	698.0	711.0	716.2
65°	49.4	59.8	110.5	158.5	458.8	542.0	573.2	597.9	631.7	644.7	647.3
67.5°	46.8	57.2	101.4	136.4	408.1	487.4	510.8	534.2	560.2	573.2	574.4
70°	42.9	54.6	93.6	120.8	356.1	425.0	444.5	469.2	490.0	496.5	500.4
72.5°	40.3	50.7	88.4	109.2	302.8	365.2	383.4	397.7	415.9	422.4	422.4
75°	36.4	45.4	83.1	97.5	248.3	298.9	314.5	328.8	343.1	345.7	341.9
77.5°	32.5	40.3	71.5	81.9	193.7	236.5	249.5	257.4	269.0	271.6	273.0
80°	27.3	35.1	55.9	63.7	140.4	174.1	183.2	189.7	200.2	200.2	202.7
82.5°	20.8	27.3	40.3	45.4	94.9	119.6	127.3	131.3	137.8	137.8	137.8
85°	13.0	16.9	26.0	29.8	57.2	72.8	78.0	79.3	84.5	85.8	85.8
87.5°	6.5	9.1	16.9	18.2	29.8	37.7	37.7	40.3	40.3	39.0	37.7
90°	12.1	21.8	31.4	33.8	53.2	79.0	91.9	81.7	61.2	45.9	45.9
92.5°	48.4	130.5	212.8	233.3	328.0	454.3	517.3	453.4	325.6	229.7	220.5
95°	116.1	266.5	416.9	454.5	807.0	1277.0	1512.1	1349.3	1023.8	779.7	751.9
97.5°	200.7	333.3	466.1	499.2	1087.1	1870.9	2262.8	2159.9	1954.2	1799.8	1747.2
100°	265.9	386.2	506.6	536.7	1189.1	2058.7	2493.6	2501.2	2516.2	2527.4	2464.7
102.5°	321.5	433.8	546.0	574.1	1235.8	2117.8	2558.9	2690.0	2952.2	3148.8	3095.1
105°	415.8	510.9	606.0	629.8	1270.4	2124.5	2551.7	2845.6	3433.3	3874.1	3845.2
107.5°	512.5	601.2	689.7	711.9	1276.9	2030.1	2406.6	2816.5	3636.4	4251.2	4258.2
110°	577.8	657.9	737.9	757.9	1267.2	1946.2	2285.8	2744.0	3660.5	4347.9	4377.9

TEST NUMBER: P938300

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	641.9	718.1	794.4	813.5	1267.5	1873.0	2175.7	2644.7	3582.7	4286.2	4332.4
115°	738.6	808.9	879.3	896.9	1279.3	1789.1	2044.0	2495.8	3399.3	4077.1	4141.1
117.5°	834.0	898.0	961.9	977.9	1303.0	1736.5	1953.3	2361.1	3176.6	3788.2	3859.2
120°	889.6	949.8	1010.0	1025.0	1322.4	1718.8	1917.1	2289.7	3034.8	3593.6	3662.6
122.5°	944.0	1004.8	1065.4	1080.6	1350.2	1709.6	1889.3	2224.7	2895.8	3399.0	3467.1
125°	1027.4	1082.8	1138.1	1151.9	1387.6	1701.9	1859.0	2144.0	2714.0	3141.5	3204.2
127.5°	1095.2	1151.0	1206.9	1220.8	1425.1	1697.5	1833.6	2078.3	2567.8	2934.8	2987.7
130°	1131.4	1191.6	1251.8	1266.8	1452.5	1700.1	1823.9	2041.8	2477.5	2804.3	2853.2
132.5°	1168.9	1229.1	1289.3	1304.3	1474.7	1702.0	1815.5	2010.5	2400.5	2693.0	2736.8
135°	1224.4	1279.3	1334.1	1347.8	1498.8	1700.3	1801.0	1964.4	2291.0	2536.0	2573.7
137.5°	1281.3	1335.6	1389.7	1403.3	1535.1	1710.8	1798.7	1936.7	2212.8	2419.9	2450.8
140°	1328.4	1378.4	1428.3	1440.8	1557.3	1712.5	1790.1	1909.4	2148.0	2326.9	2355.7
142.5°	1364.6	1410.9	1457.1	1468.6	1575.8	1718.7	1790.1	1894.9	2104.4	2261.5	2286.4
145°	1420.3	1460.6	1500.9	1511.0	1600.0	1718.7	1778.0	1863.7	2035.1	2163.7	2182.5
147.5°	1475.9	1515.1	1554.4	1564.2	1635.5	1730.5	1778.0	1845.5	1980.2	2081.4	2097.0
150°	1512.1	1547.6	1583.1	1591.9	1653.9	1736.6	1778.0	1835.0	1948.9	2034.3	2046.9
152.5°	1549.6	1576.5	1603.4	1610.1	1666.1	1740.7	1778.0	1826.7	1923.9	1996.8	2006.3
155°	1605.2	1625.1	1645.0	1649.9	1692.6	1749.5	1778.0	1816.7	1894.1	1952.1	1958.4
157.5°	1646.3	1665.7	1685.0	1689.8	1719.2	1758.4	1778.0	1808.2	1868.3	1913.5	1917.9
160°	1674.1	1689.2	1704.2	1708.0	1731.3	1762.4	1778.0	1803.8	1855.4	1894.1	1896.6
162.5°	1702.0	1713.2	1724.5	1727.3	1744.2	1766.8	1778.0	1799.8	1843.3	1876.0	1878.4
165°	1732.1	1742.3	1752.5	1755.1	1762.7	1772.9	1778.0	1793.6	1824.8	1848.2	1850.7
167.5°	1759.9	1764.7	1769.6	1770.8	1777.2	1785.9	1790.1	1800.3	1820.8	1836.1	1837.1
170°	1778.0	1782.9	1787.7	1789.0	1789.4	1789.8	1790.1	1800.3	1820.8	1836.1	1836.1
172.5°	1787.7	1788.8	1789.8	1790.1	1790.1	1790.1	1790.1	1798.2	1814.3	1826.4	1825.4
175°	1801.0	1801.0	1801.0	1801.0	1797.4	1792.6	1790.1	1795.3	1805.4	1813.1	1813.1
177.5°	1801.0	1801.0	1801.0	1801.0	1798.2	1794.4	1792.6	1796.6	1804.7	1810.7	1809.6
180°	1801.0	1801.0	1801.0	1801.0	1801.0	1801.0	1801.0	1801.0	1801.0	1801.0	1801.0

TEST NUMBER: P938300

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	404.2	404.2
2.5°	431.5	428.9
5°	554.9	557.6
7.5°	747.3	746.0
10°	929.3	941.0
12.5°	1061.8	1064.4
15°	1142.5	1147.7
17.5°	1173.7	1174.9
20°	1174.9	1172.3
22.5°	1160.7	1158.1
25°	1143.7	1142.5
27.5°	1128.1	1129.5
30°	1121.6	1125.6
32.5°	1121.6	1128.1
35°	1124.2	1130.7
37.5°	1123.0	1130.7
40°	1117.7	1126.9
42.5°	1103.5	1110.0
45°	1081.4	1089.2
47.5°	1052.7	1058.0
50°	1016.4	1021.6
52.5°	970.8	972.2
55°	916.3	921.5
57.5°	857.9	859.1
60°	792.8	796.7
62.5°	723.9	723.9
65°	651.2	653.8
67.5°	575.8	582.3
70°	499.1	500.4
72.5°	423.7	423.7
75°	345.7	347.0
77.5°	271.6	271.6
80°	201.5	202.7
82.5°	139.1	141.7
85°	87.1	87.1
87.5°	40.3	36.4
90°	45.9	45.9
92.5°	184.0	147.5
95°	641.3	530.6
97.5°	1536.5	1326.0
100°	2213.9	1963.0
102.5°	2880.2	2665.3
105°	3729.7	3614.2
107.5°	4286.1	4314.0
110°	4498.3	4618.6

TEST NUMBER: P938300

CATALOG NUMBER: SQ4-FB-150U-050D-B35-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4517.2	4702.0
115°	4397.4	4653.6
117.5°	4143.4	4427.7
120°	3938.8	4214.9
122.5°	3739.5	4011.9
125°	3455.2	3706.0
127.5°	3199.4	3411.1
130°	3048.8	3244.3
132.5°	2911.9	3087.1
135°	2724.6	2875.6
137.5°	2574.3	2697.9
140°	2471.2	2586.7
142.5°	2385.8	2485.2
145°	2257.7	2332.9
147.5°	2159.3	2221.6
150°	2097.5	2148.0
152.5°	2044.5	2082.7
155°	1983.7	2008.9
157.5°	1935.6	1953.3
160°	1906.9	1917.1
162.5°	1888.0	1897.7
165°	1861.0	1871.1
167.5°	1841.5	1845.8
170°	1836.1	1836.1
172.5°	1821.7	1817.9
175°	1813.1	1813.1
177.5°	1805.2	1801.0
180°	1801.0	1801.0

(END OF REPORT)