

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938504

Luminaire Tested: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938504
REPORT IS A COMBINATION OF REPORTS P933647 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17585.4 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 144.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938504

CATALOG NUMBER: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P938504

CATALOG NUMBER: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42
1	94	90	86	82	85	81	78	75	65	63	60	50	49	47	36	35	35
2	85	78	72	66	77	70	65	61	56	53	49	43	41	39	32	30	29
3	77	68	61	55	69	61	55	50	49	45	41	38	35	32	28	26	24
4	71	60	52	46	63	54	47	42	43	38	34	34	30	27	24	22	20
5	64	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17
6	59	47	39	33	53	43	36	30	34	29	25	27	23	20	19	17	15
7	54	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	13	11
9	47	35	27	22	42	31	25	20	26	20	17	20	16	14	15	12	10
10	43	31	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3642	3642	3642
5°	3558	4209	4895
10°	3227	6135	8115
15°	2743	8015	9799
20°	2233	9289	9986
25°	1863	9720	9783
30°	1571	9782	9765
35°	1389	9619	10017
40°	1210	9408	10278
45°	1096	9254	10319
50°	1005	9115	10147
55°	962	8911	9698
60°	985	8519	8988
65°	1025	7925	8012
70°	1092	6911	6768
75°	1211	5634	5282
80°	1322	3907	3559
85°	1174	2074	1822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10319 cd/sqm

TEST NUMBER: P938504

CATALOG NUMBER: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	0.6
10°-20°	450.0	2.6
20°-30°	787.1	4.5
30°-40°	1013.2	5.8
40°-50°	1131.7	6.4
50°-60°	1083.9	6.2
60°-70°	859.0	4.9
70°-80°	505.1	2.9
80°-90°	147.1	0.8
90°-100°	865.2	4.9
100°-110°	2274.7	12.9
110°-120°	2358.7	13.4
120°-130°	1891.9	10.8
130°-140°	1484.5	8.4
140°-150°	1139.4	6.5
150°-160°	820.6	4.7
160°-170°	502.1	2.9
170°-180°	169.6	1.0
0°-30°	1338.6	7.6
0°-40°	2351.8	13.4
0°-60°	4567.4	26.0
0°-90°	6078.7	34.6
90°-120°	5498.6	31.3
90°-150°	10014.5	56.9
90°-180°	11507.0	65.4
0°-180°	17585.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	785	785	785	785	785	
5°	765	820	924	1045	1083	71
15°	573	1058	1782	2160	2228	159
25°	366	1199	2122	2216	2218	169
35°	247	1146	1999	2112	2196	154
45°	169	914	1767	2024	2115	131
55°	121	580	1499	1741	1789	110
65°	96	308	1113	1252	1270	95
75°	71	189	611	671	674	74
85°	25	58	152	167	169	27
90°	12	33	90	45	45	12
95°	114	448	1490	768	523	127
105°	410	621	2515	3818	3562	434
115°	728	884	2014	4018	4586	719
125°	1013	1135	1832	3096	3652	899
135°	1207	1328	1775	2499	2834	934
145°	1400	1489	1752	2132	2299	877
155°	1582	1626	1752	1924	1980	727
165°	1707	1730	1752	1822	1844	482
175°	1775	1775	1764	1787	1787	168
180°	1775	1775	1775	1775	1775	

TEST NUMBER: P938504

CATALOG NUMBER: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9
2.5°	784.9	784.9	790.0	792.5	797.5	800.0	805.1	810.1	825.3	827.8	832.9
5°	764.7	774.8	807.6	820.2	855.6	903.5	923.7	956.5	1024.6	1044.9	1057.5
7.5°	734.4	757.1	837.9	858.1	946.4	1072.6	1125.6	1196.2	1304.8	1357.8	1400.7
10°	686.5	734.4	878.3	926.3	1070.1	1261.8	1360.3	1458.8	1622.7	1696.0	1723.7
12.5°	633.5	711.7	921.2	986.8	1193.8	1473.9	1592.5	1701.0	1887.7	1986.2	2001.3
15°	572.9	678.9	961.6	1057.5	1325.0	1650.5	1781.7	1915.5	2089.6	2160.3	2178.0
17.5°	519.9	653.7	999.4	1100.4	1425.9	1809.5	1943.3	2054.3	2195.6	2243.6	2256.3
20°	454.3	613.3	1024.6	1155.8	1531.9	1925.7	2054.3	2140.2	2236.0	2266.3	2271.4
22.5°	406.4	570.3	1039.8	1176.1	1602.6	1996.3	2104.8	2172.9	2238.6	2248.6	2251.2
25°	366.0	522.4	1037.2	1198.8	1663.1	2039.2	2122.5	2172.9	2210.8	2215.9	2215.9
27.5°	328.0	469.4	1027.2	1203.9	1708.6	2049.3	2114.9	2150.3	2167.9	2178.0	2178.0
30°	295.3	419.0	1001.9	1193.8	1728.7	2039.2	2092.2	2109.9	2127.5	2142.6	2150.3
32.5°	270.1	371.0	964.1	1173.5	1731.3	2014.0	2051.8	2061.9	2087.2	2122.5	2135.1
35°	247.3	323.1	921.2	1145.8	1716.1	1973.6	1998.8	2008.9	2059.4	2112.4	2130.0
37.5°	224.6	287.7	865.6	1097.9	1693.4	1925.7	1943.3	1961.0	2039.2	2102.2	2122.5
40°	201.9	257.5	800.0	1044.9	1658.1	1867.6	1882.7	1910.5	2014.0	2087.2	2107.3
42.5°	184.2	232.2	729.3	989.3	1612.7	1802.0	1824.7	1865.0	1983.6	2061.9	2084.7
45°	169.1	206.9	653.7	913.6	1554.6	1733.8	1766.7	1822.1	1948.3	2024.0	2044.3
47.5°	153.9	189.3	575.4	835.3	1491.5	1665.7	1708.6	1771.7	1900.4	1973.6	1991.3
50°	141.3	171.6	497.2	752.1	1423.4	1592.5	1643.0	1708.6	1839.8	1908.0	1930.6
52.5°	131.2	156.4	424.0	668.8	1345.1	1516.7	1574.8	1643.0	1766.7	1832.3	1847.4
55°	121.1	143.8	360.9	580.4	1264.4	1436.0	1499.1	1564.8	1685.9	1741.3	1751.5
57.5°	116.1	133.8	307.9	497.2	1178.6	1345.1	1415.8	1476.4	1590.0	1632.9	1643.0
60°	108.5	126.2	267.5	426.5	1085.3	1259.4	1319.9	1380.5	1476.4	1511.8	1519.3
62.5°	100.9	121.1	237.2	358.4	989.3	1158.4	1219.0	1274.5	1355.2	1380.5	1390.6
65°	95.9	116.1	214.5	307.9	890.9	1052.4	1113.0	1160.9	1226.5	1251.8	1256.9
67.5°	90.8	111.1	196.8	265.0	792.5	946.4	991.9	1037.2	1087.7	1113.0	1115.5
70°	83.3	106.0	181.7	234.7	691.5	825.3	863.1	911.1	951.5	964.1	971.6
72.5°	78.2	98.5	171.6	212.0	588.0	709.2	744.5	772.3	807.6	820.2	820.2
75°	70.7	88.3	161.5	189.3	482.1	580.4	610.7	638.5	666.3	671.4	663.7
77.5°	63.1	78.2	138.8	159.0	376.1	459.4	484.6	499.7	522.4	527.4	530.0
80°	53.0	68.2	108.5	123.7	272.6	338.2	355.8	368.4	388.7	388.7	393.7
82.5°	40.4	53.0	78.2	88.3	184.2	232.2	247.3	254.9	267.5	267.5	267.5
85°	25.2	32.9	50.5	58.1	111.1	141.3	151.5	153.9	164.1	166.6	166.6
87.5°	12.6	17.7	32.9	35.3	58.1	73.2	73.2	78.2	78.2	75.7	73.2
90°	11.9	21.5	30.9	33.3	52.4	77.8	90.5	80.5	60.4	45.3	45.3
92.5°	47.7	128.6	209.7	230.0	323.3	447.7	509.9	446.8	320.9	226.3	217.4
95°	114.4	262.6	410.8	447.9	795.3	1258.6	1490.3	1329.8	1009.1	768.4	741.1
97.5°	197.8	328.5	459.4	492.0	1071.4	1843.9	2230.1	2128.7	1925.9	1773.8	1722.0
100°	262.1	380.7	499.3	529.0	1171.9	2029.0	2457.6	2465.0	2479.8	2490.9	2429.1
102.5°	316.9	427.6	538.1	565.8	1217.9	2087.2	2522.0	2651.2	2909.5	3103.3	3050.4
105°	409.8	503.5	597.3	620.7	1252.0	2093.8	2514.8	2804.5	3383.7	3818.1	3789.6
107.5°	505.1	592.5	679.8	701.6	1258.4	2000.7	2371.8	2775.8	3583.8	4189.8	4196.7
110°	569.5	648.3	727.2	746.9	1248.9	1918.1	2252.7	2704.4	3607.6	4285.1	4314.7

TEST NUMBER: P938504

CATALOG NUMBER: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	632.6	707.8	782.9	801.7	1249.2	1845.9	2144.3	2606.5	3530.9	4224.3	4269.8
115°	727.9	797.2	866.6	883.9	1260.8	1763.2	2014.5	2459.7	3350.2	4018.2	4081.3
117.5°	822.0	885.0	948.0	963.8	1284.2	1711.5	1925.1	2327.0	3130.7	3733.5	3803.5
120°	876.8	936.1	995.4	1010.2	1303.3	1694.0	1889.4	2256.6	2991.0	3541.7	3609.7
122.5°	930.4	990.2	1050.0	1065.0	1330.7	1684.9	1862.0	2192.6	2853.9	3349.9	3417.0
125°	1012.6	1067.1	1121.6	1135.3	1367.6	1677.3	1832.2	2113.0	2674.8	3096.1	3157.9
127.5°	1079.3	1134.3	1189.5	1203.2	1404.5	1673.0	1807.1	2048.3	2530.7	2892.4	2944.6
130°	1115.1	1174.4	1233.7	1248.5	1431.5	1675.5	1797.6	2012.3	2441.7	2763.8	2812.0
132.5°	1152.0	1211.3	1270.6	1285.4	1453.4	1677.4	1789.3	1981.4	2365.8	2654.1	2697.3
135°	1206.7	1260.8	1314.8	1328.3	1477.2	1675.7	1775.0	1936.0	2257.9	2499.3	2536.5
137.5°	1262.8	1316.3	1369.7	1383.0	1512.9	1686.1	1772.7	1908.8	2180.8	2384.9	2415.4
140°	1309.2	1358.5	1407.7	1420.0	1534.8	1687.8	1764.3	1881.8	2116.9	2293.2	2321.7
142.5°	1344.9	1390.5	1436.0	1447.4	1553.0	1693.9	1764.3	1867.5	2074.0	2228.9	2253.3
145°	1399.7	1439.5	1479.2	1489.1	1576.9	1693.9	1752.3	1836.8	2005.7	2132.4	2150.9
147.5°	1454.6	1493.2	1531.9	1541.6	1611.8	1705.5	1752.3	1818.8	1951.6	2051.3	2066.7
150°	1490.3	1525.2	1560.2	1568.9	1630.0	1711.6	1752.3	1808.5	1920.7	2004.9	2017.3
152.5°	1527.2	1553.7	1580.2	1586.8	1642.0	1715.6	1752.3	1800.3	1896.1	1968.0	1977.3
155°	1582.1	1601.6	1621.2	1626.1	1668.2	1724.3	1752.3	1790.4	1866.7	1923.9	1930.2
157.5°	1622.5	1641.6	1660.6	1665.4	1694.4	1733.0	1752.3	1782.0	1841.3	1885.8	1890.2
160°	1650.0	1664.8	1679.6	1683.3	1706.3	1737.0	1752.3	1777.7	1828.6	1866.7	1869.2
162.5°	1677.4	1688.4	1699.6	1702.4	1719.0	1741.3	1752.3	1773.8	1816.7	1848.9	1851.3
165°	1707.1	1717.1	1727.2	1729.7	1737.2	1747.3	1752.3	1767.7	1798.5	1821.5	1824.0
167.5°	1734.5	1739.2	1744.0	1745.3	1751.6	1760.1	1764.3	1774.3	1794.4	1809.5	1810.6
170°	1752.3	1757.1	1761.9	1763.1	1763.5	1764.0	1764.3	1774.3	1794.4	1809.5	1809.5
172.5°	1761.9	1762.9	1764.0	1764.3	1764.3	1764.3	1764.3	1772.2	1788.0	1800.0	1799.0
175°	1775.0	1775.0	1775.0	1775.0	1771.4	1766.7	1764.3	1769.3	1779.4	1786.9	1786.9
177.5°	1775.0	1775.0	1775.0	1775.0	1772.2	1768.5	1766.7	1770.7	1778.6	1784.5	1783.5
180°	1775.0	1775.0	1775.0	1775.0	1775.0	1775.0	1775.0	1775.0	1775.0	1775.0	1775.0

TEST NUMBER: P938504

CATALOG NUMBER: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	784.9	784.9
2.5°	837.9	832.9
5°	1077.6	1082.7
7.5°	1451.1	1448.6
10°	1804.5	1827.2
12.5°	2061.9	2067.0
15°	2218.4	2228.5
17.5°	2278.9	2281.5
20°	2281.5	2276.4
22.5°	2253.7	2248.6
25°	2220.9	2218.4
27.5°	2190.6	2193.2
30°	2178.0	2185.6
32.5°	2178.0	2190.6
35°	2183.0	2195.6
37.5°	2180.6	2195.6
40°	2170.4	2188.1
42.5°	2142.6	2155.2
45°	2099.8	2114.9
47.5°	2044.3	2054.3
50°	1973.6	1983.6
52.5°	1885.3	1887.7
55°	1779.3	1789.4
57.5°	1665.7	1668.2
60°	1539.5	1547.1
62.5°	1405.8	1405.8
65°	1264.4	1269.5
67.5°	1118.0	1130.6
70°	969.1	971.6
72.5°	822.7	822.7
75°	671.4	673.8
77.5°	527.4	527.4
80°	391.2	393.7
82.5°	270.1	275.1
85°	169.1	169.1
87.5°	78.2	70.7
90°	45.3	45.3
92.5°	181.4	145.4
95°	632.0	523.0
97.5°	1514.3	1306.8
100°	2181.9	1934.6
102.5°	2838.5	2626.8
105°	3675.8	3562.0
107.5°	4224.2	4251.7
110°	4433.3	4551.9

TEST NUMBER: P938504

CATALOG NUMBER: SQ4-FB-150U-100D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4451.9	4634.0
115°	4333.9	4586.4
117.5°	4083.6	4363.7
120°	3881.9	4154.0
122.5°	3685.4	3953.9
125°	3405.2	3652.5
127.5°	3153.2	3361.8
130°	3004.7	3197.4
132.5°	2869.9	3042.5
135°	2685.3	2834.1
137.5°	2537.1	2658.9
140°	2435.5	2549.4
142.5°	2351.3	2449.3
145°	2225.1	2299.2
147.5°	2128.1	2189.5
150°	2067.2	2116.9
152.5°	2015.0	2052.6
155°	1955.1	1979.9
157.5°	1907.6	1925.1
160°	1879.3	1889.4
162.5°	1860.7	1870.3
165°	1834.1	1844.1
167.5°	1814.9	1819.1
170°	1809.5	1809.5
172.5°	1795.4	1791.7
175°	1786.9	1786.9
177.5°	1779.2	1775.0
180°	1775.0	1775.0

(END OF REPORT)