

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938597

Luminaire Tested: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938597
REPORT IS A COMBINATION OF REPORTS P933624 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 29358.7 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 249.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938597

CATALOG NUMBER: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P938597

CATALOG NUMBER: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47
1	95	91	87	83	86	83	79	76	68	65	63	54	52	51	41	40	39
2	86	79	72	67	78	72	66	62	59	55	51	47	44	42	36	34	32
3	78	69	61	55	71	63	56	51	51	47	43	41	37	35	31	29	27
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	27	25	23
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	22	19
6	60	48	39	34	54	44	36	31	36	30	26	29	25	21	22	19	17
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15
8	51	39	31	25	46	35	28	24	29	24	20	23	19	16	18	15	13
9	47	35	27	22	43	32	25	21	27	21	18	21	17	15	17	14	11
10	44	32	25	20	40	29	23	18	24	19	16	20	16	13	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4732	4732	4732
5°	4624	5471	6361
10°	4197	7977	10545
15°	3568	10424	12733
20°	2906	12082	12977
25°	2425	12647	12713
30°	2046	12730	12689
35°	1810	12522	13017
40°	1578	12251	13357
45°	1430	12053	13409
50°	1313	11876	13187
55°	1258	11615	12602
60°	1290	11110	11679
65°	1344	10340	10411
70°	1435	9024	8795
75°	1596	7364	6864
80°	1757	5113	4625
85°	1594	2718	2367

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 13409 cd/sqm

TEST NUMBER: P938597

CATALOG NUMBER: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	197.9	0.7
10°-20°	877.1	3.0
20°-30°	1534.2	5.2
30°-40°	1974.9	6.7
40°-50°	2205.9	7.5
50°-60°	2112.8	7.2
60°-70°	1674.4	5.7
70°-80°	984.6	3.4
80°-90°	283.8	1.0
90°-100°	1316.9	4.5
100°-110°	3462.1	11.8
110°-120°	3589.9	12.2
120°-130°	2879.5	9.8
130°-140°	2259.4	7.7
140°-150°	1734.2	5.9
150°-160°	1248.9	4.3
160°-170°	764.1	2.6
170°-180°	258.2	0.9
0°-30°	2609.2	8.9
0°-40°	4584.1	15.6
0°-60°	8902.9	30.3
0°-90°	11845.7	40.3
90°-120°	8368.8	28.5
90°-150°	15241.9	51.9
90°-180°	17513.0	59.7
0°-180°	29358.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1530	1530	1530	1530	1530	
5°	1490	1599	1800	2037	2110	138
15°	1117	2061	3473	4211	4344	311
25°	713	2337	4137	4319	4324	329
35°	482	2233	3896	4118	4280	301
45°	330	1781	3444	3945	4122	255
55°	236	1131	2922	3394	3488	215
65°	187	600	2169	2440	2474	185
75°	138	369	1190	1308	1314	144
85°	49	113	295	325	330	52
90°	18	51	138	69	69	18
95°	174	682	2268	1170	796	193
105°	624	945	3828	5811	5421	661
115°	1108	1345	3066	6116	6980	1094
125°	1541	1728	2789	4712	5559	1368
135°	1837	2022	2702	3804	4313	1421
145°	2130	2266	2667	3246	3499	1335
155°	2408	2475	2667	2928	3013	1106
165°	2598	2633	2667	2772	2807	733
175°	2702	2702	2685	2720	2720	256
180°	2702	2702	2702	2702	2702	

TEST NUMBER: P938597

CATALOG NUMBER: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0	1530.0
2.5°	1530.0	1530.0	1539.7	1544.7	1554.5	1559.4	1569.3	1579.1	1608.6	1613.6	1623.4
5°	1490.5	1510.2	1574.1	1598.8	1667.6	1761.2	1800.5	1864.5	1997.2	2036.6	2061.2
7.5°	1431.5	1475.8	1633.2	1672.6	1844.8	2090.7	2194.0	2331.8	2543.3	2646.6	2730.3
10°	1338.1	1431.5	1711.9	1805.3	2085.8	2459.6	2651.5	2843.3	3163.1	3305.7	3359.9
12.5°	1234.8	1387.2	1795.6	1923.5	2326.9	2872.9	3104.1	3315.6	3679.7	3871.5	3901.0
15°	1116.7	1323.3	1874.2	2061.2	2582.7	3217.3	3473.0	3733.8	4073.2	4211.0	4245.4
17.5°	1013.4	1274.1	1948.1	2144.8	2779.4	3527.2	3787.9	4004.3	4279.8	4373.3	4397.9
20°	885.5	1195.4	1997.2	2253.0	2986.1	3753.4	4004.3	4171.5	4358.6	4417.6	4427.4
22.5°	792.0	1111.7	2026.8	2292.4	3123.8	3891.2	4102.7	4235.5	4363.4	4383.1	4388.0
25°	713.3	1018.3	2021.8	2336.6	3241.8	3974.8	4137.1	4235.5	4309.3	4319.1	4319.1
27.5°	639.5	915.0	2002.1	2346.5	3330.4	3994.5	4122.4	4191.2	4225.7	4245.4	4245.4
30°	575.6	816.6	1952.9	2326.9	3369.7	3974.8	4078.1	4112.5	4147.0	4176.5	4191.2
32.5°	526.4	723.2	1879.2	2287.5	3374.6	3925.6	3999.5	4019.1	4068.2	4137.1	4161.8
35°	482.1	629.7	1795.6	2233.4	3345.2	3846.9	3896.1	3915.8	4014.2	4117.5	4151.9
37.5°	437.8	560.8	1687.3	2139.9	3300.9	3753.4	3787.9	3822.3	3974.8	4097.8	4137.1
40°	393.5	501.7	1559.4	2036.6	3232.0	3640.3	3669.8	3724.0	3925.6	4068.2	4107.6
42.5°	359.1	452.6	1421.7	1928.4	3143.4	3512.4	3556.7	3635.4	3866.6	4019.1	4063.4
45°	329.6	403.4	1274.1	1780.8	3030.3	3379.6	3443.5	3551.8	3797.7	3945.3	3984.6
47.5°	300.1	369.0	1121.6	1628.3	2907.3	3246.7	3330.4	3453.3	3704.3	3846.9	3881.3
50°	275.5	334.5	969.1	1466.0	2774.5	3104.1	3202.4	3330.4	3586.2	3719.0	3763.3
52.5°	255.8	305.0	826.5	1303.6	2622.0	2956.5	3069.7	3202.4	3443.5	3571.4	3600.9
55°	236.1	280.4	703.5	1131.4	2464.6	2799.1	2922.1	3050.0	3286.1	3394.3	3414.0
57.5°	226.3	260.8	600.2	969.1	2297.3	2622.0	2759.7	2877.8	3099.2	3182.8	3202.4
60°	211.5	245.9	521.4	831.4	2115.3	2454.8	2572.8	2690.9	2877.8	2946.6	2961.5
62.5°	196.8	236.1	462.4	698.6	1928.4	2258.0	2376.0	2484.2	2641.7	2690.9	2710.6
65°	186.9	226.3	418.1	600.2	1736.5	2051.4	2169.4	2262.9	2390.8	2439.9	2449.8
67.5°	177.1	216.5	383.7	516.6	1544.7	1844.8	1933.3	2021.8	2120.3	2169.4	2174.3
70°	162.3	206.6	354.2	457.5	1347.9	1608.6	1682.4	1775.9	1854.6	1879.2	1893.9
72.5°	152.5	191.9	334.5	413.2	1146.2	1382.4	1451.2	1505.3	1574.1	1598.8	1598.8
75°	137.7	172.2	314.8	369.0	939.5	1131.4	1190.5	1244.6	1298.7	1308.5	1293.8
77.5°	123.0	152.5	270.5	309.9	733.0	895.4	944.5	974.0	1018.3	1028.1	1033.1
80°	103.3	132.8	211.5	241.1	531.3	659.2	693.6	718.2	757.6	757.6	767.4
82.5°	78.7	103.3	152.5	172.2	359.1	452.6	482.1	496.8	521.4	521.4	521.4
85°	49.2	64.0	98.4	113.2	216.5	275.5	295.2	300.1	319.8	324.7	324.7
87.5°	24.6	34.4	64.0	68.9	113.2	142.6	142.6	152.5	152.5	147.6	142.6
90°	18.1	32.7	47.2	50.8	79.7	118.4	137.8	122.5	91.9	68.9	68.9
92.5°	72.5	195.7	319.1	349.9	492.0	681.3	776.0	680.0	488.3	344.5	330.8
95°	174.0	399.6	625.3	681.7	1210.6	1915.7	2268.2	2024.0	1535.8	1169.5	1128.0
97.5°	301.0	500.0	699.0	748.8	1630.6	2806.3	3394.1	3239.9	2931.2	2699.7	2620.8
100°	398.8	579.4	759.9	805.0	1783.5	3088.1	3740.4	3751.7	3774.3	3791.2	3697.1
102.5°	482.3	650.7	819.1	861.2	1853.6	3176.8	3838.4	4035.0	4428.2	4723.2	4642.6
105°	623.7	766.4	909.0	944.7	1905.6	3186.8	3827.5	4268.3	5149.8	5811.0	5767.7
107.5°	768.8	901.8	1034.7	1067.9	1915.2	3045.0	3609.9	4224.7	5454.4	6376.7	6387.2
110°	866.7	986.7	1106.8	1136.8	1900.8	2919.3	3428.6	4116.0	5490.7	6521.8	6566.9

TEST NUMBER: P938597

CATALOG NUMBER: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	962.8	1077.2	1191.7	1220.3	1901.4	2809.5	3263.6	3967.1	5374.1	6429.3	6498.6
115°	1107.9	1213.4	1319.0	1345.4	1918.9	2683.6	3066.0	3743.7	5099.1	6115.6	6211.8
117.5°	1251.1	1346.9	1442.8	1466.8	1954.5	2604.8	2930.0	3541.6	4764.9	5682.3	5788.9
120°	1334.4	1424.7	1514.9	1537.5	1983.5	2578.2	2875.6	3434.4	4552.1	5390.4	5493.9
122.5°	1416.0	1507.1	1598.2	1620.9	2025.3	2564.4	2833.9	3337.1	4343.6	5098.5	5200.6
125°	1541.2	1624.1	1707.2	1727.9	2081.5	2552.9	2788.6	3216.1	4071.1	4712.2	4806.3
127.5°	1642.6	1726.5	1810.3	1831.2	2137.6	2546.2	2750.5	3117.6	3851.7	4402.3	4481.6
130°	1697.1	1787.3	1877.5	1900.1	2178.7	2550.2	2736.0	3062.7	3716.3	4206.4	4279.8
132.5°	1753.3	1843.5	1933.7	1956.3	2211.9	2552.8	2723.3	3015.8	3600.9	4039.7	4105.4
135°	1836.6	1918.8	2001.1	2021.6	2248.3	2550.5	2701.6	2946.5	3436.5	3803.9	3860.5
137.5°	1921.9	2003.3	2084.7	2105.1	2302.6	2566.1	2697.9	2905.0	3319.2	3629.9	3676.2
140°	1992.7	2067.6	2142.6	2161.3	2335.9	2568.7	2685.2	2864.1	3221.9	3490.2	3533.6
142.5°	2047.0	2116.3	2185.6	2202.9	2363.7	2578.0	2685.2	2842.4	3156.6	3392.4	3429.7
145°	2130.4	2190.9	2251.3	2266.4	2399.9	2578.0	2667.1	2795.6	3052.6	3245.5	3273.7
147.5°	2213.8	2272.6	2331.4	2346.1	2453.1	2595.8	2667.1	2768.2	2970.5	3122.2	3145.6
150°	2268.2	2321.4	2374.6	2387.9	2480.9	2605.1	2667.1	2752.5	2923.4	3051.5	3070.4
152.5°	2324.4	2364.7	2405.0	2415.0	2499.1	2611.1	2667.1	2740.0	2885.9	2995.3	3009.6
155°	2407.9	2437.7	2467.5	2474.9	2539.0	2624.3	2667.1	2725.1	2841.2	2928.2	2937.7
157.5°	2469.5	2498.5	2527.4	2534.7	2578.8	2637.6	2667.1	2712.2	2802.4	2870.2	2876.9
160°	2511.2	2533.7	2556.3	2561.9	2597.0	2643.7	2667.1	2705.7	2783.1	2841.1	2845.0
162.5°	2552.8	2569.8	2586.6	2590.9	2616.3	2650.1	2667.1	2699.7	2765.0	2814.0	2817.6
165°	2598.2	2613.5	2628.8	2632.7	2644.1	2659.4	2667.1	2690.4	2737.1	2772.2	2776.1
167.5°	2639.9	2647.2	2654.4	2656.2	2665.9	2678.8	2685.2	2700.5	2731.1	2754.1	2755.7
170°	2667.1	2674.3	2681.6	2683.5	2684.0	2684.8	2685.2	2700.5	2731.1	2754.1	2754.1
172.5°	2681.6	2683.2	2684.8	2685.2	2685.2	2685.2	2685.2	2697.3	2721.5	2739.7	2738.2
175°	2701.6	2701.6	2701.6	2701.6	2696.1	2688.9	2685.2	2692.9	2708.2	2719.7	2719.7
177.5°	2701.6	2701.6	2701.6	2701.6	2697.3	2691.7	2688.9	2694.9	2707.0	2716.0	2714.4
180°	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6	2701.6

TEST NUMBER: P938597

CATALOG NUMBER: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1530.0	1530.0
2.5°	1633.2	1623.4
5°	2100.6	2110.4
7.5°	2828.6	2823.7
10°	3517.3	3561.6
12.5°	4019.1	4028.9
15°	4324.1	4343.7
17.5°	4442.2	4447.0
20°	4447.0	4437.2
22.5°	4393.0	4383.1
25°	4329.0	4324.1
27.5°	4270.0	4274.9
30°	4245.4	4260.1
32.5°	4245.4	4270.0
35°	4255.2	4279.8
37.5°	4250.3	4279.8
40°	4230.7	4265.1
42.5°	4176.5	4201.1
45°	4092.9	4122.4
47.5°	3984.6	4004.3
50°	3846.9	3866.6
52.5°	3674.7	3679.7
55°	3468.1	3487.8
57.5°	3246.7	3251.7
60°	3000.8	3015.5
62.5°	2740.0	2740.0
65°	2464.6	2474.4
67.5°	2179.3	2203.9
70°	1889.1	1893.9
72.5°	1603.7	1603.7
75°	1308.5	1313.5
77.5°	1028.1	1028.1
80°	762.5	767.4
82.5°	526.4	536.2
85°	329.6	329.6
87.5°	152.5	137.7
90°	68.9	68.9
92.5°	276.0	221.2
95°	961.9	795.9
97.5°	2304.9	1989.0
100°	3320.9	2944.5
102.5°	4320.3	3997.9
105°	5594.5	5421.3
107.5°	6429.1	6471.0
110°	6747.4	6928.0

TEST NUMBER: P938597

CATALOG NUMBER: SQ4-FB-150U-125D-B35-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6775.8	7053.1
115°	6596.1	6980.5
117.5°	6215.2	6641.4
120°	5908.1	6322.3
122.5°	5609.3	6017.8
125°	5182.7	5559.1
127.5°	4799.2	5116.6
130°	4573.1	4866.4
132.5°	4368.0	4630.7
135°	4087.0	4313.4
137.5°	3861.6	4046.8
140°	3706.8	3880.1
142.5°	3578.7	3727.7
145°	3386.6	3499.3
147.5°	3239.1	3332.5
150°	3146.1	3221.9
152.5°	3066.8	3124.0
155°	2975.5	3013.4
157.5°	2903.4	2930.0
160°	2860.3	2875.6
162.5°	2832.1	2846.6
165°	2791.4	2806.7
167.5°	2762.1	2768.6
170°	2754.1	2754.1
172.5°	2732.6	2727.0
175°	2719.7	2719.7
177.5°	2708.0	2701.6
180°	2701.6	2701.6

(END OF REPORT)