

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936505

Luminaire Tested: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936505
REPORT IS A COMBINATION OF REPORTS P933431 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11619.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936505

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P936505

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	19
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3561	3561	3561
5°	3480	4117	4787
10°	3158	6003	7935
15°	2685	7844	9582
20°	2187	9093	9766
25°	1825	9517	9567
30°	1539	9580	9549
35°	1362	9423	9796
40°	1188	9219	10051
45°	1076	9070	10091
50°	988	8937	9924
55°	947	8741	9484
60°	971	8361	8789
65°	1012	7781	7835
70°	1080	6791	6619
75°	1202	5542	5166
80°	1322	3848	3480
85°	1199	2045	1782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10091 cd/sqm

TEST NUMBER: P936505

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.9	1.3
10°-20°	660.1	5.7
20°-30°	1154.5	9.9
30°-40°	1486.2	12.8
40°-50°	1660.1	14.3
50°-60°	1590.0	13.7
60°-70°	1260.1	10.8
70°-80°	740.9	6.4
80°-90°	207.4	1.8
90°-100°	203.8	1.8
100°-110°	535.9	4.6
110°-120°	555.7	4.8
120°-130°	445.7	3.8
130°-140°	349.7	3.0
140°-150°	268.4	2.3
150°-160°	193.3	1.7
160°-170°	118.3	1.0
170°-180°	40.0	0.3
0°-30°	1963.5	16.9
0°-40°	3449.8	29.7
0°-60°	6699.8	57.7
0°-90°	8908.2	76.7
90°-120°	1295.4	11.1
90°-150°	2359.2	20.3
90°-180°	2711.0	23.3
0°-180°	11619.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1151	1151	1151	1151	1151	
5°	1122	1203	1355	1533	1588	104
15°	840	1551	2614	3169	3269	234
25°	537	1758	3113	3250	3254	247
35°	363	1681	2932	3098	3221	227
45°	248	1340	2591	2969	3102	192
55°	178	851	2199	2554	2625	162
65°	141	452	1632	1836	1862	139
75°	104	278	896	985	988	109
85°	37	85	222	244	248	39
90°	3	8	21	11	11	5
95°	27	106	351	181	123	30
105°	97	146	592	899	839	102
115°	172	208	475	947	1080	169
125°	238	268	432	729	860	212
135°	284	313	418	589	668	220
145°	330	351	413	502	542	207
155°	373	383	413	453	466	171
165°	402	408	413	429	434	114
175°	418	418	416	421	421	40
180°	418	418	418	418	418	

TEST NUMBER: P936505

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1151.3	1151.3	1158.7	1162.5	1169.8	1173.6	1180.9	1188.3	1210.6	1214.3	1221.7
5°	1121.7	1136.5	1184.7	1203.2	1255.0	1325.3	1355.0	1403.1	1503.0	1532.6	1551.1
7.5°	1077.3	1110.6	1229.1	1258.7	1388.2	1573.3	1651.1	1754.7	1914.0	1991.7	2054.6
10°	1006.9	1077.3	1288.3	1358.6	1569.7	1851.0	1995.4	2139.8	2380.4	2487.7	2528.4
12.5°	929.2	1043.9	1351.2	1447.5	1751.1	2161.9	2335.9	2495.2	2769.1	2913.5	2935.7
15°	840.3	995.8	1410.4	1551.1	1943.6	2421.1	2613.6	2809.8	3065.3	3168.9	3194.8
17.5°	762.6	958.8	1466.0	1614.0	2091.6	2654.3	2850.6	3013.5	3220.7	3291.0	3309.6
20°	666.3	899.6	1503.0	1695.5	2247.1	2824.6	3013.5	3139.3	3279.9	3324.4	3331.8
22.5°	596.0	836.7	1525.2	1725.1	2350.8	2928.3	3087.4	3187.5	3283.7	3298.5	3302.2
25°	536.8	766.3	1521.5	1758.4	2439.6	2991.2	3113.4	3187.5	3242.9	3250.3	3250.3
27.5°	481.3	688.5	1506.7	1765.8	2506.3	3006.0	3102.3	3154.1	3180.0	3194.8	3194.8
30°	433.1	614.6	1469.6	1751.1	2535.9	2991.2	3068.9	3094.9	3120.8	3143.0	3154.1
32.5°	396.1	544.1	1414.2	1721.5	2539.5	2954.2	3009.7	3024.6	3061.6	3113.4	3131.9
35°	362.8	473.8	1351.2	1680.7	2517.3	2894.9	2932.0	2946.8	3020.8	3098.5	3124.5
37.5°	329.5	422.1	1269.8	1610.4	2484.1	2824.6	2850.6	2876.4	2991.2	3083.8	3113.4
40°	296.2	377.6	1173.6	1532.6	2432.2	2739.5	2761.7	2802.4	2954.2	3061.6	3091.2
42.5°	270.2	340.6	1069.9	1451.2	2365.5	2643.2	2676.6	2735.8	2909.8	3024.6	3057.8
45°	248.1	303.6	958.8	1340.1	2280.5	2543.3	2591.4	2672.8	2857.9	2969.0	2998.6
47.5°	225.8	277.7	844.1	1225.4	2187.9	2443.3	2506.3	2598.8	2787.6	2894.9	2920.9
50°	207.3	251.7	729.3	1103.2	2088.0	2335.9	2410.0	2506.3	2698.8	2798.7	2832.1
52.5°	192.5	229.5	622.0	981.1	1973.2	2224.9	2310.1	2410.0	2591.4	2687.7	2709.9
55°	177.7	211.0	529.4	851.4	1854.7	2106.5	2199.0	2295.2	2473.0	2554.4	2569.2
57.5°	170.3	196.2	451.7	729.3	1728.8	1973.2	2076.8	2165.7	2332.3	2395.1	2410.0
60°	159.2	185.1	392.4	625.6	1591.8	1847.3	1936.2	2025.0	2165.7	2217.5	2228.6
62.5°	148.0	177.7	348.0	525.7	1451.2	1699.2	1788.0	1869.5	1988.0	2025.0	2039.8
65°	140.7	170.3	314.7	451.7	1306.9	1543.7	1632.5	1703.0	1799.2	1836.2	1843.6
67.5°	133.3	162.9	288.8	388.7	1162.5	1388.2	1454.9	1521.5	1595.6	1632.5	1636.3
70°	122.2	155.5	266.6	344.3	1014.3	1210.6	1266.1	1336.5	1395.7	1414.2	1425.3
72.5°	114.8	144.4	251.7	310.9	862.5	1040.3	1092.1	1132.8	1184.7	1203.2	1203.2
75°	103.7	129.5	237.0	277.7	707.0	851.4	895.9	936.6	977.3	984.7	973.6
77.5°	92.6	114.8	203.6	233.2	551.6	673.8	710.8	733.0	766.3	773.7	777.5
80°	77.7	99.9	159.2	181.4	399.8	496.0	522.0	540.5	570.1	570.1	577.5
82.5°	59.2	77.7	114.8	129.5	270.2	340.6	362.8	373.9	392.4	392.4	392.4
85°	37.0	48.1	74.1	85.2	162.9	207.3	222.1	225.8	240.6	244.3	244.3
87.5°	18.5	25.9	48.1	51.8	85.2	107.3	107.3	114.8	114.8	111.1	107.3
90°	2.8	5.0	7.3	7.8	12.3	18.3	21.3	19.0	14.2	10.6	10.6
92.5°	11.2	30.3	49.4	54.2	76.1	105.4	120.1	105.3	75.6	53.3	51.2
95°	26.9	61.8	96.8	105.5	187.4	296.5	351.1	313.3	237.7	181.0	174.6
97.5°	46.6	77.4	108.3	115.9	252.4	434.4	525.4	501.5	453.7	417.9	405.6
100°	61.7	89.7	117.6	124.6	276.1	478.0	579.0	580.8	584.2	586.8	572.3
102.5°	74.6	100.7	126.7	133.3	286.9	491.8	594.1	624.6	685.4	731.0	718.5
105°	96.6	118.6	140.7	146.2	295.0	493.2	592.4	660.6	797.1	899.4	892.7
107.5°	119.0	139.5	160.2	165.3	296.5	471.3	558.7	653.9	844.2	987.1	988.6
110°	134.1	152.7	171.3	176.0	294.2	451.9	530.7	637.1	849.8	1009.5	1016.5

TEST NUMBER: P936505

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	149.1	166.7	184.5	188.9	294.3	434.9	505.2	614.1	831.8	995.2	1005.9
115°	171.5	187.8	204.2	208.3	297.0	415.3	474.6	579.5	789.2	946.6	961.5
117.5°	193.6	208.5	223.3	227.1	302.5	403.2	453.6	548.3	737.6	879.5	896.1
120°	206.5	220.5	234.5	238.0	307.0	399.0	445.1	531.5	704.6	834.3	850.4
122.5°	219.2	233.3	247.3	250.9	313.5	396.9	438.6	516.5	672.3	789.1	804.9
125°	238.5	251.4	264.3	267.5	322.2	395.2	431.6	497.7	630.1	729.4	743.9
127.5°	254.2	267.2	280.2	283.5	330.9	394.1	425.7	482.5	596.2	681.4	693.7
130°	262.6	276.7	290.7	294.1	337.3	394.7	423.5	474.1	575.3	651.1	662.5
132.5°	271.4	285.3	299.3	302.8	342.4	395.2	421.5	466.8	557.4	625.3	635.5
135°	284.3	297.0	309.7	312.9	348.0	394.8	418.2	456.1	531.9	588.8	597.6
137.5°	297.5	310.1	322.6	325.8	356.4	397.2	417.6	449.6	513.7	561.8	569.0
140°	308.4	320.0	331.7	334.6	361.6	397.6	415.6	443.3	498.7	540.2	547.0
142.5°	316.8	327.6	338.3	341.0	365.8	399.0	415.6	439.9	488.6	525.1	530.9
145°	329.8	339.1	348.5	350.8	371.5	399.0	412.8	432.7	472.5	502.3	506.7
147.5°	342.7	351.7	360.9	363.1	379.7	401.8	412.8	428.5	459.8	483.3	486.9
150°	351.1	359.3	367.5	369.6	384.0	403.2	412.8	426.1	452.5	472.3	475.2
152.5°	359.8	366.0	372.2	373.8	386.8	404.1	412.8	424.1	446.7	463.6	465.9
155°	372.7	377.2	381.9	383.0	392.9	406.2	412.8	421.8	439.8	453.3	454.8
157.5°	382.2	386.7	391.3	392.4	399.2	408.3	412.8	419.8	433.7	444.2	445.2
160°	388.7	392.2	395.7	396.6	402.0	409.2	412.8	418.8	430.8	439.7	440.3
162.5°	395.2	397.8	400.4	401.1	405.0	410.2	412.8	417.9	428.0	435.5	436.1
165°	402.2	404.5	406.9	407.5	409.3	411.6	412.8	416.5	423.7	429.1	429.6
167.5°	408.6	409.7	410.9	411.1	412.6	414.6	415.6	418.0	422.7	426.3	426.6
170°	412.8	413.9	415.1	415.3	415.4	415.5	415.6	418.0	422.7	426.3	426.3
172.5°	415.1	415.3	415.5	415.6	415.6	415.6	415.6	417.5	421.2	424.0	423.8
175°	418.2	418.2	418.2	418.2	417.3	416.2	415.6	416.8	419.2	421.0	421.0
177.5°	418.2	418.2	418.2	418.2	417.5	416.7	416.2	417.1	419.0	420.4	420.1
180°	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2	418.2

TEST NUMBER: P936505

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1151.3	1151.3
2.5°	1229.1	1221.7
5°	1580.8	1588.2
7.5°	2128.7	2124.9
10°	2647.0	2680.2
12.5°	3024.6	3032.0
15°	3254.1	3268.9
17.5°	3342.9	3346.6
20°	3346.6	3339.2
22.5°	3305.9	3298.5
25°	3257.8	3254.1
27.5°	3213.3	3217.1
30°	3194.8	3206.0
32.5°	3194.8	3213.3
35°	3202.2	3220.7
37.5°	3198.5	3220.7
40°	3183.7	3209.6
42.5°	3143.0	3161.5
45°	3080.1	3102.3
47.5°	2998.6	3013.5
50°	2894.9	2909.8
52.5°	2765.4	2769.1
55°	2609.9	2624.7
57.5°	2443.3	2447.0
60°	2258.2	2269.3
62.5°	2062.0	2062.0
65°	1854.7	1862.1
67.5°	1640.0	1658.5
70°	1421.5	1425.3
72.5°	1206.8	1206.8
75°	984.7	988.5
77.5°	773.7	773.7
80°	573.8	577.5
82.5°	396.1	403.5
85°	248.1	248.1
87.5°	114.8	103.7
90°	10.6	10.6
92.5°	42.8	34.3
95°	148.9	123.2
97.5°	356.8	307.8
100°	514.1	455.8
102.5°	668.7	618.8
105°	865.9	839.1
107.5°	995.2	1001.6
110°	1044.4	1072.3

TEST NUMBER: P936505

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1048.8	1091.7
115°	1021.0	1080.5
117.5°	962.0	1028.0
120°	914.5	978.6
122.5°	868.2	931.5
125°	802.1	860.4
127.5°	742.8	791.9
130°	707.9	753.3
132.5°	676.1	716.8
135°	632.6	667.6
137.5°	597.7	626.4
140°	573.8	600.6
142.5°	554.0	577.0
145°	524.2	541.6
147.5°	501.4	515.8
150°	487.0	498.7
152.5°	474.7	483.5
155°	460.6	466.4
157.5°	449.4	453.6
160°	442.7	445.1
162.5°	438.3	440.6
165°	432.1	434.4
167.5°	427.5	428.5
170°	426.3	426.3
172.5°	422.9	422.1
175°	421.0	421.0
177.5°	419.2	418.2
180°	418.2	418.2

(END OF REPORT)