

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936508

Luminaire Tested: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936508
REPORT IS A COMBINATION OF REPORTS P933455 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7746.6 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 77.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936508

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P936508

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3562	3562	3562
5°	3479	4116	4787
10°	3156	6000	7936
15°	2682	7839	9583
20°	2184	9084	9767
25°	1822	9506	9568
30°	1536	9567	9551
35°	1358	9408	9797
40°	1183	9201	10052
45°	1072	9050	10092
50°	983	8914	9924
55°	941	8715	9485
60°	964	8332	8790
65°	1003	7750	7836
70°	1068	6759	6620
75°	1183	5511	5166
80°	1292	3822	3481
85°	1150	2028	1782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10092 cd/sqm

TEST NUMBER: P936508

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.3	1.3
10°-20°	440.1	5.7
20°-30°	769.8	9.9
30°-40°	990.9	12.8
40°-50°	1106.8	14.3
50°-60°	1060.1	13.7
60°-70°	840.1	10.8
70°-80°	494.0	6.4
80°-90°	138.3	1.8
90°-100°	135.9	1.8
100°-110°	357.3	4.6
110°-120°	370.4	4.8
120°-130°	297.1	3.8
130°-140°	233.1	3.0
140°-150°	179.0	2.3
150°-160°	128.9	1.7
160°-170°	78.9	1.0
170°-180°	26.6	0.3
0°-30°	1309.2	16.9
0°-40°	2300.1	29.7
0°-60°	4467.0	57.7
0°-90°	5939.4	76.7
90°-120°	863.6	11.1
90°-150°	1572.8	20.3
90°-180°	1807.0	23.3
0°-180°	7746.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	768	768	768	768	768	
5°	748	802	903	1022	1059	69
15°	560	1034	1743	2113	2180	156
25°	358	1172	2076	2167	2170	165
35°	242	1121	1955	2066	2147	151
45°	165	894	1728	1980	2068	128
55°	118	568	1466	1703	1750	108
65°	94	301	1088	1224	1242	93
75°	69	185	597	657	659	72
85°	25	57	148	163	165	26
90°	2	5	14	7	7	3
95°	18	70	234	121	82	20
105°	64	98	395	600	559	68
115°	114	139	316	631	720	113
125°	159	178	288	486	574	141
135°	190	209	279	393	445	147
145°	220	234	275	335	361	138
155°	248	255	275	302	311	114
165°	268	272	275	286	290	76
175°	279	279	277	281	281	26
180°	279	279	279	279	279	

TEST NUMBER: P936508

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7	767.7
2.5°	767.7	767.7	772.6	775.0	780.0	782.4	787.4	792.3	807.2	809.6	814.5
5°	747.9	757.8	789.9	802.2	836.8	883.7	903.4	935.5	1002.1	1021.9	1034.2
7.5°	718.2	740.5	819.5	839.2	925.6	1049.0	1100.8	1169.9	1276.1	1328.0	1369.9
10°	671.4	718.2	859.0	905.9	1046.5	1234.1	1330.4	1426.7	1587.1	1658.7	1685.8
12.5°	619.5	696.0	900.9	965.1	1167.5	1441.4	1557.4	1663.6	1846.2	1942.5	1957.3
15°	560.3	664.0	940.4	1034.2	1295.8	1614.2	1742.6	1873.4	2043.7	2112.8	2130.1
17.5°	508.5	639.3	977.4	1076.2	1394.6	1769.7	1900.6	2009.1	2147.4	2194.2	2206.7
20°	444.3	599.8	1002.1	1130.4	1498.2	1883.3	2009.1	2093.1	2186.9	2216.5	2221.4
22.5°	397.4	557.8	1016.9	1150.2	1567.3	1952.4	2058.5	2125.1	2189.4	2199.2	2201.7
25°	357.9	510.9	1014.4	1172.5	1626.6	1994.4	2075.8	2125.1	2162.2	2167.2	2167.2
27.5°	320.8	459.1	1004.6	1177.4	1671.0	2004.3	2068.4	2103.0	2120.3	2130.1	2130.1
30°	288.8	409.7	979.9	1167.5	1690.7	1994.4	2046.2	2063.5	2080.8	2095.5	2103.0
32.5°	264.1	362.9	942.9	1147.7	1693.2	1969.7	2006.7	2016.6	2041.3	2075.8	2088.1
35°	241.9	316.0	900.9	1120.6	1678.4	1930.2	1954.9	1964.8	2014.1	2065.9	2083.2
37.5°	219.7	281.4	846.6	1073.7	1656.2	1883.3	1900.6	1917.9	1994.4	2056.0	2075.8
40°	197.4	251.8	782.4	1021.9	1621.6	1826.5	1841.3	1868.5	1969.7	2041.3	2061.0
42.5°	180.2	227.1	713.3	967.5	1577.2	1762.4	1784.6	1824.0	1940.0	2016.6	2038.8
45°	165.4	202.4	639.3	893.5	1520.5	1695.7	1727.8	1782.1	1905.5	1979.5	1999.3
47.5°	150.6	185.1	562.7	817.0	1458.7	1629.1	1671.0	1732.8	1858.6	1930.2	1947.5
50°	138.2	167.8	486.2	735.5	1392.1	1557.4	1606.9	1671.0	1799.4	1866.0	1888.2
52.5°	128.3	153.0	414.7	654.1	1315.5	1483.4	1540.2	1606.9	1727.8	1792.0	1806.7
55°	118.4	140.7	353.0	567.7	1236.6	1404.5	1466.1	1530.4	1648.8	1703.1	1713.0
57.5°	113.6	130.9	301.1	486.2	1152.6	1315.5	1384.7	1444.0	1555.0	1597.0	1606.9
60°	106.1	123.4	261.6	417.1	1061.4	1231.7	1290.9	1350.1	1444.0	1478.5	1485.9
62.5°	98.7	118.4	232.0	350.5	967.5	1132.9	1192.2	1246.5	1325.4	1350.1	1360.0
65°	93.8	113.6	209.8	301.1	871.3	1029.3	1088.5	1135.4	1199.5	1224.3	1229.2
67.5°	88.8	108.6	192.5	259.2	775.0	925.6	970.1	1014.4	1063.8	1088.5	1091.0
70°	81.4	103.7	177.7	229.6	676.3	807.2	844.1	891.0	930.5	942.9	950.3
72.5°	76.5	96.3	167.8	207.3	575.1	693.6	728.1	755.3	789.9	802.2	802.2
75°	69.1	86.4	157.9	185.1	471.5	567.7	597.3	624.5	651.7	656.6	649.1
77.5°	61.7	76.5	135.7	155.5	367.8	449.3	473.9	488.7	510.9	515.8	518.4
80°	51.8	66.7	106.1	121.0	266.6	330.7	348.0	360.3	380.1	380.1	385.1
82.5°	39.5	51.8	76.5	86.4	180.2	227.1	241.9	249.3	261.6	261.6	261.6
85°	24.7	32.1	49.4	56.8	108.6	138.2	148.1	150.6	160.5	162.9	162.9
87.5°	12.3	17.3	32.1	34.6	56.8	71.5	71.5	76.5	76.5	74.1	71.5
90°	1.9	3.4	4.9	5.2	8.2	12.2	14.2	12.6	9.4	7.1	7.1
92.5°	7.5	20.2	33.0	36.1	50.8	70.3	80.0	70.1	50.4	35.6	34.2
95°	17.9	41.2	64.5	70.3	124.9	197.6	234.1	208.8	158.5	120.7	116.4
97.5°	31.1	51.7	72.1	77.2	168.2	289.5	350.2	334.4	302.5	278.6	270.5
100°	41.2	59.8	78.4	83.0	184.0	318.6	385.9	387.1	389.5	391.3	381.5
102.5°	49.8	67.2	84.5	88.8	191.3	327.8	396.1	416.4	456.9	487.4	479.0
105°	64.4	79.1	93.9	97.5	196.7	328.9	395.0	440.5	531.4	599.6	595.1
107.5°	79.3	93.0	106.8	110.2	197.6	314.2	372.5	435.9	562.8	658.0	659.1
110°	89.5	101.8	114.2	117.3	196.1	301.2	353.8	424.7	566.6	672.9	677.6

TEST NUMBER: P936508

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	99.4	111.1	122.9	125.9	196.2	289.9	336.8	409.4	554.5	663.4	670.6
115°	114.3	125.2	136.1	138.8	198.0	276.9	316.3	386.3	526.2	631.1	641.0
117.5°	129.1	139.0	148.9	151.4	201.7	268.8	302.3	365.5	491.7	586.4	597.4
120°	137.7	147.0	156.4	158.7	204.7	266.1	296.7	354.4	469.7	556.2	566.8
122.5°	146.1	155.5	164.9	167.3	209.0	264.6	292.4	344.4	448.2	526.1	536.7
125°	159.1	167.7	176.2	178.3	214.8	263.5	287.8	331.9	420.1	486.2	496.0
127.5°	169.5	178.1	186.8	188.9	220.6	262.7	283.8	321.8	397.5	454.3	462.5
130°	175.1	184.5	193.7	196.0	224.8	263.2	282.3	316.1	383.5	434.0	441.6
132.5°	180.9	190.3	199.5	201.8	228.3	263.5	281.0	311.2	371.5	416.8	423.7
135°	189.5	198.0	206.5	208.7	232.0	263.2	278.8	304.1	354.6	392.6	398.4
137.5°	198.3	206.7	215.1	217.2	237.6	264.8	278.4	299.8	342.5	374.5	379.3
140°	205.6	213.3	221.1	223.0	241.1	265.1	277.1	295.6	332.5	360.2	364.6
142.5°	211.3	218.4	225.6	227.3	244.0	266.1	277.1	293.4	325.8	350.1	353.9
145°	219.9	226.1	232.3	233.9	247.7	266.1	275.2	288.5	315.0	334.9	337.8
147.5°	228.5	234.5	240.6	242.1	253.1	267.9	275.2	285.7	306.5	322.1	324.6
150°	234.1	239.6	245.0	246.4	256.0	268.8	275.2	284.0	301.7	314.9	316.8
152.5°	239.9	244.0	248.2	249.2	257.9	269.5	275.2	282.7	297.8	309.1	310.6
155°	248.4	251.5	254.6	255.4	262.0	270.9	275.2	281.2	293.2	302.1	303.1
157.5°	254.8	257.8	260.8	261.5	266.1	272.2	275.2	279.9	289.2	296.2	296.8
160°	259.1	261.4	263.8	264.3	268.0	272.8	275.2	279.3	287.2	293.2	293.6
162.5°	263.4	265.2	266.8	267.3	269.9	273.5	275.2	278.6	285.3	290.4	290.8
165°	268.2	269.7	271.3	271.7	272.9	274.5	275.2	277.7	282.4	286.1	286.5
167.5°	272.4	273.2	273.9	274.1	275.2	276.5	277.1	278.7	281.9	284.2	284.4
170°	275.2	276.0	276.7	276.9	277.0	277.1	277.1	278.7	281.9	284.2	284.2
172.5°	276.7	276.9	277.1	277.1	277.1	277.1	277.1	278.3	280.9	282.7	282.5
175°	278.8	278.8	278.8	278.8	278.2	277.5	277.1	277.9	279.5	280.7	280.7
177.5°	278.8	278.8	278.8	278.8	278.3	277.8	277.5	278.1	279.4	280.3	280.1
180°	278.8	278.8	278.8	278.8	278.8	278.8	278.8	278.8	278.8	278.8	278.8

TEST NUMBER: P936508

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	767.7	767.7
2.5°	819.5	814.5
5°	1053.9	1058.9
7.5°	1419.2	1416.8
10°	1764.8	1787.0
12.5°	2016.6	2021.5
15°	2169.6	2179.5
17.5°	2228.8	2231.3
20°	2231.3	2226.4
22.5°	2204.1	2199.2
25°	2172.1	2169.6
27.5°	2142.4	2144.9
30°	2130.1	2137.6
32.5°	2130.1	2142.4
35°	2135.0	2147.4
37.5°	2132.6	2147.4
40°	2122.7	2140.0
42.5°	2095.5	2107.9
45°	2053.6	2068.4
47.5°	1999.3	2009.1
50°	1930.2	1940.0
52.5°	1843.8	1846.2
55°	1740.1	1750.0
57.5°	1629.1	1631.5
60°	1505.6	1513.1
62.5°	1374.8	1374.8
65°	1236.6	1241.6
67.5°	1093.4	1105.8
70°	947.8	950.3
72.5°	804.6	804.6
75°	656.6	659.0
77.5°	515.8	515.8
80°	382.6	385.1
82.5°	264.1	269.1
85°	165.4	165.4
87.5°	76.5	69.1
90°	7.1	7.1
92.5°	28.5	22.8
95°	99.3	82.1
97.5°	237.8	205.2
100°	342.7	303.8
102.5°	445.8	412.5
105°	577.3	559.4
107.5°	663.4	667.7
110°	696.2	714.9

TEST NUMBER: P936508

CATALOG NUMBER: SQ4-FB-025U-100D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	699.2	727.8
115°	680.7	720.3
117.5°	641.4	685.4
120°	609.6	652.4
122.5°	578.8	620.9
125°	534.8	573.7
127.5°	495.2	528.0
130°	471.9	502.1
132.5°	450.7	477.8
135°	421.7	445.1
137.5°	398.4	417.6
140°	382.5	400.4
142.5°	369.3	384.6
145°	349.5	361.1
147.5°	334.2	343.9
150°	324.7	332.5
152.5°	316.4	322.3
155°	307.0	310.9
157.5°	299.6	302.3
160°	295.1	296.7
162.5°	292.2	293.7
165°	288.0	289.6
167.5°	285.1	285.7
170°	284.2	284.2
172.5°	282.0	281.4
175°	280.7	280.7
177.5°	279.5	278.8
180°	278.8	278.8

(END OF REPORT)