

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936704

Luminaire Tested: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936704
REPORT IS A COMBINATION OF REPORTS P933485 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6886.5 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 56.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936704

CATALOG NUMBER: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P936704

CATALOG NUMBER: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	106	106	106	106	97	97	97	97		80	80	80		65	65	65		51	51	51
1	96	92	88	84	88	84	81	77		70	67	65		57	55	53		45	43	42
2	87	79	73	68	79	73	67	63		60	56	53		49	46	44		39	37	35
3	79	69	62	56	72	64	57	52		53	48	44		43	39	36		34	31	29
4	72	61	53	47	66	56	49	43		47	41	37		38	34	31		30	27	24
5	66	54	46	39	60	50	42	37		41	36	31		34	29	26		26	23	21
6	60	48	40	34	55	44	37	31		37	31	27		30	26	22		24	21	18
7	56	43	35	29	51	40	32	27		33	28	23		27	23	20		21	18	16
8	51	39	31	26	47	36	29	24		30	25	21		25	20	17		20	16	14
9	48	35	28	23	44	33	26	21		27	22	18		23	18	15		18	15	12
10	45	32	25	20	41	30	23	19		25	20	16		21	17	14		17	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1848	1848	1848
5°	1806	2136	2484
10°	1638	3114	4119
15°	1392	4069	4973
20°	1133	4715	5069
25°	945	4933	4965
30°	797	4965	4956
35°	705	4882	5084
40°	614	4775	5217
45°	557	4696	5237
50°	510	4626	5151
55°	489	4522	4922
60°	500	4324	4562
65°	521	4022	4066
70°	555	3508	3436
75°	615	2860	2681
80°	671	1983	1806
85°	596	1053	925

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5237 cd/sqm

TEST NUMBER: P936704

CATALOG NUMBER: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	0.7
10°-20°	228.4	3.3
20°-30°	399.5	5.8
30°-40°	514.2	7.5
40°-50°	574.4	8.3
50°-60°	550.2	8.0
60°-70°	436.0	6.3
70°-80°	256.4	3.7
80°-90°	73.5	1.1
90°-100°	285.9	4.2
100°-110°	751.7	10.9
110°-120°	779.4	11.3
120°-130°	625.2	9.1
130°-140°	490.6	7.1
140°-150°	376.5	5.5
150°-160°	271.2	3.9
160°-170°	165.9	2.4
170°-180°	56.1	0.8
0°-30°	679.4	9.9
0°-40°	1193.6	17.3
0°-60°	2318.2	33.7
0°-90°	3084.0	44.8
90°-120°	1817.1	26.4
90°-150°	3309.4	48.1
90°-180°	3802.0	55.2
0°-180°	6886.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	388	416	469	530	550	36
15°	291	537	904	1096	1131	81
25°	186	608	1077	1125	1126	86
35°	126	582	1014	1072	1114	78
45°	86	464	897	1027	1073	66
55°	62	295	761	884	908	56
65°	49	156	565	635	644	48
75°	36	96	310	341	342	38
85°	13	29	77	84	86	14
90°	4	11	30	15	15	4
95°	38	148	492	254	173	42
105°	135	205	831	1262	1177	144
115°	241	292	666	1328	1516	238
125°	335	375	606	1023	1207	297
135°	399	439	587	826	937	309
145°	463	492	579	705	760	290
155°	523	537	579	636	654	240
165°	564	572	579	602	609	159
175°	587	587	583	590	590	56
180°	587	587	587	587	587	

TEST NUMBER: P936704

CATALOG NUMBER: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	398.3	398.3	398.3	398.3	398.3	398.3	398.3	398.3	398.3	398.3	398.3
2.5°	398.3	398.3	400.9	402.2	404.7	406.1	408.6	411.2	418.9	420.1	422.7
5°	388.1	393.3	409.9	416.3	434.2	458.6	468.8	485.4	520.1	530.3	536.7
7.5°	372.7	384.3	425.3	435.5	480.4	544.4	571.3	607.2	662.2	689.1	710.9
10°	348.4	372.7	445.8	470.1	543.1	640.4	690.5	740.4	823.6	860.7	874.9
12.5°	321.5	361.2	467.6	500.8	605.9	748.1	808.3	863.3	958.2	1008.1	1015.7
15°	290.8	344.6	488.0	536.7	672.5	837.7	904.4	972.2	1060.6	1096.4	1105.4
17.5°	263.9	331.8	507.3	558.5	723.7	918.4	986.3	1042.7	1114.4	1138.7	1145.1
20°	230.5	311.2	520.1	586.7	777.6	977.3	1042.7	1086.2	1134.9	1150.3	1152.9
22.5°	206.2	289.5	527.7	596.9	813.4	1013.3	1068.3	1102.9	1136.2	1141.3	1142.6
25°	185.7	265.1	526.5	608.4	844.1	1035.0	1077.2	1102.9	1122.1	1124.7	1124.7
27.5°	166.6	238.3	521.3	611.0	867.2	1040.1	1073.4	1091.4	1100.4	1105.4	1105.4
30°	149.8	212.7	508.5	605.9	877.5	1035.0	1061.9	1070.8	1079.8	1087.6	1091.4
32.5°	137.0	188.3	489.3	595.6	878.7	1022.1	1041.4	1046.5	1059.3	1077.2	1083.6
35°	125.5	164.0	467.6	581.5	871.1	1001.7	1014.5	1019.7	1045.2	1072.2	1081.1
37.5°	114.0	146.0	439.4	557.2	859.5	977.3	986.3	995.3	1035.0	1067.0	1077.2
40°	102.5	130.6	406.1	530.3	841.5	947.9	955.6	969.7	1022.1	1059.3	1069.6
42.5°	93.5	117.8	370.2	502.1	818.5	914.6	926.2	946.6	1006.9	1046.5	1058.0
45°	85.9	105.0	331.8	463.7	789.0	880.0	896.6	924.8	988.9	1027.3	1037.5
47.5°	78.1	96.1	292.0	424.0	757.0	845.5	867.2	899.2	964.6	1001.7	1010.7
50°	71.7	87.1	252.3	381.7	722.5	808.3	833.9	867.2	933.8	968.4	979.9
52.5°	66.6	79.5	215.2	339.4	682.7	769.8	799.3	833.9	896.6	930.0	937.6
55°	61.5	73.1	183.2	294.6	641.8	728.9	760.8	794.2	855.7	883.9	889.0
57.5°	58.9	67.9	156.2	252.3	598.2	682.7	718.6	749.4	807.0	828.7	833.9
60°	55.1	64.1	135.8	216.5	550.8	639.2	669.9	700.7	749.4	767.2	771.2
62.5°	51.3	61.5	120.4	181.9	502.1	588.0	618.6	646.9	687.9	700.7	705.8
65°	48.7	58.9	108.9	156.2	452.2	534.1	564.9	589.2	622.6	635.4	637.9
67.5°	46.1	56.3	99.9	134.5	402.2	480.4	503.4	526.5	552.1	564.9	566.1
70°	42.3	53.8	92.3	119.1	351.0	418.9	438.1	462.4	482.9	489.3	493.2
72.5°	39.7	49.9	87.1	107.6	298.4	359.9	377.9	391.9	409.9	416.3	416.3
75°	35.9	44.8	81.9	96.1	244.7	294.6	310.0	324.0	338.2	340.7	336.9
77.5°	32.0	39.7	70.5	80.7	190.9	233.1	245.9	253.6	265.1	267.7	269.0
80°	26.9	34.6	55.1	62.7	138.4	171.6	180.6	187.0	197.3	197.3	199.8
82.5°	20.5	26.9	39.7	44.8	93.5	117.8	125.5	129.4	135.8	135.8	135.8
85°	12.8	16.6	25.6	29.4	56.3	71.7	76.9	78.1	83.3	84.5	84.5
87.5°	6.4	9.0	16.6	18.0	29.4	37.1	37.1	39.7	39.7	38.4	37.1
90°	3.9	7.1	10.2	11.0	17.3	25.7	29.9	26.5	20.0	15.0	15.0
92.5°	15.8	42.5	69.3	76.0	106.9	147.9	168.5	147.6	106.0	74.8	71.8
95°	37.8	86.8	135.8	148.0	262.8	415.9	492.5	439.5	333.5	253.9	245.0
97.5°	65.3	108.5	151.7	162.5	354.0	609.3	737.0	703.5	636.4	586.2	569.0
100°	86.6	125.8	164.9	174.8	387.3	670.5	812.1	814.6	819.5	823.1	802.7
102.5°	104.8	141.3	177.8	187.0	402.4	689.8	833.4	876.1	961.5	1025.5	1008.0
105°	135.4	166.4	197.4	205.1	413.8	692.0	831.0	926.7	1118.2	1261.7	1252.3
107.5°	166.9	195.8	224.6	231.9	415.8	661.1	783.8	917.3	1184.3	1384.6	1386.9
110°	188.1	214.2	240.4	246.9	412.8	633.8	744.4	893.7	1192.1	1416.0	1425.8

TEST NUMBER: P936704

CATALOG NUMBER: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	209.0	233.9	258.7	264.9	412.8	610.1	708.6	861.3	1166.8	1395.9	1411.0
115°	240.6	263.5	286.4	292.1	416.7	582.7	665.7	812.9	1107.1	1327.8	1348.7
117.5°	271.6	292.4	313.2	318.5	424.4	565.6	636.1	769.0	1034.6	1233.8	1256.9
120°	289.7	309.3	329.0	333.9	430.7	559.8	624.4	745.7	988.3	1170.4	1192.8
122.5°	307.4	327.2	347.0	351.9	439.7	556.8	615.3	724.6	943.2	1107.0	1129.2
125°	334.6	352.6	370.6	375.1	451.9	554.3	605.5	698.3	883.9	1023.2	1043.6
127.5°	356.7	374.8	393.0	397.6	464.1	552.8	597.2	676.9	836.3	955.9	973.0
130°	368.4	388.0	407.7	412.6	473.0	553.7	594.0	665.0	806.9	913.3	929.2
132.5°	380.7	400.2	419.9	424.8	480.3	554.3	591.3	654.8	781.9	877.1	891.3
135°	398.8	416.7	434.4	438.9	488.1	553.7	586.6	639.8	746.1	825.9	838.2
137.5°	417.3	435.0	452.7	457.1	499.9	557.1	585.8	630.8	720.7	788.2	798.2
140°	432.6	448.9	465.2	469.3	507.2	557.7	583.0	621.9	699.5	757.8	767.2
142.5°	444.5	459.5	474.5	478.3	513.2	559.7	583.0	617.1	685.4	736.6	744.7
145°	462.6	475.7	488.9	492.1	521.1	559.8	579.1	607.0	662.9	704.7	710.8
147.5°	480.7	493.4	506.2	509.4	532.6	563.6	579.1	601.1	644.9	677.9	682.9
150°	492.5	504.0	515.6	518.5	538.7	565.6	579.1	597.6	634.8	662.6	666.7
152.5°	504.7	513.5	522.2	524.4	542.6	567.0	579.1	595.0	626.6	650.4	653.5
155°	522.8	529.3	535.8	537.4	551.3	569.8	579.1	591.7	616.8	635.7	637.8
157.5°	536.1	542.4	548.7	550.4	559.9	572.7	579.1	588.9	608.4	623.1	624.6
160°	545.2	550.2	555.0	556.3	563.9	574.1	579.1	587.5	604.2	616.8	617.7
162.5°	554.3	558.0	561.6	562.6	568.1	575.5	579.1	586.2	600.4	611.0	611.8
165°	564.1	567.5	570.7	571.6	574.1	577.4	579.1	584.2	594.3	601.9	602.8
167.5°	573.2	574.7	576.3	576.7	578.8	581.6	583.0	586.4	593.1	598.0	598.4
170°	579.1	580.6	582.3	582.6	582.7	582.9	583.0	586.4	593.1	598.0	598.0
172.5°	582.3	582.6	582.9	583.0	583.0	583.0	583.0	585.7	591.0	594.9	594.6
175°	586.6	586.6	586.6	586.6	585.4	583.8	583.0	584.7	588.0	590.5	590.5
177.5°	586.6	586.6	586.6	586.6	585.6	584.4	583.8	585.1	587.7	589.7	589.3
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6

TEST NUMBER: P936704

CATALOG NUMBER: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	398.3	398.3
2.5°	425.3	422.7
5°	546.9	549.5
7.5°	736.5	735.3
10°	915.8	927.4
12.5°	1046.5	1049.1
15°	1125.9	1131.1
17.5°	1156.7	1157.9
20°	1157.9	1155.4
22.5°	1143.9	1141.3
25°	1127.2	1125.9
27.5°	1111.8	1113.1
30°	1105.4	1109.3
32.5°	1105.4	1111.8
35°	1108.0	1114.4
37.5°	1106.7	1114.4
40°	1101.6	1110.6
42.5°	1087.6	1094.0
45°	1065.8	1073.4
47.5°	1037.5	1042.7
50°	1001.7	1006.9
52.5°	956.8	958.2
55°	903.0	908.2
57.5°	845.5	846.7
60°	781.4	785.2
62.5°	713.5	713.5
65°	641.8	644.3
67.5°	567.5	573.9
70°	491.9	493.2
72.5°	417.6	417.6
75°	340.7	342.0
77.5°	267.7	267.7
80°	198.5	199.8
82.5°	137.0	139.6
85°	85.9	85.9
87.5°	39.7	35.9
90°	15.0	15.0
92.5°	59.9	48.0
95°	208.9	172.9
97.5°	500.4	431.9
100°	721.0	639.3
102.5°	938.0	868.0
105°	1214.7	1177.0
107.5°	1395.9	1405.0
110°	1465.0	1504.2

TEST NUMBER: P936704

CATALOG NUMBER: SQ4-FB-050U-050D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1471.2	1531.3
115°	1432.1	1515.6
117.5°	1349.5	1442.0
120°	1282.8	1372.7
122.5°	1217.9	1306.6
125°	1125.3	1207.0
127.5°	1042.0	1111.0
130°	992.9	1056.6
132.5°	948.4	1005.4
135°	887.4	936.6
137.5°	838.5	878.7
140°	804.8	842.4
142.5°	777.0	809.4
145°	735.4	759.8
147.5°	703.3	723.6
150°	683.1	699.5
152.5°	665.9	678.3
155°	646.1	654.3
157.5°	630.4	636.1
160°	621.0	624.4
162.5°	614.9	618.1
165°	606.0	609.4
167.5°	599.7	601.2
170°	598.0	598.0
172.5°	593.3	592.1
175°	590.5	590.5
177.5°	588.0	586.6
180°	586.6	586.6

(END OF REPORT)