

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936706

Luminaire Tested: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936706
REPORT IS A COMBINATION OF REPORTS P933469 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3368.0 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936706

CATALOG NUMBER: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P936706

CATALOG NUMBER: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45	45	45
1	96	92	88	84	88	84	81	77	70	67	65	57	55	53	45	43	42	37	37	37
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	39	37	35	30	30	30
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25	25	25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21	21	21
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	18	18	18
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15	15	15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13	13	13
8	51	39	31	26	47	36	29	24	30	25	21	25	20	17	20	16	14	12	12	12
9	48	35	28	23	44	33	26	21	27	22	18	23	18	15	18	15	12	10	10	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	13	11	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1765	2088	2430
10°	1599	3042	4029
15°	1357	3971	4866
20°	1104	4599	4959
25°	920	4809	4858
30°	774	4835	4849
35°	684	4751	4974
40°	596	4644	5103
45°	536	4563	5124
50°	492	4489	5039
55°	470	4384	4815
60°	479	4186	4463
65°	496	3887	3977
70°	523	3383	3362
75°	577	2751	2623
80°	618	1902	1768
85°	522	1004	903

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P936706

CATALOG NUMBER: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.2	0.7
10°-20°	111.7	3.3
20°-30°	195.4	5.8
30°-40°	251.5	7.5
40°-50°	281.0	8.3
50°-60°	269.1	8.0
60°-70°	213.3	6.3
70°-80°	125.4	3.7
80°-90°	35.9	1.1
90°-100°	139.8	4.2
100°-110°	367.6	10.9
110°-120°	381.1	11.3
120°-130°	305.7	9.1
130°-140°	239.9	7.1
140°-150°	184.1	5.5
150°-160°	132.6	3.9
160°-170°	81.1	2.4
170°-180°	27.4	0.8
0°-30°	332.3	9.9
0°-40°	583.9	17.3
0°-60°	1134.0	33.7
0°-90°	1508.6	44.8
90°-120°	888.5	26.4
90°-150°	1618.3	48.0
90°-180°	1859.0	55.2
0°-180°	3368.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	195	195	195	195	195	
5°	190	204	229	259	269	18
15°	142	262	442	536	553	40
25°	91	298	527	550	551	42
35°	61	284	496	524	545	38
45°	42	227	439	502	525	32
55°	30	144	372	432	444	27
65°	24	76	276	311	315	24
75°	18	47	152	167	167	18
85°	6	14	38	41	42	7
90°	2	5	15	7	7	2
95°	18	72	241	124	84	21
105°	66	100	406	617	576	70
115°	118	143	326	649	741	116
125°	164	183	296	500	590	145
135°	195	215	287	404	458	151
145°	226	241	283	345	372	142
155°	256	263	283	311	320	117
165°	276	280	283	294	298	78
175°	287	287	285	289	289	27
180°	287	287	287	287	287	

TEST NUMBER: P936706

CATALOG NUMBER: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	194.8	194.8	194.8	194.8	194.8	194.8	194.8	194.8	194.8	194.8	194.8
2.5°	194.8	194.8	196.1	196.7	198.0	198.7	199.9	201.1	204.9	205.5	206.8
5°	189.9	192.4	200.5	203.6	212.4	224.3	229.3	237.5	254.4	259.4	262.5
7.5°	182.3	188.0	208.0	213.0	235.0	266.3	279.5	297.0	323.9	337.1	347.7
10°	170.5	182.3	218.1	230.0	265.6	313.3	337.7	362.2	402.9	421.0	428.0
12.5°	157.3	176.7	228.7	245.0	296.4	365.9	395.4	422.4	468.7	493.2	496.9
15°	142.2	168.6	238.7	262.5	329.0	409.7	442.3	475.6	518.8	536.3	540.7
17.5°	129.1	162.3	248.2	273.2	354.0	449.3	482.5	510.1	545.1	557.0	560.1
20°	112.8	152.2	254.4	287.0	380.3	478.1	510.1	531.4	555.2	562.6	563.9
22.5°	100.9	141.6	258.2	292.0	397.9	495.6	522.6	539.5	555.7	558.3	558.9
25°	90.9	129.7	257.5	297.7	412.9	506.2	527.0	539.5	548.9	550.1	550.1
27.5°	81.4	116.6	255.0	298.9	424.2	508.7	525.1	533.9	538.3	540.7	540.7
30°	73.3	104.0	248.7	296.4	429.2	506.2	519.4	523.8	528.2	532.0	533.9
32.5°	67.1	92.1	239.4	291.3	429.8	500.0	509.4	511.9	518.2	527.0	530.0
35°	61.4	80.2	228.7	284.5	426.1	490.0	496.2	498.8	511.3	524.4	528.8
37.5°	55.8	71.5	214.9	272.5	420.4	478.1	482.5	486.9	506.2	521.9	527.0
40°	50.2	63.9	198.7	259.4	411.7	463.6	467.5	474.3	500.0	518.2	523.2
42.5°	45.8	57.6	181.1	245.6	400.4	447.4	453.0	463.1	492.5	511.9	517.5
45°	41.9	51.4	162.3	226.8	385.9	430.5	438.6	452.4	483.7	502.5	507.5
47.5°	38.2	47.0	142.9	207.4	370.3	413.6	424.2	439.8	471.9	490.0	494.4
50°	35.1	42.6	123.5	186.7	353.4	395.4	407.9	424.2	456.8	473.7	479.3
52.5°	32.6	38.9	105.3	166.1	334.0	376.6	391.0	407.9	438.6	454.9	458.7
55°	30.1	35.7	89.6	144.1	313.9	356.5	372.2	388.5	418.5	432.3	434.9
57.5°	28.9	33.3	76.4	123.5	292.6	334.0	351.5	366.5	394.7	405.4	407.9
60°	26.9	31.3	66.4	105.9	269.5	312.7	327.7	342.8	366.5	375.3	377.2
62.5°	25.0	30.1	58.9	89.0	245.6	287.6	302.6	316.4	336.4	342.8	345.2
65°	23.8	28.9	53.2	76.4	221.2	261.2	276.3	288.2	304.5	310.7	312.0
67.5°	22.6	27.6	48.8	65.8	196.7	235.0	246.2	257.5	270.0	276.3	276.9
70°	20.6	26.3	45.1	58.3	171.7	204.9	214.3	226.2	236.2	239.4	241.3
72.5°	19.4	24.5	42.6	52.7	146.0	176.1	184.8	191.8	200.5	203.6	203.6
75°	17.6	21.9	40.1	47.0	119.6	144.1	151.6	158.5	165.4	166.6	164.8
77.5°	15.7	19.4	34.5	39.5	93.4	114.0	120.3	124.0	129.7	130.9	131.6
80°	13.2	16.9	26.9	30.7	67.7	84.0	88.4	91.4	96.5	96.5	97.8
82.5°	10.0	13.2	19.4	21.9	45.8	57.6	61.4	63.3	66.4	66.4	66.4
85°	6.3	8.1	12.5	14.4	27.6	35.1	37.6	38.2	40.7	41.4	41.4
87.5°	3.2	4.4	8.1	8.8	14.4	18.2	18.2	19.4	19.4	18.8	18.2
90°	2.0	3.5	5.0	5.4	8.5	12.6	14.7	13.0	9.7	7.3	7.3
92.5°	7.7	20.7	33.9	37.2	52.2	72.3	82.4	72.2	51.8	36.6	35.1
95°	18.5	42.4	66.4	72.4	128.5	203.3	240.8	214.8	163.0	124.1	119.7
97.5°	31.9	53.1	74.2	79.5	173.1	297.9	360.3	344.0	311.2	286.6	278.2
100°	42.3	61.5	80.7	85.5	189.3	327.8	397.1	398.4	400.8	402.6	392.6
102.5°	51.2	69.1	87.0	91.4	196.8	337.3	407.5	428.4	470.2	501.5	492.9
105°	66.2	81.4	96.5	100.3	202.3	338.4	406.4	453.2	546.8	617.0	612.4
107.5°	81.6	95.7	109.8	113.4	203.3	323.4	383.3	448.6	579.2	677.1	678.2
110°	92.0	104.7	117.5	120.7	201.8	310.0	364.1	437.0	583.0	692.5	697.2

TEST NUMBER: P936706

CATALOG NUMBER: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	102.2	114.3	126.5	129.5	201.8	298.3	346.5	421.2	570.6	682.7	690.0
115°	117.6	128.8	140.0	142.8	203.7	284.9	325.5	397.4	541.3	649.3	659.5
117.5°	132.8	143.0	153.2	155.7	207.5	276.6	311.1	376.0	505.9	603.3	614.6
120°	141.7	151.3	160.8	163.3	210.6	273.8	305.3	364.6	483.3	572.4	583.4
122.5°	150.4	160.1	169.7	172.1	215.0	272.3	300.8	354.3	461.2	541.3	552.2
125°	163.6	172.4	181.2	183.4	221.0	271.0	296.1	341.5	432.3	500.3	510.3
127.5°	174.4	183.3	192.2	194.5	227.0	270.4	292.1	331.0	408.9	467.4	475.8
130°	180.2	189.8	199.3	201.7	231.4	270.8	290.5	325.2	394.6	446.6	454.4
132.5°	186.1	195.8	205.3	207.7	234.9	271.0	289.2	320.2	382.3	428.9	435.9
135°	195.0	203.7	212.5	214.6	238.7	270.8	286.8	312.8	364.8	403.9	409.8
137.5°	204.1	212.7	221.4	223.5	244.5	272.4	286.5	308.4	352.4	385.4	390.3
140°	211.6	219.5	227.5	229.5	248.0	272.7	285.1	304.1	342.1	370.6	375.2
142.5°	217.3	224.7	232.0	233.9	251.0	273.7	285.1	301.8	335.1	360.2	364.1
145°	226.2	232.6	239.0	240.6	254.8	273.8	283.2	296.8	324.1	344.6	347.5
147.5°	235.1	241.3	247.5	249.1	260.5	275.6	283.2	293.9	315.4	331.5	334.0
150°	240.8	246.4	252.1	253.5	263.4	276.6	283.2	292.2	310.4	324.0	326.1
152.5°	246.8	251.1	255.4	256.4	265.3	277.2	283.2	290.9	306.4	318.0	319.5
155°	255.6	258.8	262.0	262.7	269.6	278.6	283.2	289.4	301.7	310.9	312.0
157.5°	262.2	265.3	268.3	269.1	273.8	280.0	283.2	288.0	297.6	304.8	305.5
160°	266.7	269.0	271.4	272.0	275.7	280.7	283.2	287.3	295.5	301.7	302.1
162.5°	271.0	272.8	274.6	275.1	277.8	281.4	283.2	286.6	293.6	298.8	299.2
165°	275.9	277.5	279.2	279.5	280.8	282.3	283.2	285.6	290.6	294.3	294.7
167.5°	280.3	281.0	281.8	282.0	283.0	284.4	285.1	286.7	290.0	292.4	292.6
170°	283.2	283.9	284.7	284.9	285.0	285.1	285.1	286.7	290.0	292.4	292.4
172.5°	284.7	284.9	285.1	285.1	285.1	285.1	285.1	286.4	288.9	290.8	290.7
175°	286.8	286.8	286.8	286.8	286.3	285.4	285.1	285.9	287.6	288.8	288.8
177.5°	286.8	286.8	286.8	286.8	286.4	285.8	285.5	286.2	287.5	288.4	288.2
180°	286.8	286.8	286.8	286.8	286.8	286.8	286.8	286.8	286.8	286.8	286.8

TEST NUMBER: P936706

CATALOG NUMBER: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	194.8	194.8
2.5°	208.0	206.8
5°	267.6	268.8
7.5°	360.2	359.7
10°	448.0	453.6
12.5°	511.9	513.1
15°	550.8	553.3
17.5°	565.8	566.5
20°	566.5	565.2
22.5°	559.6	558.3
25°	551.4	550.8
27.5°	543.9	544.5
30°	540.7	542.7
32.5°	540.7	543.9
35°	542.0	545.1
37.5°	541.3	545.1
40°	538.8	543.2
42.5°	532.0	535.1
45°	521.3	525.1
47.5°	507.5	510.1
50°	490.0	492.5
52.5°	468.0	468.7
55°	441.8	444.2
57.5°	413.6	414.1
60°	382.2	384.1
62.5°	349.0	349.0
65°	313.9	315.1
67.5°	277.6	280.7
70°	240.6	241.3
72.5°	204.3	204.3
75°	166.6	167.3
77.5°	130.9	130.9
80°	97.1	97.8
82.5°	67.1	68.3
85°	41.9	41.9
87.5°	19.4	17.6
90°	7.3	7.3
92.5°	29.3	23.4
95°	102.1	84.5
97.5°	244.7	211.2
100°	352.6	312.6
102.5°	458.7	424.5
105°	594.0	575.6
107.5°	682.6	687.1
110°	716.4	735.5

TEST NUMBER: P936706

CATALOG NUMBER: SQ4-FB-050U-050D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	719.5	748.9
115°	700.3	741.1
117.5°	659.9	705.2
120°	627.3	671.3
122.5°	595.6	638.9
125°	550.2	590.2
127.5°	509.5	543.2
130°	485.6	516.7
132.5°	463.7	491.7
135°	433.9	457.9
137.5°	409.9	429.6
140°	393.6	412.0
142.5°	380.0	395.8
145°	359.6	371.5
147.5°	343.9	353.8
150°	334.1	342.1
152.5°	325.6	331.7
155°	316.0	320.0
157.5°	308.3	311.1
160°	303.7	305.3
162.5°	300.7	302.2
165°	296.4	298.0
167.5°	293.3	293.9
170°	292.4	292.4
172.5°	290.1	289.5
175°	288.8	288.8
177.5°	287.6	286.8
180°	286.8	286.8

(END OF REPORT)