

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936808

Luminaire Tested: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936808
REPORT IS A COMBINATION OF REPORTS P933486 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8215.5 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936808

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P936808

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	98	94	89	86	91	87	83	80	75	72	69	63	61	59	53	51	50
2	89	81	74	69	82	75	70	65	65	60	56	55	51	49	45	43	41
3	81	71	63	57	74	66	59	53	56	51	47	48	44	40	40	37	34
4	73	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29
5	67	55	46	40	62	51	44	38	44	38	33	37	33	29	31	28	25
6	62	49	40	34	57	46	38	32	39	33	29	33	29	25	28	24	21
7	57	44	36	30	52	41	34	28	35	29	25	30	25	22	25	22	19
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15
10	46	33	25	20	42	31	24	19	27	21	17	23	18	15	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2695	2695	2695
5°	2633	3115	3623
10°	2388	4541	6007
15°	2030	5933	7253
20°	1652	6875	7392
25°	1379	7195	7242
30°	1163	7241	7228
35°	1028	7120	7415
40°	895	6964	7608
45°	811	6850	7638
50°	744	6747	7511
55°	713	6596	7179
60°	729	6306	6653
65°	759	5866	5930
70°	808	5116	5010
75°	896	4171	3910
80°	978	2893	2634
85°	871	1535	1349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7638 cd/sqm

TEST NUMBER: P936808

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.1	0.9
10°-20°	333.1	4.1
20°-30°	582.6	7.1
30°-40°	750.0	9.1
40°-50°	837.7	10.2
50°-60°	802.3	9.8
60°-70°	635.8	7.7
70°-80°	373.9	4.6
80°-90°	106.1	1.3
90°-100°	279.6	3.4
100°-110°	735.2	8.9
110°-120°	762.3	9.3
120°-130°	611.4	7.4
130°-140°	479.8	5.8
140°-150°	368.3	4.5
150°-160°	265.2	3.2
160°-170°	162.3	2.0
170°-180°	54.8	0.7
0°-30°	990.8	12.1
0°-40°	1740.8	21.2
0°-60°	3380.8	41.2
0°-90°	4496.6	54.7
90°-120°	1777.1	21.6
90°-150°	3236.6	39.4
90°-180°	3719.0	45.3
0°-180°	8215.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	581	581	581	581	581	
5°	566	607	684	773	801	52
15°	424	783	1319	1599	1650	118
25°	271	887	1571	1640	1642	125
35°	183	848	1480	1564	1625	114
45°	125	676	1308	1498	1566	97
55°	90	430	1110	1289	1324	82
65°	71	228	824	926	940	70
75°	52	140	452	497	499	55
85°	19	43	112	123	125	20
90°	4	11	29	15	15	4
95°	37	145	482	248	169	41
105°	132	201	813	1234	1151	140
115°	235	286	651	1299	1482	232
125°	327	367	592	1001	1180	291
135°	390	429	574	808	916	302
145°	452	481	566	689	743	283
155°	511	526	566	622	640	235
165°	552	559	566	589	596	156
175°	574	574	570	578	578	54
180°	574	574	574	574	574	

TEST NUMBER: P936808

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	580.9	580.9	580.9	580.9	580.9	580.9	580.9	580.9	580.9	580.9	580.9
2.5°	580.9	580.9	584.7	586.6	590.3	592.2	595.9	599.6	610.8	612.7	616.4
5°	566.0	573.5	597.8	607.1	633.3	668.7	683.7	708.0	758.4	773.4	782.7
7.5°	543.6	560.4	620.2	635.1	700.5	793.9	833.1	885.4	965.8	1005.0	1036.7
10°	508.1	543.6	650.1	685.6	792.0	934.0	1006.9	1079.8	1201.2	1255.4	1275.9
12.5°	468.9	526.8	681.8	730.4	883.6	1091.0	1178.8	1259.1	1397.4	1470.2	1481.4
15°	424.0	502.5	711.7	782.7	980.7	1221.8	1318.9	1417.9	1546.8	1599.1	1612.2
17.5°	384.8	483.8	739.7	814.4	1055.4	1339.4	1438.5	1520.6	1625.3	1660.7	1670.1
20°	336.2	453.9	758.4	855.5	1134.0	1425.4	1520.6	1584.2	1655.1	1677.6	1681.3
22.5°	300.7	422.2	769.6	870.5	1186.3	1477.7	1558.0	1608.4	1657.0	1664.5	1666.3
25°	270.9	386.7	767.7	887.3	1231.1	1509.4	1571.1	1608.4	1636.5	1640.2	1640.2
27.5°	242.8	347.4	760.3	891.0	1264.7	1516.9	1565.5	1591.6	1604.7	1612.2	1612.2
30°	218.6	310.1	741.6	883.6	1279.7	1509.4	1548.7	1561.7	1574.8	1586.0	1591.6
32.5°	199.9	274.6	713.6	868.6	1281.5	1490.8	1518.8	1526.2	1544.9	1571.1	1580.4
35°	183.1	239.1	681.8	848.1	1270.3	1460.9	1479.5	1487.0	1524.4	1563.6	1576.7
37.5°	166.3	213.0	640.7	812.6	1253.5	1425.4	1438.5	1451.5	1509.4	1556.1	1571.1
40°	149.4	190.5	592.2	773.4	1227.4	1382.4	1393.6	1414.2	1490.8	1544.9	1559.9
42.5°	136.4	171.9	539.9	732.3	1193.7	1333.8	1350.7	1380.5	1468.3	1526.2	1543.1
45°	125.2	153.2	483.8	676.2	1150.8	1283.4	1307.7	1348.8	1442.2	1498.2	1513.2
47.5°	113.9	140.1	425.9	618.3	1104.1	1233.0	1264.7	1311.4	1406.7	1460.9	1473.9
50°	104.6	127.0	368.0	556.7	1053.6	1178.8	1216.2	1264.7	1361.9	1412.3	1429.1
52.5°	97.1	115.8	313.8	495.0	995.6	1122.8	1165.7	1216.2	1307.7	1356.3	1367.5
55°	89.7	106.5	267.1	429.6	935.9	1063.0	1109.7	1158.3	1247.9	1289.0	1296.5
57.5°	85.9	99.0	227.9	368.0	872.4	995.6	1047.9	1092.9	1176.9	1208.7	1216.2
60°	80.3	93.4	198.0	315.7	803.2	932.1	977.0	1021.8	1092.9	1119.0	1124.6
62.5°	74.7	89.7	175.6	265.3	732.3	857.4	902.2	943.3	1003.1	1021.8	1029.3
65°	71.0	85.9	158.8	227.9	659.4	779.0	823.8	859.3	907.8	926.5	930.3
67.5°	67.2	82.2	145.7	196.1	586.6	700.5	734.1	767.7	805.1	823.8	825.7
70°	61.6	78.5	134.5	173.7	511.8	610.8	638.9	674.3	704.2	713.6	719.2
72.5°	57.9	72.9	127.0	156.9	435.2	524.9	551.1	571.6	597.8	607.1	607.1
75°	52.3	65.4	119.6	140.1	356.8	429.6	452.1	472.6	493.2	496.9	491.3
77.5°	46.7	57.9	102.7	117.7	278.3	340.0	358.7	369.9	386.7	390.4	392.3
80°	39.2	50.4	80.3	91.5	201.7	250.3	263.4	272.7	287.7	287.7	291.4
82.5°	29.9	39.2	57.9	65.4	136.4	171.9	183.1	188.7	198.0	198.0	198.0
85°	18.7	24.3	37.4	43.0	82.2	104.6	112.1	113.9	121.4	123.3	123.3
87.5°	9.3	13.1	24.3	26.2	43.0	54.2	54.2	57.9	57.9	56.0	54.2
90°	3.8	6.9	10.0	10.7	16.9	25.1	29.2	26.0	19.5	14.7	14.7
92.5°	15.4	41.6	67.8	74.3	104.5	144.7	164.8	144.4	103.7	73.1	70.2
95°	37.0	84.9	132.8	144.8	257.0	406.8	481.7	429.8	326.2	248.4	239.6
97.5°	63.9	106.1	148.4	159.0	346.2	595.9	720.8	688.0	622.4	573.3	556.5
100°	84.7	123.0	161.3	170.9	378.7	655.8	794.3	796.7	801.5	805.0	785.0
102.5°	102.5	138.2	173.9	182.9	393.6	674.6	815.1	856.9	940.4	1002.9	985.8
105°	132.4	162.7	193.1	200.6	404.7	676.8	812.8	906.4	1093.6	1234.0	1224.8
107.5°	163.3	191.5	219.7	226.8	406.7	646.6	766.5	897.1	1158.3	1354.1	1356.4
110°	184.0	209.5	235.1	241.4	403.7	619.9	728.1	874.0	1165.9	1384.8	1394.5

TEST NUMBER: P936808

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	204.5	228.7	253.0	259.1	403.8	596.6	693.0	842.4	1141.2	1365.2	1380.0
115°	235.3	257.7	280.1	285.7	407.5	569.9	651.1	795.0	1082.8	1298.6	1319.0
117.5°	265.6	286.0	306.4	311.5	415.1	553.1	622.1	752.1	1011.8	1206.6	1229.2
120°	283.4	302.5	321.8	326.5	421.2	547.5	610.6	729.3	966.6	1144.6	1166.6
122.5°	300.7	320.0	339.3	344.2	430.0	544.5	601.8	708.6	922.4	1082.7	1104.4
125°	327.3	344.8	362.5	366.9	442.0	542.1	592.2	682.9	864.5	1000.7	1020.7
127.5°	348.8	366.6	384.3	388.8	453.9	540.7	584.0	662.0	817.9	934.8	951.7
130°	360.3	379.5	398.7	403.5	462.6	541.5	580.9	650.3	789.1	893.2	908.8
132.5°	372.3	391.4	410.7	415.4	469.7	542.1	578.3	640.4	764.7	857.8	871.7
135°	390.0	407.5	424.9	429.3	477.4	541.5	573.7	625.7	729.7	807.7	819.8
137.5°	408.2	425.4	442.7	447.0	488.9	544.9	572.9	616.9	704.9	770.8	780.6
140°	423.1	439.1	455.0	459.0	496.0	545.5	570.2	608.2	684.2	741.1	750.3
142.5°	434.7	449.3	464.1	467.7	501.9	547.4	570.2	603.6	670.3	720.4	728.3
145°	452.4	465.2	478.1	481.3	509.7	547.5	566.4	593.7	648.3	689.2	695.2
147.5°	470.1	482.6	495.1	498.2	520.9	551.2	566.4	587.9	630.7	663.0	667.9
150°	481.7	493.0	504.3	507.1	526.9	553.2	566.4	584.5	620.8	648.0	652.0
152.5°	493.6	502.2	510.7	512.9	530.7	554.5	566.4	581.9	612.8	636.1	639.1
155°	511.3	517.6	524.0	525.6	539.2	557.3	566.4	578.7	603.3	621.8	623.8
157.5°	524.3	530.5	536.7	538.3	547.6	560.1	566.4	575.9	595.1	609.4	610.8
160°	533.2	538.1	542.8	544.1	551.5	561.4	566.4	574.6	590.9	603.3	604.1
162.5°	542.1	545.7	549.3	550.2	555.6	562.8	566.4	573.3	587.2	597.6	598.3
165°	551.7	555.0	558.2	559.0	561.4	564.7	566.4	571.3	581.2	588.7	589.5
167.5°	560.6	562.1	563.7	564.0	566.1	568.8	570.2	573.5	580.0	584.9	585.2
170°	566.4	567.9	569.5	569.8	569.9	570.1	570.2	573.5	580.0	584.9	584.9
172.5°	569.5	569.8	570.1	570.2	570.2	570.2	570.2	572.8	578.0	581.8	581.5
175°	573.7	573.7	573.7	573.7	572.5	571.0	570.2	571.8	575.1	577.5	577.5
177.5°	573.7	573.7	573.7	573.7	572.7	571.5	571.0	572.3	574.8	576.7	576.4
180°	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7	573.7

TEST NUMBER: P936808

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	580.9	580.9
2.5°	620.2	616.4
5°	797.6	801.4
7.5°	1074.2	1072.3
10°	1335.7	1352.5
12.5°	1526.2	1530.0
15°	1642.1	1649.5
17.5°	1686.9	1688.8
20°	1688.8	1685.0
22.5°	1668.2	1664.5
25°	1643.9	1642.1
27.5°	1621.5	1623.4
30°	1612.2	1617.8
32.5°	1612.2	1621.5
35°	1615.9	1625.3
37.5°	1614.0	1625.3
40°	1606.6	1619.6
42.5°	1586.0	1595.4
45°	1554.3	1565.5
47.5°	1513.2	1520.6
50°	1460.9	1468.3
52.5°	1395.5	1397.4
55°	1317.0	1324.5
57.5°	1233.0	1234.8
60°	1139.6	1145.2
62.5°	1040.5	1040.5
65°	935.9	939.6
67.5°	827.5	836.9
70°	717.3	719.2
72.5°	609.0	609.0
75°	496.9	498.8
77.5°	390.4	390.4
80°	289.5	291.4
82.5°	199.9	203.6
85°	125.2	125.2
87.5°	57.9	52.3
90°	14.7	14.7
92.5°	58.6	47.0
95°	204.3	169.1
97.5°	489.4	422.4
100°	705.2	625.2
102.5°	917.4	848.9
105°	1188.0	1151.2
107.5°	1365.2	1374.1
110°	1432.8	1471.1

TEST NUMBER: P936808

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1438.8	1497.7
115°	1400.6	1482.3
117.5°	1319.8	1410.3
120°	1254.5	1342.5
122.5°	1191.1	1277.9
125°	1100.5	1180.5
127.5°	1019.1	1086.5
130°	971.1	1033.4
132.5°	927.6	983.3
135°	867.9	916.0
137.5°	820.1	859.4
140°	787.1	823.9
142.5°	759.9	791.6
145°	719.2	743.1
147.5°	687.8	707.7
150°	668.1	684.2
152.5°	651.3	663.4
155°	631.9	639.9
157.5°	616.5	622.1
160°	607.4	610.6
162.5°	601.4	604.5
165°	592.7	596.0
167.5°	586.6	588.0
170°	584.9	584.9
172.5°	580.3	579.1
175°	577.5	577.5
177.5°	575.1	573.7
180°	573.7	573.7

(END OF REPORT)