

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936902

Luminaire Tested: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936902
REPORT IS A COMBINATION OF REPORTS P933471 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4938.3 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936902

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P936902

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	95	91	87	93	89	85	82	78	75	72	67	65	63	58	56	55
2	90	82	75	70	84	77	71	66	67	63	59	58	55	52	50	48	45
3	82	72	64	57	76	67	60	54	59	53	49	51	47	43	44	40	38
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32
5	68	56	47	41	63	52	44	39	46	40	35	40	35	31	34	30	27
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	23
7	58	45	36	30	54	42	34	29	37	31	26	32	27	23	28	24	21
8	53	40	32	26	50	38	30	25	34	27	23	29	24	20	25	21	18
9	50	37	29	23	46	35	27	22	31	24	20	27	22	18	23	19	16
10	46	33	26	21	43	32	25	20	28	22	18	25	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3641	3641	3641
5°	3554	4205	4895
10°	3220	6127	8115
15°	2733	7998	9798
20°	2222	9262	9986
25°	1852	9684	9783
30°	1559	9738	9765
35°	1377	9569	10018
40°	1197	9350	10278
45°	1082	9189	10319
50°	991	9041	10148
55°	945	8829	9697
60°	964	8430	8988
65°	998	7829	8011
70°	1056	6814	6768
75°	1158	5541	5282
80°	1240	3828	3558
85°	1043	2020	1821

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10319 cd/sqm

TEST NUMBER: P936902

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	1.0
10°-20°	225.0	4.6
20°-30°	393.5	8.0
30°-40°	506.6	10.3
40°-50°	565.9	11.5
50°-60°	542.0	11.0
60°-70°	429.5	8.7
70°-80°	252.6	5.1
80°-90°	71.3	1.4
90°-100°	142.9	2.9
100°-110°	375.9	7.6
110°-120°	389.7	7.9
120°-130°	312.6	6.3
130°-140°	245.3	5.0
140°-150°	188.3	3.8
150°-160°	135.6	2.7
160°-170°	83.0	1.7
170°-180°	28.0	0.6
0°-30°	669.3	13.6
0°-40°	1175.9	23.8
0°-60°	2283.7	46.2
0°-90°	3037.1	61.5
90°-120°	908.5	18.4
90°-150°	1654.7	33.5
90°-180°	1901.0	38.5
0°-180°	4938.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	392	392	392	392	392	
5°	382	410	462	522	541	35
15°	286	529	891	1080	1114	80
25°	183	599	1061	1108	1109	84
35°	124	573	999	1056	1098	77
45°	84	457	883	1012	1058	65
55°	60	290	750	871	895	55
65°	48	154	556	626	635	48
75°	35	95	305	336	337	37
85°	13	29	76	83	84	13
90°	2	6	15	7	7	2
95°	19	74	246	127	86	21
105°	68	103	416	631	589	72
115°	120	146	333	664	758	119
125°	167	188	303	512	604	149
135°	199	220	293	413	468	154
145°	231	246	290	352	380	145
155°	261	269	290	318	327	120
165°	282	286	290	301	305	80
175°	293	293	292	295	295	28
180°	293	293	293	293	293	

TEST NUMBER: P936902

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	392.4	392.4	392.4	392.4	392.4	392.4	392.4	392.4	392.4	392.4	392.4
2.5°	392.4	392.4	395.0	396.2	398.7	400.0	402.5	405.0	412.7	413.9	416.4
5°	382.4	387.4	403.8	410.1	427.7	451.7	461.8	478.3	512.4	522.4	528.7
7.5°	367.2	378.6	419.0	429.1	473.2	536.3	562.8	598.1	652.4	678.9	700.3
10°	343.2	367.2	439.1	463.1	535.0	631.0	680.2	729.3	811.4	847.9	861.9
12.5°	316.8	355.8	460.6	493.4	596.9	737.0	796.3	850.5	943.9	993.1	1000.6
15°	286.4	339.4	480.7	528.7	662.5	825.3	890.9	957.8	1044.9	1080.2	1089.0
17.5°	260.0	326.8	499.7	550.2	713.0	904.8	971.6	1027.2	1097.9	1121.8	1128.1
20°	227.1	306.7	512.4	578.0	766.0	962.8	1027.2	1070.1	1118.0	1133.2	1135.7
22.5°	203.1	285.2	519.9	588.0	801.2	998.2	1052.4	1086.5	1119.3	1124.3	1125.6
25°	183.0	261.2	518.7	599.4	831.6	1019.6	1061.2	1086.5	1105.4	1107.9	1107.9
27.5°	164.1	234.7	513.6	601.9	854.2	1024.6	1057.5	1075.1	1083.9	1089.0	1089.0
30°	147.6	209.4	501.0	596.9	864.4	1019.6	1046.1	1054.9	1063.8	1071.3	1075.1
32.5°	135.0	185.5	482.1	586.8	865.6	1007.0	1025.9	1030.9	1043.5	1061.2	1067.6
35°	123.7	161.5	460.6	572.9	858.1	986.8	999.4	1004.5	1029.7	1056.2	1065.0
37.5°	112.3	143.8	432.8	548.9	846.7	962.8	971.6	980.5	1019.6	1051.2	1061.2
40°	100.9	128.7	400.0	522.4	829.0	933.8	941.3	955.3	1007.0	1043.5	1053.7
42.5°	92.2	116.1	364.7	494.7	806.3	900.9	912.3	932.6	991.9	1030.9	1042.3
45°	84.5	103.4	326.8	456.8	777.3	866.9	883.3	911.1	974.2	1012.0	1022.1
47.5°	77.0	94.6	287.7	417.7	745.8	832.9	854.2	885.9	950.2	986.8	995.6
50°	70.7	85.9	248.6	376.1	711.7	796.3	821.5	854.2	920.0	953.9	965.3
52.5°	65.6	78.2	212.0	334.4	672.6	758.4	787.4	821.5	883.3	916.1	923.7
55°	60.5	71.9	180.5	290.2	632.2	718.0	749.6	782.3	843.0	870.7	875.7
57.5°	58.1	66.8	153.9	248.6	589.3	672.6	707.9	738.2	794.9	816.4	821.5
60°	54.2	63.1	133.8	213.3	542.6	629.6	660.0	690.3	738.2	755.9	759.6
62.5°	50.5	60.5	118.6	179.2	494.7	579.2	609.5	637.3	677.7	690.3	695.3
65°	47.9	58.1	107.2	153.9	445.4	526.2	556.5	580.4	613.3	625.9	628.4
67.5°	45.5	55.5	98.5	132.5	396.2	473.2	495.9	518.7	543.9	556.5	557.7
70°	41.6	53.0	90.8	117.4	345.7	412.7	431.6	455.5	475.7	482.1	485.8
72.5°	39.2	49.2	85.9	106.0	294.0	354.6	372.3	386.1	403.8	410.1	410.1
75°	35.3	44.1	80.8	94.6	241.0	290.2	305.4	319.3	333.1	335.7	331.9
77.5°	31.5	39.2	69.4	79.5	188.0	229.7	242.3	249.8	261.2	263.8	265.0
80°	26.5	34.1	54.2	61.8	136.3	169.1	177.9	184.2	194.3	194.3	196.8
82.5°	20.2	26.5	39.2	44.1	92.2	116.1	123.7	127.5	133.8	133.8	133.8
85°	12.6	16.4	25.2	29.0	55.5	70.7	75.7	77.0	82.0	83.3	83.3
87.5°	6.3	8.8	16.4	17.7	29.0	36.6	36.6	39.2	39.2	37.8	36.6
90°	2.0	3.5	5.2	5.5	8.7	12.9	15.0	13.3	9.9	7.4	7.4
92.5°	7.8	21.2	34.7	38.0	53.4	73.9	84.2	73.8	53.0	37.4	35.9
95°	18.9	43.4	67.9	74.0	131.4	207.9	246.2	219.6	166.6	126.9	122.4
97.5°	32.7	54.2	75.8	81.3	177.0	304.6	368.4	351.7	318.2	293.1	284.5
100°	43.3	62.8	82.5	87.4	193.6	335.2	406.1	407.3	409.8	411.6	401.4
102.5°	52.3	70.7	88.9	93.5	201.2	344.9	416.7	438.1	480.7	512.7	504.0
105°	67.7	83.2	98.7	102.6	206.9	346.0	415.5	463.4	559.1	630.9	626.2
107.5°	83.5	97.9	112.3	115.9	207.9	330.6	391.9	458.7	592.2	692.3	693.4
110°	94.1	107.1	120.1	123.4	206.4	317.0	372.3	446.8	596.1	708.0	712.9

TEST NUMBER: P936902

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	104.5	116.9	129.3	132.5	206.4	305.0	354.3	430.7	583.4	698.0	705.6
115°	120.2	131.7	143.2	146.0	208.3	291.3	332.8	406.4	553.5	663.9	674.3
117.5°	135.8	146.2	156.6	159.2	212.2	282.8	318.1	384.5	517.2	616.8	628.4
120°	144.9	154.7	164.5	166.9	215.4	279.9	312.2	372.8	494.2	585.2	596.5
122.5°	153.8	163.7	173.5	176.0	219.8	278.4	307.6	362.2	471.6	553.5	564.6
125°	167.3	176.3	185.3	187.6	226.0	277.1	302.7	349.1	442.0	511.6	521.8
127.5°	178.3	187.5	196.5	198.8	232.1	276.5	298.6	338.5	418.1	477.9	486.5
130°	184.2	194.1	203.8	206.3	236.6	276.9	297.0	332.5	403.5	456.7	464.6
132.5°	190.3	200.2	209.9	212.4	240.2	277.1	295.7	327.4	390.9	438.5	445.7
135°	199.4	208.3	217.3	219.5	244.1	276.9	293.3	319.8	373.0	412.9	419.1
137.5°	208.7	217.5	226.3	228.5	250.0	278.6	292.9	315.3	360.3	394.0	399.1
140°	216.3	224.4	232.6	234.6	253.6	278.9	291.5	310.9	349.8	378.9	383.6
142.5°	222.2	229.8	237.2	239.1	256.6	279.8	291.5	308.6	342.7	368.2	372.3
145°	231.3	237.8	244.4	246.0	260.5	279.9	289.6	303.5	331.4	352.3	355.4
147.5°	240.4	246.8	253.1	254.7	266.3	281.8	289.6	300.5	322.5	338.9	341.5
150°	246.2	251.9	257.8	259.2	269.3	282.8	289.6	298.8	317.3	331.3	333.4
152.5°	252.3	256.7	261.1	262.1	271.3	283.4	289.6	297.5	313.3	325.2	326.7
155°	261.4	264.6	267.9	268.6	275.6	284.9	289.6	295.9	308.5	317.9	319.0
157.5°	268.1	271.2	274.4	275.1	279.9	286.3	289.6	294.4	304.3	311.6	312.4
160°	272.7	275.0	277.5	278.1	281.9	287.0	289.6	293.8	302.2	308.5	308.8
162.5°	277.1	279.0	280.8	281.2	284.0	287.7	289.6	293.1	300.2	305.5	305.9
165°	282.1	283.7	285.4	285.8	287.1	288.7	289.6	292.0	297.1	300.9	301.3
167.5°	286.6	287.4	288.1	288.3	289.4	290.8	291.5	293.2	296.5	299.0	299.2
170°	289.6	290.3	291.1	291.3	291.4	291.5	291.5	293.2	296.5	299.0	299.0
172.5°	291.1	291.3	291.5	291.5	291.5	291.5	291.5	292.8	295.4	297.4	297.2
175°	293.3	293.3	293.3	293.3	292.7	291.8	291.5	292.3	294.0	295.3	295.3
177.5°	293.3	293.3	293.3	293.3	292.8	292.2	291.9	292.6	293.9	294.9	294.7
180°	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3	293.3

TEST NUMBER: P936902

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	392.4	392.4
2.5°	419.0	416.4
5°	538.8	541.4
7.5°	725.6	724.3
10°	902.3	913.6
12.5°	1030.9	1033.5
15°	1109.2	1114.2
17.5°	1139.5	1140.7
20°	1140.7	1138.2
22.5°	1126.9	1124.3
25°	1110.5	1109.2
27.5°	1095.3	1096.5
30°	1089.0	1092.8
32.5°	1089.0	1095.3
35°	1091.6	1097.9
37.5°	1090.2	1097.9
40°	1085.3	1094.0
42.5°	1071.3	1077.6
45°	1049.9	1057.5
47.5°	1022.1	1027.2
50°	986.8	991.9
52.5°	942.6	943.9
55°	889.6	894.6
57.5°	832.9	834.1
60°	769.7	773.6
62.5°	702.9	702.9
65°	632.2	634.7
67.5°	559.1	565.4
70°	484.6	485.8
72.5°	411.4	411.4
75°	335.7	336.9
77.5°	263.8	263.8
80°	195.6	196.8
82.5°	135.0	137.5
85°	84.5	84.5
87.5°	39.2	35.3
90°	7.4	7.4
92.5°	30.0	24.0
95°	104.4	86.4
97.5°	250.2	215.9
100°	360.5	319.6
102.5°	469.0	434.0
105°	607.4	588.6
107.5°	697.9	702.5
110°	732.5	752.1



TEST NUMBER: P936902

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	735.6	765.7
115°	716.1	757.8
117.5°	674.7	721.0
120°	641.4	686.4
122.5°	609.0	653.3
125°	562.6	603.5
127.5°	521.0	555.4
130°	496.5	528.3
132.5°	474.2	502.7
135°	443.7	468.2
137.5°	419.1	439.3
140°	402.4	421.3
142.5°	388.5	404.7
145°	367.7	379.9
147.5°	351.6	361.8
150°	341.6	349.8
152.5°	332.9	339.1
155°	323.1	327.2
157.5°	315.2	318.1
160°	310.6	312.2
162.5°	307.5	309.0
165°	303.0	304.7
167.5°	299.9	300.5
170°	299.0	299.0
172.5°	296.6	296.0
175°	295.3	295.3
177.5°	294.0	293.3
180°	293.3	293.3

(END OF REPORT)