

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936907

Luminaire Tested: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936907
REPORT IS A COMBINATION OF REPORTS P933479 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7244.1 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936907

CATALOG NUMBER: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P936907

CATALOG NUMBER: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	95	91	87	93	89	85	82	78	75	72	67	65	63	58	56	55
2	90	82	75	70	84	77	71	66	67	63	59	58	55	52	50	48	45
3	82	72	64	57	76	67	60	54	59	53	49	51	47	43	44	40	38
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32
5	68	56	47	41	63	52	44	39	46	40	35	40	35	31	34	30	27
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	23
7	58	45	36	30	54	42	34	29	37	31	26	32	27	23	28	24	21
8	53	40	32	26	50	38	30	25	34	27	23	29	24	20	25	21	18
9	50	37	29	23	46	35	27	22	31	24	20	27	22	18	23	19	16
10	46	33	26	21	43	32	25	20	28	22	18	25	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3561	3561	3561
5°	3478	4114	4787
10°	3153	5997	7935
15°	2679	7833	9582
20°	2180	9075	9766
25°	1818	9494	9567
30°	1532	9552	9549
35°	1354	9390	9796
40°	1179	9181	10051
45°	1067	9028	10090
50°	979	8889	9924
55°	935	8687	9484
60°	957	8302	8789
65°	994	7718	7834
70°	1057	6727	6618
75°	1166	5479	5165
80°	1266	3796	3481
85°	1103	2011	1781

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10090 cd/sqm

TEST NUMBER: P936907

CATALOG NUMBER: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	1.0
10°-20°	330.0	4.6
20°-30°	577.3	8.0
30°-40°	743.1	10.3
40°-50°	830.0	11.5
50°-60°	795.0	11.0
60°-70°	630.0	8.7
70°-80°	370.5	5.1
80°-90°	104.6	1.4
90°-100°	209.7	2.9
100°-110°	551.4	7.6
110°-120°	571.7	7.9
120°-130°	458.6	6.3
130°-140°	359.8	5.0
140°-150°	276.2	3.8
150°-160°	198.9	2.7
160°-170°	121.7	1.7
170°-180°	41.1	0.6
0°-30°	981.8	13.6
0°-40°	1724.9	23.8
0°-60°	3349.9	46.2
0°-90°	4455.0	61.5
90°-120°	1332.8	18.4
90°-150°	2427.4	33.5
90°-180°	2789.0	38.5
0°-180°	7244.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	576	576	576	576	576	
5°	561	602	677	766	794	52
15°	420	776	1307	1584	1634	117
25°	268	879	1557	1625	1627	124
35°	181	840	1466	1549	1610	113
45°	124	670	1296	1484	1551	96
55°	89	426	1100	1277	1312	81
65°	70	226	816	918	931	70
75°	52	139	448	492	494	54
85°	18	43	111	122	124	20
90°	3	8	22	11	11	4
95°	28	108	361	186	127	31
105°	99	150	610	926	863	105
115°	176	214	488	974	1112	174
125°	246	275	444	750	885	218
135°	292	322	430	606	687	226
145°	339	361	425	517	557	213
155°	384	394	425	466	480	176
165°	414	419	425	442	447	117
175°	430	430	428	433	433	41
180°	430	430	430	430	430	

TEST NUMBER: P936907

CATALOG NUMBER: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6	575.6
2.5°	575.6	575.6	579.4	581.2	584.9	586.7	590.5	594.2	605.2	607.1	610.8
5°	560.9	568.2	592.3	601.6	627.5	662.7	677.4	701.5	751.5	766.3	775.6
7.5°	538.6	555.3	614.6	629.3	694.1	786.7	825.6	877.4	957.0	995.8	1027.3
10°	503.4	538.6	644.2	679.3	784.8	925.5	997.7	1069.9	1190.2	1243.9	1264.3
12.5°	464.6	522.0	675.7	723.8	875.5	1081.0	1168.0	1247.5	1384.6	1456.8	1467.9
15°	420.2	497.9	705.3	775.6	971.7	1210.6	1306.9	1404.9	1532.6	1584.4	1597.4
17.5°	381.4	479.4	733.0	807.1	1045.8	1327.2	1425.3	1506.7	1610.4	1645.5	1654.8
20°	333.2	449.8	751.5	847.8	1123.6	1412.3	1506.7	1569.7	1640.0	1662.2	1665.9
22.5°	298.0	418.3	762.6	862.5	1175.3	1464.1	1543.7	1593.7	1641.9	1649.3	1651.1
25°	268.4	383.1	760.7	879.3	1219.8	1495.6	1556.7	1593.7	1621.5	1625.2	1625.2
27.5°	240.6	344.3	753.4	882.9	1253.1	1503.0	1551.1	1577.1	1590.0	1597.4	1597.4
30°	216.6	307.3	734.9	875.5	1267.9	1495.6	1534.5	1547.5	1560.4	1571.5	1577.1
32.5°	198.1	272.1	707.0	860.7	1269.8	1477.1	1504.9	1512.2	1530.7	1556.7	1565.9
35°	181.4	237.0	675.7	840.3	1258.7	1447.5	1466.0	1473.4	1510.4	1549.3	1562.2
37.5°	164.8	211.0	634.9	805.2	1242.0	1412.3	1425.3	1438.3	1495.6	1541.8	1556.7
40°	148.0	188.8	586.7	766.3	1216.1	1369.7	1380.8	1401.2	1477.1	1530.7	1545.6
42.5°	135.1	170.3	534.9	725.6	1182.8	1321.6	1338.2	1367.8	1454.9	1512.2	1529.0
45°	124.0	151.8	479.4	670.1	1140.2	1271.6	1295.7	1336.5	1428.9	1484.5	1499.4
47.5°	112.9	138.8	422.1	612.7	1093.9	1221.7	1253.1	1299.4	1393.8	1447.5	1460.4
50°	103.7	125.9	364.6	551.6	1043.9	1168.0	1205.0	1253.1	1349.3	1399.3	1416.0
52.5°	96.3	114.8	310.9	490.5	986.6	1112.5	1155.0	1205.0	1295.7	1343.8	1355.0
55°	88.8	105.5	264.7	425.7	927.4	1053.2	1099.5	1147.6	1236.4	1277.2	1284.6
57.5°	85.2	98.1	225.8	364.6	864.4	986.6	1038.4	1082.9	1166.1	1197.6	1205.0
60°	79.6	92.6	196.2	312.8	796.0	923.6	968.1	1012.5	1082.9	1108.8	1114.3
62.5°	74.1	88.8	174.0	262.8	725.6	849.6	894.0	934.7	994.0	1012.5	1019.9
65°	70.3	85.2	157.4	225.8	653.4	771.9	816.3	851.4	899.6	918.1	921.8
67.5°	66.6	81.4	144.4	194.4	581.2	694.1	727.4	760.7	797.8	816.3	818.2
70°	61.1	77.7	133.3	172.1	507.2	605.2	633.1	668.2	697.8	707.0	712.6
72.5°	57.3	72.2	125.9	155.5	431.3	520.1	546.0	566.4	592.3	601.6	601.6
75°	51.8	64.8	118.4	138.8	353.5	425.7	447.9	468.3	488.7	492.4	486.8
77.5°	46.2	57.3	101.8	116.7	275.8	336.9	355.4	366.5	383.1	386.9	388.7
80°	38.9	50.0	79.6	90.7	199.9	248.1	261.0	270.2	285.1	285.1	288.8
82.5°	29.6	38.9	57.3	64.8	135.1	170.3	181.4	187.0	196.2	196.2	196.2
85°	18.5	24.1	37.0	42.6	81.4	103.7	111.1	112.9	120.3	122.2	122.2
87.5°	9.2	13.0	24.1	25.9	42.6	53.7	53.7	57.3	57.3	55.6	53.7
90°	2.9	5.2	7.6	8.1	12.7	18.9	21.9	19.5	14.6	10.9	10.9
92.5°	11.6	31.2	50.8	55.8	78.4	108.5	123.6	108.3	77.7	54.8	52.7
95°	27.7	63.6	99.6	108.5	192.8	305.1	361.3	322.4	244.6	186.2	179.6
97.5°	47.9	79.7	111.3	119.3	259.7	447.0	540.6	516.0	466.8	429.9	417.3
100°	63.5	92.3	121.0	128.2	284.0	491.8	595.7	597.5	601.1	603.8	588.9
102.5°	76.8	103.7	130.5	137.2	295.2	505.9	611.3	642.6	705.3	752.2	739.4
105°	99.4	122.1	144.8	150.5	303.5	507.5	609.5	679.8	820.1	925.5	918.6
107.5°	122.4	143.6	164.8	170.1	305.0	484.9	574.9	672.8	868.6	1015.5	1017.2
110°	138.0	157.1	176.2	181.0	302.7	464.9	546.0	655.5	874.5	1038.7	1045.9

TEST NUMBER: P936907

CATALOG NUMBER: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	153.4	171.6	189.8	194.4	302.8	447.5	519.8	631.9	855.9	1023.9	1035.0
115°	176.4	193.2	210.1	214.3	305.6	427.4	488.3	596.3	812.1	974.0	989.3
117.5°	199.2	214.5	229.8	233.6	311.3	414.9	466.6	564.0	758.9	905.0	922.0
120°	212.5	226.9	241.3	244.9	315.9	410.6	457.9	547.0	725.0	858.4	875.0
122.5°	225.6	240.0	254.5	258.2	322.5	408.3	451.3	531.4	691.8	812.0	828.3
125°	245.5	258.6	271.9	275.2	331.5	406.6	444.1	512.2	648.4	750.5	765.4
127.5°	261.6	275.0	288.3	291.7	340.4	405.5	438.0	496.5	613.4	701.1	713.7
130°	270.3	284.7	299.1	302.6	347.0	406.1	435.7	487.7	591.9	670.0	681.6
132.5°	279.3	293.6	308.0	311.6	352.3	406.6	433.7	480.4	573.5	643.3	653.8
135°	292.5	305.6	318.7	321.9	358.1	406.2	430.3	469.3	547.3	605.8	614.9
137.5°	306.1	319.1	331.9	335.2	366.7	408.6	429.6	462.6	528.6	578.1	585.4
140°	317.4	329.3	341.2	344.2	372.0	409.1	427.7	456.2	513.1	555.8	562.7
142.5°	326.0	337.0	348.0	350.8	376.4	410.6	427.7	452.7	502.7	540.2	546.2
145°	339.3	348.9	358.6	361.0	382.3	410.6	424.8	445.2	486.1	516.9	521.4
147.5°	352.6	361.9	371.4	373.7	390.7	413.4	424.8	440.8	473.1	497.3	501.0
150°	361.3	369.8	378.2	380.3	395.2	414.9	424.8	438.4	465.6	486.0	488.9
152.5°	370.1	376.6	383.0	384.6	398.0	415.8	424.8	436.4	459.6	477.0	479.2
155°	383.5	388.3	392.9	394.1	404.3	418.0	424.8	434.0	452.5	466.3	467.8
157.5°	393.3	397.9	402.6	403.7	410.7	420.1	424.8	432.0	446.4	457.1	458.1
160°	399.9	403.5	407.0	408.0	413.6	421.0	424.8	430.9	443.3	452.5	453.1
162.5°	406.6	409.3	412.0	412.6	416.7	422.1	424.8	430.0	440.4	448.1	448.7
165°	413.8	416.2	418.6	419.3	421.1	423.6	424.8	428.5	435.9	441.5	442.2
167.5°	420.4	421.5	422.7	423.0	424.6	426.7	427.7	430.1	435.0	438.6	438.9
170°	424.8	425.9	427.1	427.4	427.5	427.6	427.7	430.1	435.0	438.6	438.6
172.5°	427.1	427.4	427.6	427.7	427.7	427.7	427.7	429.5	433.4	436.3	436.1
175°	430.3	430.3	430.3	430.3	429.5	428.2	427.7	428.9	431.3	433.1	433.1
177.5°	430.3	430.3	430.3	430.3	429.6	428.7	428.2	429.2	431.1	432.5	432.3
180°	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3

TEST NUMBER: P936907

CATALOG NUMBER: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	575.6	575.6
2.5°	614.6	610.8
5°	790.4	794.1
7.5°	1064.3	1062.5
10°	1323.5	1340.1
12.5°	1512.2	1516.0
15°	1627.0	1634.4
17.5°	1671.5	1673.3
20°	1673.3	1669.6
22.5°	1652.9	1649.3
25°	1628.9	1627.0
27.5°	1606.7	1608.5
30°	1597.4	1602.9
32.5°	1597.4	1606.7
35°	1601.2	1610.4
37.5°	1599.3	1610.4
40°	1591.8	1604.8
42.5°	1571.5	1580.8
45°	1540.1	1551.1
47.5°	1499.4	1506.7
50°	1447.5	1454.9
52.5°	1382.7	1384.6
55°	1305.0	1312.4
57.5°	1221.7	1223.5
60°	1129.1	1134.6
62.5°	1031.0	1031.0
65°	927.4	931.0
67.5°	820.0	829.2
70°	710.8	712.6
72.5°	603.5	603.5
75°	492.4	494.2
77.5°	386.9	386.9
80°	286.9	288.8
82.5°	198.1	201.7
85°	124.0	124.0
87.5°	57.3	51.8
90°	10.9	10.9
92.5°	43.9	35.2
95°	153.2	126.7
97.5°	367.1	316.8
100°	528.9	469.0
102.5°	688.1	636.7
105°	891.0	863.4
107.5°	1023.9	1030.6
110°	1074.6	1103.3

TEST NUMBER: P936907

CATALOG NUMBER: SQ4-FB-050U-100D-B50-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1079.1	1123.2
115°	1050.5	1111.7
117.5°	989.9	1057.8
120°	940.9	1006.9
122.5°	893.4	958.4
125°	825.4	885.3
127.5°	764.3	814.9
130°	728.3	775.0
132.5°	695.6	737.5
135°	650.9	687.0
137.5°	615.0	644.6
140°	590.3	617.9
142.5°	569.9	593.7
145°	539.4	557.3
147.5°	515.8	530.7
150°	501.1	513.1
152.5°	488.4	497.5
155°	473.9	479.9
157.5°	462.4	466.6
160°	455.5	457.9
162.5°	451.0	453.4
165°	444.6	447.0
167.5°	439.9	440.9
170°	438.6	438.6
172.5°	435.2	434.3
175°	433.1	433.1
177.5°	431.3	430.3
180°	430.3	430.3

(END OF REPORT)