

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936903

Luminaire Tested: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936903
REPORT IS A COMBINATION OF REPORTS P933479 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7407.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936903

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6

Luminous Intensity Polar Plot



TEST NUMBER: P936903

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20					20				20
RC	80				70				50					30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	100	95	91	87	93	89	85	82	78	75	72	67	65	63	58	56	55	50
2	90	82	75	70	84	77	71	66	67	63	59	58	55	52	50	48	45	41
3	82	72	64	57	76	67	60	54	59	53	49	51	47	43	44	40	38	34
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32	28
5	68	56	47	41	63	52	44	39	46	40	35	40	35	31	34	30	27	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	23	21
7	58	45	36	30	54	42	34	29	37	31	26	32	27	23	28	24	21	18
8	53	40	32	26	50	38	30	25	34	27	23	29	24	20	25	21	18	16
9	50	37	29	23	46	35	27	22	31	24	20	27	22	18	23	19	16	14
10	46	33	26	21	43	32	25	20	28	22	18	25	20	16	21	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3641	3641	3641
5°	3556	4207	4894
10°	3224	6131	8114
15°	2740	8009	9798
20°	2229	9279	9986
25°	1859	9707	9782
30°	1567	9766	9764
35°	1385	9602	10016
40°	1206	9388	10277
45°	1091	9231	10317
50°	1000	9089	10147
55°	957	8882	9697
60°	979	8489	8986
65°	1016	7892	8010
70°	1081	6878	6768
75°	1193	5602	5281
80°	1292	3880	3559
85°	1127	2054	1821

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10317 cd/sqm

TEST NUMBER: P936903

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.1	1.0
10°-20°	337.5	4.6
20°-30°	590.2	8.0
30°-40°	759.8	10.3
40°-50°	848.7	11.5
50°-60°	812.9	11.0
60°-70°	644.2	8.7
70°-80°	378.8	5.1
80°-90°	106.9	1.4
90°-100°	214.4	2.9
100°-110°	563.8	7.6
110°-120°	584.6	7.9
120°-130°	468.9	6.3
130°-140°	367.9	5.0
140°-150°	282.4	3.8
150°-160°	203.4	2.7
160°-170°	124.4	1.7
170°-180°	42.0	0.6
0°-30°	1003.8	13.6
0°-40°	1763.7	23.8
0°-60°	3425.2	46.2
0°-90°	4555.1	61.5
90°-120°	1362.8	18.4
90°-150°	2482.0	33.5
90°-180°	2852.0	38.5
0°-180°	7407.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	589	589	589	589	589	
5°	574	615	693	784	812	53
15°	430	793	1336	1620	1671	120
25°	274	899	1592	1662	1664	126
35°	186	859	1499	1584	1647	116
45°	127	685	1325	1518	1586	98
55°	91	435	1124	1306	1342	83
65°	72	231	835	939	952	71
75°	53	142	458	504	505	55
85°	19	44	114	125	127	20
90°	3	8	22	11	11	4
95°	28	111	369	190	130	31
105°	102	154	623	946	883	108
115°	180	219	499	996	1137	178
125°	251	281	454	767	905	223
135°	299	329	440	619	702	231
145°	347	369	434	528	570	217
155°	392	403	434	477	491	180
165°	423	429	434	451	457	119
175°	440	440	437	443	443	42
180°	440	440	440	440	440	

TEST NUMBER: P936903

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	588.6	588.6	588.6	588.6	588.6	588.6	588.6	588.6	588.6	588.6	588.6
2.5°	588.6	588.6	592.4	594.3	598.0	599.9	603.8	607.6	618.8	620.8	624.6
5°	573.5	581.0	605.7	615.1	641.6	677.6	692.7	717.3	768.4	783.6	793.0
7.5°	550.7	567.7	628.4	643.5	709.8	804.4	844.1	897.1	978.5	1018.2	1050.4
10°	514.7	550.7	658.7	694.6	802.5	946.3	1020.1	1094.0	1217.0	1271.9	1292.7
12.5°	475.0	533.7	690.8	740.0	895.2	1105.3	1194.2	1275.6	1415.7	1489.5	1500.9
15°	429.7	509.1	721.1	793.0	993.6	1237.8	1336.2	1436.5	1567.1	1620.1	1633.3
17.5°	389.9	490.2	749.5	825.2	1069.3	1357.1	1457.3	1540.6	1646.6	1682.5	1692.0
20°	340.6	459.9	768.4	866.9	1148.9	1444.1	1540.6	1605.0	1676.9	1699.6	1703.3
22.5°	304.7	427.7	779.8	881.9	1201.8	1497.1	1578.4	1629.5	1678.8	1686.3	1688.2
25°	274.5	391.7	777.8	899.0	1247.2	1529.2	1591.7	1629.5	1658.0	1661.7	1661.7
27.5°	246.0	352.0	770.3	902.8	1281.3	1536.8	1586.0	1612.5	1625.8	1633.3	1633.3
30°	221.5	314.2	751.4	895.2	1296.4	1529.2	1569.0	1582.2	1595.5	1606.8	1612.5
32.5°	202.6	278.2	722.9	880.0	1298.3	1510.3	1538.7	1546.2	1565.1	1591.7	1601.2
35°	185.5	242.3	690.8	859.2	1287.0	1480.1	1499.0	1506.5	1544.3	1584.2	1597.3
37.5°	168.5	215.7	649.2	823.3	1270.0	1444.1	1457.3	1470.6	1529.2	1576.5	1591.7
40°	151.4	193.0	599.9	783.6	1243.4	1400.5	1411.9	1432.7	1510.3	1565.1	1580.3
42.5°	138.2	174.1	546.9	741.9	1209.4	1351.3	1368.3	1398.6	1487.6	1546.2	1563.3
45°	126.8	155.2	490.2	685.1	1165.9	1300.2	1324.9	1366.5	1461.1	1517.9	1533.1
47.5°	115.5	141.9	431.6	626.5	1118.5	1249.1	1281.3	1328.6	1425.1	1480.1	1493.2
50°	106.0	128.7	372.8	564.0	1067.4	1194.2	1232.1	1281.3	1379.7	1430.8	1447.9
52.5°	98.5	117.4	317.9	501.6	1008.8	1137.5	1181.0	1232.1	1324.9	1374.1	1385.4
55°	90.8	107.9	270.6	435.3	948.2	1076.9	1124.2	1173.4	1264.2	1305.9	1313.5
57.5°	87.1	100.3	230.9	372.8	883.9	1008.8	1061.8	1107.2	1192.3	1224.5	1232.1
60°	81.4	94.6	200.6	319.8	813.9	944.4	989.9	1035.2	1107.2	1133.7	1139.3
62.5°	75.7	90.8	177.9	268.7	741.9	868.7	914.1	955.8	1016.3	1035.2	1042.9
65°	71.9	87.1	160.9	230.9	668.1	789.2	834.7	870.6	919.9	938.8	942.5
67.5°	68.1	83.3	147.6	198.7	594.3	709.8	743.8	777.8	815.8	834.7	836.6
70°	62.5	79.5	136.3	176.0	518.6	618.8	647.3	683.2	713.5	722.9	728.7
72.5°	58.6	73.8	128.7	159.0	441.0	531.8	558.3	579.1	605.7	615.1	615.1
75°	53.0	66.3	121.1	141.9	361.5	435.3	458.0	478.8	499.7	503.5	497.7
77.5°	47.3	58.6	104.1	119.3	282.0	344.5	363.4	374.7	391.7	395.6	397.5
80°	39.7	51.1	81.4	92.7	204.4	253.6	266.8	276.3	291.5	291.5	295.3
82.5°	30.3	39.7	58.6	66.3	138.2	174.1	185.5	191.2	200.6	200.6	200.6
85°	18.9	24.6	37.8	43.5	83.3	106.0	113.5	115.5	123.0	124.9	124.9
87.5°	9.5	13.3	24.6	26.5	43.5	54.9	54.9	58.6	58.6	56.8	54.9
90°	3.0	5.3	7.7	8.3	13.0	19.3	22.4	20.0	14.9	11.2	11.2
92.5°	11.8	31.9	52.0	57.0	80.1	111.0	126.3	110.7	79.5	56.1	53.9
95°	28.4	65.0	101.8	111.0	197.1	312.0	369.4	329.7	250.1	190.4	183.6
97.5°	49.0	81.5	113.8	122.0	265.6	457.1	552.8	527.6	477.3	439.6	426.7
100°	64.9	94.4	123.8	131.1	290.4	502.9	609.1	610.9	614.6	617.4	602.1
102.5°	78.5	106.0	133.4	140.3	301.9	517.3	625.0	657.0	721.1	769.2	756.1
105°	101.6	124.8	148.0	153.9	310.3	518.9	623.2	695.0	838.6	946.3	939.2
107.5°	125.2	146.9	168.5	173.9	311.9	495.8	587.8	687.9	888.2	1038.4	1040.1
110°	141.1	160.6	180.2	185.1	309.5	475.4	558.3	670.2	894.2	1062.1	1069.4

TEST NUMBER: P936903

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	156.8	175.4	194.1	198.7	309.6	457.5	531.5	646.1	875.2	1047.0	1058.2
115°	180.4	197.6	214.8	219.1	312.5	437.0	499.3	609.7	830.4	995.9	1011.5
117.5°	203.7	219.4	234.9	238.8	318.3	424.2	477.1	576.7	775.9	925.3	942.7
120°	217.3	232.0	246.7	250.4	323.0	419.8	468.2	559.2	741.3	877.7	894.6
122.5°	230.6	245.4	260.2	264.0	329.8	417.5	461.5	543.4	707.4	830.3	846.9
125°	251.0	264.4	278.0	281.3	338.9	415.7	454.1	523.7	663.0	767.3	782.6
127.5°	267.5	281.2	294.8	298.2	348.1	414.7	447.9	507.7	627.1	716.8	729.7
130°	276.4	291.1	305.8	309.4	354.8	415.2	445.5	498.7	605.2	685.0	697.0
132.5°	285.5	300.3	315.0	318.6	360.2	415.7	443.5	491.2	586.4	657.8	668.5
135°	299.1	312.5	325.8	329.2	366.1	415.3	440.0	479.9	559.6	619.4	628.7
137.5°	313.0	326.2	339.4	342.7	374.9	417.8	439.3	473.0	540.4	591.0	598.6
140°	324.5	336.7	348.9	351.9	380.4	418.3	437.3	466.4	524.7	568.3	575.4
142.5°	333.3	344.6	355.8	358.7	384.9	419.8	437.3	462.9	514.0	552.4	558.5
145°	347.0	356.8	366.6	369.1	390.9	419.8	434.3	455.2	497.1	528.5	533.1
147.5°	360.5	370.1	379.7	382.1	399.5	422.7	434.3	450.8	483.7	508.4	512.3
150°	369.4	378.1	386.7	388.9	404.1	424.2	434.3	448.3	476.1	496.9	499.9
152.5°	378.5	385.1	391.6	393.3	406.9	425.2	434.3	446.2	470.0	487.7	490.0
155°	392.1	397.0	401.8	403.0	413.4	427.4	434.3	443.8	462.7	476.8	478.4
157.5°	402.2	406.8	411.6	412.8	419.9	429.6	434.3	441.7	456.4	467.4	468.4
160°	408.9	412.6	416.2	417.1	422.9	430.5	434.3	440.6	453.2	462.7	463.3
162.5°	415.7	418.5	421.3	421.9	426.0	431.6	434.3	439.7	450.3	458.2	458.8
165°	423.1	425.5	428.0	428.7	430.6	433.1	434.3	438.2	445.7	451.4	452.1
167.5°	429.8	431.0	432.2	432.5	434.1	436.2	437.3	439.8	444.7	448.5	448.8
170°	434.3	435.5	436.7	437.0	437.1	437.2	437.3	439.8	444.7	448.5	448.5
172.5°	436.7	437.0	437.2	437.3	437.3	437.3	437.3	439.2	443.1	446.1	445.9
175°	440.0	440.0	440.0	440.0	439.1	437.9	437.3	438.5	441.0	442.8	442.8
177.5°	440.0	440.0	440.0	440.0	439.3	438.3	437.9	438.8	440.8	442.3	442.0
180°	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0

TEST NUMBER: P936903

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	588.6	588.6
2.5°	628.4	624.6
5°	808.1	811.9
7.5°	1088.2	1086.4
10°	1353.2	1370.2
12.5°	1546.2	1550.1
15°	1663.6	1671.2
17.5°	1709.1	1710.9
20°	1710.9	1707.2
22.5°	1690.1	1686.3
25°	1665.5	1663.6
27.5°	1642.8	1644.7
30°	1633.3	1639.0
32.5°	1633.3	1642.8
35°	1637.2	1646.6
37.5°	1635.2	1646.6
40°	1627.6	1640.9
42.5°	1606.8	1616.3
45°	1574.7	1586.0
47.5°	1533.1	1540.6
50°	1480.1	1487.6
52.5°	1413.8	1415.7
55°	1334.3	1341.9
57.5°	1249.1	1251.0
60°	1154.5	1160.1
62.5°	1054.2	1054.2
65°	948.2	951.9
67.5°	838.4	847.8
70°	726.8	728.7
72.5°	617.0	617.0
75°	503.5	505.3
77.5°	395.6	395.6
80°	293.4	295.3
82.5°	202.6	206.3
85°	126.8	126.8
87.5°	58.6	53.0
90°	11.2	11.2
92.5°	44.9	36.0
95°	156.6	129.6
97.5°	375.3	323.9
100°	540.8	479.5
102.5°	703.5	651.0
105°	911.1	882.8
107.5°	1046.9	1053.7
110°	1098.7	1128.1

TEST NUMBER: P936903

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-W2A-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1103.4	1148.5
115°	1074.1	1136.7
117.5°	1012.1	1081.5
120°	962.1	1029.6
122.5°	913.5	979.9
125°	843.9	905.2
127.5°	781.5	833.2
130°	744.7	792.5
132.5°	711.3	754.1
135°	665.5	702.4
137.5°	628.9	659.0
140°	603.6	631.8
142.5°	582.7	607.0
145°	551.5	569.8
147.5°	527.4	542.6
150°	512.4	524.7
152.5°	499.4	508.7
155°	484.6	490.7
157.5°	472.8	477.1
160°	465.8	468.2
162.5°	461.2	463.6
165°	454.6	457.1
167.5°	449.8	450.9
170°	448.5	448.5
172.5°	444.9	444.1
175°	442.8	442.8
177.5°	441.0	440.0
180°	440.0	440.0

(END OF REPORT)