

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937005

Luminaire Tested: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937005
REPORT IS A COMBINATION OF REPORTS P933464 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16989.4 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 168
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937005

CATALOG NUMBER: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P937005

CATALOG NUMBER: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	101	96	92	88	95	91	87	83	80	78	75	71	69	67	62	61	59
2	91	83	76	71	86	78	72	67	70	65	61	61	58	55	54	51	49
3	83	72	64	58	77	68	61	55	61	55	50	54	49	45	47	44	41
4	75	64	55	48	70	60	52	46	53	47	42	47	42	38	42	38	34
5	69	56	47	41	64	53	45	39	47	41	36	42	37	32	37	33	29
6	63	50	41	35	59	47	39	34	42	36	31	38	32	28	33	29	25
7	58	45	36	30	55	43	35	29	38	32	27	34	29	24	30	26	22
8	54	41	32	27	51	39	31	26	35	28	24	31	26	22	27	23	20
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4561	4561	4561
5°	4458	5273	6131
10°	4045	7688	10164
15°	3439	10047	12273
20°	2801	11646	12508
25°	2337	12190	12254
30°	1972	12270	12231
35°	1745	12069	12547
40°	1521	11808	12874
45°	1378	11618	12924
50°	1265	11447	12710
55°	1213	11196	12147
60°	1243	10709	11257
65°	1296	9966	10035
70°	1383	8698	8477
75°	1538	7098	6616
80°	1694	4929	4458
85°	1536	2620	2282

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 12924 cd/sqm

TEST NUMBER: P937005

CATALOG NUMBER: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	1.1
10°-20°	845.4	5.0
20°-30°	1478.8	8.7
30°-40°	1903.6	11.2
40°-50°	2126.3	12.5
50°-60°	2036.5	12.0
60°-70°	1613.9	9.5
70°-80°	949.0	5.6
80°-90°	266.9	1.6
90°-100°	419.4	2.5
100°-110°	1102.8	6.5
110°-120°	1143.4	6.7
120°-130°	917.2	5.4
130°-140°	719.7	4.2
140°-150°	552.4	3.3
150°-160°	397.8	2.3
160°-170°	243.4	1.4
170°-180°	82.2	0.5
0°-30°	2514.9	14.8
0°-40°	4418.6	26.0
0°-60°	8581.3	50.5
0°-90°	11411.2	67.2
90°-120°	2665.6	15.7
90°-150°	4854.8	28.6
90°-180°	5578.0	32.8
0°-180°	16989.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1475	1475	1475	1475	1475	
5°	1437	1541	1736	1963	2034	133
15°	1076	1987	3348	4059	4187	300
25°	688	2252	3988	4163	4168	317
35°	465	2153	3755	3969	4125	290
45°	318	1716	3319	3803	3974	246
55°	228	1090	2817	3272	3362	207
65°	180	578	2091	2352	2385	179
75°	133	356	1148	1261	1266	139
85°	47	109	284	313	318	50
90°	6	16	44	22	22	8
95°	56	217	722	372	254	62
105°	199	301	1219	1851	1727	211
115°	353	428	977	1948	2224	348
125°	491	550	888	1501	1771	436
135°	585	644	860	1212	1374	453
145°	679	722	850	1034	1115	425
155°	767	788	850	933	960	352
165°	828	838	850	883	894	234
175°	860	860	855	866	866	82
180°	860	860	860	860	860	

TEST NUMBER: P937005

CATALOG NUMBER: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7
2.5°	1474.7	1474.7	1484.1	1488.9	1498.3	1503.1	1512.6	1522.0	1550.5	1555.3	1564.7
5°	1436.7	1455.6	1517.3	1541.0	1607.4	1697.5	1735.5	1797.1	1925.1	1963.1	1986.7
7.5°	1379.8	1422.5	1574.3	1612.2	1778.1	2015.2	2114.8	2247.6	2451.5	2551.0	2631.6
10°	1289.8	1379.8	1650.1	1740.1	2010.4	2370.8	2555.7	2740.6	3048.9	3186.3	3238.6
12.5°	1190.2	1337.1	1730.7	1854.0	2242.8	2769.1	2992.0	3195.9	3546.8	3731.7	3760.1
15°	1076.3	1275.5	1806.5	1986.7	2489.4	3101.1	3347.5	3598.9	3926.1	4058.9	4092.0
17.5°	976.8	1228.1	1877.7	2067.3	2679.0	3399.8	3651.1	3859.7	4125.2	4215.3	4239.1
20°	853.5	1152.2	1925.1	2171.6	2878.2	3617.8	3859.7	4020.9	4201.1	4258.0	4267.4
22.5°	763.4	1071.6	1953.6	2209.6	3010.9	3750.7	3954.6	4082.5	4205.8	4224.8	4229.5
25°	687.5	981.5	1948.8	2252.2	3124.7	3831.3	3987.7	4082.5	4153.7	4163.1	4163.1
27.5°	616.4	882.0	1929.8	2261.8	3210.1	3850.2	3973.5	4039.8	4073.1	4092.0	4092.0
30°	554.8	787.1	1882.4	2242.8	3248.0	3831.3	3930.8	3964.0	3997.2	4025.6	4039.8
32.5°	507.3	697.0	1811.3	2204.9	3252.7	3783.8	3855.0	3874.0	3921.3	3987.7	4011.4
35°	464.7	606.9	1730.7	2152.7	3224.4	3708.0	3755.3	3774.4	3869.2	3968.8	4001.9
37.5°	422.0	540.5	1626.4	2062.6	3181.7	3617.8	3651.1	3684.3	3831.3	3949.8	3987.7
40°	379.3	483.6	1503.1	1963.1	3115.3	3508.9	3537.2	3589.5	3783.8	3921.3	3959.2
42.5°	346.1	436.3	1370.4	1858.8	3029.9	3385.6	3428.2	3504.1	3726.9	3874.0	3916.6
45°	317.7	388.8	1228.1	1716.5	2920.8	3257.5	3319.2	3423.5	3660.5	3802.8	3840.7
47.5°	289.3	355.7	1081.1	1569.5	2802.3	3129.5	3210.1	3328.6	3570.5	3708.0	3741.1
50°	265.5	322.4	934.1	1413.0	2674.3	2992.0	3086.8	3210.1	3456.6	3584.7	3627.4
52.5°	246.6	294.0	796.6	1256.5	2527.3	2849.7	2958.8	3086.8	3319.2	3442.4	3470.8
55°	227.6	270.3	678.1	1090.5	2375.5	2698.0	2816.6	2939.9	3167.4	3271.7	3290.7
57.5°	218.1	251.3	578.5	934.1	2214.3	2527.3	2660.0	2773.9	2987.2	3067.8	3086.8
60°	203.9	237.0	502.6	801.4	2038.9	2366.1	2479.9	2593.7	2773.9	2840.2	2854.5
62.5°	189.7	227.6	445.7	673.3	1858.8	2176.4	2290.2	2394.5	2546.3	2593.7	2612.7
65°	180.2	218.1	403.0	578.5	1673.8	1977.3	2091.0	2181.2	2304.5	2351.8	2361.3
67.5°	170.7	208.7	369.9	497.9	1488.9	1778.1	1863.4	1948.8	2043.7	2091.0	2095.8
70°	156.4	199.1	341.4	440.9	1299.2	1550.5	1621.6	1711.7	1787.6	1811.3	1825.5
72.5°	147.0	184.9	322.4	398.3	1104.8	1332.4	1398.8	1451.0	1517.3	1541.0	1541.0
75°	132.7	166.0	303.5	355.7	905.6	1090.5	1147.5	1199.6	1251.7	1261.3	1247.1
77.5°	118.5	147.0	260.8	298.7	706.5	863.0	910.4	938.9	981.5	991.0	995.7
80°	99.6	128.1	203.9	232.4	512.1	635.4	668.6	692.3	730.2	730.2	739.7
82.5°	75.8	99.6	147.0	166.0	346.1	436.3	464.7	478.9	502.6	502.6	502.6
85°	47.4	61.6	94.8	109.1	208.7	265.5	284.5	289.3	308.2	313.0	313.0
87.5°	23.7	33.2	61.6	66.4	109.1	137.5	137.5	147.0	147.0	142.2	137.5
90°	5.8	10.4	15.0	16.2	25.4	37.7	43.9	39.0	29.2	21.9	21.9
92.5°	23.1	62.3	101.6	111.4	156.6	217.0	247.1	216.6	155.5	109.7	105.4
95°	55.5	127.3	199.2	217.2	385.6	610.2	722.4	644.6	489.1	372.5	359.2
97.5°	95.8	159.2	222.7	238.5	519.4	893.8	1081.1	1032.0	933.6	859.9	834.8
100°	127.0	184.6	242.0	256.4	568.1	983.6	1191.4	1195.0	1202.2	1207.6	1177.6
102.5°	153.6	207.3	260.9	274.3	590.4	1011.9	1222.6	1285.2	1410.4	1504.4	1478.7
105°	198.7	244.1	289.4	300.8	606.9	1015.1	1219.2	1359.5	1640.3	1850.9	1837.1
107.5°	244.9	287.2	329.6	340.2	610.1	970.0	1149.8	1345.7	1737.4	2031.2	2034.5
110°	276.1	314.3	352.6	362.1	605.4	929.9	1092.1	1311.1	1748.9	2077.3	2091.7

TEST NUMBER: P937005

CATALOG NUMBER: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	306.6	343.1	379.5	388.6	605.6	894.9	1039.5	1263.6	1711.7	2047.9	2069.9
115°	352.9	386.5	420.1	428.5	611.2	854.8	976.6	1192.4	1624.1	1948.0	1978.6
117.5°	398.4	429.0	459.5	467.2	622.5	829.7	933.3	1128.1	1517.7	1809.9	1843.8
120°	425.1	453.8	482.5	489.7	631.8	821.3	916.0	1094.0	1449.9	1717.0	1749.9
122.5°	451.0	480.1	509.0	516.3	645.1	816.8	902.6	1062.9	1383.5	1623.9	1656.4
125°	490.9	517.3	543.8	550.4	663.0	813.1	888.2	1024.4	1296.7	1500.9	1530.9
127.5°	523.2	549.9	576.7	583.3	680.9	811.0	876.1	993.0	1226.8	1402.2	1427.5
130°	540.6	569.4	598.0	605.2	694.0	812.3	871.5	975.6	1183.8	1339.8	1363.2
132.5°	558.4	587.2	616.0	623.2	704.6	813.1	867.4	960.6	1147.0	1286.7	1307.6
135°	585.1	611.2	637.4	643.9	716.1	812.4	860.5	938.6	1094.6	1211.7	1229.7
137.5°	612.1	638.1	664.1	670.5	733.5	817.4	859.4	925.3	1057.3	1156.2	1171.0
140°	634.7	658.6	682.4	688.4	744.0	818.2	855.3	912.2	1026.3	1111.7	1125.6
142.5°	652.0	674.1	696.2	701.7	752.9	821.2	855.3	905.3	1005.5	1080.5	1092.4
145°	678.6	697.8	717.0	721.9	764.5	821.2	849.6	890.5	972.4	1033.8	1042.7
147.5°	705.2	723.8	742.6	747.3	781.4	826.9	849.6	881.8	946.2	994.5	1002.0
150°	722.4	739.4	756.4	760.6	790.3	829.8	849.6	876.7	931.1	971.9	978.0
152.5°	740.4	753.2	766.1	769.2	796.0	831.7	849.6	872.8	919.2	954.1	958.7
155°	766.9	776.4	786.0	788.3	808.8	835.9	849.6	868.1	905.0	932.7	935.7
157.5°	786.6	795.9	805.0	807.3	821.5	840.2	849.6	864.0	892.6	914.2	916.3
160°	799.9	807.1	814.3	816.0	827.2	842.1	849.6	861.9	886.5	905.0	906.2
162.5°	813.1	818.6	824.0	825.3	833.4	844.1	849.6	859.9	880.7	896.3	897.4
165°	827.6	832.5	837.3	838.5	842.2	847.1	849.6	857.0	871.9	883.0	884.2
167.5°	840.9	843.1	845.5	846.0	849.1	853.2	855.3	860.1	869.9	877.2	877.8
170°	849.6	851.8	854.1	854.7	854.9	855.2	855.3	860.1	869.9	877.2	877.2
172.5°	854.1	854.6	855.2	855.3	855.3	855.3	855.3	859.1	866.8	872.6	872.2
175°	860.5	860.5	860.5	860.5	858.7	856.4	855.3	857.7	862.6	866.3	866.3
177.5°	860.5	860.5	860.5	860.5	859.2	857.4	856.5	858.4	862.3	865.2	864.6
180°	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5	860.5

TEST NUMBER: P937005

CATALOG NUMBER: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1474.7	1474.7
2.5°	1574.3	1564.7
5°	2024.7	2034.2
7.5°	2726.4	2721.7
10°	3390.2	3432.9
12.5°	3874.0	3883.4
15°	4167.9	4186.8
17.5°	4281.7	4286.4
20°	4286.4	4277.0
22.5°	4234.3	4224.8
25°	4172.6	4167.9
27.5°	4115.8	4120.5
30°	4092.0	4106.2
32.5°	4092.0	4115.8
35°	4101.5	4125.2
37.5°	4096.8	4125.2
40°	4077.8	4111.0
42.5°	4025.6	4049.4
45°	3945.0	3973.5
47.5°	3840.7	3859.7
50°	3708.0	3726.9
52.5°	3542.0	3546.8
55°	3342.9	3361.8
57.5°	3129.5	3134.2
60°	2892.4	2906.6
62.5°	2641.1	2641.1
65°	2375.5	2385.1
67.5°	2100.6	2124.3
70°	1820.8	1825.5
72.5°	1545.8	1545.8
75°	1261.3	1266.0
77.5°	991.0	991.0
80°	735.0	739.7
82.5°	507.3	516.9
85°	317.7	317.7
87.5°	147.0	132.7
90°	21.9	21.9
92.5°	87.9	70.4
95°	306.4	253.5
97.5°	734.1	633.5
100°	1057.8	937.9
102.5°	1376.1	1273.4
105°	1782.0	1726.8
107.5°	2047.8	2061.2
110°	2149.1	2206.7

TEST NUMBER: P937005

CATALOG NUMBER: SQ4-FB-050U-125D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2158.3	2246.6
115°	2101.0	2223.5
117.5°	1979.6	2115.4
120°	1881.9	2013.8
122.5°	1786.6	1916.8
125°	1650.8	1770.7
127.5°	1528.6	1629.7
130°	1456.7	1550.1
132.5°	1391.3	1475.0
135°	1301.8	1373.9
137.5°	1230.0	1289.0
140°	1180.7	1235.9
142.5°	1139.9	1187.4
145°	1078.7	1114.6
147.5°	1031.7	1061.5
150°	1002.1	1026.3
152.5°	976.9	995.1
155°	947.8	959.9
157.5°	924.8	933.3
160°	911.1	916.0
162.5°	902.1	906.7
165°	889.2	894.0
167.5°	879.8	881.9
170°	877.2	877.2
172.5°	870.4	868.6
175°	866.3	866.3
177.5°	862.5	860.5
180°	860.5	860.5

(END OF REPORT)