

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937108

Luminaire Tested: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937108
REPORT IS A COMBINATION OF REPORTS P933517 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8610.6 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 68.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937108

CATALOG NUMBER: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P937108

CATALOG NUMBER: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1766	2089	2430
10°	1602	3046	4028
15°	1361	3979	4864
20°	1108	4611	4957
25°	925	4825	4856
30°	779	4855	4847
35°	689	4775	4973
40°	601	4670	5102
45°	544	4593	5122
50°	499	4525	5037
55°	478	4423	4814
60°	490	4229	4461
65°	509	3934	3977
70°	543	3430	3360
75°	601	2797	2622
80°	656	1939	1766
85°	582	1030	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5122 cd/sqm

TEST NUMBER: P937108

CATALOG NUMBER: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	0.6
10°-20°	223.4	2.6
20°-30°	390.7	4.5
30°-40°	502.9	5.8
40°-50°	561.8	6.5
50°-60°	538.1	6.2
60°-70°	426.4	5.0
70°-80°	250.7	2.9
80°-90°	73.0	0.8
90°-100°	420.6	4.9
100°-110°	1105.7	12.8
110°-120°	1146.5	13.3
120°-130°	919.6	10.7
130°-140°	721.6	8.4
140°-150°	553.9	6.4
150°-160°	398.9	4.6
160°-170°	244.0	2.8
170°-180°	82.5	1.0
0°-30°	664.5	7.7
0°-40°	1167.4	13.6
0°-60°	2267.2	26.3
0°-90°	3017.3	35.0
90°-120°	2672.8	31.0
90°-150°	4867.9	56.5
90°-180°	5593.0	65.0
0°-180°	8610.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	390	390	390	390	390	
5°	380	407	458	519	537	35
15°	284	525	884	1072	1106	79
25°	182	595	1054	1100	1101	84
35°	123	569	992	1049	1090	77
45°	84	454	877	1005	1050	65
55°	60	288	744	864	888	55
65°	48	153	552	621	630	47
75°	35	94	303	333	334	37
85°	12	29	75	83	84	13
90°	6	16	44	22	22	6
95°	56	218	724	374	254	62
105°	199	302	1222	1856	1731	211
115°	354	430	979	1953	2229	349
125°	492	552	891	1505	1775	437
135°	587	646	863	1215	1378	454
145°	680	724	852	1037	1118	426
155°	769	790	852	935	962	353
165°	830	841	852	885	896	234
175°	863	863	858	869	869	82
180°	863	863	863	863	863	

TEST NUMBER: P937108

CATALOG NUMBER: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6
2.5°	389.6	389.6	392.1	393.4	395.8	397.1	399.7	402.2	409.7	410.9	413.4
5°	379.6	384.6	400.9	407.1	424.7	448.5	458.5	474.8	508.7	518.7	524.9
7.5°	364.5	375.8	415.9	425.9	469.8	532.4	558.7	593.8	647.6	674.0	695.3
10°	340.7	364.5	436.0	459.8	531.2	626.3	675.3	724.1	805.5	841.8	855.6
12.5°	314.5	353.2	457.3	489.8	592.5	731.6	790.5	844.3	937.1	985.9	993.4
15°	284.4	337.0	477.3	524.9	657.7	819.3	884.5	950.8	1037.3	1072.3	1081.1
17.5°	258.1	324.5	496.1	546.2	707.8	898.2	964.6	1019.7	1089.9	1113.7	1120.0
20°	225.5	304.4	508.7	573.8	760.5	955.9	1019.7	1062.3	1110.0	1125.0	1127.5
22.5°	201.7	283.1	516.1	583.8	795.5	991.0	1044.8	1078.7	1111.2	1116.2	1117.4
25°	181.7	259.3	514.9	595.1	825.6	1012.3	1053.6	1078.7	1097.4	1100.0	1100.0
27.5°	162.9	233.0	509.9	597.6	848.2	1017.2	1049.8	1067.4	1076.2	1081.1	1081.1
30°	146.5	208.0	497.4	592.5	858.2	1012.3	1038.5	1047.3	1056.1	1063.6	1067.4
32.5°	134.0	184.2	478.6	582.5	859.4	999.7	1018.5	1023.5	1036.0	1053.6	1059.8
35°	122.7	160.4	457.3	568.7	851.9	979.7	992.2	997.2	1022.3	1048.6	1057.3
37.5°	111.5	142.8	429.7	545.0	840.6	955.9	964.6	973.4	1012.3	1043.6	1053.6
40°	100.2	127.8	397.1	518.7	823.0	927.1	934.6	948.4	999.7	1036.0	1046.1
42.5°	91.4	115.3	362.0	491.1	800.5	894.5	905.8	925.8	984.7	1023.5	1034.8
45°	84.0	102.7	324.5	453.5	771.7	860.7	876.9	904.5	967.2	1004.7	1014.7
47.5°	76.4	94.0	285.6	414.7	740.4	826.9	848.2	879.5	943.3	979.7	988.5
50°	70.1	85.2	246.8	373.3	706.6	790.5	815.6	848.2	913.3	947.1	958.4
52.5°	65.1	77.7	210.4	331.9	667.7	752.9	781.8	815.6	876.9	909.5	917.0
55°	60.1	71.5	179.1	288.1	627.6	712.8	744.1	776.7	836.9	864.4	869.5
57.5°	57.6	66.4	152.8	246.8	585.1	667.7	702.8	732.9	789.2	810.5	815.6
60°	53.9	62.7	132.8	211.7	538.7	625.1	655.2	685.3	732.9	750.4	754.2
62.5°	50.2	60.1	117.8	177.9	491.1	575.1	605.0	632.7	672.8	685.3	690.3
65°	47.6	57.6	106.5	152.8	442.2	522.4	552.5	576.3	608.9	621.4	623.9
67.5°	45.1	55.1	97.7	131.5	393.4	469.8	492.3	514.9	539.9	552.5	553.7
70°	41.4	52.6	90.2	116.5	343.2	409.7	428.4	452.2	472.3	478.6	482.3
72.5°	38.9	48.8	85.2	105.3	291.9	352.0	369.6	383.3	400.9	407.1	407.1
75°	35.1	43.8	80.1	94.0	239.3	288.1	303.2	316.9	330.7	333.3	329.5
77.5°	31.3	38.9	68.9	78.9	186.7	228.0	240.5	248.1	259.3	261.8	263.1
80°	26.3	33.8	53.9	61.4	135.3	167.8	176.6	182.9	193.0	193.0	195.4
82.5°	20.1	26.3	38.9	43.8	91.4	115.3	122.7	126.6	132.8	132.8	132.8
85°	12.5	16.3	25.0	28.8	55.1	70.1	75.2	76.4	81.4	82.7	82.7
87.5°	6.3	8.8	16.3	17.6	28.8	36.3	36.3	38.9	38.9	37.5	36.3
90°	5.8	10.5	15.1	16.3	25.5	37.8	44.0	39.1	29.3	22.0	22.0
92.5°	23.2	62.6	102.0	111.8	157.2	217.6	247.9	217.2	156.0	110.0	105.6
95°	55.6	127.7	199.7	217.7	386.6	611.8	724.4	646.4	490.4	373.5	360.2
97.5°	96.1	159.7	223.3	239.2	520.8	896.3	1084.0	1034.7	936.1	862.3	837.1
100°	127.4	185.0	242.7	257.1	569.6	986.3	1194.6	1198.2	1205.4	1210.8	1180.8
102.5°	154.0	207.8	261.6	275.1	592.0	1014.6	1225.9	1288.6	1414.3	1508.5	1482.7
105°	199.2	244.8	290.3	301.7	608.6	1017.8	1222.4	1363.2	1644.7	1855.9	1842.0
107.5°	245.5	288.0	330.4	341.1	611.7	972.5	1152.9	1349.3	1742.0	2036.6	2039.9
110°	276.8	315.1	353.4	363.0	607.0	932.3	1095.0	1314.5	1753.6	2082.9	2097.3

TEST NUMBER: P937108

CATALOG NUMBER: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	307.5	344.0	380.5	389.7	607.2	897.3	1042.3	1267.1	1716.4	2053.4	2075.5
115°	353.8	387.5	421.2	429.6	612.8	857.0	979.2	1195.6	1628.5	1953.2	1983.9
117.5°	399.6	430.2	460.8	468.5	624.3	831.9	935.8	1131.1	1521.8	1814.8	1848.8
120°	426.2	455.0	483.8	491.0	633.4	823.4	918.4	1096.9	1453.9	1721.5	1754.6
122.5°	452.2	481.4	510.4	517.7	646.8	818.9	905.0	1065.8	1387.3	1628.3	1660.9
125°	492.2	518.7	545.2	551.8	664.7	815.3	890.6	1027.1	1300.1	1505.0	1535.0
127.5°	524.6	551.4	578.1	584.9	682.8	813.2	878.4	995.6	1230.1	1406.0	1431.3
130°	542.0	570.8	599.6	606.8	695.8	814.5	873.9	978.2	1186.9	1343.5	1366.9
132.5°	559.9	588.8	617.7	624.8	706.5	815.3	869.7	963.1	1150.0	1290.1	1311.1
135°	586.6	612.8	639.1	645.7	718.1	814.5	862.8	941.1	1097.5	1214.9	1233.0
137.5°	613.8	639.8	665.8	672.3	735.4	819.6	861.6	927.7	1060.1	1159.3	1174.0
140°	636.4	660.3	684.2	690.2	746.0	820.4	857.6	914.8	1029.0	1114.7	1128.6
142.5°	653.8	675.9	698.1	703.6	755.0	823.4	857.6	907.8	1008.2	1083.4	1095.3
145°	680.4	699.8	719.0	723.8	766.5	823.4	851.8	892.9	975.0	1036.6	1045.5
147.5°	707.0	725.8	744.7	749.3	783.5	829.0	851.8	884.1	948.7	997.1	1004.6
150°	724.4	741.4	758.4	762.6	792.3	832.0	851.8	879.1	933.6	974.5	980.6
152.5°	742.3	755.2	768.1	771.3	798.1	833.9	851.8	875.1	921.7	956.6	961.2
155°	769.0	778.5	788.0	790.4	810.9	838.2	851.8	870.3	907.4	935.2	938.2
157.5°	788.7	797.9	807.2	809.5	823.6	842.4	851.8	866.2	895.1	916.6	918.8
160°	802.0	809.2	816.4	818.2	829.4	844.3	851.8	864.1	888.9	907.4	908.6
162.5°	815.3	820.7	826.1	827.5	835.6	846.4	851.8	862.3	883.1	898.7	899.8
165°	829.8	834.6	839.6	840.8	844.4	849.4	851.8	859.3	874.2	885.4	886.6
167.5°	843.1	845.5	847.8	848.4	851.4	855.5	857.6	862.5	872.3	879.6	880.1
170°	851.8	854.1	856.5	857.0	857.2	857.5	857.6	862.5	872.3	879.6	879.6
172.5°	856.5	856.9	857.5	857.6	857.6	857.6	857.6	861.4	869.2	875.0	874.5
175°	862.8	862.8	862.8	862.8	861.1	858.7	857.6	860.0	865.0	868.6	868.6
177.5°	862.8	862.8	862.8	862.8	861.4	859.7	858.7	860.7	864.5	867.4	866.9
180°	862.8	862.8	862.8	862.8	862.8	862.8	862.8	862.8	862.8	862.8	862.8

TEST NUMBER: P937108

CATALOG NUMBER: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	389.6	389.6
2.5°	415.9	413.4
5°	534.9	537.4
7.5°	720.3	719.1
10°	895.7	907.0
12.5°	1023.5	1026.0
15°	1101.2	1106.2
17.5°	1131.3	1132.5
20°	1132.5	1130.0
22.5°	1118.7	1116.2
25°	1102.4	1101.2
27.5°	1087.4	1088.7
30°	1081.1	1084.9
32.5°	1081.1	1087.4
35°	1083.6	1089.9
37.5°	1082.4	1089.9
40°	1077.4	1086.1
42.5°	1063.6	1069.9
45°	1042.3	1049.8
47.5°	1014.7	1019.7
50°	979.7	984.7
52.5°	935.8	937.1
55°	883.2	888.2
57.5°	826.9	828.1
60°	764.2	767.9
62.5°	697.8	697.8
65°	627.6	630.2
67.5°	555.0	561.2
70°	481.1	482.3
72.5°	408.4	408.4
75°	333.3	334.5
77.5°	261.8	261.8
80°	194.2	195.4
82.5°	134.0	136.6
85°	84.0	84.0
87.5°	38.9	35.1
90°	22.0	22.0
92.5°	88.2	70.6
95°	307.3	254.2
97.5°	736.1	635.2
100°	1060.7	940.4
102.5°	1379.8	1276.9
105°	1786.6	1731.4
107.5°	2053.3	2066.7
110°	2155.0	2212.6

TEST NUMBER: P937108

CATALOG NUMBER: SQ4-FB-075U-050D-B50-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2164.0	2252.5
115°	2106.6	2229.4
117.5°	1984.9	2121.1
120°	1887.0	2019.2
122.5°	1791.4	1921.9
125°	1655.2	1775.4
127.5°	1532.7	1634.1
130°	1460.5	1554.2
132.5°	1395.0	1478.9
135°	1305.3	1377.6
137.5°	1233.3	1292.5
140°	1183.9	1239.2
142.5°	1142.9	1190.6
145°	1081.6	1117.6
147.5°	1034.4	1064.3
150°	1004.8	1029.0
152.5°	979.4	997.7
155°	950.3	962.4
157.5°	927.3	935.8
160°	913.5	918.4
162.5°	904.5	909.2
165°	891.5	896.4
167.5°	882.2	884.2
170°	879.6	879.6
172.5°	872.7	871.0
175°	868.6	868.6
177.5°	864.9	862.8
180°	862.8	862.8

(END OF REPORT)