

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937104

Luminaire Tested: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937104
REPORT IS A COMBINATION OF REPORTS P933517 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8804.2 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 68.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937104

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P937104

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	94	90	86	82	85	81	78	75	65	63	61	50	49	47	37	36	35
2	85	78	72	66	77	70	65	61	57	53	50	44	41	39	32	30	29
3	77	68	61	55	70	62	55	50	49	45	41	38	35	32	28	26	24
4	71	60	52	46	63	54	47	42	44	39	35	34	30	27	25	22	20
5	65	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17
6	59	47	39	33	53	43	36	31	35	29	25	27	23	20	20	17	15
7	55	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	14	12
9	47	35	27	22	42	32	25	20	26	21	17	20	16	14	15	12	10
10	44	32	24	20	39	29	22	18	23	18	15	18	15	12	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1848	1848	1848
5°	1806	2136	2484
10°	1638	3114	4119
15°	1392	4069	4973
20°	1133	4715	5069
25°	945	4933	4965
30°	797	4965	4956
35°	705	4882	5084
40°	614	4775	5217
45°	557	4696	5237
50°	510	4626	5151
55°	489	4522	4922
60°	500	4324	4562
65°	521	4022	4066
70°	555	3508	3436
75°	615	2860	2681
80°	671	1983	1806
85°	596	1053	925

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 5237 cd/sqm

TEST NUMBER: P937104

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	0.6
10°-20°	228.4	2.6
20°-30°	399.5	4.5
30°-40°	514.2	5.8
40°-50°	574.4	6.5
50°-60°	550.2	6.2
60°-70°	436.0	5.0
70°-80°	256.4	2.9
80°-90°	74.6	0.8
90°-100°	430.0	4.9
100°-110°	1130.6	12.8
110°-120°	1172.3	13.3
120°-130°	940.3	10.7
130°-140°	737.8	8.4
140°-150°	566.3	6.4
150°-160°	407.8	4.6
160°-170°	249.5	2.8
170°-180°	84.3	1.0
0°-30°	679.4	7.7
0°-40°	1193.6	13.6
0°-60°	2318.2	26.3
0°-90°	3085.2	35.0
90°-120°	2732.9	31.0
90°-150°	4977.3	56.5
90°-180°	5719.0	65.0
0°-180°	8804.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	398	398	398	398	398	
5°	388	416	469	530	550	36
15°	291	537	904	1096	1131	81
25°	186	608	1077	1125	1126	86
35°	126	582	1014	1072	1114	78
45°	86	464	897	1027	1073	66
55°	62	295	761	884	908	56
65°	49	156	565	635	644	48
75°	36	96	310	341	342	38
85°	13	29	77	84	86	14
90°	6	17	45	22	22	6
95°	57	223	741	382	260	63
105°	204	308	1250	1898	1770	216
115°	362	439	1001	1997	2280	357
125°	503	564	911	1539	1815	447
135°	600	660	882	1242	1408	464
145°	696	740	871	1060	1143	436
155°	786	808	871	956	984	361
165°	848	860	871	905	916	239
175°	882	882	877	888	888	84
180°	882	882	882	882	882	

TEST NUMBER: P937104

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	398.3	398.3	398.3	398.3	398.3	398.3	398.3	398.3	398.3	398.3	398.3
2.5°	398.3	398.3	400.9	402.2	404.7	406.1	408.6	411.2	418.9	420.1	422.7
5°	388.1	393.3	409.9	416.3	434.2	458.6	468.8	485.4	520.1	530.3	536.7
7.5°	372.7	384.3	425.3	435.5	480.4	544.4	571.3	607.2	662.2	689.1	710.9
10°	348.4	372.7	445.8	470.1	543.1	640.4	690.5	740.4	823.6	860.7	874.9
12.5°	321.5	361.2	467.6	500.8	605.9	748.1	808.3	863.3	958.2	1008.1	1015.7
15°	290.8	344.6	488.0	536.7	672.5	837.7	904.4	972.2	1060.6	1096.4	1105.4
17.5°	263.9	331.8	507.3	558.5	723.7	918.4	986.3	1042.7	1114.4	1138.7	1145.1
20°	230.5	311.2	520.1	586.7	777.6	977.3	1042.7	1086.2	1134.9	1150.3	1152.9
22.5°	206.2	289.5	527.7	596.9	813.4	1013.3	1068.3	1102.9	1136.2	1141.3	1142.6
25°	185.7	265.1	526.5	608.4	844.1	1035.0	1077.2	1102.9	1122.1	1124.7	1124.7
27.5°	166.6	238.3	521.3	611.0	867.2	1040.1	1073.4	1091.4	1100.4	1105.4	1105.4
30°	149.8	212.7	508.5	605.9	877.5	1035.0	1061.9	1070.8	1079.8	1087.6	1091.4
32.5°	137.0	188.3	489.3	595.6	878.7	1022.1	1041.4	1046.5	1059.3	1077.2	1083.6
35°	125.5	164.0	467.6	581.5	871.1	1001.7	1014.5	1019.7	1045.2	1072.2	1081.1
37.5°	114.0	146.0	439.4	557.2	859.5	977.3	986.3	995.3	1035.0	1067.0	1077.2
40°	102.5	130.6	406.1	530.3	841.5	947.9	955.6	969.7	1022.1	1059.3	1069.6
42.5°	93.5	117.8	370.2	502.1	818.5	914.6	926.2	946.6	1006.9	1046.5	1058.0
45°	85.9	105.0	331.8	463.7	789.0	880.0	896.6	924.8	988.9	1027.3	1037.5
47.5°	78.1	96.1	292.0	424.0	757.0	845.5	867.2	899.2	964.6	1001.7	1010.7
50°	71.7	87.1	252.3	381.7	722.5	808.3	833.9	867.2	933.8	968.4	979.9
52.5°	66.6	79.5	215.2	339.4	682.7	769.8	799.3	833.9	896.6	930.0	937.6
55°	61.5	73.1	183.2	294.6	641.8	728.9	760.8	794.2	855.7	883.9	889.0
57.5°	58.9	67.9	156.2	252.3	598.2	682.7	718.6	749.4	807.0	828.7	833.9
60°	55.1	64.1	135.8	216.5	550.8	639.2	669.9	700.7	749.4	767.2	771.2
62.5°	51.3	61.5	120.4	181.9	502.1	588.0	618.6	646.9	687.9	700.7	705.8
65°	48.7	58.9	108.9	156.2	452.2	534.1	564.9	589.2	622.6	635.4	637.9
67.5°	46.1	56.3	99.9	134.5	402.2	480.4	503.4	526.5	552.1	564.9	566.1
70°	42.3	53.8	92.3	119.1	351.0	418.9	438.1	462.4	482.9	489.3	493.2
72.5°	39.7	49.9	87.1	107.6	298.4	359.9	377.9	391.9	409.9	416.3	416.3
75°	35.9	44.8	81.9	96.1	244.7	294.6	310.0	324.0	338.2	340.7	336.9
77.5°	32.0	39.7	70.5	80.7	190.9	233.1	245.9	253.6	265.1	267.7	269.0
80°	26.9	34.6	55.1	62.7	138.4	171.6	180.6	187.0	197.3	197.3	199.8
82.5°	20.5	26.9	39.7	44.8	93.5	117.8	125.5	129.4	135.8	135.8	135.8
85°	12.8	16.6	25.6	29.4	56.3	71.7	76.9	78.1	83.3	84.5	84.5
87.5°	6.4	9.0	16.6	18.0	29.4	37.1	37.1	39.7	39.7	38.4	37.1
90°	5.9	10.7	15.5	16.6	26.1	38.7	45.0	40.0	30.0	22.5	22.5
92.5°	23.7	64.0	104.3	114.3	160.7	222.5	253.5	222.1	159.5	112.5	108.0
95°	56.8	130.5	204.2	222.6	395.3	625.5	740.7	661.0	501.5	381.9	368.3
97.5°	98.3	163.3	228.3	244.6	532.5	916.4	1108.4	1057.9	957.2	881.7	855.9
100°	130.3	189.2	248.2	262.9	582.5	1008.5	1221.4	1225.2	1232.5	1238.1	1207.3
102.5°	157.5	212.5	267.5	281.2	605.3	1037.4	1253.4	1317.6	1446.1	1542.4	1516.1
105°	203.7	250.3	296.8	308.5	622.3	1040.7	1249.9	1393.8	1681.7	1897.6	1883.5
107.5°	251.1	294.5	337.9	348.8	625.4	994.3	1178.9	1379.6	1781.2	2082.4	2085.8
110°	283.1	322.2	361.4	371.2	620.7	953.3	1119.6	1344.1	1793.0	2129.7	2144.5

TEST NUMBER: P937104

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	314.4	351.7	389.1	398.4	620.8	917.5	1065.8	1295.6	1755.0	2099.6	2122.2
115°	361.8	396.2	430.7	439.3	626.6	876.3	1001.2	1222.5	1665.1	1997.1	2028.5
117.5°	408.5	439.9	471.2	479.0	638.3	850.6	956.8	1156.5	1556.0	1855.6	1890.3
120°	435.8	465.2	494.7	502.0	647.7	841.9	939.1	1121.6	1486.6	1760.3	1794.1
122.5°	462.4	492.2	521.9	529.4	661.3	837.3	925.4	1089.8	1418.5	1664.9	1698.3
125°	503.3	530.4	557.4	564.2	679.7	833.6	910.6	1050.2	1329.4	1538.8	1569.5
127.5°	536.4	563.8	591.1	598.0	698.1	831.5	898.2	1018.0	1257.7	1437.6	1463.4
130°	554.2	583.6	613.1	620.5	711.5	832.9	893.5	1000.2	1213.6	1373.7	1397.6
132.5°	572.5	602.0	631.5	638.9	722.4	833.6	889.3	984.8	1175.9	1319.1	1340.6
135°	599.7	626.6	653.5	660.2	734.2	832.9	882.2	962.3	1122.2	1242.2	1260.7
137.5°	627.6	654.2	680.7	687.4	752.0	838.0	881.0	948.6	1083.9	1185.3	1200.4
140°	650.7	675.2	699.6	705.7	762.8	838.9	876.9	935.3	1052.1	1139.8	1153.9
142.5°	668.5	691.1	713.8	719.4	771.9	841.9	876.9	928.2	1030.8	1107.8	1119.9
145°	695.7	715.5	735.2	740.1	783.8	841.9	871.0	913.0	996.9	1059.9	1069.0
147.5°	722.9	742.1	761.4	766.2	801.1	847.7	871.0	904.0	970.0	1019.6	1027.2
150°	740.7	758.1	775.5	779.8	810.1	850.7	871.0	898.8	954.6	996.4	1002.7
152.5°	759.0	772.2	785.4	788.6	816.0	852.6	871.0	894.7	942.4	978.1	982.8
155°	786.3	796.0	805.7	808.2	829.1	857.0	871.0	889.9	927.8	956.2	959.3
157.5°	806.4	815.9	825.3	827.7	842.1	861.3	871.0	885.7	915.2	937.2	939.4
160°	820.1	827.4	834.8	836.6	848.0	863.3	871.0	883.6	908.9	927.8	929.0
162.5°	833.6	839.2	844.7	846.1	854.4	865.4	871.0	881.7	903.0	918.9	920.0
165°	848.4	853.4	858.4	859.7	863.4	868.5	871.0	878.6	893.9	905.3	906.6
167.5°	862.1	864.5	866.9	867.4	870.6	874.8	876.9	881.8	891.9	899.4	899.9
170°	871.0	873.3	875.7	876.3	876.5	876.8	876.9	881.8	891.9	899.4	899.4
172.5°	875.7	876.2	876.8	876.9	876.9	876.9	876.9	880.8	888.7	894.6	894.2
175°	882.2	882.2	882.2	882.2	880.4	878.0	876.9	879.4	884.4	888.2	888.2
177.5°	882.2	882.2	882.2	882.2	880.8	879.0	878.0	880.0	883.9	886.9	886.4
180°	882.2	882.2	882.2	882.2	882.2	882.2	882.2	882.2	882.2	882.2	882.2

TEST NUMBER: P937104

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	398.3	398.3
2.5°	425.3	422.7
5°	546.9	549.5
7.5°	736.5	735.3
10°	915.8	927.4
12.5°	1046.5	1049.1
15°	1125.9	1131.1
17.5°	1156.7	1157.9
20°	1157.9	1155.4
22.5°	1143.9	1141.3
25°	1127.2	1125.9
27.5°	1111.8	1113.1
30°	1105.4	1109.3
32.5°	1105.4	1111.8
35°	1108.0	1114.4
37.5°	1106.7	1114.4
40°	1101.6	1110.6
42.5°	1087.6	1094.0
45°	1065.8	1073.4
47.5°	1037.5	1042.7
50°	1001.7	1006.9
52.5°	956.8	958.2
55°	903.0	908.2
57.5°	845.5	846.7
60°	781.4	785.2
62.5°	713.5	713.5
65°	641.8	644.3
67.5°	567.5	573.9
70°	491.9	493.2
72.5°	417.6	417.6
75°	340.7	342.0
77.5°	267.7	267.7
80°	198.5	199.8
82.5°	137.0	139.6
85°	85.9	85.9
87.5°	39.7	35.9
90°	22.5	22.5
92.5°	90.2	72.2
95°	314.2	260.0
97.5°	752.6	649.5
100°	1084.5	961.6
102.5°	1410.8	1305.6
105°	1826.8	1770.3
107.5°	2099.5	2113.1
110°	2203.5	2262.4

TEST NUMBER: P937104

CATALOG NUMBER: SQ4-FB-075U-050D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2212.6	2303.2
115°	2154.0	2279.5
117.5°	2029.6	2168.8
120°	1929.4	2064.6
122.5°	1831.7	1965.1
125°	1692.5	1815.4
127.5°	1567.2	1670.9
130°	1493.3	1589.1
132.5°	1426.4	1512.1
135°	1334.6	1408.5
137.5°	1261.0	1321.5
140°	1210.6	1267.1
142.5°	1168.6	1217.3
145°	1105.9	1142.8
147.5°	1057.7	1088.2
150°	1027.4	1052.1
152.5°	1001.4	1020.1
155°	971.7	984.0
157.5°	948.1	956.8
160°	934.1	939.1
162.5°	924.8	929.6
165°	911.5	916.5
167.5°	902.0	904.1
170°	899.4	899.4
172.5°	892.4	890.5
175°	888.2	888.2
177.5°	884.3	882.2
180°	882.2	882.2

(END OF REPORT)