

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937405

Luminaire Tested: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937405
REPORT IS A COMBINATION OF REPORTS P933496 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19802.7 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 186
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63
1	99	94	90	86	92	88	84	81	76	73	71	65	63	61	55	53	52
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43
3	81	71	63	57	75	66	59	54	57	52	47	49	45	41	41	38	36
4	74	62	54	48	68	58	51	45	50	45	40	43	39	35	36	33	30
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	33	29	26
6	62	49	41	35	57	46	38	33	40	34	29	34	29	26	29	25	22
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17
9	49	36	28	23	46	34	27	22	30	24	20	26	21	17	22	18	15
10	46	33	26	21	43	31	24	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4561	4561	4561
5°	4458	5273	6131
10°	4045	7688	10164
15°	3439	10047	12273
20°	2801	11646	12508
25°	2337	12190	12254
30°	1972	12270	12231
35°	1745	12069	12547
40°	1521	11808	12874
45°	1378	11618	12924
50°	1265	11447	12710
55°	1213	11196	12147
60°	1243	10709	11257
65°	1296	9966	10035
70°	1383	8698	8477
75°	1538	7098	6616
80°	1694	4929	4458
85°	1536	2620	2282

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 12924 cd/sqm

TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	1.0
10°-20°	845.4	4.3
20°-30°	1478.8	7.5
30°-40°	1903.6	9.6
40°-50°	2126.3	10.7
50°-60°	2036.5	10.3
60°-70°	1613.9	8.1
70°-80°	949.0	4.8
80°-90°	268.6	1.4
90°-100°	630.9	3.2
100°-110°	1658.6	8.4
110°-120°	1719.8	8.7
120°-130°	1379.5	7.0
130°-140°	1082.4	5.5
140°-150°	830.8	4.2
150°-160°	598.3	3.0
160°-170°	366.1	1.8
170°-180°	123.7	0.6
0°-30°	2514.9	12.7
0°-40°	4418.6	22.3
0°-60°	8581.3	43.3
0°-90°	11412.8	57.6
90°-120°	4009.2	20.2
90°-150°	7301.8	36.9
90°-180°	8390.0	42.4
0°-180°	19802.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1475	1475	1475	1475	1475	
5°	1437	1541	1736	1963	2034	133
15°	1076	1987	3348	4059	4187	300
25°	688	2252	3988	4163	4168	317
35°	465	2153	3755	3969	4125	290
45°	318	1716	3319	3803	3974	246
55°	228	1090	2817	3272	3362	207
65°	180	578	2091	2352	2385	179
75°	133	356	1148	1261	1266	139
85°	47	109	284	313	318	50
90°	9	24	66	33	33	10
95°	83	327	1087	560	381	93
105°	299	452	1834	2784	2597	317
115°	531	644	1469	2930	3344	524
125°	738	828	1336	2258	2663	656
135°	880	968	1294	1822	2066	681
145°	1021	1086	1278	1555	1676	639
155°	1154	1186	1278	1403	1444	530
165°	1245	1261	1278	1328	1345	351
175°	1294	1294	1286	1303	1303	123
180°	1294	1294	1294	1294	1294	

TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7
2.5°	1474.7	1474.7	1484.1	1488.9	1498.3	1503.1	1512.6	1522.0	1550.5	1555.3	1564.7
5°	1436.7	1455.6	1517.3	1541.0	1607.4	1697.5	1735.5	1797.1	1925.1	1963.1	1986.7
7.5°	1379.8	1422.5	1574.3	1612.2	1778.1	2015.2	2114.8	2247.6	2451.5	2551.0	2631.6
10°	1289.8	1379.8	1650.1	1740.1	2010.4	2370.8	2555.7	2740.6	3048.9	3186.3	3238.6
12.5°	1190.2	1337.1	1730.7	1854.0	2242.8	2769.1	2992.0	3195.9	3546.8	3731.7	3760.1
15°	1076.3	1275.5	1806.5	1986.7	2489.4	3101.1	3347.5	3598.9	3926.1	4058.9	4092.0
17.5°	976.8	1228.1	1877.7	2067.3	2679.0	3399.8	3651.1	3859.7	4125.2	4215.3	4239.1
20°	853.5	1152.2	1925.1	2171.6	2878.2	3617.8	3859.7	4020.9	4201.1	4258.0	4267.4
22.5°	763.4	1071.6	1953.6	2209.6	3010.9	3750.7	3954.6	4082.5	4205.8	4224.8	4229.5
25°	687.5	981.5	1948.8	2252.2	3124.7	3831.3	3987.7	4082.5	4153.7	4163.1	4163.1
27.5°	616.4	882.0	1929.8	2261.8	3210.1	3850.2	3973.5	4039.8	4073.1	4092.0	4092.0
30°	554.8	787.1	1882.4	2242.8	3248.0	3831.3	3930.8	3964.0	3997.2	4025.6	4039.8
32.5°	507.3	697.0	1811.3	2204.9	3252.7	3783.8	3855.0	3874.0	3921.3	3987.7	4011.4
35°	464.7	606.9	1730.7	2152.7	3224.4	3708.0	3755.3	3774.4	3869.2	3968.8	4001.9
37.5°	422.0	540.5	1626.4	2062.6	3181.7	3617.8	3651.1	3684.3	3831.3	3949.8	3987.7
40°	379.3	483.6	1503.1	1963.1	3115.3	3508.9	3537.2	3589.5	3783.8	3921.3	3959.2
42.5°	346.1	436.3	1370.4	1858.8	3029.9	3385.6	3428.2	3504.1	3726.9	3874.0	3916.6
45°	317.7	388.8	1228.1	1716.5	2920.8	3257.5	3319.2	3423.5	3660.5	3802.8	3840.7
47.5°	289.3	355.7	1081.1	1569.5	2802.3	3129.5	3210.1	3328.6	3570.5	3708.0	3741.1
50°	265.5	322.4	934.1	1413.0	2674.3	2992.0	3086.8	3210.1	3456.6	3584.7	3627.4
52.5°	246.6	294.0	796.6	1256.5	2527.3	2849.7	2958.8	3086.8	3319.2	3442.4	3470.8
55°	227.6	270.3	678.1	1090.5	2375.5	2698.0	2816.6	2939.9	3167.4	3271.7	3290.7
57.5°	218.1	251.3	578.5	934.1	2214.3	2527.3	2660.0	2773.9	2987.2	3067.8	3086.8
60°	203.9	237.0	502.6	801.4	2038.9	2366.1	2479.9	2593.7	2773.9	2840.2	2854.5
62.5°	189.7	227.6	445.7	673.3	1858.8	2176.4	2290.2	2394.5	2546.3	2593.7	2612.7
65°	180.2	218.1	403.0	578.5	1673.8	1977.3	2091.0	2181.2	2304.5	2351.8	2361.3
67.5°	170.7	208.7	369.9	497.9	1488.9	1778.1	1863.4	1948.8	2043.7	2091.0	2095.8
70°	156.4	199.1	341.4	440.9	1299.2	1550.5	1621.6	1711.7	1787.6	1811.3	1825.5
72.5°	147.0	184.9	322.4	398.3	1104.8	1332.4	1398.8	1451.0	1517.3	1541.0	1541.0
75°	132.7	166.0	303.5	355.7	905.6	1090.5	1147.5	1199.6	1251.7	1261.3	1247.1
77.5°	118.5	147.0	260.8	298.7	706.5	863.0	910.4	938.9	981.5	991.0	995.7
80°	99.6	128.1	203.9	232.4	512.1	635.4	668.6	692.3	730.2	730.2	739.7
82.5°	75.8	99.6	147.0	166.0	346.1	436.3	464.7	478.9	502.6	502.6	502.6
85°	47.4	61.6	94.8	109.1	208.7	265.5	284.5	289.3	308.2	313.0	313.0
87.5°	23.7	33.2	61.6	66.4	109.1	137.5	137.5	147.0	147.0	142.2	137.5
90°	8.7	15.6	22.5	24.3	38.2	56.8	66.0	58.7	44.0	33.0	33.0
92.5°	34.7	93.8	152.9	167.7	235.6	326.3	371.7	325.8	234.0	165.0	158.5
95°	83.4	191.5	299.6	326.6	579.9	917.7	1086.6	969.7	735.7	560.2	540.3
97.5°	144.2	239.6	334.9	358.7	781.2	1344.4	1626.0	1552.0	1404.2	1293.3	1255.5
100°	191.1	277.6	364.1	385.6	854.4	1479.4	1791.9	1797.3	1808.1	1816.3	1771.1
102.5°	231.1	311.8	392.4	412.5	888.0	1521.9	1838.9	1933.0	2121.4	2262.7	2224.1
105°	298.8	367.2	435.4	452.5	912.9	1526.7	1833.6	2044.8	2467.2	2783.9	2763.1
107.5°	368.3	432.0	495.7	511.6	917.6	1458.8	1729.4	2024.0	2613.1	3054.8	3059.9
110°	415.2	472.7	530.2	544.6	910.6	1398.6	1642.5	1971.9	2630.4	3124.3	3145.9



TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	461.2	516.0	570.9	584.6	910.9	1346.0	1563.5	1900.5	2574.6	3080.1	3113.2
115°	530.7	581.2	631.9	644.5	919.2	1285.7	1468.8	1793.5	2442.8	2929.8	2975.8
117.5°	599.3	645.3	691.2	702.6	936.3	1247.8	1403.6	1696.6	2282.6	2722.1	2773.2
120°	639.3	682.6	725.7	736.6	950.3	1235.1	1377.6	1645.2	2180.7	2582.3	2631.9
122.5°	678.4	722.0	765.6	776.5	970.2	1228.5	1357.6	1598.6	2080.9	2442.5	2491.4
125°	738.3	778.1	817.9	827.8	997.1	1223.0	1335.9	1540.7	1950.3	2257.5	2302.6
127.5°	787.0	827.2	867.3	877.3	1024.1	1219.8	1317.7	1493.6	1845.2	2109.0	2147.0
130°	813.0	856.3	899.4	910.3	1043.7	1221.7	1310.7	1467.2	1780.3	2015.1	2050.2
132.5°	839.9	883.2	926.3	937.2	1059.6	1223.0	1304.6	1444.7	1725.0	1935.2	1966.7
135°	879.9	919.2	958.7	968.5	1077.1	1221.9	1294.2	1411.6	1646.3	1822.3	1849.4
137.5°	920.7	959.7	998.7	1008.4	1103.1	1229.3	1292.5	1391.7	1590.1	1738.9	1761.2
140°	954.5	990.4	1026.4	1035.3	1119.0	1230.6	1286.4	1372.1	1543.5	1672.0	1692.8
142.5°	980.6	1013.9	1047.0	1055.3	1132.4	1235.0	1286.4	1361.7	1512.2	1625.2	1643.0
145°	1020.6	1049.5	1078.5	1085.8	1149.8	1235.0	1277.7	1339.3	1462.5	1554.8	1568.4
147.5°	1060.6	1088.8	1117.0	1124.0	1175.3	1243.5	1277.7	1326.2	1423.0	1495.7	1506.9
150°	1086.6	1112.1	1137.6	1144.0	1188.5	1248.0	1277.7	1318.6	1400.4	1461.8	1470.9
152.5°	1113.5	1132.8	1152.1	1156.9	1197.2	1250.9	1277.7	1312.6	1382.5	1434.9	1441.7
155°	1153.5	1167.8	1182.1	1185.6	1216.3	1257.3	1277.7	1305.5	1361.1	1402.8	1407.4
157.5°	1183.0	1196.9	1210.8	1214.3	1235.4	1263.6	1277.7	1299.3	1342.5	1374.9	1378.1
160°	1203.0	1213.8	1224.7	1227.4	1244.2	1266.5	1277.7	1296.2	1333.3	1361.1	1363.0
162.5°	1223.0	1231.1	1239.1	1241.2	1253.3	1269.6	1277.7	1293.3	1324.6	1348.0	1349.8
165°	1244.7	1252.0	1259.3	1261.2	1266.7	1274.1	1277.7	1288.9	1311.2	1328.1	1329.9
167.5°	1264.6	1268.1	1271.6	1272.5	1277.2	1283.3	1286.4	1293.7	1308.3	1319.4	1320.1
170°	1277.7	1281.2	1284.7	1285.6	1285.8	1286.2	1286.4	1293.7	1308.3	1319.4	1319.4
172.5°	1284.6	1285.4	1286.2	1286.4	1286.4	1286.4	1286.4	1292.2	1303.8	1312.5	1311.8
175°	1294.2	1294.2	1294.2	1294.2	1291.6	1288.2	1286.4	1290.0	1297.4	1302.9	1302.9
177.5°	1294.2	1294.2	1294.2	1294.2	1292.2	1289.5	1288.2	1291.1	1296.9	1301.2	1300.4
180°	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2

TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1474.7	1474.7
2.5°	1574.3	1564.7
5°	2024.7	2034.2
7.5°	2726.4	2721.7
10°	3390.2	3432.9
12.5°	3874.0	3883.4
15°	4167.9	4186.8
17.5°	4281.7	4286.4
20°	4286.4	4277.0
22.5°	4234.3	4224.8
25°	4172.6	4167.9
27.5°	4115.8	4120.5
30°	4092.0	4106.2
32.5°	4092.0	4115.8
35°	4101.5	4125.2
37.5°	4096.8	4125.2
40°	4077.8	4111.0
42.5°	4025.6	4049.4
45°	3945.0	3973.5
47.5°	3840.7	3859.7
50°	3708.0	3726.9
52.5°	3542.0	3546.8
55°	3342.9	3361.8
57.5°	3129.5	3134.2
60°	2892.4	2906.6
62.5°	2641.1	2641.1
65°	2375.5	2385.1
67.5°	2100.6	2124.3
70°	1820.8	1825.5
72.5°	1545.8	1545.8
75°	1261.3	1266.0
77.5°	991.0	991.0
80°	735.0	739.7
82.5°	507.3	516.9
85°	317.7	317.7
87.5°	147.0	132.7
90°	33.0	33.0
92.5°	132.3	106.0
95°	460.8	381.4
97.5°	1104.2	952.9
100°	1590.9	1410.6
102.5°	2069.7	1915.3
105°	2680.1	2597.1
107.5°	3080.0	3100.0
110°	3232.4	3318.9



TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3246.0	3378.8
115°	3159.9	3344.1
117.5°	2977.4	3181.7
120°	2830.4	3028.8
122.5°	2687.1	2882.9
125°	2482.9	2663.1
127.5°	2299.1	2451.2
130°	2190.8	2331.4
132.5°	2092.5	2218.4
135°	1957.9	2066.4
137.5°	1849.9	1938.7
140°	1775.8	1858.8
142.5°	1714.5	1785.8
145°	1622.4	1676.3
147.5°	1551.7	1596.5
150°	1507.2	1543.5
152.5°	1469.2	1496.5
155°	1425.5	1443.6
157.5°	1390.9	1403.6
160°	1370.3	1377.6
162.5°	1356.7	1363.7
165°	1337.2	1344.6
167.5°	1323.3	1326.4
170°	1319.4	1319.4
172.5°	1309.1	1306.4
175°	1302.9	1302.9
177.5°	1297.3	1294.2
180°	1294.2	1294.2

(END OF REPORT)