

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937404

Luminaire Tested: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937404
REPORT IS A COMBINATION OF REPORTS P933520 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13499.0 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937404

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8

Luminous Intensity Polar Plot



TEST NUMBER: P937404

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	99	94	90	86	92	88	84	81	76	73	71	65	63	61	55	53	52
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43
3	81	71	63	57	75	66	59	54	57	52	47	49	45	41	41	38	36
4	74	62	54	48	68	58	51	45	50	45	40	43	39	35	36	33	30
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	33	29	26
6	62	49	41	35	57	46	38	33	40	34	29	34	29	26	29	25	22
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17
9	49	36	28	23	46	34	27	22	30	24	20	26	21	18	22	18	15
10	46	33	26	21	43	31	24	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4556	5391	6269
10°	4133	7858	10393
15°	3512	10266	12550
20°	2860	11897	12790
25°	2385	12449	12530
30°	2012	12528	12506
35°	1779	12320	12830
40°	1550	12050	13164
45°	1404	11851	13216
50°	1287	11673	12997
55°	1233	11413	12421
60°	1262	10911	11511
65°	1313	10149	10261
70°	1399	8851	8669
75°	1550	7217	6765
80°	1694	5004	4558
85°	1504	2656	2333

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 13216 cd/sqm

TEST NUMBER: P937404

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.0	1.0
10°-20°	576.3	4.3
20°-30°	1008.1	7.5
30°-40°	1297.7	9.6
40°-50°	1449.4	10.7
50°-60°	1388.2	10.3
60°-70°	1100.2	8.2
70°-80°	646.9	4.8
80°-90°	183.1	1.4
90°-100°	430.0	3.2
100°-110°	1130.6	8.4
110°-120°	1172.3	8.7
120°-130°	940.3	7.0
130°-140°	737.8	5.5
140°-150°	566.3	4.2
150°-160°	407.8	3.0
160°-170°	249.5	1.8
170°-180°	84.3	0.6
0°-30°	1714.4	12.7
0°-40°	3012.1	22.3
0°-60°	5849.7	43.3
0°-90°	7780.0	57.6
90°-120°	2732.9	20.2
90°-150°	4977.3	36.9
90°-180°	5719.0	42.4
0°-180°	13499.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1005	1005	1005	1005	1005	
5°	979	1050	1183	1338	1387	90
15°	734	1354	2282	2767	2854	204
25°	469	1535	2718	2838	2841	216
35°	317	1468	2560	2705	2812	198
45°	217	1170	2263	2592	2709	168
55°	155	744	1920	2230	2292	141
65°	123	394	1425	1603	1626	122
75°	90	242	782	860	863	95
85°	32	74	194	213	217	34
90°	6	17	45	22	22	7
95°	57	223	741	382	260	63
105°	204	308	1250	1898	1770	216
115°	362	439	1001	1997	2280	357
125°	503	564	911	1539	1815	447
135°	600	660	882	1242	1408	464
145°	696	740	871	1060	1143	436
155°	786	808	871	956	984	361
165°	848	860	871	905	916	239
175°	882	882	877	888	888	84
180°	882	882	882	882	882	

TEST NUMBER: P937404

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2	1005.2
2.5°	1005.2	1005.2	1011.7	1015.0	1021.4	1024.6	1031.1	1037.6	1057.0	1060.2	1066.6
5°	979.4	992.3	1034.4	1050.5	1095.8	1157.2	1183.1	1225.1	1312.3	1338.1	1354.3
7.5°	940.6	969.7	1073.1	1099.0	1212.1	1373.8	1441.6	1532.1	1671.1	1739.0	1794.0
10°	879.2	940.6	1124.8	1186.2	1370.5	1616.1	1742.2	1868.3	2078.4	2172.1	2207.7
12.5°	811.3	911.5	1179.8	1263.8	1528.9	1887.7	2039.6	2178.5	2417.8	2543.8	2563.2
15°	733.7	869.5	1231.5	1354.3	1696.9	2113.9	2282.0	2453.3	2676.4	2766.8	2789.5
17.5°	665.8	837.2	1280.0	1409.3	1826.2	2317.6	2488.8	2631.1	2812.1	2873.5	2889.6
20°	581.8	785.5	1312.3	1480.3	1962.0	2466.3	2631.1	2740.9	2863.9	2902.6	2909.0
22.5°	520.4	730.5	1331.7	1506.2	2052.5	2556.7	2695.8	2783.0	2867.0	2880.0	2883.2
25°	468.7	669.1	1328.5	1535.4	2130.1	2611.7	2718.4	2783.0	2831.5	2838.0	2838.0
27.5°	420.2	601.2	1315.5	1541.8	2188.3	2624.6	2708.7	2753.9	2776.6	2789.5	2789.5
30°	378.2	536.5	1283.2	1528.9	2214.2	2611.7	2679.5	2702.2	2724.8	2744.2	2753.9
32.5°	345.9	475.1	1234.7	1503.0	2217.3	2579.4	2627.9	2640.8	2673.1	2718.4	2734.5
35°	316.8	413.7	1179.8	1467.5	2197.9	2527.7	2560.0	2572.9	2637.5	2705.4	2728.1
37.5°	287.6	368.4	1108.7	1406.0	2168.9	2466.3	2488.8	2511.5	2611.7	2692.5	2718.4
40°	258.6	329.7	1024.6	1338.1	2123.6	2391.9	2411.3	2446.8	2579.4	2673.1	2698.9
42.5°	236.0	297.4	934.2	1267.1	2065.5	2307.9	2337.0	2388.6	2540.6	2640.8	2669.9
45°	216.6	265.0	837.2	1170.1	1991.1	2220.6	2262.6	2333.7	2495.3	2592.3	2618.1
47.5°	197.2	242.4	737.0	1069.9	1910.3	2133.3	2188.3	2269.1	2433.9	2527.7	2550.3
50°	181.0	219.8	636.8	963.2	1823.0	2039.6	2104.2	2188.3	2356.4	2443.7	2472.7
52.5°	168.1	200.4	543.0	856.5	1722.8	1942.6	2017.0	2104.2	2262.6	2346.6	2366.0
55°	155.2	184.2	462.2	743.5	1619.4	1839.1	1920.0	2004.1	2159.2	2230.3	2243.2
57.5°	148.7	171.3	394.3	636.8	1509.5	1722.8	1813.4	1890.9	2036.3	2091.3	2104.2
60°	139.0	161.6	342.7	546.3	1389.9	1612.9	1690.4	1768.1	1890.9	1936.2	1945.8
62.5°	129.3	155.2	303.9	459.0	1267.1	1483.6	1561.2	1632.3	1735.7	1768.1	1781.0
65°	122.8	148.7	274.8	394.3	1141.0	1347.9	1425.4	1486.8	1570.9	1603.3	1609.7
67.5°	116.3	142.2	252.1	339.4	1015.0	1212.1	1270.2	1328.5	1393.2	1425.4	1428.7
70°	106.7	135.8	232.7	300.6	885.7	1057.0	1105.4	1166.8	1218.6	1234.7	1244.5
72.5°	100.2	126.1	219.8	271.5	753.1	908.3	953.6	989.1	1034.4	1050.5	1050.5
75°	90.5	113.2	206.9	242.4	617.4	743.5	782.2	817.8	853.3	859.8	850.1
77.5°	80.8	100.2	177.8	203.6	481.6	588.3	620.6	640.0	669.1	675.6	678.8
80°	67.9	87.3	139.0	158.3	349.1	433.1	455.7	472.0	497.7	497.7	504.2
82.5°	51.8	67.9	100.2	113.2	236.0	297.4	316.8	326.4	342.7	342.7	342.7
85°	32.3	42.0	64.7	74.3	142.2	181.0	194.0	197.2	210.1	213.3	213.3
87.5°	16.1	22.6	42.0	45.3	74.3	93.8	93.8	100.2	100.2	96.9	93.8
90°	5.9	10.7	15.5	16.6	26.1	38.7	45.0	40.0	30.0	22.5	22.5
92.5°	23.7	64.0	104.3	114.3	160.7	222.5	253.5	222.1	159.5	112.5	108.0
95°	56.8	130.5	204.2	222.6	395.3	625.5	740.7	661.0	501.5	381.9	368.3
97.5°	98.3	163.3	228.3	244.6	532.5	916.4	1108.4	1057.9	957.2	881.7	855.9
100°	130.3	189.2	248.2	262.9	582.5	1008.5	1221.4	1225.2	1232.5	1238.1	1207.3
102.5°	157.5	212.5	267.5	281.2	605.3	1037.4	1253.4	1317.6	1446.1	1542.4	1516.1
105°	203.7	250.3	296.8	308.5	622.3	1040.7	1249.9	1393.8	1681.7	1897.6	1883.5
107.5°	251.1	294.5	337.9	348.8	625.4	994.3	1178.9	1379.6	1781.2	2082.4	2085.8
110°	283.1	322.2	361.4	371.2	620.7	953.3	1119.6	1344.1	1793.0	2129.7	2144.5

TEST NUMBER: P937404

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	314.4	351.7	389.1	398.4	620.8	917.5	1065.8	1295.6	1755.0	2099.6	2122.2
115°	361.8	396.2	430.7	439.3	626.6	876.3	1001.2	1222.5	1665.1	1997.1	2028.5
117.5°	408.5	439.9	471.2	479.0	638.3	850.6	956.8	1156.5	1556.0	1855.6	1890.3
120°	435.8	465.2	494.7	502.0	647.7	841.9	939.1	1121.6	1486.6	1760.3	1794.1
122.5°	462.4	492.2	521.9	529.4	661.3	837.3	925.4	1089.8	1418.5	1664.9	1698.3
125°	503.3	530.4	557.4	564.2	679.7	833.6	910.6	1050.2	1329.4	1538.8	1569.5
127.5°	536.4	563.8	591.1	598.0	698.1	831.5	898.2	1018.0	1257.7	1437.6	1463.4
130°	554.2	583.6	613.1	620.5	711.5	832.9	893.5	1000.2	1213.6	1373.7	1397.6
132.5°	572.5	602.0	631.5	638.9	722.4	833.6	889.3	984.8	1175.9	1319.1	1340.6
135°	599.7	626.6	653.5	660.2	734.2	832.9	882.2	962.3	1122.2	1242.2	1260.7
137.5°	627.6	654.2	680.7	687.4	752.0	838.0	881.0	948.6	1083.9	1185.3	1200.4
140°	650.7	675.2	699.6	705.7	762.8	838.9	876.9	935.3	1052.1	1139.8	1153.9
142.5°	668.5	691.1	713.8	719.4	771.9	841.9	876.9	928.2	1030.8	1107.8	1119.9
145°	695.7	715.5	735.2	740.1	783.8	841.9	871.0	913.0	996.9	1059.9	1069.0
147.5°	722.9	742.1	761.4	766.2	801.1	847.7	871.0	904.0	970.0	1019.6	1027.2
150°	740.7	758.1	775.5	779.8	810.1	850.7	871.0	898.8	954.6	996.4	1002.7
152.5°	759.0	772.2	785.4	788.6	816.0	852.6	871.0	894.7	942.4	978.1	982.8
155°	786.3	796.0	805.7	808.2	829.1	857.0	871.0	889.9	927.8	956.2	959.3
157.5°	806.4	815.9	825.3	827.7	842.1	861.3	871.0	885.7	915.2	937.2	939.4
160°	820.1	827.4	834.8	836.6	848.0	863.3	871.0	883.6	908.9	927.8	929.0
162.5°	833.6	839.2	844.7	846.1	854.4	865.4	871.0	881.7	903.0	918.9	920.0
165°	848.4	853.4	858.4	859.7	863.4	868.5	871.0	878.6	893.9	905.3	906.6
167.5°	862.1	864.5	866.9	867.4	870.6	874.8	876.9	881.8	891.9	899.4	899.9
170°	871.0	873.3	875.7	876.3	876.5	876.8	876.9	881.8	891.9	899.4	899.4
172.5°	875.7	876.2	876.8	876.9	876.9	876.9	876.9	880.8	888.7	894.6	894.2
175°	882.2	882.2	882.2	882.2	880.4	878.0	876.9	879.4	884.4	888.2	888.2
177.5°	882.2	882.2	882.2	882.2	880.8	879.0	878.0	880.0	883.9	886.9	886.4
180°	882.2	882.2	882.2	882.2	882.2	882.2	882.2	882.2	882.2	882.2	882.2

TEST NUMBER: P937404

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1005.2	1005.2
2.5°	1073.1	1066.6
5°	1380.2	1386.7
7.5°	1858.5	1855.4
10°	2311.1	2340.2
12.5°	2640.8	2647.3
15°	2841.2	2854.1
17.5°	2918.8	2922.0
20°	2922.0	2915.5
22.5°	2886.5	2880.0
25°	2844.5	2841.2
27.5°	2805.6	2808.8
30°	2789.5	2799.2
32.5°	2789.5	2805.6
35°	2796.0	2812.1
37.5°	2792.7	2812.1
40°	2779.8	2802.4
42.5°	2744.2	2760.4
45°	2689.3	2708.7
47.5°	2618.1	2631.1
50°	2527.7	2540.6
52.5°	2414.5	2417.8
55°	2278.7	2291.7
57.5°	2133.3	2136.5
60°	1971.7	1981.4
62.5°	1800.4	1800.4
65°	1619.4	1625.9
67.5°	1431.9	1448.1
70°	1241.2	1244.5
72.5°	1053.7	1053.7
75°	859.8	863.0
77.5°	675.6	675.6
80°	501.0	504.2
82.5°	345.9	352.3
85°	216.6	216.6
87.5°	100.2	90.5
90°	22.5	22.5
92.5°	90.2	72.2
95°	314.2	260.0
97.5°	752.6	649.5
100°	1084.5	961.6
102.5°	1410.8	1305.6
105°	1826.8	1770.3
107.5°	2099.5	2113.1
110°	2203.5	2262.4

TEST NUMBER: P937404

CATALOG NUMBER: SQ4-FB-075U-125D-B40-1D-UNV-W2A-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2212.6	2303.2
115°	2154.0	2279.5
117.5°	2029.6	2168.8
120°	1929.4	2064.6
122.5°	1831.7	1965.1
125°	1692.5	1815.4
127.5°	1567.2	1670.9
130°	1493.3	1589.1
132.5°	1426.4	1512.1
135°	1334.6	1408.5
137.5°	1261.0	1321.5
140°	1210.6	1267.1
142.5°	1168.6	1217.3
145°	1105.9	1142.8
147.5°	1057.7	1088.2
150°	1027.4	1052.1
152.5°	1001.4	1020.1
155°	971.7	984.0
157.5°	948.1	956.8
160°	934.1	939.1
162.5°	924.8	929.6
165°	911.5	916.5
167.5°	902.0	904.1
170°	899.4	899.4
172.5°	892.4	890.5
175°	888.2	888.2
177.5°	884.3	882.2
180°	882.2	882.2

(END OF REPORT)