

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937605

Luminaire Tested: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937605
REPORT IS A COMBINATION OF REPORTS P933558 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18005.7 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 147.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937605

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P937605

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45
1	95	90	86	83	86	82	78	75	66	64	62	52	50	49	39	38	37
2	86	78	72	67	77	71	66	61	58	54	50	45	42	40	34	32	30
3	78	68	61	55	70	62	56	50	50	46	42	39	36	33	29	27	25
4	71	60	52	46	64	55	48	42	44	39	35	35	31	28	26	23	21
5	65	53	45	39	58	48	41	36	39	34	30	31	27	24	23	20	18
6	60	47	39	33	54	43	36	31	35	30	26	28	24	21	21	18	16
7	55	42	34	29	49	39	32	27	32	26	22	25	21	18	19	16	14
8	51	38	31	25	46	35	28	23	29	23	20	23	19	16	17	14	12
9	47	35	27	22	42	32	25	21	26	21	17	21	17	14	16	13	11
10	44	32	24	20	40	29	23	18	24	19	15	19	15	12	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2695	2695	2695
5°	2634	3116	3623
10°	2390	4544	6007
15°	2032	5938	7253
20°	1655	6882	7392
25°	1381	7204	7242
30°	1165	7251	7228
35°	1031	7133	7415
40°	899	6978	7608
45°	814	6866	7638
50°	748	6765	7512
55°	717	6616	7178
60°	735	6329	6653
65°	766	5890	5930
70°	818	5140	5010
75°	910	4195	3909
80°	1000	2913	2634
85°	907	1548	1348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 7638 cd/sqm

TEST NUMBER: P937605

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	0.6
10°-20°	499.6	2.8
20°-30°	873.9	4.9
30°-40°	1125.0	6.2
40°-50°	1256.5	7.0
50°-60°	1203.5	6.7
60°-70°	953.8	5.3
70°-80°	560.8	3.1
80°-90°	162.4	0.9
90°-100°	846.5	4.7
100°-110°	2225.5	12.4
110°-120°	2307.6	12.8
120°-130°	1851.0	10.3
130°-140°	1452.3	8.1
140°-150°	1114.7	6.2
150°-160°	802.8	4.5
160°-170°	491.2	2.7
170°-180°	165.9	0.9
0°-30°	1486.2	8.3
0°-40°	2611.2	14.5
0°-60°	5071.2	28.2
0°-90°	6748.2	37.5
90°-120°	5379.5	29.9
90°-150°	9797.5	54.4
90°-180°	11257.0	62.5
0°-180°	18005.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	871	871	871	871	871	
5°	849	911	1026	1160	1202	78
15°	636	1174	1978	2399	2474	177
25°	406	1331	2357	2460	2463	187
35°	275	1272	2219	2345	2438	171
45°	188	1014	1962	2247	2348	145
55°	134	644	1664	1934	1987	123
65°	106	342	1236	1390	1410	106
75°	78	210	678	745	748	82
85°	28	64	168	185	188	30
90°	12	33	88	44	44	12
95°	112	438	1458	752	512	124
105°	401	607	2460	3735	3485	425
115°	712	865	1971	3931	4487	703
125°	991	1111	1792	3029	3573	880
135°	1181	1300	1737	2445	2773	913
145°	1369	1457	1714	2086	2249	858
155°	1548	1591	1714	1882	1937	711
165°	1670	1692	1714	1782	1804	471
175°	1737	1737	1726	1748	1748	165
180°	1737	1737	1737	1737	1737	

TEST NUMBER: P937605

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4	871.4
2.5°	871.4	871.4	877.0	879.8	885.4	888.2	893.8	899.4	916.3	919.1	924.7
5°	849.0	860.2	896.6	910.6	949.9	1003.1	1025.5	1062.1	1137.7	1160.1	1174.1
7.5°	815.4	840.6	930.3	952.7	1050.8	1190.9	1249.8	1328.2	1448.7	1507.6	1555.2
10°	762.1	815.4	975.1	1028.3	1188.1	1401.1	1510.4	1619.6	1801.8	1883.0	1913.9
12.5°	703.3	790.2	1022.7	1095.7	1325.4	1636.5	1768.2	1888.6	2096.0	2205.3	2222.1
15°	636.1	753.7	1067.7	1174.1	1471.1	1832.6	1978.3	2126.8	2320.1	2398.6	2418.2
17.5°	577.2	725.7	1109.7	1221.8	1583.2	2009.1	2157.6	2280.9	2437.8	2491.1	2505.1
20°	504.4	680.9	1137.7	1283.4	1700.9	2138.0	2280.9	2376.2	2482.7	2516.3	2521.9
22.5°	451.1	633.3	1154.5	1305.8	1779.4	2216.5	2337.0	2412.6	2485.5	2496.7	2499.5
25°	406.3	580.0	1151.7	1331.0	1846.6	2264.1	2356.6	2412.6	2454.6	2460.2	2460.2
27.5°	364.3	521.2	1140.5	1336.6	1897.0	2275.3	2348.2	2387.4	2407.0	2418.2	2418.2
30°	327.8	465.1	1112.5	1325.4	1919.5	2264.1	2323.0	2342.6	2362.2	2379.0	2387.4
32.5°	299.8	411.9	1070.5	1303.0	1922.3	2236.1	2278.1	2289.3	2317.3	2356.6	2370.6
35°	274.6	358.7	1022.7	1272.2	1905.5	2191.3	2219.3	2230.5	2286.5	2345.4	2365.0
37.5°	249.4	319.4	961.1	1219.0	1880.2	2138.0	2157.6	2177.2	2264.1	2334.2	2356.6
40°	224.2	285.8	888.2	1160.1	1841.0	2073.6	2090.4	2121.2	2236.1	2317.3	2339.8
42.5°	204.5	257.8	809.8	1098.5	1790.6	2000.7	2025.9	2070.8	2202.5	2289.3	2314.5
45°	187.7	229.8	725.7	1014.3	1726.1	1925.1	1961.5	2023.1	2163.2	2247.3	2269.7
47.5°	170.9	210.2	638.9	927.5	1656.1	1849.4	1897.0	1967.1	2110.0	2191.3	2210.9
50°	156.9	190.5	552.0	835.0	1580.4	1768.2	1824.2	1897.0	2042.8	2118.4	2143.6
52.5°	145.7	173.7	470.7	742.5	1493.6	1684.1	1748.5	1824.2	1961.5	2034.3	2051.2
55°	134.5	159.7	400.7	644.5	1403.9	1594.4	1664.5	1737.3	1871.8	1933.5	1944.7
57.5°	128.9	148.5	341.8	552.0	1308.6	1493.6	1572.0	1639.3	1765.4	1813.0	1824.2
60°	120.5	140.1	297.0	473.5	1205.0	1398.3	1465.5	1532.8	1639.3	1678.5	1686.9
62.5°	112.1	134.5	263.4	397.9	1098.5	1286.2	1353.5	1415.1	1504.8	1532.8	1544.0
65°	106.5	128.9	238.2	341.8	989.1	1168.5	1235.8	1289.0	1361.9	1389.9	1395.5
67.5°	100.9	123.3	218.6	294.2	879.8	1050.8	1101.3	1151.7	1207.8	1235.8	1238.6
70°	92.5	117.7	201.7	260.6	767.7	916.3	958.3	1011.5	1056.4	1070.5	1078.9
72.5°	86.9	109.3	190.5	235.4	652.9	787.4	826.6	857.4	896.6	910.6	910.6
75°	78.5	98.1	179.3	210.2	535.2	644.5	678.1	708.9	739.7	745.3	736.9
77.5°	70.0	86.9	154.1	176.5	417.5	510.0	538.0	554.8	580.0	585.6	588.4
80°	58.8	75.7	120.5	137.3	302.6	375.5	395.1	409.1	431.5	431.5	437.1
82.5°	44.8	58.8	86.9	98.1	204.5	257.8	274.6	283.0	297.0	297.0	297.0
85°	28.0	36.4	56.0	64.4	123.3	156.9	168.1	170.9	182.1	184.9	184.9
87.5°	14.0	19.6	36.4	39.2	64.4	81.3	81.3	86.9	86.9	84.1	81.3
90°	11.7	21.0	30.3	32.6	51.3	76.1	88.5	78.7	59.0	44.3	44.3
92.5°	46.6	125.8	205.1	224.9	316.3	438.0	498.8	437.2	313.9	221.5	212.7
95°	111.9	256.9	402.0	438.2	778.1	1231.4	1458.0	1301.1	987.1	751.7	725.0
97.5°	193.4	321.4	449.3	481.4	1048.1	1803.8	2181.7	2082.5	1884.2	1735.4	1684.7
100°	256.4	372.4	488.4	517.4	1146.4	1985.0	2404.4	2411.7	2426.2	2437.0	2376.6
102.5°	310.0	418.2	526.5	553.6	1191.5	2042.1	2467.3	2593.7	2846.5	3036.1	2984.2
105°	401.0	492.6	584.3	607.2	1224.9	2048.5	2460.3	2743.7	3310.4	3735.3	3707.5
107.5°	494.2	579.6	665.1	686.5	1231.1	1957.3	2320.4	2715.7	3506.1	4099.0	4105.7
110°	557.1	634.3	711.4	730.8	1221.8	1876.5	2203.9	2645.7	3529.4	4192.2	4221.2

TEST NUMBER: P937605

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	618.9	692.5	766.0	784.4	1222.2	1806.0	2097.9	2550.1	3454.5	4132.8	4177.3
115°	712.1	780.0	847.8	864.8	1233.4	1725.0	1970.8	2406.5	3277.7	3931.1	3992.8
117.5°	804.2	865.8	927.5	942.9	1256.4	1674.4	1883.4	2276.5	3062.9	3652.6	3721.1
120°	857.8	915.8	973.9	988.4	1275.1	1657.4	1848.5	2207.7	2926.1	3465.0	3531.5
122.5°	910.3	968.8	1027.3	1042.0	1301.9	1648.4	1821.7	2145.1	2792.1	3277.3	3343.0
125°	990.7	1044.0	1097.4	1110.7	1338.0	1641.0	1792.5	2067.3	2616.9	3029.1	3089.5
127.5°	1055.9	1109.8	1163.7	1177.1	1374.1	1636.7	1768.1	2004.0	2475.8	2829.7	2880.7
130°	1090.9	1148.9	1206.9	1221.4	1400.5	1639.4	1758.7	1968.8	2388.9	2703.9	2751.1
132.5°	1127.1	1185.1	1243.1	1257.5	1421.8	1640.9	1750.5	1938.5	2314.6	2596.7	2638.9
135°	1180.7	1233.4	1286.3	1299.5	1445.2	1639.5	1736.6	1894.1	2208.9	2445.1	2481.5
137.5°	1235.4	1287.7	1340.0	1353.1	1480.1	1649.5	1734.3	1867.3	2133.6	2333.3	2363.1
140°	1280.9	1329.1	1377.2	1389.2	1501.5	1651.2	1726.0	1841.0	2071.1	2243.6	2271.4
142.5°	1315.8	1360.4	1404.9	1416.0	1519.3	1657.1	1726.0	1827.1	2029.1	2180.6	2204.5
145°	1369.4	1408.3	1447.1	1456.9	1542.7	1657.2	1714.5	1797.0	1962.2	2086.2	2104.3
147.5°	1423.0	1460.9	1498.7	1508.1	1576.9	1668.6	1714.5	1779.5	1909.5	2007.0	2022.0
150°	1458.0	1492.2	1526.3	1534.9	1594.8	1674.6	1714.5	1769.4	1879.1	1961.5	1973.6
152.5°	1494.1	1520.0	1546.0	1552.4	1606.4	1678.4	1714.5	1761.3	1855.0	1925.3	1934.5
155°	1547.7	1566.9	1586.1	1590.9	1632.1	1687.0	1714.5	1751.7	1826.3	1882.2	1888.3
157.5°	1587.3	1606.0	1624.7	1629.4	1657.8	1695.6	1714.5	1743.4	1801.4	1844.9	1849.2
160°	1614.1	1628.7	1643.2	1646.8	1669.3	1699.4	1714.5	1739.3	1789.0	1826.3	1828.7
162.5°	1640.9	1651.8	1662.7	1665.4	1681.8	1703.5	1714.5	1735.4	1777.3	1808.8	1811.1
165°	1670.1	1679.9	1689.8	1692.2	1699.6	1709.5	1714.5	1729.5	1759.5	1782.0	1784.4
167.5°	1696.9	1701.6	1706.2	1707.4	1713.6	1721.9	1726.0	1735.9	1755.6	1770.4	1771.4
170°	1714.5	1719.1	1723.8	1724.9	1725.3	1725.8	1726.0	1735.9	1755.6	1770.4	1770.4
172.5°	1723.7	1724.7	1725.8	1726.0	1726.0	1726.0	1726.0	1733.8	1749.4	1761.1	1760.1
175°	1736.6	1736.6	1736.6	1736.6	1733.0	1728.4	1726.0	1731.0	1740.8	1748.2	1748.2
177.5°	1736.6	1736.6	1736.6	1736.6	1733.9	1730.2	1728.4	1732.3	1740.0	1745.8	1744.8
180°	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6

TEST NUMBER: P937605

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	871.4	871.4
2.5°	930.3	924.7
5°	1196.5	1202.2
7.5°	1611.2	1608.4
10°	2003.5	2028.7
12.5°	2289.3	2294.9
15°	2463.1	2474.3
17.5°	2530.3	2533.1
20°	2533.1	2527.5
22.5°	2502.3	2496.7
25°	2465.9	2463.1
27.5°	2432.2	2435.0
30°	2418.2	2426.6
32.5°	2418.2	2432.2
35°	2423.8	2437.8
37.5°	2421.0	2437.8
40°	2409.8	2429.4
42.5°	2379.0	2393.0
45°	2331.4	2348.2
47.5°	2269.7	2280.9
50°	2191.3	2202.5
52.5°	2093.2	2096.0
55°	1975.5	1986.7
57.5°	1849.4	1852.2
60°	1709.3	1717.7
62.5°	1560.8	1560.8
65°	1403.9	1409.5
67.5°	1241.4	1255.4
70°	1076.1	1078.9
72.5°	913.5	913.5
75°	745.3	748.1
77.5°	585.6	585.6
80°	434.3	437.1
82.5°	299.8	305.4
85°	187.7	187.7
87.5°	86.9	78.5
90°	44.3	44.3
92.5°	177.4	142.2
95°	618.3	511.6
97.5°	1481.6	1278.6
100°	2134.7	1892.8
102.5°	2777.1	2569.9
105°	3596.1	3484.8
107.5°	4132.7	4159.6
110°	4337.2	4453.3

TEST NUMBER: P937605

CATALOG NUMBER: SQ4-FB-100U-075D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4355.5	4533.7
115°	4240.0	4487.0
117.5°	3995.1	4269.1
120°	3797.7	4064.0
122.5°	3605.5	3868.2
125°	3331.4	3573.3
127.5°	3084.9	3289.0
130°	2939.6	3128.2
132.5°	2807.8	2976.7
135°	2627.1	2772.7
137.5°	2482.2	2601.4
140°	2382.8	2494.2
142.5°	2300.3	2396.2
145°	2176.9	2249.4
147.5°	2082.1	2142.1
150°	2022.4	2071.1
152.5°	1971.3	2008.1
155°	1912.6	1937.0
157.5°	1866.3	1883.4
160°	1838.6	1848.5
162.5°	1820.5	1829.8
165°	1794.3	1804.1
167.5°	1775.5	1779.6
170°	1770.4	1770.4
172.5°	1756.5	1752.8
175°	1748.2	1748.2
177.5°	1740.7	1736.6
180°	1736.6	1736.6

(END OF REPORT)