

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937705

Luminaire Tested: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937705
REPORT IS A COMBINATION OF REPORTS P933559 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20170.7 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 174
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937705

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P937705

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20					20				20
RC	80				70				50					30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	96	91	87	84	88	84	80	77	69	67	65	56	55	53	44	43	42	36
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34	30
3	79	69	62	56	72	63	57	52	53	48	44	43	39	36	33	31	29	24
4	72	61	53	46	65	56	49	43	46	41	37	38	34	30	29	27	24	20
5	66	54	46	39	60	49	42	37	41	36	31	33	29	26	26	23	21	17
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	20	18	15
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	21	18	16	13
8	51	39	31	26	47	36	29	24	30	24	20	25	20	17	19	16	14	11
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	44	32	25	20	41	30	23	19	25	20	16	21	16	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3561	3561	3561
5°	3480	4117	4787
10°	3158	6003	7935
15°	2685	7844	9582
20°	2187	9093	9766
25°	1825	9517	9567
30°	1539	9580	9549
35°	1362	9423	9796
40°	1188	9219	10051
45°	1076	9070	10091
50°	988	8937	9924
55°	947	8741	9484
60°	971	8361	8789
65°	1012	7781	7835
70°	1080	6791	6619
75°	1202	5542	5166
80°	1322	3848	3480
85°	1199	2045	1782

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 10091 cd/sqm

TEST NUMBER: P937705

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.9	0.7
10°-20°	660.1	3.3
20°-30°	1154.5	5.7
30°-40°	1486.2	7.4
40°-50°	1660.1	8.2
50°-60°	1590.0	7.9
60°-70°	1260.1	6.2
70°-80°	740.9	3.7
80°-90°	212.5	1.1
90°-100°	846.5	4.2
100°-110°	2225.5	11.0
110°-120°	2307.6	11.4
120°-130°	1851.0	9.2
130°-140°	1452.3	7.2
140°-150°	1114.7	5.5
150°-160°	802.8	4.0
160°-170°	491.2	2.4
170°-180°	165.9	0.8
0°-30°	1963.5	9.7
0°-40°	3449.8	17.1
0°-60°	6699.8	33.2
0°-90°	8913.3	44.2
90°-120°	5379.5	26.7
90°-150°	9797.5	48.6
90°-180°	11257.0	55.8
0°-180°	20170.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1151	1151	1151	1151	1151	
5°	1122	1203	1355	1533	1588	104
15°	840	1551	2614	3169	3269	234
25°	537	1758	3113	3250	3254	247
35°	363	1681	2932	3098	3221	227
45°	248	1340	2591	2969	3102	192
55°	178	851	2199	2554	2625	162
65°	141	452	1632	1836	1862	139
75°	104	278	896	985	988	109
85°	37	85	222	244	248	39
90°	12	33	88	44	44	12
95°	112	438	1458	752	512	124
105°	401	607	2460	3735	3485	425
115°	712	865	1971	3931	4487	703
125°	991	1111	1792	3029	3573	880
135°	1181	1300	1737	2445	2773	913
145°	1369	1457	1714	2086	2249	858
155°	1548	1591	1714	1882	1937	711
165°	1670	1692	1714	1782	1804	471
175°	1737	1737	1726	1748	1748	165
180°	1737	1737	1737	1737	1737	

TEST NUMBER: P937705

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1151.3	1151.3	1158.7	1162.5	1169.8	1173.6	1180.9	1188.3	1210.6	1214.3	1221.7
5°	1121.7	1136.5	1184.7	1203.2	1255.0	1325.3	1355.0	1403.1	1503.0	1532.6	1551.1
7.5°	1077.3	1110.6	1229.1	1258.7	1388.2	1573.3	1651.1	1754.7	1914.0	1991.7	2054.6
10°	1006.9	1077.3	1288.3	1358.6	1569.7	1851.0	1995.4	2139.8	2380.4	2487.7	2528.4
12.5°	929.2	1043.9	1351.2	1447.5	1751.1	2161.9	2335.9	2495.2	2769.1	2913.5	2935.7
15°	840.3	995.8	1410.4	1551.1	1943.6	2421.1	2613.6	2809.8	3065.3	3168.9	3194.8
17.5°	762.6	958.8	1466.0	1614.0	2091.6	2654.3	2850.6	3013.5	3220.7	3291.0	3309.6
20°	666.3	899.6	1503.0	1695.5	2247.1	2824.6	3013.5	3139.3	3279.9	3324.4	3331.8
22.5°	596.0	836.7	1525.2	1725.1	2350.8	2928.3	3087.4	3187.5	3283.7	3298.5	3302.2
25°	536.8	766.3	1521.5	1758.4	2439.6	2991.2	3113.4	3187.5	3242.9	3250.3	3250.3
27.5°	481.3	688.5	1506.7	1765.8	2506.3	3006.0	3102.3	3154.1	3180.0	3194.8	3194.8
30°	433.1	614.6	1469.6	1751.1	2535.9	2991.2	3068.9	3094.9	3120.8	3143.0	3154.1
32.5°	396.1	544.1	1414.2	1721.5	2539.5	2954.2	3009.7	3024.6	3061.6	3113.4	3131.9
35°	362.8	473.8	1351.2	1680.7	2517.3	2894.9	2932.0	2946.8	3020.8	3098.5	3124.5
37.5°	329.5	422.1	1269.8	1610.4	2484.1	2824.6	2850.6	2876.4	2991.2	3083.8	3113.4
40°	296.2	377.6	1173.6	1532.6	2432.2	2739.5	2761.7	2802.4	2954.2	3061.6	3091.2
42.5°	270.2	340.6	1069.9	1451.2	2365.5	2643.2	2676.6	2735.8	2909.8	3024.6	3057.8
45°	248.1	303.6	958.8	1340.1	2280.5	2543.3	2591.4	2672.8	2857.9	2969.0	2998.6
47.5°	225.8	277.7	844.1	1225.4	2187.9	2443.3	2506.3	2598.8	2787.6	2894.9	2920.9
50°	207.3	251.7	729.3	1103.2	2088.0	2335.9	2410.0	2506.3	2698.8	2798.7	2832.1
52.5°	192.5	229.5	622.0	981.1	1973.2	2224.9	2310.1	2410.0	2591.4	2687.7	2709.9
55°	177.7	211.0	529.4	851.4	1854.7	2106.5	2199.0	2295.2	2473.0	2554.4	2569.2
57.5°	170.3	196.2	451.7	729.3	1728.8	1973.2	2076.8	2165.7	2332.3	2395.1	2410.0
60°	159.2	185.1	392.4	625.6	1591.8	1847.3	1936.2	2025.0	2165.7	2217.5	2228.6
62.5°	148.0	177.7	348.0	525.7	1451.2	1699.2	1788.0	1869.5	1988.0	2025.0	2039.8
65°	140.7	170.3	314.7	451.7	1306.9	1543.7	1632.5	1703.0	1799.2	1836.2	1843.6
67.5°	133.3	162.9	288.8	388.7	1162.5	1388.2	1454.9	1521.5	1595.6	1632.5	1636.3
70°	122.2	155.5	266.6	344.3	1014.3	1210.6	1266.1	1336.5	1395.7	1414.2	1425.3
72.5°	114.8	144.4	251.7	310.9	862.5	1040.3	1092.1	1132.8	1184.7	1203.2	1203.2
75°	103.7	129.5	237.0	277.7	707.0	851.4	895.9	936.6	977.3	984.7	973.6
77.5°	92.6	114.8	203.6	233.2	551.6	673.8	710.8	733.0	766.3	773.7	777.5
80°	77.7	99.9	159.2	181.4	399.8	496.0	522.0	540.5	570.1	570.1	577.5
82.5°	59.2	77.7	114.8	129.5	270.2	340.6	362.8	373.9	392.4	392.4	392.4
85°	37.0	48.1	74.1	85.2	162.9	207.3	222.1	225.8	240.6	244.3	244.3
87.5°	18.5	25.9	48.1	51.8	85.2	107.3	107.3	114.8	114.8	111.1	107.3
90°	11.7	21.0	30.3	32.6	51.3	76.1	88.5	78.7	59.0	44.3	44.3
92.5°	46.6	125.8	205.1	224.9	316.3	438.0	498.8	437.2	313.9	221.5	212.7
95°	111.9	256.9	402.0	438.2	778.1	1231.4	1458.0	1301.1	987.1	751.7	725.0
97.5°	193.4	321.4	449.3	481.4	1048.1	1803.8	2181.7	2082.5	1884.2	1735.4	1684.7
100°	256.4	372.4	488.4	517.4	1146.4	1985.0	2404.4	2411.7	2426.2	2437.0	2376.6
102.5°	310.0	418.2	526.5	553.6	1191.5	2042.1	2467.3	2593.7	2846.5	3036.1	2984.2
105°	401.0	492.6	584.3	607.2	1224.9	2048.5	2460.3	2743.7	3310.4	3735.3	3707.5
107.5°	494.2	579.6	665.1	686.5	1231.1	1957.3	2320.4	2715.7	3506.1	4099.0	4105.7
110°	557.1	634.3	711.4	730.8	1221.8	1876.5	2203.9	2645.7	3529.4	4192.2	4221.2

TEST NUMBER: P937705

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	618.9	692.5	766.0	784.4	1222.2	1806.0	2097.9	2550.1	3454.5	4132.8	4177.3
115°	712.1	780.0	847.8	864.8	1233.4	1725.0	1970.8	2406.5	3277.7	3931.1	3992.8
117.5°	804.2	865.8	927.5	942.9	1256.4	1674.4	1883.4	2276.5	3062.9	3652.6	3721.1
120°	857.8	915.8	973.9	988.4	1275.1	1657.4	1848.5	2207.7	2926.1	3465.0	3531.5
122.5°	910.3	968.8	1027.3	1042.0	1301.9	1648.4	1821.7	2145.1	2792.1	3277.3	3343.0
125°	990.7	1044.0	1097.4	1110.7	1338.0	1641.0	1792.5	2067.3	2616.9	3029.1	3089.5
127.5°	1055.9	1109.8	1163.7	1177.1	1374.1	1636.7	1768.1	2004.0	2475.8	2829.7	2880.7
130°	1090.9	1148.9	1206.9	1221.4	1400.5	1639.4	1758.7	1968.8	2388.9	2703.9	2751.1
132.5°	1127.1	1185.1	1243.1	1257.5	1421.8	1640.9	1750.5	1938.5	2314.6	2596.7	2638.9
135°	1180.7	1233.4	1286.3	1299.5	1445.2	1639.5	1736.6	1894.1	2208.9	2445.1	2481.5
137.5°	1235.4	1287.7	1340.0	1353.1	1480.1	1649.5	1734.3	1867.3	2133.6	2333.3	2363.1
140°	1280.9	1329.1	1377.2	1389.2	1501.5	1651.2	1726.0	1841.0	2071.1	2243.6	2271.4
142.5°	1315.8	1360.4	1404.9	1416.0	1519.3	1657.1	1726.0	1827.1	2029.1	2180.6	2204.5
145°	1369.4	1408.3	1447.1	1456.9	1542.7	1657.2	1714.5	1797.0	1962.2	2086.2	2104.3
147.5°	1423.0	1460.9	1498.7	1508.1	1576.9	1668.6	1714.5	1779.5	1909.5	2007.0	2022.0
150°	1458.0	1492.2	1526.3	1534.9	1594.8	1674.6	1714.5	1769.4	1879.1	1961.5	1973.6
152.5°	1494.1	1520.0	1546.0	1552.4	1606.4	1678.4	1714.5	1761.3	1855.0	1925.3	1934.5
155°	1547.7	1566.9	1586.1	1590.9	1632.1	1687.0	1714.5	1751.7	1826.3	1882.2	1888.3
157.5°	1587.3	1606.0	1624.7	1629.4	1657.8	1695.6	1714.5	1743.4	1801.4	1844.9	1849.2
160°	1614.1	1628.7	1643.2	1646.8	1669.3	1699.4	1714.5	1739.3	1789.0	1826.3	1828.7
162.5°	1640.9	1651.8	1662.7	1665.4	1681.8	1703.5	1714.5	1735.4	1777.3	1808.8	1811.1
165°	1670.1	1679.9	1689.8	1692.2	1699.6	1709.5	1714.5	1729.5	1759.5	1782.0	1784.4
167.5°	1696.9	1701.6	1706.2	1707.4	1713.6	1721.9	1726.0	1735.9	1755.6	1770.4	1771.4
170°	1714.5	1719.1	1723.8	1724.9	1725.3	1725.8	1726.0	1735.9	1755.6	1770.4	1770.4
172.5°	1723.7	1724.7	1725.8	1726.0	1726.0	1726.0	1726.0	1733.8	1749.4	1761.1	1760.1
175°	1736.6	1736.6	1736.6	1736.6	1733.0	1728.4	1726.0	1731.0	1740.8	1748.2	1748.2
177.5°	1736.6	1736.6	1736.6	1736.6	1733.9	1730.2	1728.4	1732.3	1740.0	1745.8	1744.8
180°	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6	1736.6

TEST NUMBER: P937705

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1151.3	1151.3
2.5°	1229.1	1221.7
5°	1580.8	1588.2
7.5°	2128.7	2124.9
10°	2647.0	2680.2
12.5°	3024.6	3032.0
15°	3254.1	3268.9
17.5°	3342.9	3346.6
20°	3346.6	3339.2
22.5°	3305.9	3298.5
25°	3257.8	3254.1
27.5°	3213.3	3217.1
30°	3194.8	3206.0
32.5°	3194.8	3213.3
35°	3202.2	3220.7
37.5°	3198.5	3220.7
40°	3183.7	3209.6
42.5°	3143.0	3161.5
45°	3080.1	3102.3
47.5°	2998.6	3013.5
50°	2894.9	2909.8
52.5°	2765.4	2769.1
55°	2609.9	2624.7
57.5°	2443.3	2447.0
60°	2258.2	2269.3
62.5°	2062.0	2062.0
65°	1854.7	1862.1
67.5°	1640.0	1658.5
70°	1421.5	1425.3
72.5°	1206.8	1206.8
75°	984.7	988.5
77.5°	773.7	773.7
80°	573.8	577.5
82.5°	396.1	403.5
85°	248.1	248.1
87.5°	114.8	103.7
90°	44.3	44.3
92.5°	177.4	142.2
95°	618.3	511.6
97.5°	1481.6	1278.6
100°	2134.7	1892.8
102.5°	2777.1	2569.9
105°	3596.1	3484.8
107.5°	4132.7	4159.6
110°	4337.2	4453.3

TEST NUMBER: P937705

CATALOG NUMBER: SQ4-FB-100U-100D-B50-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4355.5	4533.7
115°	4240.0	4487.0
117.5°	3995.1	4269.1
120°	3797.7	4064.0
122.5°	3605.5	3868.2
125°	3331.4	3573.3
127.5°	3084.9	3289.0
130°	2939.6	3128.2
132.5°	2807.8	2976.7
135°	2627.1	2772.7
137.5°	2482.2	2601.4
140°	2382.8	2494.2
142.5°	2300.3	2396.2
145°	2176.9	2249.4
147.5°	2082.1	2142.1
150°	2022.4	2071.1
152.5°	1971.3	2008.1
155°	1912.6	1937.0
157.5°	1866.3	1883.4
160°	1838.6	1848.5
162.5°	1820.5	1829.8
165°	1794.3	1804.1
167.5°	1775.5	1779.6
170°	1770.4	1770.4
172.5°	1756.5	1752.8
175°	1748.2	1748.2
177.5°	1740.7	1736.6
180°	1736.6	1736.6

(END OF REPORT)