

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937806

Luminaire Tested: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937806
REPORT IS A COMBINATION OF REPORTS P933568 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7557.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 68.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937806

CATALOG NUMBER: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4

Luminous Intensity Polar Plot



TEST NUMBER: P937806

CATALOG NUMBER: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56
1	97	93	89	85	90	86	82	79	72	70	67	60	58	57	49	48	47
2	88	80	74	68	81	74	69	64	63	59	55	52	49	46	42	40	38
3	80	70	62	56	73	65	58	53	55	50	45	46	42	39	37	34	32
4	73	62	53	47	67	57	50	44	48	43	38	40	36	32	33	30	27
5	67	54	46	40	61	50	43	37	43	37	32	36	31	28	29	26	23
6	61	49	40	34	56	45	37	32	38	32	28	32	27	24	26	23	20
7	56	44	35	30	52	40	33	28	34	29	24	29	24	21	24	20	17
8	52	39	31	26	48	37	29	24	31	25	21	26	22	18	22	18	15
9	48	36	28	23	44	33	26	21	28	23	19	24	19	16	20	16	14
10	45	33	25	20	41	30	24	19	26	21	17	22	18	15	18	15	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4561	4561	4561
5°	4451	5267	6130
10°	4032	7672	10163
15°	3423	10017	12272
20°	2784	11600	12508
25°	2320	12130	12253
30°	1953	12196	12230
35°	1724	11985	12546
40°	1501	11712	12873
45°	1356	11508	12923
50°	1241	11324	12709
55°	1184	11058	12146
60°	1210	10558	11256
65°	1252	9805	10034
70°	1323	8533	8477
75°	1453	6940	6616
80°	1554	4797	4458
85°	1308	2530	2282

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 45°

Luminance: 12923 cd/sqm

TEST NUMBER: P937806

CATALOG NUMBER: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.6	0.8
10°-20°	281.8	3.7
20°-30°	492.9	6.5
30°-40°	634.5	8.4
40°-50°	708.7	9.4
50°-60°	678.8	9.0
60°-70°	537.9	7.1
70°-80°	316.3	4.2
80°-90°	90.1	1.2
90°-100°	282.1	3.7
100°-110°	741.8	9.8
110°-120°	769.2	10.2
120°-130°	617.0	8.2
130°-140°	484.1	6.4
140°-150°	371.6	4.9
150°-160°	267.6	3.5
160°-170°	163.7	2.2
170°-180°	55.3	0.7
0°-30°	838.2	11.1
0°-40°	1472.7	19.5
0°-60°	2860.2	37.8
0°-90°	3804.6	50.3
90°-120°	1793.2	23.7
90°-150°	3265.8	43.2
90°-180°	3752.0	49.6
0°-180°	7557.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	492	492	492	492	492	
5°	479	514	578	654	678	44
15°	359	662	1116	1353	1396	100
25°	229	751	1329	1388	1389	106
35°	155	718	1252	1323	1375	97
45°	106	572	1106	1268	1324	82
55°	76	364	939	1090	1120	69
65°	60	193	697	784	795	60
75°	44	118	382	420	422	46
85°	16	36	95	104	106	17
90°	4	11	30	15	15	4
95°	37	146	486	251	170	41
105°	134	202	820	1245	1162	142
115°	237	288	657	1310	1496	234
125°	330	370	598	1010	1191	293
135°	394	433	579	815	924	304
145°	456	486	572	695	750	286
155°	516	530	572	627	646	237
165°	557	564	572	594	601	157
175°	579	579	575	583	583	55
180°	579	579	579	579	579	

TEST NUMBER: P937806

CATALOG NUMBER: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5
2.5°	491.5	491.5	494.6	496.2	499.4	501.0	504.2	507.3	516.8	518.4	521.5
5°	478.9	485.2	505.8	513.6	535.7	565.8	578.4	599.0	641.7	654.3	662.2
7.5°	459.9	474.1	524.7	537.3	592.6	671.6	704.9	749.2	817.1	850.2	877.1
10°	429.8	459.9	549.9	580.0	670.1	790.2	851.8	913.5	1016.2	1062.1	1079.4
12.5°	396.7	445.7	576.8	617.9	747.6	923.0	997.2	1065.2	1182.2	1243.8	1253.2
15°	358.7	425.2	602.1	662.2	829.7	1033.6	1115.8	1199.5	1308.6	1352.8	1363.9
17.5°	325.6	409.4	625.9	689.1	892.9	1133.1	1216.9	1286.5	1374.9	1405.0	1412.9
20°	284.5	384.1	641.7	723.8	959.3	1205.9	1286.5	1340.2	1400.3	1419.2	1422.4
22.5°	254.4	357.2	651.1	736.5	1003.6	1250.1	1318.1	1360.7	1401.8	1408.2	1409.7
25°	229.2	327.2	649.6	750.7	1041.5	1277.0	1329.2	1360.7	1384.5	1387.6	1387.6
27.5°	205.5	293.9	643.2	753.8	1069.9	1283.3	1324.4	1346.5	1357.6	1363.9	1363.9
30°	184.9	262.4	627.5	747.6	1082.6	1277.0	1310.1	1321.2	1332.3	1341.8	1346.5
32.5°	169.1	232.3	603.7	734.9	1084.2	1261.2	1284.9	1291.2	1307.0	1329.2	1337.0
35°	154.9	202.3	576.8	717.5	1074.7	1235.9	1251.7	1258.0	1289.6	1322.8	1333.8
37.5°	140.7	180.2	542.1	687.5	1060.5	1205.9	1216.9	1228.0	1277.0	1316.5	1329.2
40°	126.5	161.2	501.0	654.3	1038.3	1169.5	1179.0	1196.4	1261.2	1307.0	1319.6
42.5°	115.3	145.4	456.7	619.5	1009.8	1128.5	1142.7	1168.0	1242.2	1291.2	1305.5
45°	105.9	129.6	409.4	572.1	973.5	1085.8	1106.3	1141.1	1220.1	1267.5	1280.1
47.5°	96.4	118.5	360.3	523.1	934.0	1043.1	1069.9	1109.5	1190.0	1235.9	1247.0
50°	88.5	107.5	311.3	470.9	891.3	997.2	1028.9	1069.9	1152.1	1194.8	1209.1
52.5°	82.2	98.0	265.5	418.8	842.4	949.8	986.2	1028.9	1106.3	1147.4	1156.9
55°	75.8	90.0	226.0	363.5	791.8	899.3	938.8	979.9	1055.7	1090.4	1096.8
57.5°	72.7	83.8	192.8	311.3	738.0	842.4	886.6	924.6	995.6	1022.5	1028.9
60°	68.0	79.0	167.6	267.1	679.6	788.7	826.6	864.5	924.6	946.7	951.4
62.5°	63.2	75.8	148.6	224.4	619.5	725.4	763.4	798.1	848.7	864.5	870.8
65°	60.1	72.7	134.3	192.8	557.9	659.0	697.0	727.0	768.1	783.9	787.1
67.5°	56.9	69.6	123.3	166.0	496.2	592.6	621.1	649.6	681.2	697.0	698.5
70°	52.1	66.4	113.8	147.0	433.0	516.8	540.5	570.5	595.8	603.7	608.5
72.5°	49.0	61.6	107.5	132.7	368.3	444.1	466.3	483.6	505.8	513.6	513.6
75°	44.3	55.3	101.2	118.5	301.9	363.5	382.5	399.8	417.2	420.4	415.6
77.5°	39.5	49.0	87.0	99.6	235.5	287.7	303.5	312.9	327.2	330.3	331.9
80°	33.2	42.7	68.0	77.4	170.6	211.7	222.9	230.7	243.4	243.4	246.6
82.5°	25.3	33.2	49.0	55.3	115.3	145.4	154.9	159.6	167.6	167.6	167.6
85°	15.8	20.5	31.6	36.3	69.6	88.5	94.8	96.4	102.7	104.3	104.3
87.5°	7.9	11.0	20.5	22.1	36.3	45.9	45.9	49.0	49.0	47.4	45.9
90°	3.9	7.0	10.1	10.8	17.1	25.4	29.5	26.2	19.7	14.8	14.8
92.5°	15.5	41.9	68.4	75.0	105.4	146.0	166.3	145.7	104.6	73.8	70.9
95°	37.3	85.6	134.0	146.1	259.4	410.4	486.0	433.7	329.0	250.6	241.7
97.5°	64.4	107.1	149.8	160.5	349.4	601.3	727.2	694.1	628.0	578.4	561.5
100°	85.5	124.1	162.8	172.5	382.2	661.7	801.5	803.9	808.7	812.3	792.1
102.5°	103.3	139.4	175.5	184.6	397.2	680.7	822.5	864.6	948.9	1012.0	994.7
105°	133.7	164.2	194.7	202.4	408.3	682.8	820.1	914.6	1103.4	1245.1	1235.9
107.5°	164.8	193.2	221.7	228.8	410.4	652.4	773.4	905.2	1168.7	1366.3	1368.6
110°	185.7	211.5	237.1	243.6	407.2	625.5	734.6	881.9	1176.5	1397.4	1407.1

TEST NUMBER: P937806

CATALOG NUMBER: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	206.3	230.8	255.3	261.4	407.4	602.0	699.3	850.0	1151.4	1377.6	1392.4
115°	237.3	259.9	282.5	288.2	411.1	575.1	657.0	802.2	1092.6	1310.4	1331.0
117.5°	268.1	288.6	309.2	314.3	418.8	558.2	627.8	758.9	1021.0	1217.6	1240.4
120°	285.9	305.2	324.6	329.4	425.0	552.5	616.2	735.9	975.4	1155.0	1177.2
122.5°	303.5	323.0	342.5	347.4	433.9	549.5	607.2	715.0	930.6	1092.4	1114.3
125°	330.3	348.0	365.8	370.2	446.0	547.0	597.5	689.1	872.3	1009.7	1029.8
127.5°	351.9	369.9	387.9	392.4	458.0	545.5	589.4	668.0	825.3	943.2	960.2
130°	363.6	382.9	402.3	407.1	466.8	546.5	586.3	656.3	796.3	901.3	917.0
132.5°	375.7	395.0	414.3	419.2	473.9	547.0	583.5	646.1	771.5	865.5	879.6
135°	393.6	411.1	428.8	433.2	481.8	546.5	578.9	631.4	736.3	815.0	827.2
137.5°	411.8	429.3	446.6	451.0	493.3	549.8	578.1	622.4	711.1	777.7	787.6
140°	426.9	443.0	459.1	463.1	500.5	550.4	575.3	613.6	690.3	747.9	757.1
142.5°	438.6	453.5	468.3	472.0	506.5	552.4	575.3	609.0	676.3	726.8	734.9
145°	456.4	469.4	482.3	485.6	514.3	552.5	571.5	599.1	654.1	695.4	701.4
147.5°	474.4	487.0	499.5	502.7	525.7	556.2	571.5	593.2	636.5	669.0	674.1
150°	486.0	497.4	508.7	511.6	531.6	558.3	571.5	589.8	626.3	653.8	657.8
152.5°	498.0	506.6	515.3	517.4	535.5	559.5	571.5	587.1	618.3	641.8	644.8
155°	515.9	522.3	528.7	530.3	544.1	562.4	571.5	583.9	608.8	627.4	629.4
157.5°	529.1	535.4	541.5	543.1	552.6	565.2	571.5	581.1	600.5	614.9	616.3
160°	538.1	542.9	547.7	548.9	556.5	566.5	571.5	579.8	596.4	608.8	609.6
162.5°	547.0	550.6	554.2	555.2	560.6	567.9	571.5	578.5	592.4	602.9	603.6
165°	556.7	559.9	563.2	564.0	566.6	569.8	571.5	576.6	586.6	594.0	594.9
167.5°	565.6	567.2	568.8	569.2	571.2	573.9	575.3	578.6	585.2	590.1	590.5
170°	571.5	573.0	574.6	575.0	575.1	575.3	575.3	578.6	585.2	590.1	590.1
172.5°	574.6	575.0	575.3	575.3	575.3	575.3	575.3	578.0	583.1	587.0	586.7
175°	578.9	578.9	578.9	578.9	577.7	576.1	575.3	577.0	580.3	582.7	582.7
177.5°	578.9	578.9	578.9	578.9	578.0	576.7	576.1	577.4	580.0	582.0	581.6
180°	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9	578.9

TEST NUMBER: P937806

CATALOG NUMBER: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	491.5	491.5
2.5°	524.7	521.5
5°	674.8	678.0
7.5°	908.8	907.2
10°	1130.0	1144.2
12.5°	1291.2	1294.3
15°	1389.2	1395.5
17.5°	1427.2	1428.7
20°	1428.7	1425.6
22.5°	1411.3	1408.2
25°	1390.7	1389.2
27.5°	1371.8	1373.4
30°	1363.9	1368.7
32.5°	1363.9	1371.8
35°	1367.1	1374.9
37.5°	1365.5	1374.9
40°	1359.2	1370.2
42.5°	1341.8	1349.6
45°	1314.9	1324.4
47.5°	1280.1	1286.5
50°	1235.9	1242.2
52.5°	1180.6	1182.2
55°	1114.2	1120.5
57.5°	1043.1	1044.7
60°	964.1	968.8
62.5°	880.3	880.3
65°	791.8	794.9
67.5°	700.1	708.1
70°	606.9	608.5
72.5°	515.2	515.2
75°	420.4	422.0
77.5°	330.3	330.3
80°	245.0	246.6
82.5°	169.1	172.2
85°	105.9	105.9
87.5°	49.0	44.3
90°	14.8	14.8
92.5°	59.1	47.4
95°	206.1	170.5
97.5°	493.8	426.2
100°	711.5	630.9
102.5°	925.7	856.7
105°	1198.7	1161.6
107.5°	1377.6	1386.5
110°	1445.7	1484.4

TEST NUMBER: P937806

CATALOG NUMBER: SQ4-FB-100U-125D-B50-1D-UNV-W2A-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1451.8	1511.2
115°	1413.3	1495.7
117.5°	1331.7	1423.0
120°	1265.9	1354.7
122.5°	1201.9	1289.4
125°	1110.4	1191.1
127.5°	1028.3	1096.3
130°	979.9	1042.7
132.5°	935.9	992.2
135°	875.6	924.2
137.5°	827.4	867.1
140°	794.3	831.4
142.5°	766.8	798.8
145°	725.6	749.8
147.5°	694.1	714.0
150°	674.1	690.3
152.5°	657.1	669.4
155°	637.5	645.7
157.5°	622.1	627.8
160°	612.9	616.2
162.5°	606.8	609.9
165°	598.1	601.4
167.5°	591.8	593.2
170°	590.1	590.1
172.5°	585.5	584.3
175°	582.7	582.7
177.5°	580.3	578.9
180°	578.9	578.9

(END OF REPORT)