

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937901

Luminaire Tested: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937901
REPORT IS A COMBINATION OF REPORTS P933589 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18959.6 lumens
Efficiency: N/A
Efficacy: 132.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 142.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937901

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12

Luminous Intensity Polar Plot



TEST NUMBER: P937901

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	84	80	81	78	75	72	60	58	56	44	42	41	28	28	27
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22
3	76	66	59	54	67	59	53	48	46	42	38	33	30	28	22	20	19
4	69	58	51	45	61	52	46	41	40	36	32	29	26	24	19	17	16
5	63	52	44	38	56	46	39	34	36	31	27	26	23	20	17	15	13
6	58	46	38	33	51	41	34	29	32	27	23	23	20	17	15	13	12
7	53	41	34	28	47	37	30	26	29	24	20	21	18	15	14	12	10
8	49	37	30	25	44	33	27	22	26	21	18	19	16	13	12	10	9
9	46	34	27	22	40	30	24	20	24	19	16	17	14	12	11	9	8
10	42	31	24	19	38	28	21	17	22	17	14	16	13	10	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1848	1848	1848
5°	1807	2137	2485
10°	1639	3116	4119
15°	1394	4072	4974
20°	1135	4720	5069
25°	947	4940	4966
30°	799	4973	4957
35°	707	4891	5085
40°	617	4786	5217
45°	558	4708	5238
50°	513	4639	5151
55°	492	4537	4923
60°	504	4340	4562
65°	526	4039	4067
70°	561	3525	3436
75°	624	2876	2681
80°	687	1997	1807
85°	622	1062	924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 5493 cd/sqm

TEST NUMBER: P937901

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	0.4
10°-20°	342.6	1.8
20°-30°	599.3	3.2
30°-40°	771.5	4.1
40°-50°	861.7	4.5
50°-60°	825.3	4.4
60°-70°	654.1	3.4
70°-80°	384.6	2.0
80°-90°	115.3	0.6
90°-100°	1077.4	5.7
100°-110°	2832.5	14.9
110°-120°	2937.0	15.5
120°-130°	2355.8	12.4
130°-140°	1848.5	9.7
140°-150°	1418.8	7.5
150°-160°	1021.8	5.4
160°-170°	625.2	3.3
170°-180°	211.2	1.1
0°-30°	1019.2	5.4
0°-40°	1790.7	9.4
0°-60°	3477.7	18.3
0°-90°	4631.6	24.4
90°-120°	6846.8	36.1
90°-150°	12469.9	65.8
90°-180°	14328.0	75.6
0°-180°	18959.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	582	624	703	796	824	54
15°	436	805	1357	1645	1697	121
25°	279	913	1616	1687	1689	128
35°	188	872	1522	1608	1672	118
45°	129	696	1345	1541	1610	100
55°	92	442	1141	1326	1362	84
65°	73	234	848	953	967	72
75°	54	144	465	511	513	56
85°	19	44	115	127	129	20
90°	15	42	113	56	56	13
95°	142	558	1856	957	651	158
105°	510	773	3131	4754	4435	541
115°	906	1101	2508	5003	5711	895
125°	1261	1414	2281	3855	4548	1119
135°	1503	1654	2210	3112	3529	1163
145°	1743	1854	2182	2655	2863	1092
155°	1970	2025	2182	2396	2465	905
165°	2126	2154	2182	2268	2296	600
175°	2210	2210	2197	2225	2225	210
180°	2210	2210	2210	2210	2210	

TEST NUMBER: P937901

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6	597.6
2.5°	597.6	597.6	601.5	603.4	607.2	609.1	613.0	616.8	628.4	630.3	634.1
5°	582.3	589.9	614.9	624.5	651.4	687.9	703.3	728.3	780.1	795.5	805.2
7.5°	559.2	576.4	637.9	653.3	720.6	816.7	857.0	910.9	993.5	1033.8	1066.4
10°	522.7	559.2	668.7	705.3	814.7	960.8	1035.7	1110.7	1235.6	1291.4	1312.5
12.5°	482.3	541.9	701.4	751.3	908.9	1122.2	1212.6	1295.2	1437.4	1512.3	1523.8
15°	436.2	516.9	732.1	805.2	1008.9	1256.7	1356.7	1458.5	1591.1	1644.9	1658.4
17.5°	395.8	497.7	760.9	837.8	1085.7	1377.8	1479.6	1564.2	1671.8	1708.3	1717.9
20°	345.9	467.0	780.1	880.1	1166.4	1466.2	1564.2	1629.5	1702.6	1725.6	1729.4
22.5°	309.4	434.2	791.7	895.5	1220.2	1520.0	1602.6	1654.5	1704.5	1712.1	1714.0
25°	278.7	397.8	789.8	912.8	1266.3	1552.6	1616.1	1654.5	1683.3	1687.2	1687.2
27.5°	249.8	357.5	782.0	916.6	1300.9	1560.4	1610.3	1637.2	1650.6	1658.4	1658.4
30°	224.8	319.0	762.9	908.9	1316.3	1552.6	1593.0	1606.5	1619.9	1631.4	1637.2
32.5°	205.6	282.5	734.0	893.5	1318.2	1533.4	1562.3	1569.9	1589.1	1616.1	1625.7
35°	188.3	246.0	701.4	872.4	1306.7	1502.7	1521.9	1529.6	1568.0	1608.4	1621.8
37.5°	171.0	219.1	659.1	835.9	1289.3	1466.2	1479.6	1493.0	1552.6	1600.7	1616.1
40°	153.8	196.0	609.1	795.5	1262.5	1422.0	1433.6	1454.7	1533.4	1589.1	1604.5
42.5°	140.3	176.8	555.3	753.3	1227.9	1372.0	1389.3	1420.1	1510.3	1569.9	1587.2
45°	128.7	157.6	497.7	695.6	1183.7	1320.1	1345.1	1387.4	1483.5	1541.1	1556.5
47.5°	117.2	144.1	438.2	636.0	1135.7	1268.2	1300.9	1348.9	1446.9	1502.7	1516.2
50°	107.6	130.6	378.6	572.6	1083.7	1212.6	1251.0	1300.9	1400.9	1452.7	1470.0
52.5°	99.9	119.2	322.8	509.2	1024.2	1154.9	1199.1	1251.0	1345.1	1395.1	1406.6
55°	92.3	109.5	274.8	442.0	962.7	1093.4	1141.4	1191.4	1283.6	1325.9	1333.6
57.5°	88.4	101.8	234.5	378.6	897.4	1024.2	1078.0	1124.1	1210.6	1243.3	1251.0
60°	82.6	96.1	203.7	324.8	826.3	958.9	1005.0	1051.1	1124.1	1151.1	1156.8
62.5°	76.9	92.3	180.6	272.8	753.3	882.0	928.2	970.4	1031.9	1051.1	1058.8
65°	73.1	88.4	163.3	234.5	678.3	801.3	847.5	883.9	933.9	953.1	956.9
67.5°	69.1	84.5	149.8	201.8	603.4	720.6	755.2	789.8	828.2	847.5	849.4
70°	63.4	80.7	138.4	178.7	526.5	628.4	657.2	693.7	724.5	734.0	739.8
72.5°	59.6	75.0	130.6	161.4	447.7	540.0	566.9	588.0	614.9	624.5	624.5
75°	53.8	67.2	123.0	144.1	367.0	442.0	465.0	486.2	507.3	511.1	505.4
77.5°	48.0	59.6	105.7	121.1	286.3	349.7	368.9	380.5	397.8	401.6	403.5
80°	40.4	51.9	82.6	94.2	207.5	257.5	270.9	280.6	296.0	296.0	299.8
82.5°	30.8	40.4	59.6	67.2	140.3	176.8	188.3	194.1	203.7	203.7	203.7
85°	19.2	25.0	38.4	44.2	84.5	107.6	115.3	117.2	124.9	126.8	126.8
87.5°	9.6	13.5	25.0	26.9	44.2	55.8	55.8	59.6	59.6	57.7	55.8
90°	14.8	26.6	38.6	41.5	65.2	96.8	112.7	100.2	75.2	56.3	56.3
92.5°	59.3	160.2	261.1	286.3	402.5	557.4	634.9	556.4	399.5	281.8	270.6
95°	142.4	327.0	511.6	557.7	990.3	1567.3	1855.7	1655.9	1256.4	956.8	922.8
97.5°	246.2	409.0	571.9	612.6	1334.0	2295.9	2776.9	2650.6	2398.1	2208.7	2144.1
100°	326.3	474.1	621.7	658.7	1459.1	2526.5	3060.2	3069.5	3087.9	3101.7	3024.8
102.5°	394.6	532.4	670.1	704.6	1516.5	2599.0	3140.3	3301.1	3622.9	3864.2	3798.3
105°	510.3	627.0	743.7	772.9	1559.0	2607.2	3131.3	3492.0	4213.3	4754.2	4718.8
107.5°	629.0	737.7	846.5	873.7	1567.0	2491.3	2953.4	3456.4	4462.4	5217.0	5225.6
110°	709.1	807.3	905.5	930.1	1555.0	2388.4	2805.0	3367.4	4492.1	5335.7	5372.6

TEST NUMBER: P937901

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	787.7	881.3	974.9	998.3	1555.5	2298.6	2670.1	3245.7	4396.7	5260.0	5316.8
115°	906.3	992.6	1079.1	1100.6	1569.9	2195.5	2508.4	3062.9	4171.7	5003.4	5082.0
117.5°	1023.6	1102.0	1180.5	1200.1	1599.1	2131.1	2397.1	2897.6	3898.3	4648.8	4736.0
120°	1091.8	1165.6	1239.5	1257.9	1622.8	2109.4	2352.6	2809.9	3724.3	4410.1	4494.8
122.5°	1158.5	1233.0	1307.5	1326.1	1656.9	2098.0	2318.5	2730.2	3553.7	4171.2	4254.8
125°	1260.9	1328.8	1396.7	1413.7	1703.0	2088.6	2281.4	2631.1	3330.7	3855.2	3932.2
127.5°	1344.0	1412.5	1481.1	1498.2	1748.9	2083.1	2250.3	2550.5	3151.1	3601.6	3666.5
130°	1388.5	1462.3	1536.1	1554.5	1782.5	2086.5	2238.4	2505.7	3040.4	3441.4	3501.4
132.5°	1434.4	1508.2	1582.1	1600.6	1809.7	2088.6	2228.0	2467.3	2946.0	3305.0	3358.7
135°	1502.7	1569.9	1637.2	1654.0	1839.4	2086.7	2210.3	2410.7	2811.5	3112.2	3158.5
137.5°	1572.4	1639.0	1705.5	1722.2	1883.8	2099.5	2207.3	2376.7	2715.5	2969.7	3007.6
140°	1630.2	1691.5	1752.8	1768.2	1911.1	2101.6	2196.9	2343.2	2635.9	2855.4	2890.9
142.5°	1674.7	1731.4	1788.1	1802.3	1933.8	2109.2	2196.9	2325.4	2582.6	2775.4	2805.9
145°	1743.0	1792.4	1841.9	1854.2	1963.5	2109.2	2182.1	2287.2	2497.5	2655.2	2678.3
147.5°	1811.2	1859.3	1907.4	1919.5	2007.0	2123.7	2182.1	2264.8	2430.3	2554.3	2573.4
150°	1855.7	1899.2	1942.8	1953.6	2029.8	2131.3	2182.1	2252.0	2391.7	2496.5	2511.9
152.5°	1901.7	1934.6	1967.7	1975.9	2044.7	2136.2	2182.1	2241.8	2361.0	2450.5	2462.3
155°	1969.9	1994.3	2018.7	2024.8	2077.2	2147.1	2182.1	2229.5	2324.5	2395.6	2403.4
157.5°	2020.4	2044.1	2067.9	2073.8	2109.9	2158.0	2182.1	2218.9	2292.8	2348.2	2353.6
160°	2054.5	2072.9	2091.4	2096.0	2124.7	2163.0	2182.1	2213.7	2277.0	2324.5	2327.6
162.5°	2088.6	2102.4	2116.3	2119.7	2140.5	2168.2	2182.1	2208.8	2262.2	2302.2	2305.2
165°	2125.6	2138.1	2150.7	2153.8	2163.3	2175.8	2182.1	2201.2	2239.4	2268.0	2271.2
167.5°	2159.8	2165.7	2171.7	2173.1	2181.0	2191.6	2196.9	2209.4	2234.4	2253.2	2254.6
170°	2182.1	2188.0	2193.9	2195.4	2195.8	2196.5	2196.9	2209.4	2234.4	2253.2	2253.2
172.5°	2193.9	2195.3	2196.6	2196.9	2196.9	2196.9	2196.9	2206.8	2226.6	2241.4	2240.2
175°	2210.3	2210.3	2210.3	2210.3	2205.8	2199.8	2196.9	2203.2	2215.7	2225.1	2225.1
177.5°	2210.3	2210.3	2210.3	2210.3	2206.8	2202.1	2199.8	2204.8	2214.6	2222.1	2220.8
180°	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3	2210.3

TEST NUMBER: P937901

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	597.6	597.6
2.5°	637.9	634.1
5°	820.5	824.4
7.5°	1104.9	1103.0
10°	1374.0	1391.2
12.5°	1569.9	1573.7
15°	1689.1	1696.7
17.5°	1735.2	1737.1
20°	1737.1	1733.3
22.5°	1715.9	1712.1
25°	1691.0	1689.1
27.5°	1667.9	1669.9
30°	1658.4	1664.1
32.5°	1658.4	1667.9
35°	1662.2	1671.8
37.5°	1660.3	1671.8
40°	1652.5	1666.0
42.5°	1631.4	1641.1
45°	1598.8	1610.3
47.5°	1556.5	1564.2
50°	1502.7	1510.3
52.5°	1435.5	1437.4
55°	1354.8	1362.4
57.5°	1268.2	1270.1
60°	1172.2	1177.9
62.5°	1070.4	1070.4
65°	962.7	966.6
67.5°	851.3	860.8
70°	737.9	739.8
72.5°	626.5	626.5
75°	511.1	513.0
77.5°	401.6	401.6
80°	297.9	299.8
82.5°	205.6	209.4
85°	128.7	128.7
87.5°	59.6	53.8
90°	56.3	56.3
92.5°	225.8	181.0
95°	787.0	651.2
97.5°	1885.6	1627.2
100°	2716.9	2409.0
102.5°	3534.6	3270.9
105°	4577.0	4435.3
107.5°	5259.9	5294.1
110°	5520.3	5667.9

TEST NUMBER: P937901

CATALOG NUMBER: SQ4-FB-125U-050D-B40-1D-UNV-W2A-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	5543.5	5770.3
115°	5396.5	5711.0
117.5°	5084.8	5433.6
120°	4833.6	5172.5
122.5°	4589.1	4923.3
125°	4240.1	4548.0
127.5°	3926.3	4186.1
130°	3741.4	3981.4
132.5°	3573.6	3788.5
135°	3343.6	3528.9
137.5°	3159.2	3310.9
140°	3032.7	3174.4
142.5°	2927.8	3049.8
145°	2770.6	2862.9
147.5°	2649.9	2726.4
150°	2574.0	2636.0
152.5°	2509.1	2555.9
155°	2434.4	2465.3
157.5°	2375.4	2397.1
160°	2340.1	2352.6
162.5°	2317.0	2328.9
165°	2283.7	2296.3
167.5°	2259.8	2265.1
170°	2253.2	2253.2
172.5°	2235.6	2231.0
175°	2225.1	2225.1
177.5°	2215.5	2210.3
180°	2210.3	2210.3

(END OF REPORT)